

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333736

Luminaire Tested: **S125RDIW-S1270D1560U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333736  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1560U835-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 11160.0 lumens  
Efficiency: N/A  
Efficacy: 134.6 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



56% Up

44% Dn



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44																				
1	97	93	89	86	89	85	82	79	71	69	66	58	56	55	45	44	44	38																				
2	88	81	75	71	81	75	70	65	62	59	56	51	48	46	40	39	37	32																				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28																				
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24																				
5	68	57	49	43	62	52	45	40	44	39	35	36	33	30	29	27	24	21																				
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19																				
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17																				
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17	15																				
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13																				
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12264	12264	12264	12264
5°	14110	12280	10845	12280
10°	16184	12218	9569	12218
15°	17481	12092	8506	12092
20°	19276	11947	7854	11947
25°	22308	11754	7288	11754
30°	24276	11551	6918	11551
35°	20478	11315	6576	11315
40°	14300	10890	6283	10890
45°	10609	10316	5994	10316
50°	8459	9720	5749	9720
55°	7179	8979	5530	8979
60°	6203	8317	5176	8317
65°	5527	7600	4455	7600
70°	4857	6962	4062	6962
75°	4202	6029	3813	6029
80°	3187	5073	3187	5073
85°	2660	3987	3001	3987



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.1	1.6
10°-20°	533.6	4.8
20°-30°	846.1	7.6
30°-40°	1020.3	9.1
40°-50°	911.2	8.2
50°-60°	698.8	6.3
60°-70°	454.1	4.1
70°-80°	220.8	2.0
80°-90°	56.9	0.5
90°-100°	73.8	0.7
100°-110°	454.8	4.1
110°-120°	824.9	7.4
120°-130°	1058.6	9.5
130°-140°	1138.6	10.2
140°-150°	1068.8	9.6
150°-160°	864.5	7.7
160°-170°	559.1	5.0
170°-180°	192.9	1.7
0°-30°	1561.8	14.0
0°-40°	2582.2	23.1
0°-60°	4192.1	37.6
0°-90°	4923.9	44.1
90°-120°	1353.5	12.1
90°-150°	4619.5	41.4
90°-180°	6236.0	55.9
0°-180°	11160.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2176	1894	1673	1894	2176	217
15°	2614	1808	1272	1808	2614	749
25°	3130	1649	1023	1649	3130	1437
35°	2597	1435	834	1435	2597	1569
45°	1162	1130	656	1130	1162	927
55°	638	797	491	797	638	579
65°	362	497	292	497	362	360
75°	168	242	153	242	168	179
85°	36	54	40	54	36	42
90°	36	2	36	2	36	17
95°	32	86	32	86	32	26
105°	447	443	447	443	447	404
115°	825	831	825	831	825	819
125°	1182	1182	1182	1182	1182	1051
135°	1468	1474	1468	1474	1468	1133
145°	1704	1709	1704	1709	1704	1064
155°	1868	1882	1868	1882	1868	861
165°	1975	1986	1975	1986	1975	557
175°	2022	2031	2022	2031	2022	192
180°	2031	2031	2031	2031	2031	



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1997.4	1996.2	1998.7	1991.8	1992.4	1981.8	1981.8	1973.7	1963.1	1955.0	1951.3
5°	2176.4	2178.0	2174.8	2163.1	2155.4	2143.7	2130.4	2107.0	2087.5	2068.8	2054.0
7.5°	2360.7	2361.8	2351.5	2347.9	2328.2	2313.9	2284.4	2252.6	2224.4	2188.6	2161.1
10°	2467.9	2467.2	2456.2	2447.7	2430.5	2408.7	2379.9	2342.4	2307.4	2268.4	2231.0
12.5°	2530.3	2528.3	2524.8	2514.4	2498.5	2479.2	2454.7	2417.9	2374.7	2332.0	2288.3
15°	2614.5	2609.0	2598.9	2585.6	2563.0	2540.4	2513.1	2480.4	2439.1	2390.8	2350.2
17.5°	2718.6	2718.8	2703.2	2684.8	2654.1	2614.2	2572.1	2519.2	2463.1	2409.9	2366.8
20°	2804.7	2802.3	2786.8	2750.9	2715.8	2665.9	2617.6	2552.9	2484.3	2414.9	2361.1
22.5°	2928.2	2922.1	2905.9	2858.8	2804.4	2740.1	2666.2	2587.2	2504.3	2425.5	2354.9
25°	3130.5	3125.8	3093.9	3039.3	2962.9	2863.9	2767.3	2658.9	2539.7	2436.0	2350.2
27.5°	3269.0	3263.8	3240.1	3194.8	3124.3	3020.1	2889.3	2744.5	2595.6	2453.0	2329.3
30°	3255.2	3266.9	3263.8	3242.8	3189.8	3096.2	2975.4	2812.5	2635.5	2467.9	2320.6
32.5°	3059.4	3069.9	3097.3	3138.6	3141.7	3104.3	3014.1	2863.6	2680.4	2489.8	2313.7
35°	2597.3	2611.4	2664.4	2747.8	2856.9	2948.1	2966.8	2885.8	2721.3	2516.3	2303.5
37.5°	1996.8	2073.5	2118.1	2205.9	2370.8	2538.6	2699.9	2759.3	2689.3	2505.4	2286.8
40°	1696.2	1714.9	1794.4	1893.4	2032.2	2206.8	2436.8	2602.8	2608.2	2480.4	2260.6
42.5°	1451.8	1475.5	1530.0	1609.1	1727.9	1902.5	2139.9	2359.0	2460.5	2411.8	2226.3
45°	1161.5	1179.4	1219.2	1280.0	1371.2	1515.4	1719.6	1972.9	2174.1	2252.8	2134.3
47.5°	954.1	963.8	998.4	1044.7	1112.2	1217.3	1375.4	1595.3	1836.5	2005.7	1989.0
50°	841.9	852.8	879.3	914.4	971.3	1060.1	1186.4	1369.6	1618.3	1824.8	1866.2
52.5°	754.6	763.6	780.1	813.3	860.3	928.6	1030.5	1196.2	1420.0	1639.6	1735.2
55°	637.6	643.9	657.1	675.8	713.3	762.4	850.4	965.0	1145.9	1367.3	1507.6
57.5°	541.3	544.4	552.8	570.1	596.0	631.9	695.5	792.6	922.3	1121.7	1276.5
60°	480.2	483.3	494.2	505.9	526.2	558.9	608.8	676.6	801.3	965.8	1122.5
62.5°	431.5	433.4	438.1	449.8	467.6	492.8	532.1	587.4	686.6	831.1	979.1
65°	361.7	362.5	364.0	373.4	384.3	403.0	428.7	467.7	542.5	651.7	782.6
67.5°	294.7	295.7	301.2	304.5	315.9	325.7	340.8	370.6	423.3	496.9	598.7
70°	257.2	256.5	261.9	265.8	269.7	281.4	291.5	315.7	348.4	404.6	489.5
72.5°	222.3	220.3	222.6	224.0	229.2	237.1	247.3	262.1	287.3	326.0	391.0
75°	168.4	169.2	169.2	170.7	174.6	177.7	180.8	188.6	202.7	228.4	263.5
77.5°	118.2	116.9	120.2	120.7	123.0	126.4	129.1	132.2	138.0	148.6	166.7
80°	85.7	85.7	86.5	88.9	88.1	89.6	93.5	96.7	103.7	109.9	116.1
82.5°	65.8	65.2	65.9	66.4	66.3	67.8	69.2	69.8	72.5	75.6	80.0
85°	35.9	35.9	36.6	36.6	37.4	37.4	38.2	38.2	38.2	39.0	39.8
87.5°	20.9	20.1	19.3	19.1	19.5	20.5	19.5	18.6	18.2	17.9	18.1
90°	36.1	35.1	34.1	33.1	32.1	30.8	29.1	27.4	25.8	24.1	21.7
92.5°	33.7	33.3	32.8	32.3	31.8	30.8	29.1	27.4	25.8	24.1	22.0
95°	31.6	31.6	31.6	31.6	31.6	30.8	29.1	27.4	25.8	24.1	36.8
97.5°	31.6	31.6	31.6	31.6	31.6	36.3	45.8	55.2	64.6	74.1	99.2
100°	31.6	33.0	34.3	35.6	37.0	62.6	112.4	162.2	212.1	261.9	260.6
102.5°	189.4	212.1	234.9	257.6	280.4	296.5	305.9	315.3	324.8	334.2	333.4
105°	447.1	447.4	447.8	448.1	448.4	448.6	448.6	448.6	448.6	448.6	448.6
107.5°	563.6	564.6	565.6	566.6	567.6	568.1	568.0	568.0	567.9	567.8	567.2
110°	644.3	644.0	643.6	643.3	643.0	643.3	644.3	645.3	646.3	647.3	646.6



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	716.5	717.0	717.5	718.0	718.4	719.3	720.6	721.8	723.1	724.4	724.0
115°	824.9	826.9	828.9	831.0	833.0	834.6	836.0	837.3	838.6	840.0	839.7
117.5°	940.5	941.4	942.3	943.2	944.0	945.3	947.1	948.8	950.5	952.3	951.0
120°	1011.6	1013.3	1014.9	1016.6	1018.3	1019.5	1020.1	1020.8	1021.5	1022.1	1021.1
122.5°	1079.0	1081.0	1082.9	1084.9	1086.8	1088.1	1088.8	1089.4	1090.1	1090.8	1090.3
125°	1181.7	1182.7	1183.7	1184.7	1185.7	1186.9	1188.2	1189.6	1190.9	1192.2	1192.2
127.5°	1268.1	1270.6	1273.1	1275.5	1278.0	1279.6	1280.4	1281.1	1281.8	1282.6	1282.8
130°	1330.7	1332.4	1334.1	1335.8	1337.4	1338.8	1339.8	1340.8	1341.8	1342.8	1342.4
132.5°	1388.5	1390.2	1391.9	1393.6	1395.2	1396.2	1396.4	1396.6	1396.8	1397.0	1397.7
135°	1467.7	1469.7	1471.7	1473.7	1475.7	1477.1	1477.8	1478.4	1479.1	1479.8	1480.4
137.5°	1547.2	1548.9	1550.7	1552.4	1554.2	1555.0	1554.8	1554.7	1554.6	1554.4	1555.0
140°	1594.2	1596.2	1598.2	1600.2	1602.2	1602.9	1602.2	1601.5	1600.9	1600.2	1600.5
142.5°	1638.7	1640.7	1642.7	1644.7	1646.8	1647.7	1647.6	1647.4	1647.3	1647.2	1646.7
145°	1704.1	1706.1	1708.1	1710.1	1712.1	1712.9	1712.6	1712.3	1711.9	1711.6	1711.6
147.5°	1758.0	1760.4	1762.8	1765.2	1767.6	1768.6	1768.2	1767.8	1767.4	1767.0	1766.6
150°	1792.9	1795.6	1798.2	1800.9	1803.6	1804.6	1803.9	1803.2	1802.6	1801.9	1801.2
152.5°	1825.4	1827.8	1830.2	1832.6	1835.0	1835.9	1835.2	1834.6	1833.9	1833.2	1832.6
155°	1868.1	1870.8	1873.5	1876.2	1878.8	1879.7	1878.7	1877.7	1876.7	1875.7	1875.0
157.5°	1904.0	1906.6	1909.3	1912.0	1914.7	1915.5	1914.4	1913.3	1912.3	1911.2	1911.1
160°	1926.9	1929.5	1932.2	1934.9	1937.6	1938.2	1936.9	1935.5	1934.2	1932.9	1932.5
162.5°	1947.3	1950.3	1953.2	1956.2	1959.1	1959.6	1957.8	1955.9	1954.0	1952.1	1951.8
165°	1975.0	1977.7	1980.4	1983.1	1985.7	1986.1	1984.1	1982.0	1980.0	1978.0	1977.7
167.5°	1994.3	1997.3	2000.3	2003.3	2006.3	2006.6	2004.2	2001.8	1999.4	1997.0	1996.7
170°	2005.1	2008.1	2011.2	2014.2	2017.2	2017.3	2014.7	2012.0	2009.3	2006.6	2006.3
172.5°	2012.4	2015.4	2018.4	2021.4	2024.4	2024.7	2022.3	2019.9	2017.5	2015.1	2014.5
175°	2021.7	2024.7	2027.7	2030.7	2033.7	2033.9	2031.2	2028.5	2025.9	2023.2	2022.9
177.5°	2027.1	2029.2	2031.4	2033.5	2035.7	2035.8	2033.9	2032.1	2030.2	2028.3	2028.0
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1951.3	1946.9	1938.8	1931.3	1922.0	1913.9	1908.2	1901.4	1892.7	1882.1	1873.3
5°	2037.6	2020.5	1997.9	1978.4	1953.5	1934.0	1913.7	1894.2	1874.7	1849.8	1828.0
7.5°	2133.4	2098.0	2063.5	2020.2	1980.9	1945.8	1912.1	1878.0	1844.6	1809.2	1775.1
10°	2192.0	2149.1	2101.6	2047.0	1997.1	1949.6	1905.9	1863.0	1817.8	1778.1	1735.2
12.5°	2246.9	2191.5	2137.1	2068.2	2008.3	1950.2	1894.7	1841.2	1792.9	1741.3	1695.3
15°	2296.4	2241.9	2181.1	2096.9	2013.5	1943.3	1877.8	1808.5	1748.4	1690.8	1639.3
17.5°	2315.6	2258.4	2187.8	2106.9	2015.7	1927.4	1843.1	1767.0	1696.4	1629.2	1571.3
20°	2308.1	2252.8	2180.3	2103.1	2005.7	1913.7	1822.5	1738.3	1659.6	1588.6	1527.1
22.5°	2290.1	2232.8	2162.8	2081.3	1988.8	1891.3	1793.8	1704.0	1621.5	1548.1	1480.9
25°	2262.9	2185.0	2113.3	2033.7	1945.7	1849.0	1748.4	1649.4	1561.4	1486.5	1413.3
27.5°	2234.7	2137.4	2046.2	1967.2	1874.1	1787.9	1690.9	1589.4	1496.8	1420.6	1345.4
30°	2209.1	2100.0	1999.4	1909.8	1821.7	1739.9	1647.9	1548.9	1453.8	1375.1	1298.7
32.5°	2177.3	2061.3	1950.8	1847.4	1762.5	1681.3	1598.0	1503.4	1410.8	1329.5	1251.9
35°	2137.4	1989.3	1869.3	1759.4	1665.0	1586.3	1511.5	1435.1	1342.3	1258.1	1182.5
37.5°	2085.0	1917.0	1778.1	1658.3	1558.9	1479.8	1420.7	1350.9	1266.2	1185.6	1115.5
40°	2053.2	1864.6	1712.6	1594.1	1489.6	1406.2	1350.9	1291.7	1214.5	1138.9	1068.7
42.5°	2010.8	1816.6	1646.5	1523.0	1417.9	1337.6	1281.7	1229.9	1165.2	1094.0	1018.8
45°	1927.7	1723.5	1545.0	1412.5	1306.5	1227.7	1175.5	1129.5	1080.4	1014.9	949.4
47.5°	1819.5	1626.4	1439.6	1294.9	1191.1	1118.0	1067.3	1031.0	995.9	940.2	876.6
50°	1732.9	1546.6	1364.1	1223.8	1113.1	1043.8	996.2	967.4	935.4	884.7	831.7
52.5°	1630.6	1464.2	1285.6	1142.1	1037.7	972.7	927.0	898.2	871.8	830.5	780.0
55°	1469.4	1323.6	1159.9	1029.7	933.9	868.4	824.7	797.4	781.9	746.8	707.0
57.5°	1283.4	1178.9	1034.6	909.1	824.3	759.6	727.6	704.4	686.8	662.0	633.9
60°	1153.7	1080.4	951.0	831.7	753.8	692.2	663.4	643.9	627.5	606.5	584.6
62.5°	1022.1	968.8	856.2	753.8	682.1	630.5	603.5	585.9	567.0	552.8	531.6
65°	845.8	798.2	720.3	640.0	573.7	532.4	512.9	497.3	485.6	470.0	455.2
67.5°	657.9	638.6	584.8	529.4	481.9	445.1	428.3	417.4	403.3	394.0	383.8
70°	542.5	533.2	495.0	458.4	413.9	389.0	373.4	368.7	351.6	342.2	335.2
72.5°	440.3	435.9	413.9	388.5	357.2	335.3	321.0	315.7	304.8	297.3	292.8
75°	301.7	303.2	299.3	283.0	271.3	257.2	244.8	241.6	233.9	227.6	223.7
77.5°	190.8	198.8	199.1	198.3	193.6	185.1	179.9	177.6	169.9	167.6	166.7
80°	131.0	139.5	147.3	146.5	145.0	142.7	138.8	136.4	132.5	130.2	128.6
82.5°	87.3	95.3	101.8	106.0	105.7	103.4	100.7	99.6	98.8	97.1	96.8
85°	41.3	42.9	45.2	50.7	54.6	55.3	54.6	53.8	51.4	52.2	53.0
87.5°	18.2	17.8	17.9	17.4	16.2	18.8	20.2	20.3	19.5	18.8	18.1
90°	19.4	17.1	14.7	12.2	9.5	6.9	4.2	1.5	4.2	6.9	9.5
92.5°	19.9	17.9	15.8	15.7	17.6	19.4	21.3	23.2	21.3	19.4	17.6
95°	49.5	62.2	74.9	81.8	82.8	83.8	84.8	85.8	84.8	83.8	82.8
97.5°	124.4	149.5	174.7	186.4	184.6	182.7	180.9	179.1	180.9	182.7	184.6
100°	259.3	257.9	256.6	255.4	254.4	253.4	252.4	251.4	252.4	253.4	254.4
102.5°	332.6	331.8	331.0	329.9	328.7	327.4	326.1	324.9	326.1	327.4	328.7
105°	448.6	448.6	448.6	447.9	446.6	445.3	443.9	442.6	443.9	445.3	446.6
107.5°	566.5	565.8	565.1	564.8	564.8	564.8	564.8	564.8	564.8	564.8	564.8
110°	646.0	645.3	644.6	644.3	644.3	644.3	644.3	644.3	644.3	644.3	644.3





TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	723.6	723.2	722.8	722.2	721.4	720.6	719.8	719.0	719.8	720.6	721.4
115°	839.3	839.0	838.6	837.6	836.0	834.3	832.6	831.0	832.6	834.3	836.0
117.5°	949.7	948.5	947.2	946.6	946.7	946.7	946.8	946.9	946.8	946.7	946.7
120°	1020.1	1019.1	1018.1	1017.8	1018.1	1018.5	1018.8	1019.1	1018.8	1018.5	1018.1
122.5°	1089.8	1089.4	1088.9	1088.0	1086.8	1085.5	1084.2	1083.0	1084.2	1085.5	1086.8
125°	1192.2	1192.2	1192.2	1191.1	1188.7	1186.4	1184.0	1181.7	1184.0	1186.4	1188.7
127.5°	1283.0	1283.2	1283.4	1282.6	1281.0	1279.3	1277.6	1275.9	1277.6	1279.3	1281.0
130°	1342.1	1341.8	1341.4	1340.4	1338.8	1337.1	1335.4	1333.7	1335.4	1337.1	1338.8
132.5°	1398.4	1399.2	1399.9	1399.3	1397.4	1395.4	1393.5	1391.5	1393.5	1395.4	1397.4
135°	1481.1	1481.8	1482.4	1481.8	1479.8	1477.8	1475.7	1473.7	1475.7	1477.8	1479.8
137.5°	1555.6	1556.2	1556.8	1556.3	1554.5	1552.8	1551.0	1549.3	1551.0	1552.8	1554.5
140°	1600.9	1601.2	1601.5	1601.4	1600.7	1600.0	1599.4	1598.7	1599.4	1600.0	1600.7
142.5°	1646.2	1645.8	1645.3	1644.8	1644.4	1644.0	1643.6	1643.2	1643.6	1644.0	1644.4
145°	1711.6	1711.6	1711.6	1711.3	1710.6	1709.9	1709.2	1708.6	1709.2	1709.9	1710.6
147.5°	1766.2	1765.8	1765.4	1765.2	1765.4	1765.5	1765.6	1765.8	1765.6	1765.5	1765.4
150°	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1801.2	1800.6	1799.9
152.5°	1831.9	1831.2	1830.5	1830.9	1832.4	1833.9	1835.4	1836.8	1835.4	1833.9	1832.4
155°	1874.3	1873.7	1873.0	1873.7	1875.7	1877.7	1879.7	1881.7	1879.7	1877.7	1875.7
157.5°	1911.1	1911.0	1910.9	1911.5	1912.7	1913.9	1915.1	1916.3	1915.1	1913.9	1912.7
160°	1932.2	1931.9	1931.5	1932.4	1934.4	1936.4	1938.4	1940.4	1938.4	1936.4	1934.4
162.5°	1951.5	1951.1	1950.8	1951.6	1953.6	1955.7	1957.7	1959.7	1957.7	1955.7	1953.6
165°	1977.4	1977.0	1976.7	1977.5	1979.5	1981.5	1983.6	1985.6	1983.6	1981.5	1979.5
167.5°	1996.3	1996.0	1995.7	1996.5	1998.6	2000.7	2002.8	2004.8	2002.8	2000.7	1998.6
170°	2006.0	2005.6	2005.3	2006.3	2008.6	2011.0	2013.3	2015.7	2013.3	2011.0	2008.6
172.5°	2013.9	2013.3	2012.7	2013.5	2015.9	2018.2	2020.6	2022.9	2020.6	2018.2	2015.9
175°	2022.5	2022.2	2021.9	2022.7	2024.7	2026.7	2028.7	2030.7	2028.7	2026.7	2024.7
177.5°	2027.8	2027.5	2027.2	2027.9	2029.5	2031.1	2032.7	2034.3	2032.7	2031.1	2029.5
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1867.1	1858.4	1852.1	1839.6	1830.9	1827.2	1820.3	1818.4	1825.3	1820.3	1819.7
5°	1811.6	1789.0	1771.1	1753.1	1733.6	1721.2	1702.5	1699.3	1694.7	1687.6	1686.1
7.5°	1745.0	1715.6	1692.5	1662.9	1637.1	1616.4	1593.0	1581.9	1575.9	1566.8	1554.7
10°	1700.1	1665.0	1633.9	1604.2	1572.3	1546.6	1523.2	1505.2	1493.5	1482.6	1478.0
12.5°	1655.8	1620.1	1580.2	1544.4	1508.7	1479.8	1453.9	1442.3	1429.3	1416.5	1405.6
15°	1587.1	1539.5	1495.9	1454.6	1424.2	1393.0	1368.0	1350.9	1331.4	1326.0	1304.9
17.5°	1514.1	1467.5	1416.4	1372.9	1337.6	1303.3	1275.9	1256.4	1241.8	1221.7	1212.0
20°	1468.6	1413.3	1363.4	1323.6	1284.6	1244.1	1216.0	1199.7	1185.6	1169.3	1161.5
22.5°	1420.0	1365.9	1314.7	1268.1	1228.5	1188.6	1168.6	1151.7	1135.7	1120.6	1110.3
25°	1348.6	1294.0	1240.2	1191.9	1150.6	1121.7	1098.3	1078.8	1070.3	1055.5	1044.5
27.5°	1277.9	1219.9	1164.1	1115.9	1083.5	1055.0	1035.8	1020.4	1004.9	992.0	982.5
30°	1232.4	1173.2	1112.4	1074.2	1039.9	1012.6	991.5	976.7	965.0	953.3	946.3
32.5°	1186.9	1125.8	1071.8	1030.5	998.1	974.5	952.9	938.7	926.4	913.4	905.2
35°	1113.9	1051.6	1007.9	967.4	935.4	913.6	898.8	878.5	868.4	859.0	850.4
37.5°	1046.1	988.1	940.9	905.3	877.6	855.9	836.7	825.8	813.3	804.9	797.8
40°	996.2	943.2	900.3	862.9	842.7	818.5	800.6	786.5	777.2	766.3	758.5
42.5°	951.3	902.1	860.4	826.8	801.5	781.1	763.8	749.7	737.9	730.1	723.5
45°	887.9	838.8	798.2	767.0	743.7	724.2	706.2	699.2	683.6	674.3	671.2
47.5°	822.2	778.3	739.1	710.4	686.4	668.0	651.2	636.9	628.3	619.1	614.1
50°	778.0	735.9	699.2	671.2	647.8	627.5	611.9	602.6	590.9	582.3	576.1
52.5°	733.7	694.7	658.1	631.2	611.0	590.7	573.3	563.9	552.8	547.4	543.0
55°	670.4	629.1	597.9	571.4	550.3	531.6	515.3	505.9	498.9	493.4	491.9
57.5°	598.7	565.9	536.9	513.1	491.2	473.6	459.3	450.4	444.2	443.4	438.7
60°	551.9	522.3	495.8	470.0	451.3	435.0	422.5	412.4	406.1	405.3	403.8
62.5°	505.1	476.7	452.1	429.5	412.7	396.9	385.1	373.7	370.0	366.1	362.6
65°	435.7	410.0	389.8	371.8	353.9	340.6	329.0	321.9	313.4	308.7	300.1
67.5°	367.6	347.7	328.2	313.1	299.0	286.4	276.7	266.3	260.5	256.8	250.5
70°	322.7	307.1	287.6	271.3	260.4	250.2	242.4	230.7	226.8	223.7	220.6
72.5°	280.3	266.6	250.2	237.0	226.1	216.5	207.5	202.0	198.2	195.0	193.2
75°	220.6	207.4	193.3	184.0	176.2	168.4	163.7	159.8	158.2	157.5	154.3
77.5°	162.0	155.0	143.7	136.3	131.1	128.0	123.8	121.8	121.6	118.2	117.1
80°	123.9	120.0	110.7	107.6	103.7	100.6	98.2	94.3	90.4	88.9	86.5
82.5°	92.1	88.2	84.5	79.5	76.2	74.4	72.0	70.6	71.1	68.9	67.8
85°	49.1	45.2	43.7	42.9	41.3	42.9	42.1	41.3	40.5	39.8	40.5
87.5°	18.0	18.5	18.4	20.1	18.7	19.8	20.1	19.8	20.2	20.5	20.1
90°	12.2	14.7	17.1	19.4	21.7	24.1	25.8	27.4	29.1	30.8	32.1
92.5°	15.7	15.8	17.9	19.9	22.0	24.1	25.8	27.4	29.1	30.8	31.8
95°	81.8	74.9	62.2	49.5	36.8	24.1	25.8	27.4	29.1	30.8	31.6
97.5°	186.4	174.7	149.5	124.4	99.2	74.1	64.6	55.2	45.8	36.3	31.6
100°	255.4	256.6	257.9	259.3	260.6	261.9	212.1	162.2	112.4	62.6	37.0
102.5°	329.9	331.0	331.8	332.6	333.4	334.2	324.8	315.3	305.9	296.5	280.4
105°	447.9	448.6	448.6	448.6	448.6	448.6	448.6	448.6	448.6	448.6	448.4
107.5°	564.8	565.1	565.8	566.5	567.2	567.8	567.9	568.0	568.0	568.1	567.6
110°	644.3	644.6	645.3	646.0	646.6	647.3	646.3	645.3	644.3	643.3	643.0



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	722.2	722.8	723.2	723.6	724.0	724.4	723.1	721.8	720.6	719.3	718.4
115°	837.6	838.6	839.0	839.3	839.7	840.0	838.6	837.3	836.0	834.6	833.0
117.5°	946.6	947.2	948.5	949.7	951.0	952.3	950.5	948.8	947.1	945.3	944.0
120°	1017.8	1018.1	1019.1	1020.1	1021.1	1022.1	1021.5	1020.8	1020.1	1019.5	1018.3
122.5°	1088.0	1088.9	1089.4	1089.8	1090.3	1090.8	1090.1	1089.4	1088.8	1088.1	1086.8
125°	1191.1	1192.2	1192.2	1192.2	1192.2	1192.2	1190.9	1189.6	1188.2	1186.9	1185.7
127.5°	1282.6	1283.4	1283.2	1283.0	1282.8	1282.6	1281.8	1281.1	1280.4	1279.6	1278.0
130°	1340.4	1341.4	1341.8	1342.1	1342.4	1342.8	1341.8	1340.8	1339.8	1338.8	1337.4
132.5°	1399.3	1399.9	1399.2	1398.4	1397.7	1397.0	1396.8	1396.6	1396.4	1396.2	1395.2
135°	1481.8	1482.4	1481.8	1481.1	1480.4	1479.8	1479.1	1478.4	1477.8	1477.1	1475.7
137.5°	1556.3	1556.8	1556.2	1555.6	1555.0	1554.4	1554.6	1554.7	1554.8	1555.0	1554.2
140°	1601.4	1601.5	1601.2	1600.9	1600.5	1600.2	1600.9	1601.5	1602.2	1602.9	1602.2
142.5°	1644.8	1645.3	1645.8	1646.2	1646.7	1647.2	1647.3	1647.4	1647.6	1647.7	1646.8
145°	1711.3	1711.6	1711.6	1711.6	1711.6	1711.6	1711.9	1712.3	1712.6	1712.9	1712.1
147.5°	1765.2	1765.4	1765.8	1766.2	1766.6	1767.0	1767.4	1767.8	1768.2	1768.6	1767.6
150°	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1802.6	1803.2	1803.9	1804.6	1803.6
152.5°	1830.9	1830.5	1831.2	1831.9	1832.6	1833.2	1833.9	1834.6	1835.2	1835.9	1835.0
155°	1873.7	1873.0	1873.7	1874.3	1875.0	1875.7	1876.7	1877.7	1878.7	1879.7	1878.8
157.5°	1911.5	1910.9	1911.0	1911.1	1911.1	1911.2	1912.3	1913.3	1914.4	1915.5	1914.7
160°	1932.4	1931.5	1931.9	1932.2	1932.5	1932.9	1934.2	1935.5	1936.9	1938.2	1937.6
162.5°	1951.6	1950.8	1951.1	1951.5	1951.8	1952.1	1954.0	1955.9	1957.8	1959.6	1959.1
165°	1977.5	1976.7	1977.0	1977.4	1977.7	1978.0	1980.0	1982.0	1984.1	1986.1	1985.7
167.5°	1996.5	1995.7	1996.0	1996.3	1996.7	1997.0	1999.4	2001.8	2004.2	2006.6	2006.3
170°	2006.3	2005.3	2005.6	2006.0	2006.3	2006.6	2009.3	2012.0	2014.7	2017.3	2017.2
172.5°	2013.5	2012.7	2013.3	2013.9	2014.5	2015.1	2017.5	2019.9	2022.3	2024.7	2024.4
175°	2022.7	2021.9	2022.2	2022.5	2022.9	2023.2	2025.9	2028.5	2031.2	2033.9	2033.7
177.5°	2027.9	2027.2	2027.5	2027.8	2028.0	2028.3	2030.2	2032.1	2033.9	2035.8	2035.7
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1819.1	1812.2	1810.3	1812.8	1810.3	1812.2	1819.1	1819.7	1820.3	1825.3	1818.4
5°	1678.3	1670.5	1674.4	1672.8	1674.4	1670.5	1678.3	1686.1	1687.6	1694.7	1699.3
7.5°	1554.5	1544.8	1534.5	1537.8	1534.5	1544.8	1554.5	1554.7	1566.8	1575.9	1581.9
10°	1467.8	1460.0	1455.3	1459.2	1455.3	1460.0	1467.8	1478.0	1482.6	1493.5	1505.2
12.5°	1394.9	1390.2	1386.1	1384.4	1386.1	1390.2	1394.9	1405.6	1416.5	1429.3	1442.3
15°	1295.5	1286.2	1282.3	1272.2	1282.3	1286.2	1295.5	1304.9	1326.0	1331.4	1350.9
17.5°	1204.0	1200.9	1190.8	1186.4	1190.8	1200.9	1204.0	1212.0	1221.7	1241.8	1256.4
20°	1149.8	1146.7	1136.5	1142.8	1136.5	1146.7	1149.8	1161.5	1169.3	1185.6	1199.7
22.5°	1104.9	1098.0	1094.7	1092.9	1094.7	1098.0	1104.9	1110.3	1120.6	1135.7	1151.7
25°	1041.4	1031.3	1027.4	1022.7	1027.4	1031.3	1041.4	1044.5	1055.5	1070.3	1078.8
27.5°	978.1	972.7	967.5	966.3	967.5	972.7	978.1	982.5	992.0	1004.9	1020.4
30°	937.0	931.5	927.6	927.6	927.6	931.5	937.0	946.3	953.3	965.0	976.7
32.5°	900.2	896.0	892.1	891.5	892.1	896.0	900.2	905.2	913.4	926.4	938.7
35°	846.6	840.3	838.8	834.1	838.8	840.3	846.6	850.4	859.0	868.4	878.5
37.5°	790.9	785.7	785.6	785.1	785.6	785.7	790.9	797.8	804.9	813.3	825.8
40°	755.3	751.4	750.7	745.2	750.7	751.4	755.3	758.5	766.3	777.2	786.5
42.5°	717.3	715.3	712.6	710.3	712.6	715.3	717.3	723.5	730.1	737.9	749.7
45°	665.7	660.2	660.2	656.3	660.2	660.2	665.7	671.2	674.3	683.6	699.2
47.5°	612.4	608.2	608.6	604.6	608.6	608.2	612.4	614.1	619.1	628.3	636.9
50°	576.8	574.5	573.7	572.2	573.7	574.5	576.8	576.1	582.3	590.9	602.6
52.5°	541.3	540.2	543.2	539.7	543.2	540.2	541.3	543.0	547.4	552.8	563.9
55°	493.4	491.1	495.8	491.1	495.8	491.1	493.4	491.9	493.4	498.9	505.9
57.5°	438.4	436.2	440.4	438.1	440.4	436.2	438.4	438.7	443.4	444.2	450.4
60°	402.2	397.6	399.9	400.7	399.9	397.6	402.2	403.8	405.3	406.1	412.4
62.5°	359.2	356.4	358.1	354.5	358.1	356.4	359.2	362.6	366.1	370.0	373.7
65°	298.6	296.2	293.1	291.5	293.1	296.2	298.6	300.1	308.7	313.4	321.9
67.5°	250.8	245.2	245.1	246.3	245.1	245.2	250.8	250.5	256.8	260.5	266.3
70°	215.9	215.9	215.1	215.1	215.1	215.9	215.9	220.6	223.7	226.8	230.7
72.5°	191.6	191.0	189.6	189.0	189.6	191.0	191.6	193.2	195.0	198.2	202.0
75°	154.3	155.1	153.6	152.8	153.6	155.1	154.3	154.3	157.5	158.2	159.8
77.5°	114.0	110.7	112.4	110.7	112.4	110.7	114.0	117.1	118.2	121.6	121.8
80°	86.5	85.7	88.1	85.7	88.1	85.7	86.5	86.5	88.9	90.4	94.3
82.5°	68.4	67.7	68.8	67.0	68.8	67.7	68.4	67.8	68.9	71.1	70.6
85°	41.3	40.5	39.8	40.5	39.8	40.5	41.3	40.5	39.8	40.5	41.3
87.5°	21.0	20.5	20.7	20.9	20.7	20.5	21.0	20.1	20.5	20.2	19.8
90°	33.1	34.1	35.1	36.1	35.1	34.1	33.1	32.1	30.8	29.1	27.4
92.5°	32.3	32.8	33.3	33.7	33.3	32.8	32.3	31.8	30.8	29.1	27.4
95°	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	30.8	29.1	27.4
97.5°	31.6	31.6	31.6	31.6	31.6	31.6	31.6	31.6	36.3	45.8	55.2
100°	35.6	34.3	33.0	31.6	33.0	34.3	35.6	37.0	62.6	112.4	162.2
102.5°	257.6	234.9	212.1	189.4	212.1	234.9	257.6	280.4	296.5	305.9	315.3
105°	448.1	447.8	447.4	447.1	447.4	447.8	448.1	448.4	448.6	448.6	448.6
107.5°	566.6	565.6	564.6	563.6	564.6	565.6	566.6	567.6	568.1	568.0	568.0
110°	643.3	643.6	644.0	644.3	644.0	643.6	643.3	643.0	643.3	644.3	645.3



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	718.0	717.5	717.0	716.5	717.0	717.5	718.0	718.4	719.3	720.6	721.8
115°	831.0	828.9	826.9	824.9	826.9	828.9	831.0	833.0	834.6	836.0	837.3
117.5°	943.2	942.3	941.4	940.5	941.4	942.3	943.2	944.0	945.3	947.1	948.8
120°	1016.6	1014.9	1013.3	1011.6	1013.3	1014.9	1016.6	1018.3	1019.5	1020.1	1020.8
122.5°	1084.9	1082.9	1081.0	1079.0	1081.0	1082.9	1084.9	1086.8	1088.1	1088.8	1089.4
125°	1184.7	1183.7	1182.7	1181.7	1182.7	1183.7	1184.7	1185.7	1186.9	1188.2	1189.6
127.5°	1275.5	1273.1	1270.6	1268.1	1270.6	1273.1	1275.5	1278.0	1279.6	1280.4	1281.1
130°	1335.8	1334.1	1332.4	1330.7	1332.4	1334.1	1335.8	1337.4	1338.8	1339.8	1340.8
132.5°	1393.6	1391.9	1390.2	1388.5	1390.2	1391.9	1393.6	1395.2	1396.2	1396.4	1396.6
135°	1473.7	1471.7	1469.7	1467.7	1469.7	1471.7	1473.7	1475.7	1477.1	1477.8	1478.4
137.5°	1552.4	1550.7	1548.9	1547.2	1548.9	1550.7	1552.4	1554.2	1555.0	1554.8	1554.7
140°	1600.2	1598.2	1596.2	1594.2	1596.2	1598.2	1600.2	1602.2	1602.9	1602.2	1601.5
142.5°	1644.7	1642.7	1640.7	1638.7	1640.7	1642.7	1644.7	1646.8	1647.7	1647.6	1647.4
145°	1710.1	1708.1	1706.1	1704.1	1706.1	1708.1	1710.1	1712.1	1712.9	1712.6	1712.3
147.5°	1765.2	1762.8	1760.4	1758.0	1760.4	1762.8	1765.2	1767.6	1768.6	1768.2	1767.8
150°	1800.9	1798.2	1795.6	1792.9	1795.6	1798.2	1800.9	1803.6	1804.6	1803.9	1803.2
152.5°	1832.6	1830.2	1827.8	1825.4	1827.8	1830.2	1832.6	1835.0	1835.9	1835.2	1834.6
155°	1876.2	1873.5	1870.8	1868.1	1870.8	1873.5	1876.2	1878.8	1879.7	1878.7	1877.7
157.5°	1912.0	1909.3	1906.6	1904.0	1906.6	1909.3	1912.0	1914.7	1915.5	1914.4	1913.3
160°	1934.9	1932.2	1929.5	1926.9	1929.5	1932.2	1934.9	1937.6	1938.2	1936.9	1935.5
162.5°	1956.2	1953.2	1950.3	1947.3	1950.3	1953.2	1956.2	1959.1	1959.6	1957.8	1955.9
165°	1983.1	1980.4	1977.7	1975.0	1977.7	1980.4	1983.1	1985.7	1986.1	1984.1	1982.0
167.5°	2003.3	2000.3	1997.3	1994.3	1997.3	2000.3	2003.3	2006.3	2006.6	2004.2	2001.8
170°	2014.2	2011.2	2008.1	2005.1	2008.1	2011.2	2014.2	2017.2	2017.3	2014.7	2012.0
172.5°	2021.4	2018.4	2015.4	2012.4	2015.4	2018.4	2021.4	2024.4	2024.7	2022.3	2019.9
175°	2030.7	2027.7	2024.7	2021.7	2024.7	2027.7	2030.7	2033.7	2033.9	2031.2	2028.5
177.5°	2033.5	2031.4	2029.2	2027.1	2029.2	2031.4	2033.5	2035.7	2035.8	2033.9	2032.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1820.3	1827.2	1830.9	1839.6	1852.1	1858.4	1867.1	1873.3	1882.1	1892.7	1901.4
5°	1702.5	1721.2	1733.6	1753.1	1771.1	1789.0	1811.6	1828.0	1849.8	1874.7	1894.2
7.5°	1593.0	1616.4	1637.1	1662.9	1692.5	1715.6	1745.0	1775.1	1809.2	1844.6	1878.0
10°	1523.2	1546.6	1572.3	1604.2	1633.9	1665.0	1700.1	1735.2	1778.1	1817.8	1863.0
12.5°	1453.9	1479.8	1508.7	1544.4	1580.2	1620.1	1655.8	1695.3	1741.3	1792.9	1841.2
15°	1368.0	1393.0	1424.2	1454.6	1495.9	1539.5	1587.1	1639.3	1690.8	1748.4	1808.5
17.5°	1275.9	1303.3	1337.6	1372.9	1416.4	1467.5	1514.1	1571.3	1629.2	1696.4	1767.0
20°	1216.0	1244.1	1284.6	1323.6	1363.4	1413.3	1468.6	1527.1	1588.6	1659.6	1738.3
22.5°	1168.6	1188.6	1228.5	1268.1	1314.7	1365.9	1420.0	1480.9	1548.1	1621.5	1704.0
25°	1098.3	1121.7	1150.6	1191.9	1240.2	1294.0	1348.6	1413.3	1486.5	1561.4	1649.4
27.5°	1035.8	1055.0	1083.5	1115.9	1164.1	1219.9	1277.9	1345.4	1420.6	1496.8	1589.4
30°	991.5	1012.6	1039.9	1074.2	1112.4	1173.2	1232.4	1298.7	1375.1	1453.8	1548.9
32.5°	952.9	974.5	998.1	1030.5	1071.8	1125.8	1186.9	1251.9	1329.5	1410.8	1503.4
35°	898.8	913.6	935.4	967.4	1007.9	1051.6	1113.9	1182.5	1258.1	1342.3	1435.1
37.5°	836.7	855.9	877.6	905.3	940.9	988.1	1046.1	1115.5	1185.6	1266.2	1350.9
40°	800.6	818.5	842.7	862.9	900.3	943.2	996.2	1068.7	1138.9	1214.5	1291.7
42.5°	763.8	781.1	801.5	826.8	860.4	902.1	951.3	1018.8	1094.0	1165.2	1229.9
45°	706.2	724.2	743.7	767.0	798.2	838.8	887.9	949.4	1014.9	1080.4	1129.5
47.5°	651.2	668.0	686.4	710.4	739.1	778.3	822.2	876.6	940.2	995.9	1031.0
50°	611.9	627.5	647.8	671.2	699.2	735.9	778.0	831.7	884.7	935.4	967.4
52.5°	573.3	590.7	611.0	631.2	658.1	694.7	733.7	780.0	830.5	871.8	898.2
55°	515.3	531.6	550.3	571.4	597.9	629.1	670.4	707.0	746.8	781.9	797.4
57.5°	459.3	473.6	491.2	513.1	536.9	565.9	598.7	633.9	662.0	686.8	704.4
60°	422.5	435.0	451.3	470.0	495.8	522.3	551.9	584.6	606.5	627.5	643.9
62.5°	385.1	396.9	412.7	429.5	452.1	476.7	505.1	531.6	552.8	567.0	585.9
65°	329.0	340.6	353.9	371.8	389.8	410.0	435.7	455.2	470.0	485.6	497.3
67.5°	276.7	286.4	299.0	313.1	328.2	347.7	367.6	383.8	394.0	403.3	417.4
70°	242.4	250.2	260.4	271.3	287.6	307.1	322.7	335.2	342.2	351.6	368.7
72.5°	207.5	216.5	226.1	237.0	250.2	266.6	280.3	292.8	297.3	304.8	315.7
75°	163.7	168.4	176.2	184.0	193.3	207.4	220.6	223.7	227.6	233.9	241.6
77.5°	123.8	128.0	131.1	136.3	143.7	155.0	162.0	166.7	167.6	169.9	177.6
80°	98.2	100.6	103.7	107.6	110.7	120.0	123.9	128.6	130.2	132.5	136.4
82.5°	72.0	74.4	76.2	79.5	84.5	88.2	92.1	96.8	97.1	98.8	99.6
85°	42.1	42.9	41.3	42.9	43.7	45.2	49.1	53.0	52.2	51.4	53.8
87.5°	20.1	19.8	18.7	20.1	18.4	18.5	18.0	18.1	18.8	19.5	20.3
90°	25.8	24.1	21.7	19.4	17.1	14.7	12.2	9.5	6.9	4.2	1.5
92.5°	25.8	24.1	22.0	19.9	17.9	15.8	15.7	17.6	19.4	21.3	23.2
95°	25.8	24.1	36.8	49.5	62.2	74.9	81.8	82.8	83.8	84.8	85.8
97.5°	64.6	74.1	99.2	124.4	149.5	174.7	186.4	184.6	182.7	180.9	179.1
100°	212.1	261.9	260.6	259.3	257.9	256.6	255.4	254.4	253.4	252.4	251.4
102.5°	324.8	334.2	333.4	332.6	331.8	331.0	329.9	328.7	327.4	326.1	324.9
105°	448.6	448.6	448.6	448.6	448.6	448.6	447.9	446.6	445.3	443.9	442.6
107.5°	567.9	567.8	567.2	566.5	565.8	565.1	564.8	564.8	564.8	564.8	564.8
110°	646.3	647.3	646.6	646.0	645.3	644.6	644.3	644.3	644.3	644.3	644.3



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	723.1	724.4	724.0	723.6	723.2	722.8	722.2	721.4	720.6	719.8	719.0
115°	838.6	840.0	839.7	839.3	839.0	838.6	837.6	836.0	834.3	832.6	831.0
117.5°	950.5	952.3	951.0	949.7	948.5	947.2	946.6	946.7	946.7	946.8	946.9
120°	1021.5	1022.1	1021.1	1020.1	1019.1	1018.1	1017.8	1018.1	1018.5	1018.8	1019.1
122.5°	1090.1	1090.8	1090.3	1089.8	1089.4	1088.9	1088.0	1086.8	1085.5	1084.2	1083.0
125°	1190.9	1192.2	1192.2	1192.2	1192.2	1192.2	1191.1	1188.7	1186.4	1184.0	1181.7
127.5°	1281.8	1282.6	1282.8	1283.0	1283.2	1283.4	1282.6	1281.0	1279.3	1277.6	1275.9
130°	1341.8	1342.8	1342.4	1342.1	1341.8	1341.4	1340.4	1338.8	1337.1	1335.4	1333.7
132.5°	1396.8	1397.0	1397.7	1398.4	1399.2	1399.9	1399.3	1397.4	1395.4	1393.5	1391.5
135°	1479.1	1479.8	1480.4	1481.1	1481.8	1482.4	1481.8	1479.8	1477.8	1475.7	1473.7
137.5°	1554.6	1554.4	1555.0	1555.6	1556.2	1556.8	1556.3	1554.5	1552.8	1551.0	1549.3
140°	1600.9	1600.2	1600.5	1600.9	1601.2	1601.5	1601.4	1600.7	1600.0	1599.4	1598.7
142.5°	1647.3	1647.2	1646.7	1646.2	1645.8	1645.3	1644.8	1644.4	1644.0	1643.6	1643.2
145°	1711.9	1711.6	1711.6	1711.6	1711.6	1711.6	1711.3	1710.6	1709.9	1709.2	1708.6
147.5°	1767.4	1767.0	1766.6	1766.2	1765.8	1765.4	1765.2	1765.4	1765.5	1765.6	1765.8
150°	1802.6	1801.9	1801.2	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9
152.5°	1833.9	1833.2	1832.6	1831.9	1831.2	1830.5	1830.9	1832.4	1833.9	1835.4	1836.8
155°	1876.7	1875.7	1875.0	1874.3	1873.7	1873.0	1873.7	1875.7	1877.7	1879.7	1881.7
157.5°	1912.3	1911.2	1911.1	1911.1	1911.0	1910.9	1911.5	1912.7	1913.9	1915.1	1916.3
160°	1934.2	1932.9	1932.5	1932.2	1931.9	1931.5	1932.4	1934.4	1936.4	1938.4	1940.4
162.5°	1954.0	1952.1	1951.8	1951.5	1951.1	1950.8	1951.6	1953.6	1955.7	1957.7	1959.7
165°	1980.0	1978.0	1977.7	1977.4	1977.0	1976.7	1977.5	1979.5	1981.5	1983.6	1985.6
167.5°	1999.4	1997.0	1996.7	1996.3	1996.0	1995.7	1996.5	1998.6	2000.7	2002.8	2004.8
170°	2009.3	2006.6	2006.3	2006.0	2005.6	2005.3	2006.3	2008.6	2011.0	2013.3	2015.7
172.5°	2017.5	2015.1	2014.5	2013.9	2013.3	2012.7	2013.5	2015.9	2018.2	2020.6	2022.9
175°	2025.9	2023.2	2022.9	2022.5	2022.2	2021.9	2022.7	2024.7	2026.7	2028.7	2030.7
177.5°	2030.2	2028.3	2028.0	2027.8	2027.5	2027.2	2027.9	2029.5	2031.1	2032.7	2034.3
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1908.2	1913.9	1922.0	1931.3	1938.8	1946.9	1951.3	1951.3	1955.0	1963.1	1973.7
5°	1913.7	1934.0	1953.5	1978.4	1997.9	2020.5	2037.6	2054.0	2068.8	2087.5	2107.0
7.5°	1912.1	1945.8	1980.9	2020.2	2063.5	2098.0	2133.4	2161.1	2188.6	2224.4	2252.6
10°	1905.9	1949.6	1997.1	2047.0	2101.6	2149.1	2192.0	2231.0	2268.4	2307.4	2342.4
12.5°	1894.7	1950.2	2008.3	2068.2	2137.1	2191.5	2246.9	2288.3	2332.0	2374.7	2417.9
15°	1877.8	1943.3	2013.5	2096.9	2181.1	2241.9	2296.4	2350.2	2390.8	2439.1	2480.4
17.5°	1843.1	1927.4	2015.7	2106.9	2187.8	2258.4	2315.6	2366.8	2409.9	2463.1	2519.2
20°	1822.5	1913.7	2005.7	2103.1	2180.3	2252.8	2308.1	2361.1	2414.9	2484.3	2552.9
22.5°	1793.8	1891.3	1988.8	2081.3	2162.8	2232.8	2290.1	2354.9	2425.5	2504.3	2587.2
25°	1748.4	1849.0	1945.7	2033.7	2113.3	2185.0	2262.9	2350.2	2436.0	2539.7	2658.9
27.5°	1690.9	1787.9	1874.1	1967.2	2046.2	2137.4	2234.7	2329.3	2453.0	2595.6	2744.5
30°	1647.9	1739.9	1821.7	1909.8	1999.4	2100.0	2209.1	2320.6	2467.9	2635.5	2812.5
32.5°	1598.0	1681.3	1762.5	1847.4	1950.8	2061.3	2177.3	2313.7	2489.8	2680.4	2863.6
35°	1511.5	1586.3	1665.0	1759.4	1869.3	1989.3	2137.4	2303.5	2516.3	2721.3	2885.8
37.5°	1420.7	1479.8	1558.9	1658.3	1778.1	1917.0	2085.0	2286.8	2505.4	2689.3	2759.3
40°	1350.9	1406.2	1489.6	1594.1	1712.6	1864.6	2053.2	2260.6	2480.4	2608.2	2602.8
42.5°	1281.7	1337.6	1417.9	1523.0	1646.5	1816.6	2010.8	2226.3	2411.8	2460.5	2359.0
45°	1175.5	1227.7	1306.5	1412.5	1545.0	1723.5	1927.7	2134.3	2252.8	2174.1	1972.9
47.5°	1067.3	1118.0	1191.1	1294.9	1439.6	1626.4	1819.5	1989.0	2005.7	1836.5	1595.3
50°	996.2	1043.8	1113.1	1223.8	1364.1	1546.6	1732.9	1866.2	1824.8	1618.3	1369.6
52.5°	927.0	972.7	1037.7	1142.1	1285.6	1464.2	1630.6	1735.2	1639.6	1420.0	1196.2
55°	824.7	868.4	933.9	1029.7	1159.9	1323.6	1469.4	1507.6	1367.3	1145.9	965.0
57.5°	727.6	759.6	824.3	909.1	1034.6	1178.9	1283.4	1276.5	1121.7	922.3	792.6
60°	663.4	692.2	753.8	831.7	951.0	1080.4	1153.7	1122.5	965.8	801.3	676.6
62.5°	603.5	630.5	682.1	753.8	856.2	968.8	1022.1	979.1	831.1	686.6	587.4
65°	512.9	532.4	573.7	640.0	720.3	798.2	845.8	782.6	651.7	542.5	467.7
67.5°	428.3	445.1	481.9	529.4	584.8	638.6	657.9	598.7	496.9	423.3	370.6
70°	373.4	389.0	413.9	458.4	495.0	533.2	542.5	489.5	404.6	348.4	315.7
72.5°	321.0	335.3	357.2	388.5	413.9	435.9	440.3	391.0	326.0	287.3	262.1
75°	244.8	257.2	271.3	283.0	299.3	303.2	301.7	263.5	228.4	202.7	188.6
77.5°	179.9	185.1	193.6	198.3	199.1	198.8	190.8	166.7	148.6	138.0	132.2
80°	138.8	142.7	145.0	146.5	147.3	139.5	131.0	116.1	109.9	103.7	96.7
82.5°	100.7	103.4	105.7	106.0	101.8	95.3	87.3	80.0	75.6	72.5	69.8
85°	54.6	55.3	54.6	50.7	45.2	42.9	41.3	39.8	39.0	38.2	38.2
87.5°	20.2	18.8	16.2	17.4	17.9	17.8	18.2	18.1	17.9	18.2	18.6
90°	4.2	6.9	9.5	12.2	14.7	17.1	19.4	21.7	24.1	25.8	27.4
92.5°	21.3	19.4	17.6	15.7	15.8	17.9	19.9	22.0	24.1	25.8	27.4
95°	84.8	83.8	82.8	81.8	74.9	62.2	49.5	36.8	24.1	25.8	27.4
97.5°	180.9	182.7	184.6	186.4	174.7	149.5	124.4	99.2	74.1	64.6	55.2
100°	252.4	253.4	254.4	255.4	256.6	257.9	259.3	260.6	261.9	212.1	162.2
102.5°	326.1	327.4	328.7	329.9	331.0	331.8	332.6	333.4	334.2	324.8	315.3
105°	443.9	445.3	446.6	447.9	448.6	448.6	448.6	448.6	448.6	448.6	448.6
107.5°	564.8	564.8	564.8	564.8	565.1	565.8	566.5	567.2	567.8	567.9	568.0
110°	644.3	644.3	644.3	644.3	644.6	645.3	646.0	646.6	647.3	646.3	645.3





TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	719.8	720.6	721.4	722.2	722.8	723.2	723.6	724.0	724.4	723.1	721.8
115°	832.6	834.3	836.0	837.6	838.6	839.0	839.3	839.7	840.0	838.6	837.3
117.5°	946.8	946.7	946.7	946.6	947.2	948.5	949.7	951.0	952.3	950.5	948.8
120°	1018.8	1018.5	1018.1	1017.8	1018.1	1019.1	1020.1	1021.1	1022.1	1021.5	1020.8
122.5°	1084.2	1085.5	1086.8	1088.0	1088.9	1089.4	1089.8	1090.3	1090.8	1090.1	1089.4
125°	1184.0	1186.4	1188.7	1191.1	1192.2	1192.2	1192.2	1192.2	1192.2	1190.9	1189.6
127.5°	1277.6	1279.3	1281.0	1282.6	1283.4	1283.2	1283.0	1282.8	1282.6	1281.8	1281.1
130°	1335.4	1337.1	1338.8	1340.4	1341.4	1341.8	1342.1	1342.4	1342.8	1341.8	1340.8
132.5°	1393.5	1395.4	1397.4	1399.3	1399.9	1399.2	1398.4	1397.7	1397.0	1396.8	1396.6
135°	1475.7	1477.8	1479.8	1481.8	1482.4	1481.8	1481.1	1480.4	1479.8	1479.1	1478.4
137.5°	1551.0	1552.8	1554.5	1556.3	1556.8	1556.2	1555.6	1555.0	1554.4	1554.6	1554.7
140°	1599.4	1600.0	1600.7	1601.4	1601.5	1601.2	1600.9	1600.5	1600.2	1600.9	1601.5
142.5°	1643.6	1644.0	1644.4	1644.8	1645.3	1645.8	1646.2	1646.7	1647.2	1647.3	1647.4
145°	1709.2	1709.9	1710.6	1711.3	1711.6	1711.6	1711.6	1711.6	1711.6	1711.9	1712.3
147.5°	1765.6	1765.5	1765.4	1765.2	1765.4	1765.8	1766.2	1766.6	1767.0	1767.4	1767.8
150°	1801.2	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1802.6	1803.2
152.5°	1835.4	1833.9	1832.4	1830.9	1830.5	1831.2	1831.9	1832.6	1833.2	1833.9	1834.6
155°	1879.7	1877.7	1875.7	1873.7	1873.0	1873.7	1874.3	1875.0	1875.7	1876.7	1877.7
157.5°	1915.1	1913.9	1912.7	1911.5	1910.9	1911.0	1911.1	1911.1	1911.2	1912.3	1913.3
160°	1938.4	1936.4	1934.4	1932.4	1931.5	1931.9	1932.2	1932.5	1932.9	1934.2	1935.5
162.5°	1957.7	1955.7	1953.6	1951.6	1950.8	1951.1	1951.5	1951.8	1952.1	1954.0	1955.9
165°	1983.6	1981.5	1979.5	1977.5	1976.7	1977.0	1977.4	1977.7	1978.0	1980.0	1982.0
167.5°	2002.8	2000.7	1998.6	1996.5	1995.7	1996.0	1996.3	1996.7	1997.0	1999.4	2001.8
170°	2013.3	2011.0	2008.6	2006.3	2005.3	2005.6	2006.0	2006.3	2006.6	2009.3	2012.0
172.5°	2020.6	2018.2	2015.9	2013.5	2012.7	2013.3	2013.9	2014.5	2015.1	2017.5	2019.9
175°	2028.7	2026.7	2024.7	2022.7	2021.9	2022.2	2022.5	2022.9	2023.2	2025.9	2028.5
177.5°	2032.7	2031.1	2029.5	2027.9	2027.2	2027.5	2027.8	2028.0	2028.3	2030.2	2032.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1981.8	1981.8	1992.4	1991.8	1998.7	1996.2	1997.4
5°	2130.4	2143.7	2155.4	2163.1	2174.8	2178.0	2176.4
7.5°	2284.4	2313.9	2328.2	2347.9	2351.5	2361.8	2360.7
10°	2379.9	2408.7	2430.5	2447.7	2456.2	2467.2	2467.9
12.5°	2454.7	2479.2	2498.5	2514.4	2524.8	2528.3	2530.3
15°	2513.1	2540.4	2563.0	2585.6	2598.9	2609.0	2614.5
17.5°	2572.1	2614.2	2654.1	2684.8	2703.2	2718.8	2718.6
20°	2617.6	2665.9	2715.8	2750.9	2786.8	2802.3	2804.7
22.5°	2666.2	2740.1	2804.4	2858.8	2905.9	2922.1	2928.2
25°	2767.3	2863.9	2962.9	3039.3	3093.9	3125.8	3130.5
27.5°	2889.3	3020.1	3124.3	3194.8	3240.1	3263.8	3269.0
30°	2975.4	3096.2	3189.8	3242.8	3263.8	3266.9	3255.2
32.5°	3014.1	3104.3	3141.7	3138.6	3097.3	3069.9	3059.4
35°	2966.8	2948.1	2856.9	2747.8	2664.4	2611.4	2597.3
37.5°	2699.9	2538.6	2370.8	2205.9	2118.1	2073.5	1996.8
40°	2436.8	2206.8	2032.2	1893.4	1794.4	1714.9	1696.2
42.5°	2139.9	1902.5	1727.9	1609.1	1530.0	1475.5	1451.8
45°	1719.6	1515.4	1371.2	1280.0	1219.2	1179.4	1161.5
47.5°	1375.4	1217.3	1112.2	1044.7	998.4	963.8	954.1
50°	1186.4	1060.1	971.3	914.4	879.3	852.8	841.9
52.5°	1030.5	928.6	860.3	813.3	780.1	763.6	754.6
55°	850.4	762.4	713.3	675.8	657.1	643.9	637.6
57.5°	695.5	631.9	596.0	570.1	552.8	544.4	541.3
60°	608.8	558.9	526.2	505.9	494.2	483.3	480.2
62.5°	532.1	492.8	467.6	449.8	438.1	433.4	431.5
65°	428.7	403.0	384.3	373.4	364.0	362.5	361.7
67.5°	340.8	325.7	315.9	304.5	301.2	295.7	294.7
70°	291.5	281.4	269.7	265.8	261.9	256.5	257.2
72.5°	247.3	237.1	229.2	224.0	222.6	220.3	222.3
75°	180.8	177.7	174.6	170.7	169.2	169.2	168.4
77.5°	129.1	126.4	123.0	120.7	120.2	116.9	118.2
80°	93.5	89.6	88.1	88.9	86.5	85.7	85.7
82.5°	69.2	67.8	66.3	66.4	65.9	65.2	65.8
85°	38.2	37.4	37.4	36.6	36.6	35.9	35.9
87.5°	19.5	20.5	19.5	19.1	19.3	20.1	20.9
90°	29.1	30.8	32.1	33.1	34.1	35.1	36.1
92.5°	29.1	30.8	31.8	32.3	32.8	33.3	33.7
95°	29.1	30.8	31.6	31.6	31.6	31.6	31.6
97.5°	45.8	36.3	31.6	31.6	31.6	31.6	31.6
100°	112.4	62.6	37.0	35.6	34.3	33.0	31.6
102.5°	305.9	296.5	280.4	257.6	234.9	212.1	189.4
105°	448.6	448.6	448.4	448.1	447.8	447.4	447.1
107.5°	568.0	568.1	567.6	566.6	565.6	564.6	563.6
110°	644.3	643.3	643.0	643.3	643.6	644.0	644.3



TEST NUMBER: P333736

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	720.6	719.3	718.4	718.0	717.5	717.0	716.5
115°	836.0	834.6	833.0	831.0	828.9	826.9	824.9
117.5°	947.1	945.3	944.0	943.2	942.3	941.4	940.5
120°	1020.1	1019.5	1018.3	1016.6	1014.9	1013.3	1011.6
122.5°	1088.8	1088.1	1086.8	1084.9	1082.9	1081.0	1079.0
125°	1188.2	1186.9	1185.7	1184.7	1183.7	1182.7	1181.7
127.5°	1280.4	1279.6	1278.0	1275.5	1273.1	1270.6	1268.1
130°	1339.8	1338.8	1337.4	1335.8	1334.1	1332.4	1330.7
132.5°	1396.4	1396.2	1395.2	1393.6	1391.9	1390.2	1388.5
135°	1477.8	1477.1	1475.7	1473.7	1471.7	1469.7	1467.7
137.5°	1554.8	1555.0	1554.2	1552.4	1550.7	1548.9	1547.2
140°	1602.2	1602.9	1602.2	1600.2	1598.2	1596.2	1594.2
142.5°	1647.6	1647.7	1646.8	1644.7	1642.7	1640.7	1638.7
145°	1712.6	1712.9	1712.1	1710.1	1708.1	1706.1	1704.1
147.5°	1768.2	1768.6	1767.6	1765.2	1762.8	1760.4	1758.0
150°	1803.9	1804.6	1803.6	1800.9	1798.2	1795.6	1792.9
152.5°	1835.2	1835.9	1835.0	1832.6	1830.2	1827.8	1825.4
155°	1878.7	1879.7	1878.8	1876.2	1873.5	1870.8	1868.1
157.5°	1914.4	1915.5	1914.7	1912.0	1909.3	1906.6	1904.0
160°	1936.9	1938.2	1937.6	1934.9	1932.2	1929.5	1926.9
162.5°	1957.8	1959.6	1959.1	1956.2	1953.2	1950.3	1947.3
165°	1984.1	1986.1	1985.7	1983.1	1980.4	1977.7	1975.0
167.5°	2004.2	2006.6	2006.3	2003.3	2000.3	1997.3	1994.3
170°	2014.7	2017.3	2017.2	2014.2	2011.2	2008.1	2005.1
172.5°	2022.3	2024.7	2024.4	2021.4	2018.4	2015.4	2012.4
175°	2031.2	2033.9	2033.7	2030.7	2027.7	2024.7	2021.7
177.5°	2033.9	2035.8	2035.7	2033.5	2031.4	2029.2	2027.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7

(END OF REPORT)