

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333738

Luminaire Tested: **S125RDIW-S1270D1560U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333738  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1560U835-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11117.0 lumens  
Efficiency: N/A  
Efficacy: 134.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333738

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333738

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44					44			
1	97	92	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43	37					37			
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	37	32					32			
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27					27			
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23					23			
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20					20			
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18					18			
7	58	46	38	32	53	42	35	30	36	30	26	30	25	22	24	21	19	16					16			
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14					14			
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13					13			
10	46	35	28	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12					12			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13332	13332	13332
5°	13363	13211	13291
10°	13262	13088	13088
15°	13104	12822	12718
20°	12902	12451	12302
25°	12666	12088	11821
30°	12371	11662	11290
35°	12071	11223	10694
40°	11790	10765	10108
45°	11449	10253	9470
50°	11106	9697	8804
55°	10709	9164	8094
60°	10311	8519	7330
65°	9840	7768	6457
70°	9304	6830	5565
75°	8559	5757	4629
80°	7539	4523	3887
85°	6358	3698	3468



TEST NUMBER: P333738

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	194.1	1.7
10°-20°	542.5	4.9
20°-30°	786.6	7.1
30°-40°	896.5	8.1
40°-50°	873.9	7.9
50°-60°	735.6	6.6
60°-70°	515.6	4.6
70°-80°	265.0	2.4
80°-90°	71.2	0.6
90°-100°	73.8	0.7
100°-110°	454.8	4.1
110°-120°	824.9	7.4
120°-130°	1058.6	9.5
130°-140°	1138.6	10.2
140°-150°	1068.8	9.6
150°-160°	864.5	7.8
160°-170°	559.1	5.0
170°-180°	192.9	1.7
0°-30°	1523.2	13.7
0°-40°	2419.7	21.8
0°-60°	4029.1	36.2
0°-90°	4881.0	43.9
90°-120°	1353.5	12.2
90°-150°	4619.5	41.6
90°-180°	6236.0	56.1
0°-180°	11117.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2064	2064	2064	2064	2064	
5°	2061	2054	2038	2052	2050	195
15°	1960	1949	1918	1915	1902	552
25°	1777	1752	1696	1676	1659	817
35°	1531	1492	1424	1380	1356	958
45°	1254	1206	1123	1062	1037	967
55°	951	899	814	746	719	850
65°	644	589	508	448	422	638
75°	343	295	231	198	186	363
85°	86	59	50	48	47	96
90°	2	13	24	31	36	8
95°	86	78	24	31	32	109
105°	443	448	449	448	447	469
115°	831	838	840	834	825	823
125°	1182	1192	1192	1186	1182	1055
135°	1474	1482	1480	1476	1468	1136
145°	1709	1711	1712	1712	1704	1068
155°	1882	1873	1876	1879	1868	867
165°	1986	1977	1978	1986	1975	561
175°	2031	2022	2023	2034	2022	193
180°	2031	2031	2031	2031	2031	



TEST NUMBER: P333738

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2068.0	2067.2	2066.3	2065.5	2064.7	2062.9	2060.1	2057.3	2054.6	2051.8	2054.6
5°	2061.2	2059.8	2058.4	2057.0	2055.6	2053.0	2049.2	2045.4	2041.6	2037.8	2041.2
7.5°	2040.9	2039.6	2038.3	2036.9	2035.6	2032.7	2028.1	2023.5	2019.0	2014.4	2016.8
10°	2022.2	2021.1	2020.1	2019.1	2018.0	2015.1	2010.2	2005.4	2000.5	1995.7	1996.7
12.5°	2001.0	1999.7	1998.3	1997.0	1995.7	1991.8	1985.3	1978.8	1972.2	1965.7	1966.5
15°	1959.8	1957.7	1955.7	1953.6	1951.5	1946.8	1939.5	1932.3	1925.0	1917.7	1917.4
17.5°	1913.3	1910.2	1907.0	1903.8	1900.6	1894.4	1885.3	1876.1	1867.0	1857.8	1856.1
20°	1877.2	1873.7	1870.2	1866.8	1863.3	1856.0	1845.0	1833.9	1822.8	1811.7	1810.0
22.5°	1837.3	1833.8	1830.3	1826.9	1823.4	1815.9	1804.2	1792.6	1780.9	1769.3	1765.9
25°	1777.4	1772.2	1767.0	1761.8	1756.6	1747.6	1734.8	1722.0	1709.1	1696.3	1691.8
27.5°	1708.8	1702.5	1696.2	1689.9	1683.6	1673.6	1659.8	1646.1	1632.4	1618.7	1612.4
30°	1658.9	1652.3	1645.7	1639.2	1632.6	1622.0	1607.4	1592.9	1578.3	1563.8	1555.8
32.5°	1610.3	1602.6	1594.9	1587.2	1579.5	1568.2	1553.4	1538.6	1523.7	1508.9	1500.1
35°	1531.1	1522.7	1514.4	1506.1	1497.8	1485.8	1470.2	1454.7	1439.1	1423.5	1413.4
37.5°	1453.4	1443.3	1433.2	1423.1	1412.9	1399.8	1383.8	1367.7	1351.6	1335.5	1323.5
40°	1398.5	1388.1	1377.7	1367.3	1357.0	1343.4	1326.8	1310.2	1293.5	1276.9	1263.8
42.5°	1341.2	1330.5	1319.8	1309.1	1298.5	1284.5	1267.4	1250.2	1233.0	1215.8	1203.2
45°	1253.5	1243.5	1233.4	1223.4	1213.3	1198.8	1179.7	1160.7	1141.6	1122.6	1108.7
47.5°	1162.8	1152.2	1141.6	1131.0	1120.4	1105.5	1086.3	1067.1	1047.9	1028.7	1014.4
50°	1105.4	1094.0	1082.5	1071.1	1059.7	1044.1	1024.3	1004.6	984.8	965.1	950.5
52.5°	1043.0	1031.3	1019.6	1007.9	996.2	981.0	962.4	943.8	925.1	906.5	890.8
55°	951.1	940.0	928.9	917.8	906.7	891.5	872.1	852.7	833.3	813.9	798.3
57.5°	858.1	846.3	834.4	822.6	810.7	795.5	776.8	758.0	739.3	720.6	705.4
60°	798.3	786.1	774.0	761.9	749.8	734.3	715.6	696.9	678.2	659.5	644.3
62.5°	734.7	723.1	711.5	699.9	688.4	673.1	654.1	635.1	616.1	597.1	583.0
65°	643.9	632.1	620.4	608.6	596.8	581.7	563.4	545.0	526.6	508.3	494.4
67.5°	553.8	542.0	530.2	518.5	506.7	492.0	474.4	456.8	439.2	421.6	408.9
70°	492.7	480.9	469.1	457.3	445.6	431.0	413.7	396.4	379.0	361.7	351.0
72.5°	432.8	421.3	409.8	398.3	386.8	372.9	356.7	340.5	324.3	308.1	298.2
75°	343.0	332.6	322.2	311.8	301.4	289.0	274.4	259.9	245.3	230.7	223.1
77.5°	253.8	245.5	237.2	228.9	220.6	210.6	198.9	187.3	175.7	164.0	158.7
80°	202.7	194.4	186.1	177.7	169.4	160.4	150.7	141.0	131.3	121.6	118.5
82.5°	152.8	145.3	137.8	130.3	122.9	115.8	109.1	102.5	95.8	89.2	87.7
85°	85.8	79.5	73.3	67.0	60.8	56.8	55.1	53.4	51.6	49.9	49.5
87.5°	29.0	27.6	26.2	24.8	23.4	22.8	23.0	23.1	23.3	23.5	23.9
90°	1.5	4.2	6.9	9.5	12.2	14.7	17.1	19.4	21.7	24.1	25.8
92.5°	23.2	21.3	19.4	17.6	15.7	15.8	17.9	19.9	22.0	24.1	25.8
95°	85.8	84.8	83.8	82.8	81.8	74.9	62.2	49.5	36.8	24.1	25.8
97.5°	179.1	180.9	182.7	184.6	186.4	174.7	149.5	124.4	99.2	74.1	64.6
100°	251.4	252.4	253.4	254.4	255.4	256.6	257.9	259.3	260.6	261.9	212.1
102.5°	324.9	326.1	327.4	328.7	329.9	331.0	331.8	332.6	333.4	334.2	324.8
105°	442.6	443.9	445.3	446.6	447.9	448.6	448.6	448.6	448.6	448.6	448.6
107.5°	564.8	564.8	564.8	564.8	564.8	565.1	565.8	566.5	567.2	567.8	567.9
110°	644.3	644.3	644.3	644.3	644.3	644.6	645.3	646.0	646.6	647.3	646.3



TEST NUMBER: P333738

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	719.0	719.8	720.6	721.4	722.2	722.8	723.2	723.6	724.0	724.4	723.1
115°	831.0	832.6	834.3	836.0	837.6	838.6	839.0	839.3	839.7	840.0	838.6
117.5°	946.9	946.8	946.7	946.7	946.6	947.2	948.5	949.7	951.0	952.3	950.5
120°	1019.1	1018.8	1018.5	1018.1	1017.8	1018.1	1019.1	1020.1	1021.1	1022.1	1021.5
122.5°	1083.0	1084.2	1085.5	1086.8	1088.0	1088.9	1089.4	1089.8	1090.3	1090.8	1090.1
125°	1181.7	1184.0	1186.4	1188.7	1191.1	1192.2	1192.2	1192.2	1192.2	1192.2	1190.9
127.5°	1275.9	1277.6	1279.3	1281.0	1282.6	1283.4	1283.2	1283.0	1282.8	1282.6	1281.8
130°	1333.7	1335.4	1337.1	1338.8	1340.4	1341.4	1341.8	1342.1	1342.4	1342.8	1341.8
132.5°	1391.5	1393.5	1395.4	1397.4	1399.3	1399.9	1399.2	1398.4	1397.7	1397.0	1396.8
135°	1473.7	1475.7	1477.8	1479.8	1481.8	1482.4	1481.8	1481.1	1480.4	1479.8	1479.1
137.5°	1549.3	1551.0	1552.8	1554.5	1556.3	1556.8	1556.2	1555.6	1555.0	1554.4	1554.6
140°	1598.7	1599.4	1600.0	1600.7	1601.4	1601.5	1601.2	1600.9	1600.5	1600.2	1600.9
142.5°	1643.2	1643.6	1644.0	1644.4	1644.8	1645.3	1645.8	1646.2	1646.7	1647.2	1647.3
145°	1708.6	1709.2	1709.9	1710.6	1711.3	1711.6	1711.6	1711.6	1711.6	1711.6	1711.9
147.5°	1765.8	1765.6	1765.5	1765.4	1765.2	1765.4	1765.8	1766.2	1766.6	1767.0	1767.4
150°	1801.9	1801.2	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1802.6
152.5°	1836.8	1835.4	1833.9	1832.4	1830.9	1830.5	1831.2	1831.9	1832.6	1833.2	1833.9
155°	1881.7	1879.7	1877.7	1875.7	1873.7	1873.0	1873.7	1874.3	1875.0	1875.7	1876.7
157.5°	1916.3	1915.1	1913.9	1912.7	1911.5	1910.9	1911.0	1911.1	1911.1	1911.2	1912.3
160°	1940.4	1938.4	1936.4	1934.4	1932.4	1931.5	1931.9	1932.2	1932.5	1932.9	1934.2
162.5°	1959.7	1957.7	1955.7	1953.6	1951.6	1950.8	1951.1	1951.5	1951.8	1952.1	1954.0
165°	1985.6	1983.6	1981.5	1979.5	1977.5	1976.7	1977.0	1977.4	1977.7	1978.0	1980.0
167.5°	2004.8	2002.8	2000.7	1998.6	1996.5	1995.7	1996.0	1996.3	1996.7	1997.0	1999.4
170°	2015.7	2013.3	2011.0	2008.6	2006.3	2005.3	2005.6	2006.0	2006.3	2006.6	2009.3
172.5°	2022.9	2020.6	2018.2	2015.9	2013.5	2012.7	2013.3	2013.9	2014.5	2015.1	2017.5
175°	2030.7	2028.7	2026.7	2024.7	2022.7	2021.9	2022.2	2022.5	2022.9	2023.2	2025.9
177.5°	2034.3	2032.7	2031.1	2029.5	2027.9	2027.2	2027.5	2027.8	2028.0	2028.3	2030.2
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333738

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2057.3	2060.1	2062.9	2064.1	2063.9	2063.6	2063.3	2063.0
5°	2044.7	2048.2	2051.6	2053.0	2052.3	2051.6	2050.9	2050.2
7.5°	2019.2	2021.7	2024.1	2024.9	2024.1	2023.4	2022.6	2021.9
10°	1997.7	1998.8	1999.8	1999.8	1998.8	1997.7	1996.7	1995.7
12.5°	1967.3	1968.0	1968.8	1968.4	1966.8	1965.2	1963.6	1962.0
15°	1917.0	1916.7	1916.3	1914.6	1911.5	1908.4	1905.2	1902.1
17.5°	1854.4	1852.6	1850.9	1848.8	1846.2	1843.6	1841.1	1838.5
20°	1808.2	1806.5	1804.8	1802.3	1799.2	1796.1	1793.0	1789.9
22.5°	1762.5	1759.1	1755.7	1752.7	1750.2	1747.6	1745.0	1742.5
25°	1687.3	1682.8	1678.3	1674.1	1670.3	1666.5	1662.7	1658.9
27.5°	1606.1	1599.8	1593.5	1588.5	1584.8	1581.1	1577.4	1573.8
30°	1547.9	1539.9	1531.9	1526.4	1523.3	1520.1	1517.0	1513.9
32.5°	1491.3	1482.5	1473.7	1467.3	1463.4	1459.4	1455.5	1451.5
35°	1403.4	1393.3	1383.3	1375.8	1371.0	1366.1	1361.3	1356.4
37.5°	1311.4	1299.4	1287.3	1278.9	1274.2	1269.5	1264.8	1260.1
40°	1250.6	1237.4	1224.3	1215.6	1211.4	1207.3	1203.1	1199.0
42.5°	1190.6	1178.0	1165.4	1156.0	1149.9	1143.8	1137.7	1131.6
45°	1094.8	1081.0	1067.1	1057.6	1052.4	1047.2	1042.0	1036.8
47.5°	1000.2	985.9	971.6	961.6	955.8	950.1	944.3	938.6
50°	936.0	921.4	906.9	897.0	891.8	886.6	881.4	876.2
52.5°	875.1	859.5	843.8	833.4	828.2	823.0	817.8	812.6
55°	782.7	767.1	751.5	740.9	735.4	729.8	724.3	718.8
57.5°	690.1	674.9	659.6	649.6	644.6	639.7	634.8	629.9
60°	629.0	613.8	598.5	588.3	583.1	577.9	572.7	567.5
62.5°	568.9	554.7	540.6	530.9	525.7	520.5	515.3	510.1
65°	480.6	466.7	452.8	443.3	438.1	432.9	427.7	422.5
67.5°	396.2	383.5	370.9	362.4	358.3	354.1	350.0	345.8
70°	340.2	329.5	318.8	311.3	307.1	303.0	298.8	294.7
72.5°	288.3	278.4	268.4	262.1	259.3	256.6	253.8	251.0
75°	215.5	207.9	200.3	195.2	192.8	190.4	188.0	185.5
77.5°	153.3	148.0	142.7	139.1	137.3	135.5	133.7	131.9
80°	115.4	112.3	109.1	107.2	106.5	105.8	105.2	104.5
82.5°	86.3	84.8	83.4	82.4	82.0	81.6	81.2	80.8
85°	49.2	48.9	48.5	48.2	47.8	47.5	47.1	46.8
87.5°	24.2	24.5	24.9	25.0	24.9	24.8	24.8	24.7
90°	27.4	29.1	30.8	32.1	33.1	34.1	35.1	36.1
92.5°	27.4	29.1	30.8	31.8	32.3	32.8	33.3	33.7
95°	27.4	29.1	30.8	31.6	31.6	31.6	31.6	31.6
97.5°	55.2	45.8	36.3	31.6	31.6	31.6	31.6	31.6
100°	162.2	112.4	62.6	37.0	35.6	34.3	33.0	31.6
102.5°	315.3	305.9	296.5	280.4	257.6	234.9	212.1	189.4
105°	448.6	448.6	448.6	448.4	448.1	447.8	447.4	447.1
107.5°	568.0	568.0	568.1	567.6	566.6	565.6	564.6	563.6
110°	645.3	644.3	643.3	643.0	643.3	643.6	644.0	644.3





TEST NUMBER: P333738

CATALOG NUMBER: S125RDIW-S1270D1560U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	721.8	720.6	719.3	718.4	718.0	717.5	717.0	716.5
115°	837.3	836.0	834.6	833.0	831.0	828.9	826.9	824.9
117.5°	948.8	947.1	945.3	944.0	943.2	942.3	941.4	940.5
120°	1020.8	1020.1	1019.5	1018.3	1016.6	1014.9	1013.3	1011.6
122.5°	1089.4	1088.8	1088.1	1086.8	1084.9	1082.9	1081.0	1079.0
125°	1189.6	1188.2	1186.9	1185.7	1184.7	1183.7	1182.7	1181.7
127.5°	1281.1	1280.4	1279.6	1278.0	1275.5	1273.1	1270.6	1268.1
130°	1340.8	1339.8	1338.8	1337.4	1335.8	1334.1	1332.4	1330.7
132.5°	1396.6	1396.4	1396.2	1395.2	1393.6	1391.9	1390.2	1388.5
135°	1478.4	1477.8	1477.1	1475.7	1473.7	1471.7	1469.7	1467.7
137.5°	1554.7	1554.8	1555.0	1554.2	1552.4	1550.7	1548.9	1547.2
140°	1601.5	1602.2	1602.9	1602.2	1600.2	1598.2	1596.2	1594.2
142.5°	1647.4	1647.6	1647.7	1646.8	1644.7	1642.7	1640.7	1638.7
145°	1712.3	1712.6	1712.9	1712.1	1710.1	1708.1	1706.1	1704.1
147.5°	1767.8	1768.2	1768.6	1767.6	1765.2	1762.8	1760.4	1758.0
150°	1803.2	1803.9	1804.6	1803.6	1800.9	1798.2	1795.6	1792.9
152.5°	1834.6	1835.2	1835.9	1835.0	1832.6	1830.2	1827.8	1825.4
155°	1877.7	1878.7	1879.7	1878.8	1876.2	1873.5	1870.8	1868.1
157.5°	1913.3	1914.4	1915.5	1914.7	1912.0	1909.3	1906.6	1904.0
160°	1935.5	1936.9	1938.2	1937.6	1934.9	1932.2	1929.5	1926.9
162.5°	1955.9	1957.8	1959.6	1959.1	1956.2	1953.2	1950.3	1947.3
165°	1982.0	1984.1	1986.1	1985.7	1983.1	1980.4	1977.7	1975.0
167.5°	2001.8	2004.2	2006.6	2006.3	2003.3	2000.3	1997.3	1994.3
170°	2012.0	2014.7	2017.3	2017.2	2014.2	2011.2	2008.1	2005.1
172.5°	2019.9	2022.3	2024.7	2024.4	2021.4	2018.4	2015.4	2012.4
175°	2028.5	2031.2	2033.9	2033.7	2030.7	2027.7	2024.7	2021.7
177.5°	2032.1	2033.9	2035.8	2035.7	2033.5	2031.4	2029.2	2027.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7

(END OF REPORT)