

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333725

Luminaire Tested: **S125RDIW-S1270D770U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333725  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D770U835-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7583.6 lumens  
Efficiency: N/A  
Efficacy: 126.8 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct  
  
Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65
1	102	97	94	90	95	92	89	86	81	79	77	72	70	68	63	61	60	56
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51	48
3	85	76	69	63	80	72	65	60	64	59	55	57	53	49	50	47	44	41
4	78	67	60	54	73	64	57	51	57	51	47	51	46	43	45	41	39	35
5	72	60	52	46	67	57	50	44	51	45	41	46	41	37	40	37	34	31
6	66	54	46	40	62	52	44	39	46	40	36	41	37	33	37	33	30	27
7	62	49	41	36	58	47	39	34	42	36	32	38	33	29	34	30	27	24
8	57	45	37	32	54	43	36	31	39	33	28	35	30	26	31	27	24	22
9	53	41	33	28	50	39	32	27	35	30	25	32	27	24	29	25	22	20
10	50	38	30	26	47	36	29	25	33	27	23	30	25	21	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	12264	12264	12264	12264
5°	14110	12280	10845	12280
10°	16184	12218	9569	12218
15°	17481	12092	8506	12092
20°	19276	11947	7854	11947
25°	22308	11754	7288	11754
30°	24276	11551	6918	11551
35°	20478	11315	6576	11315
40°	14300	10890	6283	10890
45°	10609	10316	5994	10316
50°	8459	9720	5749	9720
55°	7179	8979	5530	8979
60°	6203	8317	5176	8317
65°	5527	7600	4455	7600
70°	4857	6962	4062	6962
75°	4202	6029	3813	6029
80°	3187	5073	3187	5073
85°	2660	3987	3001	3987



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	182.1	2.4
10°-20°	533.6	7.0
20°-30°	846.1	11.2
30°-40°	1020.3	13.5
40°-50°	911.2	12.0
50°-60°	698.8	9.2
60°-70°	454.1	6.0
70°-80°	220.8	2.9
80°-90°	54.8	0.7
90°-100°	63.9	0.8
100°-110°	188.7	2.5
110°-120°	319.6	4.2
120°-130°	420.6	5.5
130°-140°	471.2	6.2
140°-150°	461.9	6.1
150°-160°	387.9	5.1
160°-170°	257.9	3.4
170°-180°	90.2	1.2
0°-30°	1561.8	20.6
0°-40°	2582.2	34.0
0°-60°	4192.1	55.3
0°-90°	4921.8	64.9
90°-120°	572.1	7.5
90°-150°	1925.8	25.4
90°-180°	2662.0	35.1
0°-180°	7583.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2176	1894	1673	1894	2176	217
15°	2614	1808	1272	1808	2614	749
25°	3130	1649	1023	1649	3130	1437
35°	2597	1435	834	1435	2597	1569
45°	1162	1130	656	1130	1162	927
55°	638	797	491	797	638	579
65°	362	497	292	497	362	360
75°	168	242	153	242	168	179
85°	36	54	40	54	36	42
90°	18	1	18	1	18	12
95°	64	48	64	48	64	65
105°	184	169	184	169	184	195
115°	323	320	323	320	323	319
125°	470	467	470	467	470	420
135°	610	607	610	607	610	470
145°	739	736	739	736	739	461
155°	842	842	842	842	842	387
165°	913	915	913	915	913	257
175°	948	952	948	952	948	90
180°	954	954	954	954	954	



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1997.4	1996.2	1998.7	1991.8	1992.4	1981.8	1981.8	1973.7	1963.1	1955.0	1951.3
5°	2176.4	2178.0	2174.8	2163.1	2155.4	2143.7	2130.4	2107.0	2087.5	2068.8	2054.0
7.5°	2360.7	2361.8	2351.5	2347.9	2328.2	2313.9	2284.4	2252.6	2224.4	2188.6	2161.1
10°	2467.9	2467.2	2456.2	2447.7	2430.5	2408.7	2379.9	2342.4	2307.4	2268.4	2231.0
12.5°	2530.3	2528.3	2524.8	2514.4	2498.5	2479.2	2454.7	2417.9	2374.7	2332.0	2288.3
15°	2614.5	2609.0	2598.9	2585.6	2563.0	2540.4	2513.1	2480.4	2439.1	2390.8	2350.2
17.5°	2718.6	2718.8	2703.2	2684.8	2654.1	2614.2	2572.1	2519.2	2463.1	2409.9	2366.8
20°	2804.7	2802.3	2786.8	2750.9	2715.8	2665.9	2617.6	2552.9	2484.3	2414.9	2361.1
22.5°	2928.2	2922.1	2905.9	2858.8	2804.4	2740.1	2666.2	2587.2	2504.3	2425.5	2354.9
25°	3130.5	3125.8	3093.9	3039.3	2962.9	2863.9	2767.3	2658.9	2539.7	2436.0	2350.2
27.5°	3269.0	3263.8	3240.1	3194.8	3124.3	3020.1	2889.3	2744.5	2595.6	2453.0	2329.3
30°	3255.2	3266.9	3263.8	3242.8	3189.8	3096.2	2975.4	2812.5	2635.5	2467.9	2320.6
32.5°	3059.4	3069.9	3097.3	3138.6	3141.7	3104.3	3014.1	2863.6	2680.4	2489.8	2313.7
35°	2597.3	2611.4	2664.4	2747.8	2856.9	2948.1	2966.8	2885.8	2721.3	2516.3	2303.5
37.5°	1996.8	2073.5	2118.1	2205.9	2370.8	2538.6	2699.9	2759.3	2689.3	2505.4	2286.8
40°	1696.2	1714.9	1794.4	1893.4	2032.2	2206.8	2436.8	2602.8	2608.2	2480.4	2260.6
42.5°	1451.8	1475.5	1530.0	1609.1	1727.9	1902.5	2139.9	2359.0	2460.5	2411.8	2226.3
45°	1161.5	1179.4	1219.2	1280.0	1371.2	1515.4	1719.6	1972.9	2174.1	2252.8	2134.3
47.5°	954.1	963.8	998.4	1044.7	1112.2	1217.3	1375.4	1595.3	1836.5	2005.7	1989.0
50°	841.9	852.8	879.3	914.4	971.3	1060.1	1186.4	1369.6	1618.3	1824.8	1866.2
52.5°	754.6	763.6	780.1	813.3	860.3	928.6	1030.5	1196.2	1420.0	1639.6	1735.2
55°	637.6	643.9	657.1	675.8	713.3	762.4	850.4	965.0	1145.9	1367.3	1507.6
57.5°	541.3	544.4	552.8	570.1	596.0	631.9	695.5	792.6	922.3	1121.7	1276.5
60°	480.2	483.3	494.2	505.9	526.2	558.9	608.8	676.6	801.3	965.8	1122.5
62.5°	431.5	433.4	438.1	449.8	467.6	492.8	532.1	587.4	686.6	831.1	979.1
65°	361.7	362.5	364.0	373.4	384.3	403.0	428.7	467.7	542.5	651.7	782.6
67.5°	294.7	295.7	301.2	304.5	315.9	325.7	340.8	370.6	423.3	496.9	598.7
70°	257.2	256.5	261.9	265.8	269.7	281.4	291.5	315.7	348.4	404.6	489.5
72.5°	222.3	220.3	222.6	224.0	229.2	237.1	247.3	262.1	287.3	326.0	391.0
75°	168.4	169.2	169.2	170.7	174.6	177.7	180.8	188.6	202.7	228.4	263.5
77.5°	118.2	116.9	120.2	120.7	123.0	126.4	129.1	132.2	138.0	148.6	166.7
80°	85.7	85.7	86.5	88.9	88.1	89.6	93.5	96.7	103.7	109.9	116.1
82.5°	65.8	65.2	65.9	66.4	66.3	67.8	69.2	69.8	72.5	75.6	80.0
85°	35.9	35.9	36.6	36.6	37.4	37.4	38.2	38.2	38.2	39.0	39.8
87.5°	17.3	16.6	15.8	15.7	16.3	17.4	16.6	15.8	15.6	15.5	15.9
90°	17.8	17.3	16.8	16.3	15.8	15.2	14.4	13.5	12.7	11.9	10.7
92.5°	35.0	34.7	34.3	34.0	33.6	32.9	31.8	30.7	29.6	28.5	27.1
95°	63.8	63.5	63.2	62.9	62.5	61.8	60.6	59.5	58.3	57.2	55.5
97.5°	96.8	96.6	96.4	96.2	96.0	95.4	94.3	93.2	92.1	91.0	88.7
100°	121.7	121.4	121.1	120.8	120.4	119.5	118.0	116.5	115.1	113.6	111.4
102.5°	146.7	146.2	145.8	145.3	144.8	143.8	142.2	140.6	139.0	137.3	136.2
105°	184.1	183.6	183.1	182.6	182.1	181.4	180.4	179.4	178.4	177.4	176.4
107.5°	222.4	222.4	222.5	222.5	222.5	222.3	221.8	221.3	220.8	220.3	219.6
110°	250.9	251.1	251.2	251.4	251.6	251.4	250.9	250.4	249.9	249.4	248.9



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	278.8	279.1	279.4	279.7	280.0	280.0	279.8	279.6	279.4	279.1	278.5
115°	322.9	323.1	323.3	323.4	323.6	323.7	323.9	324.1	324.2	324.4	324.1
117.5°	366.0	366.6	367.3	368.0	368.6	368.9	368.7	368.6	368.5	368.4	368.1
120°	395.7	396.3	397.0	397.7	398.3	398.6	398.6	398.6	398.6	398.6	398.5
122.5°	425.4	425.9	426.4	426.9	427.5	427.8	427.9	428.1	428.2	428.3	427.9
125°	469.9	470.1	470.2	470.4	470.6	470.8	471.1	471.5	471.8	472.1	472.0
127.5°	512.7	513.0	513.3	513.7	514.0	514.2	514.4	514.6	514.7	514.9	514.7
130°	541.2	541.5	541.8	542.2	542.5	542.7	542.9	543.1	543.2	543.4	543.1
132.5°	567.9	568.4	568.8	569.3	569.7	570.1	570.2	570.4	570.6	570.7	570.8
135°	609.5	610.1	610.8	611.4	612.1	612.4	612.4	612.4	612.4	612.4	612.3
137.5°	650.1	651.0	651.8	652.6	653.4	653.8	653.6	653.4	653.2	653.0	652.6
140°	676.3	677.1	677.9	678.8	679.6	679.8	679.5	679.2	678.8	678.5	678.0
142.5°	701.2	702.0	702.9	703.7	704.5	704.8	704.6	704.4	704.2	704.0	703.4
145°	738.6	739.1	739.6	740.1	740.6	740.9	740.9	740.9	740.9	740.9	740.4
147.5°	770.6	771.7	772.8	773.9	775.0	775.4	775.0	774.6	774.2	773.8	773.4
150°	794.3	794.6	795.0	795.3	795.6	795.8	795.8	795.8	795.8	795.8	795.1
152.5°	813.9	814.5	815.1	815.7	816.3	816.4	816.0	815.6	815.2	814.8	814.5
155°	841.8	842.6	843.5	844.3	845.1	845.2	844.5	843.9	843.2	842.6	842.4
157.5°	865.1	866.2	867.3	868.4	869.5	869.7	869.0	868.4	867.7	867.1	866.9
160°	881.2	882.0	882.8	883.6	884.5	884.5	883.9	883.2	882.6	881.9	881.7
162.5°	894.8	895.8	896.7	897.7	898.7	898.7	897.9	897.2	896.4	895.6	895.5
165°	913.1	914.1	915.1	916.1	917.0	917.2	916.6	915.9	915.2	914.6	914.4
167.5°	927.6	928.7	929.7	930.7	931.7	931.7	930.8	929.8	928.8	927.8	927.8
170°	935.4	936.5	937.7	938.8	940.0	940.1	939.1	938.1	937.1	936.1	936.1
172.5°	941.9	942.9	943.9	945.0	946.0	946.0	945.0	944.0	943.0	942.0	942.0
175°	948.0	949.1	950.3	951.4	952.6	952.7	951.7	950.7	949.7	948.7	948.7
177.5°	951.5	952.5	953.4	954.3	955.2	955.3	954.5	953.7	952.9	952.1	952.3
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1951.3	1946.9	1938.8	1931.3	1922.0	1913.9	1908.2	1901.4	1892.7	1882.1	1873.3
5°	2037.6	2020.5	1997.9	1978.4	1953.5	1934.0	1913.7	1894.2	1874.7	1849.8	1828.0
7.5°	2133.4	2098.0	2063.5	2020.2	1980.9	1945.8	1912.1	1878.0	1844.6	1809.2	1775.1
10°	2192.0	2149.1	2101.6	2047.0	1997.1	1949.6	1905.9	1863.0	1817.8	1778.1	1735.2
12.5°	2246.9	2191.5	2137.1	2068.2	2008.3	1950.2	1894.7	1841.2	1792.9	1741.3	1695.3
15°	2296.4	2241.9	2181.1	2096.9	2013.5	1943.3	1877.8	1808.5	1748.4	1690.8	1639.3
17.5°	2315.6	2258.4	2187.8	2106.9	2015.7	1927.4	1843.1	1767.0	1696.4	1629.2	1571.3
20°	2308.1	2252.8	2180.3	2103.1	2005.7	1913.7	1822.5	1738.3	1659.6	1588.6	1527.1
22.5°	2290.1	2232.8	2162.8	2081.3	1988.8	1891.3	1793.8	1704.0	1621.5	1548.1	1480.9
25°	2262.9	2185.0	2113.3	2033.7	1945.7	1849.0	1748.4	1649.4	1561.4	1486.5	1413.3
27.5°	2234.7	2137.4	2046.2	1967.2	1874.1	1787.9	1690.9	1589.4	1496.8	1420.6	1345.4
30°	2209.1	2100.0	1999.4	1909.8	1821.7	1739.9	1647.9	1548.9	1453.8	1375.1	1298.7
32.5°	2177.3	2061.3	1950.8	1847.4	1762.5	1681.3	1598.0	1503.4	1410.8	1329.5	1251.9
35°	2137.4	1989.3	1869.3	1759.4	1665.0	1586.3	1511.5	1435.1	1342.3	1258.1	1182.5
37.5°	2085.0	1917.0	1778.1	1658.3	1558.9	1479.8	1420.7	1350.9	1266.2	1185.6	1115.5
40°	2053.2	1864.6	1712.6	1594.1	1489.6	1406.2	1350.9	1291.7	1214.5	1138.9	1068.7
42.5°	2010.8	1816.6	1646.5	1523.0	1417.9	1337.6	1281.7	1229.9	1165.2	1094.0	1018.8
45°	1927.7	1723.5	1545.0	1412.5	1306.5	1227.7	1175.5	1129.5	1080.4	1014.9	949.4
47.5°	1819.5	1626.4	1439.6	1294.9	1191.1	1118.0	1067.3	1031.0	995.9	940.2	876.6
50°	1732.9	1546.6	1364.1	1223.8	1113.1	1043.8	996.2	967.4	935.4	884.7	831.7
52.5°	1630.6	1464.2	1285.6	1142.1	1037.7	972.7	927.0	898.2	871.8	830.5	780.0
55°	1469.4	1323.6	1159.9	1029.7	933.9	868.4	824.7	797.4	781.9	746.8	707.0
57.5°	1283.4	1178.9	1034.6	909.1	824.3	759.6	727.6	704.4	686.8	662.0	633.9
60°	1153.7	1080.4	951.0	831.7	753.8	692.2	663.4	643.9	627.5	606.5	584.6
62.5°	1022.1	968.8	856.2	753.8	682.1	630.5	603.5	585.9	567.0	552.8	531.6
65°	845.8	798.2	720.3	640.0	573.7	532.4	512.9	497.3	485.6	470.0	455.2
67.5°	657.9	638.6	584.8	529.4	481.9	445.1	428.3	417.4	403.3	394.0	383.8
70°	542.5	533.2	495.0	458.4	413.9	389.0	373.4	368.7	351.6	342.2	335.2
72.5°	440.3	435.9	413.9	388.5	357.2	335.3	321.0	315.7	304.8	297.3	292.8
75°	301.7	303.2	299.3	283.0	271.3	257.2	244.8	241.6	233.9	227.6	223.7
77.5°	190.8	198.8	199.1	198.3	193.6	185.1	179.9	177.6	169.9	167.6	166.7
80°	131.0	139.5	147.3	146.5	145.0	142.7	138.8	136.4	132.5	130.2	128.6
82.5°	87.3	95.3	101.8	106.0	105.7	103.4	100.7	99.6	98.8	97.1	96.8
85°	41.3	42.9	45.2	50.7	54.6	55.3	54.6	53.8	51.4	52.2	53.0
87.5°	16.3	16.0	16.4	16.2	15.3	18.1	19.7	20.1	19.1	18.1	17.2
90°	9.6	8.4	7.3	6.0	4.7	3.4	2.1	0.7	2.1	3.4	4.7
92.5°	25.7	24.3	22.8	21.7	20.7	19.8	18.9	18.0	18.9	19.8	20.7
95°	53.9	52.2	50.6	49.6	49.2	48.9	48.6	48.3	48.6	48.9	49.2
97.5°	86.5	84.2	81.9	80.7	80.6	80.4	80.3	80.2	80.3	80.4	80.6
100°	109.3	107.1	105.0	103.9	103.9	103.9	103.9	103.9	103.9	103.9	103.9
102.5°	135.2	134.1	133.0	132.1	131.4	130.8	130.1	129.5	130.1	130.8	131.4
105°	175.4	174.5	173.5	172.6	171.7	170.9	170.1	169.3	170.1	170.9	171.7
107.5°	218.8	218.1	217.3	216.5	215.7	214.9	214.0	213.2	214.0	214.9	215.7
110°	248.4	247.9	247.4	246.8	246.0	245.1	244.3	243.5	244.3	245.1	246.0





TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	277.9	277.2	276.6	276.1	275.7	275.2	274.8	274.4	274.8	275.2	275.7
115°	323.7	323.4	323.1	322.6	321.9	321.3	320.6	320.0	320.6	321.3	321.9
117.5°	367.8	367.5	367.2	366.9	366.6	366.3	366.0	365.7	366.0	366.3	366.6
120°	398.3	398.1	398.0	397.5	396.7	395.8	395.0	394.2	395.0	395.8	396.7
122.5°	427.5	427.0	426.6	426.3	426.0	425.7	425.4	425.1	425.4	425.7	426.0
125°	471.8	471.6	471.5	470.9	469.9	468.9	467.9	466.9	467.9	468.9	469.9
127.5°	514.5	514.3	514.1	513.7	513.2	512.6	512.0	511.5	512.0	512.6	513.2
130°	542.7	542.4	542.1	541.5	540.7	539.9	539.0	538.2	539.0	539.9	540.7
132.5°	570.8	570.9	571.0	570.3	569.0	567.6	566.3	564.9	566.3	567.6	569.0
135°	612.1	611.9	611.8	611.2	610.2	609.2	608.2	607.2	608.2	609.2	610.2
137.5°	652.2	651.9	651.5	650.9	649.9	648.9	648.0	647.0	648.0	648.9	649.9
140°	677.5	677.0	676.5	675.9	675.0	674.2	673.4	672.6	673.4	674.2	675.0
142.5°	702.8	702.2	701.5	700.9	700.2	699.5	698.8	698.1	698.8	699.5	700.2
145°	739.9	739.4	738.9	738.3	737.6	737.0	736.3	735.7	736.3	737.0	737.6
147.5°	773.0	772.6	772.2	771.9	771.5	771.1	770.8	770.4	770.8	771.1	771.5
150°	794.5	793.8	793.2	792.9	793.1	793.2	793.4	793.6	793.4	793.2	793.1
152.5°	814.3	814.0	813.7	813.5	813.3	813.0	812.8	812.6	812.8	813.0	813.3
155°	842.2	842.1	841.9	841.8	841.8	841.8	841.8	841.8	841.8	841.8	841.8
157.5°	866.7	866.6	866.4	866.5	866.9	867.2	867.6	868.0	867.6	867.2	866.9
160°	881.6	881.4	881.2	881.4	881.9	882.4	882.9	883.4	882.9	882.4	881.9
162.5°	895.5	895.5	895.4	895.6	896.0	896.3	896.7	897.1	896.7	896.3	896.0
165°	914.2	914.1	913.9	914.0	914.3	914.7	915.0	915.3	915.0	914.7	914.3
167.5°	927.8	927.8	927.8	928.1	928.8	929.4	930.1	930.8	930.1	929.4	928.8
170°	936.1	936.1	936.1	936.4	937.1	937.7	938.4	939.1	938.4	937.7	937.1
172.5°	942.0	942.0	942.0	942.4	943.0	943.7	944.3	945.0	944.3	943.7	943.0
175°	948.7	948.7	948.7	949.0	949.7	950.4	951.0	951.7	951.0	950.4	949.7
177.5°	952.4	952.5	952.7	953.0	953.5	954.0	954.6	955.1	954.6	954.0	953.5
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1867.1	1858.4	1852.1	1839.6	1830.9	1827.2	1820.3	1818.4	1825.3	1820.3	1819.7
5°	1811.6	1789.0	1771.1	1753.1	1733.6	1721.2	1702.5	1699.3	1694.7	1687.6	1686.1
7.5°	1745.0	1715.6	1692.5	1662.9	1637.1	1616.4	1593.0	1581.9	1575.9	1566.8	1554.7
10°	1700.1	1665.0	1633.9	1604.2	1572.3	1546.6	1523.2	1505.2	1493.5	1482.6	1478.0
12.5°	1655.8	1620.1	1580.2	1544.4	1508.7	1479.8	1453.9	1442.3	1429.3	1416.5	1405.6
15°	1587.1	1539.5	1495.9	1454.6	1424.2	1393.0	1368.0	1350.9	1331.4	1326.0	1304.9
17.5°	1514.1	1467.5	1416.4	1372.9	1337.6	1303.3	1275.9	1256.4	1241.8	1221.7	1212.0
20°	1468.6	1413.3	1363.4	1323.6	1284.6	1244.1	1216.0	1199.7	1185.6	1169.3	1161.5
22.5°	1420.0	1365.9	1314.7	1268.1	1228.5	1188.6	1168.6	1151.7	1135.7	1120.6	1110.3
25°	1348.6	1294.0	1240.2	1191.9	1150.6	1121.7	1098.3	1078.8	1070.3	1055.5	1044.5
27.5°	1277.9	1219.9	1164.1	1115.9	1083.5	1055.0	1035.8	1020.4	1004.9	992.0	982.5
30°	1232.4	1173.2	1112.4	1074.2	1039.9	1012.6	991.5	976.7	965.0	953.3	946.3
32.5°	1186.9	1125.8	1071.8	1030.5	998.1	974.5	952.9	938.7	926.4	913.4	905.2
35°	1113.9	1051.6	1007.9	967.4	935.4	913.6	898.8	878.5	868.4	859.0	850.4
37.5°	1046.1	988.1	940.9	905.3	877.6	855.9	836.7	825.8	813.3	804.9	797.8
40°	996.2	943.2	900.3	862.9	842.7	818.5	800.6	786.5	777.2	766.3	758.5
42.5°	951.3	902.1	860.4	826.8	801.5	781.1	763.8	749.7	737.9	730.1	723.5
45°	887.9	838.8	798.2	767.0	743.7	724.2	706.2	699.2	683.6	674.3	671.2
47.5°	822.2	778.3	739.1	710.4	686.4	668.0	651.2	636.9	628.3	619.1	614.1
50°	778.0	735.9	699.2	671.2	647.8	627.5	611.9	602.6	590.9	582.3	576.1
52.5°	733.7	694.7	658.1	631.2	611.0	590.7	573.3	563.9	552.8	547.4	543.0
55°	670.4	629.1	597.9	571.4	550.3	531.6	515.3	505.9	498.9	493.4	491.9
57.5°	598.7	565.9	536.9	513.1	491.2	473.6	459.3	450.4	444.2	443.4	438.7
60°	551.9	522.3	495.8	470.0	451.3	435.0	422.5	412.4	406.1	405.3	403.8
62.5°	505.1	476.7	452.1	429.5	412.7	396.9	385.1	373.7	370.0	366.1	362.6
65°	435.7	410.0	389.8	371.8	353.9	340.6	329.0	321.9	313.4	308.7	300.1
67.5°	367.6	347.7	328.2	313.1	299.0	286.4	276.7	266.3	260.5	256.8	250.5
70°	322.7	307.1	287.6	271.3	260.4	250.2	242.4	230.7	226.8	223.7	220.6
72.5°	280.3	266.6	250.2	237.0	226.1	216.5	207.5	202.0	198.2	195.0	193.2
75°	220.6	207.4	193.3	184.0	176.2	168.4	163.7	159.8	158.2	157.5	154.3
77.5°	162.0	155.0	143.7	136.3	131.1	128.0	123.8	121.8	121.6	118.2	117.1
80°	123.9	120.0	110.7	107.6	103.7	100.6	98.2	94.3	90.4	88.9	86.5
82.5°	92.1	88.2	84.5	79.5	76.2	74.4	72.0	70.6	71.1	68.9	67.8
85°	49.1	45.2	43.7	42.9	41.3	42.9	42.1	41.3	40.5	39.8	40.5
87.5°	16.8	17.0	16.6	18.1	16.5	17.3	17.5	17.0	17.2	17.4	16.9
90°	6.0	7.3	8.4	9.6	10.7	11.9	12.7	13.5	14.4	15.2	15.8
92.5°	21.7	22.8	24.3	25.7	27.1	28.5	29.6	30.7	31.8	32.9	33.6
95°	49.6	50.6	52.2	53.9	55.5	57.2	58.3	59.5	60.6	61.8	62.5
97.5°	80.7	81.9	84.2	86.5	88.7	91.0	92.1	93.2	94.3	95.4	96.0
100°	103.9	105.0	107.1	109.3	111.4	113.6	115.1	116.5	118.0	119.5	120.4
102.5°	132.1	133.0	134.1	135.2	136.2	137.3	139.0	140.6	142.2	143.8	144.8
105°	172.6	173.5	174.5	175.4	176.4	177.4	178.4	179.4	180.4	181.4	182.1
107.5°	216.5	217.3	218.1	218.8	219.6	220.3	220.8	221.3	221.8	222.3	222.5
110°	246.8	247.4	247.9	248.4	248.9	249.4	249.9	250.4	250.9	251.4	251.6



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	276.1	276.6	277.2	277.9	278.5	279.1	279.4	279.6	279.8	280.0	280.0
115°	322.6	323.1	323.4	323.7	324.1	324.4	324.2	324.1	323.9	323.7	323.6
117.5°	366.9	367.2	367.5	367.8	368.1	368.4	368.5	368.6	368.7	368.9	368.6
120°	397.5	398.0	398.1	398.3	398.5	398.6	398.6	398.6	398.6	398.6	398.3
122.5°	426.3	426.6	427.0	427.5	427.9	428.3	428.2	428.1	427.9	427.8	427.5
125°	470.9	471.5	471.6	471.8	472.0	472.1	471.8	471.5	471.1	470.8	470.6
127.5°	513.7	514.1	514.3	514.5	514.7	514.9	514.7	514.6	514.4	514.2	514.0
130°	541.5	542.1	542.4	542.7	543.1	543.4	543.2	543.1	542.9	542.7	542.5
132.5°	570.3	571.0	570.9	570.8	570.8	570.7	570.6	570.4	570.2	570.1	569.7
135°	611.2	611.8	611.9	612.1	612.3	612.4	612.4	612.4	612.4	612.4	612.1
137.5°	650.9	651.5	651.9	652.2	652.6	653.0	653.2	653.4	653.6	653.8	653.4
140°	675.9	676.5	677.0	677.5	678.0	678.5	678.8	679.2	679.5	679.8	679.6
142.5°	700.9	701.5	702.2	702.8	703.4	704.0	704.2	704.4	704.6	704.8	704.5
145°	738.3	738.9	739.4	739.9	740.4	740.9	740.9	740.9	740.9	740.9	740.6
147.5°	771.9	772.2	772.6	773.0	773.4	773.8	774.2	774.6	775.0	775.4	775.0
150°	792.9	793.2	793.8	794.5	795.1	795.8	795.8	795.8	795.8	795.8	795.6
152.5°	813.5	813.7	814.0	814.3	814.5	814.8	815.2	815.6	816.0	816.4	816.3
155°	841.8	841.9	842.1	842.2	842.4	842.6	843.2	843.9	844.5	845.2	845.1
157.5°	866.5	866.4	866.6	866.7	866.9	867.1	867.7	868.4	869.0	869.7	869.5
160°	881.4	881.2	881.4	881.6	881.7	881.9	882.6	883.2	883.9	884.5	884.5
162.5°	895.6	895.4	895.5	895.5	895.5	895.6	896.4	897.2	897.9	898.7	898.7
165°	914.0	913.9	914.1	914.2	914.4	914.6	915.2	915.9	916.6	917.2	917.0
167.5°	928.1	927.8	927.8	927.8	927.8	927.8	928.8	929.8	930.8	931.7	931.7
170°	936.4	936.1	936.1	936.1	936.1	936.1	937.1	938.1	939.1	940.1	940.0
172.5°	942.4	942.0	942.0	942.0	942.0	942.0	943.0	944.0	945.0	946.0	946.0
175°	949.0	948.7	948.7	948.7	948.7	948.7	949.7	950.7	951.7	952.7	952.6
177.5°	953.0	952.7	952.5	952.4	952.3	952.1	952.9	953.7	954.5	955.3	955.2
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1819.1	1812.2	1810.3	1812.8	1810.3	1812.2	1819.1	1819.7	1820.3	1825.3	1818.4
5°	1678.3	1670.5	1674.4	1672.8	1674.4	1670.5	1678.3	1686.1	1687.6	1694.7	1699.3
7.5°	1554.5	1544.8	1534.5	1537.8	1534.5	1544.8	1554.5	1554.7	1566.8	1575.9	1581.9
10°	1467.8	1460.0	1455.3	1459.2	1455.3	1460.0	1467.8	1478.0	1482.6	1493.5	1505.2
12.5°	1394.9	1390.2	1386.1	1384.4	1386.1	1390.2	1394.9	1405.6	1416.5	1429.3	1442.3
15°	1295.5	1286.2	1282.3	1272.2	1282.3	1286.2	1295.5	1304.9	1326.0	1331.4	1350.9
17.5°	1204.0	1200.9	1190.8	1186.4	1190.8	1200.9	1204.0	1212.0	1221.7	1241.8	1256.4
20°	1149.8	1146.7	1136.5	1142.8	1136.5	1146.7	1149.8	1161.5	1169.3	1185.6	1199.7
22.5°	1104.9	1098.0	1094.7	1092.9	1094.7	1098.0	1104.9	1110.3	1120.6	1135.7	1151.7
25°	1041.4	1031.3	1027.4	1022.7	1027.4	1031.3	1041.4	1044.5	1055.5	1070.3	1078.8
27.5°	978.1	972.7	967.5	966.3	967.5	972.7	978.1	982.5	992.0	1004.9	1020.4
30°	937.0	931.5	927.6	927.6	927.6	931.5	937.0	946.3	953.3	965.0	976.7
32.5°	900.2	896.0	892.1	891.5	892.1	896.0	900.2	905.2	913.4	926.4	938.7
35°	846.6	840.3	838.8	834.1	838.8	840.3	846.6	850.4	859.0	868.4	878.5
37.5°	790.9	785.7	785.6	785.1	785.6	785.7	790.9	797.8	804.9	813.3	825.8
40°	755.3	751.4	750.7	745.2	750.7	751.4	755.3	758.5	766.3	777.2	786.5
42.5°	717.3	715.3	712.6	710.3	712.6	715.3	717.3	723.5	730.1	737.9	749.7
45°	665.7	660.2	660.2	656.3	660.2	660.2	665.7	671.2	674.3	683.6	699.2
47.5°	612.4	608.2	608.6	604.6	608.6	608.2	612.4	614.1	619.1	628.3	636.9
50°	576.8	574.5	573.7	572.2	573.7	574.5	576.8	576.1	582.3	590.9	602.6
52.5°	541.3	540.2	543.2	539.7	543.2	540.2	541.3	543.0	547.4	552.8	563.9
55°	493.4	491.1	495.8	491.1	495.8	491.1	493.4	491.9	493.4	498.9	505.9
57.5°	438.4	436.2	440.4	438.1	440.4	436.2	438.4	438.7	443.4	444.2	450.4
60°	402.2	397.6	399.9	400.7	399.9	397.6	402.2	403.8	405.3	406.1	412.4
62.5°	359.2	356.4	358.1	354.5	358.1	356.4	359.2	362.6	366.1	370.0	373.7
65°	298.6	296.2	293.1	291.5	293.1	296.2	298.6	300.1	308.7	313.4	321.9
67.5°	250.8	245.2	245.1	246.3	245.1	245.2	250.8	250.5	256.8	260.5	266.3
70°	215.9	215.9	215.1	215.1	215.1	215.9	215.9	220.6	223.7	226.8	230.7
72.5°	191.6	191.0	189.6	189.0	189.6	191.0	191.6	193.2	195.0	198.2	202.0
75°	154.3	155.1	153.6	152.8	153.6	155.1	154.3	154.3	157.5	158.2	159.8
77.5°	114.0	110.7	112.4	110.7	112.4	110.7	114.0	117.1	118.2	121.6	121.8
80°	86.5	85.7	88.1	85.7	88.1	85.7	86.5	86.5	88.9	90.4	94.3
82.5°	68.4	67.7	68.8	67.0	68.8	67.7	68.4	67.8	68.9	71.1	70.6
85°	41.3	40.5	39.8	40.5	39.8	40.5	41.3	40.5	39.8	40.5	41.3
87.5°	17.6	17.1	17.2	17.3	17.2	17.1	17.6	16.9	17.4	17.2	17.0
90°	16.3	16.8	17.3	17.8	17.3	16.8	16.3	15.8	15.2	14.4	13.5
92.5°	34.0	34.3	34.7	35.0	34.7	34.3	34.0	33.6	32.9	31.8	30.7
95°	62.9	63.2	63.5	63.8	63.5	63.2	62.9	62.5	61.8	60.6	59.5
97.5°	96.2	96.4	96.6	96.8	96.6	96.4	96.2	96.0	95.4	94.3	93.2
100°	120.8	121.1	121.4	121.7	121.4	121.1	120.8	120.4	119.5	118.0	116.5
102.5°	145.3	145.8	146.2	146.7	146.2	145.8	145.3	144.8	143.8	142.2	140.6
105°	182.6	183.1	183.6	184.1	183.6	183.1	182.6	182.1	181.4	180.4	179.4
107.5°	222.5	222.5	222.4	222.4	222.4	222.5	222.5	222.5	222.3	221.8	221.3
110°	251.4	251.2	251.1	250.9	251.1	251.2	251.4	251.6	251.4	250.9	250.4



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	279.7	279.4	279.1	278.8	279.1	279.4	279.7	280.0	280.0	279.8	279.6
115°	323.4	323.3	323.1	322.9	323.1	323.3	323.4	323.6	323.7	323.9	324.1
117.5°	368.0	367.3	366.6	366.0	366.6	367.3	368.0	368.6	368.9	368.7	368.6
120°	397.7	397.0	396.3	395.7	396.3	397.0	397.7	398.3	398.6	398.6	398.6
122.5°	426.9	426.4	425.9	425.4	425.9	426.4	426.9	427.5	427.8	427.9	428.1
125°	470.4	470.2	470.1	469.9	470.1	470.2	470.4	470.6	470.8	471.1	471.5
127.5°	513.7	513.3	513.0	512.7	513.0	513.3	513.7	514.0	514.2	514.4	514.6
130°	542.2	541.8	541.5	541.2	541.5	541.8	542.2	542.5	542.7	542.9	543.1
132.5°	569.3	568.8	568.4	567.9	568.4	568.8	569.3	569.7	570.1	570.2	570.4
135°	611.4	610.8	610.1	609.5	610.1	610.8	611.4	612.1	612.4	612.4	612.4
137.5°	652.6	651.8	651.0	650.1	651.0	651.8	652.6	653.4	653.8	653.6	653.4
140°	678.8	677.9	677.1	676.3	677.1	677.9	678.8	679.6	679.8	679.5	679.2
142.5°	703.7	702.9	702.0	701.2	702.0	702.9	703.7	704.5	704.8	704.6	704.4
145°	740.1	739.6	739.1	738.6	739.1	739.6	740.1	740.6	740.9	740.9	740.9
147.5°	773.9	772.8	771.7	770.6	771.7	772.8	773.9	775.0	775.4	775.0	774.6
150°	795.3	795.0	794.6	794.3	794.6	795.0	795.3	795.6	795.8	795.8	795.8
152.5°	815.7	815.1	814.5	813.9	814.5	815.1	815.7	816.3	816.4	816.0	815.6
155°	844.3	843.5	842.6	841.8	842.6	843.5	844.3	845.1	845.2	844.5	843.9
157.5°	868.4	867.3	866.2	865.1	866.2	867.3	868.4	869.5	869.7	869.0	868.4
160°	883.6	882.8	882.0	881.2	882.0	882.8	883.6	884.5	884.5	883.9	883.2
162.5°	897.7	896.7	895.8	894.8	895.8	896.7	897.7	898.7	898.7	897.9	897.2
165°	916.1	915.1	914.1	913.1	914.1	915.1	916.1	917.0	917.2	916.6	915.9
167.5°	930.7	929.7	928.7	927.6	928.7	929.7	930.7	931.7	931.7	930.8	929.8
170°	938.8	937.7	936.5	935.4	936.5	937.7	938.8	940.0	940.1	939.1	938.1
172.5°	945.0	943.9	942.9	941.9	942.9	943.9	945.0	946.0	946.0	945.0	944.0
175°	951.4	950.3	949.1	948.0	949.1	950.3	951.4	952.6	952.7	951.7	950.7
177.5°	954.3	953.4	952.5	951.5	952.5	953.4	954.3	955.2	955.3	954.5	953.7
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1820.3	1827.2	1830.9	1839.6	1852.1	1858.4	1867.1	1873.3	1882.1	1892.7	1901.4
5°	1702.5	1721.2	1733.6	1753.1	1771.1	1789.0	1811.6	1828.0	1849.8	1874.7	1894.2
7.5°	1593.0	1616.4	1637.1	1662.9	1692.5	1715.6	1745.0	1775.1	1809.2	1844.6	1878.0
10°	1523.2	1546.6	1572.3	1604.2	1633.9	1665.0	1700.1	1735.2	1778.1	1817.8	1863.0
12.5°	1453.9	1479.8	1508.7	1544.4	1580.2	1620.1	1655.8	1695.3	1741.3	1792.9	1841.2
15°	1368.0	1393.0	1424.2	1454.6	1495.9	1539.5	1587.1	1639.3	1690.8	1748.4	1808.5
17.5°	1275.9	1303.3	1337.6	1372.9	1416.4	1467.5	1514.1	1571.3	1629.2	1696.4	1767.0
20°	1216.0	1244.1	1284.6	1323.6	1363.4	1413.3	1468.6	1527.1	1588.6	1659.6	1738.3
22.5°	1168.6	1188.6	1228.5	1268.1	1314.7	1365.9	1420.0	1480.9	1548.1	1621.5	1704.0
25°	1098.3	1121.7	1150.6	1191.9	1240.2	1294.0	1348.6	1413.3	1486.5	1561.4	1649.4
27.5°	1035.8	1055.0	1083.5	1115.9	1164.1	1219.9	1277.9	1345.4	1420.6	1496.8	1589.4
30°	991.5	1012.6	1039.9	1074.2	1112.4	1173.2	1232.4	1298.7	1375.1	1453.8	1548.9
32.5°	952.9	974.5	998.1	1030.5	1071.8	1125.8	1186.9	1251.9	1329.5	1410.8	1503.4
35°	898.8	913.6	935.4	967.4	1007.9	1051.6	1113.9	1182.5	1258.1	1342.3	1435.1
37.5°	836.7	855.9	877.6	905.3	940.9	988.1	1046.1	1115.5	1185.6	1266.2	1350.9
40°	800.6	818.5	842.7	862.9	900.3	943.2	996.2	1068.7	1138.9	1214.5	1291.7
42.5°	763.8	781.1	801.5	826.8	860.4	902.1	951.3	1018.8	1094.0	1165.2	1229.9
45°	706.2	724.2	743.7	767.0	798.2	838.8	887.9	949.4	1014.9	1080.4	1129.5
47.5°	651.2	668.0	686.4	710.4	739.1	778.3	822.2	876.6	940.2	995.9	1031.0
50°	611.9	627.5	647.8	671.2	699.2	735.9	778.0	831.7	884.7	935.4	967.4
52.5°	573.3	590.7	611.0	631.2	658.1	694.7	733.7	780.0	830.5	871.8	898.2
55°	515.3	531.6	550.3	571.4	597.9	629.1	670.4	707.0	746.8	781.9	797.4
57.5°	459.3	473.6	491.2	513.1	536.9	565.9	598.7	633.9	662.0	686.8	704.4
60°	422.5	435.0	451.3	470.0	495.8	522.3	551.9	584.6	606.5	627.5	643.9
62.5°	385.1	396.9	412.7	429.5	452.1	476.7	505.1	531.6	552.8	567.0	585.9
65°	329.0	340.6	353.9	371.8	389.8	410.0	435.7	455.2	470.0	485.6	497.3
67.5°	276.7	286.4	299.0	313.1	328.2	347.7	367.6	383.8	394.0	403.3	417.4
70°	242.4	250.2	260.4	271.3	287.6	307.1	322.7	335.2	342.2	351.6	368.7
72.5°	207.5	216.5	226.1	237.0	250.2	266.6	280.3	292.8	297.3	304.8	315.7
75°	163.7	168.4	176.2	184.0	193.3	207.4	220.6	223.7	227.6	233.9	241.6
77.5°	123.8	128.0	131.1	136.3	143.7	155.0	162.0	166.7	167.6	169.9	177.6
80°	98.2	100.6	103.7	107.6	110.7	120.0	123.9	128.6	130.2	132.5	136.4
82.5°	72.0	74.4	76.2	79.5	84.5	88.2	92.1	96.8	97.1	98.8	99.6
85°	42.1	42.9	41.3	42.9	43.7	45.2	49.1	53.0	52.2	51.4	53.8
87.5°	17.5	17.3	16.5	18.1	16.6	17.0	16.8	17.2	18.1	19.1	20.1
90°	12.7	11.9	10.7	9.6	8.4	7.3	6.0	4.7	3.4	2.1	0.7
92.5°	29.6	28.5	27.1	25.7	24.3	22.8	21.7	20.7	19.8	18.9	18.0
95°	58.3	57.2	55.5	53.9	52.2	50.6	49.6	49.2	48.9	48.6	48.3
97.5°	92.1	91.0	88.7	86.5	84.2	81.9	80.7	80.6	80.4	80.3	80.2
100°	115.1	113.6	111.4	109.3	107.1	105.0	103.9	103.9	103.9	103.9	103.9
102.5°	139.0	137.3	136.2	135.2	134.1	133.0	132.1	131.4	130.8	130.1	129.5
105°	178.4	177.4	176.4	175.4	174.5	173.5	172.6	171.7	170.9	170.1	169.3
107.5°	220.8	220.3	219.6	218.8	218.1	217.3	216.5	215.7	214.9	214.0	213.2
110°	249.9	249.4	248.9	248.4	247.9	247.4	246.8	246.0	245.1	244.3	243.5



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	279.4	279.1	278.5	277.9	277.2	276.6	276.1	275.7	275.2	274.8	274.4
115°	324.2	324.4	324.1	323.7	323.4	323.1	322.6	321.9	321.3	320.6	320.0
117.5°	368.5	368.4	368.1	367.8	367.5	367.2	366.9	366.6	366.3	366.0	365.7
120°	398.6	398.6	398.5	398.3	398.1	398.0	397.5	396.7	395.8	395.0	394.2
122.5°	428.2	428.3	427.9	427.5	427.0	426.6	426.3	426.0	425.7	425.4	425.1
125°	471.8	472.1	472.0	471.8	471.6	471.5	470.9	469.9	468.9	467.9	466.9
127.5°	514.7	514.9	514.7	514.5	514.3	514.1	513.7	513.2	512.6	512.0	511.5
130°	543.2	543.4	543.1	542.7	542.4	542.1	541.5	540.7	539.9	539.0	538.2
132.5°	570.6	570.7	570.8	570.8	570.9	571.0	570.3	569.0	567.6	566.3	564.9
135°	612.4	612.4	612.3	612.1	611.9	611.8	611.2	610.2	609.2	608.2	607.2
137.5°	653.2	653.0	652.6	652.2	651.9	651.5	650.9	649.9	648.9	648.0	647.0
140°	678.8	678.5	678.0	677.5	677.0	676.5	675.9	675.0	674.2	673.4	672.6
142.5°	704.2	704.0	703.4	702.8	702.2	701.5	700.9	700.2	699.5	698.8	698.1
145°	740.9	740.9	740.4	739.9	739.4	738.9	738.3	737.6	737.0	736.3	735.7
147.5°	774.2	773.8	773.4	773.0	772.6	772.2	771.9	771.5	771.1	770.8	770.4
150°	795.8	795.8	795.1	794.5	793.8	793.2	792.9	793.1	793.2	793.4	793.6
152.5°	815.2	814.8	814.5	814.3	814.0	813.7	813.5	813.3	813.0	812.8	812.6
155°	843.2	842.6	842.4	842.2	842.1	841.9	841.8	841.8	841.8	841.8	841.8
157.5°	867.7	867.1	866.9	866.7	866.6	866.4	866.5	866.9	867.2	867.6	868.0
160°	882.6	881.9	881.7	881.6	881.4	881.2	881.4	881.9	882.4	882.9	883.4
162.5°	896.4	895.6	895.5	895.5	895.5	895.4	895.6	896.0	896.3	896.7	897.1
165°	915.2	914.6	914.4	914.2	914.1	913.9	914.0	914.3	914.7	915.0	915.3
167.5°	928.8	927.8	927.8	927.8	927.8	927.8	928.1	928.8	929.4	930.1	930.8
170°	937.1	936.1	936.1	936.1	936.1	936.1	936.4	937.1	937.7	938.4	939.1
172.5°	943.0	942.0	942.0	942.0	942.0	942.0	942.4	943.0	943.7	944.3	945.0
175°	949.7	948.7	948.7	948.7	948.7	948.7	949.0	949.7	950.4	951.0	951.7
177.5°	952.9	952.1	952.3	952.4	952.5	952.7	953.0	953.5	954.0	954.6	955.1
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1908.2	1913.9	1922.0	1931.3	1938.8	1946.9	1951.3	1951.3	1955.0	1963.1	1973.7
5°	1913.7	1934.0	1953.5	1978.4	1997.9	2020.5	2037.6	2054.0	2068.8	2087.5	2107.0
7.5°	1912.1	1945.8	1980.9	2020.2	2063.5	2098.0	2133.4	2161.1	2188.6	2224.4	2252.6
10°	1905.9	1949.6	1997.1	2047.0	2101.6	2149.1	2192.0	2231.0	2268.4	2307.4	2342.4
12.5°	1894.7	1950.2	2008.3	2068.2	2137.1	2191.5	2246.9	2288.3	2332.0	2374.7	2417.9
15°	1877.8	1943.3	2013.5	2096.9	2181.1	2241.9	2296.4	2350.2	2390.8	2439.1	2480.4
17.5°	1843.1	1927.4	2015.7	2106.9	2187.8	2258.4	2315.6	2366.8	2409.9	2463.1	2519.2
20°	1822.5	1913.7	2005.7	2103.1	2180.3	2252.8	2308.1	2361.1	2414.9	2484.3	2552.9
22.5°	1793.8	1891.3	1988.8	2081.3	2162.8	2232.8	2290.1	2354.9	2425.5	2504.3	2587.2
25°	1748.4	1849.0	1945.7	2033.7	2113.3	2185.0	2262.9	2350.2	2436.0	2539.7	2658.9
27.5°	1690.9	1787.9	1874.1	1967.2	2046.2	2137.4	2234.7	2329.3	2453.0	2595.6	2744.5
30°	1647.9	1739.9	1821.7	1909.8	1999.4	2100.0	2209.1	2320.6	2467.9	2635.5	2812.5
32.5°	1598.0	1681.3	1762.5	1847.4	1950.8	2061.3	2177.3	2313.7	2489.8	2680.4	2863.6
35°	1511.5	1586.3	1665.0	1759.4	1869.3	1989.3	2137.4	2303.5	2516.3	2721.3	2885.8
37.5°	1420.7	1479.8	1558.9	1658.3	1778.1	1917.0	2085.0	2286.8	2505.4	2689.3	2759.3
40°	1350.9	1406.2	1489.6	1594.1	1712.6	1864.6	2053.2	2260.6	2480.4	2608.2	2602.8
42.5°	1281.7	1337.6	1417.9	1523.0	1646.5	1816.6	2010.8	2226.3	2411.8	2460.5	2359.0
45°	1175.5	1227.7	1306.5	1412.5	1545.0	1723.5	1927.7	2134.3	2252.8	2174.1	1972.9
47.5°	1067.3	1118.0	1191.1	1294.9	1439.6	1626.4	1819.5	1989.0	2005.7	1836.5	1595.3
50°	996.2	1043.8	1113.1	1223.8	1364.1	1546.6	1732.9	1866.2	1824.8	1618.3	1369.6
52.5°	927.0	972.7	1037.7	1142.1	1285.6	1464.2	1630.6	1735.2	1639.6	1420.0	1196.2
55°	824.7	868.4	933.9	1029.7	1159.9	1323.6	1469.4	1507.6	1367.3	1145.9	965.0
57.5°	727.6	759.6	824.3	909.1	1034.6	1178.9	1283.4	1276.5	1121.7	922.3	792.6
60°	663.4	692.2	753.8	831.7	951.0	1080.4	1153.7	1122.5	965.8	801.3	676.6
62.5°	603.5	630.5	682.1	753.8	856.2	968.8	1022.1	979.1	831.1	686.6	587.4
65°	512.9	532.4	573.7	640.0	720.3	798.2	845.8	782.6	651.7	542.5	467.7
67.5°	428.3	445.1	481.9	529.4	584.8	638.6	657.9	598.7	496.9	423.3	370.6
70°	373.4	389.0	413.9	458.4	495.0	533.2	542.5	489.5	404.6	348.4	315.7
72.5°	321.0	335.3	357.2	388.5	413.9	435.9	440.3	391.0	326.0	287.3	262.1
75°	244.8	257.2	271.3	283.0	299.3	303.2	301.7	263.5	228.4	202.7	188.6
77.5°	179.9	185.1	193.6	198.3	199.1	198.8	190.8	166.7	148.6	138.0	132.2
80°	138.8	142.7	145.0	146.5	147.3	139.5	131.0	116.1	109.9	103.7	96.7
82.5°	100.7	103.4	105.7	106.0	101.8	95.3	87.3	80.0	75.6	72.5	69.8
85°	54.6	55.3	54.6	50.7	45.2	42.9	41.3	39.8	39.0	38.2	38.2
87.5°	19.7	18.1	15.3	16.2	16.4	16.0	16.3	15.9	15.5	15.6	15.8
90°	2.1	3.4	4.7	6.0	7.3	8.4	9.6	10.7	11.9	12.7	13.5
92.5°	18.9	19.8	20.7	21.7	22.8	24.3	25.7	27.1	28.5	29.6	30.7
95°	48.6	48.9	49.2	49.6	50.6	52.2	53.9	55.5	57.2	58.3	59.5
97.5°	80.3	80.4	80.6	80.7	81.9	84.2	86.5	88.7	91.0	92.1	93.2
100°	103.9	103.9	103.9	103.9	105.0	107.1	109.3	111.4	113.6	115.1	116.5
102.5°	130.1	130.8	131.4	132.1	133.0	134.1	135.2	136.2	137.3	139.0	140.6
105°	170.1	170.9	171.7	172.6	173.5	174.5	175.4	176.4	177.4	178.4	179.4
107.5°	214.0	214.9	215.7	216.5	217.3	218.1	218.8	219.6	220.3	220.8	221.3
110°	244.3	245.1	246.0	246.8	247.4	247.9	248.4	248.9	249.4	249.9	250.4





TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	274.8	275.2	275.7	276.1	276.6	277.2	277.9	278.5	279.1	279.4	279.6
115°	320.6	321.3	321.9	322.6	323.1	323.4	323.7	324.1	324.4	324.2	324.1
117.5°	366.0	366.3	366.6	366.9	367.2	367.5	367.8	368.1	368.4	368.5	368.6
120°	395.0	395.8	396.7	397.5	398.0	398.1	398.3	398.5	398.6	398.6	398.6
122.5°	425.4	425.7	426.0	426.3	426.6	427.0	427.5	427.9	428.3	428.2	428.1
125°	467.9	468.9	469.9	470.9	471.5	471.6	471.8	472.0	472.1	471.8	471.5
127.5°	512.0	512.6	513.2	513.7	514.1	514.3	514.5	514.7	514.9	514.7	514.6
130°	539.0	539.9	540.7	541.5	542.1	542.4	542.7	543.1	543.4	543.2	543.1
132.5°	566.3	567.6	569.0	570.3	571.0	570.9	570.8	570.8	570.7	570.6	570.4
135°	608.2	609.2	610.2	611.2	611.8	611.9	612.1	612.3	612.4	612.4	612.4
137.5°	648.0	648.9	649.9	650.9	651.5	651.9	652.2	652.6	653.0	653.2	653.4
140°	673.4	674.2	675.0	675.9	676.5	677.0	677.5	678.0	678.5	678.8	679.2
142.5°	698.8	699.5	700.2	700.9	701.5	702.2	702.8	703.4	704.0	704.2	704.4
145°	736.3	737.0	737.6	738.3	738.9	739.4	739.9	740.4	740.9	740.9	740.9
147.5°	770.8	771.1	771.5	771.9	772.2	772.6	773.0	773.4	773.8	774.2	774.6
150°	793.4	793.2	793.1	792.9	793.2	793.8	794.5	795.1	795.8	795.8	795.8
152.5°	812.8	813.0	813.3	813.5	813.7	814.0	814.3	814.5	814.8	815.2	815.6
155°	841.8	841.8	841.8	841.8	841.9	842.1	842.2	842.4	842.6	843.2	843.9
157.5°	867.6	867.2	866.9	866.5	866.4	866.6	866.7	866.9	867.1	867.7	868.4
160°	882.9	882.4	881.9	881.4	881.2	881.4	881.6	881.7	881.9	882.6	883.2
162.5°	896.7	896.3	896.0	895.6	895.4	895.5	895.5	895.5	895.6	896.4	897.2
165°	915.0	914.7	914.3	914.0	913.9	914.1	914.2	914.4	914.6	915.2	915.9
167.5°	930.1	929.4	928.8	928.1	927.8	927.8	927.8	927.8	927.8	928.8	929.8
170°	938.4	937.7	937.1	936.4	936.1	936.1	936.1	936.1	936.1	937.1	938.1
172.5°	944.3	943.7	943.0	942.4	942.0	942.0	942.0	942.0	942.0	943.0	944.0
175°	951.0	950.4	949.7	949.0	948.7	948.7	948.7	948.7	948.7	949.7	950.7
177.5°	954.6	954.0	953.5	953.0	952.7	952.5	952.4	952.3	952.1	952.9	953.7
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9	1898.9
2.5°	1981.8	1981.8	1992.4	1991.8	1998.7	1996.2	1997.4
5°	2130.4	2143.7	2155.4	2163.1	2174.8	2178.0	2176.4
7.5°	2284.4	2313.9	2328.2	2347.9	2351.5	2361.8	2360.7
10°	2379.9	2408.7	2430.5	2447.7	2456.2	2467.2	2467.9
12.5°	2454.7	2479.2	2498.5	2514.4	2524.8	2528.3	2530.3
15°	2513.1	2540.4	2563.0	2585.6	2598.9	2609.0	2614.5
17.5°	2572.1	2614.2	2654.1	2684.8	2703.2	2718.8	2718.6
20°	2617.6	2665.9	2715.8	2750.9	2786.8	2802.3	2804.7
22.5°	2666.2	2740.1	2804.4	2858.8	2905.9	2922.1	2928.2
25°	2767.3	2863.9	2962.9	3039.3	3093.9	3125.8	3130.5
27.5°	2889.3	3020.1	3124.3	3194.8	3240.1	3263.8	3269.0
30°	2975.4	3096.2	3189.8	3242.8	3263.8	3266.9	3255.2
32.5°	3014.1	3104.3	3141.7	3138.6	3097.3	3069.9	3059.4
35°	2966.8	2948.1	2856.9	2747.8	2664.4	2611.4	2597.3
37.5°	2699.9	2538.6	2370.8	2205.9	2118.1	2073.5	1996.8
40°	2436.8	2206.8	2032.2	1893.4	1794.4	1714.9	1696.2
42.5°	2139.9	1902.5	1727.9	1609.1	1530.0	1475.5	1451.8
45°	1719.6	1515.4	1371.2	1280.0	1219.2	1179.4	1161.5
47.5°	1375.4	1217.3	1112.2	1044.7	998.4	963.8	954.1
50°	1186.4	1060.1	971.3	914.4	879.3	852.8	841.9
52.5°	1030.5	928.6	860.3	813.3	780.1	763.6	754.6
55°	850.4	762.4	713.3	675.8	657.1	643.9	637.6
57.5°	695.5	631.9	596.0	570.1	552.8	544.4	541.3
60°	608.8	558.9	526.2	505.9	494.2	483.3	480.2
62.5°	532.1	492.8	467.6	449.8	438.1	433.4	431.5
65°	428.7	403.0	384.3	373.4	364.0	362.5	361.7
67.5°	340.8	325.7	315.9	304.5	301.2	295.7	294.7
70°	291.5	281.4	269.7	265.8	261.9	256.5	257.2
72.5°	247.3	237.1	229.2	224.0	222.6	220.3	222.3
75°	180.8	177.7	174.6	170.7	169.2	169.2	168.4
77.5°	129.1	126.4	123.0	120.7	120.2	116.9	118.2
80°	93.5	89.6	88.1	88.9	86.5	85.7	85.7
82.5°	69.2	67.8	66.3	66.4	65.9	65.2	65.8
85°	38.2	37.4	37.4	36.6	36.6	35.9	35.9
87.5°	16.6	17.4	16.3	15.7	15.8	16.6	17.3
90°	14.4	15.2	15.8	16.3	16.8	17.3	17.8
92.5°	31.8	32.9	33.6	34.0	34.3	34.7	35.0
95°	60.6	61.8	62.5	62.9	63.2	63.5	63.8
97.5°	94.3	95.4	96.0	96.2	96.4	96.6	96.8
100°	118.0	119.5	120.4	120.8	121.1	121.4	121.7
102.5°	142.2	143.8	144.8	145.3	145.8	146.2	146.7
105°	180.4	181.4	182.1	182.6	183.1	183.6	184.1
107.5°	221.8	222.3	222.5	222.5	222.5	222.4	222.4
110°	250.9	251.4	251.6	251.4	251.2	251.1	250.9



TEST NUMBER: P333725

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	279.8	280.0	280.0	279.7	279.4	279.1	278.8
115°	323.9	323.7	323.6	323.4	323.3	323.1	322.9
117.5°	368.7	368.9	368.6	368.0	367.3	366.6	366.0
120°	398.6	398.6	398.3	397.7	397.0	396.3	395.7
122.5°	427.9	427.8	427.5	426.9	426.4	425.9	425.4
125°	471.1	470.8	470.6	470.4	470.2	470.1	469.9
127.5°	514.4	514.2	514.0	513.7	513.3	513.0	512.7
130°	542.9	542.7	542.5	542.2	541.8	541.5	541.2
132.5°	570.2	570.1	569.7	569.3	568.8	568.4	567.9
135°	612.4	612.4	612.1	611.4	610.8	610.1	609.5
137.5°	653.6	653.8	653.4	652.6	651.8	651.0	650.1
140°	679.5	679.8	679.6	678.8	677.9	677.1	676.3
142.5°	704.6	704.8	704.5	703.7	702.9	702.0	701.2
145°	740.9	740.9	740.6	740.1	739.6	739.1	738.6
147.5°	775.0	775.4	775.0	773.9	772.8	771.7	770.6
150°	795.8	795.8	795.6	795.3	795.0	794.6	794.3
152.5°	816.0	816.4	816.3	815.7	815.1	814.5	813.9
155°	844.5	845.2	845.1	844.3	843.5	842.6	841.8
157.5°	869.0	869.7	869.5	868.4	867.3	866.2	865.1
160°	883.9	884.5	884.5	883.6	882.8	882.0	881.2
162.5°	897.9	898.7	898.7	897.7	896.7	895.8	894.8
165°	916.6	917.2	917.0	916.1	915.1	914.1	913.1
167.5°	930.8	931.7	931.7	930.7	929.7	928.7	927.6
170°	939.1	940.1	940.0	938.8	937.7	936.5	935.4
172.5°	945.0	946.0	946.0	945.0	943.9	942.9	941.9
175°	951.7	952.7	952.6	951.4	950.3	949.1	948.0
177.5°	954.5	955.3	955.2	954.3	953.4	952.5	951.5
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9

(END OF REPORT)