

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333698-927

Luminaire Tested: **S125RDIW-S850D1560U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333698-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1560U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7516.8 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333698-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333698-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42	34			34
1	94	90	87	83	85	82	79	76	66	63	61	51	49	48	37	36	35	29			29
2	86	79	73	68	77	71	67	62	58	54	51	45	42	40	33	31	30	25			25
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21			21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18			18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	24	21	19	16			16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14			14
7	56	44	36	31	50	40	34	29	33	28	24	26	22	20	20	17	15	12			12
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	15	14	11			11
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12	10			10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11	9			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7035	7035	7035
5°	7052	6971	7014
10°	6998	6906	6906
15°	6915	6766	6711
20°	6808	6570	6491
25°	6683	6379	6238
30°	6528	6154	5957
35°	6370	5922	5643
40°	6222	5681	5334
45°	6042	5411	4997
50°	5861	5117	4646
55°	5650	4835	4271
60°	5441	4495	3867
65°	5193	4099	3406
70°	4910	3603	2936
75°	4517	3039	2443
80°	3976	2388	2049
85°	3349	1949	1830



TEST NUMBER: P333698-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.4	1.4
10°-20°	286.2	3.8
20°-30°	415.1	5.5
30°-40°	473.1	6.3
40°-50°	461.1	6.1
50°-60°	388.2	5.2
60°-70°	272.1	3.6
70°-80°	139.9	1.9
80°-90°	38.7	0.5
90°-100°	58.5	0.8
100°-110°	360.3	4.8
110°-120°	653.4	8.7
120°-130°	838.6	11.2
130°-140°	902.0	12.0
140°-150°	846.7	11.3
150°-160°	684.9	9.1
160°-170°	442.9	5.9
170°-180°	152.8	2.0
0°-30°	803.8	10.7
0°-40°	1276.8	17.0
0°-60°	2126.1	28.3
0°-90°	2576.8	34.3
90°-120°	1072.2	14.3
90°-150°	3659.5	48.7
90°-180°	4940.0	65.7
0°-180°	7516.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1089	1089	1089	1089	1089	
5°	1088	1084	1075	1083	1082	103
15°	1034	1029	1012	1011	1004	291
25°	938	925	895	885	875	431
35°	808	787	751	728	716	506
45°	662	636	592	561	547	510
55°	502	474	429	394	379	449
65°	340	311	268	236	223	336
75°	181	156	122	104	98	192
85°	45	31	26	26	25	51
90°	1	11	19	25	29	5
95°	68	62	19	25	25	87
105°	351	355	355	355	354	372
115°	658	664	665	661	654	652
125°	936	944	944	940	936	836
135°	1167	1174	1172	1170	1163	900
145°	1354	1356	1356	1357	1350	846
155°	1491	1484	1486	1489	1480	686
165°	1573	1566	1567	1573	1565	444
175°	1609	1602	1603	1611	1602	153
180°	1609	1609	1609	1609	1609	



TEST NUMBER: P333698-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1091.2	1090.8	1090.4	1090.0	1089.5	1088.5	1087.1	1085.6	1084.2	1082.7	1084.2
5°	1087.7	1087.0	1086.2	1085.4	1084.7	1083.4	1081.3	1079.3	1077.3	1075.3	1077.1
7.5°	1077.0	1076.3	1075.5	1074.8	1074.2	1072.6	1070.2	1067.8	1065.4	1063.0	1064.2
10°	1067.1	1066.5	1066.0	1065.4	1064.9	1063.3	1060.8	1058.2	1055.7	1053.1	1053.6
12.5°	1055.9	1055.2	1054.5	1053.8	1053.1	1051.1	1047.6	1044.2	1040.8	1037.3	1037.7
15°	1034.2	1033.1	1032.0	1030.9	1029.8	1027.3	1023.5	1019.6	1015.8	1011.9	1011.8
17.5°	1009.6	1008.0	1006.3	1004.6	1002.9	999.7	994.8	990.0	985.2	980.3	979.5
20°	990.5	988.7	986.9	985.1	983.3	979.4	973.6	967.7	961.9	956.0	955.1
22.5°	969.5	967.7	965.8	964.0	962.2	958.2	952.0	945.9	939.8	933.7	931.8
25°	937.9	935.2	932.4	929.7	926.9	922.2	915.4	908.6	901.9	895.2	892.8
27.5°	901.7	898.4	895.1	891.8	888.4	883.1	875.9	868.6	861.4	854.1	850.8
30°	875.4	871.9	868.5	865.0	861.5	855.9	848.3	840.6	832.9	825.2	821.0
32.5°	849.7	845.7	841.6	837.6	833.5	827.5	819.8	811.9	804.1	796.2	791.6
35°	807.9	803.5	799.2	794.7	790.4	784.0	775.9	767.6	759.4	751.1	745.8
37.5°	766.9	761.6	756.3	750.9	745.6	738.7	730.2	721.7	713.2	704.7	698.4
40°	738.0	732.5	727.0	721.5	716.1	708.9	700.1	691.3	682.6	673.8	666.9
42.5°	707.7	702.1	696.5	690.8	685.2	677.9	668.8	659.7	650.6	641.6	634.9
45°	661.5	656.2	650.9	645.5	640.2	632.6	622.5	612.5	602.5	592.4	585.0
47.5°	613.6	608.0	602.4	596.8	591.2	583.4	573.2	563.1	552.9	542.8	535.3
50°	583.3	577.3	571.2	565.2	559.2	551.0	540.5	530.1	519.7	509.3	501.6
52.5°	550.4	544.2	538.1	531.9	525.7	517.7	507.9	498.0	488.1	478.3	470.1
55°	501.8	496.0	490.2	484.3	478.5	470.4	460.2	450.0	439.7	429.4	421.2
57.5°	452.8	446.6	440.3	434.0	427.9	419.8	409.9	400.0	390.1	380.2	372.2
60°	421.2	414.9	408.4	402.0	395.6	387.5	377.6	367.7	357.9	348.0	340.0
62.5°	387.7	381.6	375.5	369.3	363.2	355.2	345.2	335.2	325.1	315.1	307.7
65°	339.8	333.6	327.3	321.2	314.9	307.0	297.3	287.6	277.9	268.2	260.9
67.5°	292.2	286.0	279.8	273.6	267.4	259.6	250.3	241.1	231.8	222.4	215.8
70°	260.0	253.7	247.6	241.3	235.1	227.4	218.3	209.1	200.0	190.8	185.2
72.5°	228.4	222.3	216.3	210.2	204.1	196.8	188.2	179.7	171.1	162.6	157.3
75°	181.0	175.5	170.0	164.5	159.1	152.5	144.8	137.1	129.4	121.8	117.7
77.5°	134.0	129.5	125.2	120.8	116.4	111.1	105.0	98.9	92.7	86.6	83.7
80°	106.9	102.6	98.2	93.8	89.4	84.7	79.5	74.4	69.3	64.2	62.5
82.5°	80.6	76.7	72.7	68.8	64.8	61.1	57.6	54.1	50.5	47.1	46.3
85°	45.2	42.0	38.7	35.4	32.1	29.9	29.1	28.1	27.3	26.3	26.1
87.5°	15.4	14.8	14.2	13.5	13.0	12.8	13.0	13.2	13.5	13.7	13.9
90°	1.2	3.3	5.5	7.5	9.7	11.6	13.5	15.4	17.2	19.1	20.4
92.5°	18.4	16.9	15.4	13.9	12.4	12.5	14.2	15.8	17.4	19.1	20.4
95°	68.0	67.2	66.4	65.6	64.8	59.3	49.3	39.2	29.2	19.1	20.4
97.5°	141.9	143.3	144.7	146.2	147.7	138.4	118.4	98.5	78.6	58.7	51.2
100°	199.2	199.9	200.7	201.5	202.3	203.3	204.3	205.4	206.4	207.5	168.0
102.5°	257.4	258.3	259.4	260.4	261.3	262.2	262.8	263.5	264.1	264.7	257.3
105°	350.6	351.6	352.8	353.8	354.8	355.4	355.4	355.4	355.4	355.4	355.4
107.5°	447.4	447.4	447.4	447.4	447.4	447.7	448.2	448.8	449.3	449.8	449.9
110°	510.4	510.4	510.4	510.4	510.4	510.6	511.2	511.7	512.2	512.8	512.0



TEST NUMBER: P333698-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	569.6	570.2	570.8	571.5	572.1	572.6	572.9	573.2	573.5	573.9	572.8
115°	658.3	659.6	660.9	662.3	663.5	664.3	664.6	664.9	665.2	665.4	664.3
117.5°	750.1	750.0	750.0	750.0	749.9	750.4	751.4	752.3	753.4	754.4	753.0
120°	807.3	807.1	806.8	806.5	806.3	806.5	807.3	808.1	808.9	809.7	809.2
122.5°	857.9	858.9	859.9	860.9	861.9	862.6	863.0	863.3	863.7	864.1	863.6
125°	936.1	937.9	939.8	941.7	943.6	944.4	944.4	944.4	944.4	944.4	943.4
127.5°	1010.7	1012.1	1013.4	1014.8	1016.1	1016.7	1016.5	1016.4	1016.2	1016.1	1015.4
130°	1056.5	1057.9	1059.2	1060.6	1061.8	1062.6	1063.0	1063.2	1063.4	1063.7	1063.0
132.5°	1102.3	1103.9	1105.4	1107.0	1108.5	1109.0	1108.4	1107.8	1107.2	1106.7	1106.5
135°	1167.4	1169.0	1170.7	1172.3	1173.9	1174.3	1173.9	1173.3	1172.7	1172.3	1171.7
137.5°	1227.3	1228.7	1230.1	1231.4	1232.9	1233.3	1232.8	1232.3	1231.8	1231.4	1231.5
140°	1266.5	1267.0	1267.5	1268.0	1268.6	1268.7	1268.4	1268.2	1267.9	1267.7	1268.2
142.5°	1301.7	1302.0	1302.3	1302.7	1303.0	1303.4	1303.8	1304.1	1304.5	1304.9	1305.0
145°	1353.5	1354.0	1354.6	1355.1	1355.7	1355.9	1355.9	1355.9	1355.9	1355.9	1356.1
147.5°	1398.8	1398.7	1398.6	1398.5	1398.4	1398.5	1398.8	1399.2	1399.5	1399.8	1400.1
150°	1427.4	1426.9	1426.4	1425.8	1425.3	1425.3	1425.8	1426.4	1426.9	1427.4	1428.0
152.5°	1455.1	1454.0	1452.8	1451.6	1450.4	1450.1	1450.6	1451.2	1451.8	1452.2	1452.8
155°	1490.6	1489.1	1487.5	1485.9	1484.3	1483.8	1484.3	1484.8	1485.3	1485.9	1486.7
157.5°	1518.1	1517.1	1516.2	1515.2	1514.3	1513.8	1513.9	1513.9	1513.9	1514.0	1514.9
160°	1537.2	1535.6	1534.0	1532.4	1530.8	1530.1	1530.4	1530.7	1530.9	1531.2	1532.2
162.5°	1552.4	1550.9	1549.3	1547.6	1546.0	1545.4	1545.6	1545.9	1546.2	1546.4	1547.9
165°	1573.0	1571.4	1569.7	1568.1	1566.5	1565.9	1566.1	1566.5	1566.7	1566.9	1568.5
167.5°	1588.2	1586.6	1584.9	1583.3	1581.6	1581.0	1581.2	1581.4	1581.8	1582.0	1583.9
170°	1596.8	1594.9	1593.1	1591.2	1589.4	1588.6	1588.8	1589.1	1589.4	1589.6	1591.7
172.5°	1602.5	1600.7	1598.8	1597.0	1595.1	1594.4	1594.9	1595.4	1595.9	1596.3	1598.2
175°	1608.7	1607.1	1605.5	1603.9	1602.3	1601.7	1602.0	1602.2	1602.5	1602.7	1604.9
177.5°	1611.5	1610.3	1609.0	1607.7	1606.5	1605.9	1606.1	1606.4	1606.5	1606.8	1608.3
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7



TEST NUMBER: P333698-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1085.6	1087.1	1088.5	1089.3	1089.1	1088.9	1088.8	1088.6
5°	1079.0	1080.8	1082.6	1083.4	1083.0	1082.6	1082.3	1081.9
7.5°	1065.6	1066.8	1068.1	1068.5	1068.1	1067.7	1067.3	1066.9
10°	1054.2	1054.7	1055.3	1055.3	1054.7	1054.2	1053.6	1053.1
12.5°	1038.1	1038.5	1038.9	1038.7	1037.8	1037.0	1036.2	1035.3
15°	1011.6	1011.4	1011.2	1010.3	1008.7	1007.0	1005.4	1003.7
17.5°	978.5	977.6	976.7	975.6	974.2	972.9	971.5	970.2
20°	954.2	953.2	952.4	951.1	949.4	947.8	946.1	944.5
22.5°	930.0	928.3	926.5	924.9	923.5	922.2	920.8	919.5
25°	890.4	888.0	885.7	883.4	881.4	879.4	877.4	875.4
27.5°	847.5	844.1	840.8	838.2	836.3	834.3	832.4	830.4
30°	816.8	812.6	808.3	805.5	803.8	802.2	800.5	798.8
32.5°	787.0	782.3	777.7	774.3	772.2	770.2	768.0	766.0
35°	740.5	735.2	729.9	726.0	723.4	720.9	718.4	715.7
37.5°	692.1	685.6	679.3	674.9	672.4	669.9	667.4	665.0
40°	659.9	653.0	646.0	641.4	639.3	637.1	634.9	632.7
42.5°	628.3	621.6	615.0	610.0	606.8	603.6	600.3	597.1
45°	577.7	570.5	563.1	558.1	555.3	552.6	549.9	547.1
47.5°	527.8	520.2	512.7	507.4	504.4	501.4	498.3	495.3
50°	493.9	486.2	478.6	473.3	470.6	467.9	465.1	462.4
52.5°	461.8	453.5	445.3	439.7	437.0	434.3	431.6	428.8
55°	413.0	404.8	396.6	390.9	388.1	385.2	382.2	379.3
57.5°	364.2	356.2	348.1	342.8	340.2	337.5	335.0	332.4
60°	331.9	323.8	315.8	310.5	307.7	305.0	302.2	299.4
62.5°	300.2	292.7	285.3	280.2	277.4	274.6	272.0	269.2
65°	253.6	246.3	238.9	233.9	231.2	228.5	225.7	222.9
67.5°	209.1	202.4	195.7	191.2	189.1	186.9	184.7	182.5
70°	179.5	173.9	168.2	164.3	162.1	159.9	157.7	155.5
72.5°	152.1	146.9	141.6	138.3	136.8	135.4	134.0	132.5
75°	113.8	109.7	105.7	103.1	101.7	100.4	99.2	97.9
77.5°	80.9	78.1	75.3	73.4	72.5	71.5	70.6	69.6
80°	60.9	59.3	57.6	56.6	56.2	55.8	55.5	55.1
82.5°	45.6	44.8	44.0	43.5	43.3	43.1	42.9	42.6
85°	26.0	25.7	25.6	25.4	25.2	25.0	24.9	24.7
87.5°	14.2	14.5	14.7	14.9	14.9	14.9	14.9	15.0
90°	21.7	23.1	24.4	25.4	26.2	27.0	27.8	28.6
92.5°	21.7	23.1	24.4	25.2	25.6	26.0	26.4	26.7
95°	21.7	23.1	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	43.7	36.3	28.8	25.0	25.0	25.0	25.0	25.0
100°	128.5	89.0	49.6	29.3	28.2	27.2	26.1	25.0
102.5°	249.8	242.3	234.9	222.1	204.1	186.1	168.0	150.0
105°	355.4	355.4	355.4	355.2	355.0	354.7	354.4	354.2
107.5°	450.0	450.0	450.0	449.6	448.9	448.1	447.3	446.5
110°	511.2	510.4	509.6	509.4	509.6	509.8	510.2	510.4



TEST NUMBER: P333698-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	571.8	570.8	569.8	569.1	568.8	568.4	568.0	567.6
115°	663.3	662.3	661.2	659.9	658.3	656.6	655.1	653.5
117.5°	751.6	750.3	748.8	747.8	747.2	746.5	745.8	745.0
120°	808.7	808.1	807.6	806.7	805.3	804.0	802.7	801.4
122.5°	863.0	862.5	862.0	860.9	859.4	857.9	856.3	854.8
125°	942.4	941.3	940.2	939.3	938.5	937.7	936.9	936.1
127.5°	1014.9	1014.3	1013.7	1012.4	1010.4	1008.5	1006.5	1004.6
130°	1062.2	1061.4	1060.6	1059.5	1058.2	1056.9	1055.5	1054.2
132.5°	1106.4	1106.2	1106.0	1105.3	1104.0	1102.6	1101.3	1099.9
135°	1171.2	1170.7	1170.1	1169.0	1167.4	1165.9	1164.3	1162.7
137.5°	1231.6	1231.7	1231.8	1231.2	1229.8	1228.4	1227.0	1225.7
140°	1268.7	1269.2	1269.8	1269.2	1267.7	1266.1	1264.5	1262.9
142.5°	1305.0	1305.2	1305.3	1304.6	1302.9	1301.3	1299.7	1298.1
145°	1356.5	1356.7	1356.9	1356.3	1354.7	1353.1	1351.5	1350.0
147.5°	1400.4	1400.7	1401.1	1400.3	1398.4	1396.5	1394.6	1392.7
150°	1428.5	1429.0	1429.6	1428.8	1426.6	1424.5	1422.4	1420.3
152.5°	1453.3	1453.8	1454.4	1453.7	1451.8	1449.9	1448.0	1446.0
155°	1487.5	1488.3	1489.1	1488.4	1486.3	1484.2	1482.0	1479.9
157.5°	1515.7	1516.6	1517.4	1516.8	1514.7	1512.5	1510.4	1508.3
160°	1533.3	1534.4	1535.4	1534.9	1532.8	1530.7	1528.5	1526.5
162.5°	1549.4	1550.9	1552.4	1552.0	1549.7	1547.3	1545.0	1542.6
165°	1570.1	1571.8	1573.4	1573.0	1571.0	1568.8	1566.7	1564.6
167.5°	1585.8	1587.7	1589.6	1589.4	1587.0	1584.6	1582.2	1579.8
170°	1593.9	1596.0	1598.1	1598.0	1595.6	1593.2	1590.8	1588.4
172.5°	1600.1	1602.0	1603.9	1603.7	1601.3	1598.9	1596.6	1594.2
175°	1606.9	1609.1	1611.2	1611.1	1608.7	1606.3	1603.9	1601.6
177.5°	1609.8	1611.2	1612.7	1612.6	1610.9	1609.2	1607.5	1605.8
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7

(END OF REPORT)