

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333726

Luminaire Tested: **S125RDIW-S1270D770U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333726
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D770U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7948.3 lumens
Efficiency: N/A
Efficacy: 132.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333726

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333726

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	50	48	44
3	84	74	67	61	78	70	63	58	62	57	52	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	45	39	34	39	35	31	34	31	28	25
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25	22
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13332	13332	13332
5°	13363	13211	13291
10°	13262	13088	13088
15°	13104	12822	12718
20°	12902	12451	12302
25°	12666	12088	11821
30°	12371	11662	11290
35°	12071	11223	10694
40°	11790	10765	10108
45°	11449	10253	9470
50°	11106	9697	8804
55°	10709	9164	8094
60°	10311	8519	7330
65°	9840	7768	6457
70°	9304	6830	5565
75°	8559	5757	4629
80°	7539	4523	3887
85°	6358	3698	3468



TEST NUMBER: P333726

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.1	2.4
10°-20°	542.5	6.8
20°-30°	786.6	9.9
30°-40°	896.5	11.3
40°-50°	873.9	11.0
50°-60°	735.6	9.3
60°-70°	515.6	6.5
70°-80°	265.0	3.3
80°-90°	69.0	0.9
90°-100°	36.3	0.5
100°-110°	223.9	2.8
110°-120°	406.0	5.1
120°-130°	521.1	6.6
130°-140°	560.5	7.1
140°-150°	526.1	6.6
150°-160°	425.5	5.4
160°-170°	275.2	3.5
170°-180°	94.9	1.2
0°-30°	1523.2	19.2
0°-40°	2419.7	30.4
0°-60°	4029.1	50.7
0°-90°	4878.8	61.4
90°-120°	666.2	8.4
90°-150°	2273.8	28.6
90°-180°	3069.0	38.6
0°-180°	7948.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2064	2064	2064	2064	2064	
5°	2061	2054	2038	2052	2050	195
15°	1960	1949	1918	1915	1902	552
25°	1777	1752	1696	1676	1659	817
35°	1531	1492	1424	1380	1356	958
45°	1254	1206	1123	1062	1037	967
55°	951	899	814	746	719	850
65°	644	589	508	448	422	638
75°	343	295	231	198	186	363
85°	86	59	50	48	47	96
90°	1	7	12	15	18	6
95°	42	39	12	15	16	54
105°	218	221	221	221	220	231
115°	409	413	414	410	406	405
125°	582	587	587	584	582	519
135°	725	730	728	727	722	559
145°	841	842	842	843	839	526
155°	926	922	923	925	920	427
165°	977	973	974	978	972	276
175°	1000	995	996	1001	995	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P333726

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2068.0	2067.2	2066.3	2065.5	2064.7	2062.9	2060.1	2057.3	2054.6	2051.8	2054.6
5°	2061.2	2059.8	2058.4	2057.0	2055.6	2053.0	2049.2	2045.4	2041.6	2037.8	2041.2
7.5°	2040.9	2039.6	2038.3	2036.9	2035.6	2032.7	2028.1	2023.5	2019.0	2014.4	2016.8
10°	2022.2	2021.1	2020.1	2019.1	2018.0	2015.1	2010.2	2005.4	2000.5	1995.7	1996.7
12.5°	2001.0	1999.7	1998.3	1997.0	1995.7	1991.8	1985.3	1978.8	1972.2	1965.7	1966.5
15°	1959.8	1957.7	1955.7	1953.6	1951.5	1946.8	1939.5	1932.3	1925.0	1917.7	1917.4
17.5°	1913.3	1910.2	1907.0	1903.8	1900.6	1894.4	1885.3	1876.1	1867.0	1857.8	1856.1
20°	1877.2	1873.7	1870.2	1866.8	1863.3	1856.0	1845.0	1833.9	1822.8	1811.7	1810.0
22.5°	1837.3	1833.8	1830.3	1826.9	1823.4	1815.9	1804.2	1792.6	1780.9	1769.3	1765.9
25°	1777.4	1772.2	1767.0	1761.8	1756.6	1747.6	1734.8	1722.0	1709.1	1696.3	1691.8
27.5°	1708.8	1702.5	1696.2	1689.9	1683.6	1673.6	1659.8	1646.1	1632.4	1618.7	1612.4
30°	1658.9	1652.3	1645.7	1639.2	1632.6	1622.0	1607.4	1592.9	1578.3	1563.8	1555.8
32.5°	1610.3	1602.6	1594.9	1587.2	1579.5	1568.2	1553.4	1538.6	1523.7	1508.9	1500.1
35°	1531.1	1522.7	1514.4	1506.1	1497.8	1485.8	1470.2	1454.7	1439.1	1423.5	1413.4
37.5°	1453.4	1443.3	1433.2	1423.1	1412.9	1399.8	1383.8	1367.7	1351.6	1335.5	1323.5
40°	1398.5	1388.1	1377.7	1367.3	1357.0	1343.4	1326.8	1310.2	1293.5	1276.9	1263.8
42.5°	1341.2	1330.5	1319.8	1309.1	1298.5	1284.5	1267.4	1250.2	1233.0	1215.8	1203.2
45°	1253.5	1243.5	1233.4	1223.4	1213.3	1198.8	1179.7	1160.7	1141.6	1122.6	1108.7
47.5°	1162.8	1152.2	1141.6	1131.0	1120.4	1105.5	1086.3	1067.1	1047.9	1028.7	1014.4
50°	1105.4	1094.0	1082.5	1071.1	1059.7	1044.1	1024.3	1004.6	984.8	965.1	950.5
52.5°	1043.0	1031.3	1019.6	1007.9	996.2	981.0	962.4	943.8	925.1	906.5	890.8
55°	951.1	940.0	928.9	917.8	906.7	891.5	872.1	852.7	833.3	813.9	798.3
57.5°	858.1	846.3	834.4	822.6	810.7	795.5	776.8	758.0	739.3	720.6	705.4
60°	798.3	786.1	774.0	761.9	749.8	734.3	715.6	696.9	678.2	659.5	644.3
62.5°	734.7	723.1	711.5	699.9	688.4	673.1	654.1	635.1	616.1	597.1	583.0
65°	643.9	632.1	620.4	608.6	596.8	581.7	563.4	545.0	526.6	508.3	494.4
67.5°	553.8	542.0	530.2	518.5	506.7	492.0	474.4	456.8	439.2	421.6	408.9
70°	492.7	480.9	469.1	457.3	445.6	431.0	413.7	396.4	379.0	361.7	351.0
72.5°	432.8	421.3	409.8	398.3	386.8	372.9	356.7	340.5	324.3	308.1	298.2
75°	343.0	332.6	322.2	311.8	301.4	289.0	274.4	259.9	245.3	230.7	223.1
77.5°	253.8	245.5	237.2	228.9	220.6	210.6	198.9	187.3	175.7	164.0	158.7
80°	202.7	194.4	186.1	177.7	169.4	160.4	150.7	141.0	131.3	121.6	118.5
82.5°	152.8	145.3	137.8	130.3	122.9	115.8	109.1	102.5	95.8	89.2	87.7
85°	85.8	79.5	73.3	67.0	60.8	56.8	55.1	53.4	51.6	49.9	49.5
87.5°	28.8	27.2	25.5	23.8	22.1	21.3	21.2	21.2	21.1	21.1	21.2
90°	0.7	2.1	3.4	4.7	6.0	7.2	8.4	9.6	10.7	11.9	12.7
92.5°	11.4	10.5	9.6	8.6	7.7	7.8	8.8	9.8	10.8	11.9	12.7
95°	42.2	41.7	41.2	40.8	40.3	36.9	30.6	24.4	18.1	11.9	12.7
97.5°	88.2	89.1	90.0	90.8	91.7	86.0	73.6	61.2	48.8	36.5	31.8
100°	123.7	124.2	124.7	125.2	125.7	126.3	127.0	127.6	128.3	128.9	104.4
102.5°	159.9	160.5	161.2	161.8	162.4	162.9	163.3	163.7	164.1	164.5	159.9
105°	217.8	218.5	219.2	219.8	220.5	220.8	220.8	220.8	220.8	220.8	220.8
107.5°	278.0	278.0	278.0	278.0	278.0	278.2	278.5	278.8	279.2	279.5	279.5
110°	317.1	317.1	317.1	317.1	317.1	317.3	317.6	318.0	318.3	318.6	318.1



TEST NUMBER: P333726

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	353.9	354.3	354.7	355.1	355.5	355.8	356.0	356.2	356.4	356.6	355.9
115°	409.0	409.8	410.7	411.5	412.3	412.8	413.0	413.1	413.3	413.5	412.8
117.5°	466.1	466.0	466.0	466.0	465.9	466.2	466.9	467.5	468.1	468.7	467.9
120°	501.6	501.5	501.3	501.1	501.0	501.1	501.6	502.1	502.6	503.1	502.8
122.5°	533.0	533.7	534.3	534.9	535.6	536.0	536.2	536.4	536.7	536.9	536.6
125°	581.7	582.8	584.0	585.1	586.3	586.8	586.8	586.8	586.8	586.8	586.2
127.5°	628.0	628.9	629.7	630.5	631.3	631.7	631.6	631.5	631.4	631.3	630.9
130°	656.5	657.3	658.1	659.0	659.8	660.3	660.4	660.6	660.8	660.9	660.4
132.5°	684.9	685.9	686.9	687.8	688.8	689.1	688.7	688.3	688.0	687.6	687.5
135°	725.4	726.4	727.4	728.4	729.4	729.7	729.4	729.0	728.7	728.4	728.0
137.5°	762.6	763.5	764.3	765.2	766.0	766.3	766.0	765.7	765.4	765.1	765.2
140°	786.9	787.2	787.6	787.9	788.2	788.3	788.1	788.0	787.8	787.6	788.0
142.5°	808.8	809.0	809.2	809.4	809.6	809.8	810.1	810.3	810.5	810.8	810.8
145°	841.0	841.3	841.7	842.0	842.3	842.5	842.5	842.5	842.5	842.5	842.6
147.5°	869.2	869.1	869.0	869.0	868.9	869.0	869.2	869.3	869.5	869.7	869.9
150°	886.9	886.6	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9	887.3
152.5°	904.1	903.4	902.7	902.0	901.2	901.0	901.4	901.7	902.0	902.3	902.7
155°	926.2	925.2	924.2	923.2	922.3	921.9	922.3	922.6	922.9	923.2	923.7
157.5°	943.2	942.7	942.1	941.5	940.9	940.6	940.6	940.7	940.7	940.7	941.3
160°	955.1	954.1	953.1	952.1	951.2	950.7	950.9	951.1	951.2	951.4	952.1
162.5°	964.6	963.6	962.6	961.6	960.6	960.2	960.4	960.6	960.7	960.9	961.8
165°	977.3	976.3	975.4	974.4	973.4	973.0	973.1	973.3	973.5	973.6	974.6
167.5°	986.8	985.8	984.8	983.8	982.7	982.3	982.5	982.6	982.8	983.0	984.1
170°	992.2	991.0	989.8	988.7	987.5	987.0	987.2	987.4	987.5	987.7	989.0
172.5°	995.7	994.6	993.4	992.2	991.1	990.7	991.0	991.3	991.6	991.9	993.0
175°	999.6	998.6	997.6	996.6	995.6	995.2	995.4	995.5	995.7	995.9	997.2
177.5°	1001.3	1000.5	999.8	999.0	998.2	997.8	998.0	998.1	998.2	998.4	999.3
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333726

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3	2064.3
2.5°	2057.3	2060.1	2062.9	2064.1	2063.9	2063.6	2063.3	2063.0
5°	2044.7	2048.2	2051.6	2053.0	2052.3	2051.6	2050.9	2050.2
7.5°	2019.2	2021.7	2024.1	2024.9	2024.1	2023.4	2022.6	2021.9
10°	1997.7	1998.8	1999.8	1999.8	1998.8	1997.7	1996.7	1995.7
12.5°	1967.3	1968.0	1968.8	1968.4	1966.8	1965.2	1963.6	1962.0
15°	1917.0	1916.7	1916.3	1914.6	1911.5	1908.4	1905.2	1902.1
17.5°	1854.4	1852.6	1850.9	1848.8	1846.2	1843.6	1841.1	1838.5
20°	1808.2	1806.5	1804.8	1802.3	1799.2	1796.1	1793.0	1789.9
22.5°	1762.5	1759.1	1755.7	1752.7	1750.2	1747.6	1745.0	1742.5
25°	1687.3	1682.8	1678.3	1674.1	1670.3	1666.5	1662.7	1658.9
27.5°	1606.1	1599.8	1593.5	1588.5	1584.8	1581.1	1577.4	1573.8
30°	1547.9	1539.9	1531.9	1526.4	1523.3	1520.1	1517.0	1513.9
32.5°	1491.3	1482.5	1473.7	1467.3	1463.4	1459.4	1455.5	1451.5
35°	1403.4	1393.3	1383.3	1375.8	1371.0	1366.1	1361.3	1356.4
37.5°	1311.4	1299.4	1287.3	1278.9	1274.2	1269.5	1264.8	1260.1
40°	1250.6	1237.4	1224.3	1215.6	1211.4	1207.3	1203.1	1199.0
42.5°	1190.6	1178.0	1165.4	1156.0	1149.9	1143.8	1137.7	1131.6
45°	1094.8	1081.0	1067.1	1057.6	1052.4	1047.2	1042.0	1036.8
47.5°	1000.2	985.9	971.6	961.6	955.8	950.1	944.3	938.6
50°	936.0	921.4	906.9	897.0	891.8	886.6	881.4	876.2
52.5°	875.1	859.5	843.8	833.4	828.2	823.0	817.8	812.6
55°	782.7	767.1	751.5	740.9	735.4	729.8	724.3	718.8
57.5°	690.1	674.9	659.6	649.6	644.6	639.7	634.8	629.9
60°	629.0	613.8	598.5	588.3	583.1	577.9	572.7	567.5
62.5°	568.9	554.7	540.6	530.9	525.7	520.5	515.3	510.1
65°	480.6	466.7	452.8	443.3	438.1	432.9	427.7	422.5
67.5°	396.2	383.5	370.9	362.4	358.3	354.1	350.0	345.8
70°	340.2	329.5	318.8	311.3	307.1	303.0	298.8	294.7
72.5°	288.3	278.4	268.4	262.1	259.3	256.6	253.8	251.0
75°	215.5	207.9	200.3	195.2	192.8	190.4	188.0	185.5
77.5°	153.3	148.0	142.7	139.1	137.3	135.5	133.7	131.9
80°	115.4	112.3	109.1	107.2	106.5	105.8	105.2	104.5
82.5°	86.3	84.8	83.4	82.4	82.0	81.6	81.2	80.8
85°	49.2	48.9	48.5	48.2	47.8	47.5	47.1	46.8
87.5°	21.4	21.6	21.7	21.7	21.6	21.4	21.2	21.0
90°	13.5	14.3	15.1	15.8	16.3	16.8	17.3	17.8
92.5°	13.5	14.3	15.1	15.7	15.9	16.1	16.4	16.6
95°	13.5	14.3	15.1	15.6	15.6	15.6	15.6	15.6
97.5°	27.2	22.5	17.9	15.6	15.6	15.6	15.6	15.6
100°	79.9	55.3	30.8	18.2	17.5	16.9	16.2	15.6
102.5°	155.2	150.6	145.9	138.0	126.8	115.6	104.4	93.2
105°	220.8	220.8	220.8	220.7	220.6	220.4	220.2	220.1
107.5°	279.6	279.6	279.6	279.4	278.9	278.4	277.9	277.4
110°	317.6	317.1	316.6	316.5	316.6	316.8	317.0	317.1



TEST NUMBER: P333726

CATALOG NUMBER: S125RDIW-S1270D770U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	355.3	354.7	354.0	353.6	353.4	353.2	352.9	352.7
115°	412.1	411.5	410.8	410.0	409.0	408.0	407.0	406.0
117.5°	467.0	466.2	465.3	464.7	464.2	463.8	463.4	463.0
120°	502.5	502.1	501.8	501.2	500.4	499.6	498.8	497.9
122.5°	536.2	535.9	535.6	534.9	534.0	533.0	532.1	531.1
125°	585.5	584.9	584.2	583.6	583.1	582.6	582.2	581.7
127.5°	630.6	630.2	629.9	629.1	627.8	626.6	625.4	624.2
130°	660.0	659.5	659.0	658.3	657.5	656.7	655.8	655.0
132.5°	687.4	687.3	687.2	686.8	685.9	685.1	684.3	683.5
135°	727.7	727.4	727.1	726.4	725.4	724.4	723.4	722.4
137.5°	765.3	765.3	765.4	765.0	764.1	763.3	762.4	761.6
140°	788.3	788.6	789.0	788.6	787.6	786.7	785.7	784.7
142.5°	810.9	811.0	811.0	810.6	809.6	808.6	807.6	806.6
145°	842.8	843.0	843.1	842.7	841.7	840.7	839.8	838.8
147.5°	870.1	870.3	870.5	870.0	868.9	867.7	866.5	865.3
150°	887.6	887.9	888.3	887.8	886.4	885.1	883.8	882.5
152.5°	903.0	903.3	903.7	903.2	902.0	900.9	899.7	898.5
155°	924.2	924.7	925.2	924.8	923.5	922.2	920.9	919.5
157.5°	941.8	942.3	942.8	942.4	941.1	939.8	938.5	937.2
160°	952.7	953.4	954.0	953.7	952.4	951.1	949.8	948.4
162.5°	962.7	963.6	964.6	964.3	962.9	961.4	960.0	958.5
165°	975.6	976.6	977.6	977.4	976.1	974.8	973.5	972.1
167.5°	985.3	986.5	987.7	987.6	986.1	984.6	983.1	981.6
170°	990.3	991.7	993.0	992.9	991.4	989.9	988.4	987.0
172.5°	994.2	995.4	996.6	996.4	995.0	993.5	992.0	990.5
175°	998.5	999.8	1001.1	1001.0	999.6	998.1	996.6	995.1
177.5°	1000.2	1001.1	1002.1	1002.0	1000.9	999.9	998.8	997.8
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6

(END OF REPORT)