

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333699-927

Luminaire Tested: **S125RDIW-S850D1560U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333699-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1560U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6860.8 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333699-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333699-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32
2	87	80	74	69	78	72	67	63	59	55	52	47	44	42	35	34	32	27
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23
4	72	62	54	49	65	57	50	45	46	42	38	37	33	31	28	26	24	20
5	66	55	47	42	60	50	44	38	41	36	32	33	29	27	25	23	21	17
6	61	50	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	57	45	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16	14
8	52	40	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7035	7035	7035
5°	7052	6971	7014
10°	6998	6906	6906
15°	6915	6766	6711
20°	6808	6570	6491
25°	6683	6379	6238
30°	6528	6154	5957
35°	6370	5922	5643
40°	6222	5681	5334
45°	6042	5411	4997
50°	5861	5117	4646
55°	5650	4835	4271
60°	5441	4495	3867
65°	5193	4099	3406
70°	4910	3603	2936
75°	4517	3039	2443
80°	3976	2388	2049
85°	3349	1949	1830



TEST NUMBER: P333699-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.4	1.5
10°-20°	286.2	4.2
20°-30°	415.1	6.1
30°-40°	473.1	6.9
40°-50°	461.1	6.7
50°-60°	388.2	5.7
60°-70°	272.1	4.0
70°-80°	139.9	2.0
80°-90°	38.7	0.6
90°-100°	102.8	1.5
100°-110°	303.6	4.4
110°-120°	514.3	7.5
120°-130°	676.9	9.9
130°-140°	758.4	11.1
140°-150°	743.3	10.8
150°-160°	624.3	9.1
160°-170°	415.0	6.0
170°-180°	145.2	2.1
0°-30°	803.8	11.7
0°-40°	1276.8	18.6
0°-60°	2126.1	31.0
0°-90°	2576.8	37.6
90°-120°	920.8	13.4
90°-150°	3099.4	45.2
90°-180°	4284.0	62.4
0°-180°	6860.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1089	1089	1089	1089	1089	
5°	1088	1084	1075	1083	1082	103
15°	1034	1029	1012	1011	1004	291
25°	938	925	895	885	875	431
35°	808	787	751	728	716	506
45°	662	636	592	561	547	510
55°	502	474	429	394	379	449
65°	340	311	268	236	223	336
75°	181	156	122	104	98	192
85°	45	31	26	26	25	51
90°	1	11	19	25	29	6
95°	78	81	92	100	103	83
105°	272	278	286	292	296	291
115°	515	520	522	521	520	509
125°	752	758	760	758	756	673
135°	977	984	986	985	981	753
145°	1184	1189	1192	1192	1189	740
155°	1355	1355	1356	1360	1355	624
165°	1473	1471	1472	1476	1470	415
175°	1532	1527	1527	1533	1526	145
180°	1535	1535	1535	1535	1535	



TEST NUMBER: P333699-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1091.2	1090.8	1090.4	1090.0	1089.5	1088.5	1087.1	1085.6	1084.2	1082.7	1084.2
5°	1087.7	1087.0	1086.2	1085.4	1084.7	1083.4	1081.3	1079.3	1077.3	1075.3	1077.1
7.5°	1077.0	1076.3	1075.5	1074.8	1074.2	1072.6	1070.2	1067.8	1065.4	1063.0	1064.2
10°	1067.1	1066.5	1066.0	1065.4	1064.9	1063.3	1060.8	1058.2	1055.7	1053.1	1053.6
12.5°	1055.9	1055.2	1054.5	1053.8	1053.1	1051.1	1047.6	1044.2	1040.8	1037.3	1037.7
15°	1034.2	1033.1	1032.0	1030.9	1029.8	1027.3	1023.5	1019.6	1015.8	1011.9	1011.8
17.5°	1009.6	1008.0	1006.3	1004.6	1002.9	999.7	994.8	990.0	985.2	980.3	979.5
20°	990.5	988.7	986.9	985.1	983.3	979.4	973.6	967.7	961.9	956.0	955.1
22.5°	969.5	967.7	965.8	964.0	962.2	958.2	952.0	945.9	939.8	933.7	931.8
25°	937.9	935.2	932.4	929.7	926.9	922.2	915.4	908.6	901.9	895.2	892.8
27.5°	901.7	898.4	895.1	891.8	888.4	883.1	875.9	868.6	861.4	854.1	850.8
30°	875.4	871.9	868.5	865.0	861.5	855.9	848.3	840.6	832.9	825.2	821.0
32.5°	849.7	845.7	841.6	837.6	833.5	827.5	819.8	811.9	804.1	796.2	791.6
35°	807.9	803.5	799.2	794.7	790.4	784.0	775.9	767.6	759.4	751.1	745.8
37.5°	766.9	761.6	756.3	750.9	745.6	738.7	730.2	721.7	713.2	704.7	698.4
40°	738.0	732.5	727.0	721.5	716.1	708.9	700.1	691.3	682.6	673.8	666.9
42.5°	707.7	702.1	696.5	690.8	685.2	677.9	668.8	659.7	650.6	641.6	634.9
45°	661.5	656.2	650.9	645.5	640.2	632.6	622.5	612.5	602.5	592.4	585.0
47.5°	613.6	608.0	602.4	596.8	591.2	583.4	573.2	563.1	552.9	542.8	535.3
50°	583.3	577.3	571.2	565.2	559.2	551.0	540.5	530.1	519.7	509.3	501.6
52.5°	550.4	544.2	538.1	531.9	525.7	517.7	507.9	498.0	488.1	478.3	470.1
55°	501.8	496.0	490.2	484.3	478.5	470.4	460.2	450.0	439.7	429.4	421.2
57.5°	452.8	446.6	440.3	434.0	427.9	419.8	409.9	400.0	390.1	380.2	372.2
60°	421.2	414.9	408.4	402.0	395.6	387.5	377.6	367.7	357.9	348.0	340.0
62.5°	387.7	381.6	375.5	369.3	363.2	355.2	345.2	335.2	325.1	315.1	307.7
65°	339.8	333.6	327.3	321.2	314.9	307.0	297.3	287.6	277.9	268.2	260.9
67.5°	292.2	286.0	279.8	273.6	267.4	259.6	250.3	241.1	231.8	222.4	215.8
70°	260.0	253.7	247.6	241.3	235.1	227.4	218.3	209.1	200.0	190.8	185.2
72.5°	228.4	222.3	216.3	210.2	204.1	196.8	188.2	179.7	171.1	162.6	157.3
75°	181.0	175.5	170.0	164.5	159.1	152.5	144.8	137.1	129.4	121.8	117.7
77.5°	134.0	129.5	125.2	120.8	116.4	111.1	105.0	98.9	92.7	86.6	83.7
80°	106.9	102.6	98.2	93.8	89.4	84.7	79.5	74.4	69.3	64.2	62.5
82.5°	80.6	76.7	72.7	68.8	64.8	61.1	57.6	54.1	50.5	47.1	46.3
85°	45.2	42.0	38.7	35.4	32.1	29.9	29.1	28.1	27.3	26.3	26.1
87.5°	15.4	14.8	14.2	13.5	13.0	12.8	13.0	13.2	13.5	13.7	13.9
90°	1.2	3.3	5.5	7.6	9.7	11.6	13.5	15.4	17.3	19.1	20.4
92.5°	28.9	30.4	31.9	33.4	34.9	36.8	39.1	41.3	43.6	45.9	47.6
95°	77.6	78.2	78.7	79.2	79.8	81.4	84.1	86.7	89.4	92.0	93.9
97.5°	129.0	129.2	129.4	129.7	129.9	131.8	135.5	139.2	142.8	146.5	148.2
100°	167.2	167.2	167.2	167.2	167.2	169.0	172.5	175.9	179.4	182.8	185.2
102.5°	208.3	209.5	210.5	211.5	212.6	214.0	215.8	217.5	219.3	221.0	223.6
105°	272.4	273.7	275.0	276.4	277.7	279.2	280.7	282.3	283.9	285.6	287.2
107.5°	343.1	344.4	345.8	347.1	348.4	349.7	350.9	352.1	353.4	354.6	355.4
110°	391.9	393.2	394.5	395.9	397.2	398.2	399.0	399.8	400.6	401.4	402.2



TEST NUMBER: P333699-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	441.6	442.3	443.0	443.6	444.3	445.2	446.2	447.2	448.2	449.2	449.6
115°	514.9	516.0	517.1	518.1	519.2	520.0	520.5	521.0	521.6	522.1	521.8
117.5°	588.5	589.0	589.5	589.9	590.4	590.9	591.4	591.8	592.3	592.9	593.0
120°	634.4	635.7	637.1	638.4	639.7	640.5	640.8	641.0	641.3	641.6	641.6
122.5°	684.1	684.6	685.1	685.6	686.0	686.6	687.3	688.0	688.6	689.4	689.1
125°	751.5	753.0	754.7	756.3	757.9	758.8	759.1	759.3	759.6	759.9	759.3
127.5°	823.2	824.1	825.0	825.9	826.8	827.4	827.8	828.1	828.4	828.7	828.4
130°	866.2	867.5	868.9	870.1	871.5	872.4	873.0	873.5	874.0	874.6	874.3
132.5°	909.2	911.4	913.5	915.8	917.9	918.9	918.9	918.7	918.6	918.5	918.2
135°	977.3	978.9	980.5	982.1	983.7	984.6	984.8	985.2	985.4	985.6	985.6
137.5°	1041.3	1042.9	1044.4	1045.9	1047.5	1048.5	1049.2	1049.7	1050.3	1050.9	1051.2
140°	1082.4	1083.8	1085.1	1086.4	1087.7	1088.8	1089.6	1090.4	1091.2	1092.0	1092.5
142.5°	1123.6	1124.7	1125.8	1126.9	1128.0	1129.0	1130.0	1131.1	1132.1	1133.1	1133.4
145°	1184.0	1185.0	1186.1	1187.2	1188.3	1189.1	1189.9	1190.7	1191.5	1192.3	1192.3
147.5°	1239.9	1240.5	1241.0	1241.7	1242.2	1242.9	1243.5	1244.1	1244.8	1245.4	1246.0
150°	1277.2	1276.9	1276.7	1276.4	1276.1	1276.5	1277.6	1278.7	1279.7	1280.8	1280.8
152.5°	1307.7	1308.1	1308.5	1308.8	1309.2	1309.6	1310.1	1310.5	1310.9	1311.4	1312.0
155°	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9	1355.3	1355.5	1355.7	1356.1	1357.1
157.5°	1396.9	1396.3	1395.7	1395.1	1394.6	1394.4	1394.6	1395.0	1395.2	1395.4	1396.5
160°	1421.7	1420.9	1420.1	1419.4	1418.6	1418.3	1418.6	1418.8	1419.1	1419.4	1420.4
162.5°	1443.8	1443.1	1442.6	1442.0	1441.4	1441.1	1441.1	1441.2	1441.3	1441.3	1442.6
165°	1473.1	1472.6	1472.0	1471.6	1471.0	1470.8	1471.2	1471.4	1471.6	1472.0	1473.0
167.5°	1497.9	1496.9	1495.9	1494.8	1493.7	1493.2	1493.2	1493.2	1493.2	1493.2	1494.8
170°	1511.3	1510.3	1509.2	1508.2	1507.1	1506.6	1506.6	1506.6	1506.6	1506.6	1508.2
172.5°	1520.9	1519.9	1518.8	1517.7	1516.6	1516.2	1516.2	1516.2	1516.2	1516.2	1517.7
175°	1531.7	1530.6	1529.5	1528.4	1527.4	1526.9	1526.9	1526.9	1526.9	1526.9	1528.4
177.5°	1537.2	1536.3	1535.5	1534.6	1533.7	1533.2	1533.0	1532.8	1532.6	1532.4	1533.7
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333699-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1085.6	1087.1	1088.5	1089.3	1089.1	1088.9	1088.8	1088.6
5°	1079.0	1080.8	1082.6	1083.4	1083.0	1082.6	1082.3	1081.9
7.5°	1065.6	1066.8	1068.1	1068.5	1068.1	1067.7	1067.3	1066.9
10°	1054.2	1054.7	1055.3	1055.3	1054.7	1054.2	1053.6	1053.1
12.5°	1038.1	1038.5	1038.9	1038.7	1037.8	1037.0	1036.2	1035.3
15°	1011.6	1011.4	1011.2	1010.3	1008.7	1007.0	1005.4	1003.7
17.5°	978.5	977.6	976.7	975.6	974.2	972.9	971.5	970.2
20°	954.2	953.2	952.4	951.1	949.4	947.8	946.1	944.5
22.5°	930.0	928.3	926.5	924.9	923.5	922.2	920.8	919.5
25°	890.4	888.0	885.7	883.4	881.4	879.4	877.4	875.4
27.5°	847.5	844.1	840.8	838.2	836.3	834.3	832.4	830.4
30°	816.8	812.6	808.3	805.5	803.8	802.2	800.5	798.8
32.5°	787.0	782.3	777.7	774.3	772.2	770.2	768.0	766.0
35°	740.5	735.2	729.9	726.0	723.4	720.9	718.4	715.7
37.5°	692.1	685.6	679.3	674.9	672.4	669.9	667.4	665.0
40°	659.9	653.0	646.0	641.4	639.3	637.1	634.9	632.7
42.5°	628.3	621.6	615.0	610.0	606.8	603.6	600.3	597.1
45°	577.7	570.5	563.1	558.1	555.3	552.6	549.9	547.1
47.5°	527.8	520.2	512.7	507.4	504.4	501.4	498.3	495.3
50°	493.9	486.2	478.6	473.3	470.6	467.9	465.1	462.4
52.5°	461.8	453.5	445.3	439.7	437.0	434.3	431.6	428.8
55°	413.0	404.8	396.6	390.9	388.1	385.2	382.2	379.3
57.5°	364.2	356.2	348.1	342.8	340.2	337.5	335.0	332.4
60°	331.9	323.8	315.8	310.5	307.7	305.0	302.2	299.4
62.5°	300.2	292.7	285.3	280.2	277.4	274.6	272.0	269.2
65°	253.6	246.3	238.9	233.9	231.2	228.5	225.7	222.9
67.5°	209.1	202.4	195.7	191.2	189.1	186.9	184.7	182.5
70°	179.5	173.9	168.2	164.3	162.1	159.9	157.7	155.5
72.5°	152.1	146.9	141.6	138.3	136.8	135.4	134.0	132.5
75°	113.8	109.7	105.7	103.1	101.7	100.4	99.2	97.9
77.5°	80.9	78.1	75.3	73.4	72.5	71.5	70.6	69.6
80°	60.9	59.3	57.6	56.6	56.2	55.8	55.5	55.1
82.5°	45.6	44.8	44.0	43.5	43.3	43.1	42.9	42.6
85°	26.0	25.7	25.6	25.4	25.2	25.0	24.9	24.7
87.5°	14.3	14.5	14.7	14.9	14.9	14.9	15.0	15.0
90°	21.8	23.1	24.4	25.5	26.3	27.1	27.9	28.7
92.5°	49.4	51.1	52.9	54.0	54.7	55.2	55.8	56.4
95°	95.7	97.6	99.4	100.6	101.2	101.7	102.2	102.7
97.5°	150.0	151.7	153.4	154.6	154.9	155.2	155.5	155.8
100°	187.6	190.0	192.3	193.8	194.3	194.9	195.4	195.9
102.5°	226.2	228.9	231.4	233.1	233.9	234.6	235.4	236.1
105°	288.8	290.3	291.9	293.1	293.9	294.7	295.5	296.3
107.5°	356.2	357.0	357.7	358.1	358.1	358.1	358.0	357.9
110°	403.1	403.9	404.6	404.9	404.6	404.3	404.1	403.9



TEST NUMBER: P333699-927

CATALOG NUMBER: S125RDIW-S850D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.0	450.4	450.7	450.7	450.2	449.7	449.2	448.8
115°	521.6	521.3	521.0	520.8	520.5	520.2	520.0	519.8
117.5°	593.3	593.5	593.7	593.3	592.2	591.1	590.1	589.0
120°	641.6	641.6	641.6	641.0	640.0	638.9	637.9	636.8
122.5°	689.0	688.7	688.5	688.0	687.1	686.3	685.4	684.6
125°	758.8	758.3	757.7	757.3	757.1	756.8	756.5	756.3
127.5°	828.1	827.9	827.6	827.2	826.6	826.2	825.6	825.1
130°	874.0	873.8	873.5	873.1	872.6	872.0	871.5	871.0
132.5°	918.0	917.7	917.4	917.0	916.2	915.4	914.7	913.9
135°	985.6	985.6	985.6	985.2	984.0	983.0	981.9	980.9
137.5°	1051.5	1051.9	1052.2	1051.7	1050.4	1049.0	1047.7	1046.3
140°	1093.1	1093.6	1094.1	1093.7	1092.4	1091.1	1089.7	1088.4
142.5°	1133.7	1134.0	1134.4	1133.9	1132.5	1131.2	1129.9	1128.5
145°	1192.3	1192.3	1192.3	1191.9	1191.1	1190.3	1189.5	1188.7
147.5°	1246.7	1247.3	1247.9	1247.4	1245.5	1243.7	1242.0	1240.2
150°	1280.8	1280.8	1280.8	1280.5	1279.9	1279.5	1278.9	1278.3
152.5°	1312.6	1313.3	1313.9	1313.8	1312.8	1311.9	1310.9	1310.0
155°	1358.1	1359.2	1360.3	1360.2	1358.8	1357.5	1356.1	1354.9
157.5°	1397.6	1398.7	1399.7	1399.4	1397.6	1395.8	1394.1	1392.3
160°	1421.5	1422.5	1423.6	1423.5	1422.1	1420.8	1419.5	1418.2
162.5°	1443.9	1445.2	1446.4	1446.3	1444.8	1443.2	1441.7	1440.1
165°	1474.0	1475.1	1476.2	1475.9	1474.3	1472.7	1471.2	1469.5
167.5°	1496.4	1497.9	1499.5	1499.5	1497.9	1496.3	1494.6	1492.9
170°	1509.7	1511.3	1512.9	1512.8	1510.9	1509.1	1507.2	1505.4
172.5°	1519.3	1520.9	1522.5	1522.5	1520.8	1519.2	1517.5	1515.9
175°	1530.1	1531.7	1533.3	1533.1	1531.3	1529.4	1527.6	1525.7
177.5°	1534.9	1536.2	1537.5	1537.4	1535.9	1534.4	1532.9	1531.4
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2

(END OF REPORT)