

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333652

Luminaire Tested: **S125RDIW-S375D1340U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333652  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1340U835-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6825.5 lumens  
Efficiency: N/A  
Efficacy: 146.5 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	92	87	84	81	81	78	75	72	59	57	55	42	41	40	27	26	25	18
2	83	77	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	16
3	76	67	60	55	67	60	54	50	46	42	39	33	31	29	21	20	19	13
4	70	60	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	12
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14	10
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12	9
7	54	43	35	30	48	38	32	27	30	25	22	22	18	16	14	12	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	29	23	19	22	18	15	17	14	11	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	3635	3635	3635	3635
5°	4182	3640	3215	3640
10°	4798	3621	2837	3621
15°	5182	3584	2521	3584
20°	5714	3542	2328	3542
25°	6613	3484	2161	3484
30°	7196	3424	2051	3424
35°	6070	3354	1949	3354
40°	4239	3228	1862	3228
45°	3145	3058	1777	3058
50°	2508	2882	1704	2882
55°	2128	2662	1639	2662
60°	1838	2466	1535	2466
65°	1638	2253	1320	2253
70°	1441	2064	1205	2064
75°	1245	1787	1130	1787
80°	945	1503	945	1503
85°	785	1178	889	1178



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	54.0	0.8
10°-20°	158.2	2.3
20°-30°	250.8	3.7
30°-40°	302.5	4.4
40°-50°	270.1	4.0
50°-60°	207.1	3.0
60°-70°	134.6	2.0
70°-80°	65.4	1.0
80°-90°	19.3	0.3
90°-100°	63.5	0.9
100°-110°	391.2	5.7
110°-120°	709.5	10.4
120°-130°	910.5	13.3
130°-140°	979.3	14.3
140°-150°	919.2	13.5
150°-160°	743.6	10.9
160°-170°	480.9	7.0
170°-180°	165.9	2.4
0°-30°	463.0	6.8
0°-40°	765.4	11.2
0°-60°	1242.7	18.2
0°-90°	1462.0	21.4
90°-120°	1164.1	17.1
90°-150°	3973.2	58.2
90°-180°	5364.0	78.6
0°-180°	6825.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	563	563	563	563	563	
5°	645	562	496	562	645	64
15°	775	536	377	536	775	222
25°	928	489	303	489	928	426
35°	770	425	247	425	770	465
45°	344	335	195	335	344	275
55°	189	236	146	236	189	172
65°	107	147	86	147	107	107
75°	50	72	45	72	50	53
85°	11	16	12	16	11	13
90°	31	1	31	1	31	14
95°	27	74	27	74	27	22
105°	384	381	384	381	384	348
115°	710	715	710	715	710	704
125°	1016	1016	1016	1016	1016	904
135°	1262	1268	1262	1268	1262	974
145°	1466	1470	1466	1470	1466	916
155°	1607	1618	1607	1618	1607	741
165°	1699	1708	1699	1708	1699	479
175°	1739	1747	1739	1747	1739	165
180°	1747	1747	1747	1747	1747	



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	592.1	591.7	592.5	590.4	590.6	587.5	587.5	585.1	581.9	579.5	578.4
5°	645.1	645.6	644.7	641.2	638.9	635.4	631.5	624.6	618.8	613.2	608.9
7.5°	699.8	700.1	697.0	696.0	690.1	685.9	677.2	667.7	659.4	648.7	640.6
10°	731.6	731.3	728.1	725.5	720.5	714.0	705.4	694.4	684.0	672.4	661.3
12.5°	750.0	749.4	748.4	745.3	740.6	734.9	727.6	716.7	703.9	691.3	678.3
15°	775.0	773.4	770.4	766.4	759.7	753.0	745.0	735.3	723.0	708.7	696.7
17.5°	805.9	805.9	801.3	795.8	786.7	774.9	762.4	746.8	730.1	714.4	701.6
20°	831.4	830.7	826.1	815.4	805.0	790.2	775.9	756.7	736.4	715.8	699.9
22.5°	868.0	866.2	861.4	847.4	831.3	812.2	790.3	766.9	742.3	719.0	698.0
25°	928.0	926.6	917.1	900.9	878.3	848.9	820.3	788.2	752.8	722.1	696.7
27.5°	969.0	967.5	960.4	947.0	926.1	895.2	856.5	813.5	769.4	727.1	690.5
30°	964.9	968.4	967.5	961.2	945.5	917.8	882.0	833.7	781.2	731.6	687.9
32.5°	906.9	910.0	918.1	930.4	931.3	920.2	893.4	848.8	794.5	738.0	685.8
35°	769.9	774.1	789.8	814.5	846.9	873.9	879.4	855.4	806.6	745.9	682.8
37.5°	591.9	614.6	627.9	653.9	702.8	752.5	800.3	817.9	797.2	742.6	677.9
40°	502.8	508.3	531.9	561.3	602.4	654.1	722.3	771.5	773.1	735.3	670.1
42.5°	430.3	437.4	453.5	477.0	512.2	563.9	634.3	699.3	729.3	714.9	659.9
45°	344.3	349.6	361.4	379.4	406.4	449.2	509.7	584.8	644.4	667.8	632.7
47.5°	282.8	285.7	295.9	309.7	329.7	360.8	407.7	472.9	544.4	594.5	589.6
50°	249.6	252.8	260.6	271.0	287.9	314.2	351.7	406.0	479.7	540.9	553.2
52.5°	223.7	226.4	231.3	241.1	255.0	275.2	305.5	354.6	420.9	486.0	514.4
55°	189.0	190.9	194.8	200.3	211.4	226.0	252.1	286.1	339.7	405.3	446.9
57.5°	160.5	161.4	163.9	169.0	176.7	187.3	206.2	234.9	273.4	332.5	378.4
60°	142.3	143.3	146.5	150.0	156.0	165.7	180.5	200.6	237.5	286.3	332.7
62.5°	127.9	128.5	129.9	133.3	138.6	146.1	157.7	174.1	203.5	246.4	290.2
65°	107.2	107.4	107.9	110.7	113.9	119.5	127.1	138.6	160.8	193.2	232.0
67.5°	87.3	87.7	89.3	90.3	93.6	96.5	101.0	109.8	125.5	147.3	177.5
70°	76.3	76.0	77.6	78.8	79.9	83.4	86.4	93.6	103.3	119.9	145.1
72.5°	65.9	65.3	66.0	66.4	67.9	70.3	73.3	77.7	85.2	96.6	115.9
75°	49.9	50.1	50.1	50.6	51.8	52.7	53.6	55.9	60.1	67.7	78.1
77.5°	35.0	34.7	35.6	35.8	36.5	37.5	38.3	39.2	40.9	44.0	49.4
80°	25.4	25.4	25.6	26.3	26.1	26.6	27.7	28.7	30.7	32.6	34.4
82.5°	19.5	19.3	19.5	19.7	19.6	20.1	20.5	20.7	21.5	22.4	23.7
85°	10.6	10.6	10.9	10.9	11.1	11.1	11.3	11.3	11.3	11.6	11.8
87.5°	10.3	9.9	9.6	9.4	9.4	9.5	9.1	8.6	8.3	8.0	7.8
90°	31.1	30.2	29.3	28.5	27.6	26.5	25.0	23.6	22.2	20.7	18.7
92.5°	29.0	28.6	28.2	27.8	27.4	26.5	25.0	23.6	22.2	20.7	18.9
95°	27.2	27.2	27.2	27.2	27.2	26.5	25.0	23.6	22.2	20.7	31.6
97.5°	27.2	27.2	27.2	27.2	27.2	31.2	39.4	47.5	55.6	63.7	85.3
100°	27.2	28.3	29.5	30.6	31.8	53.8	96.7	139.5	182.4	225.3	224.1
102.5°	162.9	182.4	202.0	221.6	241.1	255.0	263.1	271.2	279.3	287.4	286.7
105°	384.5	384.8	385.1	385.4	385.7	385.8	385.8	385.8	385.8	385.8	385.8
107.5°	484.8	485.6	486.5	487.3	488.2	488.6	488.6	488.5	488.4	488.4	487.8
110°	554.2	553.9	553.6	553.3	553.0	553.3	554.2	555.0	555.9	556.7	556.2



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	616.3	616.7	617.1	617.5	617.9	618.7	619.8	620.8	621.9	623.0	622.7
115°	709.5	711.2	713.0	714.7	716.4	717.9	719.0	720.2	721.3	722.5	722.2
117.5°	809.0	809.7	810.5	811.2	811.9	813.1	814.6	816.1	817.6	819.1	818.0
120°	870.1	871.5	872.9	874.4	875.8	876.8	877.4	878.0	878.6	879.1	878.3
122.5°	928.1	929.7	931.4	933.1	934.7	935.9	936.4	937.0	937.6	938.2	937.8
125°	1016.4	1017.2	1018.1	1019.0	1019.8	1020.8	1022.0	1023.1	1024.3	1025.4	1025.4
127.5°	1090.7	1092.8	1095.0	1097.1	1099.2	1100.6	1101.2	1101.9	1102.5	1103.1	1103.3
130°	1144.6	1146.0	1147.4	1148.9	1150.3	1151.5	1152.3	1153.2	1154.1	1154.9	1154.6
132.5°	1194.3	1195.7	1197.2	1198.6	1200.0	1200.8	1201.0	1201.2	1201.4	1201.5	1202.2
135°	1262.4	1264.1	1265.8	1267.6	1269.3	1270.4	1271.0	1271.6	1272.2	1272.7	1273.3
137.5°	1330.7	1332.2	1333.7	1335.2	1336.7	1337.4	1337.3	1337.2	1337.1	1337.0	1337.5
140°	1371.1	1372.9	1374.6	1376.3	1378.0	1378.6	1378.0	1377.5	1376.9	1376.3	1376.6
142.5°	1409.5	1411.2	1412.9	1414.6	1416.4	1417.2	1417.1	1416.9	1416.8	1416.7	1416.3
145°	1465.7	1467.4	1469.1	1470.8	1472.6	1473.3	1473.0	1472.7	1472.4	1472.1	1472.1
147.5°	1512.0	1514.1	1516.1	1518.2	1520.3	1521.2	1520.8	1520.5	1520.1	1519.8	1519.4
150°	1542.0	1544.3	1546.6	1548.9	1551.2	1552.1	1551.5	1551.0	1550.4	1549.8	1549.2
152.5°	1570.0	1572.1	1574.2	1576.2	1578.3	1579.0	1578.5	1577.9	1577.3	1576.7	1576.2
155°	1606.8	1609.1	1611.4	1613.7	1616.0	1616.7	1615.8	1615.0	1614.1	1613.3	1612.7
157.5°	1637.6	1639.9	1642.2	1644.5	1646.8	1647.5	1646.6	1645.7	1644.7	1643.8	1643.8
160°	1657.3	1659.6	1661.9	1664.2	1666.5	1667.1	1665.9	1664.8	1663.6	1662.5	1662.2
162.5°	1674.9	1677.4	1679.9	1682.5	1685.0	1685.5	1683.9	1682.2	1680.6	1679.0	1678.7
165°	1698.7	1701.0	1703.3	1705.6	1707.9	1708.2	1706.5	1704.7	1703.0	1701.3	1701.0
167.5°	1715.3	1717.9	1720.5	1723.0	1725.6	1725.9	1723.8	1721.8	1719.7	1717.6	1717.3
170°	1724.6	1727.2	1729.8	1732.4	1735.0	1735.1	1732.8	1730.5	1728.2	1725.9	1725.6
172.5°	1730.8	1733.4	1736.0	1738.6	1741.2	1741.4	1739.4	1737.3	1735.2	1733.1	1732.6
175°	1738.8	1741.4	1744.0	1746.6	1749.2	1749.3	1747.0	1744.7	1742.4	1740.1	1739.9
177.5°	1743.5	1745.3	1747.2	1749.0	1750.9	1751.0	1749.4	1747.8	1746.2	1744.5	1744.3
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	578.4	577.1	574.7	572.5	569.7	567.3	565.6	563.6	561.0	557.9	555.3
5°	604.0	598.9	592.2	586.4	579.0	573.3	567.3	561.5	555.7	548.3	541.8
7.5°	632.4	621.9	611.7	598.8	587.2	576.8	566.8	556.7	546.8	536.3	526.2
10°	649.8	637.0	623.0	606.8	592.0	577.9	565.0	552.2	538.8	527.1	514.4
12.5°	666.0	649.6	633.5	613.1	595.3	578.1	561.6	545.8	531.5	516.2	502.5
15°	680.7	664.5	646.5	621.6	596.8	576.0	556.6	536.1	518.3	501.2	485.9
17.5°	686.4	669.4	648.5	624.5	597.5	571.3	546.3	523.8	502.8	482.9	465.8
20°	684.2	667.8	646.3	623.4	594.5	567.3	540.2	515.3	491.9	470.9	452.7
22.5°	678.8	661.9	641.1	616.9	589.5	560.6	531.7	505.1	480.7	458.9	439.0
25°	670.8	647.7	626.4	602.8	576.7	548.1	518.3	488.9	462.8	440.6	418.9
27.5°	662.4	633.6	606.5	583.1	555.5	530.0	501.2	471.1	443.7	421.1	398.8
30°	654.8	622.5	592.7	566.1	540.0	515.7	488.5	459.1	430.9	407.6	385.0
32.5°	645.4	611.0	578.3	547.6	522.4	498.4	473.7	445.6	418.2	394.1	371.1
35°	633.6	589.7	554.1	521.5	493.6	470.2	448.0	425.4	397.9	372.9	350.5
37.5°	618.1	568.2	527.1	491.6	462.1	438.7	421.1	400.4	375.3	351.5	330.7
40°	608.6	552.7	507.7	472.5	441.6	416.8	400.4	382.9	360.0	337.6	316.8
42.5°	596.1	538.5	488.1	451.5	420.3	396.5	379.9	364.6	345.4	324.3	302.0
45°	571.4	510.9	458.0	418.7	387.3	363.9	348.4	334.8	320.3	300.8	281.4
47.5°	539.4	482.1	426.7	383.8	353.1	331.4	316.4	305.6	295.2	278.7	259.9
50°	513.7	458.4	404.4	362.8	330.0	309.4	295.3	286.8	277.3	262.3	246.5
52.5°	483.3	434.0	381.1	338.6	307.6	288.3	274.8	266.2	258.4	246.2	231.2
55°	435.6	392.3	343.8	305.2	276.8	257.4	244.5	236.4	231.8	221.4	209.6
57.5°	380.4	349.5	306.7	269.5	244.3	225.2	215.7	208.8	203.6	196.2	187.9
60°	342.0	320.3	281.9	246.5	223.4	205.2	196.6	190.9	186.0	179.8	173.3
62.5°	303.0	287.2	253.8	223.4	202.2	186.9	178.9	173.7	168.1	163.9	157.6
65°	250.7	236.6	213.5	189.7	170.1	157.8	152.0	147.4	144.0	139.3	134.9
67.5°	195.0	189.3	173.3	156.9	142.8	131.9	126.9	123.7	119.6	116.8	113.8
70°	160.8	158.0	146.7	135.9	122.7	115.3	110.7	109.3	104.2	101.4	99.4
72.5°	130.5	129.2	122.7	115.2	105.9	99.4	95.2	93.6	90.3	88.1	86.8
75°	89.4	89.9	88.7	83.9	80.4	76.3	72.6	71.6	69.3	67.5	66.3
77.5°	56.6	58.9	59.0	58.8	57.4	54.9	53.3	52.6	50.4	49.7	49.4
80°	38.8	41.4	43.7	43.4	43.0	42.3	41.1	40.4	39.3	38.6	38.1
82.5°	25.9	28.2	30.2	31.4	31.3	30.6	29.9	29.5	29.3	28.8	28.7
85°	12.2	12.7	13.4	15.0	16.2	16.4	16.2	15.9	15.3	15.5	15.7
87.5°	7.6	7.2	7.0	6.5	5.9	6.4	6.4	6.2	6.3	6.4	6.4
90°	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	17.1	15.4	13.6	13.5	15.1	16.7	18.3	19.9	18.3	16.7	15.1
95°	42.6	53.5	64.4	70.3	71.2	72.1	72.9	73.8	72.9	72.1	71.2
97.5°	107.0	128.6	150.2	160.3	158.7	157.2	155.6	154.1	155.6	157.2	158.7
100°	223.0	221.8	220.7	219.7	218.8	217.9	217.1	216.2	217.1	217.9	218.8
102.5°	286.1	285.4	284.7	283.8	282.7	281.6	280.5	279.4	280.5	281.6	282.7
105°	385.8	385.8	385.8	385.3	384.1	383.0	381.8	380.7	381.8	383.0	384.1
107.5°	487.2	486.7	486.1	485.8	485.8	485.8	485.8	485.8	485.8	485.8	485.8
110°	555.6	555.0	554.4	554.2	554.2	554.2	554.2	554.2	554.2	554.2	554.2





TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	622.3	622.0	621.7	621.1	620.4	619.8	619.1	618.4	619.1	619.8	620.4
115°	721.9	721.6	721.3	720.5	719.0	717.6	716.1	714.7	716.1	717.6	719.0
117.5°	816.9	815.8	814.7	814.2	814.2	814.3	814.3	814.4	814.3	814.3	814.2
120°	877.4	876.5	875.7	875.4	875.7	876.0	876.3	876.5	876.3	876.0	875.7
122.5°	937.4	937.0	936.6	935.8	934.7	933.6	932.5	931.4	932.5	933.6	934.7
125°	1025.4	1025.4	1025.4	1024.4	1022.4	1020.4	1018.4	1016.4	1018.4	1020.4	1022.4
127.5°	1103.5	1103.6	1103.8	1103.2	1101.7	1100.3	1098.9	1097.4	1098.9	1100.3	1101.7
130°	1154.3	1154.1	1153.8	1152.9	1151.5	1150.0	1148.6	1147.1	1148.6	1150.0	1151.5
132.5°	1202.8	1203.4	1204.1	1203.5	1201.9	1200.2	1198.5	1196.9	1198.5	1200.2	1201.9
135°	1273.9	1274.5	1275.0	1274.5	1272.7	1271.0	1269.3	1267.6	1269.3	1271.0	1272.7
137.5°	1338.0	1338.5	1339.0	1338.5	1337.0	1335.5	1334.0	1332.6	1334.0	1335.5	1337.0
140°	1376.9	1377.2	1377.5	1377.3	1376.7	1376.2	1375.6	1375.0	1375.6	1376.2	1376.7
142.5°	1415.9	1415.5	1415.1	1414.7	1414.4	1414.0	1413.7	1413.3	1413.7	1414.0	1414.4
145°	1472.1	1472.1	1472.1	1471.8	1471.3	1470.7	1470.1	1469.5	1470.1	1470.7	1471.3
147.5°	1519.1	1518.7	1518.4	1518.3	1518.4	1518.5	1518.6	1518.7	1518.6	1518.5	1518.4
150°	1548.7	1548.1	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8	1549.2	1548.7	1548.1
152.5°	1575.6	1575.0	1574.4	1574.8	1576.1	1577.3	1578.6	1579.8	1578.6	1577.3	1576.1
155°	1612.1	1611.5	1611.0	1611.5	1613.3	1615.0	1616.7	1618.4	1616.7	1615.0	1613.3
157.5°	1643.7	1643.6	1643.6	1644.1	1645.1	1646.1	1647.2	1648.2	1647.2	1646.1	1645.1
160°	1661.9	1661.6	1661.3	1662.0	1663.7	1665.5	1667.2	1668.9	1667.2	1665.5	1663.7
162.5°	1678.5	1678.2	1677.9	1678.6	1680.3	1682.0	1683.8	1685.5	1683.8	1682.0	1680.3
165°	1700.7	1700.4	1700.1	1700.9	1702.6	1704.3	1706.0	1707.8	1706.0	1704.3	1702.6
167.5°	1717.0	1716.7	1716.5	1717.2	1719.0	1720.8	1722.6	1724.3	1722.6	1720.8	1719.0
170°	1725.3	1725.0	1724.7	1725.6	1727.6	1729.6	1731.7	1733.7	1731.7	1729.6	1727.6
172.5°	1732.1	1731.6	1731.1	1731.8	1733.8	1735.9	1737.9	1739.9	1737.9	1735.9	1733.8
175°	1739.6	1739.3	1739.0	1739.7	1741.4	1743.2	1744.9	1746.6	1744.9	1743.2	1741.4
177.5°	1744.1	1743.9	1743.6	1744.2	1745.6	1747.0	1748.3	1749.7	1748.3	1747.0	1745.6
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	553.4	550.9	549.0	545.3	542.7	541.6	539.6	539.0	541.1	539.6	539.4
5°	537.0	530.3	525.0	519.7	513.9	510.2	504.6	503.7	502.3	500.3	499.8
7.5°	517.3	508.5	501.7	492.9	485.3	479.1	472.2	468.9	467.1	464.4	460.8
10°	504.0	493.6	484.3	475.5	466.1	458.4	451.5	446.2	442.7	439.5	438.1
12.5°	490.8	480.2	468.4	457.8	447.2	438.7	431.0	427.5	423.7	419.9	416.7
15°	470.4	456.4	443.4	431.2	422.2	412.9	405.5	400.4	394.7	393.0	386.8
17.5°	448.8	435.0	419.8	407.0	396.5	386.3	378.2	372.4	368.1	362.1	359.3
20°	435.3	418.9	404.1	392.3	380.8	368.8	360.5	355.6	351.5	346.6	344.3
22.5°	420.9	404.9	389.7	375.9	364.2	352.3	346.4	341.4	336.7	332.2	329.1
25°	399.7	383.6	367.6	353.3	341.1	332.5	325.6	319.8	317.3	312.9	309.6
27.5°	378.8	361.6	345.1	330.8	321.2	312.7	307.0	302.5	297.9	294.1	291.2
30°	365.3	347.8	329.7	318.4	308.2	300.2	293.9	289.5	286.1	282.6	280.5
32.5°	351.8	333.7	317.7	305.5	295.9	288.9	282.5	278.2	274.6	270.8	268.3
35°	330.2	311.7	298.8	286.8	277.3	270.8	266.4	260.4	257.4	254.6	252.1
37.5°	310.1	292.9	278.9	268.4	260.1	253.7	248.0	244.8	241.1	238.6	236.5
40°	295.3	279.6	266.9	255.8	249.8	242.6	237.3	233.1	230.4	227.1	224.8
42.5°	282.0	267.4	255.0	245.1	237.6	231.5	226.4	222.2	218.7	216.4	214.5
45°	263.2	248.6	236.6	227.4	220.4	214.7	209.3	207.3	202.6	199.9	198.9
47.5°	243.7	230.7	219.1	210.6	203.5	198.0	193.0	188.8	186.2	183.5	182.0
50°	230.6	218.1	207.3	198.9	192.0	186.0	181.4	178.6	175.1	172.6	170.8
52.5°	217.5	205.9	195.1	187.1	181.1	175.1	169.9	167.2	163.9	162.3	161.0
55°	198.7	186.5	177.2	169.4	163.1	157.6	152.7	150.0	147.9	146.3	145.8
57.5°	177.5	167.8	159.2	152.1	145.6	140.4	136.1	133.5	131.7	131.4	130.0
60°	163.6	154.8	147.0	139.3	133.8	128.9	125.2	122.2	120.4	120.2	119.7
62.5°	149.7	141.3	134.0	127.3	122.3	117.7	114.1	110.8	109.7	108.5	107.5
65°	129.2	121.5	115.5	110.2	104.9	101.0	97.5	95.4	92.9	91.5	89.0
67.5°	109.0	103.1	97.3	92.8	88.6	84.9	82.0	78.9	77.2	76.1	74.3
70°	95.7	91.0	85.3	80.4	77.2	74.2	71.9	68.4	67.2	66.3	65.4
72.5°	83.1	79.0	74.2	70.2	67.0	64.2	61.5	59.9	58.7	57.8	57.3
75°	65.4	61.5	57.3	54.5	52.2	49.9	48.5	47.4	46.9	46.7	45.8
77.5°	48.0	45.9	42.6	40.4	38.9	37.9	36.7	36.1	36.0	35.0	34.7
80°	36.7	35.6	32.8	31.9	30.7	29.8	29.1	28.0	26.8	26.3	25.6
82.5°	27.3	26.2	25.0	23.6	22.6	22.0	21.4	20.9	21.1	20.4	20.1
85°	14.6	13.4	12.9	12.7	12.2	12.7	12.5	12.2	12.0	11.8	12.0
87.5°	6.7	7.2	7.4	8.1	8.0	8.6	8.9	9.0	9.3	9.5	9.6
90°	10.5	12.7	14.7	16.7	18.7	20.7	22.2	23.6	25.0	26.5	27.6
92.5°	13.5	13.6	15.4	17.1	18.9	20.7	22.2	23.6	25.0	26.5	27.4
95°	70.3	64.4	53.5	42.6	31.6	20.7	22.2	23.6	25.0	26.5	27.2
97.5°	160.3	150.2	128.6	107.0	85.3	63.7	55.6	47.5	39.4	31.2	27.2
100°	219.7	220.7	221.8	223.0	224.1	225.3	182.4	139.5	96.7	53.8	31.8
102.5°	283.8	284.7	285.4	286.1	286.7	287.4	279.3	271.2	263.1	255.0	241.1
105°	385.3	385.8	385.8	385.8	385.8	385.8	385.8	385.8	385.8	385.8	385.7
107.5°	485.8	486.1	486.7	487.2	487.8	488.4	488.4	488.5	488.6	488.6	488.2
110°	554.2	554.4	555.0	555.6	556.2	556.7	555.9	555.0	554.2	553.3	553.0



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	621.1	621.7	622.0	622.3	622.7	623.0	621.9	620.8	619.8	618.7	617.9
115°	720.5	721.3	721.6	721.9	722.2	722.5	721.3	720.2	719.0	717.9	716.4
117.5°	814.2	814.7	815.8	816.9	818.0	819.1	817.6	816.1	814.6	813.1	811.9
120°	875.4	875.7	876.5	877.4	878.3	879.1	878.6	878.0	877.4	876.8	875.8
122.5°	935.8	936.6	937.0	937.4	937.8	938.2	937.6	937.0	936.4	935.9	934.7
125°	1024.4	1025.4	1025.4	1025.4	1025.4	1025.4	1024.3	1023.1	1022.0	1020.8	1019.8
127.5°	1103.2	1103.8	1103.6	1103.5	1103.3	1103.1	1102.5	1101.9	1101.2	1100.6	1099.2
130°	1152.9	1153.8	1154.1	1154.3	1154.6	1154.9	1154.1	1153.2	1152.3	1151.5	1150.3
132.5°	1203.5	1204.1	1203.4	1202.8	1202.2	1201.5	1201.4	1201.2	1201.0	1200.8	1200.0
135°	1274.5	1275.0	1274.5	1273.9	1273.3	1272.7	1272.2	1271.6	1271.0	1270.4	1269.3
137.5°	1338.5	1339.0	1338.5	1338.0	1337.5	1337.0	1337.1	1337.2	1337.3	1337.4	1336.7
140°	1377.3	1377.5	1377.2	1376.9	1376.6	1376.3	1376.9	1377.5	1378.0	1378.6	1378.0
142.5°	1414.7	1415.1	1415.5	1415.9	1416.3	1416.7	1416.8	1416.9	1417.1	1417.2	1416.4
145°	1471.8	1472.1	1472.1	1472.1	1472.1	1472.1	1472.4	1472.7	1473.0	1473.3	1472.6
147.5°	1518.3	1518.4	1518.7	1519.1	1519.4	1519.8	1520.1	1520.5	1520.8	1521.2	1520.3
150°	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8	1550.4	1551.0	1551.5	1552.1	1551.2
152.5°	1574.8	1574.4	1575.0	1575.6	1576.2	1576.7	1577.3	1577.9	1578.5	1579.0	1578.3
155°	1611.5	1611.0	1611.5	1612.1	1612.7	1613.3	1614.1	1615.0	1615.8	1616.7	1616.0
157.5°	1644.1	1643.6	1643.6	1643.7	1643.8	1643.8	1644.7	1645.7	1646.6	1647.5	1646.8
160°	1662.0	1661.3	1661.6	1661.9	1662.2	1662.5	1663.6	1664.8	1665.9	1667.1	1666.5
162.5°	1678.6	1677.9	1678.2	1678.5	1678.7	1679.0	1680.6	1682.2	1683.9	1685.5	1685.0
165°	1700.9	1700.1	1700.4	1700.7	1701.0	1701.3	1703.0	1704.7	1706.5	1708.2	1707.9
167.5°	1717.2	1716.5	1716.7	1717.0	1717.3	1717.6	1719.7	1721.8	1723.8	1725.9	1725.6
170°	1725.6	1724.7	1725.0	1725.3	1725.6	1725.9	1728.2	1730.5	1732.8	1735.1	1735.0
172.5°	1731.8	1731.1	1731.6	1732.1	1732.6	1733.1	1735.2	1737.3	1739.4	1741.4	1741.2
175°	1739.7	1739.0	1739.3	1739.6	1739.9	1740.1	1742.4	1744.7	1747.0	1749.3	1749.2
177.5°	1744.2	1743.6	1743.9	1744.1	1744.3	1744.5	1746.2	1747.8	1749.4	1751.0	1750.9
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.2	537.2	536.6	537.4	536.6	537.2	539.2	539.4	539.6	541.1	539.0
5°	497.5	495.2	496.3	495.9	496.3	495.2	497.5	499.8	500.3	502.3	503.7
7.5°	460.8	457.9	454.9	455.8	454.9	457.9	460.8	460.8	464.4	467.1	468.9
10°	435.1	432.8	431.4	432.6	431.4	432.8	435.1	438.1	439.5	442.7	446.2
12.5°	413.5	412.1	410.9	410.4	410.9	412.1	413.5	416.7	419.9	423.7	427.5
15°	384.0	381.3	380.1	377.1	380.1	381.3	384.0	386.8	393.0	394.7	400.4
17.5°	356.9	356.0	353.0	351.7	353.0	356.0	356.9	359.3	362.1	368.1	372.4
20°	340.8	339.9	336.9	338.7	336.9	339.9	340.8	344.3	346.6	351.5	355.6
22.5°	327.5	325.5	324.5	324.0	324.5	325.5	327.5	329.1	332.2	336.7	341.4
25°	308.7	305.7	304.5	303.2	304.5	305.7	308.7	309.6	312.9	317.3	319.8
27.5°	289.9	288.3	286.8	286.4	286.8	288.3	289.9	291.2	294.1	297.9	302.5
30°	277.7	276.1	275.0	275.0	275.0	276.1	277.7	280.5	282.6	286.1	289.5
32.5°	266.8	265.6	264.4	264.2	264.4	265.6	266.8	268.3	270.8	274.6	278.2
35°	250.9	249.1	248.6	247.2	248.6	249.1	250.9	252.1	254.6	257.4	260.4
37.5°	234.4	232.9	232.9	232.7	232.9	232.9	234.4	236.5	238.6	241.1	244.8
40°	223.9	222.7	222.5	220.9	222.5	222.7	223.9	224.8	227.1	230.4	233.1
42.5°	212.6	212.0	211.2	210.5	211.2	212.0	212.6	214.5	216.4	218.7	222.2
45°	197.3	195.7	195.7	194.6	195.7	195.7	197.3	198.9	199.9	202.6	207.3
47.5°	181.5	180.3	180.4	179.2	180.4	180.3	181.5	182.0	183.5	186.2	188.8
50°	171.0	170.3	170.1	169.6	170.1	170.3	171.0	170.8	172.6	175.1	178.6
52.5°	160.5	160.1	161.0	160.0	161.0	160.1	160.5	161.0	162.3	163.9	167.2
55°	146.3	145.6	147.0	145.6	147.0	145.6	146.3	145.8	146.3	147.9	150.0
57.5°	130.0	129.3	130.6	129.9	130.6	129.3	130.0	130.0	131.4	131.7	133.5
60°	119.2	117.8	118.5	118.8	118.5	117.8	119.2	119.7	120.2	120.4	122.2
62.5°	106.5	105.6	106.2	105.1	106.2	105.6	106.5	107.5	108.5	109.7	110.8
65°	88.5	87.8	86.9	86.4	86.9	87.8	88.5	89.0	91.5	92.9	95.4
67.5°	74.4	72.7	72.6	73.0	72.6	72.7	74.4	74.3	76.1	77.2	78.9
70°	64.0	64.0	63.8	63.8	63.8	64.0	64.0	65.4	66.3	67.2	68.4
72.5°	56.8	56.6	56.2	56.0	56.2	56.6	56.8	57.3	57.8	58.7	59.9
75°	45.8	46.0	45.5	45.3	45.5	46.0	45.8	45.8	46.7	46.9	47.4
77.5°	33.8	32.8	33.3	32.8	33.3	32.8	33.8	34.7	35.0	36.0	36.1
80°	25.6	25.4	26.1	25.4	26.1	25.4	25.6	25.6	26.3	26.8	28.0
82.5°	20.3	20.1	20.4	19.9	20.4	20.1	20.3	20.1	20.4	21.1	20.9
85°	12.2	12.0	11.8	12.0	11.8	12.0	12.2	12.0	11.8	12.0	12.2
87.5°	9.9	9.9	10.1	10.3	10.1	9.9	9.9	9.6	9.5	9.3	9.0
90°	28.5	29.3	30.2	31.1	30.2	29.3	28.5	27.6	26.5	25.0	23.6
92.5°	27.8	28.2	28.6	29.0	28.6	28.2	27.8	27.4	26.5	25.0	23.6
95°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	26.5	25.0	23.6
97.5°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	31.2	39.4	47.5
100°	30.6	29.5	28.3	27.2	28.3	29.5	30.6	31.8	53.8	96.7	139.5
102.5°	221.6	202.0	182.4	162.9	182.4	202.0	221.6	241.1	255.0	263.1	271.2
105°	385.4	385.1	384.8	384.5	384.8	385.1	385.4	385.7	385.8	385.8	385.8
107.5°	487.3	486.5	485.6	484.8	485.6	486.5	487.3	488.2	488.6	488.6	488.5
110°	553.3	553.6	553.9	554.2	553.9	553.6	553.3	553.0	553.3	554.2	555.0



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	617.5	617.1	616.7	616.3	616.7	617.1	617.5	617.9	618.7	619.8	620.8
115°	714.7	713.0	711.2	709.5	711.2	713.0	714.7	716.4	717.9	719.0	720.2
117.5°	811.2	810.5	809.7	809.0	809.7	810.5	811.2	811.9	813.1	814.6	816.1
120°	874.4	872.9	871.5	870.1	871.5	872.9	874.4	875.8	876.8	877.4	878.0
122.5°	933.1	931.4	929.7	928.1	929.7	931.4	933.1	934.7	935.9	936.4	937.0
125°	1019.0	1018.1	1017.2	1016.4	1017.2	1018.1	1019.0	1019.8	1020.8	1022.0	1023.1
127.5°	1097.1	1095.0	1092.8	1090.7	1092.8	1095.0	1097.1	1099.2	1100.6	1101.2	1101.9
130°	1148.9	1147.4	1146.0	1144.6	1146.0	1147.4	1148.9	1150.3	1151.5	1152.3	1153.2
132.5°	1198.6	1197.2	1195.7	1194.3	1195.7	1197.2	1198.6	1200.0	1200.8	1201.0	1201.2
135°	1267.6	1265.8	1264.1	1262.4	1264.1	1265.8	1267.6	1269.3	1270.4	1271.0	1271.6
137.5°	1335.2	1333.7	1332.2	1330.7	1332.2	1333.7	1335.2	1336.7	1337.4	1337.3	1337.2
140°	1376.3	1374.6	1372.9	1371.1	1372.9	1374.6	1376.3	1378.0	1378.6	1378.0	1377.5
142.5°	1414.6	1412.9	1411.2	1409.5	1411.2	1412.9	1414.6	1416.4	1417.2	1417.1	1416.9
145°	1470.8	1469.1	1467.4	1465.7	1467.4	1469.1	1470.8	1472.6	1473.3	1473.0	1472.7
147.5°	1518.2	1516.1	1514.1	1512.0	1514.1	1516.1	1518.2	1520.3	1521.2	1520.8	1520.5
150°	1548.9	1546.6	1544.3	1542.0	1544.3	1546.6	1548.9	1551.2	1552.1	1551.5	1551.0
152.5°	1576.2	1574.2	1572.1	1570.0	1572.1	1574.2	1576.2	1578.3	1579.0	1578.5	1577.9
155°	1613.7	1611.4	1609.1	1606.8	1609.1	1611.4	1613.7	1616.0	1616.7	1615.8	1615.0
157.5°	1644.5	1642.2	1639.9	1637.6	1639.9	1642.2	1644.5	1646.8	1647.5	1646.6	1645.7
160°	1664.2	1661.9	1659.6	1657.3	1659.6	1661.9	1664.2	1666.5	1667.1	1665.9	1664.8
162.5°	1682.5	1679.9	1677.4	1674.9	1677.4	1679.9	1682.5	1685.0	1685.5	1683.9	1682.2
165°	1705.6	1703.3	1701.0	1698.7	1701.0	1703.3	1705.6	1707.9	1708.2	1706.5	1704.7
167.5°	1723.0	1720.5	1717.9	1715.3	1717.9	1720.5	1723.0	1725.6	1725.9	1723.8	1721.8
170°	1732.4	1729.8	1727.2	1724.6	1727.2	1729.8	1732.4	1735.0	1735.1	1732.8	1730.5
172.5°	1738.6	1736.0	1733.4	1730.8	1733.4	1736.0	1738.6	1741.2	1741.4	1739.4	1737.3
175°	1746.6	1744.0	1741.4	1738.8	1741.4	1744.0	1746.6	1749.2	1749.3	1747.0	1744.7
177.5°	1749.0	1747.2	1745.3	1743.5	1745.3	1747.2	1749.0	1750.9	1751.0	1749.4	1747.8
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	539.6	541.6	542.7	545.3	549.0	550.9	553.4	555.3	557.9	561.0	563.6
5°	504.6	510.2	513.9	519.7	525.0	530.3	537.0	541.8	548.3	555.7	561.5
7.5°	472.2	479.1	485.3	492.9	501.7	508.5	517.3	526.2	536.3	546.8	556.7
10°	451.5	458.4	466.1	475.5	484.3	493.6	504.0	514.4	527.1	538.8	552.2
12.5°	431.0	438.7	447.2	457.8	468.4	480.2	490.8	502.5	516.2	531.5	545.8
15°	405.5	412.9	422.2	431.2	443.4	456.4	470.4	485.9	501.2	518.3	536.1
17.5°	378.2	386.3	396.5	407.0	419.8	435.0	448.8	465.8	482.9	502.8	523.8
20°	360.5	368.8	380.8	392.3	404.1	418.9	435.3	452.7	470.9	491.9	515.3
22.5°	346.4	352.3	364.2	375.9	389.7	404.9	420.9	439.0	458.9	480.7	505.1
25°	325.6	332.5	341.1	353.3	367.6	383.6	399.7	418.9	440.6	462.8	488.9
27.5°	307.0	312.7	321.2	330.8	345.1	361.6	378.8	398.8	421.1	443.7	471.1
30°	293.9	300.2	308.2	318.4	329.7	347.8	365.3	385.0	407.6	430.9	459.1
32.5°	282.5	288.9	295.9	305.5	317.7	333.7	351.8	371.1	394.1	418.2	445.6
35°	266.4	270.8	277.3	286.8	298.8	311.7	330.2	350.5	372.9	397.9	425.4
37.5°	248.0	253.7	260.1	268.4	278.9	292.9	310.1	330.7	351.5	375.3	400.4
40°	237.3	242.6	249.8	255.8	266.9	279.6	295.3	316.8	337.6	360.0	382.9
42.5°	226.4	231.5	237.6	245.1	255.0	267.4	282.0	302.0	324.3	345.4	364.6
45°	209.3	214.7	220.4	227.4	236.6	248.6	263.2	281.4	300.8	320.3	334.8
47.5°	193.0	198.0	203.5	210.6	219.1	230.7	243.7	259.9	278.7	295.2	305.6
50°	181.4	186.0	192.0	198.9	207.3	218.1	230.6	246.5	262.3	277.3	286.8
52.5°	169.9	175.1	181.1	187.1	195.1	205.9	217.5	231.2	246.2	258.4	266.2
55°	152.7	157.6	163.1	169.4	177.2	186.5	198.7	209.6	221.4	231.8	236.4
57.5°	136.1	140.4	145.6	152.1	159.2	167.8	177.5	187.9	196.2	203.6	208.8
60°	125.2	128.9	133.8	139.3	147.0	154.8	163.6	173.3	179.8	186.0	190.9
62.5°	114.1	117.7	122.3	127.3	134.0	141.3	149.7	157.6	163.9	168.1	173.7
65°	97.5	101.0	104.9	110.2	115.5	121.5	129.2	134.9	139.3	144.0	147.4
67.5°	82.0	84.9	88.6	92.8	97.3	103.1	109.0	113.8	116.8	119.6	123.7
70°	71.9	74.2	77.2	80.4	85.3	91.0	95.7	99.4	101.4	104.2	109.3
72.5°	61.5	64.2	67.0	70.2	74.2	79.0	83.1	86.8	88.1	90.3	93.6
75°	48.5	49.9	52.2	54.5	57.3	61.5	65.4	66.3	67.5	69.3	71.6
77.5°	36.7	37.9	38.9	40.4	42.6	45.9	48.0	49.4	49.7	50.4	52.6
80°	29.1	29.8	30.7	31.9	32.8	35.6	36.7	38.1	38.6	39.3	40.4
82.5°	21.4	22.0	22.6	23.6	25.0	26.2	27.3	28.7	28.8	29.3	29.5
85°	12.5	12.7	12.2	12.7	12.9	13.4	14.6	15.7	15.5	15.3	15.9
87.5°	8.9	8.6	8.0	8.1	7.4	7.2	6.7	6.4	6.4	6.3	6.2
90°	22.2	20.7	18.7	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3
92.5°	22.2	20.7	18.9	17.1	15.4	13.6	13.5	15.1	16.7	18.3	19.9
95°	22.2	20.7	31.6	42.6	53.5	64.4	70.3	71.2	72.1	72.9	73.8
97.5°	55.6	63.7	85.3	107.0	128.6	150.2	160.3	158.7	157.2	155.6	154.1
100°	182.4	225.3	224.1	223.0	221.8	220.7	219.7	218.8	217.9	217.1	216.2
102.5°	279.3	287.4	286.7	286.1	285.4	284.7	283.8	282.7	281.6	280.5	279.4
105°	385.8	385.8	385.8	385.8	385.8	385.8	385.3	384.1	383.0	381.8	380.7
107.5°	488.4	488.4	487.8	487.2	486.7	486.1	485.8	485.8	485.8	485.8	485.8
110°	555.9	556.7	556.2	555.6	555.0	554.4	554.2	554.2	554.2	554.2	554.2



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	621.9	623.0	622.7	622.3	622.0	621.7	621.1	620.4	619.8	619.1	618.4
115°	721.3	722.5	722.2	721.9	721.6	721.3	720.5	719.0	717.6	716.1	714.7
117.5°	817.6	819.1	818.0	816.9	815.8	814.7	814.2	814.2	814.3	814.3	814.4
120°	878.6	879.1	878.3	877.4	876.5	875.7	875.4	875.7	876.0	876.3	876.5
122.5°	937.6	938.2	937.8	937.4	937.0	936.6	935.8	934.7	933.6	932.5	931.4
125°	1024.3	1025.4	1025.4	1025.4	1025.4	1025.4	1024.4	1022.4	1020.4	1018.4	1016.4
127.5°	1102.5	1103.1	1103.3	1103.5	1103.6	1103.8	1103.2	1101.7	1100.3	1098.9	1097.4
130°	1154.1	1154.9	1154.6	1154.3	1154.1	1153.8	1152.9	1151.5	1150.0	1148.6	1147.1
132.5°	1201.4	1201.5	1202.2	1202.8	1203.4	1204.1	1203.5	1201.9	1200.2	1198.5	1196.9
135°	1272.2	1272.7	1273.3	1273.9	1274.5	1275.0	1274.5	1272.7	1271.0	1269.3	1267.6
137.5°	1337.1	1337.0	1337.5	1338.0	1338.5	1339.0	1338.5	1337.0	1335.5	1334.0	1332.6
140°	1376.9	1376.3	1376.6	1376.9	1377.2	1377.5	1377.3	1376.7	1376.2	1375.6	1375.0
142.5°	1416.8	1416.7	1416.3	1415.9	1415.5	1415.1	1414.7	1414.4	1414.0	1413.7	1413.3
145°	1472.4	1472.1	1472.1	1472.1	1472.1	1472.1	1471.8	1471.3	1470.7	1470.1	1469.5
147.5°	1520.1	1519.8	1519.4	1519.1	1518.7	1518.4	1518.3	1518.4	1518.5	1518.6	1518.7
150°	1550.4	1549.8	1549.2	1548.7	1548.1	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8
152.5°	1577.3	1576.7	1576.2	1575.6	1575.0	1574.4	1574.8	1576.1	1577.3	1578.6	1579.8
155°	1614.1	1613.3	1612.7	1612.1	1611.5	1611.0	1611.5	1613.3	1615.0	1616.7	1618.4
157.5°	1644.7	1643.8	1643.8	1643.7	1643.6	1643.6	1644.1	1645.1	1646.1	1647.2	1648.2
160°	1663.6	1662.5	1662.2	1661.9	1661.6	1661.3	1662.0	1663.7	1665.5	1667.2	1668.9
162.5°	1680.6	1679.0	1678.7	1678.5	1678.2	1677.9	1678.6	1680.3	1682.0	1683.8	1685.5
165°	1703.0	1701.3	1701.0	1700.7	1700.4	1700.1	1700.9	1702.6	1704.3	1706.0	1707.8
167.5°	1719.7	1717.6	1717.3	1717.0	1716.7	1716.5	1717.2	1719.0	1720.8	1722.6	1724.3
170°	1728.2	1725.9	1725.6	1725.3	1725.0	1724.7	1725.6	1727.6	1729.6	1731.7	1733.7
172.5°	1735.2	1733.1	1732.6	1732.1	1731.6	1731.1	1731.8	1733.8	1735.9	1737.9	1739.9
175°	1742.4	1740.1	1739.9	1739.6	1739.3	1739.0	1739.7	1741.4	1743.2	1744.9	1746.6
177.5°	1746.2	1744.5	1744.3	1744.1	1743.9	1743.6	1744.2	1745.6	1747.0	1748.3	1749.7
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	565.6	567.3	569.7	572.5	574.7	577.1	578.4	578.4	579.5	581.9	585.1
5°	567.3	573.3	579.0	586.4	592.2	598.9	604.0	608.9	613.2	618.8	624.6
7.5°	566.8	576.8	587.2	598.8	611.7	621.9	632.4	640.6	648.7	659.4	667.7
10°	565.0	577.9	592.0	606.8	623.0	637.0	649.8	661.3	672.4	684.0	694.4
12.5°	561.6	578.1	595.3	613.1	633.5	649.6	666.0	678.3	691.3	703.9	716.7
15°	556.6	576.0	596.8	621.6	646.5	664.5	680.7	696.7	708.7	723.0	735.3
17.5°	546.3	571.3	597.5	624.5	648.5	669.4	686.4	701.6	714.4	730.1	746.8
20°	540.2	567.3	594.5	623.4	646.3	667.8	684.2	699.9	715.8	736.4	756.7
22.5°	531.7	560.6	589.5	616.9	641.1	661.9	678.8	698.0	719.0	742.3	766.9
25°	518.3	548.1	576.7	602.8	626.4	647.7	670.8	696.7	722.1	752.8	788.2
27.5°	501.2	530.0	555.5	583.1	606.5	633.6	662.4	690.5	727.1	769.4	813.5
30°	488.5	515.7	540.0	566.1	592.7	622.5	654.8	687.9	731.6	781.2	833.7
32.5°	473.7	498.4	522.4	547.6	578.3	611.0	645.4	685.8	738.0	794.5	848.8
35°	448.0	470.2	493.6	521.5	554.1	589.7	633.6	682.8	745.9	806.6	855.4
37.5°	421.1	438.7	462.1	491.6	527.1	568.2	618.1	677.9	742.6	797.2	817.9
40°	400.4	416.8	441.6	472.5	507.7	552.7	608.6	670.1	735.3	773.1	771.5
42.5°	379.9	396.5	420.3	451.5	488.1	538.5	596.1	659.9	714.9	729.3	699.3
45°	348.4	363.9	387.3	418.7	458.0	510.9	571.4	632.7	667.8	644.4	584.8
47.5°	316.4	331.4	353.1	383.8	426.7	482.1	539.4	589.6	594.5	544.4	472.9
50°	295.3	309.4	330.0	362.8	404.4	458.4	513.7	553.2	540.9	479.7	406.0
52.5°	274.8	288.3	307.6	338.6	381.1	434.0	483.3	514.4	486.0	420.9	354.6
55°	244.5	257.4	276.8	305.2	343.8	392.3	435.6	446.9	405.3	339.7	286.1
57.5°	215.7	225.2	244.3	269.5	306.7	349.5	380.4	378.4	332.5	273.4	234.9
60°	196.6	205.2	223.4	246.5	281.9	320.3	342.0	332.7	286.3	237.5	200.6
62.5°	178.9	186.9	202.2	223.4	253.8	287.2	303.0	290.2	246.4	203.5	174.1
65°	152.0	157.8	170.1	189.7	213.5	236.6	250.7	232.0	193.2	160.8	138.6
67.5°	126.9	131.9	142.8	156.9	173.3	189.3	195.0	177.5	147.3	125.5	109.8
70°	110.7	115.3	122.7	135.9	146.7	158.0	160.8	145.1	119.9	103.3	93.6
72.5°	95.2	99.4	105.9	115.2	122.7	129.2	130.5	115.9	96.6	85.2	77.7
75°	72.6	76.3	80.4	83.9	88.7	89.9	89.4	78.1	67.7	60.1	55.9
77.5°	53.3	54.9	57.4	58.8	59.0	58.9	56.6	49.4	44.0	40.9	39.2
80°	41.1	42.3	43.0	43.4	43.7	41.4	38.8	34.4	32.6	30.7	28.7
82.5°	29.9	30.6	31.3	31.4	30.2	28.2	25.9	23.7	22.4	21.5	20.7
85°	16.2	16.4	16.2	15.0	13.4	12.7	12.2	11.8	11.6	11.3	11.3
87.5°	6.4	6.4	5.9	6.5	7.0	7.2	7.6	7.8	8.0	8.3	8.6
90°	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.7	22.2	23.6
92.5°	18.3	16.7	15.1	13.5	13.6	15.4	17.1	18.9	20.7	22.2	23.6
95°	72.9	72.1	71.2	70.3	64.4	53.5	42.6	31.6	20.7	22.2	23.6
97.5°	155.6	157.2	158.7	160.3	150.2	128.6	107.0	85.3	63.7	55.6	47.5
100°	217.1	217.9	218.8	219.7	220.7	221.8	223.0	224.1	225.3	182.4	139.5
102.5°	280.5	281.6	282.7	283.8	284.7	285.4	286.1	286.7	287.4	279.3	271.2
105°	381.8	383.0	384.1	385.3	385.8	385.8	385.8	385.8	385.8	385.8	385.8
107.5°	485.8	485.8	485.8	485.8	486.1	486.7	487.2	487.8	488.4	488.4	488.5
110°	554.2	554.2	554.2	554.2	554.4	555.0	555.6	556.2	556.7	555.9	555.0





TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	619.1	619.8	620.4	621.1	621.7	622.0	622.3	622.7	623.0	621.9	620.8
115°	716.1	717.6	719.0	720.5	721.3	721.6	721.9	722.2	722.5	721.3	720.2
117.5°	814.3	814.3	814.2	814.2	814.7	815.8	816.9	818.0	819.1	817.6	816.1
120°	876.3	876.0	875.7	875.4	875.7	876.5	877.4	878.3	879.1	878.6	878.0
122.5°	932.5	933.6	934.7	935.8	936.6	937.0	937.4	937.8	938.2	937.6	937.0
125°	1018.4	1020.4	1022.4	1024.4	1025.4	1025.4	1025.4	1025.4	1025.4	1024.3	1023.1
127.5°	1098.9	1100.3	1101.7	1103.2	1103.8	1103.6	1103.5	1103.3	1103.1	1102.5	1101.9
130°	1148.6	1150.0	1151.5	1152.9	1153.8	1154.1	1154.3	1154.6	1154.9	1154.1	1153.2
132.5°	1198.5	1200.2	1201.9	1203.5	1204.1	1203.4	1202.8	1202.2	1201.5	1201.4	1201.2
135°	1269.3	1271.0	1272.7	1274.5	1275.0	1274.5	1273.9	1273.3	1272.7	1272.2	1271.6
137.5°	1334.0	1335.5	1337.0	1338.5	1339.0	1338.5	1338.0	1337.5	1337.0	1337.1	1337.2
140°	1375.6	1376.2	1376.7	1377.3	1377.5	1377.2	1376.9	1376.6	1376.3	1376.9	1377.5
142.5°	1413.7	1414.0	1414.4	1414.7	1415.1	1415.5	1415.9	1416.3	1416.7	1416.8	1416.9
145°	1470.1	1470.7	1471.3	1471.8	1472.1	1472.1	1472.1	1472.1	1472.1	1472.4	1472.7
147.5°	1518.6	1518.5	1518.4	1518.3	1518.4	1518.7	1519.1	1519.4	1519.8	1520.1	1520.5
150°	1549.2	1548.7	1548.1	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8	1550.4	1551.0
152.5°	1578.6	1577.3	1576.1	1574.8	1574.4	1575.0	1575.6	1576.2	1576.7	1577.3	1577.9
155°	1616.7	1615.0	1613.3	1611.5	1611.0	1611.5	1612.1	1612.7	1613.3	1614.1	1615.0
157.5°	1647.2	1646.1	1645.1	1644.1	1643.6	1643.6	1643.7	1643.8	1643.8	1644.7	1645.7
160°	1667.2	1665.5	1663.7	1662.0	1661.3	1661.6	1661.9	1662.2	1662.5	1663.6	1664.8
162.5°	1683.8	1682.0	1680.3	1678.6	1677.9	1678.2	1678.5	1678.7	1679.0	1680.6	1682.2
165°	1706.0	1704.3	1702.6	1700.9	1700.1	1700.4	1700.7	1701.0	1701.3	1703.0	1704.7
167.5°	1722.6	1720.8	1719.0	1717.2	1716.5	1716.7	1717.0	1717.3	1717.6	1719.7	1721.8
170°	1731.7	1729.6	1727.6	1725.6	1724.7	1725.0	1725.3	1725.6	1725.9	1728.2	1730.5
172.5°	1737.9	1735.9	1733.8	1731.8	1731.1	1731.6	1732.1	1732.6	1733.1	1735.2	1737.3
175°	1744.9	1743.2	1741.4	1739.7	1739.0	1739.3	1739.6	1739.9	1740.1	1742.4	1744.7
177.5°	1748.3	1747.0	1745.6	1744.2	1743.6	1743.9	1744.1	1744.3	1744.5	1746.2	1747.8
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	562.9	562.9	562.9	562.9	562.9	562.9	562.9
2.5°	587.5	587.5	590.6	590.4	592.5	591.7	592.1
5°	631.5	635.4	638.9	641.2	644.7	645.6	645.1
7.5°	677.2	685.9	690.1	696.0	697.0	700.1	699.8
10°	705.4	714.0	720.5	725.5	728.1	731.3	731.6
12.5°	727.6	734.9	740.6	745.3	748.4	749.4	750.0
15°	745.0	753.0	759.7	766.4	770.4	773.4	775.0
17.5°	762.4	774.9	786.7	795.8	801.3	805.9	805.9
20°	775.9	790.2	805.0	815.4	826.1	830.7	831.4
22.5°	790.3	812.2	831.3	847.4	861.4	866.2	868.0
25°	820.3	848.9	878.3	900.9	917.1	926.6	928.0
27.5°	856.5	895.2	926.1	947.0	960.4	967.5	969.0
30°	882.0	917.8	945.5	961.2	967.5	968.4	964.9
32.5°	893.4	920.2	931.3	930.4	918.1	910.0	906.9
35°	879.4	873.9	846.9	814.5	789.8	774.1	769.9
37.5°	800.3	752.5	702.8	653.9	627.9	614.6	591.9
40°	722.3	654.1	602.4	561.3	531.9	508.3	502.8
42.5°	634.3	563.9	512.2	477.0	453.5	437.4	430.3
45°	509.7	449.2	406.4	379.4	361.4	349.6	344.3
47.5°	407.7	360.8	329.7	309.7	295.9	285.7	282.8
50°	351.7	314.2	287.9	271.0	260.6	252.8	249.6
52.5°	305.5	275.2	255.0	241.1	231.3	226.4	223.7
55°	252.1	226.0	211.4	200.3	194.8	190.9	189.0
57.5°	206.2	187.3	176.7	169.0	163.9	161.4	160.5
60°	180.5	165.7	156.0	150.0	146.5	143.3	142.3
62.5°	157.7	146.1	138.6	133.3	129.9	128.5	127.9
65°	127.1	119.5	113.9	110.7	107.9	107.4	107.2
67.5°	101.0	96.5	93.6	90.3	89.3	87.7	87.3
70°	86.4	83.4	79.9	78.8	77.6	76.0	76.3
72.5°	73.3	70.3	67.9	66.4	66.0	65.3	65.9
75°	53.6	52.7	51.8	50.6	50.1	50.1	49.9
77.5°	38.3	37.5	36.5	35.8	35.6	34.7	35.0
80°	27.7	26.6	26.1	26.3	25.6	25.4	25.4
82.5°	20.5	20.1	19.6	19.7	19.5	19.3	19.5
85°	11.3	11.1	11.1	10.9	10.9	10.6	10.6
87.5°	9.1	9.5	9.4	9.4	9.6	9.9	10.3
90°	25.0	26.5	27.6	28.5	29.3	30.2	31.1
92.5°	25.0	26.5	27.4	27.8	28.2	28.6	29.0
95°	25.0	26.5	27.2	27.2	27.2	27.2	27.2
97.5°	39.4	31.2	27.2	27.2	27.2	27.2	27.2
100°	96.7	53.8	31.8	30.6	29.5	28.3	27.2
102.5°	263.1	255.0	241.1	221.6	202.0	182.4	162.9
105°	385.8	385.8	385.7	385.4	385.1	384.8	384.5
107.5°	488.6	488.6	488.2	487.3	486.5	485.6	484.8
110°	554.2	553.3	553.0	553.3	553.6	553.9	554.2



TEST NUMBER: P333652

CATALOG NUMBER: S125RDIW-S375D1340U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	619.8	618.7	617.9	617.5	617.1	616.7	616.3
115°	719.0	717.9	716.4	714.7	713.0	711.2	709.5
117.5°	814.6	813.1	811.9	811.2	810.5	809.7	809.0
120°	877.4	876.8	875.8	874.4	872.9	871.5	870.1
122.5°	936.4	935.9	934.7	933.1	931.4	929.7	928.1
125°	1022.0	1020.8	1019.8	1019.0	1018.1	1017.2	1016.4
127.5°	1101.2	1100.6	1099.2	1097.1	1095.0	1092.8	1090.7
130°	1152.3	1151.5	1150.3	1148.9	1147.4	1146.0	1144.6
132.5°	1201.0	1200.8	1200.0	1198.6	1197.2	1195.7	1194.3
135°	1271.0	1270.4	1269.3	1267.6	1265.8	1264.1	1262.4
137.5°	1337.3	1337.4	1336.7	1335.2	1333.7	1332.2	1330.7
140°	1378.0	1378.6	1378.0	1376.3	1374.6	1372.9	1371.1
142.5°	1417.1	1417.2	1416.4	1414.6	1412.9	1411.2	1409.5
145°	1473.0	1473.3	1472.6	1470.8	1469.1	1467.4	1465.7
147.5°	1520.8	1521.2	1520.3	1518.2	1516.1	1514.1	1512.0
150°	1551.5	1552.1	1551.2	1548.9	1546.6	1544.3	1542.0
152.5°	1578.5	1579.0	1578.3	1576.2	1574.2	1572.1	1570.0
155°	1615.8	1616.7	1616.0	1613.7	1611.4	1609.1	1606.8
157.5°	1646.6	1647.5	1646.8	1644.5	1642.2	1639.9	1637.6
160°	1665.9	1667.1	1666.5	1664.2	1661.9	1659.6	1657.3
162.5°	1683.9	1685.5	1685.0	1682.5	1679.9	1677.4	1674.9
165°	1706.5	1708.2	1707.9	1705.6	1703.3	1701.0	1698.7
167.5°	1723.8	1725.9	1725.6	1723.0	1720.5	1717.9	1715.3
170°	1732.8	1735.1	1735.0	1732.4	1729.8	1727.2	1724.6
172.5°	1739.4	1741.4	1741.2	1738.6	1736.0	1733.4	1730.8
175°	1747.0	1749.3	1749.2	1746.6	1744.0	1741.4	1738.8
177.5°	1749.4	1751.0	1750.9	1749.0	1747.2	1745.3	1743.5
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6

(END OF REPORT)