

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333680-927

Luminaire Tested: **S125RDIW-S850D470U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333680-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D470U927-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4081.7 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	62	60	59
2	93	85	79	74	87	81	75	71	71	67	64	63	60	57	55	53	51
3	85	76	68	63	79	71	65	60	63	58	54	56	52	49	49	46	44
4	78	67	59	53	73	64	56	51	57	51	47	50	46	42	44	41	38
5	72	60	52	46	67	57	50	44	51	45	40	45	40	37	40	36	33
6	66	54	46	40	62	51	44	39	46	40	35	41	36	32	36	32	29
7	61	49	41	35	58	47	39	34	42	36	31	37	32	29	33	29	26
8	57	45	37	31	54	42	35	30	38	32	28	34	29	26	30	27	24
9	53	41	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21
10	50	38	30	25	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6471	6471	6471	6471
5°	7445	6480	5723	6480
10°	8540	6447	5050	6447
15°	9225	6381	4488	6381
20°	10172	6304	4144	6304
25°	11771	6202	3846	6202
30°	12810	6095	3650	6095
35°	10806	5970	3470	5970
40°	7546	5746	3315	5746
45°	5598	5444	3163	5444
50°	4464	5129	3033	5129
55°	3788	4738	2917	4738
60°	3273	4389	2731	4389
65°	2916	4010	2350	4010
70°	2564	3675	2143	3675
75°	2218	3182	2011	3182
80°	1681	2678	1681	2678
85°	1401	2104	1586	2104



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.1	2.4
10°-20°	281.6	6.9
20°-30°	446.5	10.9
30°-40°	538.4	13.2
40°-50°	480.8	11.8
50°-60°	368.7	9.0
60°-70°	239.6	5.9
70°-80°	116.5	2.9
80°-90°	28.8	0.7
90°-100°	17.6	0.4
100°-110°	108.3	2.7
110°-120°	196.4	4.8
120°-130°	252.0	6.2
130°-140°	271.1	6.6
140°-150°	254.4	6.2
150°-160°	205.8	5.0
160°-170°	133.1	3.3
170°-180°	45.9	1.1
0°-30°	824.2	20.2
0°-40°	1362.6	33.4
0°-60°	2212.2	54.2
0°-90°	2597.1	63.6
90°-120°	322.2	7.9
90°-150°	1099.7	26.9
90°-180°	1485.0	36.4
0°-180°	4081.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1002	1002	1002	1002	1002	
5°	1148	1000	883	1000	1148	115
15°	1380	954	671	954	1380	395
25°	1652	870	540	870	1652	758
35°	1371	757	440	757	1371	828
45°	613	596	346	596	613	489
55°	336	421	259	421	336	305
65°	191	262	154	262	191	190
75°	89	128	81	128	89	95
85°	19	28	21	28	19	22
90°	9	0	9	0	9	5
95°	8	20	8	20	8	6
105°	106	105	106	105	106	96
115°	196	198	196	198	196	195
125°	281	281	281	281	281	250
135°	349	351	349	351	349	270
145°	406	407	406	407	406	253
155°	445	448	445	448	445	205
165°	470	473	470	473	470	133
175°	481	484	481	484	481	46
180°	484	484	484	484	484	



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1054.0	1053.4	1054.7	1051.1	1051.4	1045.8	1045.8	1041.5	1035.9	1031.7	1029.7
5°	1148.4	1149.3	1147.6	1141.5	1137.3	1131.2	1124.2	1111.8	1101.5	1091.7	1083.9
7.5°	1245.7	1246.3	1240.9	1239.0	1228.6	1221.0	1205.5	1188.7	1173.8	1154.8	1140.4
10°	1302.3	1301.9	1296.2	1291.6	1282.5	1271.1	1255.8	1236.0	1217.6	1197.0	1177.3
12.5°	1335.2	1334.1	1332.3	1326.8	1318.4	1308.2	1295.3	1275.9	1253.1	1230.6	1207.5
15°	1379.7	1376.7	1371.4	1364.4	1352.5	1340.5	1326.2	1308.9	1287.1	1261.6	1240.2
17.5°	1434.6	1434.6	1426.5	1416.7	1400.5	1379.5	1357.2	1329.4	1299.7	1271.7	1248.9
20°	1480.0	1478.8	1470.5	1451.6	1433.1	1406.8	1381.2	1347.1	1310.9	1274.3	1245.9
22.5°	1545.2	1542.0	1533.4	1508.6	1479.9	1446.0	1406.9	1365.2	1321.4	1279.9	1242.7
25°	1651.9	1649.5	1632.6	1603.9	1563.5	1511.2	1460.2	1403.1	1340.1	1285.5	1240.2
27.5°	1725.0	1722.3	1709.8	1685.8	1648.7	1593.7	1524.6	1448.3	1369.7	1294.4	1229.2
30°	1717.8	1723.9	1722.3	1711.2	1683.2	1633.9	1570.1	1484.2	1390.8	1302.3	1224.6
32.5°	1614.4	1619.9	1634.4	1656.2	1657.9	1638.2	1590.5	1511.1	1414.4	1313.8	1220.9
35°	1370.6	1378.0	1406.0	1450.0	1507.5	1555.7	1565.6	1522.8	1436.0	1327.8	1215.5
37.5°	1053.7	1094.2	1117.7	1164.0	1251.0	1339.6	1424.7	1456.0	1419.1	1322.1	1206.7
40°	895.1	904.9	946.9	999.2	1072.4	1164.5	1285.9	1373.5	1376.3	1308.9	1192.9
42.5°	766.0	778.6	807.4	849.1	911.8	1003.9	1129.2	1244.8	1298.4	1272.7	1174.8
45°	612.9	622.3	643.3	675.4	723.6	799.6	907.4	1041.1	1147.2	1188.7	1126.2
47.5°	503.5	508.6	526.9	551.3	586.9	642.4	725.8	841.9	969.2	1058.4	1049.6
50°	444.3	450.0	464.0	482.5	512.5	559.4	626.1	722.7	854.0	963.0	984.8
52.5°	398.2	403.0	411.7	429.2	453.9	490.0	543.8	631.2	749.3	865.2	915.6
55°	336.4	339.8	346.7	356.6	376.4	402.3	448.8	509.2	604.7	721.5	795.5
57.5°	285.7	287.2	291.8	300.9	314.5	333.4	367.0	418.3	486.7	591.9	673.6
60°	253.4	255.0	260.8	267.0	277.7	294.9	321.2	357.0	422.9	509.6	592.3
62.5°	227.8	228.7	231.2	237.3	246.7	260.1	280.7	310.0	362.3	438.6	516.7
65°	190.8	191.3	192.1	197.0	202.8	212.7	226.2	246.8	286.3	343.9	413.0
67.5°	155.5	156.1	158.9	160.7	166.7	171.8	179.8	195.6	223.4	262.2	315.9
70°	135.8	135.3	138.2	140.3	142.4	148.5	153.8	166.6	183.9	213.5	258.3
72.5°	117.3	116.2	117.5	118.2	121.0	125.2	130.5	138.3	151.6	172.0	206.4
75°	88.9	89.3	89.3	90.1	92.1	93.8	95.5	99.6	106.9	120.5	139.0
77.5°	62.3	61.7	63.5	63.7	64.9	66.7	68.1	69.8	72.8	78.4	87.9
80°	45.2	45.2	45.6	46.9	46.5	47.3	49.4	51.0	54.7	58.0	61.3
82.5°	34.7	34.4	34.8	35.0	34.9	35.8	36.5	36.8	38.3	39.9	42.2
85°	18.9	18.9	19.3	19.3	19.7	19.7	20.1	20.1	20.1	20.6	21.0
87.5°	9.0	8.6	8.2	8.2	8.5	9.0	8.6	8.2	8.2	8.1	8.2
90°	8.6	8.4	8.2	7.9	7.7	7.3	6.9	6.5	6.1	5.7	5.1
92.5°	8.0	7.9	7.8	7.7	7.6	7.3	6.9	6.5	6.1	5.7	5.2
95°	7.5	7.5	7.5	7.5	7.5	7.3	6.9	6.5	6.1	5.7	8.8
97.5°	7.5	7.5	7.5	7.5	7.5	8.6	10.9	13.2	15.4	17.7	23.6
100°	7.5	7.8	8.2	8.5	8.8	14.9	26.8	38.7	50.5	62.3	62.0
102.5°	45.1	50.5	55.9	61.3	66.8	70.6	72.8	75.1	77.3	79.5	79.4
105°	106.5	106.5	106.6	106.7	106.8	106.8	106.8	106.8	106.8	106.8	106.8
107.5°	134.2	134.4	134.7	134.9	135.1	135.2	135.2	135.2	135.2	135.1	135.0
110°	153.4	153.3	153.2	153.1	153.0	153.1	153.4	153.6	153.8	154.1	153.9



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	170.6	170.7	170.8	171.0	171.0	171.3	171.5	171.8	172.1	172.5	172.4
115°	196.4	196.9	197.3	197.8	198.3	198.7	199.0	199.3	199.6	199.9	199.9
117.5°	223.9	224.1	224.3	224.5	224.7	225.1	225.5	225.9	226.3	226.7	226.4
120°	240.8	241.2	241.6	242.0	242.4	242.7	242.9	243.0	243.2	243.4	243.1
122.5°	256.9	257.4	257.8	258.3	258.7	259.0	259.2	259.4	259.5	259.7	259.6
125°	281.3	281.5	281.8	282.0	282.3	282.6	282.9	283.2	283.5	283.8	283.8
127.5°	301.9	302.5	303.1	303.6	304.3	304.7	304.8	305.0	305.1	305.3	305.4
130°	316.8	317.2	317.6	318.0	318.4	318.7	318.9	319.2	319.4	319.6	319.6
132.5°	330.6	331.0	331.4	331.8	332.2	332.4	332.4	332.5	332.6	332.6	332.7
135°	349.4	349.9	350.4	350.9	351.3	351.6	351.8	352.0	352.1	352.3	352.4
137.5°	368.4	368.8	369.2	369.6	370.0	370.2	370.2	370.1	370.1	370.0	370.2
140°	379.5	380.0	380.5	381.0	381.4	381.6	381.4	381.3	381.1	381.0	381.0
142.5°	390.1	390.6	391.1	391.6	392.1	392.3	392.2	392.2	392.1	392.1	392.1
145°	405.7	406.2	406.6	407.1	407.6	407.8	407.7	407.7	407.6	407.5	407.5
147.5°	418.5	419.1	419.7	420.3	420.8	421.0	421.0	420.9	420.7	420.6	420.6
150°	426.8	427.5	428.1	428.7	429.4	429.6	429.4	429.3	429.1	429.0	428.8
152.5°	434.6	435.1	435.7	436.3	436.9	437.0	436.9	436.7	436.6	436.4	436.3
155°	444.7	445.4	446.0	446.6	447.3	447.5	447.3	447.0	446.8	446.6	446.4
157.5°	453.3	453.9	454.6	455.2	455.8	456.0	455.7	455.5	455.3	455.0	455.0
160°	458.8	459.4	460.0	460.7	461.3	461.4	461.1	460.8	460.5	460.2	460.1
162.5°	463.6	464.3	465.0	465.7	466.4	466.5	466.1	465.6	465.2	464.8	464.7
165°	470.2	470.8	471.4	472.1	472.8	472.9	472.4	471.9	471.3	470.9	470.8
167.5°	474.8	475.5	476.2	476.9	477.7	477.7	477.1	476.6	476.0	475.4	475.3
170°	477.4	478.1	478.8	479.5	480.2	480.3	479.7	479.0	478.3	477.7	477.6
172.5°	479.1	479.8	480.5	481.3	482.0	482.0	481.4	480.9	480.3	479.7	479.6
175°	481.3	482.0	482.8	483.5	484.2	484.2	483.5	482.9	482.3	481.6	481.6
177.5°	482.6	483.1	483.6	484.1	484.7	484.7	484.2	483.8	483.3	482.9	482.8
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1029.7	1027.4	1023.1	1019.1	1014.2	1010.0	1006.9	1003.4	998.7	993.2	988.6
5°	1075.2	1066.2	1054.2	1044.0	1030.8	1020.6	1009.9	999.6	989.3	976.1	964.6
7.5°	1125.8	1107.1	1088.9	1066.0	1045.3	1026.7	1009.0	991.0	973.4	954.7	936.7
10°	1156.7	1134.1	1109.0	1080.1	1053.8	1028.7	1005.8	983.1	959.3	938.3	915.6
12.5°	1185.7	1156.4	1127.8	1091.4	1059.8	1029.1	999.8	971.6	946.1	918.9	894.6
15°	1211.8	1183.0	1151.0	1106.5	1062.5	1025.5	990.9	954.3	922.7	892.2	865.1
17.5°	1221.9	1191.8	1154.4	1111.7	1063.7	1017.1	972.6	932.4	895.2	859.7	829.2
20°	1218.0	1188.7	1150.5	1109.8	1058.4	1009.9	961.7	917.3	875.8	838.3	805.8
22.5°	1208.4	1178.2	1141.3	1098.3	1049.5	998.0	946.6	899.2	855.6	816.9	781.5
25°	1194.1	1153.0	1115.2	1073.2	1026.7	975.7	922.7	870.4	823.9	784.4	745.8
27.5°	1179.2	1127.9	1079.7	1038.1	989.0	943.4	892.3	838.7	789.9	749.6	710.0
30°	1165.8	1108.2	1055.1	1007.8	961.3	918.1	869.6	817.3	767.1	725.6	685.3
32.5°	1149.0	1087.7	1029.4	974.9	930.0	887.2	843.3	793.3	744.4	701.6	660.6
35°	1127.9	1049.7	986.4	928.4	878.6	837.1	797.6	757.2	708.3	663.9	624.0
37.5°	1100.3	1011.5	938.3	875.1	822.6	780.9	749.7	712.9	668.2	625.7	588.6
40°	1083.5	983.9	903.7	841.2	786.1	742.0	712.9	681.6	640.9	600.9	564.0
42.5°	1061.1	958.6	868.9	803.7	748.2	705.8	676.3	649.0	614.9	577.3	537.7
45°	1017.2	909.5	815.3	745.4	689.4	647.8	620.3	596.0	570.1	535.6	501.0
47.5°	960.1	858.3	759.6	683.3	628.5	589.9	563.2	544.1	525.5	496.1	462.6
50°	914.4	816.1	719.9	645.8	587.4	550.8	525.7	510.5	493.6	466.8	438.9
52.5°	860.5	772.7	678.3	602.7	547.6	513.3	489.2	474.0	460.0	438.2	411.6
55°	775.4	698.5	612.0	543.4	492.8	458.2	435.2	420.8	412.6	394.0	373.1
57.5°	677.2	622.1	545.9	479.7	435.0	400.8	384.0	371.7	362.4	349.3	334.5
60°	608.8	570.1	501.8	438.9	397.8	365.3	350.1	339.8	331.1	320.0	308.5
62.5°	539.3	511.2	451.8	397.8	359.9	332.7	318.5	309.2	299.2	291.8	280.5
65°	446.3	421.2	380.1	337.7	302.8	280.9	270.7	262.4	256.3	248.0	240.2
67.5°	347.1	337.0	308.6	279.4	254.3	234.9	226.0	220.2	212.9	207.9	202.6
70°	286.3	281.4	261.2	241.9	218.4	205.3	197.0	194.6	185.5	180.6	176.9
72.5°	232.3	230.0	218.4	205.0	188.5	177.0	169.4	166.6	160.8	156.9	154.5
75°	159.1	160.0	158.0	149.3	143.1	135.8	129.1	127.5	123.4	120.1	118.0
77.5°	100.7	104.9	105.0	104.6	102.2	97.7	94.9	93.7	89.7	88.4	87.9
80°	69.1	73.6	77.7	77.3	76.5	75.3	73.2	72.0	69.9	68.7	67.9
82.5°	46.1	50.3	53.7	55.9	55.8	54.6	53.2	52.6	52.1	51.3	51.1
85°	21.8	22.7	23.8	26.8	28.8	29.2	28.8	28.4	27.2	27.6	28.0
87.5°	8.5	8.4	8.6	8.5	8.0	9.5	10.4	10.6	10.1	9.5	9.0
90°	4.6	4.0	3.5	2.9	2.3	1.7	1.0	0.4	1.0	1.7	2.3
92.5°	4.8	4.3	3.7	3.7	4.2	4.6	5.1	5.5	5.1	4.6	4.2
95°	11.8	14.8	17.8	19.5	19.7	20.0	20.2	20.4	20.2	20.0	19.7
97.5°	29.6	35.6	41.6	44.4	44.0	43.5	43.1	42.6	43.1	43.5	44.0
100°	61.7	61.4	61.1	60.8	60.6	60.4	60.1	59.8	60.1	60.4	60.6
102.5°	79.1	79.0	78.8	78.6	78.3	78.0	77.6	77.3	77.6	78.0	78.3
105°	106.8	106.8	106.8	106.6	106.3	106.0	105.7	105.4	105.7	106.0	106.3
107.5°	134.8	134.7	134.5	134.4	134.4	134.4	134.4	134.4	134.4	134.4	134.4
110°	153.8	153.6	153.4	153.4	153.4	153.4	153.4	153.4	153.4	153.4	153.4



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	172.3	172.1	172.1	171.9	171.7	171.5	171.3	171.2	171.3	171.5	171.7
115°	199.8	199.7	199.6	199.4	199.0	198.6	198.2	197.8	198.2	198.6	199.0
117.5°	226.1	225.8	225.5	225.4	225.4	225.4	225.4	225.5	225.4	225.4	225.4
120°	242.9	242.6	242.4	242.3	242.4	242.5	242.6	242.6	242.6	242.5	242.4
122.5°	259.4	259.4	259.2	259.0	258.7	258.4	258.1	257.9	258.1	258.4	258.7
125°	283.8	283.8	283.8	283.5	283.0	282.4	281.9	281.3	281.9	282.4	283.0
127.5°	305.5	305.5	305.5	305.4	305.0	304.6	304.2	303.7	304.2	304.6	305.0
130°	319.5	319.4	319.3	319.1	318.7	318.3	317.9	317.5	317.9	318.3	318.7
132.5°	333.0	333.1	333.3	333.1	332.6	332.2	331.8	331.3	331.8	332.2	332.6
135°	352.6	352.8	352.9	352.8	352.3	351.8	351.3	350.9	351.3	351.8	352.3
137.5°	370.3	370.5	370.7	370.5	370.1	369.6	369.2	368.8	369.2	369.6	370.1
140°	381.1	381.2	381.3	381.2	381.0	380.9	380.7	380.6	380.7	380.9	381.0
142.5°	391.9	391.8	391.7	391.6	391.5	391.4	391.3	391.2	391.3	391.4	391.5
145°	407.5	407.5	407.5	407.4	407.3	407.1	406.9	406.8	406.9	407.1	407.3
147.5°	420.5	420.4	420.3	420.3	420.3	420.3	420.3	420.4	420.3	420.3	420.3
150°	428.6	428.5	428.3	428.3	428.5	428.6	428.8	429.0	428.8	428.6	428.5
152.5°	436.1	435.9	435.8	435.9	436.3	436.6	437.0	437.3	437.0	436.6	436.3
155°	446.2	446.1	445.9	446.1	446.6	447.0	447.5	448.0	447.5	447.0	446.6
157.5°	455.0	455.0	455.0	455.0	455.3	455.7	455.9	456.2	455.9	455.7	455.3
160°	460.0	459.9	459.9	460.0	460.5	461.0	461.4	461.9	461.4	461.0	460.5
162.5°	464.6	464.5	464.5	464.6	465.1	465.6	466.0	466.5	466.0	465.6	465.1
165°	470.7	470.6	470.6	470.8	471.3	471.7	472.2	472.7	472.2	471.7	471.3
167.5°	475.2	475.2	475.1	475.3	475.8	476.3	476.8	477.3	476.8	476.3	475.8
170°	477.5	477.4	477.4	477.6	478.2	478.7	479.3	479.9	479.3	478.7	478.2
172.5°	479.4	479.3	479.2	479.3	479.9	480.5	481.0	481.6	481.0	480.5	479.9
175°	481.5	481.4	481.3	481.6	482.0	482.5	483.0	483.5	483.0	482.5	482.0
177.5°	482.8	482.7	482.6	482.8	483.2	483.5	483.9	484.3	483.9	483.5	483.2
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	985.2	980.6	977.3	970.7	966.1	964.2	960.6	959.6	963.2	960.6	960.2
5°	955.9	944.0	934.5	925.1	914.8	908.2	898.3	896.8	894.2	890.6	889.7
7.5°	920.8	905.3	893.1	877.5	863.9	852.9	840.6	834.8	831.6	826.8	820.4
10°	897.1	878.6	862.1	846.5	829.7	816.1	803.7	794.3	788.1	782.4	779.9
12.5°	873.8	854.9	833.9	814.9	796.1	780.9	767.2	761.0	754.2	747.5	741.7
15°	837.5	812.4	789.3	767.5	751.5	735.1	721.9	712.9	702.6	699.7	688.6
17.5°	799.0	774.4	747.4	724.5	705.8	687.8	673.3	663.0	655.3	644.7	639.5
20°	775.0	745.8	719.5	698.5	677.9	656.5	641.7	633.0	625.7	617.0	612.9
22.5°	749.3	720.7	693.8	669.2	648.2	627.2	616.7	607.7	599.3	591.4	585.9
25°	711.6	682.9	654.4	628.9	607.1	591.9	579.6	569.3	564.7	557.0	551.2
27.5°	674.4	643.7	614.3	588.9	571.8	556.7	546.6	538.4	530.3	523.5	518.5
30°	650.3	619.1	587.0	566.8	548.7	534.3	523.2	515.4	509.2	503.0	499.4
32.5°	626.3	594.1	565.6	543.8	526.6	514.3	502.8	495.4	488.9	482.0	477.7
35°	587.8	554.9	531.9	510.5	493.6	482.1	474.3	463.6	458.2	453.3	448.8
37.5°	552.0	521.4	496.5	477.8	463.1	451.6	441.6	435.8	429.2	424.8	421.0
40°	525.7	497.7	475.1	455.3	444.7	431.9	422.5	415.0	410.1	404.3	400.2
42.5°	502.0	476.0	454.0	436.3	422.9	412.2	403.1	395.6	389.4	385.2	381.8
45°	468.5	442.6	421.2	404.7	392.4	382.1	372.6	369.0	360.8	355.8	354.2
47.5°	433.9	410.7	390.1	374.9	362.3	352.5	343.6	336.0	331.5	326.7	324.1
50°	410.5	388.3	369.0	354.2	341.8	331.1	322.9	318.0	311.8	307.3	304.0
52.5°	387.1	366.6	347.3	333.1	322.4	311.7	302.5	297.5	291.8	288.8	286.5
55°	353.8	331.9	315.5	301.5	290.4	280.5	271.9	267.0	263.2	260.4	259.5
57.5°	315.9	298.7	283.4	270.8	259.2	249.9	242.3	237.7	234.4	233.9	231.5
60°	291.2	275.6	261.6	248.0	238.1	229.5	222.9	217.6	214.3	213.9	213.1
62.5°	266.6	251.6	238.6	226.6	217.8	209.5	203.2	197.2	195.2	193.1	191.4
65°	230.0	216.3	205.7	196.2	186.7	179.7	173.6	169.8	165.3	162.9	158.4
67.5°	194.0	183.5	173.2	165.2	157.8	151.1	146.0	140.5	137.4	135.5	132.2
70°	170.3	162.1	151.8	143.1	137.4	132.1	127.9	121.8	119.7	118.0	116.4
72.5°	147.9	140.7	132.1	125.1	119.3	114.2	109.5	106.6	104.6	102.9	102.0
75°	116.4	109.4	102.0	97.0	93.0	88.9	86.3	84.3	83.5	83.1	81.4
77.5°	85.5	81.8	75.8	71.9	69.2	67.6	65.4	64.2	64.2	62.3	61.8
80°	65.4	63.4	58.4	56.8	54.7	53.1	51.8	49.7	47.7	46.9	45.6
82.5°	48.6	46.6	44.6	42.0	40.2	39.2	38.0	37.2	37.5	36.4	35.8
85°	25.9	23.8	23.1	22.7	21.8	22.7	22.2	21.8	21.4	21.0	21.4
87.5°	8.8	9.0	8.7	9.5	8.6	9.0	9.1	8.9	9.0	9.0	8.8
90°	2.9	3.5	4.0	4.6	5.1	5.7	6.1	6.5	6.9	7.3	7.7
92.5°	3.7	3.7	4.3	4.8	5.2	5.7	6.1	6.5	6.9	7.3	7.6
95°	19.5	17.8	14.8	11.8	8.8	5.7	6.1	6.5	6.9	7.3	7.5
97.5°	44.4	41.6	35.6	29.6	23.6	17.7	15.4	13.2	10.9	8.6	7.5
100°	60.8	61.1	61.4	61.7	62.0	62.3	50.5	38.7	26.8	14.9	8.8
102.5°	78.6	78.8	79.0	79.1	79.4	79.5	77.3	75.1	72.8	70.6	66.8
105°	106.6	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8	106.8
107.5°	134.4	134.5	134.7	134.8	135.0	135.1	135.2	135.2	135.2	135.2	135.1
110°	153.4	153.4	153.6	153.8	153.9	154.1	153.8	153.6	153.4	153.1	153.0



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	171.9	172.1	172.1	172.3	172.4	172.5	172.1	171.8	171.5	171.3	171.0
115°	199.4	199.6	199.7	199.8	199.9	199.9	199.6	199.3	199.0	198.7	198.3
117.5°	225.4	225.5	225.8	226.1	226.4	226.7	226.3	225.9	225.5	225.1	224.7
120°	242.3	242.4	242.6	242.9	243.1	243.4	243.2	243.0	242.9	242.7	242.4
122.5°	259.0	259.2	259.4	259.4	259.6	259.7	259.5	259.4	259.2	259.0	258.7
125°	283.5	283.8	283.8	283.8	283.8	283.8	283.5	283.2	282.9	282.6	282.3
127.5°	305.4	305.5	305.5	305.5	305.4	305.3	305.1	305.0	304.8	304.7	304.3
130°	319.1	319.3	319.4	319.5	319.6	319.6	319.4	319.2	318.9	318.7	318.4
132.5°	333.1	333.3	333.1	333.0	332.7	332.6	332.6	332.5	332.4	332.4	332.2
135°	352.8	352.9	352.8	352.6	352.4	352.3	352.1	352.0	351.8	351.6	351.3
137.5°	370.5	370.7	370.5	370.3	370.2	370.0	370.1	370.1	370.2	370.2	370.0
140°	381.2	381.3	381.2	381.1	381.0	381.0	381.1	381.3	381.4	381.6	381.4
142.5°	391.6	391.7	391.8	391.9	392.1	392.1	392.1	392.2	392.2	392.3	392.1
145°	407.4	407.5	407.5	407.5	407.5	407.5	407.6	407.7	407.7	407.8	407.6
147.5°	420.3	420.3	420.4	420.5	420.6	420.6	420.7	420.9	421.0	421.0	420.8
150°	428.3	428.3	428.5	428.6	428.8	429.0	429.1	429.3	429.4	429.6	429.4
152.5°	435.9	435.8	435.9	436.1	436.3	436.4	436.6	436.7	436.9	437.0	436.9
155°	446.1	445.9	446.1	446.2	446.4	446.6	446.8	447.0	447.3	447.5	447.3
157.5°	455.0	455.0	455.0	455.0	455.0	455.0	455.3	455.5	455.7	456.0	455.8
160°	460.0	459.9	459.9	460.0	460.1	460.2	460.5	460.8	461.1	461.4	461.3
162.5°	464.6	464.5	464.5	464.6	464.7	464.8	465.2	465.6	466.1	466.5	466.4
165°	470.8	470.6	470.6	470.7	470.8	470.9	471.3	471.9	472.4	472.9	472.8
167.5°	475.3	475.1	475.2	475.2	475.3	475.4	476.0	476.6	477.1	477.7	477.7
170°	477.6	477.4	477.4	477.5	477.6	477.7	478.3	479.0	479.7	480.3	480.2
172.5°	479.3	479.2	479.3	479.4	479.6	479.7	480.3	480.9	481.4	482.0	482.0
175°	481.6	481.3	481.4	481.5	481.6	481.6	482.3	482.9	483.5	484.2	484.2
177.5°	482.8	482.6	482.7	482.8	482.8	482.9	483.3	483.8	484.2	484.7	484.7
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	959.9	956.3	955.3	956.6	955.3	956.3	959.9	960.2	960.6	963.2	959.6
5°	885.6	881.5	883.5	882.7	883.5	881.5	885.6	889.7	890.6	894.2	896.8
7.5°	820.3	815.2	809.8	811.5	809.8	815.2	820.3	820.4	826.8	831.6	834.8
10°	774.5	770.5	767.9	770.0	767.9	770.5	774.5	779.9	782.4	788.1	794.3
12.5°	736.0	733.6	731.4	730.6	731.4	733.6	736.0	741.7	747.5	754.2	761.0
15°	683.7	678.7	676.7	671.3	676.7	678.7	683.7	688.6	699.7	702.6	712.9
17.5°	635.3	633.7	628.4	626.1	628.4	633.7	635.3	639.5	644.7	655.3	663.0
20°	606.7	605.1	599.8	603.0	599.8	605.1	606.7	612.9	617.0	625.7	633.0
22.5°	583.0	579.4	577.7	576.7	577.7	579.4	583.0	585.9	591.4	599.3	607.7
25°	549.5	544.2	542.2	539.7	542.2	544.2	549.5	551.2	557.0	564.7	569.3
27.5°	516.2	513.3	510.6	509.9	510.6	513.3	516.2	518.5	523.5	530.3	538.4
30°	494.4	491.5	489.5	489.5	489.5	491.5	494.4	499.4	503.0	509.2	515.4
32.5°	475.0	472.8	470.7	470.4	470.7	472.8	475.0	477.7	482.0	488.9	495.4
35°	446.7	443.5	442.6	440.1	442.6	443.5	446.7	448.8	453.3	458.2	463.6
37.5°	417.3	414.6	414.5	414.3	414.5	414.6	417.3	421.0	424.8	429.2	435.8
40°	398.6	396.6	396.1	393.2	396.1	396.6	398.6	400.2	404.3	410.1	415.0
42.5°	378.5	377.5	376.0	374.8	376.0	377.5	378.5	381.8	385.2	389.4	395.6
45°	351.3	348.4	348.4	346.3	348.4	348.4	351.3	354.2	355.8	360.8	369.0
47.5°	323.1	320.9	321.2	319.0	321.2	320.9	323.1	324.1	326.7	331.5	336.0
50°	304.4	303.2	302.8	301.9	302.8	303.2	304.4	304.0	307.3	311.8	318.0
52.5°	285.7	285.0	286.6	284.8	286.6	285.0	285.7	286.5	288.8	291.8	297.5
55°	260.4	259.1	261.6	259.1	261.6	259.1	260.4	259.5	260.4	263.2	267.0
57.5°	231.3	230.2	232.4	231.2	232.4	230.2	231.3	231.5	233.9	234.4	237.7
60°	212.2	209.8	211.0	211.4	211.0	209.8	212.2	213.1	213.9	214.3	217.6
62.5°	189.6	188.1	188.9	187.1	188.9	188.1	189.6	191.4	193.1	195.2	197.2
65°	157.6	156.3	154.6	153.8	154.6	156.3	157.6	158.4	162.9	165.3	169.8
67.5°	132.4	129.4	129.4	130.0	129.4	129.4	132.4	132.2	135.5	137.4	140.5
70°	113.9	113.9	113.5	113.5	113.5	113.9	113.9	116.4	118.0	119.7	121.8
72.5°	101.1	100.8	100.1	99.7	100.1	100.8	101.1	102.0	102.9	104.6	106.6
75°	81.4	81.8	81.0	80.6	81.0	81.8	81.4	81.4	83.1	83.5	84.3
77.5°	60.1	58.4	59.3	58.4	59.3	58.4	60.1	61.8	62.3	64.2	64.2
80°	45.6	45.2	46.5	45.2	46.5	45.2	45.6	45.6	46.9	47.7	49.7
82.5°	36.1	35.7	36.3	35.4	36.3	35.7	36.1	35.8	36.4	37.5	37.2
85°	21.8	21.4	21.0	21.4	21.0	21.4	21.8	21.4	21.0	21.4	21.8
87.5°	9.1	8.9	8.9	9.0	8.9	8.9	9.1	8.8	9.0	9.0	8.9
90°	7.9	8.2	8.4	8.6	8.4	8.2	7.9	7.7	7.3	6.9	6.5
92.5°	7.7	7.8	7.9	8.0	7.9	7.8	7.7	7.6	7.3	6.9	6.5
95°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.3	6.9	6.5
97.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	8.6	10.9	13.2
100°	8.5	8.2	7.8	7.5	7.8	8.2	8.5	8.8	14.9	26.8	38.7
102.5°	61.3	55.9	50.5	45.1	50.5	55.9	61.3	66.8	70.6	72.8	75.1
105°	106.7	106.6	106.5	106.5	106.5	106.6	106.7	106.8	106.8	106.8	106.8
107.5°	134.9	134.7	134.4	134.2	134.4	134.7	134.9	135.1	135.2	135.2	135.2
110°	153.1	153.2	153.3	153.4	153.3	153.2	153.1	153.0	153.1	153.4	153.6



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	171.0	170.8	170.7	170.6	170.7	170.8	171.0	171.0	171.3	171.5	171.8
115°	197.8	197.3	196.9	196.4	196.9	197.3	197.8	198.3	198.7	199.0	199.3
117.5°	224.5	224.3	224.1	223.9	224.1	224.3	224.5	224.7	225.1	225.5	225.9
120°	242.0	241.6	241.2	240.8	241.2	241.6	242.0	242.4	242.7	242.9	243.0
122.5°	258.3	257.8	257.4	256.9	257.4	257.8	258.3	258.7	259.0	259.2	259.4
125°	282.0	281.8	281.5	281.3	281.5	281.8	282.0	282.3	282.6	282.9	283.2
127.5°	303.6	303.1	302.5	301.9	302.5	303.1	303.6	304.3	304.7	304.8	305.0
130°	318.0	317.6	317.2	316.8	317.2	317.6	318.0	318.4	318.7	318.9	319.2
132.5°	331.8	331.4	331.0	330.6	331.0	331.4	331.8	332.2	332.4	332.4	332.5
135°	350.9	350.4	349.9	349.4	349.9	350.4	350.9	351.3	351.6	351.8	352.0
137.5°	369.6	369.2	368.8	368.4	368.8	369.2	369.6	370.0	370.2	370.2	370.1
140°	381.0	380.5	380.0	379.5	380.0	380.5	381.0	381.4	381.6	381.4	381.3
142.5°	391.6	391.1	390.6	390.1	390.6	391.1	391.6	392.1	392.3	392.2	392.2
145°	407.1	406.6	406.2	405.7	406.2	406.6	407.1	407.6	407.8	407.7	407.7
147.5°	420.3	419.7	419.1	418.5	419.1	419.7	420.3	420.8	421.0	421.0	420.9
150°	428.7	428.1	427.5	426.8	427.5	428.1	428.7	429.4	429.6	429.4	429.3
152.5°	436.3	435.7	435.1	434.6	435.1	435.7	436.3	436.9	437.0	436.9	436.7
155°	446.6	446.0	445.4	444.7	445.4	446.0	446.6	447.3	447.5	447.3	447.0
157.5°	455.2	454.6	453.9	453.3	453.9	454.6	455.2	455.8	456.0	455.7	455.5
160°	460.7	460.0	459.4	458.8	459.4	460.0	460.7	461.3	461.4	461.1	460.8
162.5°	465.7	465.0	464.3	463.6	464.3	465.0	465.7	466.4	466.5	466.1	465.6
165°	472.1	471.4	470.8	470.2	470.8	471.4	472.1	472.8	472.9	472.4	471.9
167.5°	476.9	476.2	475.5	474.8	475.5	476.2	476.9	477.7	477.7	477.1	476.6
170°	479.5	478.8	478.1	477.4	478.1	478.8	479.5	480.2	480.3	479.7	479.0
172.5°	481.3	480.5	479.8	479.1	479.8	480.5	481.3	482.0	482.0	481.4	480.9
175°	483.5	482.8	482.0	481.3	482.0	482.8	483.5	484.2	484.2	483.5	482.9
177.5°	484.1	483.6	483.1	482.6	483.1	483.6	484.1	484.7	484.7	484.2	483.8
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	960.6	964.2	966.1	970.7	977.3	980.6	985.2	988.6	993.2	998.7	1003.4
5°	898.3	908.2	914.8	925.1	934.5	944.0	955.9	964.6	976.1	989.3	999.6
7.5°	840.6	852.9	863.9	877.5	893.1	905.3	920.8	936.7	954.7	973.4	991.0
10°	803.7	816.1	829.7	846.5	862.1	878.6	897.1	915.6	938.3	959.3	983.1
12.5°	767.2	780.9	796.1	814.9	833.9	854.9	873.8	894.6	918.9	946.1	971.6
15°	721.9	735.1	751.5	767.5	789.3	812.4	837.5	865.1	892.2	922.7	954.3
17.5°	673.3	687.8	705.8	724.5	747.4	774.4	799.0	829.2	859.7	895.2	932.4
20°	641.7	656.5	677.9	698.5	719.5	745.8	775.0	805.8	838.3	875.8	917.3
22.5°	616.7	627.2	648.2	669.2	693.8	720.7	749.3	781.5	816.9	855.6	899.2
25°	579.6	591.9	607.1	628.9	654.4	682.9	711.6	745.8	784.4	823.9	870.4
27.5°	546.6	556.7	571.8	588.9	614.3	643.7	674.4	710.0	749.6	789.9	838.7
30°	523.2	534.3	548.7	566.8	587.0	619.1	650.3	685.3	725.6	767.1	817.3
32.5°	502.8	514.3	526.6	543.8	565.6	594.1	626.3	660.6	701.6	744.4	793.3
35°	474.3	482.1	493.6	510.5	531.9	554.9	587.8	624.0	663.9	708.3	757.2
37.5°	441.6	451.6	463.1	477.8	496.5	521.4	552.0	588.6	625.7	668.2	712.9
40°	422.5	431.9	444.7	455.3	475.1	497.7	525.7	564.0	600.9	640.9	681.6
42.5°	403.1	412.2	422.9	436.3	454.0	476.0	502.0	537.7	577.3	614.9	649.0
45°	372.6	382.1	392.4	404.7	421.2	442.6	468.5	501.0	535.6	570.1	596.0
47.5°	343.6	352.5	362.3	374.9	390.1	410.7	433.9	462.6	496.1	525.5	544.1
50°	322.9	331.1	341.8	354.2	369.0	388.3	410.5	438.9	466.8	493.6	510.5
52.5°	302.5	311.7	322.4	333.1	347.3	366.6	387.1	411.6	438.2	460.0	474.0
55°	271.9	280.5	290.4	301.5	315.5	331.9	353.8	373.1	394.0	412.6	420.8
57.5°	242.3	249.9	259.2	270.8	283.4	298.7	315.9	334.5	349.3	362.4	371.7
60°	222.9	229.5	238.1	248.0	261.6	275.6	291.2	308.5	320.0	331.1	339.8
62.5°	203.2	209.5	217.8	226.6	238.6	251.6	266.6	280.5	291.8	299.2	309.2
65°	173.6	179.7	186.7	196.2	205.7	216.3	230.0	240.2	248.0	256.3	262.4
67.5°	146.0	151.1	157.8	165.2	173.2	183.5	194.0	202.6	207.9	212.9	220.2
70°	127.9	132.1	137.4	143.1	151.8	162.1	170.3	176.9	180.6	185.5	194.6
72.5°	109.5	114.2	119.3	125.1	132.1	140.7	147.9	154.5	156.9	160.8	166.6
75°	86.3	88.9	93.0	97.0	102.0	109.4	116.4	118.0	120.1	123.4	127.5
77.5°	65.4	67.6	69.2	71.9	75.8	81.8	85.5	87.9	88.4	89.7	93.7
80°	51.8	53.1	54.7	56.8	58.4	63.4	65.4	67.9	68.7	69.9	72.0
82.5°	38.0	39.2	40.2	42.0	44.6	46.6	48.6	51.1	51.3	52.1	52.6
85°	22.2	22.7	21.8	22.7	23.1	23.8	25.9	28.0	27.6	27.2	28.4
87.5°	9.1	9.0	8.6	9.5	8.7	9.0	8.8	9.0	9.5	10.1	10.6
90°	6.1	5.7	5.1	4.6	4.0	3.5	2.9	2.3	1.7	1.0	0.4
92.5°	6.1	5.7	5.2	4.8	4.3	3.7	3.7	4.2	4.6	5.1	5.5
95°	6.1	5.7	8.8	11.8	14.8	17.8	19.5	19.7	20.0	20.2	20.4
97.5°	15.4	17.7	23.6	29.6	35.6	41.6	44.4	44.0	43.5	43.1	42.6
100°	50.5	62.3	62.0	61.7	61.4	61.1	60.8	60.6	60.4	60.1	59.8
102.5°	77.3	79.5	79.4	79.1	79.0	78.8	78.6	78.3	78.0	77.6	77.3
105°	106.8	106.8	106.8	106.8	106.8	106.8	106.6	106.3	106.0	105.7	105.4
107.5°	135.2	135.1	135.0	134.8	134.7	134.5	134.4	134.4	134.4	134.4	134.4
110°	153.8	154.1	153.9	153.8	153.6	153.4	153.4	153.4	153.4	153.4	153.4



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	172.1	172.5	172.4	172.3	172.1	172.1	171.9	171.7	171.5	171.3	171.2
115°	199.6	199.9	199.9	199.8	199.7	199.6	199.4	199.0	198.6	198.2	197.8
117.5°	226.3	226.7	226.4	226.1	225.8	225.5	225.4	225.4	225.4	225.4	225.5
120°	243.2	243.4	243.1	242.9	242.6	242.4	242.3	242.4	242.5	242.6	242.6
122.5°	259.5	259.7	259.6	259.4	259.4	259.2	259.0	258.7	258.4	258.1	257.9
125°	283.5	283.8	283.8	283.8	283.8	283.8	283.5	283.0	282.4	281.9	281.3
127.5°	305.1	305.3	305.4	305.5	305.5	305.5	305.4	305.0	304.6	304.2	303.7
130°	319.4	319.6	319.6	319.5	319.4	319.3	319.1	318.7	318.3	317.9	317.5
132.5°	332.6	332.6	332.7	333.0	333.1	333.3	333.1	332.6	332.2	331.8	331.3
135°	352.1	352.3	352.4	352.6	352.8	352.9	352.8	352.3	351.8	351.3	350.9
137.5°	370.1	370.0	370.2	370.3	370.5	370.7	370.5	370.1	369.6	369.2	368.8
140°	381.1	381.0	381.0	381.1	381.2	381.3	381.2	381.0	380.9	380.7	380.6
142.5°	392.1	392.1	392.1	391.9	391.8	391.7	391.6	391.5	391.4	391.3	391.2
145°	407.6	407.5	407.5	407.5	407.5	407.5	407.4	407.3	407.1	406.9	406.8
147.5°	420.7	420.6	420.6	420.5	420.4	420.3	420.3	420.3	420.3	420.3	420.4
150°	429.1	429.0	428.8	428.6	428.5	428.3	428.3	428.5	428.6	428.8	429.0
152.5°	436.6	436.4	436.3	436.1	435.9	435.8	435.9	436.3	436.6	437.0	437.3
155°	446.8	446.6	446.4	446.2	446.1	445.9	446.1	446.6	447.0	447.5	448.0
157.5°	455.3	455.0	455.0	455.0	455.0	455.0	455.0	455.3	455.7	455.9	456.2
160°	460.5	460.2	460.1	460.0	459.9	459.9	460.0	460.5	461.0	461.4	461.9
162.5°	465.2	464.8	464.7	464.6	464.5	464.5	464.6	465.1	465.6	466.0	466.5
165°	471.3	470.9	470.8	470.7	470.6	470.6	470.8	471.3	471.7	472.2	472.7
167.5°	476.0	475.4	475.3	475.2	475.2	475.1	475.3	475.8	476.3	476.8	477.3
170°	478.3	477.7	477.6	477.5	477.4	477.4	477.6	478.2	478.7	479.3	479.9
172.5°	480.3	479.7	479.6	479.4	479.3	479.2	479.3	479.9	480.5	481.0	481.6
175°	482.3	481.6	481.6	481.5	481.4	481.3	481.6	482.0	482.5	483.0	483.5
177.5°	483.3	482.9	482.8	482.8	482.7	482.6	482.8	483.2	483.5	483.9	484.3
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1006.9	1010.0	1014.2	1019.1	1023.1	1027.4	1029.7	1029.7	1031.7	1035.9	1041.5
5°	1009.9	1020.6	1030.8	1044.0	1054.2	1066.2	1075.2	1083.9	1091.7	1101.5	1111.8
7.5°	1009.0	1026.7	1045.3	1066.0	1088.9	1107.1	1125.8	1140.4	1154.8	1173.8	1188.7
10°	1005.8	1028.7	1053.8	1080.1	1109.0	1134.1	1156.7	1177.3	1197.0	1217.6	1236.0
12.5°	999.8	1029.1	1059.8	1091.4	1127.8	1156.4	1185.7	1207.5	1230.6	1253.1	1275.9
15°	990.9	1025.5	1062.5	1106.5	1151.0	1183.0	1211.8	1240.2	1261.6	1287.1	1308.9
17.5°	972.6	1017.1	1063.7	1111.7	1154.4	1191.8	1221.9	1248.9	1271.7	1299.7	1329.4
20°	961.7	1009.9	1058.4	1109.8	1150.5	1188.7	1218.0	1245.9	1274.3	1310.9	1347.1
22.5°	946.6	998.0	1049.5	1098.3	1141.3	1178.2	1208.4	1242.7	1279.9	1321.4	1365.2
25°	922.7	975.7	1026.7	1073.2	1115.2	1153.0	1194.1	1240.2	1285.5	1340.1	1403.1
27.5°	892.3	943.4	989.0	1038.1	1079.7	1127.9	1179.2	1229.2	1294.4	1369.7	1448.3
30°	869.6	918.1	961.3	1007.8	1055.1	1108.2	1165.8	1224.6	1302.3	1390.8	1484.2
32.5°	843.3	887.2	930.0	974.9	1029.4	1087.7	1149.0	1220.9	1313.8	1414.4	1511.1
35°	797.6	837.1	878.6	928.4	986.4	1049.7	1127.9	1215.5	1327.8	1436.0	1522.8
37.5°	749.7	780.9	822.6	875.1	938.3	1011.5	1100.3	1206.7	1322.1	1419.1	1456.0
40°	712.9	742.0	786.1	841.2	903.7	983.9	1083.5	1192.9	1308.9	1376.3	1373.5
42.5°	676.3	705.8	748.2	803.7	868.9	958.6	1061.1	1174.8	1272.7	1298.4	1244.8
45°	620.3	647.8	689.4	745.4	815.3	909.5	1017.2	1126.2	1188.7	1147.2	1041.1
47.5°	563.2	589.9	628.5	683.3	759.6	858.3	960.1	1049.6	1058.4	969.2	841.9
50°	525.7	550.8	587.4	645.8	719.9	816.1	914.4	984.8	963.0	854.0	722.7
52.5°	489.2	513.3	547.6	602.7	678.3	772.7	860.5	915.6	865.2	749.3	631.2
55°	435.2	458.2	492.8	543.4	612.0	698.5	775.4	795.5	721.5	604.7	509.2
57.5°	384.0	400.8	435.0	479.7	545.9	622.1	677.2	673.6	591.9	486.7	418.3
60°	350.1	365.3	397.8	438.9	501.8	570.1	608.8	592.3	509.6	422.9	357.0
62.5°	318.5	332.7	359.9	397.8	451.8	511.2	539.3	516.7	438.6	362.3	310.0
65°	270.7	280.9	302.8	337.7	380.1	421.2	446.3	413.0	343.9	286.3	246.8
67.5°	226.0	234.9	254.3	279.4	308.6	337.0	347.1	315.9	262.2	223.4	195.6
70°	197.0	205.3	218.4	241.9	261.2	281.4	286.3	258.3	213.5	183.9	166.6
72.5°	169.4	177.0	188.5	205.0	218.4	230.0	232.3	206.4	172.0	151.6	138.3
75°	129.1	135.8	143.1	149.3	158.0	160.0	159.1	139.0	120.5	106.9	99.6
77.5°	94.9	97.7	102.2	104.6	105.0	104.9	100.7	87.9	78.4	72.8	69.8
80°	73.2	75.3	76.5	77.3	77.7	73.6	69.1	61.3	58.0	54.7	51.0
82.5°	53.2	54.6	55.8	55.9	53.7	50.3	46.1	42.2	39.9	38.3	36.8
85°	28.8	29.2	28.8	26.8	23.8	22.7	21.8	21.0	20.6	20.1	20.1
87.5°	10.4	9.5	8.0	8.5	8.6	8.4	8.5	8.2	8.1	8.2	8.2
90°	1.0	1.7	2.3	2.9	3.5	4.0	4.6	5.1	5.7	6.1	6.5
92.5°	5.1	4.6	4.2	3.7	3.7	4.3	4.8	5.2	5.7	6.1	6.5
95°	20.2	20.0	19.7	19.5	17.8	14.8	11.8	8.8	5.7	6.1	6.5
97.5°	43.1	43.5	44.0	44.4	41.6	35.6	29.6	23.6	17.7	15.4	13.2
100°	60.1	60.4	60.6	60.8	61.1	61.4	61.7	62.0	62.3	50.5	38.7
102.5°	77.6	78.0	78.3	78.6	78.8	79.0	79.1	79.4	79.5	77.3	75.1
105°	105.7	106.0	106.3	106.6	106.8	106.8	106.8	106.8	106.8	106.8	106.8
107.5°	134.4	134.4	134.4	134.4	134.5	134.7	134.8	135.0	135.1	135.2	135.2
110°	153.4	153.4	153.4	153.4	153.4	153.6	153.8	153.9	154.1	153.8	153.6



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	171.3	171.5	171.7	171.9	172.1	172.1	172.3	172.4	172.5	172.1	171.8
115°	198.2	198.6	199.0	199.4	199.6	199.7	199.8	199.9	199.9	199.6	199.3
117.5°	225.4	225.4	225.4	225.4	225.5	225.8	226.1	226.4	226.7	226.3	225.9
120°	242.6	242.5	242.4	242.3	242.4	242.6	242.9	243.1	243.4	243.2	243.0
122.5°	258.1	258.4	258.7	259.0	259.2	259.4	259.4	259.6	259.7	259.5	259.4
125°	281.9	282.4	283.0	283.5	283.8	283.8	283.8	283.8	283.8	283.5	283.2
127.5°	304.2	304.6	305.0	305.4	305.5	305.5	305.5	305.4	305.3	305.1	305.0
130°	317.9	318.3	318.7	319.1	319.3	319.4	319.5	319.6	319.6	319.4	319.2
132.5°	331.8	332.2	332.6	333.1	333.3	333.1	333.0	332.7	332.6	332.6	332.5
135°	351.3	351.8	352.3	352.8	352.9	352.8	352.6	352.4	352.3	352.1	352.0
137.5°	369.2	369.6	370.1	370.5	370.7	370.5	370.3	370.2	370.0	370.1	370.1
140°	380.7	380.9	381.0	381.2	381.3	381.2	381.1	381.0	381.0	381.1	381.3
142.5°	391.3	391.4	391.5	391.6	391.7	391.8	391.9	392.1	392.1	392.1	392.2
145°	406.9	407.1	407.3	407.4	407.5	407.5	407.5	407.5	407.5	407.6	407.7
147.5°	420.3	420.3	420.3	420.3	420.3	420.4	420.5	420.6	420.6	420.7	420.9
150°	428.8	428.6	428.5	428.3	428.3	428.5	428.6	428.8	429.0	429.1	429.3
152.5°	437.0	436.6	436.3	435.9	435.8	435.9	436.1	436.3	436.4	436.6	436.7
155°	447.5	447.0	446.6	446.1	445.9	446.1	446.2	446.4	446.6	446.8	447.0
157.5°	455.9	455.7	455.3	455.0	455.0	455.0	455.0	455.0	455.0	455.3	455.5
160°	461.4	461.0	460.5	460.0	459.9	459.9	460.0	460.1	460.2	460.5	460.8
162.5°	466.0	465.6	465.1	464.6	464.5	464.5	464.6	464.7	464.8	465.2	465.6
165°	472.2	471.7	471.3	470.8	470.6	470.6	470.7	470.8	470.9	471.3	471.9
167.5°	476.8	476.3	475.8	475.3	475.1	475.2	475.2	475.3	475.4	476.0	476.6
170°	479.3	478.7	478.2	477.6	477.4	477.4	477.5	477.6	477.7	478.3	479.0
172.5°	481.0	480.5	479.9	479.3	479.2	479.3	479.4	479.6	479.7	480.3	480.9
175°	483.0	482.5	482.0	481.6	481.3	481.4	481.5	481.6	481.6	482.3	482.9
177.5°	483.9	483.5	483.2	482.8	482.6	482.7	482.8	482.8	482.9	483.3	483.8
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0	1002.0
2.5°	1045.8	1045.8	1051.4	1051.1	1054.7	1053.4	1054.0
5°	1124.2	1131.2	1137.3	1141.5	1147.6	1149.3	1148.4
7.5°	1205.5	1221.0	1228.6	1239.0	1240.9	1246.3	1245.7
10°	1255.8	1271.1	1282.5	1291.6	1296.2	1301.9	1302.3
12.5°	1295.3	1308.2	1318.4	1326.8	1332.3	1334.1	1335.2
15°	1326.2	1340.5	1352.5	1364.4	1371.4	1376.7	1379.7
17.5°	1357.2	1379.5	1400.5	1416.7	1426.5	1434.6	1434.6
20°	1381.2	1406.8	1433.1	1451.6	1470.5	1478.8	1480.0
22.5°	1406.9	1446.0	1479.9	1508.6	1533.4	1542.0	1545.2
25°	1460.2	1511.2	1563.5	1603.9	1632.6	1649.5	1651.9
27.5°	1524.6	1593.7	1648.7	1685.8	1709.8	1722.3	1725.0
30°	1570.1	1633.9	1683.2	1711.2	1722.3	1723.9	1717.8
32.5°	1590.5	1638.2	1657.9	1656.2	1634.4	1619.9	1614.4
35°	1565.6	1555.7	1507.5	1450.0	1406.0	1378.0	1370.6
37.5°	1424.7	1339.6	1251.0	1164.0	1117.7	1094.2	1053.7
40°	1285.9	1164.5	1072.4	999.2	946.9	904.9	895.1
42.5°	1129.2	1003.9	911.8	849.1	807.4	778.6	766.0
45°	907.4	799.6	723.6	675.4	643.3	622.3	612.9
47.5°	725.8	642.4	586.9	551.3	526.9	508.6	503.5
50°	626.1	559.4	512.5	482.5	464.0	450.0	444.3
52.5°	543.8	490.0	453.9	429.2	411.7	403.0	398.2
55°	448.8	402.3	376.4	356.6	346.7	339.8	336.4
57.5°	367.0	333.4	314.5	300.9	291.8	287.2	285.7
60°	321.2	294.9	277.7	267.0	260.8	255.0	253.4
62.5°	280.7	260.1	246.7	237.3	231.2	228.7	227.8
65°	226.2	212.7	202.8	197.0	192.1	191.3	190.8
67.5°	179.8	171.8	166.7	160.7	158.9	156.1	155.5
70°	153.8	148.5	142.4	140.3	138.2	135.3	135.8
72.5°	130.5	125.2	121.0	118.2	117.5	116.2	117.3
75°	95.5	93.8	92.1	90.1	89.3	89.3	88.9
77.5°	68.1	66.7	64.9	63.7	63.5	61.7	62.3
80°	49.4	47.3	46.5	46.9	45.6	45.2	45.2
82.5°	36.5	35.8	34.9	35.0	34.8	34.4	34.7
85°	20.1	19.7	19.7	19.3	19.3	18.9	18.9
87.5°	8.6	9.0	8.5	8.2	8.2	8.6	9.0
90°	6.9	7.3	7.7	7.9	8.2	8.4	8.6
92.5°	6.9	7.3	7.6	7.7	7.8	7.9	8.0
95°	6.9	7.3	7.5	7.5	7.5	7.5	7.5
97.5°	10.9	8.6	7.5	7.5	7.5	7.5	7.5
100°	26.8	14.9	8.8	8.5	8.2	7.8	7.5
102.5°	72.8	70.6	66.8	61.3	55.9	50.5	45.1
105°	106.8	106.8	106.8	106.7	106.6	106.5	106.5
107.5°	135.2	135.2	135.1	134.9	134.7	134.4	134.2
110°	153.4	153.1	153.0	153.1	153.2	153.3	153.4



TEST NUMBER: P333680-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	171.5	171.3	171.0	171.0	170.8	170.7	170.6
115°	199.0	198.7	198.3	197.8	197.3	196.9	196.4
117.5°	225.5	225.1	224.7	224.5	224.3	224.1	223.9
120°	242.9	242.7	242.4	242.0	241.6	241.2	240.8
122.5°	259.2	259.0	258.7	258.3	257.8	257.4	256.9
125°	282.9	282.6	282.3	282.0	281.8	281.5	281.3
127.5°	304.8	304.7	304.3	303.6	303.1	302.5	301.9
130°	318.9	318.7	318.4	318.0	317.6	317.2	316.8
132.5°	332.4	332.4	332.2	331.8	331.4	331.0	330.6
135°	351.8	351.6	351.3	350.9	350.4	349.9	349.4
137.5°	370.2	370.2	370.0	369.6	369.2	368.8	368.4
140°	381.4	381.6	381.4	381.0	380.5	380.0	379.5
142.5°	392.2	392.3	392.1	391.6	391.1	390.6	390.1
145°	407.7	407.8	407.6	407.1	406.6	406.2	405.7
147.5°	421.0	421.0	420.8	420.3	419.7	419.1	418.5
150°	429.4	429.6	429.4	428.7	428.1	427.5	426.8
152.5°	436.9	437.0	436.9	436.3	435.7	435.1	434.6
155°	447.3	447.5	447.3	446.6	446.0	445.4	444.7
157.5°	455.7	456.0	455.8	455.2	454.6	453.9	453.3
160°	461.1	461.4	461.3	460.7	460.0	459.4	458.8
162.5°	466.1	466.5	466.4	465.7	465.0	464.3	463.6
165°	472.4	472.9	472.8	472.1	471.4	470.8	470.2
167.5°	477.1	477.7	477.7	476.9	476.2	475.5	474.8
170°	479.7	480.3	480.2	479.5	478.8	478.1	477.4
172.5°	481.4	482.0	482.0	481.3	480.5	479.8	479.1
175°	483.5	484.2	484.2	483.5	482.8	482.0	481.3
177.5°	484.2	484.7	484.7	484.1	483.6	483.1	482.6
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5

(END OF REPORT)