

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333682-927

Luminaire Tested: **S125RDIW-S850D470U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333682-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D470U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4059.0 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333682-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333682-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68	63
1	101	97	93	89	95	91	88	85	80	78	75	70	68	67	61	60	58	54
2	92	85	79	74	86	80	74	70	71	66	63	62	59	56	54	52	50	46
3	84	75	67	62	79	71	64	59	62	57	53	55	51	48	48	45	43	39
4	77	66	58	52	72	63	56	50	56	50	46	49	45	41	43	40	37	34
5	71	59	51	45	67	56	49	43	50	44	39	44	40	36	39	35	32	29
6	66	53	45	39	61	51	43	38	45	39	35	40	35	32	35	32	29	26
7	61	48	40	35	57	46	39	33	41	35	31	37	32	28	32	28	25	23
8	57	44	36	31	53	42	35	30	38	32	27	34	29	25	30	26	23	21
9	53	40	33	28	50	38	31	27	35	29	25	31	26	23	28	24	21	19
10	49	37	30	25	46	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7035	7035	7035
5°	7052	6971	7014
10°	6998	6906	6906
15°	6915	6766	6711
20°	6808	6570	6491
25°	6683	6379	6238
30°	6528	6154	5957
35°	6370	5922	5643
40°	6222	5681	5334
45°	6042	5411	4997
50°	5861	5117	4646
55°	5650	4835	4271
60°	5441	4495	3867
65°	5193	4099	3406
70°	4910	3603	2936
75°	4517	3039	2443
80°	3976	2388	2049
85°	3349	1949	1830



TEST NUMBER: P333682-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.4	2.5
10°-20°	286.2	7.1
20°-30°	415.1	10.2
30°-40°	473.1	11.7
40°-50°	461.1	11.4
50°-60°	388.2	9.6
60°-70°	272.1	6.7
70°-80°	139.9	3.4
80°-90°	36.3	0.9
90°-100°	17.6	0.4
100°-110°	108.3	2.7
110°-120°	196.4	4.8
120°-130°	252.0	6.2
130°-140°	271.1	6.7
140°-150°	254.4	6.3
150°-160°	205.8	5.1
160°-170°	133.1	3.3
170°-180°	45.9	1.1
0°-30°	803.8	19.8
0°-40°	1276.8	31.5
0°-60°	2126.1	52.4
0°-90°	2574.4	63.4
90°-120°	322.2	7.9
90°-150°	1099.7	27.1
90°-180°	1485.0	36.6
0°-180°	4059.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1089	1089	1089	1089	1089	
5°	1088	1084	1075	1083	1082	103
15°	1034	1029	1012	1011	1004	291
25°	938	925	895	885	875	431
35°	808	787	751	728	716	506
45°	662	636	592	561	547	510
55°	502	474	429	394	379	449
65°	340	311	268	236	223	336
75°	181	156	122	104	98	192
85°	45	31	26	26	25	51
90°	0	3	6	8	9	3
95°	20	19	6	7	8	26
105°	105	107	107	107	106	112
115°	198	200	200	198	196	196
125°	281	284	284	282	281	251
135°	351	353	352	351	349	270
145°	407	407	408	408	406	254
155°	448	446	447	447	445	206
165°	473	471	471	473	470	133
175°	484	481	482	484	481	46
180°	484	484	484	484	484	



TEST NUMBER: P333682-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1091.2	1090.8	1090.4	1090.0	1089.5	1088.5	1087.1	1085.6	1084.2	1082.7	1084.2
5°	1087.7	1087.0	1086.2	1085.4	1084.7	1083.4	1081.3	1079.3	1077.3	1075.3	1077.1
7.5°	1077.0	1076.3	1075.5	1074.8	1074.2	1072.6	1070.2	1067.8	1065.4	1063.0	1064.2
10°	1067.1	1066.5	1066.0	1065.4	1064.9	1063.3	1060.8	1058.2	1055.7	1053.1	1053.6
12.5°	1055.9	1055.2	1054.5	1053.8	1053.1	1051.1	1047.6	1044.2	1040.8	1037.3	1037.7
15°	1034.2	1033.1	1032.0	1030.9	1029.8	1027.3	1023.5	1019.6	1015.8	1011.9	1011.8
17.5°	1009.6	1008.0	1006.3	1004.6	1002.9	999.7	994.8	990.0	985.2	980.3	979.5
20°	990.5	988.7	986.9	985.1	983.3	979.4	973.6	967.7	961.9	956.0	955.1
22.5°	969.5	967.7	965.8	964.0	962.2	958.2	952.0	945.9	939.8	933.7	931.8
25°	937.9	935.2	932.4	929.7	926.9	922.2	915.4	908.6	901.9	895.2	892.8
27.5°	901.7	898.4	895.1	891.8	888.4	883.1	875.9	868.6	861.4	854.1	850.8
30°	875.4	871.9	868.5	865.0	861.5	855.9	848.3	840.6	832.9	825.2	821.0
32.5°	849.7	845.7	841.6	837.6	833.5	827.5	819.8	811.9	804.1	796.2	791.6
35°	807.9	803.5	799.2	794.7	790.4	784.0	775.9	767.6	759.4	751.1	745.8
37.5°	766.9	761.6	756.3	750.9	745.6	738.7	730.2	721.7	713.2	704.7	698.4
40°	738.0	732.5	727.0	721.5	716.1	708.9	700.1	691.3	682.6	673.8	666.9
42.5°	707.7	702.1	696.5	690.8	685.2	677.9	668.8	659.7	650.6	641.6	634.9
45°	661.5	656.2	650.9	645.5	640.2	632.6	622.5	612.5	602.5	592.4	585.0
47.5°	613.6	608.0	602.4	596.8	591.2	583.4	573.2	563.1	552.9	542.8	535.3
50°	583.3	577.3	571.2	565.2	559.2	551.0	540.5	530.1	519.7	509.3	501.6
52.5°	550.4	544.2	538.1	531.9	525.7	517.7	507.9	498.0	488.1	478.3	470.1
55°	501.8	496.0	490.2	484.3	478.5	470.4	460.2	450.0	439.7	429.4	421.2
57.5°	452.8	446.6	440.3	434.0	427.9	419.8	409.9	400.0	390.1	380.2	372.2
60°	421.2	414.9	408.4	402.0	395.6	387.5	377.6	367.7	357.9	348.0	340.0
62.5°	387.7	381.6	375.5	369.3	363.2	355.2	345.2	335.2	325.1	315.1	307.7
65°	339.8	333.6	327.3	321.2	314.9	307.0	297.3	287.6	277.9	268.2	260.9
67.5°	292.2	286.0	279.8	273.6	267.4	259.6	250.3	241.1	231.8	222.4	215.8
70°	260.0	253.7	247.6	241.3	235.1	227.4	218.3	209.1	200.0	190.8	185.2
72.5°	228.4	222.3	216.3	210.2	204.1	196.8	188.2	179.7	171.1	162.6	157.3
75°	181.0	175.5	170.0	164.5	159.1	152.5	144.8	137.1	129.4	121.8	117.7
77.5°	134.0	129.5	125.2	120.8	116.4	111.1	105.0	98.9	92.7	86.6	83.7
80°	106.9	102.6	98.2	93.8	89.4	84.7	79.5	74.4	69.3	64.2	62.5
82.5°	80.6	76.7	72.7	68.8	64.8	61.1	57.6	54.1	50.5	47.1	46.3
85°	45.2	42.0	38.7	35.4	32.1	29.9	29.1	28.1	27.3	26.3	26.1
87.5°	15.2	14.3	13.4	12.5	11.6	11.2	11.1	11.1	11.1	11.0	11.1
90°	0.4	1.0	1.7	2.3	2.9	3.5	4.0	4.6	5.1	5.7	6.1
92.5°	5.5	5.1	4.6	4.2	3.7	3.7	4.3	4.8	5.2	5.7	6.1
95°	20.4	20.2	20.0	19.7	19.5	17.8	14.8	11.8	8.8	5.7	6.1
97.5°	42.6	43.1	43.5	44.0	44.4	41.6	35.6	29.6	23.6	17.7	15.4
100°	59.8	60.1	60.4	60.6	60.8	61.1	61.4	61.7	62.0	62.3	50.5
102.5°	77.3	77.6	78.0	78.3	78.6	78.8	79.0	79.1	79.4	79.5	77.3
105°	105.4	105.7	106.0	106.3	106.6	106.8	106.8	106.8	106.8	106.8	106.8
107.5°	134.4	134.4	134.4	134.4	134.4	134.5	134.7	134.8	135.0	135.1	135.2
110°	153.4	153.4	153.4	153.4	153.4	153.4	153.6	153.8	153.9	154.1	153.8



TEST NUMBER: P333682-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	171.2	171.3	171.5	171.7	171.9	172.1	172.1	172.3	172.4	172.5	172.1
115°	197.8	198.2	198.6	199.0	199.4	199.6	199.7	199.8	199.9	199.9	199.6
117.5°	225.5	225.4	225.4	225.4	225.4	225.5	225.8	226.1	226.4	226.7	226.3
120°	242.6	242.6	242.5	242.4	242.3	242.4	242.6	242.9	243.1	243.4	243.2
122.5°	257.9	258.1	258.4	258.7	259.0	259.2	259.4	259.4	259.6	259.7	259.5
125°	281.3	281.9	282.4	283.0	283.5	283.8	283.8	283.8	283.8	283.8	283.5
127.5°	303.7	304.2	304.6	305.0	305.4	305.5	305.5	305.5	305.4	305.3	305.1
130°	317.5	317.9	318.3	318.7	319.1	319.3	319.4	319.5	319.6	319.6	319.4
132.5°	331.3	331.8	332.2	332.6	333.1	333.3	333.1	333.0	332.7	332.6	332.6
135°	350.9	351.3	351.8	352.3	352.8	352.9	352.8	352.6	352.4	352.3	352.1
137.5°	368.8	369.2	369.6	370.1	370.5	370.7	370.5	370.3	370.2	370.0	370.1
140°	380.6	380.7	380.9	381.0	381.2	381.3	381.2	381.1	381.0	381.0	381.1
142.5°	391.2	391.3	391.4	391.5	391.6	391.7	391.8	391.9	392.1	392.1	392.1
145°	406.8	406.9	407.1	407.3	407.4	407.5	407.5	407.5	407.5	407.5	407.6
147.5°	420.4	420.3	420.3	420.3	420.3	420.3	420.4	420.5	420.6	420.6	420.7
150°	429.0	428.8	428.6	428.5	428.3	428.3	428.5	428.6	428.8	429.0	429.1
152.5°	437.3	437.0	436.6	436.3	435.9	435.8	435.9	436.1	436.3	436.4	436.6
155°	448.0	447.5	447.0	446.6	446.1	445.9	446.1	446.2	446.4	446.6	446.8
157.5°	456.2	455.9	455.7	455.3	455.0	455.0	455.0	455.0	455.0	455.0	455.3
160°	461.9	461.4	461.0	460.5	460.0	459.9	459.9	460.0	460.1	460.2	460.5
162.5°	466.5	466.0	465.6	465.1	464.6	464.5	464.5	464.6	464.7	464.8	465.2
165°	472.7	472.2	471.7	471.3	470.8	470.6	470.6	470.7	470.8	470.9	471.3
167.5°	477.3	476.8	476.3	475.8	475.3	475.1	475.2	475.2	475.3	475.4	476.0
170°	479.9	479.3	478.7	478.2	477.6	477.4	477.4	477.5	477.6	477.7	478.3
172.5°	481.6	481.0	480.5	479.9	479.3	479.2	479.3	479.4	479.6	479.7	480.3
175°	483.5	483.0	482.5	482.0	481.6	481.3	481.4	481.5	481.6	481.6	482.3
177.5°	484.3	483.9	483.5	483.2	482.8	482.6	482.7	482.8	482.8	482.9	483.3
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5



TEST NUMBER: P333682-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1085.6	1087.1	1088.5	1089.3	1089.1	1088.9	1088.8	1088.6
5°	1079.0	1080.8	1082.6	1083.4	1083.0	1082.6	1082.3	1081.9
7.5°	1065.6	1066.8	1068.1	1068.5	1068.1	1067.7	1067.3	1066.9
10°	1054.2	1054.7	1055.3	1055.3	1054.7	1054.2	1053.6	1053.1
12.5°	1038.1	1038.5	1038.9	1038.7	1037.8	1037.0	1036.2	1035.3
15°	1011.6	1011.4	1011.2	1010.3	1008.7	1007.0	1005.4	1003.7
17.5°	978.5	977.6	976.7	975.6	974.2	972.9	971.5	970.2
20°	954.2	953.2	952.4	951.1	949.4	947.8	946.1	944.5
22.5°	930.0	928.3	926.5	924.9	923.5	922.2	920.8	919.5
25°	890.4	888.0	885.7	883.4	881.4	879.4	877.4	875.4
27.5°	847.5	844.1	840.8	838.2	836.3	834.3	832.4	830.4
30°	816.8	812.6	808.3	805.5	803.8	802.2	800.5	798.8
32.5°	787.0	782.3	777.7	774.3	772.2	770.2	768.0	766.0
35°	740.5	735.2	729.9	726.0	723.4	720.9	718.4	715.7
37.5°	692.1	685.6	679.3	674.9	672.4	669.9	667.4	665.0
40°	659.9	653.0	646.0	641.4	639.3	637.1	634.9	632.7
42.5°	628.3	621.6	615.0	610.0	606.8	603.6	600.3	597.1
45°	577.7	570.5	563.1	558.1	555.3	552.6	549.9	547.1
47.5°	527.8	520.2	512.7	507.4	504.4	501.4	498.3	495.3
50°	493.9	486.2	478.6	473.3	470.6	467.9	465.1	462.4
52.5°	461.8	453.5	445.3	439.7	437.0	434.3	431.6	428.8
55°	413.0	404.8	396.6	390.9	388.1	385.2	382.2	379.3
57.5°	364.2	356.2	348.1	342.8	340.2	337.5	335.0	332.4
60°	331.9	323.8	315.8	310.5	307.7	305.0	302.2	299.4
62.5°	300.2	292.7	285.3	280.2	277.4	274.6	272.0	269.2
65°	253.6	246.3	238.9	233.9	231.2	228.5	225.7	222.9
67.5°	209.1	202.4	195.7	191.2	189.1	186.9	184.7	182.5
70°	179.5	173.9	168.2	164.3	162.1	159.9	157.7	155.5
72.5°	152.1	146.9	141.6	138.3	136.8	135.4	134.0	132.5
75°	113.8	109.7	105.7	103.1	101.7	100.4	99.2	97.9
77.5°	80.9	78.1	75.3	73.4	72.5	71.5	70.6	69.6
80°	60.9	59.3	57.6	56.6	56.2	55.8	55.5	55.1
82.5°	45.6	44.8	44.0	43.5	43.3	43.1	42.9	42.6
85°	26.0	25.7	25.6	25.4	25.2	25.0	24.9	24.7
87.5°	11.2	11.2	11.3	11.3	11.2	11.2	11.0	10.9
90°	6.5	6.9	7.3	7.7	7.9	8.2	8.4	8.6
92.5°	6.5	6.9	7.3	7.6	7.7	7.8	7.9	8.0
95°	6.5	6.9	7.3	7.5	7.5	7.5	7.5	7.5
97.5°	13.2	10.9	8.6	7.5	7.5	7.5	7.5	7.5
100°	38.7	26.8	14.9	8.8	8.5	8.2	7.8	7.5
102.5°	75.1	72.8	70.6	66.8	61.3	55.9	50.5	45.1
105°	106.8	106.8	106.8	106.8	106.7	106.6	106.5	106.5
107.5°	135.2	135.2	135.2	135.1	134.9	134.7	134.4	134.2
110°	153.6	153.4	153.1	153.0	153.1	153.2	153.3	153.4



TEST NUMBER: P333682-927

CATALOG NUMBER: S125RDIW-S850D470U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	171.8	171.5	171.3	171.0	171.0	170.8	170.7	170.6
115°	199.3	199.0	198.7	198.3	197.8	197.3	196.9	196.4
117.5°	225.9	225.5	225.1	224.7	224.5	224.3	224.1	223.9
120°	243.0	242.9	242.7	242.4	242.0	241.6	241.2	240.8
122.5°	259.4	259.2	259.0	258.7	258.3	257.8	257.4	256.9
125°	283.2	282.9	282.6	282.3	282.0	281.8	281.5	281.3
127.5°	305.0	304.8	304.7	304.3	303.6	303.1	302.5	301.9
130°	319.2	318.9	318.7	318.4	318.0	317.6	317.2	316.8
132.5°	332.5	332.4	332.4	332.2	331.8	331.4	331.0	330.6
135°	352.0	351.8	351.6	351.3	350.9	350.4	349.9	349.4
137.5°	370.1	370.2	370.2	370.0	369.6	369.2	368.8	368.4
140°	381.3	381.4	381.6	381.4	381.0	380.5	380.0	379.5
142.5°	392.2	392.2	392.3	392.1	391.6	391.1	390.6	390.1
145°	407.7	407.7	407.8	407.6	407.1	406.6	406.2	405.7
147.5°	420.9	421.0	421.0	420.8	420.3	419.7	419.1	418.5
150°	429.3	429.4	429.6	429.4	428.7	428.1	427.5	426.8
152.5°	436.7	436.9	437.0	436.9	436.3	435.7	435.1	434.6
155°	447.0	447.3	447.5	447.3	446.6	446.0	445.4	444.7
157.5°	455.5	455.7	456.0	455.8	455.2	454.6	453.9	453.3
160°	460.8	461.1	461.4	461.3	460.7	460.0	459.4	458.8
162.5°	465.6	466.1	466.5	466.4	465.7	465.0	464.3	463.6
165°	471.9	472.4	472.9	472.8	472.1	471.4	470.8	470.2
167.5°	476.6	477.1	477.7	477.7	476.9	476.2	475.5	474.8
170°	479.0	479.7	480.3	480.2	479.5	478.8	478.1	477.4
172.5°	480.9	481.4	482.0	482.0	481.3	480.5	479.8	479.1
175°	482.9	483.5	484.2	484.2	483.5	482.8	482.0	481.3
177.5°	483.8	484.2	484.7	484.7	484.1	483.6	483.1	482.6
180°	483.5	483.5	483.5	483.5	483.5	483.5	483.5	483.5

(END OF REPORT)