

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333687-927

Luminaire Tested: **S125RDIW-S850D770U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333687-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S850D770U927-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4683.7 lumens  
Efficiency: N/A  
Efficacy: 104.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333687-927

CATALOG NUMBER: S125RDIW-S850D770U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333687-927

CATALOG NUMBER: S125RDIW-S850D770U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	91	88	92	88	85	82	76	73	71	65	63	61	54	53	52	47
2	90	83	77	72	84	77	72	68	67	63	59	57	54	51	48	46	44	40
3	83	73	66	60	77	68	62	57	59	54	50	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	48	53	47	43	45	41	38	38	35	33	29
5	70	58	50	44	64	54	47	42	47	42	37	41	36	33	34	31	29	25
6	64	52	44	38	59	49	42	36	43	37	33	37	32	29	31	28	25	22
7	59	47	39	34	55	44	37	32	39	33	29	34	29	26	29	25	22	20
8	55	43	35	30	51	40	33	28	35	30	26	31	26	23	26	23	20	18
9	51	39	32	27	48	37	30	25	32	27	23	28	24	21	24	21	18	16
10	48	36	29	24	45	34	27	23	30	25	21	26	22	19	23	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	7035	7035	7035
5°	7052	6971	7014
10°	6998	6906	6906
15°	6915	6766	6711
20°	6808	6570	6491
25°	6683	6379	6238
30°	6528	6154	5957
35°	6370	5922	5643
40°	6222	5681	5334
45°	6042	5411	4997
50°	5861	5117	4646
55°	5650	4835	4271
60°	5441	4495	3867
65°	5193	4099	3406
70°	4910	3603	2936
75°	4517	3039	2443
80°	3976	2388	2049
85°	3349	1949	1830



TEST NUMBER: P333687-927

CATALOG NUMBER: S125RDIW-S850D770U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.4	2.2
10°-20°	286.2	6.1
20°-30°	415.1	8.9
30°-40°	473.1	10.1
40°-50°	461.1	9.8
50°-60°	388.2	8.3
60°-70°	272.1	5.8
70°-80°	139.9	3.0
80°-90°	37.0	0.8
90°-100°	50.6	1.1
100°-110°	149.5	3.2
110°-120°	253.2	5.4
120°-130°	333.2	7.1
130°-140°	373.3	8.0
140°-150°	365.9	7.8
150°-160°	307.3	6.6
160°-170°	204.3	4.4
170°-180°	71.5	1.5
0°-30°	803.8	17.2
0°-40°	1276.8	27.3
0°-60°	2126.1	45.4
0°-90°	2575.1	55.0
90°-120°	453.2	9.7
90°-150°	1525.6	32.6
90°-180°	2109.0	45.0
0°-180°	4683.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1089	1089	1089	1089	1089	
5°	1088	1084	1075	1083	1082	103
15°	1034	1029	1012	1011	1004	291
25°	938	925	895	885	875	431
35°	808	787	751	728	716	506
45°	662	636	592	561	547	510
55°	502	474	429	394	379	449
65°	340	311	268	236	223	336
75°	181	156	122	104	98	192
85°	45	31	26	26	25	51
90°	1	5	9	12	14	4
95°	38	40	45	49	50	41
105°	134	137	140	144	146	143
115°	254	256	257	256	256	251
125°	370	373	374	373	372	331
135°	481	484	485	485	483	371
145°	583	585	587	587	585	364
155°	667	667	668	670	667	307
165°	725	724	724	726	723	204
175°	754	752	752	755	751	72
180°	756	756	756	756	756	



TEST NUMBER: P333687-927

CATALOG NUMBER: S125RDIW-S850D770U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1091.2	1090.8	1090.4	1090.0	1089.5	1088.5	1087.1	1085.6	1084.2	1082.7	1084.2
5°	1087.7	1087.0	1086.2	1085.4	1084.7	1083.4	1081.3	1079.3	1077.3	1075.3	1077.1
7.5°	1077.0	1076.3	1075.5	1074.8	1074.2	1072.6	1070.2	1067.8	1065.4	1063.0	1064.2
10°	1067.1	1066.5	1066.0	1065.4	1064.9	1063.3	1060.8	1058.2	1055.7	1053.1	1053.6
12.5°	1055.9	1055.2	1054.5	1053.8	1053.1	1051.1	1047.6	1044.2	1040.8	1037.3	1037.7
15°	1034.2	1033.1	1032.0	1030.9	1029.8	1027.3	1023.5	1019.6	1015.8	1011.9	1011.8
17.5°	1009.6	1008.0	1006.3	1004.6	1002.9	999.7	994.8	990.0	985.2	980.3	979.5
20°	990.5	988.7	986.9	985.1	983.3	979.4	973.6	967.7	961.9	956.0	955.1
22.5°	969.5	967.7	965.8	964.0	962.2	958.2	952.0	945.9	939.8	933.7	931.8
25°	937.9	935.2	932.4	929.7	926.9	922.2	915.4	908.6	901.9	895.2	892.8
27.5°	901.7	898.4	895.1	891.8	888.4	883.1	875.9	868.6	861.4	854.1	850.8
30°	875.4	871.9	868.5	865.0	861.5	855.9	848.3	840.6	832.9	825.2	821.0
32.5°	849.7	845.7	841.6	837.6	833.5	827.5	819.8	811.9	804.1	796.2	791.6
35°	807.9	803.5	799.2	794.7	790.4	784.0	775.9	767.6	759.4	751.1	745.8
37.5°	766.9	761.6	756.3	750.9	745.6	738.7	730.2	721.7	713.2	704.7	698.4
40°	738.0	732.5	727.0	721.5	716.1	708.9	700.1	691.3	682.6	673.8	666.9
42.5°	707.7	702.1	696.5	690.8	685.2	677.9	668.8	659.7	650.6	641.6	634.9
45°	661.5	656.2	650.9	645.5	640.2	632.6	622.5	612.5	602.5	592.4	585.0
47.5°	613.6	608.0	602.4	596.8	591.2	583.4	573.2	563.1	552.9	542.8	535.3
50°	583.3	577.3	571.2	565.2	559.2	551.0	540.5	530.1	519.7	509.3	501.6
52.5°	550.4	544.2	538.1	531.9	525.7	517.7	507.9	498.0	488.1	478.3	470.1
55°	501.8	496.0	490.2	484.3	478.5	470.4	460.2	450.0	439.7	429.4	421.2
57.5°	452.8	446.6	440.3	434.0	427.9	419.8	409.9	400.0	390.1	380.2	372.2
60°	421.2	414.9	408.4	402.0	395.6	387.5	377.6	367.7	357.9	348.0	340.0
62.5°	387.7	381.6	375.5	369.3	363.2	355.2	345.2	335.2	325.1	315.1	307.7
65°	339.8	333.6	327.3	321.2	314.9	307.0	297.3	287.6	277.9	268.2	260.9
67.5°	292.2	286.0	279.8	273.6	267.4	259.6	250.3	241.1	231.8	222.4	215.8
70°	260.0	253.7	247.6	241.3	235.1	227.4	218.3	209.1	200.0	190.8	185.2
72.5°	228.4	222.3	216.3	210.2	204.1	196.8	188.2	179.7	171.1	162.6	157.3
75°	181.0	175.5	170.0	164.5	159.1	152.5	144.8	137.1	129.4	121.8	117.7
77.5°	134.0	129.5	125.2	120.8	116.4	111.1	105.0	98.9	92.7	86.6	83.7
80°	106.9	102.6	98.2	93.8	89.4	84.7	79.5	74.4	69.3	64.2	62.5
82.5°	80.6	76.7	72.7	68.8	64.8	61.1	57.6	54.1	50.5	47.1	46.3
85°	45.2	42.0	38.7	35.4	32.1	29.9	29.1	28.1	27.3	26.3	26.1
87.5°	15.3	14.4	13.6	12.8	12.0	11.6	11.6	11.6	11.7	11.7	11.9
90°	0.6	1.7	2.7	3.7	4.8	5.8	6.7	7.6	8.5	9.4	10.1
92.5°	14.3	15.0	15.7	16.4	17.2	18.1	19.3	20.4	21.5	22.6	23.4
95°	38.3	38.5	38.7	39.0	39.3	40.1	41.4	42.7	44.0	45.3	46.2
97.5°	63.5	63.6	63.7	63.8	63.9	64.9	66.7	68.5	70.3	72.1	73.0
100°	82.3	82.3	82.3	82.3	82.3	83.2	84.8	86.6	88.2	90.0	91.2
102.5°	102.6	103.1	103.6	104.1	104.6	105.4	106.2	107.1	107.9	108.8	110.1
105°	134.1	134.8	135.4	136.0	136.7	137.4	138.2	138.9	139.7	140.5	141.3
107.5°	168.9	169.5	170.2	170.9	171.5	172.1	172.8	173.3	174.0	174.5	174.9
110°	192.9	193.5	194.2	194.9	195.5	196.0	196.4	196.8	197.2	197.6	198.0



TEST NUMBER: P333687-927

CATALOG NUMBER: S125RDIW-S850D770U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.4	217.7	218.0	218.4	218.7	219.1	219.6	220.1	220.6	221.1	221.3
115°	253.5	254.0	254.5	255.0	255.6	256.0	256.2	256.4	256.7	257.0	256.8
117.5°	289.7	289.9	290.2	290.4	290.7	290.9	291.1	291.4	291.6	291.8	291.9
120°	312.3	312.9	313.5	314.3	314.9	315.3	315.4	315.5	315.7	315.8	315.8
122.5°	336.8	337.0	337.2	337.5	337.7	337.9	338.3	338.7	339.0	339.3	339.2
125°	369.9	370.7	371.5	372.2	373.0	373.5	373.6	373.8	373.9	374.0	373.8
127.5°	405.2	405.6	406.1	406.5	406.9	407.3	407.4	407.6	407.7	407.9	407.7
130°	426.4	427.0	427.7	428.3	429.0	429.4	429.7	429.9	430.2	430.5	430.3
132.5°	447.5	448.6	449.6	450.8	451.8	452.3	452.3	452.2	452.2	452.1	452.0
135°	481.0	481.8	482.6	483.4	484.2	484.7	484.7	484.9	485.1	485.1	485.1
137.5°	512.5	513.3	514.0	514.8	515.6	516.1	516.4	516.7	517.0	517.3	517.5
140°	532.8	533.5	534.1	534.7	535.4	535.9	536.3	536.7	537.1	537.5	537.7
142.5°	553.0	553.6	554.1	554.7	555.2	555.7	556.3	556.7	557.2	557.7	557.9
145°	582.8	583.3	583.8	584.3	584.9	585.3	585.7	586.1	586.5	586.9	586.9
147.5°	610.3	610.6	610.9	611.2	611.5	611.7	612.0	612.4	612.7	613.0	613.3
150°	628.7	628.5	628.4	628.3	628.1	628.4	628.8	629.4	629.9	630.4	630.4
152.5°	643.7	643.9	644.0	644.3	644.4	644.6	644.8	645.1	645.2	645.5	645.8
155°	666.9	666.9	666.9	666.9	666.9	666.9	667.1	667.2	667.3	667.5	668.0
157.5°	687.6	687.3	687.0	686.7	686.4	686.3	686.5	686.6	686.7	686.9	687.4
160°	699.8	699.4	699.0	698.6	698.2	698.1	698.2	698.4	698.5	698.6	699.2
162.5°	710.7	710.3	710.0	709.8	709.5	709.3	709.4	709.4	709.4	709.5	710.1
165°	725.1	724.8	724.6	724.3	724.1	724.0	724.1	724.2	724.4	724.5	725.0
167.5°	737.4	736.8	736.3	735.8	735.2	735.0	735.0	735.0	735.0	735.0	735.8
170°	743.9	743.4	742.8	742.4	741.8	741.6	741.6	741.6	741.6	741.6	742.4
172.5°	748.6	748.1	747.6	747.0	746.6	746.2	746.2	746.2	746.2	746.2	747.0
175°	753.9	753.4	752.9	752.3	751.8	751.5	751.5	751.5	751.5	751.5	752.3
177.5°	756.6	756.2	755.7	755.3	754.9	754.7	754.6	754.5	754.4	754.2	754.9
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7



TEST NUMBER: P333687-927

CATALOG NUMBER: S125RDIW-S850D770U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3	1089.3
2.5°	1085.6	1087.1	1088.5	1089.3	1089.1	1088.9	1088.8	1088.6
5°	1079.0	1080.8	1082.6	1083.4	1083.0	1082.6	1082.3	1081.9
7.5°	1065.6	1066.8	1068.1	1068.5	1068.1	1067.7	1067.3	1066.9
10°	1054.2	1054.7	1055.3	1055.3	1054.7	1054.2	1053.6	1053.1
12.5°	1038.1	1038.5	1038.9	1038.7	1037.8	1037.0	1036.2	1035.3
15°	1011.6	1011.4	1011.2	1010.3	1008.7	1007.0	1005.4	1003.7
17.5°	978.5	977.6	976.7	975.6	974.2	972.9	971.5	970.2
20°	954.2	953.2	952.4	951.1	949.4	947.8	946.1	944.5
22.5°	930.0	928.3	926.5	924.9	923.5	922.2	920.8	919.5
25°	890.4	888.0	885.7	883.4	881.4	879.4	877.4	875.4
27.5°	847.5	844.1	840.8	838.2	836.3	834.3	832.4	830.4
30°	816.8	812.6	808.3	805.5	803.8	802.2	800.5	798.8
32.5°	787.0	782.3	777.7	774.3	772.2	770.2	768.0	766.0
35°	740.5	735.2	729.9	726.0	723.4	720.9	718.4	715.7
37.5°	692.1	685.6	679.3	674.9	672.4	669.9	667.4	665.0
40°	659.9	653.0	646.0	641.4	639.3	637.1	634.9	632.7
42.5°	628.3	621.6	615.0	610.0	606.8	603.6	600.3	597.1
45°	577.7	570.5	563.1	558.1	555.3	552.6	549.9	547.1
47.5°	527.8	520.2	512.7	507.4	504.4	501.4	498.3	495.3
50°	493.9	486.2	478.6	473.3	470.6	467.9	465.1	462.4
52.5°	461.8	453.5	445.3	439.7	437.0	434.3	431.6	428.8
55°	413.0	404.8	396.6	390.9	388.1	385.2	382.2	379.3
57.5°	364.2	356.2	348.1	342.8	340.2	337.5	335.0	332.4
60°	331.9	323.8	315.8	310.5	307.7	305.0	302.2	299.4
62.5°	300.2	292.7	285.3	280.2	277.4	274.6	272.0	269.2
65°	253.6	246.3	238.9	233.9	231.2	228.5	225.7	222.9
67.5°	209.1	202.4	195.7	191.2	189.1	186.9	184.7	182.5
70°	179.5	173.9	168.2	164.3	162.1	159.9	157.7	155.5
72.5°	152.1	146.9	141.6	138.3	136.8	135.4	134.0	132.5
75°	113.8	109.7	105.7	103.1	101.7	100.4	99.2	97.9
77.5°	80.9	78.1	75.3	73.4	72.5	71.5	70.6	69.6
80°	60.9	59.3	57.6	56.6	56.2	55.8	55.5	55.1
82.5°	45.6	44.8	44.0	43.5	43.3	43.1	42.9	42.6
85°	26.0	25.7	25.6	25.4	25.2	25.0	24.9	24.7
87.5°	12.0	12.1	12.3	12.3	12.3	12.2	12.1	12.0
90°	10.7	11.4	12.0	12.5	12.9	13.3	13.7	14.1
92.5°	24.3	25.2	26.1	26.6	26.9	27.2	27.5	27.7
95°	47.1	48.0	49.0	49.5	49.8	50.1	50.3	50.5
97.5°	73.8	74.7	75.6	76.0	76.2	76.4	76.5	76.7
100°	92.3	93.5	94.7	95.4	95.7	95.9	96.2	96.4
102.5°	111.4	112.6	113.9	114.7	115.1	115.5	115.8	116.2
105°	142.1	142.9	143.7	144.3	144.7	145.0	145.4	145.8
107.5°	175.3	175.7	176.1	176.3	176.3	176.3	176.2	176.2
110°	198.4	198.8	199.2	199.3	199.2	199.0	198.9	198.8





TEST NUMBER: P333687-927

CATALOG NUMBER: S125RDIW-S850D770U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	221.5	221.7	221.8	221.8	221.6	221.3	221.1	220.9
115°	256.7	256.6	256.4	256.4	256.2	256.1	256.0	255.8
117.5°	292.0	292.1	292.2	292.0	291.5	291.0	290.4	289.9
120°	315.8	315.8	315.8	315.5	315.1	314.5	313.9	313.5
122.5°	339.1	339.0	338.9	338.7	338.2	337.8	337.4	337.0
125°	373.5	373.2	373.0	372.8	372.6	372.5	372.4	372.2
127.5°	407.7	407.5	407.3	407.2	406.9	406.6	406.4	406.2
130°	430.2	430.1	429.9	429.8	429.5	429.2	429.0	428.7
132.5°	451.9	451.7	451.6	451.3	451.0	450.6	450.3	449.9
135°	485.1	485.1	485.1	484.9	484.3	483.9	483.3	482.8
137.5°	517.6	517.8	517.9	517.6	517.0	516.3	515.7	515.0
140°	538.1	538.3	538.5	538.4	537.7	537.0	536.4	535.8
142.5°	558.0	558.2	558.3	558.1	557.5	556.8	556.1	555.5
145°	586.9	586.9	586.9	586.7	586.3	585.9	585.5	585.1
147.5°	613.6	613.9	614.3	613.9	613.1	612.2	611.3	610.5
150°	630.4	630.4	630.4	630.3	630.0	629.8	629.5	629.2
152.5°	646.1	646.4	646.7	646.7	646.2	645.7	645.2	644.8
155°	668.5	669.0	669.6	669.5	668.8	668.2	667.5	666.9
157.5°	687.9	688.4	689.0	688.8	687.9	687.1	686.2	685.3
160°	699.7	700.2	700.7	700.7	700.0	699.3	698.7	698.1
162.5°	710.7	711.3	711.9	711.9	711.1	710.3	709.6	708.8
165°	725.6	726.1	726.6	726.4	725.7	724.9	724.1	723.3
167.5°	736.6	737.4	738.1	738.1	737.3	736.5	735.7	734.8
170°	743.1	743.9	744.7	744.7	743.7	742.8	741.9	741.0
172.5°	747.8	748.6	749.4	749.4	748.6	747.7	746.9	746.2
175°	753.1	753.9	754.7	754.6	753.7	752.8	751.9	751.0
177.5°	755.5	756.1	756.8	756.7	756.0	755.3	754.6	753.8
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7

(END OF REPORT)