

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333642

Luminaire Tested: **S125RDIW-S375D470U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333642
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D470U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3320.9 lumens
Efficiency: N/A
Efficacy: 144.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333642

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333642

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	18	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3952	3952	3952
5°	3961	3916	3940
10°	3931	3880	3880
15°	3884	3801	3770
20°	3824	3691	3647
25°	3755	3583	3504
30°	3667	3457	3347
35°	3578	3327	3170
40°	3495	3191	2996
45°	3394	3040	2807
50°	3293	2875	2609
55°	3174	2716	2399
60°	3056	2525	2173
65°	2917	2303	1913
70°	2757	2024	1648
75°	2538	1707	1372
80°	2235	1339	1153
85°	1882	1097	1030



TEST NUMBER: P333642

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.5	1.7
10°-20°	160.8	4.8
20°-30°	233.2	7.0
30°-40°	265.7	8.0
40°-50°	259.0	7.8
50°-60°	218.0	6.6
60°-70°	152.8	4.6
70°-80°	78.6	2.4
80°-90°	21.1	0.6
90°-100°	22.2	0.7
100°-110°	136.7	4.1
110°-120°	247.9	7.5
120°-130°	318.1	9.6
130°-140°	342.2	10.3
140°-150°	321.2	9.7
150°-160°	259.8	7.8
160°-170°	168.0	5.1
170°-180°	58.0	1.7
0°-30°	451.5	13.6
0°-40°	717.3	21.6
0°-60°	1194.3	36.0
0°-90°	1446.9	43.6
90°-120°	406.7	12.2
90°-150°	1388.2	41.8
90°-180°	1874.0	56.4
0°-180°	3320.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	612	612	612	612	612	
5°	611	609	604	608	608	58
15°	581	578	568	568	564	164
25°	527	519	503	497	492	242
35°	454	442	422	409	402	284
45°	372	358	333	315	307	287
55°	282	267	241	221	213	252
65°	191	175	151	133	125	189
75°	102	88	68	59	55	108
85°	25	17	15	14	14	29
90°	0	4	7	9	11	2
95°	26	24	7	9	10	33
105°	133	135	135	135	134	141
115°	250	252	252	251	248	247
125°	355	358	358	356	355	317
135°	443	445	445	444	441	341
145°	514	514	514	515	512	321
155°	566	563	564	565	561	260
165°	597	594	594	597	594	168
175°	610	608	608	611	608	58
180°	610	610	610	610	610	



TEST NUMBER: P333642

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9
2.5°	613.0	612.8	612.5	612.3	612.0	611.5	610.7	609.8	609.0	608.2	609.0
5°	611.0	610.6	610.2	609.7	609.3	608.6	607.4	606.3	605.2	604.0	605.1
7.5°	605.0	604.6	604.2	603.8	603.4	602.5	601.2	599.8	598.5	597.1	597.8
10°	599.4	599.1	598.8	598.5	598.2	597.3	595.9	594.4	593.0	591.6	591.9
12.5°	593.1	592.7	592.4	592.0	591.6	590.4	588.5	586.6	584.6	582.7	582.9
15°	580.9	580.3	579.7	579.1	578.5	577.1	574.9	572.8	570.6	568.5	568.4
17.5°	567.2	566.2	565.3	564.3	563.4	561.6	558.8	556.1	553.4	550.7	550.2
20°	556.4	555.4	554.4	553.4	552.3	550.2	546.9	543.6	540.3	537.0	536.5
22.5°	544.6	543.6	542.6	541.5	540.5	538.3	534.8	531.4	527.9	524.5	523.5
25°	526.9	525.3	523.8	522.2	520.7	518.0	514.2	510.4	506.6	502.8	501.5
27.5°	506.5	504.7	502.8	500.9	499.0	496.1	492.0	487.9	483.9	479.8	477.9
30°	491.7	489.8	487.8	485.9	483.9	480.8	476.5	472.2	467.9	463.5	461.2
32.5°	477.3	475.0	472.8	470.5	468.2	464.9	460.5	456.1	451.7	447.3	444.7
35°	453.8	451.4	448.9	446.4	444.0	440.4	435.8	431.2	426.6	422.0	419.0
37.5°	430.8	427.8	424.8	421.8	418.8	414.9	410.2	405.4	400.7	395.9	392.3
40°	414.6	411.5	408.4	405.3	402.2	398.2	393.3	388.4	383.4	378.5	374.6
42.5°	397.5	394.4	391.2	388.1	384.9	380.8	375.7	370.6	365.5	360.4	356.7
45°	371.6	368.6	365.6	362.6	359.7	355.3	349.7	344.1	338.4	332.8	328.6
47.5°	344.7	341.5	338.4	335.2	332.1	327.7	322.0	316.3	310.6	304.9	300.7
50°	327.7	324.3	320.9	317.5	314.1	309.5	303.6	297.8	291.9	286.1	281.8
52.5°	309.2	305.7	302.2	298.8	295.3	290.8	285.3	279.7	274.2	268.7	264.1
55°	281.9	278.6	275.3	272.1	268.8	264.3	258.5	252.7	247.0	241.2	236.6
57.5°	254.4	250.9	247.3	243.8	240.3	235.8	230.2	224.7	219.2	213.6	209.1
60°	236.6	233.0	229.4	225.8	222.2	217.7	212.1	206.6	201.0	195.5	191.0
62.5°	217.8	214.3	210.9	207.5	204.0	199.5	193.9	188.3	182.6	177.0	172.8
65°	190.9	187.4	183.9	180.4	176.9	172.4	167.0	161.6	156.1	150.7	146.6
67.5°	164.2	160.7	157.2	153.7	150.2	145.8	140.6	135.4	130.2	125.0	121.2
70°	146.0	142.6	139.1	135.6	132.1	127.8	122.6	117.5	112.4	107.2	104.0
72.5°	128.3	124.9	121.5	118.1	114.7	110.5	105.7	100.9	96.1	91.3	88.4
75°	101.7	98.6	95.5	92.4	89.4	85.7	81.3	77.0	72.7	68.4	66.1
77.5°	75.2	72.8	70.3	67.8	65.4	62.4	59.0	55.5	52.1	48.6	47.0
80°	60.1	57.6	55.2	52.7	50.2	47.6	44.7	41.8	38.9	36.0	35.1
82.5°	45.3	43.1	40.9	38.6	36.4	34.3	32.4	30.4	28.4	26.4	26.0
85°	25.4	23.6	21.7	19.9	18.0	16.8	16.3	15.8	15.3	14.8	14.7
87.5°	8.6	8.2	7.8	7.4	6.9	6.8	6.8	6.9	6.9	7.0	7.1
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.1	5.8	6.5	7.2	7.7
92.5°	7.0	6.4	5.8	5.3	4.7	4.7	5.4	6.0	6.6	7.2	7.7
95°	25.8	25.5	25.2	24.9	24.6	22.5	18.7	14.9	11.1	7.2	7.7
97.5°	53.8	54.4	54.9	55.5	56.0	52.5	44.9	37.4	29.8	22.3	19.4
100°	75.5	75.9	76.2	76.5	76.8	77.1	77.5	77.9	78.3	78.7	63.7
102.5°	97.6	98.0	98.4	98.8	99.2	99.5	99.7	99.9	100.2	100.4	97.6
105°	133.0	133.4	133.8	134.2	134.6	134.8	134.8	134.8	134.8	134.8	134.8
107.5°	169.7	169.7	169.7	169.7	169.7	169.8	170.0	170.2	170.4	170.6	170.7
110°	193.6	193.6	193.6	193.6	193.6	193.7	193.9	194.1	194.3	194.5	194.2



TEST NUMBER: P333642

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	216.1	216.3	216.5	216.8	217.0	217.2	217.3	217.5	217.6	217.7	217.3
115°	249.7	250.2	250.7	251.2	251.7	252.0	252.1	252.2	252.3	252.4	252.0
117.5°	284.6	284.5	284.5	284.5	284.5	284.7	285.0	285.4	285.8	286.2	285.7
120°	306.3	306.2	306.1	306.0	305.9	306.0	306.3	306.6	306.9	307.2	307.0
122.5°	325.5	325.8	326.2	326.6	327.0	327.2	327.4	327.5	327.7	327.8	327.6
125°	355.1	355.8	356.5	357.2	357.9	358.3	358.3	358.3	358.3	358.3	357.9
127.5°	383.4	384.0	384.5	385.0	385.5	385.7	385.6	385.6	385.5	385.4	385.2
130°	400.8	401.3	401.8	402.3	402.8	403.1	403.2	403.3	403.4	403.5	403.2
132.5°	418.2	418.8	419.4	419.9	420.5	420.7	420.5	420.3	420.0	419.8	419.8
135°	442.9	443.5	444.1	444.7	445.3	445.5	445.3	445.1	444.9	444.7	444.5
137.5°	465.6	466.1	466.6	467.2	467.7	467.9	467.7	467.5	467.3	467.1	467.2
140°	480.4	480.6	480.8	481.0	481.2	481.3	481.2	481.1	481.0	480.9	481.1
142.5°	493.8	494.0	494.1	494.2	494.3	494.4	494.6	494.7	494.9	495.0	495.0
145°	513.5	513.7	513.9	514.1	514.3	514.4	514.4	514.4	514.4	514.4	514.5
147.5°	530.7	530.6	530.6	530.5	530.5	530.5	530.7	530.8	530.9	531.0	531.1
150°	541.5	541.3	541.1	540.9	540.7	540.7	540.9	541.1	541.3	541.5	541.7
152.5°	552.0	551.6	551.1	550.7	550.2	550.1	550.3	550.5	550.7	550.9	551.1
155°	565.5	564.9	564.3	563.7	563.1	562.9	563.1	563.3	563.5	563.7	564.0
157.5°	575.9	575.5	575.2	574.8	574.4	574.3	574.3	574.3	574.3	574.4	574.7
160°	583.1	582.5	581.9	581.3	580.7	580.5	580.6	580.7	580.8	580.9	581.3
162.5°	588.9	588.3	587.7	587.1	586.5	586.3	586.4	586.5	586.6	586.7	587.2
165°	596.7	596.1	595.5	594.9	594.3	594.0	594.1	594.2	594.3	594.4	595.0
167.5°	602.5	601.9	601.3	600.6	600.0	599.7	599.8	599.9	600.0	600.1	600.9
170°	605.8	605.1	604.3	603.6	602.9	602.6	602.7	602.8	602.9	603.0	603.8
172.5°	607.9	607.2	606.5	605.8	605.1	604.9	605.0	605.2	605.4	605.6	606.3
175°	610.3	609.7	609.1	608.5	607.9	607.6	607.7	607.8	607.9	608.0	608.8
177.5°	611.4	610.9	610.4	609.9	609.4	609.2	609.3	609.4	609.5	609.6	610.1
180°	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3



TEST NUMBER: P333642

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	611.9	611.9	611.9	611.9	611.9	611.9	611.9	611.9
2.5°	609.8	610.7	611.5	611.9	611.8	611.7	611.6	611.5
5°	606.1	607.1	608.1	608.6	608.4	608.1	607.9	607.7
7.5°	598.5	599.3	600.0	600.2	600.0	599.8	599.6	599.3
10°	592.2	592.5	592.8	592.8	592.5	592.2	591.9	591.6
12.5°	583.1	583.4	583.6	583.5	583.0	582.5	582.1	581.6
15°	568.2	568.1	568.0	567.5	566.6	565.7	564.8	563.8
17.5°	549.7	549.2	548.7	548.0	547.3	546.5	545.7	545.0
20°	536.0	535.5	535.0	534.3	533.3	532.4	531.5	530.6
22.5°	522.4	521.4	520.4	519.5	518.8	518.0	517.3	516.5
25°	500.2	498.8	497.5	496.3	495.1	494.0	492.9	491.7
27.5°	476.1	474.2	472.3	470.9	469.8	468.7	467.6	466.5
30°	458.8	456.5	454.1	452.5	451.5	450.6	449.7	448.8
32.5°	442.1	439.5	436.8	435.0	433.8	432.6	431.4	430.3
35°	416.0	413.0	410.0	407.8	406.4	405.0	403.5	402.1
37.5°	388.7	385.2	381.6	379.1	377.7	376.3	374.9	373.5
40°	370.7	366.8	362.9	360.3	359.1	357.9	356.6	355.4
42.5°	352.9	349.2	345.4	342.7	340.9	339.0	337.2	335.4
45°	324.5	320.4	316.3	313.5	312.0	310.4	308.9	307.3
47.5°	296.5	292.2	288.0	285.0	283.3	281.6	279.9	278.2
50°	277.4	273.1	268.8	265.9	264.4	262.8	261.3	259.7
52.5°	259.4	254.8	250.1	247.0	245.5	244.0	242.4	240.9
55°	232.0	227.4	222.8	219.6	218.0	216.3	214.7	213.1
57.5°	204.6	200.1	195.5	192.5	191.1	189.6	188.2	186.7
60°	186.5	181.9	177.4	174.4	172.8	171.3	169.8	168.2
62.5°	168.6	164.4	160.2	157.4	155.8	154.3	152.8	151.2
65°	142.4	138.3	134.2	131.4	129.9	128.3	126.8	125.2
67.5°	117.4	113.7	109.9	107.4	106.2	105.0	103.7	102.5
70°	100.9	97.7	94.5	92.3	91.0	89.8	88.6	87.3
72.5°	85.4	82.5	79.6	77.7	76.9	76.1	75.2	74.4
75°	63.9	61.6	59.4	57.9	57.2	56.4	55.7	55.0
77.5°	45.5	43.9	42.3	41.2	40.7	40.2	39.6	39.1
80°	34.2	33.3	32.4	31.8	31.6	31.4	31.2	31.0
82.5°	25.6	25.1	24.7	24.4	24.3	24.2	24.1	23.9
85°	14.6	14.5	14.4	14.3	14.2	14.1	14.0	13.9
87.5°	7.2	7.3	7.4	7.4	7.4	7.4	7.4	7.3
90°	8.2	8.7	9.2	9.7	10.0	10.3	10.6	10.9
92.5°	8.2	8.7	9.2	9.6	9.7	9.9	10.0	10.1
95°	8.2	8.7	9.2	9.5	9.5	9.5	9.5	9.5
97.5°	16.6	13.8	10.9	9.5	9.5	9.5	9.5	9.5
100°	48.8	33.8	18.8	11.1	10.7	10.3	9.9	9.5
102.5°	94.8	91.9	89.1	84.3	77.4	70.6	63.7	56.9
105°	134.8	134.8	134.8	134.8	134.7	134.6	134.5	134.4
107.5°	170.7	170.7	170.7	170.6	170.3	170.0	169.7	169.4
110°	193.9	193.6	193.3	193.2	193.3	193.4	193.5	193.6



TEST NUMBER: P333642

CATALOG NUMBER: S125RDIW-S375D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	216.9	216.5	216.2	215.9	215.8	215.6	215.5	215.3
115°	251.6	251.2	250.8	250.3	249.7	249.1	248.5	247.9
117.5°	285.1	284.6	284.1	283.7	283.4	283.2	282.9	282.7
120°	306.8	306.6	306.4	306.0	305.5	305.0	304.5	304.0
122.5°	327.4	327.2	327.0	326.6	326.0	325.4	324.9	324.3
125°	357.5	357.1	356.7	356.3	356.0	355.7	355.4	355.1
127.5°	385.0	384.8	384.6	384.1	383.3	382.6	381.8	381.1
130°	402.9	402.6	402.3	401.9	401.4	400.9	400.4	399.9
132.5°	419.7	419.6	419.6	419.3	418.8	418.3	417.8	417.3
135°	444.3	444.1	443.9	443.5	442.9	442.3	441.7	441.1
137.5°	467.2	467.3	467.3	467.1	466.5	466.0	465.5	465.0
140°	481.3	481.5	481.7	481.5	480.9	480.3	479.7	479.1
142.5°	495.1	495.1	495.2	494.9	494.3	493.7	493.1	492.5
145°	514.6	514.7	514.8	514.5	513.9	513.3	512.7	512.1
147.5°	531.3	531.4	531.5	531.2	530.5	529.8	529.0	528.3
150°	541.9	542.1	542.3	542.0	541.2	540.4	539.6	538.8
152.5°	551.3	551.5	551.7	551.5	550.7	550.0	549.3	548.6
155°	564.3	564.6	564.9	564.6	563.8	563.0	562.2	561.4
157.5°	575.0	575.3	575.6	575.4	574.6	573.8	573.0	572.2
160°	581.7	582.1	582.5	582.3	581.5	580.7	579.9	579.1
162.5°	587.8	588.4	588.9	588.8	587.9	587.0	586.1	585.2
165°	595.7	596.3	596.9	596.8	596.0	595.1	594.3	593.5
167.5°	601.6	602.3	603.0	603.0	602.0	601.1	600.2	599.3
170°	604.6	605.5	606.3	606.2	605.3	604.4	603.5	602.6
172.5°	607.0	607.7	608.5	608.4	607.5	606.6	605.7	604.8
175°	609.6	610.4	611.2	611.2	610.3	609.4	608.5	607.6
177.5°	610.7	611.2	611.8	611.8	611.1	610.5	609.8	609.2
180°	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3

(END OF REPORT)