

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333446-830

Luminaire Tested: **S125DIW-S1090D1050U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333446-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1050U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8136.7 lumens
Efficiency: N/A
Efficacy: 133.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333446-830

CATALOG NUMBER: S125DIW-S1090D1050U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333446-830

CATALOG NUMBER: S125DIW-S1090D1050U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	50	48	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26
5	68	57	48	42	63	53	45	40	45	40	35	38	34	31	32	29	26	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16
9	50	38	30	25	46	36	29	24	31	25	22	26	22	19	22	19	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10388	10388	10388
5°	10410	10311	10377
10°	10347	10238	10297
15°	10235	10116	10158
20°	10074	9943	9961
25°	9902	9738	9729
30°	9688	9517	9470
35°	9460	9280	9150
40°	9226	9022	8893
45°	8972	8786	8611
50°	8694	8501	8246
55°	8425	8180	7952
60°	8103	7856	7576
65°	7719	7467	7213
70°	7353	7017	6775
75°	6697	6478	6253
80°	5962	5869	5724
85°	5180	5283	4994



TEST NUMBER: P333446-830

CATALOG NUMBER: S125DIW-S1090D1050U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.6	1.9
10°-20°	428.4	5.3
20°-30°	632.5	7.8
30°-40°	738.0	9.1
40°-50°	741.2	9.1
50°-60°	650.7	8.0
60°-70°	484.8	6.0
70°-80°	277.2	3.4
80°-90°	83.3	1.0
90°-100°	46.7	0.6
100°-110°	288.0	3.5
110°-120°	522.3	6.4
120°-130°	670.4	8.2
130°-140°	721.0	8.9
140°-150°	676.8	8.3
150°-160°	547.5	6.7
160°-170°	354.1	4.4
170°-180°	122.1	1.5
0°-30°	1212.5	14.9
0°-40°	1950.5	24.0
0°-60°	3342.4	41.1
0°-90°	4187.8	51.5
90°-120°	857.1	10.5
90°-150°	2925.3	36.0
90°-180°	3949.0	48.5
0°-180°	8136.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1608	1608	1608	1608	1608	
5°	1606	1603	1590	1601	1601	152
15°	1531	1526	1513	1519	1519	431
25°	1390	1383	1367	1369	1365	639
35°	1200	1194	1177	1170	1160	750
45°	982	977	962	947	943	757
55°	748	744	726	715	706	668
65°	505	502	489	477	472	501
75°	268	266	260	256	251	286
85°	70	71	71	70	67	78
90°	1	8	15	20	23	6
95°	54	50	15	20	20	69
105°	280	284	284	284	283	297
115°	526	531	532	528	522	521
125°	748	755	755	751	748	668
135°	933	939	937	935	929	719
145°	1082	1084	1084	1084	1079	676
155°	1192	1186	1188	1190	1183	549
165°	1257	1252	1252	1258	1251	355
175°	1286	1281	1281	1288	1280	122
180°	1286	1286	1286	1286	1286	



TEST NUMBER: P333446-830

CATALOG NUMBER: S125DIW-S1090D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1612.4	1611.7	1611.0	1610.3	1609.7	1608.2	1605.9	1603.6	1601.4	1599.1	1601.4
5°	1605.8	1605.2	1604.7	1604.1	1603.5	1601.9	1599.0	1596.2	1593.4	1590.5	1593.1
7.5°	1591.0	1590.4	1589.9	1589.3	1588.7	1586.9	1583.8	1580.6	1577.5	1574.4	1577.0
10°	1577.8	1577.3	1576.7	1576.1	1575.6	1573.7	1570.6	1567.4	1564.3	1561.2	1563.5
12.5°	1561.5	1560.5	1559.4	1558.4	1557.5	1555.5	1552.6	1549.7	1546.8	1543.9	1545.8
15°	1530.7	1529.8	1529.0	1528.1	1527.3	1525.3	1522.2	1519.1	1516.0	1512.9	1514.3
17.5°	1495.3	1494.1	1492.8	1491.6	1490.3	1488.1	1484.9	1481.7	1478.5	1475.2	1477.0
20°	1465.8	1465.3	1464.7	1464.1	1463.6	1461.4	1457.7	1454.1	1450.4	1446.7	1448.7
22.5°	1436.2	1435.3	1434.3	1433.2	1432.2	1429.9	1426.5	1423.1	1419.7	1416.2	1417.5
25°	1389.5	1388.1	1386.7	1385.3	1383.8	1381.3	1377.6	1373.9	1370.3	1366.6	1367.2
27.5°	1334.7	1333.9	1333.0	1332.2	1331.3	1329.1	1325.2	1321.4	1317.7	1313.9	1314.0
30°	1299.1	1298.3	1297.4	1296.6	1295.7	1293.2	1288.9	1284.7	1280.4	1276.2	1275.6
32.5°	1260.5	1259.1	1257.8	1256.5	1255.3	1252.7	1248.9	1245.1	1241.3	1237.6	1236.5
35°	1199.9	1198.7	1197.6	1196.5	1195.3	1192.8	1188.8	1184.9	1180.9	1177.0	1175.5
37.5°	1137.0	1135.6	1134.2	1132.7	1131.3	1128.8	1125.0	1121.3	1117.6	1113.9	1111.7
40°	1094.3	1092.9	1091.5	1090.1	1088.6	1085.9	1081.9	1078.0	1074.0	1070.1	1067.5
42.5°	1048.5	1047.3	1046.1	1044.9	1043.7	1041.1	1037.2	1033.2	1029.3	1025.3	1022.9
45°	982.3	981.2	980.1	978.9	977.8	975.5	972.1	968.7	965.4	962.0	958.6
47.5°	911.1	911.1	911.2	911.3	911.3	909.3	905.2	901.1	897.0	893.0	889.5
50°	865.3	864.4	863.6	862.7	861.9	859.7	856.3	852.9	849.5	846.1	842.4
52.5°	818.4	817.7	817.2	816.5	816.0	813.8	810.2	806.5	803.0	799.3	796.1
55°	748.2	747.3	746.5	745.6	744.8	742.3	738.4	734.4	730.5	726.5	724.0
57.5°	674.1	673.6	673.3	672.8	672.3	670.4	667.0	663.7	660.4	657.0	653.7
60°	627.3	626.1	625.0	623.9	622.7	620.7	617.6	614.4	611.3	608.2	605.4
62.5°	578.4	577.5	576.6	575.7	574.9	573.1	570.3	567.7	565.1	562.4	559.3
65°	505.1	504.5	504.0	503.4	502.8	501.1	497.9	494.8	491.7	488.6	486.1
67.5°	434.1	432.9	431.8	430.6	429.4	427.6	425.3	423.0	420.7	418.4	416.2
70°	389.4	388.0	386.5	385.1	383.7	381.7	379.2	376.6	374.1	371.6	369.9
72.5°	340.5	339.5	338.6	337.6	336.7	335.4	333.8	332.1	330.5	328.8	326.9
75°	268.4	267.9	267.3	266.7	266.2	265.2	263.8	262.4	261.0	259.6	258.7
77.5°	202.1	201.8	201.6	201.4	201.1	200.7	199.8	199.1	198.3	197.5	197.0
80°	160.3	160.3	160.3	160.3	160.3	160.0	159.5	158.9	158.3	157.8	157.5
82.5°	123.7	123.2	122.8	122.3	121.9	121.6	121.5	121.4	121.2	121.1	120.6
85°	69.9	70.2	70.5	70.8	71.1	71.3	71.3	71.3	71.3	71.3	71.0
87.5°	27.7	28.0	28.4	28.7	29.0	29.2	29.3	29.4	29.4	29.5	29.7
90°	0.9	2.6	4.3	6.0	7.7	9.3	10.8	12.3	13.8	15.3	16.3
92.5°	14.7	13.5	12.3	11.1	9.9	10.0	11.3	12.6	13.9	15.3	16.3
95°	54.3	53.7	53.1	52.4	51.8	47.4	39.4	31.4	23.3	15.3	16.3
97.5°	113.5	114.6	115.7	116.9	118.0	110.7	94.7	78.8	62.9	46.9	40.9
100°	159.2	159.9	160.4	161.1	161.7	162.5	163.3	164.2	165.0	165.9	134.3
102.5°	205.8	206.5	207.4	208.1	209.0	209.6	210.1	210.6	211.1	211.6	205.7
105°	280.2	281.1	281.9	282.8	283.6	284.1	284.1	284.1	284.1	284.1	284.1
107.5°	357.7	357.7	357.7	357.7	357.7	357.9	358.3	358.7	359.1	359.6	359.6
110°	408.0	408.0	408.0	408.0	408.0	408.2	408.6	409.1	409.4	409.9	409.3



TEST NUMBER: P333446-830

CATALOG NUMBER: S125DIW-S1090D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	455.2	455.8	456.3	456.8	457.3	457.7	458.0	458.2	458.5	458.7	457.9
115°	526.2	527.3	528.3	529.3	530.5	531.0	531.3	531.5	531.7	531.9	531.0
117.5°	599.6	599.6	599.6	599.5	599.5	599.8	600.6	601.4	602.2	603.0	601.9
120°	645.4	645.2	644.9	644.7	644.5	644.7	645.4	646.0	646.6	647.2	646.9
122.5°	685.8	686.5	687.4	688.2	689.0	689.6	689.8	690.1	690.4	690.7	690.3
125°	748.3	749.8	751.3	752.7	754.2	755.0	755.0	755.0	755.0	755.0	754.1
127.5°	807.9	809.1	810.1	811.2	812.2	812.7	812.6	812.5	812.3	812.2	811.7
130°	844.6	845.6	846.7	847.7	848.9	849.4	849.7	849.9	850.1	850.3	849.7
132.5°	881.2	882.4	883.6	884.9	886.1	886.5	886.0	885.5	885.0	884.7	884.5
135°	933.2	934.5	935.8	937.1	938.3	938.8	938.3	937.9	937.5	937.1	936.6
137.5°	981.1	982.2	983.3	984.4	985.5	985.9	985.5	985.1	984.7	984.3	984.4
140°	1012.4	1012.8	1013.2	1013.6	1014.1	1014.2	1014.0	1013.7	1013.5	1013.3	1013.7
142.5°	1040.6	1040.8	1041.1	1041.3	1041.6	1041.9	1042.2	1042.5	1042.7	1043.0	1043.1
145°	1081.9	1082.4	1082.8	1083.3	1083.6	1083.8	1083.8	1083.8	1083.8	1083.8	1084.1
147.5°	1118.1	1118.1	1118.0	1117.9	1117.9	1117.9	1118.1	1118.4	1118.7	1118.9	1119.2
150°	1141.0	1140.7	1140.2	1139.8	1139.3	1139.3	1139.8	1140.2	1140.7	1141.0	1141.5
152.5°	1163.2	1162.2	1161.3	1160.4	1159.4	1159.2	1159.6	1160.1	1160.5	1160.8	1161.3
155°	1191.6	1190.3	1189.0	1187.8	1186.5	1186.1	1186.5	1186.9	1187.3	1187.8	1188.4
157.5°	1213.5	1212.8	1212.0	1211.3	1210.4	1210.1	1210.1	1210.1	1210.2	1210.2	1211.0
160°	1228.8	1227.5	1226.2	1224.9	1223.7	1223.1	1223.3	1223.6	1223.8	1224.0	1224.8
162.5°	1241.0	1239.7	1238.4	1237.2	1235.9	1235.3	1235.6	1235.8	1236.0	1236.1	1237.4
165°	1257.4	1256.1	1254.8	1253.6	1252.3	1251.7	1252.0	1252.2	1252.4	1252.5	1253.9
167.5°	1269.5	1268.3	1267.0	1265.6	1264.3	1263.8	1263.9	1264.1	1264.4	1264.6	1266.1
170°	1276.4	1275.0	1273.5	1272.0	1270.5	1269.9	1270.1	1270.3	1270.5	1270.7	1272.4
172.5°	1281.0	1279.5	1278.0	1276.6	1275.1	1274.5	1274.9	1275.3	1275.6	1276.0	1277.5
175°	1285.9	1284.7	1283.4	1282.1	1280.8	1280.3	1280.5	1280.7	1281.0	1281.2	1282.9
177.5°	1288.3	1287.2	1286.2	1285.2	1284.2	1283.7	1283.9	1284.1	1284.2	1284.4	1285.6
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9



TEST NUMBER: P333446-830

CATALOG NUMBER: S125DIW-S1090D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1603.6	1605.9	1608.2	1609.2	1609.0	1608.7	1608.5	1608.4
5°	1595.6	1598.2	1600.7	1601.9	1601.6	1601.3	1601.0	1600.7
7.5°	1579.4	1582.0	1584.4	1585.5	1585.3	1585.0	1584.7	1584.4
10°	1565.8	1568.0	1570.3	1571.3	1571.0	1570.7	1570.5	1570.2
12.5°	1547.6	1549.4	1551.1	1552.1	1552.0	1551.9	1551.9	1551.8
15°	1515.7	1517.1	1518.5	1519.3	1519.3	1519.3	1519.3	1519.3
17.5°	1478.8	1480.5	1482.2	1482.4	1481.0	1479.6	1478.2	1476.8
20°	1450.7	1452.6	1454.6	1454.9	1453.5	1452.1	1450.7	1449.3
22.5°	1418.8	1420.1	1421.4	1421.5	1420.6	1419.7	1418.7	1417.7
25°	1367.7	1368.3	1368.9	1368.7	1367.8	1367.0	1366.1	1365.3
27.5°	1314.1	1314.2	1314.4	1314.0	1313.2	1312.3	1311.5	1310.6
30°	1275.1	1274.5	1273.9	1273.3	1272.4	1271.6	1270.7	1269.9
32.5°	1235.5	1234.4	1233.5	1232.2	1230.7	1229.2	1227.6	1226.1
35°	1174.1	1172.7	1171.3	1169.5	1167.2	1165.0	1162.7	1160.5
37.5°	1109.7	1107.6	1105.5	1103.8	1102.5	1101.2	1099.9	1098.6
40°	1065.0	1062.4	1059.9	1058.2	1057.3	1056.5	1055.6	1054.8
42.5°	1020.7	1018.3	1016.1	1014.2	1013.0	1011.6	1010.3	1009.0
45°	955.2	951.8	948.4	946.2	945.4	944.5	943.7	942.8
47.5°	886.1	882.6	879.2	876.5	874.5	872.5	870.5	868.6
50°	838.8	835.1	831.4	828.6	826.6	824.6	822.7	820.7
52.5°	792.9	789.7	786.5	783.7	781.5	779.3	777.1	774.9
55°	721.4	718.9	716.3	714.1	712.1	710.1	708.1	706.2
57.5°	650.5	647.2	643.9	641.8	640.7	639.6	638.6	637.4
60°	602.6	599.7	596.9	594.5	592.5	590.5	588.5	586.5
62.5°	556.3	553.3	550.2	547.9	546.4	544.9	543.3	541.8
65°	483.5	481.0	478.4	476.5	475.4	474.3	473.2	472.0
67.5°	414.1	411.9	409.7	408.3	407.6	407.0	406.3	405.7
70°	368.2	366.5	364.8	363.4	362.2	361.1	360.0	358.8
72.5°	325.0	323.0	321.1	319.6	318.5	317.4	316.2	315.1
75°	257.9	257.0	256.2	255.1	254.0	252.9	251.8	250.6
77.5°	196.4	196.0	195.5	194.8	194.0	193.2	192.4	191.6
80°	157.2	156.9	156.7	156.2	155.6	155.0	154.5	153.9
82.5°	120.1	119.6	119.1	118.8	118.7	118.6	118.5	118.3
85°	70.7	70.4	70.1	69.7	69.1	68.5	68.0	67.4
87.5°	30.0	30.2	30.3	30.3	30.0	29.7	29.3	29.0
90°	17.3	18.5	19.5	20.4	21.0	21.6	22.2	22.9
92.5°	17.3	18.5	19.5	20.2	20.5	20.7	21.0	21.4
95°	17.3	18.5	19.5	20.0	20.0	20.0	20.0	20.0
97.5°	35.0	28.9	23.0	20.0	20.0	20.0	20.0	20.0
100°	102.7	71.2	39.6	23.4	22.5	21.7	20.8	20.0
102.5°	199.6	193.7	187.8	177.6	163.2	148.7	134.3	119.9
105°	284.1	284.1	284.1	284.0	283.8	283.5	283.3	283.1
107.5°	359.7	359.7	359.8	359.5	358.8	358.2	357.5	356.9
110°	408.6	408.0	407.4	407.2	407.4	407.6	407.7	408.0



TEST NUMBER: P333446-830

CATALOG NUMBER: S125DIW-S1090D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	457.1	456.3	455.5	455.0	454.7	454.3	454.0	453.7
115°	530.2	529.3	528.5	527.4	526.2	524.9	523.7	522.4
117.5°	600.9	599.7	598.6	597.8	597.3	596.7	596.2	595.6
120°	646.4	646.0	645.5	644.8	643.8	642.7	641.7	640.6
122.5°	689.8	689.5	689.0	688.2	687.0	685.8	684.6	683.3
125°	753.3	752.4	751.6	750.8	750.3	749.6	748.9	748.3
127.5°	811.2	810.8	810.3	809.3	807.8	806.2	804.6	803.0
130°	849.0	848.4	847.7	846.9	845.8	844.8	843.8	842.7
132.5°	884.4	884.2	884.1	883.5	882.5	881.4	880.3	879.3
135°	936.2	935.8	935.4	934.5	933.2	932.0	930.7	929.4
137.5°	984.5	984.6	984.7	984.2	983.1	981.9	980.9	979.8
140°	1014.2	1014.6	1015.0	1014.6	1013.3	1012.0	1010.8	1009.5
142.5°	1043.2	1043.3	1043.4	1042.8	1041.5	1040.3	1039.0	1037.7
145°	1084.3	1084.5	1084.7	1084.2	1082.9	1081.7	1080.3	1079.1
147.5°	1119.5	1119.7	1119.9	1119.4	1117.8	1116.3	1114.7	1113.2
150°	1141.9	1142.4	1142.7	1142.1	1140.4	1138.7	1137.0	1135.3
152.5°	1161.7	1162.2	1162.5	1162.1	1160.5	1159.0	1157.4	1155.9
155°	1189.0	1189.7	1190.3	1189.8	1188.1	1186.4	1184.7	1183.0
157.5°	1211.6	1212.3	1213.0	1212.5	1210.8	1209.1	1207.4	1205.7
160°	1225.7	1226.5	1227.4	1226.9	1225.3	1223.6	1221.9	1220.2
162.5°	1238.6	1239.7	1241.0	1240.6	1238.7	1236.9	1235.0	1233.1
165°	1255.1	1256.4	1257.6	1257.4	1255.7	1254.1	1252.4	1250.7
167.5°	1267.6	1269.1	1270.7	1270.5	1268.6	1266.7	1264.8	1262.9
170°	1274.1	1275.8	1277.5	1277.3	1275.4	1273.6	1271.7	1269.7
172.5°	1279.1	1280.6	1282.1	1282.0	1280.1	1278.1	1276.2	1274.3
175°	1284.6	1286.3	1288.0	1287.9	1285.9	1284.0	1282.1	1280.3
177.5°	1286.8	1288.0	1289.2	1289.1	1287.7	1286.4	1285.1	1283.6
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9

(END OF REPORT)