

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333458-830

Luminaire Tested: **S125DIW-S1090D1560U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333458-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1560U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10066.8 lumens
Efficiency: N/A
Efficacy: 131.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333458-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333458-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	41	36	56	45	38	33	38	33	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15	13
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10388	10388	10388
5°	10410	10311	10377
10°	10347	10238	10297
15°	10235	10116	10158
20°	10074	9943	9961
25°	9902	9738	9729
30°	9688	9517	9470
35°	9460	9280	9150
40°	9226	9022	8893
45°	8972	8786	8611
50°	8694	8501	8246
55°	8425	8180	7952
60°	8103	7856	7576
65°	7719	7467	7213
70°	7353	7017	6775
75°	6697	6478	6253
80°	5962	5869	5724
85°	5180	5283	4994



TEST NUMBER: P333458-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.6	1.5
10°-20°	428.4	4.3
20°-30°	632.5	6.3
30°-40°	738.0	7.3
40°-50°	741.2	7.4
50°-60°	650.7	6.5
60°-70°	484.8	4.8
70°-80°	277.2	2.8
80°-90°	84.6	0.8
90°-100°	69.6	0.7
100°-110°	428.7	4.3
110°-120°	777.5	7.7
120°-130°	997.8	9.9
130°-140°	1073.2	10.7
140°-150°	1007.4	10.0
150°-160°	814.9	8.1
160°-170°	527.0	5.2
170°-180°	181.8	1.8
0°-30°	1212.5	12.0
0°-40°	1950.5	19.4
0°-60°	3342.4	33.2
0°-90°	4189.1	41.6
90°-120°	1275.7	12.7
90°-150°	4354.1	43.3
90°-180°	5878.0	58.4
0°-180°	10066.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1608	1608	1608	1608	1608	
5°	1606	1603	1590	1601	1601	152
15°	1531	1526	1513	1519	1519	431
25°	1390	1383	1367	1369	1365	639
35°	1200	1194	1177	1170	1160	750
45°	982	977	962	947	943	757
55°	748	744	726	715	706	668
65°	505	502	489	477	472	501
75°	268	266	260	256	251	286
85°	70	71	71	70	67	78
90°	1	13	23	30	34	7
95°	81	74	23	29	30	103
105°	417	422	423	423	421	442
115°	783	790	792	786	778	776
125°	1114	1123	1124	1118	1114	994
135°	1389	1397	1395	1392	1383	1070
145°	1610	1613	1613	1614	1606	1007
155°	1774	1766	1768	1771	1761	817
165°	1872	1864	1864	1872	1862	528
175°	1914	1906	1907	1917	1906	182
180°	1914	1914	1914	1914	1914	



TEST NUMBER: P333458-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1612.4	1611.7	1611.0	1610.3	1609.7	1608.2	1605.9	1603.6	1601.4	1599.1	1601.4
5°	1605.8	1605.2	1604.7	1604.1	1603.5	1601.9	1599.0	1596.2	1593.4	1590.5	1593.1
7.5°	1591.0	1590.4	1589.9	1589.3	1588.7	1586.9	1583.8	1580.6	1577.5	1574.4	1577.0
10°	1577.8	1577.3	1576.7	1576.1	1575.6	1573.7	1570.6	1567.4	1564.3	1561.2	1563.5
12.5°	1561.5	1560.5	1559.4	1558.4	1557.5	1555.5	1552.6	1549.7	1546.8	1543.9	1545.8
15°	1530.7	1529.8	1529.0	1528.1	1527.3	1525.3	1522.2	1519.1	1516.0	1512.9	1514.3
17.5°	1495.3	1494.1	1492.8	1491.6	1490.3	1488.1	1484.9	1481.7	1478.5	1475.2	1477.0
20°	1465.8	1465.3	1464.7	1464.1	1463.6	1461.4	1457.7	1454.1	1450.4	1446.7	1448.7
22.5°	1436.2	1435.3	1434.3	1433.2	1432.2	1429.9	1426.5	1423.1	1419.7	1416.2	1417.5
25°	1389.5	1388.1	1386.7	1385.3	1383.8	1381.3	1377.6	1373.9	1370.3	1366.6	1367.2
27.5°	1334.7	1333.9	1333.0	1332.2	1331.3	1329.1	1325.2	1321.4	1317.7	1313.9	1314.0
30°	1299.1	1298.3	1297.4	1296.6	1295.7	1293.2	1288.9	1284.7	1280.4	1276.2	1275.6
32.5°	1260.5	1259.1	1257.8	1256.5	1255.3	1252.7	1248.9	1245.1	1241.3	1237.6	1236.5
35°	1199.9	1198.7	1197.6	1196.5	1195.3	1192.8	1188.8	1184.9	1180.9	1177.0	1175.5
37.5°	1137.0	1135.6	1134.2	1132.7	1131.3	1128.8	1125.0	1121.3	1117.6	1113.9	1111.7
40°	1094.3	1092.9	1091.5	1090.1	1088.6	1085.9	1081.9	1078.0	1074.0	1070.1	1067.5
42.5°	1048.5	1047.3	1046.1	1044.9	1043.7	1041.1	1037.2	1033.2	1029.3	1025.3	1022.9
45°	982.3	981.2	980.1	978.9	977.8	975.5	972.1	968.7	965.4	962.0	958.6
47.5°	911.1	911.1	911.2	911.3	911.3	909.3	905.2	901.1	897.0	893.0	889.5
50°	865.3	864.4	863.6	862.7	861.9	859.7	856.3	852.9	849.5	846.1	842.4
52.5°	818.4	817.7	817.2	816.5	816.0	813.8	810.2	806.5	803.0	799.3	796.1
55°	748.2	747.3	746.5	745.6	744.8	742.3	738.4	734.4	730.5	726.5	724.0
57.5°	674.1	673.6	673.3	672.8	672.3	670.4	667.0	663.7	660.4	657.0	653.7
60°	627.3	626.1	625.0	623.9	622.7	620.7	617.6	614.4	611.3	608.2	605.4
62.5°	578.4	577.5	576.6	575.7	574.9	573.1	570.3	567.7	565.1	562.4	559.3
65°	505.1	504.5	504.0	503.4	502.8	501.1	497.9	494.8	491.7	488.6	486.1
67.5°	434.1	432.9	431.8	430.6	429.4	427.6	425.3	423.0	420.7	418.4	416.2
70°	389.4	388.0	386.5	385.1	383.7	381.7	379.2	376.6	374.1	371.6	369.9
72.5°	340.5	339.5	338.6	337.6	336.7	335.4	333.8	332.1	330.5	328.8	326.9
75°	268.4	267.9	267.3	266.7	266.2	265.2	263.8	262.4	261.0	259.6	258.7
77.5°	202.1	201.8	201.6	201.4	201.1	200.7	199.8	199.1	198.3	197.5	197.0
80°	160.3	160.3	160.3	160.3	160.3	160.0	159.5	158.9	158.3	157.8	157.5
82.5°	123.7	123.2	122.8	122.3	121.9	121.6	121.5	121.4	121.2	121.1	120.6
85°	69.9	70.2	70.5	70.8	71.1	71.3	71.3	71.3	71.3	71.3	71.0
87.5°	27.8	28.3	28.7	29.3	29.8	30.2	30.3	30.5	30.8	31.0	31.3
90°	1.4	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3
92.5°	21.9	20.1	18.3	16.6	14.8	14.9	16.9	18.8	20.7	22.7	24.3
95°	80.9	79.9	79.0	78.0	77.1	70.6	58.6	46.7	34.7	22.7	24.3
97.5°	168.8	170.5	172.2	174.0	175.7	164.7	140.9	117.3	93.5	69.8	60.9
100°	237.0	237.9	238.8	239.8	240.7	241.9	243.1	244.4	245.6	246.9	199.9
102.5°	306.2	307.4	308.6	309.8	310.9	312.0	312.7	313.5	314.2	315.0	306.1
105°	417.2	418.4	419.7	420.9	422.2	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	532.3	532.3	532.3	532.3	532.3	532.6	533.3	534.0	534.6	535.2	535.3
110°	607.3	607.3	607.3	607.3	607.3	607.6	608.2	608.9	609.4	610.1	609.2



TEST NUMBER: P333458-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	677.7	678.4	679.2	680.0	680.7	681.3	681.6	682.0	682.4	682.8	681.6
115°	783.3	784.8	786.4	788.0	789.5	790.4	790.8	791.1	791.5	791.7	790.4
117.5°	892.5	892.4	892.3	892.3	892.2	892.8	894.0	895.1	896.4	897.6	895.9
120°	960.5	960.3	960.0	959.6	959.3	959.6	960.5	961.5	962.4	963.4	962.8
122.5°	1020.8	1021.9	1023.1	1024.4	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5
125°	1113.8	1116.0	1118.2	1120.4	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5
127.5°	1202.6	1204.2	1205.8	1207.4	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2
130°	1257.1	1258.7	1260.3	1261.9	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7
132.5°	1311.5	1313.4	1315.2	1317.1	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5
135°	1389.0	1390.9	1392.9	1394.8	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1
137.5°	1460.3	1461.9	1463.6	1465.2	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3
140°	1506.8	1507.5	1508.1	1508.7	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9
142.5°	1548.8	1549.2	1549.5	1549.9	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7
145°	1610.4	1611.0	1611.7	1612.3	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5
147.5°	1664.3	1664.2	1664.1	1664.0	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8
150°	1698.4	1697.7	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0
152.5°	1731.3	1729.9	1728.5	1727.1	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5
155°	1773.6	1771.7	1769.8	1767.9	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9
157.5°	1806.2	1805.1	1803.9	1802.8	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4
160°	1828.9	1827.0	1825.1	1823.3	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1
162.5°	1847.1	1845.2	1843.3	1841.4	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7
165°	1871.5	1869.6	1867.6	1865.8	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2
167.5°	1889.6	1887.7	1885.7	1883.8	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5
170°	1899.9	1897.6	1895.5	1893.2	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9
172.5°	1906.7	1904.5	1902.2	1900.1	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6
175°	1914.0	1912.1	1910.3	1908.4	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5
177.5°	1917.4	1915.9	1914.4	1912.9	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333458-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1603.6	1605.9	1608.2	1609.2	1609.0	1608.7	1608.5	1608.4
5°	1595.6	1598.2	1600.7	1601.9	1601.6	1601.3	1601.0	1600.7
7.5°	1579.4	1582.0	1584.4	1585.5	1585.3	1585.0	1584.7	1584.4
10°	1565.8	1568.0	1570.3	1571.3	1571.0	1570.7	1570.5	1570.2
12.5°	1547.6	1549.4	1551.1	1552.1	1552.0	1551.9	1551.9	1551.8
15°	1515.7	1517.1	1518.5	1519.3	1519.3	1519.3	1519.3	1519.3
17.5°	1478.8	1480.5	1482.2	1482.4	1481.0	1479.6	1478.2	1476.8
20°	1450.7	1452.6	1454.6	1454.9	1453.5	1452.1	1450.7	1449.3
22.5°	1418.8	1420.1	1421.4	1421.5	1420.6	1419.7	1418.7	1417.7
25°	1367.7	1368.3	1368.9	1368.7	1367.8	1367.0	1366.1	1365.3
27.5°	1314.1	1314.2	1314.4	1314.0	1313.2	1312.3	1311.5	1310.6
30°	1275.1	1274.5	1273.9	1273.3	1272.4	1271.6	1270.7	1269.9
32.5°	1235.5	1234.4	1233.5	1232.2	1230.7	1229.2	1227.6	1226.1
35°	1174.1	1172.7	1171.3	1169.5	1167.2	1165.0	1162.7	1160.5
37.5°	1109.7	1107.6	1105.5	1103.8	1102.5	1101.2	1099.9	1098.6
40°	1065.0	1062.4	1059.9	1058.2	1057.3	1056.5	1055.6	1054.8
42.5°	1020.7	1018.3	1016.1	1014.2	1013.0	1011.6	1010.3	1009.0
45°	955.2	951.8	948.4	946.2	945.4	944.5	943.7	942.8
47.5°	886.1	882.6	879.2	876.5	874.5	872.5	870.5	868.6
50°	838.8	835.1	831.4	828.6	826.6	824.6	822.7	820.7
52.5°	792.9	789.7	786.5	783.7	781.5	779.3	777.1	774.9
55°	721.4	718.9	716.3	714.1	712.1	710.1	708.1	706.2
57.5°	650.5	647.2	643.9	641.8	640.7	639.6	638.6	637.4
60°	602.6	599.7	596.9	594.5	592.5	590.5	588.5	586.5
62.5°	556.3	553.3	550.2	547.9	546.4	544.9	543.3	541.8
65°	483.5	481.0	478.4	476.5	475.4	474.3	473.2	472.0
67.5°	414.1	411.9	409.7	408.3	407.6	407.0	406.3	405.7
70°	368.2	366.5	364.8	363.4	362.2	361.1	360.0	358.8
72.5°	325.0	323.0	321.1	319.6	318.5	317.4	316.2	315.1
75°	257.9	257.0	256.2	255.1	254.0	252.9	251.8	250.6
77.5°	196.4	196.0	195.5	194.8	194.0	193.2	192.4	191.6
80°	157.2	156.9	156.7	156.2	155.6	155.0	154.5	153.9
82.5°	120.1	119.6	119.1	118.8	118.7	118.6	118.5	118.3
85°	70.7	70.4	70.1	69.7	69.1	68.5	68.0	67.4
87.5°	31.7	32.0	32.2	32.3	32.0	31.8	31.5	31.2
90°	25.8	27.4	29.0	30.3	31.2	32.1	33.1	34.0
92.5°	25.8	27.4	29.0	30.0	30.4	30.9	31.4	31.8
95°	25.8	27.4	29.0	29.8	29.8	29.8	29.8	29.8
97.5°	52.0	43.2	34.2	29.8	29.8	29.8	29.8	29.8
100°	152.9	105.9	59.0	34.9	33.6	32.3	31.1	29.8
102.5°	297.2	288.3	279.5	264.3	242.8	221.4	199.9	178.5
105°	422.8	422.8	422.8	422.6	422.4	422.1	421.7	421.4
107.5°	535.4	535.4	535.5	535.0	534.0	533.1	532.2	531.2
110°	608.2	607.3	606.3	606.1	606.3	606.6	607.0	607.3



TEST NUMBER: P333458-830

CATALOG NUMBER: S125DIW-S1090D1560U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	680.3	679.2	678.0	677.1	676.7	676.3	675.8	675.3
115°	789.2	788.0	786.6	785.1	783.3	781.3	779.4	777.5
117.5°	894.3	892.7	891.0	889.8	889.0	888.2	887.3	886.5
120°	962.1	961.5	960.9	959.8	958.2	956.6	955.1	953.5
122.5°	1026.8	1026.2	1025.6	1024.4	1022.6	1020.7	1018.9	1017.0
125°	1121.2	1119.9	1118.7	1117.6	1116.6	1115.7	1114.7	1113.8
127.5°	1207.5	1206.8	1206.1	1204.6	1202.2	1200.0	1197.6	1195.2
130°	1263.8	1262.8	1261.9	1260.6	1259.0	1257.4	1255.8	1254.2
132.5°	1316.4	1316.2	1316.0	1315.0	1313.5	1311.9	1310.3	1308.7
135°	1393.5	1392.9	1392.2	1390.9	1389.0	1387.1	1385.3	1383.4
137.5°	1465.4	1465.5	1465.7	1464.9	1463.2	1461.6	1459.9	1458.3
140°	1509.5	1510.1	1510.8	1510.1	1508.3	1506.4	1504.5	1502.6
142.5°	1552.7	1552.9	1553.0	1552.2	1550.2	1548.3	1546.4	1544.5
145°	1613.9	1614.2	1614.5	1613.7	1611.8	1610.0	1608.1	1606.2
147.5°	1666.2	1666.6	1667.0	1666.0	1663.8	1661.5	1659.3	1657.0
150°	1699.6	1700.3	1700.9	1700.0	1697.4	1694.9	1692.4	1689.9
152.5°	1729.2	1729.8	1730.4	1729.6	1727.3	1725.0	1722.8	1720.5
155°	1769.8	1770.8	1771.7	1770.8	1768.4	1765.9	1763.3	1760.8
157.5°	1803.4	1804.4	1805.4	1804.7	1802.1	1799.6	1797.1	1794.6
160°	1824.3	1825.6	1826.8	1826.3	1823.7	1821.2	1818.6	1816.2
162.5°	1843.5	1845.3	1847.0	1846.5	1843.8	1841.0	1838.2	1835.4
165°	1868.1	1870.1	1872.0	1871.6	1869.2	1866.6	1864.1	1861.5
167.5°	1886.8	1889.0	1891.3	1891.0	1888.2	1885.4	1882.5	1879.7
170°	1896.4	1898.9	1901.4	1901.3	1898.5	1895.6	1892.7	1889.9
172.5°	1903.8	1906.1	1908.4	1908.1	1905.3	1902.4	1899.6	1896.8
175°	1911.9	1914.5	1917.0	1916.8	1914.0	1911.2	1908.4	1905.5
177.5°	1915.3	1917.0	1918.8	1918.7	1916.7	1914.7	1912.6	1910.6
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0

(END OF REPORT)