

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333434-830

Luminaire Tested: **S125DIW-S1090D470U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333434-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D470U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5952.7 lumens
Efficiency: N/A
Efficacy: 128.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333434-830

CATALOG NUMBER: S125DIW-S1090D470U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333434-830

CATALOG NUMBER: S125DIW-S1090D470U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	59
2	93	85	79	74	88	81	75	70	73	68	64	65	62	59	58	55	53	49
3	85	75	67	61	80	71	64	59	64	59	54	58	53	50	51	48	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	36
5	71	59	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	38	33	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	24
8	57	44	36	30	54	42	35	29	38	32	28	35	30	26	32	27	24	22
9	53	40	32	27	50	39	31	26	35	29	25	32	27	23	29	25	22	20
10	50	37	30	25	47	35	29	24	33	27	22	30	25	21	27	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10388	10388	10388
5°	10410	10311	10377
10°	10347	10238	10297
15°	10235	10116	10158
20°	10074	9943	9961
25°	9902	9738	9729
30°	9688	9517	9470
35°	9460	9280	9150
40°	9226	9022	8893
45°	8972	8786	8611
50°	8694	8501	8246
55°	8425	8180	7952
60°	8103	7856	7576
65°	7719	7467	7213
70°	7353	7017	6775
75°	6697	6478	6253
80°	5962	5869	5724
85°	5180	5283	4994



TEST NUMBER: P333434-830

CATALOG NUMBER: S125DIW-S1090D470U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.6	2.5
10°-20°	428.4	7.2
20°-30°	632.5	10.6
30°-40°	738.0	12.4
40°-50°	741.2	12.5
50°-60°	650.7	10.9
60°-70°	484.8	8.1
70°-80°	277.2	4.7
80°-90°	81.8	1.4
90°-100°	20.9	0.4
100°-110°	128.8	2.2
110°-120°	233.6	3.9
120°-130°	299.9	5.0
130°-140°	322.5	5.4
140°-150°	302.7	5.1
150°-160°	244.9	4.1
160°-170°	158.4	2.7
170°-180°	54.6	0.9
0°-30°	1212.5	20.4
0°-40°	1950.5	32.8
0°-60°	3342.4	56.1
0°-90°	4186.3	70.3
90°-120°	383.4	6.4
90°-150°	1308.5	22.0
90°-180°	1766.0	29.7
0°-180°	5952.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1608	1608	1608	1608	1608	
5°	1606	1603	1590	1601	1601	152
15°	1531	1526	1513	1519	1519	431
25°	1390	1383	1367	1369	1365	639
35°	1200	1194	1177	1170	1160	750
45°	982	977	962	947	943	757
55°	748	744	726	715	706	668
65°	505	502	489	477	472	501
75°	268	266	260	256	251	286
85°	70	71	71	70	67	78
90°	0	4	7	9	10	5
95°	24	22	7	9	9	31
105°	125	127	127	127	127	133
115°	235	237	238	236	234	233
125°	335	338	338	336	335	299
135°	418	420	419	418	416	322
145°	484	485	485	485	483	303
155°	533	531	531	532	529	245
165°	562	560	560	563	559	159
175°	575	573	573	576	573	55
180°	575	575	575	575	575	



TEST NUMBER: P333434-830

CATALOG NUMBER: S125DIW-S1090D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1612.4	1611.7	1611.0	1610.3	1609.7	1608.2	1605.9	1603.6	1601.4	1599.1	1601.4
5°	1605.8	1605.2	1604.7	1604.1	1603.5	1601.9	1599.0	1596.2	1593.4	1590.5	1593.1
7.5°	1591.0	1590.4	1589.9	1589.3	1588.7	1586.9	1583.8	1580.6	1577.5	1574.4	1577.0
10°	1577.8	1577.3	1576.7	1576.1	1575.6	1573.7	1570.6	1567.4	1564.3	1561.2	1563.5
12.5°	1561.5	1560.5	1559.4	1558.4	1557.5	1555.5	1552.6	1549.7	1546.8	1543.9	1545.8
15°	1530.7	1529.8	1529.0	1528.1	1527.3	1525.3	1522.2	1519.1	1516.0	1512.9	1514.3
17.5°	1495.3	1494.1	1492.8	1491.6	1490.3	1488.1	1484.9	1481.7	1478.5	1475.2	1477.0
20°	1465.8	1465.3	1464.7	1464.1	1463.6	1461.4	1457.7	1454.1	1450.4	1446.7	1448.7
22.5°	1436.2	1435.3	1434.3	1433.2	1432.2	1429.9	1426.5	1423.1	1419.7	1416.2	1417.5
25°	1389.5	1388.1	1386.7	1385.3	1383.8	1381.3	1377.6	1373.9	1370.3	1366.6	1367.2
27.5°	1334.7	1333.9	1333.0	1332.2	1331.3	1329.1	1325.2	1321.4	1317.7	1313.9	1314.0
30°	1299.1	1298.3	1297.4	1296.6	1295.7	1293.2	1288.9	1284.7	1280.4	1276.2	1275.6
32.5°	1260.5	1259.1	1257.8	1256.5	1255.3	1252.7	1248.9	1245.1	1241.3	1237.6	1236.5
35°	1199.9	1198.7	1197.6	1196.5	1195.3	1192.8	1188.8	1184.9	1180.9	1177.0	1175.5
37.5°	1137.0	1135.6	1134.2	1132.7	1131.3	1128.8	1125.0	1121.3	1117.6	1113.9	1111.7
40°	1094.3	1092.9	1091.5	1090.1	1088.6	1085.9	1081.9	1078.0	1074.0	1070.1	1067.5
42.5°	1048.5	1047.3	1046.1	1044.9	1043.7	1041.1	1037.2	1033.2	1029.3	1025.3	1022.9
45°	982.3	981.2	980.1	978.9	977.8	975.5	972.1	968.7	965.4	962.0	958.6
47.5°	911.1	911.1	911.2	911.3	911.3	909.3	905.2	901.1	897.0	893.0	889.5
50°	865.3	864.4	863.6	862.7	861.9	859.7	856.3	852.9	849.5	846.1	842.4
52.5°	818.4	817.7	817.2	816.5	816.0	813.8	810.2	806.5	803.0	799.3	796.1
55°	748.2	747.3	746.5	745.6	744.8	742.3	738.4	734.4	730.5	726.5	724.0
57.5°	674.1	673.6	673.3	672.8	672.3	670.4	667.0	663.7	660.4	657.0	653.7
60°	627.3	626.1	625.0	623.9	622.7	620.7	617.6	614.4	611.3	608.2	605.4
62.5°	578.4	577.5	576.6	575.7	574.9	573.1	570.3	567.7	565.1	562.4	559.3
65°	505.1	504.5	504.0	503.4	502.8	501.1	497.9	494.8	491.7	488.6	486.1
67.5°	434.1	432.9	431.8	430.6	429.4	427.6	425.3	423.0	420.7	418.4	416.2
70°	389.4	388.0	386.5	385.1	383.7	381.7	379.2	376.6	374.1	371.6	369.9
72.5°	340.5	339.5	338.6	337.6	336.7	335.4	333.8	332.1	330.5	328.8	326.9
75°	268.4	267.9	267.3	266.7	266.2	265.2	263.8	262.4	261.0	259.6	258.7
77.5°	202.1	201.8	201.6	201.4	201.1	200.7	199.8	199.1	198.3	197.5	197.0
80°	160.3	160.3	160.3	160.3	160.3	160.0	159.5	158.9	158.3	157.8	157.5
82.5°	123.7	123.2	122.8	122.3	121.9	121.6	121.5	121.4	121.2	121.1	120.6
85°	69.9	70.2	70.5	70.8	71.1	71.3	71.3	71.3	71.3	71.3	71.0
87.5°	27.5	27.7	27.9	28.0	28.2	28.2	28.1	28.0	27.9	27.8	27.9
90°	0.5	1.2	2.0	2.7	3.5	4.1	4.8	5.5	6.1	6.8	7.3
92.5°	6.6	6.0	5.5	5.0	4.4	4.4	5.1	5.7	6.2	6.8	7.3
95°	24.3	24.0	23.8	23.5	23.2	21.2	17.6	14.0	10.5	6.8	7.3
97.5°	50.7	51.3	51.7	52.3	52.8	49.5	42.3	35.3	28.1	21.0	18.3
100°	71.2	71.5	71.8	72.1	72.4	72.7	73.0	73.4	73.8	74.2	60.0
102.5°	92.0	92.4	92.7	93.1	93.5	93.8	94.0	94.2	94.4	94.6	92.0
105°	125.4	125.7	126.1	126.5	126.9	127.1	127.1	127.1	127.1	127.1	127.1
107.5°	159.9	159.9	159.9	159.9	159.9	160.0	160.2	160.4	160.6	160.8	160.9
110°	182.5	182.5	182.5	182.5	182.5	182.6	182.8	182.9	183.1	183.3	183.0



TEST NUMBER: P333434-830

CATALOG NUMBER: S125DIW-S1090D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	203.7	203.9	204.1	204.3	204.5	204.7	204.8	205.0	205.1	205.2	204.8
115°	235.4	235.8	236.3	236.8	237.2	237.5	237.6	237.7	237.8	237.9	237.5
117.5°	268.2	268.2	268.2	268.2	268.2	268.3	268.6	269.0	269.4	269.8	269.3
120°	288.7	288.6	288.5	288.4	288.3	288.4	288.7	289.0	289.3	289.5	289.4
122.5°	306.8	307.1	307.5	307.8	308.2	308.4	308.6	308.7	308.9	309.0	308.8
125°	334.7	335.4	336.0	336.7	337.3	337.7	337.7	337.7	337.7	337.7	337.3
127.5°	361.4	361.9	362.4	362.9	363.4	363.5	363.4	363.4	363.4	363.3	363.1
130°	377.8	378.2	378.7	379.2	379.7	379.9	380.0	380.1	380.2	380.3	380.0
132.5°	394.2	394.7	395.3	395.8	396.3	396.5	396.3	396.2	395.9	395.7	395.7
135°	417.5	418.0	418.6	419.1	419.7	419.9	419.7	419.5	419.3	419.1	419.0
137.5°	438.8	439.3	439.8	440.4	440.8	441.0	440.8	440.6	440.5	440.3	440.4
140°	452.8	453.0	453.2	453.4	453.6	453.6	453.6	453.5	453.4	453.3	453.5
142.5°	465.4	465.6	465.7	465.8	465.9	466.0	466.2	466.3	466.5	466.6	466.6
145°	484.0	484.2	484.4	484.6	484.7	484.8	484.8	484.8	484.8	484.8	484.9
147.5°	500.2	500.1	500.1	500.0	500.0	500.0	500.2	500.3	500.4	500.5	500.6
150°	510.4	510.2	510.0	509.8	509.6	509.6	509.8	510.0	510.2	510.4	510.6
152.5°	520.3	519.9	519.4	519.1	518.6	518.5	518.7	518.9	519.1	519.2	519.4
155°	533.0	532.4	531.9	531.3	530.7	530.6	530.7	530.9	531.1	531.3	531.6
157.5°	542.8	542.4	542.2	541.8	541.4	541.3	541.3	541.3	541.3	541.4	541.7
160°	549.6	549.0	548.5	547.9	547.3	547.1	547.2	547.3	547.4	547.5	547.9
162.5°	555.1	554.5	553.9	553.4	552.8	552.6	552.7	552.8	552.9	553.0	553.5
165°	562.4	561.8	561.3	560.7	560.2	559.9	560.0	560.1	560.2	560.2	560.8
167.5°	567.9	567.3	566.8	566.1	565.5	565.2	565.3	565.4	565.5	565.6	566.4
170°	571.0	570.3	569.6	568.9	568.3	568.0	568.1	568.2	568.3	568.4	569.1
172.5°	573.0	572.3	571.7	571.0	570.3	570.1	570.2	570.4	570.6	570.8	571.5
175°	575.2	574.7	574.1	573.5	573.0	572.7	572.8	572.9	573.0	573.1	573.8
177.5°	576.3	575.8	575.3	574.9	574.4	574.2	574.3	574.4	574.5	574.6	575.0
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2



TEST NUMBER: P333434-830

CATALOG NUMBER: S125DIW-S1090D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1603.6	1605.9	1608.2	1609.2	1609.0	1608.7	1608.5	1608.4
5°	1595.6	1598.2	1600.7	1601.9	1601.6	1601.3	1601.0	1600.7
7.5°	1579.4	1582.0	1584.4	1585.5	1585.3	1585.0	1584.7	1584.4
10°	1565.8	1568.0	1570.3	1571.3	1571.0	1570.7	1570.5	1570.2
12.5°	1547.6	1549.4	1551.1	1552.1	1552.0	1551.9	1551.9	1551.8
15°	1515.7	1517.1	1518.5	1519.3	1519.3	1519.3	1519.3	1519.3
17.5°	1478.8	1480.5	1482.2	1482.4	1481.0	1479.6	1478.2	1476.8
20°	1450.7	1452.6	1454.6	1454.9	1453.5	1452.1	1450.7	1449.3
22.5°	1418.8	1420.1	1421.4	1421.5	1420.6	1419.7	1418.7	1417.7
25°	1367.7	1368.3	1368.9	1368.7	1367.8	1367.0	1366.1	1365.3
27.5°	1314.1	1314.2	1314.4	1314.0	1313.2	1312.3	1311.5	1310.6
30°	1275.1	1274.5	1273.9	1273.3	1272.4	1271.6	1270.7	1269.9
32.5°	1235.5	1234.4	1233.5	1232.2	1230.7	1229.2	1227.6	1226.1
35°	1174.1	1172.7	1171.3	1169.5	1167.2	1165.0	1162.7	1160.5
37.5°	1109.7	1107.6	1105.5	1103.8	1102.5	1101.2	1099.9	1098.6
40°	1065.0	1062.4	1059.9	1058.2	1057.3	1056.5	1055.6	1054.8
42.5°	1020.7	1018.3	1016.1	1014.2	1013.0	1011.6	1010.3	1009.0
45°	955.2	951.8	948.4	946.2	945.4	944.5	943.7	942.8
47.5°	886.1	882.6	879.2	876.5	874.5	872.5	870.5	868.6
50°	838.8	835.1	831.4	828.6	826.6	824.6	822.7	820.7
52.5°	792.9	789.7	786.5	783.7	781.5	779.3	777.1	774.9
55°	721.4	718.9	716.3	714.1	712.1	710.1	708.1	706.2
57.5°	650.5	647.2	643.9	641.8	640.7	639.6	638.6	637.4
60°	602.6	599.7	596.9	594.5	592.5	590.5	588.5	586.5
62.5°	556.3	553.3	550.2	547.9	546.4	544.9	543.3	541.8
65°	483.5	481.0	478.4	476.5	475.4	474.3	473.2	472.0
67.5°	414.1	411.9	409.7	408.3	407.6	407.0	406.3	405.7
70°	368.2	366.5	364.8	363.4	362.2	361.1	360.0	358.8
72.5°	325.0	323.0	321.1	319.6	318.5	317.4	316.2	315.1
75°	257.9	257.0	256.2	255.1	254.0	252.9	251.8	250.6
77.5°	196.4	196.0	195.5	194.8	194.0	193.2	192.4	191.6
80°	157.2	156.9	156.7	156.2	155.6	155.0	154.5	153.9
82.5°	120.1	119.6	119.1	118.8	118.7	118.6	118.5	118.3
85°	70.7	70.4	70.1	69.7	69.1	68.5	68.0	67.4
87.5°	28.0	28.1	28.2	28.1	27.6	27.2	26.9	26.5
90°	7.7	8.2	8.7	9.1	9.4	9.7	10.0	10.3
92.5°	7.7	8.2	8.7	9.0	9.1	9.3	9.4	9.5
95°	7.7	8.2	8.7	9.0	9.0	9.0	9.0	9.0
97.5°	15.6	13.0	10.3	9.0	9.0	9.0	9.0	9.0
100°	46.0	31.9	17.7	10.5	10.1	9.7	9.3	9.0
102.5°	89.4	86.6	84.0	79.5	73.0	66.5	60.0	53.6
105°	127.1	127.1	127.1	127.1	127.0	126.9	126.8	126.7
107.5°	160.9	160.9	160.9	160.8	160.5	160.2	159.9	159.7
110°	182.8	182.5	182.2	182.1	182.2	182.3	182.4	182.5



TEST NUMBER: P333434-830

CATALOG NUMBER: S125DIW-S1090D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	204.4	204.1	203.8	203.5	203.4	203.2	203.1	202.9
115°	237.1	236.8	236.4	235.9	235.4	234.8	234.2	233.7
117.5°	268.7	268.2	267.8	267.4	267.1	266.9	266.6	266.5
120°	289.2	289.0	288.8	288.4	287.9	287.5	287.0	286.5
122.5°	308.6	308.4	308.2	307.8	307.3	306.7	306.2	305.7
125°	337.0	336.6	336.2	335.8	335.5	335.3	335.0	334.7
127.5°	362.9	362.7	362.5	362.0	361.3	360.6	359.9	359.2
130°	379.8	379.5	379.2	378.8	378.3	377.9	377.4	376.9
132.5°	395.6	395.5	395.5	395.2	394.7	394.3	393.8	393.3
135°	418.8	418.6	418.4	418.0	417.5	416.9	416.3	415.8
137.5°	440.4	440.5	440.5	440.3	439.7	439.2	438.8	438.3
140°	453.6	453.8	454.0	453.8	453.3	452.7	452.1	451.6
142.5°	466.7	466.7	466.7	466.5	465.9	465.3	464.8	464.2
145°	485.0	485.1	485.2	484.9	484.4	483.8	483.2	482.7
147.5°	500.8	500.9	501.0	500.7	500.0	499.4	498.6	497.9
150°	510.8	511.0	511.1	510.9	510.1	509.3	508.6	507.8
152.5°	519.6	519.8	520.0	519.8	519.1	518.4	517.7	517.1
155°	531.9	532.2	532.4	532.2	531.4	530.7	529.9	529.1
157.5°	542.0	542.2	542.5	542.3	541.6	540.8	540.1	539.3
160°	548.3	548.7	549.0	548.8	548.1	547.3	546.6	545.8
162.5°	554.0	554.6	555.1	555.0	554.1	553.3	552.4	551.6
165°	561.5	562.0	562.6	562.5	561.8	560.9	560.2	559.4
167.5°	567.0	567.7	568.4	568.4	567.4	566.6	565.7	564.9
170°	569.9	570.7	571.5	571.4	570.5	569.7	568.8	568.0
172.5°	572.1	572.8	573.5	573.4	572.6	571.7	570.9	570.0
175°	574.6	575.3	576.1	576.1	575.2	574.4	573.5	572.7
177.5°	575.6	576.1	576.6	576.6	576.0	575.4	574.8	574.2
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2

(END OF REPORT)