

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333662

Luminaire Tested: **S125RDIW-S610D470U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333662
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D470U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4251.8 lumens
Efficiency: N/A
Efficacy: 140.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333662

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333662

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	54	53	48
2	91	83	77	72	84	78	72	68	67	63	60	57	55	52	49	46	45	40
3	83	73	66	60	77	69	62	57	59	55	51	51	47	44	43	40	38	34
4	76	65	57	51	70	61	54	49	53	48	43	46	41	38	39	36	33	30
5	70	58	50	44	65	55	47	42	48	42	37	41	37	33	35	32	29	26
6	64	52	44	38	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	47	39	34	55	44	37	32	39	33	29	34	29	26	29	26	23	20
8	55	43	35	30	51	40	33	29	36	30	26	31	27	23	27	23	21	18
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	16
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6497	6497	6497
5°	6512	6438	6477
10°	6462	6378	6378
15°	6386	6248	6197
20°	6287	6068	5994
25°	6173	5890	5761
30°	6029	5683	5502
35°	5882	5469	5211
40°	5746	5246	4926
45°	5580	4996	4615
50°	5413	4725	4290
55°	5219	4466	3944
60°	5025	4151	3573
65°	4795	3785	3147
70°	4534	3329	2712
75°	4172	2805	2256
80°	3675	2205	1893
85°	3097	1801	1690



TEST NUMBER: P333662

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.6	2.2
10°-20°	264.3	6.2
20°-30°	383.3	9.0
30°-40°	436.9	10.3
40°-50°	425.9	10.0
50°-60°	358.5	8.4
60°-70°	251.3	5.9
70°-80°	129.2	3.0
80°-90°	33.9	0.8
90°-100°	22.2	0.5
100°-110°	136.7	3.2
110°-120°	247.9	5.8
120°-130°	318.1	7.5
130°-140°	342.2	8.0
140°-150°	321.2	7.6
150°-160°	259.8	6.1
160°-170°	168.0	4.0
170°-180°	58.0	1.4
0°-30°	742.3	17.5
0°-40°	1179.2	27.7
0°-60°	1963.5	46.2
0°-90°	2377.8	55.9
90°-120°	406.7	9.6
90°-150°	1388.2	32.7
90°-180°	1874.0	44.1
0°-180°	4251.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1006	1006	1006	1006	1006	
5°	1004	1001	993	1000	999	95
15°	955	950	934	933	927	269
25°	866	854	827	817	808	398
35°	746	727	694	672	661	467
45°	611	588	547	518	505	471
55°	464	438	397	364	350	414
65°	314	287	248	218	206	311
75°	167	144	112	96	90	177
85°	42	29	24	24	23	47
90°	0	4	7	9	11	3
95°	26	24	7	9	10	33
105°	133	135	135	135	134	141
115°	250	252	252	251	248	247
125°	355	358	358	356	355	317
135°	443	445	445	444	441	341
145°	514	514	514	515	512	321
155°	566	563	564	565	561	260
165°	597	594	594	597	594	168
175°	610	608	608	611	608	58
180°	610	610	610	610	610	



TEST NUMBER: P333662

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1007.8	1007.4	1007.0	1006.6	1006.2	1005.3	1003.9	1002.6	1001.2	999.9	1001.2
5°	1004.4	1003.8	1003.1	1002.4	1001.7	1000.5	998.6	996.8	994.9	993.0	994.7
7.5°	994.6	993.9	993.3	992.6	992.0	990.6	988.3	986.1	983.9	981.6	982.8
10°	985.4	984.9	984.4	983.9	983.4	982.0	979.6	977.3	974.9	972.5	973.0
12.5°	975.1	974.5	973.8	973.2	972.5	970.6	967.5	964.3	961.1	957.9	958.3
15°	955.1	954.0	953.0	952.0	951.0	948.7	945.2	941.6	938.1	934.5	934.4
17.5°	932.4	930.9	929.3	927.8	926.2	923.2	918.7	914.3	909.8	905.4	904.5
20°	914.8	913.1	911.4	909.7	908.0	904.5	899.1	893.7	888.3	882.9	882.0
22.5°	895.3	893.6	892.0	890.3	888.6	884.9	879.2	873.6	867.9	862.2	860.6
25°	866.2	863.6	861.1	858.6	856.0	851.6	845.4	839.1	832.9	826.6	824.5
27.5°	832.7	829.7	826.6	823.5	820.4	815.6	808.9	802.2	795.5	788.8	785.7
30°	808.4	805.2	802.0	798.8	795.6	790.4	783.3	776.3	769.2	762.1	758.2
32.5°	784.7	781.0	777.2	773.5	769.7	764.2	757.0	749.8	742.5	735.3	731.0
35°	746.1	742.1	738.0	734.0	729.9	724.1	716.5	708.9	701.3	693.7	688.8
37.5°	708.3	703.3	698.4	693.5	688.6	682.2	674.3	666.5	658.7	650.8	645.0
40°	681.5	676.5	671.4	666.3	661.3	654.7	646.6	638.5	630.4	622.3	615.9
42.5°	653.6	648.4	643.2	638.0	632.8	626.0	617.6	609.2	600.9	592.5	586.3
45°	610.9	606.0	601.1	596.2	591.3	584.2	574.9	565.6	556.3	547.0	540.3
47.5°	566.7	561.5	556.3	551.2	546.0	538.7	529.4	520.0	510.7	501.3	494.4
50°	538.7	533.1	527.5	522.0	516.4	508.8	499.2	489.6	479.9	470.3	463.2
52.5°	508.3	502.6	496.9	491.2	485.5	478.1	469.0	459.9	450.8	441.7	434.1
55°	463.5	458.1	452.7	447.3	441.9	434.4	425.0	415.5	406.1	396.6	389.0
57.5°	418.2	412.4	406.6	400.9	395.1	387.6	378.5	369.4	360.3	351.2	343.7
60°	389.0	383.1	377.2	371.3	365.4	357.9	348.7	339.6	330.5	321.4	314.0
62.5°	358.0	352.4	346.7	341.1	335.5	328.0	318.8	309.5	300.3	291.0	284.1
65°	313.8	308.1	302.3	296.6	290.8	283.5	274.5	265.6	256.6	247.7	240.9
67.5°	269.9	264.1	258.4	252.7	246.9	239.8	231.2	222.6	214.0	205.4	199.3
70°	240.1	234.4	228.6	222.9	217.1	210.0	201.6	193.2	184.7	176.3	171.0
72.5°	210.9	205.3	199.7	194.1	188.5	181.7	173.8	165.9	158.0	150.1	145.3
75°	167.2	162.1	157.0	152.0	146.9	140.8	133.7	126.6	119.5	112.4	108.7
77.5°	123.7	119.6	115.6	111.5	107.5	102.6	96.9	91.3	85.6	79.9	77.3
80°	98.8	94.7	90.7	86.6	82.6	78.2	73.4	68.7	64.0	59.3	57.7
82.5°	74.5	70.8	67.2	63.5	59.9	56.4	53.2	49.9	46.7	43.5	42.8
85°	41.8	38.7	35.7	32.7	29.6	27.7	26.8	26.0	25.2	24.3	24.1
87.5°	14.1	13.3	12.5	11.7	10.9	10.5	10.5	10.6	10.6	10.6	10.7
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.1	5.8	6.5	7.2	7.7
92.5°	7.0	6.4	5.8	5.3	4.7	4.7	5.4	6.0	6.6	7.2	7.7
95°	25.8	25.5	25.2	24.9	24.6	22.5	18.7	14.9	11.1	7.2	7.7
97.5°	53.8	54.4	54.9	55.5	56.0	52.5	44.9	37.4	29.8	22.3	19.4
100°	75.5	75.9	76.2	76.5	76.8	77.1	77.5	77.9	78.3	78.7	63.7
102.5°	97.6	98.0	98.4	98.8	99.2	99.5	99.7	99.9	100.2	100.4	97.6
105°	133.0	133.4	133.8	134.2	134.6	134.8	134.8	134.8	134.8	134.8	134.8
107.5°	169.7	169.7	169.7	169.7	169.7	169.8	170.0	170.2	170.4	170.6	170.7
110°	193.6	193.6	193.6	193.6	193.6	193.7	193.9	194.1	194.3	194.5	194.2



TEST NUMBER: P333662

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	216.1	216.3	216.5	216.8	217.0	217.2	217.3	217.5	217.6	217.7	217.3
115°	249.7	250.2	250.7	251.2	251.7	252.0	252.1	252.2	252.3	252.4	252.0
117.5°	284.6	284.5	284.5	284.5	284.5	284.7	285.0	285.4	285.8	286.2	285.7
120°	306.3	306.2	306.1	306.0	305.9	306.0	306.3	306.6	306.9	307.2	307.0
122.5°	325.5	325.8	326.2	326.6	327.0	327.2	327.4	327.5	327.7	327.8	327.6
125°	355.1	355.8	356.5	357.2	357.9	358.3	358.3	358.3	358.3	358.3	357.9
127.5°	383.4	384.0	384.5	385.0	385.5	385.7	385.6	385.6	385.5	385.4	385.2
130°	400.8	401.3	401.8	402.3	402.8	403.1	403.2	403.3	403.4	403.5	403.2
132.5°	418.2	418.8	419.4	419.9	420.5	420.7	420.5	420.3	420.0	419.8	419.8
135°	442.9	443.5	444.1	444.7	445.3	445.5	445.3	445.1	444.9	444.7	444.5
137.5°	465.6	466.1	466.6	467.2	467.7	467.9	467.7	467.5	467.3	467.1	467.2
140°	480.4	480.6	480.8	481.0	481.2	481.3	481.2	481.1	481.0	480.9	481.1
142.5°	493.8	494.0	494.1	494.2	494.3	494.4	494.6	494.7	494.9	495.0	495.0
145°	513.5	513.7	513.9	514.1	514.3	514.4	514.4	514.4	514.4	514.4	514.5
147.5°	530.7	530.6	530.6	530.5	530.5	530.5	530.7	530.8	530.9	531.0	531.1
150°	541.5	541.3	541.1	540.9	540.7	540.7	540.9	541.1	541.3	541.5	541.7
152.5°	552.0	551.6	551.1	550.7	550.2	550.1	550.3	550.5	550.7	550.9	551.1
155°	565.5	564.9	564.3	563.7	563.1	562.9	563.1	563.3	563.5	563.7	564.0
157.5°	575.9	575.5	575.2	574.8	574.4	574.3	574.3	574.3	574.3	574.4	574.7
160°	583.1	582.5	581.9	581.3	580.7	580.5	580.6	580.7	580.8	580.9	581.3
162.5°	588.9	588.3	587.7	587.1	586.5	586.3	586.4	586.5	586.6	586.7	587.2
165°	596.7	596.1	595.5	594.9	594.3	594.0	594.1	594.2	594.3	594.4	595.0
167.5°	602.5	601.9	601.3	600.6	600.0	599.7	599.8	599.9	600.0	600.1	600.9
170°	605.8	605.1	604.3	603.6	602.9	602.6	602.7	602.8	602.9	603.0	603.8
172.5°	607.9	607.2	606.5	605.8	605.1	604.9	605.0	605.2	605.4	605.6	606.3
175°	610.3	609.7	609.1	608.5	607.9	607.6	607.7	607.8	607.9	608.0	608.8
177.5°	611.4	610.9	610.4	609.9	609.4	609.2	609.3	609.4	609.5	609.6	610.1
180°	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3



TEST NUMBER: P333662

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0	1006.0
2.5°	1002.6	1003.9	1005.3	1005.9	1005.8	1005.6	1005.5	1005.4
5°	996.4	998.1	999.8	1000.5	1000.1	999.8	999.5	999.1
7.5°	984.0	985.2	986.4	986.8	986.4	986.0	985.7	985.3
10°	973.5	974.0	974.6	974.6	974.0	973.5	973.0	972.5
12.5°	958.7	959.1	959.4	959.2	958.4	957.7	956.9	956.1
15°	934.2	934.0	933.9	933.0	931.5	930.0	928.5	926.9
17.5°	903.7	902.8	902.0	900.9	899.7	898.4	897.2	895.9
20°	881.2	880.3	879.5	878.3	876.8	875.3	873.8	872.2
22.5°	858.9	857.2	855.6	854.1	852.9	851.6	850.4	849.1
25°	822.3	820.1	817.9	815.8	814.0	812.1	810.3	808.4
27.5°	782.7	779.6	776.5	774.1	772.3	770.5	768.7	766.9
30°	754.3	750.4	746.5	743.8	742.3	740.8	739.3	737.8
32.5°	726.7	722.5	718.2	715.1	713.1	711.2	709.3	707.4
35°	683.9	679.0	674.1	670.5	668.1	665.7	663.4	661.0
37.5°	639.1	633.2	627.3	623.2	620.9	618.7	616.4	614.1
40°	609.4	603.0	596.6	592.4	590.4	588.3	586.3	584.3
42.5°	580.2	574.0	567.9	563.3	560.4	557.4	554.4	551.5
45°	533.5	526.8	520.0	515.4	512.9	510.3	507.8	505.3
47.5°	487.4	480.4	473.5	468.6	465.8	463.0	460.2	457.4
50°	456.1	449.0	441.9	437.1	434.6	432.1	429.5	427.0
52.5°	426.5	418.8	411.2	406.1	403.6	401.1	398.5	396.0
55°	381.4	373.8	366.2	361.1	358.4	355.7	353.0	350.3
57.5°	336.3	328.9	321.5	316.5	314.1	311.7	309.4	307.0
60°	306.5	299.1	291.7	286.7	284.2	281.6	279.1	276.6
62.5°	277.2	270.3	263.4	258.7	256.2	253.7	251.1	248.6
65°	234.2	227.4	220.7	216.0	213.5	211.0	208.4	205.9
67.5°	193.1	186.9	180.7	176.6	174.6	172.6	170.5	168.5
70°	165.8	160.6	155.3	151.7	149.7	147.7	145.6	143.6
72.5°	140.5	135.6	130.8	127.7	126.4	125.0	123.7	122.3
75°	105.0	101.3	97.6	95.1	94.0	92.8	91.6	90.4
77.5°	74.7	72.1	69.5	67.8	66.9	66.0	65.2	64.3
80°	56.2	54.7	53.2	52.3	51.9	51.6	51.2	50.9
82.5°	42.0	41.3	40.6	40.2	40.0	39.8	39.6	39.4
85°	24.0	23.8	23.6	23.5	23.3	23.1	23.0	22.8
87.5°	10.8	10.9	11.0	11.0	10.9	10.8	10.8	10.7
90°	8.2	8.7	9.2	9.7	10.0	10.3	10.6	10.9
92.5°	8.2	8.7	9.2	9.6	9.7	9.9	10.0	10.1
95°	8.2	8.7	9.2	9.5	9.5	9.5	9.5	9.5
97.5°	16.6	13.8	10.9	9.5	9.5	9.5	9.5	9.5
100°	48.8	33.8	18.8	11.1	10.7	10.3	9.9	9.5
102.5°	94.8	91.9	89.1	84.3	77.4	70.6	63.7	56.9
105°	134.8	134.8	134.8	134.8	134.7	134.6	134.5	134.4
107.5°	170.7	170.7	170.7	170.6	170.3	170.0	169.7	169.4
110°	193.9	193.6	193.3	193.2	193.3	193.4	193.5	193.6



TEST NUMBER: P333662

CATALOG NUMBER: S125RDIW-S610D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	216.9	216.5	216.2	215.9	215.8	215.6	215.5	215.3
115°	251.6	251.2	250.8	250.3	249.7	249.1	248.5	247.9
117.5°	285.1	284.6	284.1	283.7	283.4	283.2	282.9	282.7
120°	306.8	306.6	306.4	306.0	305.5	305.0	304.5	304.0
122.5°	327.4	327.2	327.0	326.6	326.0	325.4	324.9	324.3
125°	357.5	357.1	356.7	356.3	356.0	355.7	355.4	355.1
127.5°	385.0	384.8	384.6	384.1	383.3	382.6	381.8	381.1
130°	402.9	402.6	402.3	401.9	401.4	400.9	400.4	399.9
132.5°	419.7	419.6	419.6	419.3	418.8	418.3	417.8	417.3
135°	444.3	444.1	443.9	443.5	442.9	442.3	441.7	441.1
137.5°	467.2	467.3	467.3	467.1	466.5	466.0	465.5	465.0
140°	481.3	481.5	481.7	481.5	480.9	480.3	479.7	479.1
142.5°	495.1	495.1	495.2	494.9	494.3	493.7	493.1	492.5
145°	514.6	514.7	514.8	514.5	513.9	513.3	512.7	512.1
147.5°	531.3	531.4	531.5	531.2	530.5	529.8	529.0	528.3
150°	541.9	542.1	542.3	542.0	541.2	540.4	539.6	538.8
152.5°	551.3	551.5	551.7	551.5	550.7	550.0	549.3	548.6
155°	564.3	564.6	564.9	564.6	563.8	563.0	562.2	561.4
157.5°	575.0	575.3	575.6	575.4	574.6	573.8	573.0	572.2
160°	581.7	582.1	582.5	582.3	581.5	580.7	579.9	579.1
162.5°	587.8	588.4	588.9	588.8	587.9	587.0	586.1	585.2
165°	595.7	596.3	596.9	596.8	596.0	595.1	594.3	593.5
167.5°	601.6	602.3	603.0	603.0	602.0	601.1	600.2	599.3
170°	604.6	605.5	606.3	606.2	605.3	604.4	603.5	602.6
172.5°	607.0	607.7	608.5	608.4	607.5	606.6	605.7	604.8
175°	609.6	610.4	611.2	611.2	610.3	609.4	608.5	607.6
177.5°	610.7	611.2	611.8	611.8	611.1	610.5	609.8	609.2
180°	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3

(END OF REPORT)