

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333436-830

Luminaire Tested: **S125DIW-S1090D770U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333436-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D770U830-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7124.5 lumens  
Efficiency: N/A  
Efficacy: 132.9 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55	51
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	69	63	58	61	56	52	53	49	46	45	43	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31
5	70	59	51	44	65	55	48	42	49	43	38	42	38	34	37	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9680	9680	9680	9680
5°	11210	9713	8504	9713
10°	13042	9663	7451	9663
15°	14437	9591	6873	9591
20°	16160	9479	6410	9479
25°	18932	9352	6183	9352
30°	20448	9228	5988	9228
35°	16812	8993	5858	8993
40°	11950	8667	5718	8667
45°	9180	8227	5636	8227
50°	7837	7683	5626	7683
55°	6977	7149	5674	7149
60°	6294	6566	5818	6566
65°	5813	5978	5969	5978
70°	5285	5370	6056	5370
75°	4666	4729	5999	4729
80°	3927	3857	5490	3857
85°	3105	2779	4431	2779



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.3	2.0
10°-20°	429.6	6.0
20°-30°	697.6	9.8
30°-40°	850.9	11.9
40°-50°	774.1	10.9
50°-60°	616.6	8.7
60°-70°	429.5	6.0
70°-80°	229.0	3.2
80°-90°	59.8	0.8
90°-100°	34.2	0.5
100°-110°	211.0	3.0
110°-120°	382.7	5.4
120°-130°	491.1	6.9
130°-140°	528.2	7.4
140°-150°	495.8	7.0
150°-160°	401.1	5.6
160°-170°	259.4	3.6
170°-180°	89.5	1.3
0°-30°	1271.5	17.8
0°-40°	2122.4	29.8
0°-60°	3513.1	49.3
0°-90°	4231.3	59.4
90°-120°	627.9	8.8
90°-150°	2143.1	30.1
90°-180°	2893.0	40.6
0°-180°	7124.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1499	1499	1499	1499	1499	
5°	1729	1498	1312	1498	1729	174
15°	2159	1434	1028	1434	2159	618
25°	2657	1312	868	1312	2657	1213
35°	2132	1141	743	1141	2132	1305
45°	1005	901	617	901	1005	804
55°	620	635	504	635	620	558
65°	380	391	391	391	380	378
75°	187	190	240	190	187	201
85°	42	38	60	38	42	49
90°	17	1	17	1	17	9
95°	15	40	15	40	15	12
105°	208	205	208	205	208	188
115°	383	386	383	386	383	380
125°	548	548	548	548	548	488
135°	681	684	681	684	681	525
145°	791	793	791	793	791	494
155°	867	873	867	873	867	399
165°	916	921	916	921	916	259
175°	938	942	938	942	938	89
180°	942	942	942	942	942	



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1585.4	1583.3	1581.3	1577.2	1580.3	1571.6	1567.5	1560.4	1551.7	1548.7	1545.1
5°	1729.1	1732.3	1735.5	1722.1	1723.3	1714.5	1694.1	1677.5	1664.2	1647.0	1634.9
7.5°	1902.1	1894.6	1894.0	1885.4	1870.5	1858.5	1837.1	1809.9	1783.6	1753.5	1728.7
10°	1988.7	1989.3	1983.6	1973.4	1957.5	1946.1	1918.1	1891.3	1858.9	1820.7	1793.4
12.5°	2053.8	2056.4	2049.3	2035.5	2027.7	2002.1	1980.2	1948.3	1909.8	1879.2	1837.7
15°	2159.2	2152.2	2147.1	2129.9	2116.6	2089.8	2054.8	2021.8	1979.7	1941.0	1902.1
17.5°	2260.7	2266.2	2256.7	2241.1	2199.6	2168.4	2121.5	2076.2	2023.9	1971.9	1925.5
20°	2351.3	2356.4	2341.7	2314.4	2264.7	2233.6	2171.9	2113.4	2053.0	1986.1	1935.2
22.5°	2464.3	2460.2	2440.4	2398.9	2355.9	2298.2	2231.5	2160.2	2084.4	2009.0	1941.4
25°	2656.7	2629.9	2617.8	2566.4	2509.7	2425.1	2333.5	2229.1	2135.0	2035.1	1948.6
27.5°	2763.3	2754.9	2741.4	2705.5	2646.0	2555.5	2447.5	2320.4	2187.5	2061.4	1948.2
30°	2741.9	2743.2	2744.4	2733.0	2694.8	2626.8	2519.2	2382.5	2224.7	2082.8	1951.7
32.5°	2552.6	2575.7	2597.8	2624.0	2634.8	2621.7	2554.4	2430.8	2268.4	2107.2	1949.7
35°	2132.4	2139.5	2211.3	2282.6	2379.3	2454.4	2504.6	2449.9	2313.1	2128.0	1947.3
37.5°	1662.7	1697.0	1746.8	1827.3	1966.9	2091.9	2252.6	2326.5	2282.4	2134.8	1942.9
40°	1417.4	1449.2	1481.7	1563.7	1681.4	1832.8	2015.3	2171.2	2207.5	2113.4	1927.6
42.5°	1228.0	1253.3	1289.3	1350.9	1449.3	1583.5	1757.8	1961.5	2086.9	2051.3	1895.5
45°	1005.1	1021.1	1049.0	1098.1	1169.3	1274.2	1428.2	1650.9	1844.9	1909.1	1819.5
47.5°	860.4	860.3	882.0	915.9	967.2	1056.4	1170.3	1344.7	1552.0	1705.3	1698.2
50°	780.0	776.7	793.9	823.2	863.9	923.1	1031.9	1171.2	1370.3	1544.0	1592.3
52.5°	710.8	711.1	721.7	743.3	777.4	827.9	909.2	1034.8	1204.9	1383.2	1474.2
55°	619.6	617.1	629.1	643.9	668.6	701.7	760.3	856.3	994.3	1169.9	1288.3
57.5°	536.1	543.2	548.0	558.2	578.8	601.0	650.3	720.8	830.3	981.0	1106.1
60°	487.3	494.3	498.1	508.3	524.8	543.9	582.1	639.3	731.6	861.4	985.4
62.5°	443.6	449.0	450.3	459.4	473.0	491.5	521.5	569.7	642.5	756.0	877.5
65°	380.4	380.4	383.0	392.5	398.9	415.4	438.3	473.3	531.9	620.3	724.0
67.5°	319.6	322.6	322.1	326.2	332.1	345.0	361.4	390.2	433.6	498.1	581.1
70°	279.9	282.5	281.8	285.0	291.3	299.6	313.0	340.4	371.6	426.9	498.1
72.5°	244.3	245.3	243.6	247.9	251.7	258.9	273.8	288.4	317.5	364.3	422.8
75°	187.0	188.3	189.5	192.1	196.0	199.7	207.4	222.1	241.1	276.1	313.7
77.5°	140.3	137.8	140.8	140.4	142.6	145.5	152.3	160.0	175.7	197.8	226.9
80°	105.6	106.2	106.2	106.9	110.1	112.0	117.7	123.4	135.5	152.0	172.4
82.5°	77.1	78.8	77.8	78.9	81.5	82.9	86.1	90.9	97.8	110.8	125.5
85°	41.9	38.8	40.1	41.4	41.4	41.9	44.5	46.5	50.2	55.3	61.1
87.5°	15.6	16.5	16.9	16.8	17.2	17.1	18.9	18.9	20.2	21.6	23.4
90°	16.8	16.3	15.8	15.4	14.9	14.2	13.5	12.7	12.0	11.2	10.1
92.5°	15.6	15.5	15.2	15.0	14.8	14.2	13.5	12.7	12.0	11.2	10.2
95°	14.7	14.7	14.7	14.7	14.7	14.2	13.5	12.7	12.0	11.2	17.1
97.5°	14.7	14.7	14.7	14.7	14.7	16.9	21.2	25.6	30.0	34.4	46.0
100°	14.7	15.3	15.9	16.5	17.2	29.0	52.1	75.3	98.4	121.5	120.9
102.5°	87.8	98.4	109.0	119.5	130.1	137.5	141.9	146.3	150.7	155.0	154.7
105°	207.5	207.5	207.7	207.9	208.0	208.1	208.1	208.1	208.1	208.1	208.1
107.5°	261.5	261.9	262.4	262.9	263.3	263.5	263.5	263.5	263.4	263.4	263.2
110°	298.9	298.8	298.6	298.4	298.3	298.4	298.9	299.4	299.8	300.3	300.0



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	332.4	332.6	332.9	333.1	333.3	333.7	334.3	334.9	335.5	336.1	335.9
115°	382.7	383.6	384.6	385.5	386.4	387.2	387.9	388.4	389.1	389.7	389.6
117.5°	436.4	436.8	437.2	437.5	438.0	438.6	439.4	440.2	441.0	441.8	441.2
120°	469.3	470.1	470.9	471.6	472.4	473.0	473.3	473.6	473.9	474.2	473.7
122.5°	500.6	501.5	502.4	503.3	504.2	504.8	505.1	505.4	505.8	506.1	505.9
125°	548.3	548.7	549.1	549.6	550.1	550.6	551.3	551.9	552.5	553.1	553.1
127.5°	588.3	589.5	590.6	591.7	593.0	593.7	594.0	594.4	594.7	595.0	595.1
130°	617.4	618.1	619.0	619.7	620.5	621.1	621.6	622.1	622.5	622.9	622.8
132.5°	644.2	645.0	645.7	646.5	647.3	647.7	647.8	647.9	648.0	648.1	648.5
135°	680.9	681.8	682.8	683.7	684.7	685.3	685.6	685.9	686.2	686.5	686.8
137.5°	717.8	718.6	719.4	720.2	721.0	721.4	721.3	721.3	721.2	721.1	721.4
140°	739.6	740.6	741.5	742.3	743.3	743.7	743.3	743.0	742.7	742.3	742.5
142.5°	760.3	761.2	762.1	763.1	764.0	764.4	764.4	764.3	764.2	764.2	763.9
145°	790.6	791.5	792.4	793.3	794.3	794.7	794.6	794.4	794.2	794.1	794.1
147.5°	815.6	816.7	817.8	819.0	820.0	820.5	820.3	820.1	819.9	819.7	819.5
150°	831.8	833.0	834.2	835.5	836.8	837.3	836.9	836.6	836.3	835.9	835.7
152.5°	846.9	848.0	849.1	850.2	851.3	851.8	851.4	851.1	850.8	850.5	850.2
155°	866.7	868.0	869.2	870.4	871.7	872.0	871.6	871.1	870.6	870.2	869.9
157.5°	883.4	884.6	885.8	887.0	888.3	888.6	888.2	887.7	887.2	886.6	886.6
160°	893.9	895.2	896.5	897.7	898.9	899.2	898.6	898.0	897.4	896.7	896.5
162.5°	903.4	904.8	906.2	907.6	908.9	909.2	908.2	907.4	906.5	905.7	905.5
165°	916.2	917.6	918.8	920.0	921.2	921.4	920.5	919.5	918.6	917.7	917.6
167.5°	925.2	926.6	928.0	929.4	930.9	930.9	929.8	928.7	927.6	926.5	926.3
170°	930.3	931.6	933.0	934.4	935.9	935.9	934.7	933.4	932.2	930.9	930.8
172.5°	933.6	935.0	936.4	937.8	939.1	939.3	938.2	937.1	935.9	934.9	934.6
175°	937.9	939.3	940.8	942.2	943.5	943.6	942.4	941.1	939.9	938.7	938.5
177.5°	940.5	941.4	942.4	943.4	944.4	944.5	943.6	942.7	941.9	941.0	940.8
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1542.1	1538.5	1534.5	1527.3	1518.6	1514.1	1506.9	1502.4	1493.2	1485.5	1477.4
5°	1620.3	1603.8	1588.6	1568.8	1547.2	1533.1	1516.6	1498.2	1479.1	1459.3	1437.8
7.5°	1701.4	1672.1	1640.3	1606.1	1572.6	1541.8	1512.4	1483.6	1456.6	1424.0	1396.4
10°	1755.9	1718.9	1679.5	1633.0	1587.9	1548.4	1508.4	1473.4	1437.8	1399.6	1365.8
12.5°	1810.2	1761.1	1705.4	1654.4	1600.1	1552.5	1505.3	1460.7	1415.9	1373.7	1334.3
15°	1848.7	1805.4	1753.9	1681.4	1620.3	1554.8	1492.4	1434.5	1380.4	1333.4	1283.8
17.5°	1874.1	1818.3	1762.9	1693.4	1613.4	1540.0	1469.4	1403.2	1342.2	1282.5	1234.6
20°	1878.6	1821.4	1763.5	1695.4	1613.4	1529.4	1458.8	1379.2	1313.7	1252.0	1193.4
22.5°	1877.1	1812.2	1749.2	1679.1	1599.1	1521.7	1436.3	1355.3	1284.2	1223.5	1162.4
25°	1862.7	1793.4	1714.5	1643.9	1565.0	1482.9	1396.4	1312.4	1239.9	1170.5	1110.1
27.5°	1850.8	1760.8	1671.5	1589.1	1513.0	1437.8	1354.9	1268.9	1188.5	1118.2	1061.3
30°	1836.0	1737.4	1636.8	1551.0	1472.7	1399.6	1321.4	1237.4	1153.4	1084.7	1023.6
32.5°	1822.8	1707.9	1601.8	1508.3	1425.4	1354.2	1282.1	1202.2	1119.7	1050.1	989.0
35°	1797.1	1664.2	1542.8	1437.1	1348.7	1275.5	1215.1	1140.7	1065.0	997.5	939.0
37.5°	1764.7	1606.9	1476.6	1365.8	1268.9	1191.8	1135.6	1078.5	1005.8	940.8	887.9
40°	1739.3	1566.2	1428.2	1314.9	1214.5	1134.3	1082.1	1028.0	967.6	907.2	851.2
42.5°	1707.2	1529.7	1379.3	1257.4	1157.9	1079.9	1025.1	979.2	925.9	869.5	817.6
45°	1648.3	1463.2	1300.3	1169.3	1068.7	991.7	935.2	900.8	860.7	807.3	763.4
47.5°	1561.7	1383.4	1214.9	1079.7	976.0	904.7	851.6	818.6	790.4	750.6	710.9
50°	1484.8	1323.9	1153.4	1019.2	915.5	843.6	794.6	764.7	740.5	709.9	676.3
52.5°	1398.8	1249.1	1092.8	960.1	857.4	786.6	738.6	712.3	692.1	670.2	637.1
55°	1262.2	1134.9	989.9	863.9	769.1	699.7	657.8	634.9	618.4	601.8	581.5
57.5°	1111.6	1012.1	883.6	768.5	681.2	618.1	578.9	556.7	543.8	535.3	523.3
60°	1005.8	920.6	809.8	704.8	619.6	563.6	525.5	508.3	497.5	490.5	481.5
62.5°	907.6	837.5	735.0	639.2	564.7	511.7	477.7	461.0	450.6	447.2	439.9
65°	762.8	708.7	624.1	544.6	481.0	435.7	407.2	391.2	384.8	381.1	381.7
67.5°	620.1	587.2	519.2	451.4	400.7	362.8	339.9	327.6	324.4	319.3	319.2
70°	533.1	508.3	451.0	391.9	346.7	317.4	297.1	284.4	281.2	278.6	278.1
72.5°	456.3	434.5	384.8	337.4	296.8	271.2	254.3	246.7	241.5	240.0	239.9
75°	342.9	330.8	291.3	253.8	225.8	208.0	196.6	189.5	185.8	185.1	185.8
77.5°	243.7	233.2	208.1	181.5	163.9	150.4	140.7	138.3	133.9	134.1	133.5
80°	183.2	176.3	160.3	139.3	124.7	113.2	108.1	103.7	102.5	100.5	102.5
82.5°	132.8	125.4	114.5	101.1	89.1	82.2	77.1	75.7	74.9	74.1	74.5
85°	65.5	66.2	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.3	36.9
87.5°	24.2	23.0	20.7	18.9	16.1	14.4	13.7	13.9	12.6	12.3	13.1
90°	9.0	7.9	6.8	5.7	4.4	3.2	2.0	0.7	2.0	3.2	4.4
92.5°	9.2	8.3	7.4	7.3	8.1	9.0	9.9	10.7	9.9	9.0	8.1
95°	23.0	28.8	34.8	38.0	38.5	38.8	39.3	39.8	39.3	38.8	38.5
97.5°	57.7	69.4	81.1	86.4	85.6	84.8	84.0	83.1	84.0	84.8	85.6
100°	120.3	119.7	119.0	118.5	118.0	117.5	117.1	116.6	117.1	117.5	118.0
102.5°	154.3	153.9	153.5	153.1	152.5	151.9	151.3	150.7	151.3	151.9	152.5
105°	208.1	208.1	208.1	207.8	207.2	206.6	205.9	205.3	205.9	206.6	207.2
107.5°	262.8	262.5	262.2	262.0	262.0	262.0	262.0	262.0	262.0	262.0	262.0
110°	299.7	299.4	299.1	298.9	298.9	298.9	298.9	298.9	298.9	298.9	298.9





TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	335.7	335.5	335.4	335.1	334.7	334.3	333.9	333.6	333.9	334.3	334.7
115°	389.4	389.3	389.1	388.6	387.9	387.1	386.3	385.5	386.3	387.1	387.9
117.5°	440.6	440.1	439.4	439.1	439.2	439.2	439.2	439.3	439.2	439.2	439.2
120°	473.3	472.8	472.3	472.2	472.3	472.5	472.7	472.8	472.7	472.5	472.3
122.5°	505.6	505.4	505.2	504.8	504.2	503.6	503.0	502.4	503.0	503.6	504.2
125°	553.1	553.1	553.1	552.6	551.5	550.4	549.3	548.3	549.3	550.4	551.5
127.5°	595.2	595.3	595.4	595.0	594.3	593.5	592.8	591.9	592.8	593.5	594.3
130°	622.6	622.5	622.4	621.9	621.1	620.3	619.5	618.8	619.5	620.3	621.1
132.5°	648.8	649.1	649.5	649.2	648.3	647.4	646.5	645.5	646.5	647.4	648.3
135°	687.1	687.5	687.8	687.5	686.5	685.6	684.7	683.7	684.7	685.6	686.5
137.5°	721.7	722.0	722.3	722.0	721.2	720.4	719.6	718.8	719.6	720.4	721.2
140°	742.7	742.8	743.0	742.9	742.6	742.3	742.0	741.7	742.0	742.3	742.6
142.5°	763.7	763.6	763.3	763.1	762.9	762.7	762.5	762.3	762.5	762.7	762.9
145°	794.1	794.1	794.1	793.9	793.6	793.3	793.0	792.7	793.0	793.3	793.6
147.5°	819.4	819.3	819.1	819.0	819.1	819.1	819.2	819.3	819.2	819.1	819.1
150°	835.4	835.0	834.7	834.7	835.0	835.4	835.7	835.9	835.7	835.4	835.0
152.5°	849.9	849.6	849.2	849.4	850.2	850.8	851.5	852.2	851.5	850.8	850.2
155°	869.6	869.3	868.9	869.3	870.2	871.1	872.0	873.0	872.0	871.1	870.2
157.5°	886.6	886.6	886.6	886.8	887.4	888.0	888.5	889.0	888.5	888.0	887.4
160°	896.5	896.3	896.1	896.5	897.4	898.3	899.3	900.2	899.3	898.3	897.4
162.5°	905.4	905.2	905.0	905.4	906.3	907.3	908.2	909.2	908.2	907.3	906.3
165°	917.4	917.2	917.1	917.5	918.4	919.4	920.2	921.1	920.2	919.4	918.4
167.5°	926.1	926.0	925.9	926.2	927.3	928.2	929.2	930.1	929.2	928.2	927.3
170°	930.7	930.5	930.3	930.8	931.9	932.9	934.1	935.2	934.1	932.9	931.9
172.5°	934.3	934.1	933.8	934.2	935.2	936.3	937.5	938.5	937.5	936.3	935.2
175°	938.3	938.2	938.0	938.4	939.3	940.3	941.2	942.2	941.2	940.3	939.3
177.5°	940.8	940.7	940.5	940.8	941.6	942.4	943.0	943.8	943.0	942.4	941.6
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1472.8	1467.3	1462.6	1452.5	1446.9	1439.3	1433.1	1439.7	1432.7	1435.7	1431.2
5°	1426.9	1409.1	1396.4	1377.9	1362.1	1347.4	1336.6	1334.6	1329.6	1327.0	1319.4
7.5°	1371.7	1349.4	1327.6	1303.3	1283.0	1262.3	1249.1	1238.1	1230.9	1221.3	1214.8
10°	1339.2	1309.2	1283.8	1254.5	1229.1	1206.8	1189.0	1180.1	1171.9	1159.7	1155.3
12.5°	1298.9	1268.0	1237.0	1205.7	1181.2	1156.4	1141.1	1127.7	1121.9	1108.3	1106.9
15°	1250.8	1204.3	1173.7	1141.9	1108.2	1087.9	1075.2	1060.5	1054.1	1044.6	1037.6
17.5°	1193.2	1151.7	1113.5	1080.6	1051.7	1034.5	1018.8	1008.7	997.8	991.6	980.1
20°	1151.5	1112.0	1073.8	1038.9	1016.6	996.8	984.1	974.6	963.2	960.0	948.6
22.5°	1116.3	1072.8	1036.2	1006.8	982.5	960.3	946.5	940.0	932.1	922.3	920.0
25°	1059.2	1014.1	982.9	953.7	932.0	911.6	902.1	893.8	886.2	879.2	876.7
27.5°	1009.8	969.5	932.5	906.1	887.2	868.6	860.3	850.2	844.6	839.0	832.1
30°	975.2	933.9	901.4	876.0	855.6	839.1	830.2	823.2	818.1	813.0	809.2
32.5°	939.6	901.4	869.9	845.0	824.6	812.1	804.3	799.3	793.7	787.6	782.8
35°	892.6	850.6	820.0	798.4	782.5	773.0	764.0	759.6	753.2	753.2	748.1
37.5°	839.5	803.2	776.3	756.6	742.3	733.8	724.1	721.0	717.0	714.3	712.5
40°	807.9	774.2	748.8	729.1	713.8	706.8	699.2	694.1	691.5	688.3	687.0
42.5°	775.3	743.2	718.8	700.6	687.3	681.4	674.2	670.6	665.5	661.4	660.6
45°	725.9	694.7	672.4	657.8	646.3	639.3	634.9	627.3	624.7	619.6	619.0
47.5°	678.9	649.0	627.2	615.2	605.1	599.4	592.4	584.8	581.8	579.3	579.0
50°	643.9	616.4	596.1	584.7	575.1	566.8	559.9	554.8	552.8	552.8	554.1
52.5°	608.2	584.8	567.6	553.6	544.6	535.7	529.3	526.2	523.3	526.4	528.7
55°	556.0	532.4	519.7	506.4	497.5	487.3	484.1	482.9	481.0	486.1	488.6
57.5°	500.8	484.3	469.4	456.1	448.1	442.2	437.9	437.2	440.7	443.2	451.4
60°	465.7	446.6	433.2	423.0	413.5	409.7	408.4	407.2	409.7	416.7	427.5
62.5°	427.0	411.5	397.1	389.5	382.5	376.1	375.9	376.6	381.7	389.7	400.5
65°	370.2	356.8	347.3	338.5	332.7	328.9	330.2	332.7	338.5	349.2	361.4
67.5°	312.6	303.5	294.9	287.7	282.2	282.2	283.5	287.3	294.1	306.5	317.5
70°	275.5	265.3	258.3	255.1	250.6	248.1	251.9	258.3	264.0	275.5	285.0
72.5°	238.3	229.7	224.2	222.1	220.1	218.1	219.3	226.2	233.9	245.4	256.5
75°	183.2	180.0	176.3	173.7	171.7	173.1	174.3	180.7	187.0	199.2	211.9
77.5°	133.7	130.4	128.1	127.5	126.5	127.1	130.6	135.3	141.6	150.4	160.0
80°	101.1	99.9	98.6	97.9	97.9	98.6	103.7	106.9	112.6	120.8	128.5
82.5°	73.7	72.9	72.7	72.5	73.0	73.1	76.3	80.4	85.1	91.3	97.9
85°	38.8	37.5	39.4	40.1	38.8	40.7	41.9	44.5	46.5	49.6	52.8
87.5°	13.9	15.1	14.8	15.6	15.7	17.0	16.7	18.9	20.0	21.2	20.8
90°	5.7	6.8	7.9	9.0	10.1	11.2	12.0	12.7	13.5	14.2	14.9
92.5°	7.3	7.4	8.3	9.2	10.2	11.2	12.0	12.7	13.5	14.2	14.8
95°	38.0	34.8	28.8	23.0	17.1	11.2	12.0	12.7	13.5	14.2	14.7
97.5°	86.4	81.1	69.4	57.7	46.0	34.4	30.0	25.6	21.2	16.9	14.7
100°	118.5	119.0	119.7	120.3	120.9	121.5	98.4	75.3	52.1	29.0	17.2
102.5°	153.1	153.5	153.9	154.3	154.7	155.0	150.7	146.3	141.9	137.5	130.1
105°	207.8	208.1	208.1	208.1	208.1	208.1	208.1	208.1	208.1	208.1	208.0
107.5°	262.0	262.2	262.5	262.8	263.2	263.4	263.4	263.5	263.5	263.5	263.3
110°	298.9	299.1	299.4	299.7	300.0	300.3	299.8	299.4	298.9	298.4	298.3



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	335.1	335.4	335.5	335.7	335.9	336.1	335.5	334.9	334.3	333.7	333.3
115°	388.6	389.1	389.3	389.4	389.6	389.7	389.1	388.4	387.9	387.2	386.4
117.5°	439.1	439.4	440.1	440.6	441.2	441.8	441.0	440.2	439.4	438.6	438.0
120°	472.2	472.3	472.8	473.3	473.7	474.2	473.9	473.6	473.3	473.0	472.4
122.5°	504.8	505.2	505.4	505.6	505.9	506.1	505.8	505.4	505.1	504.8	504.2
125°	552.6	553.1	553.1	553.1	553.1	553.1	552.5	551.9	551.3	550.6	550.1
127.5°	595.0	595.4	595.3	595.2	595.1	595.0	594.7	594.4	594.0	593.7	593.0
130°	621.9	622.4	622.5	622.6	622.8	622.9	622.5	622.1	621.6	621.1	620.5
132.5°	649.2	649.5	649.1	648.8	648.5	648.1	648.0	647.9	647.8	647.7	647.3
135°	687.5	687.8	687.5	687.1	686.8	686.5	686.2	685.9	685.6	685.3	684.7
137.5°	722.0	722.3	722.0	721.7	721.4	721.1	721.2	721.3	721.3	721.4	721.0
140°	742.9	743.0	742.8	742.7	742.5	742.3	742.7	743.0	743.3	743.7	743.3
142.5°	763.1	763.3	763.6	763.7	763.9	764.2	764.2	764.3	764.4	764.4	764.0
145°	793.9	794.1	794.1	794.1	794.1	794.1	794.2	794.4	794.6	794.7	794.3
147.5°	819.0	819.1	819.3	819.4	819.5	819.7	819.9	820.1	820.3	820.5	820.0
150°	834.7	834.7	835.0	835.4	835.7	835.9	836.3	836.6	836.9	837.3	836.8
152.5°	849.4	849.2	849.6	849.9	850.2	850.5	850.8	851.1	851.4	851.8	851.3
155°	869.3	868.9	869.3	869.6	869.9	870.2	870.6	871.1	871.6	872.0	871.7
157.5°	886.8	886.6	886.6	886.6	886.6	886.6	887.2	887.7	888.2	888.6	888.3
160°	896.5	896.1	896.3	896.5	896.5	896.7	897.4	898.0	898.6	899.2	898.9
162.5°	905.4	905.0	905.2	905.4	905.5	905.7	906.5	907.4	908.2	909.2	908.9
165°	917.5	917.1	917.2	917.4	917.6	917.7	918.6	919.5	920.5	921.4	921.2
167.5°	926.2	925.9	926.0	926.1	926.3	926.5	927.6	928.7	929.8	930.9	930.9
170°	930.8	930.3	930.5	930.7	930.8	930.9	932.2	933.4	934.7	935.9	935.9
172.5°	934.2	933.8	934.1	934.3	934.6	934.9	935.9	937.1	938.2	939.3	939.1
175°	938.4	938.0	938.2	938.3	938.5	938.7	939.9	941.1	942.4	943.6	943.5
177.5°	940.8	940.5	940.7	940.8	940.8	941.0	941.9	942.7	943.6	944.5	944.4
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1428.0	1431.6	1428.6	1432.7	1428.6	1431.6	1428.0	1431.2	1435.7	1432.7	1439.7
5°	1316.3	1310.5	1314.3	1311.7	1314.3	1310.5	1316.3	1319.4	1327.0	1329.6	1334.6
7.5°	1213.0	1207.5	1201.2	1198.3	1201.2	1207.5	1213.0	1214.8	1221.3	1230.9	1238.1
10°	1148.3	1141.3	1140.7	1136.2	1140.7	1141.3	1148.3	1155.3	1159.7	1171.9	1180.1
12.5°	1101.0	1094.5	1087.2	1085.3	1087.2	1094.5	1101.0	1106.9	1108.3	1121.9	1127.7
15°	1033.8	1028.7	1024.3	1028.0	1024.3	1028.7	1033.8	1037.6	1044.6	1054.1	1060.5
17.5°	977.9	973.7	973.0	968.3	973.0	973.7	977.9	980.1	991.6	997.8	1008.7
20°	942.8	939.6	940.9	932.6	940.9	939.6	942.8	948.6	960.0	963.2	974.6
22.5°	914.8	908.6	907.9	906.2	907.9	908.6	914.8	920.0	922.3	932.1	940.0
25°	870.9	867.7	864.6	867.7	864.6	867.7	870.9	876.7	879.2	886.2	893.8
27.5°	832.6	828.8	827.9	828.3	827.9	828.8	832.6	832.1	839.0	844.6	850.2
30°	809.2	802.9	803.5	802.9	803.5	802.9	809.2	809.2	813.0	818.1	823.2
32.5°	783.7	779.4	778.5	777.4	778.5	779.4	783.7	782.8	787.6	793.7	799.3
35°	746.2	746.2	743.0	743.0	743.0	746.2	746.2	748.1	753.2	753.2	759.6
37.5°	711.0	710.3	708.4	708.7	708.4	710.3	711.0	712.5	714.3	717.0	721.0
40°	684.5	683.9	681.9	678.2	681.9	683.9	684.5	687.0	688.3	691.5	694.1
42.5°	659.0	657.0	656.0	654.8	656.0	657.0	659.0	660.6	661.4	665.5	670.6
45°	619.0	619.0	617.7	617.1	617.7	619.0	619.0	619.0	619.6	624.7	627.3
47.5°	580.0	581.2	583.6	583.2	583.6	581.2	580.0	579.0	579.3	581.8	584.8
50°	556.7	557.3	559.2	559.9	559.2	557.3	556.7	554.1	552.8	552.8	554.8
52.5°	530.7	534.4	536.8	536.4	536.8	534.4	530.7	528.7	526.4	523.3	526.2
55°	494.3	498.8	503.2	503.9	503.2	498.8	494.3	488.6	486.1	481.0	482.9
57.5°	458.3	464.5	469.2	470.8	469.2	464.5	458.3	451.4	443.2	440.7	437.2
60°	433.9	442.1	447.9	450.4	447.9	442.1	433.9	427.5	416.7	409.7	407.2
62.5°	410.5	419.7	425.5	425.9	425.5	419.7	410.5	400.5	389.7	381.7	376.6
65°	372.1	381.7	386.8	390.6	386.8	381.7	372.1	361.4	349.2	338.5	332.7
67.5°	330.9	340.4	346.1	349.1	346.1	340.4	330.9	317.5	306.5	294.1	287.3
70°	301.0	310.5	318.1	320.7	318.1	310.5	301.0	285.0	275.5	264.0	258.3
72.5°	271.4	279.9	286.1	289.1	286.1	279.9	271.4	256.5	245.4	233.9	226.2
75°	220.1	231.6	237.3	240.4	237.3	231.6	220.1	211.9	199.2	187.0	180.7
77.5°	169.8	180.1	183.6	185.2	183.6	180.1	169.8	160.0	150.4	141.6	135.3
80°	136.1	142.5	146.9	147.6	146.9	142.5	136.1	128.5	120.8	112.6	106.9
82.5°	104.6	109.9	111.3	113.0	111.3	109.9	104.6	97.9	91.3	85.1	80.4
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.8	49.6	46.5	44.5
87.5°	21.9	21.5	21.6	22.7	21.6	21.5	21.9	20.8	21.2	20.0	18.9
90°	15.4	15.8	16.3	16.8	16.3	15.8	15.4	14.9	14.2	13.5	12.7
92.5°	15.0	15.2	15.5	15.6	15.5	15.2	15.0	14.8	14.2	13.5	12.7
95°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.2	13.5	12.7
97.5°	14.7	14.7	14.7	14.7	14.7	14.7	14.7	14.7	16.9	21.2	25.6
100°	16.5	15.9	15.3	14.7	15.3	15.9	16.5	17.2	29.0	52.1	75.3
102.5°	119.5	109.0	98.4	87.8	98.4	109.0	119.5	130.1	137.5	141.9	146.3
105°	207.9	207.7	207.5	207.5	207.5	207.7	207.9	208.0	208.1	208.1	208.1
107.5°	262.9	262.4	261.9	261.5	261.9	262.4	262.9	263.3	263.5	263.5	263.5
110°	298.4	298.6	298.8	298.9	298.8	298.6	298.4	298.3	298.4	298.9	299.4



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	333.1	332.9	332.6	332.4	332.6	332.9	333.1	333.3	333.7	334.3	334.9
115°	385.5	384.6	383.6	382.7	383.6	384.6	385.5	386.4	387.2	387.9	388.4
117.5°	437.5	437.2	436.8	436.4	436.8	437.2	437.5	438.0	438.6	439.4	440.2
120°	471.6	470.9	470.1	469.3	470.1	470.9	471.6	472.4	473.0	473.3	473.6
122.5°	503.3	502.4	501.5	500.6	501.5	502.4	503.3	504.2	504.8	505.1	505.4
125°	549.6	549.1	548.7	548.3	548.7	549.1	549.6	550.1	550.6	551.3	551.9
127.5°	591.7	590.6	589.5	588.3	589.5	590.6	591.7	593.0	593.7	594.0	594.4
130°	619.7	619.0	618.1	617.4	618.1	619.0	619.7	620.5	621.1	621.6	622.1
132.5°	646.5	645.7	645.0	644.2	645.0	645.7	646.5	647.3	647.7	647.8	647.9
135°	683.7	682.8	681.8	680.9	681.8	682.8	683.7	684.7	685.3	685.6	685.9
137.5°	720.2	719.4	718.6	717.8	718.6	719.4	720.2	721.0	721.4	721.3	721.3
140°	742.3	741.5	740.6	739.6	740.6	741.5	742.3	743.3	743.7	743.3	743.0
142.5°	763.1	762.1	761.2	760.3	761.2	762.1	763.1	764.0	764.4	764.4	764.3
145°	793.3	792.4	791.5	790.6	791.5	792.4	793.3	794.3	794.7	794.6	794.4
147.5°	819.0	817.8	816.7	815.6	816.7	817.8	819.0	820.0	820.5	820.3	820.1
150°	835.5	834.2	833.0	831.8	833.0	834.2	835.5	836.8	837.3	836.9	836.6
152.5°	850.2	849.1	848.0	846.9	848.0	849.1	850.2	851.3	851.8	851.4	851.1
155°	870.4	869.2	868.0	866.7	868.0	869.2	870.4	871.7	872.0	871.6	871.1
157.5°	887.0	885.8	884.6	883.4	884.6	885.8	887.0	888.3	888.6	888.2	887.7
160°	897.7	896.5	895.2	893.9	895.2	896.5	897.7	898.9	899.2	898.6	898.0
162.5°	907.6	906.2	904.8	903.4	904.8	906.2	907.6	908.9	909.2	908.2	907.4
165°	920.0	918.8	917.6	916.2	917.6	918.8	920.0	921.2	921.4	920.5	919.5
167.5°	929.4	928.0	926.6	925.2	926.6	928.0	929.4	930.9	930.9	929.8	928.7
170°	934.4	933.0	931.6	930.3	931.6	933.0	934.4	935.9	935.9	934.7	933.4
172.5°	937.8	936.4	935.0	933.6	935.0	936.4	937.8	939.1	939.3	938.2	937.1
175°	942.2	940.8	939.3	937.9	939.3	940.8	942.2	943.5	943.6	942.4	941.1
177.5°	943.4	942.4	941.4	940.5	941.4	942.4	943.4	944.4	944.5	943.6	942.7
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1433.1	1439.3	1446.9	1452.5	1462.6	1467.3	1472.8	1477.4	1485.5	1493.2	1502.4
5°	1336.6	1347.4	1362.1	1377.9	1396.4	1409.1	1426.9	1437.8	1459.3	1479.1	1498.2
7.5°	1249.1	1262.3	1283.0	1303.3	1327.6	1349.4	1371.7	1396.4	1424.0	1456.6	1483.6
10°	1189.0	1206.8	1229.1	1254.5	1283.8	1309.2	1339.2	1365.8	1399.6	1437.8	1473.4
12.5°	1141.1	1156.4	1181.2	1205.7	1237.0	1268.0	1298.9	1334.3	1373.7	1415.9	1460.7
15°	1075.2	1087.9	1108.2	1141.9	1173.7	1204.3	1250.8	1283.8	1333.4	1380.4	1434.5
17.5°	1018.8	1034.5	1051.7	1080.6	1113.5	1151.7	1193.2	1234.6	1282.5	1342.2	1403.2
20°	984.1	996.8	1016.6	1038.9	1073.8	1112.0	1151.5	1193.4	1252.0	1313.7	1379.2
22.5°	946.5	960.3	982.5	1006.8	1036.2	1072.8	1116.3	1162.4	1223.5	1284.2	1355.3
25°	902.1	911.6	932.0	953.7	982.9	1014.1	1059.2	1110.1	1170.5	1239.9	1312.4
27.5°	860.3	868.6	887.2	906.1	932.5	969.5	1009.8	1061.3	1118.2	1188.5	1268.9
30°	830.2	839.1	855.6	876.0	901.4	933.9	975.2	1023.6	1084.7	1153.4	1237.4
32.5°	804.3	812.1	824.6	845.0	869.9	901.4	939.6	989.0	1050.1	1119.7	1202.2
35°	764.0	773.0	782.5	798.4	820.0	850.6	892.6	939.0	997.5	1065.0	1140.7
37.5°	724.1	733.8	742.3	756.6	776.3	803.2	839.5	887.9	940.8	1005.8	1078.5
40°	699.2	706.8	713.8	729.1	748.8	774.2	807.9	851.2	907.2	967.6	1028.0
42.5°	674.2	681.4	687.3	700.6	718.8	743.2	775.3	817.6	869.5	925.9	979.2
45°	634.9	639.3	646.3	657.8	672.4	694.7	725.9	763.4	807.3	860.7	900.8
47.5°	592.4	599.4	605.1	615.2	627.2	649.0	678.9	710.9	750.6	790.4	818.6
50°	559.9	566.8	575.1	584.7	596.1	616.4	643.9	676.3	709.9	740.5	764.7
52.5°	529.3	535.7	544.6	553.6	567.6	584.8	608.2	637.1	670.2	692.1	712.3
55°	484.1	487.3	497.5	506.4	519.7	532.4	556.0	581.5	601.8	618.4	634.9
57.5°	437.9	442.2	448.1	456.1	469.4	484.3	500.8	523.3	535.3	543.8	556.7
60°	408.4	409.7	413.5	423.0	433.2	446.6	465.7	481.5	490.5	497.5	508.3
62.5°	375.9	376.1	382.5	389.5	397.1	411.5	427.0	439.9	447.2	450.6	461.0
65°	330.2	328.9	332.7	338.5	347.3	356.8	370.2	381.7	381.1	384.8	391.2
67.5°	283.5	282.2	282.2	287.7	294.9	303.5	312.6	319.2	319.3	324.4	327.6
70°	251.9	248.1	250.6	255.1	258.3	265.3	275.5	278.1	278.6	281.2	284.4
72.5°	219.3	218.1	220.1	222.1	224.2	229.7	238.3	239.9	240.0	241.5	246.7
75°	174.3	173.1	171.7	173.7	176.3	180.0	183.2	185.8	185.1	185.8	189.5
77.5°	130.6	127.1	126.5	127.5	128.1	130.4	133.7	133.5	134.1	133.9	138.3
80°	103.7	98.6	97.9	97.9	98.6	99.9	101.1	102.5	100.5	102.5	103.7
82.5°	76.3	73.1	73.0	72.5	72.7	72.9	73.7	74.5	74.1	74.9	75.7
85°	41.9	40.7	38.8	40.1	39.4	37.5	38.8	36.9	36.3	36.9	37.5
87.5°	16.7	17.0	15.7	15.6	14.8	15.1	13.9	13.1	12.3	12.6	13.9
90°	12.0	11.2	10.1	9.0	7.9	6.8	5.7	4.4	3.2	2.0	0.7
92.5°	12.0	11.2	10.2	9.2	8.3	7.4	7.3	8.1	9.0	9.9	10.7
95°	12.0	11.2	17.1	23.0	28.8	34.8	38.0	38.5	38.8	39.3	39.8
97.5°	30.0	34.4	46.0	57.7	69.4	81.1	86.4	85.6	84.8	84.0	83.1
100°	98.4	121.5	120.9	120.3	119.7	119.0	118.5	118.0	117.5	117.1	116.6
102.5°	150.7	155.0	154.7	154.3	153.9	153.5	153.1	152.5	151.9	151.3	150.7
105°	208.1	208.1	208.1	208.1	208.1	208.1	207.8	207.2	206.6	205.9	205.3
107.5°	263.4	263.4	263.2	262.8	262.5	262.2	262.0	262.0	262.0	262.0	262.0
110°	299.8	300.3	300.0	299.7	299.4	299.1	298.9	298.9	298.9	298.9	298.9



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	335.5	336.1	335.9	335.7	335.5	335.4	335.1	334.7	334.3	333.9	333.6
115°	389.1	389.7	389.6	389.4	389.3	389.1	388.6	387.9	387.1	386.3	385.5
117.5°	441.0	441.8	441.2	440.6	440.1	439.4	439.1	439.2	439.2	439.2	439.3
120°	473.9	474.2	473.7	473.3	472.8	472.3	472.2	472.3	472.5	472.7	472.8
122.5°	505.8	506.1	505.9	505.6	505.4	505.2	504.8	504.2	503.6	503.0	502.4
125°	552.5	553.1	553.1	553.1	553.1	553.1	552.6	551.5	550.4	549.3	548.3
127.5°	594.7	595.0	595.1	595.2	595.3	595.4	595.0	594.3	593.5	592.8	591.9
130°	622.5	622.9	622.8	622.6	622.5	622.4	621.9	621.1	620.3	619.5	618.8
132.5°	648.0	648.1	648.5	648.8	649.1	649.5	649.2	648.3	647.4	646.5	645.5
135°	686.2	686.5	686.8	687.1	687.5	687.8	687.5	686.5	685.6	684.7	683.7
137.5°	721.2	721.1	721.4	721.7	722.0	722.3	722.0	721.2	720.4	719.6	718.8
140°	742.7	742.3	742.5	742.7	742.8	743.0	742.9	742.6	742.3	742.0	741.7
142.5°	764.2	764.2	763.9	763.7	763.6	763.3	763.1	762.9	762.7	762.5	762.3
145°	794.2	794.1	794.1	794.1	794.1	794.1	793.9	793.6	793.3	793.0	792.7
147.5°	819.9	819.7	819.5	819.4	819.3	819.1	819.0	819.1	819.1	819.2	819.3
150°	836.3	835.9	835.7	835.4	835.0	834.7	834.7	835.0	835.4	835.7	835.9
152.5°	850.8	850.5	850.2	849.9	849.6	849.2	849.4	850.2	850.8	851.5	852.2
155°	870.6	870.2	869.9	869.6	869.3	868.9	869.3	870.2	871.1	872.0	873.0
157.5°	887.2	886.6	886.6	886.6	886.6	886.6	886.8	887.4	888.0	888.5	889.0
160°	897.4	896.7	896.5	896.5	896.3	896.1	896.5	897.4	898.3	899.3	900.2
162.5°	906.5	905.7	905.5	905.4	905.2	905.0	905.4	906.3	907.3	908.2	909.2
165°	918.6	917.7	917.6	917.4	917.2	917.1	917.5	918.4	919.4	920.2	921.1
167.5°	927.6	926.5	926.3	926.1	926.0	925.9	926.2	927.3	928.2	929.2	930.1
170°	932.2	930.9	930.8	930.7	930.5	930.3	930.8	931.9	932.9	934.1	935.2
172.5°	935.9	934.9	934.6	934.3	934.1	933.8	934.2	935.2	936.3	937.5	938.5
175°	939.9	938.7	938.5	938.3	938.2	938.0	938.4	939.3	940.3	941.2	942.2
177.5°	941.9	941.0	940.8	940.8	940.7	940.5	940.8	941.6	942.4	943.0	943.8
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1506.9	1514.1	1518.6	1527.3	1534.5	1538.5	1542.1	1545.1	1548.7	1551.7	1560.4
5°	1516.6	1533.1	1547.2	1568.8	1588.6	1603.8	1620.3	1634.9	1647.0	1664.2	1677.5
7.5°	1512.4	1541.8	1572.6	1606.1	1640.3	1672.1	1701.4	1728.7	1753.5	1783.6	1809.9
10°	1508.4	1548.4	1587.9	1633.0	1679.5	1718.9	1755.9	1793.4	1820.7	1858.9	1891.3
12.5°	1505.3	1552.5	1600.1	1654.4	1705.4	1761.1	1810.2	1837.7	1879.2	1909.8	1948.3
15°	1492.4	1554.8	1620.3	1681.4	1753.9	1805.4	1848.7	1902.1	1941.0	1979.7	2021.8
17.5°	1469.4	1540.0	1613.4	1693.4	1762.9	1818.3	1874.1	1925.5	1971.9	2023.9	2076.2
20°	1458.8	1529.4	1613.4	1695.4	1763.5	1821.4	1878.6	1935.2	1986.1	2053.0	2113.4
22.5°	1436.3	1521.7	1599.1	1679.1	1749.2	1812.2	1877.1	1941.4	2009.0	2084.4	2160.2
25°	1396.4	1482.9	1565.0	1643.9	1714.5	1793.4	1862.7	1948.6	2035.1	2135.0	2229.1
27.5°	1354.9	1437.8	1513.0	1589.1	1671.5	1760.8	1850.8	1948.2	2061.4	2187.5	2320.4
30°	1321.4	1399.6	1472.7	1551.0	1636.8	1737.4	1836.0	1951.7	2082.8	2224.7	2382.5
32.5°	1282.1	1354.2	1425.4	1508.3	1601.8	1707.9	1822.8	1949.7	2107.2	2268.4	2430.8
35°	1215.1	1275.5	1348.7	1437.1	1542.8	1664.2	1797.1	1947.3	2128.0	2313.1	2449.9
37.5°	1135.6	1191.8	1268.9	1365.8	1476.6	1606.9	1764.7	1942.9	2134.8	2282.4	2326.5
40°	1082.1	1134.3	1214.5	1314.9	1428.2	1566.2	1739.3	1927.6	2113.4	2207.5	2171.2
42.5°	1025.1	1079.9	1157.9	1257.4	1379.3	1529.7	1707.2	1895.5	2051.3	2086.9	1961.5
45°	935.2	991.7	1068.7	1169.3	1300.3	1463.2	1648.3	1819.5	1909.1	1844.9	1650.9
47.5°	851.6	904.7	976.0	1079.7	1214.9	1383.4	1561.7	1698.2	1705.3	1552.0	1344.7
50°	794.6	843.6	915.5	1019.2	1153.4	1323.9	1484.8	1592.3	1544.0	1370.3	1171.2
52.5°	738.6	786.6	857.4	960.1	1092.8	1249.1	1398.8	1474.2	1383.2	1204.9	1034.8
55°	657.8	699.7	769.1	863.9	989.9	1134.9	1262.2	1288.3	1169.9	994.3	856.3
57.5°	578.9	618.1	681.2	768.5	883.6	1012.1	1111.6	1106.1	981.0	830.3	720.8
60°	525.5	563.6	619.6	704.8	809.8	920.6	1005.8	985.4	861.4	731.6	639.3
62.5°	477.7	511.7	564.7	639.2	735.0	837.5	907.6	877.5	756.0	642.5	569.7
65°	407.2	435.7	481.0	544.6	624.1	708.7	762.8	724.0	620.3	531.9	473.3
67.5°	339.9	362.8	400.7	451.4	519.2	587.2	620.1	581.1	498.1	433.6	390.2
70°	297.1	317.4	346.7	391.9	451.0	508.3	533.1	498.1	426.9	371.6	340.4
72.5°	254.3	271.2	296.8	337.4	384.8	434.5	456.3	422.8	364.3	317.5	288.4
75°	196.6	208.0	225.8	253.8	291.3	330.8	342.9	313.7	276.1	241.1	222.1
77.5°	140.7	150.4	163.9	181.5	208.1	233.2	243.7	226.9	197.8	175.7	160.0
80°	108.1	113.2	124.7	139.3	160.3	176.3	183.2	172.4	152.0	135.5	123.4
82.5°	77.1	82.2	89.1	101.1	114.5	125.4	132.8	125.5	110.8	97.8	90.9
85°	37.5	40.7	44.5	49.6	59.8	66.2	65.5	61.1	55.3	50.2	46.5
87.5°	13.7	14.4	16.1	18.9	20.7	23.0	24.2	23.4	21.6	20.2	18.9
90°	2.0	3.2	4.4	5.7	6.8	7.9	9.0	10.1	11.2	12.0	12.7
92.5°	9.9	9.0	8.1	7.3	7.4	8.3	9.2	10.2	11.2	12.0	12.7
95°	39.3	38.8	38.5	38.0	34.8	28.8	23.0	17.1	11.2	12.0	12.7
97.5°	84.0	84.8	85.6	86.4	81.1	69.4	57.7	46.0	34.4	30.0	25.6
100°	117.1	117.5	118.0	118.5	119.0	119.7	120.3	120.9	121.5	98.4	75.3
102.5°	151.3	151.9	152.5	153.1	153.5	153.9	154.3	154.7	155.0	150.7	146.3
105°	205.9	206.6	207.2	207.8	208.1	208.1	208.1	208.1	208.1	208.1	208.1
107.5°	262.0	262.0	262.0	262.0	262.2	262.5	262.8	263.2	263.4	263.4	263.5
110°	298.9	298.9	298.9	298.9	299.1	299.4	299.7	300.0	300.3	299.8	299.4





TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	333.9	334.3	334.7	335.1	335.4	335.5	335.7	335.9	336.1	335.5	334.9
115°	386.3	387.1	387.9	388.6	389.1	389.3	389.4	389.6	389.7	389.1	388.4
117.5°	439.2	439.2	439.2	439.1	439.4	440.1	440.6	441.2	441.8	441.0	440.2
120°	472.7	472.5	472.3	472.2	472.3	472.8	473.3	473.7	474.2	473.9	473.6
122.5°	503.0	503.6	504.2	504.8	505.2	505.4	505.6	505.9	506.1	505.8	505.4
125°	549.3	550.4	551.5	552.6	553.1	553.1	553.1	553.1	553.1	552.5	551.9
127.5°	592.8	593.5	594.3	595.0	595.4	595.3	595.2	595.1	595.0	594.7	594.4
130°	619.5	620.3	621.1	621.9	622.4	622.5	622.6	622.8	622.9	622.5	622.1
132.5°	646.5	647.4	648.3	649.2	649.5	649.1	648.8	648.5	648.1	648.0	647.9
135°	684.7	685.6	686.5	687.5	687.8	687.5	687.1	686.8	686.5	686.2	685.9
137.5°	719.6	720.4	721.2	722.0	722.3	722.0	721.7	721.4	721.1	721.2	721.3
140°	742.0	742.3	742.6	742.9	743.0	742.8	742.7	742.5	742.3	742.7	743.0
142.5°	762.5	762.7	762.9	763.1	763.3	763.6	763.7	763.9	764.2	764.2	764.3
145°	793.0	793.3	793.6	793.9	794.1	794.1	794.1	794.1	794.1	794.2	794.4
147.5°	819.2	819.1	819.1	819.0	819.1	819.3	819.4	819.5	819.7	819.9	820.1
150°	835.7	835.4	835.0	834.7	834.7	835.0	835.4	835.7	835.9	836.3	836.6
152.5°	851.5	850.8	850.2	849.4	849.2	849.6	849.9	850.2	850.5	850.8	851.1
155°	872.0	871.1	870.2	869.3	868.9	869.3	869.6	869.9	870.2	870.6	871.1
157.5°	888.5	888.0	887.4	886.8	886.6	886.6	886.6	886.6	886.6	887.2	887.7
160°	899.3	898.3	897.4	896.5	896.1	896.3	896.5	896.5	896.7	897.4	898.0
162.5°	908.2	907.3	906.3	905.4	905.0	905.2	905.4	905.5	905.7	906.5	907.4
165°	920.2	919.4	918.4	917.5	917.1	917.2	917.4	917.6	917.7	918.6	919.5
167.5°	929.2	928.2	927.3	926.2	925.9	926.0	926.1	926.3	926.5	927.6	928.7
170°	934.1	932.9	931.9	930.8	930.3	930.5	930.7	930.8	930.9	932.2	933.4
172.5°	937.5	936.3	935.2	934.2	933.8	934.1	934.3	934.6	934.9	935.9	937.1
175°	941.2	940.3	939.3	938.4	938.0	938.2	938.3	938.5	938.7	939.9	941.1
177.5°	943.0	942.4	941.6	940.8	940.5	940.7	940.8	940.8	941.0	941.9	942.7
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8	1498.8
2.5°	1567.5	1571.6	1580.3	1577.2	1581.3	1583.3	1585.4
5°	1694.1	1714.5	1723.3	1722.1	1735.5	1732.3	1729.1
7.5°	1837.1	1858.5	1870.5	1885.4	1894.0	1894.6	1902.1
10°	1918.1	1946.1	1957.5	1973.4	1983.6	1989.3	1988.7
12.5°	1980.2	2002.1	2027.7	2035.5	2049.3	2056.4	2053.8
15°	2054.8	2089.8	2116.6	2129.9	2147.1	2152.2	2159.2
17.5°	2121.5	2168.4	2199.6	2241.1	2256.7	2266.2	2260.7
20°	2171.9	2233.6	2264.7	2314.4	2341.7	2356.4	2351.3
22.5°	2231.5	2298.2	2355.9	2398.9	2440.4	2460.2	2464.3
25°	2333.5	2425.1	2509.7	2566.4	2617.8	2629.9	2656.7
27.5°	2447.5	2555.5	2646.0	2705.5	2741.4	2754.9	2763.3
30°	2519.2	2626.8	2694.8	2733.0	2744.4	2743.2	2741.9
32.5°	2554.4	2621.7	2634.8	2624.0	2597.8	2575.7	2552.6
35°	2504.6	2454.4	2379.3	2282.6	2211.3	2139.5	2132.4
37.5°	2252.6	2091.9	1966.9	1827.3	1746.8	1697.0	1662.7
40°	2015.3	1832.8	1681.4	1563.7	1481.7	1449.2	1417.4
42.5°	1757.8	1583.5	1449.3	1350.9	1289.3	1253.3	1228.0
45°	1428.2	1274.2	1169.3	1098.1	1049.0	1021.1	1005.1
47.5°	1170.3	1056.4	967.2	915.9	882.0	860.3	860.4
50°	1031.9	923.1	863.9	823.2	793.9	776.7	780.0
52.5°	909.2	827.9	777.4	743.3	721.7	711.1	710.8
55°	760.3	701.7	668.6	643.9	629.1	617.1	619.6
57.5°	650.3	601.0	578.8	558.2	548.0	543.2	536.1
60°	582.1	543.9	524.8	508.3	498.1	494.3	487.3
62.5°	521.5	491.5	473.0	459.4	450.3	449.0	443.6
65°	438.3	415.4	398.9	392.5	383.0	380.4	380.4
67.5°	361.4	345.0	332.1	326.2	322.1	322.6	319.6
70°	313.0	299.6	291.3	285.0	281.8	282.5	279.9
72.5°	273.8	258.9	251.7	247.9	243.6	245.3	244.3
75°	207.4	199.7	196.0	192.1	189.5	188.3	187.0
77.5°	152.3	145.5	142.6	140.4	140.8	137.8	140.3
80°	117.7	112.0	110.1	106.9	106.2	106.2	105.6
82.5°	86.1	82.9	81.5	78.9	77.8	78.8	77.1
85°	44.5	41.9	41.4	41.4	40.1	38.8	41.9
87.5°	18.9	17.1	17.2	16.8	16.9	16.5	15.6
90°	13.5	14.2	14.9	15.4	15.8	16.3	16.8
92.5°	13.5	14.2	14.8	15.0	15.2	15.5	15.6
95°	13.5	14.2	14.7	14.7	14.7	14.7	14.7
97.5°	21.2	16.9	14.7	14.7	14.7	14.7	14.7
100°	52.1	29.0	17.2	16.5	15.9	15.3	14.7
102.5°	141.9	137.5	130.1	119.5	109.0	98.4	87.8
105°	208.1	208.1	208.0	207.9	207.7	207.5	207.5
107.5°	263.5	263.5	263.3	262.9	262.4	261.9	261.5
110°	298.9	298.4	298.3	298.4	298.6	298.8	298.9



TEST NUMBER: P333436-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	334.3	333.7	333.3	333.1	332.9	332.6	332.4
115°	387.9	387.2	386.4	385.5	384.6	383.6	382.7
117.5°	439.4	438.6	438.0	437.5	437.2	436.8	436.4
120°	473.3	473.0	472.4	471.6	470.9	470.1	469.3
122.5°	505.1	504.8	504.2	503.3	502.4	501.5	500.6
125°	551.3	550.6	550.1	549.6	549.1	548.7	548.3
127.5°	594.0	593.7	593.0	591.7	590.6	589.5	588.3
130°	621.6	621.1	620.5	619.7	619.0	618.1	617.4
132.5°	647.8	647.7	647.3	646.5	645.7	645.0	644.2
135°	685.6	685.3	684.7	683.7	682.8	681.8	680.9
137.5°	721.3	721.4	721.0	720.2	719.4	718.6	717.8
140°	743.3	743.7	743.3	742.3	741.5	740.6	739.6
142.5°	764.4	764.4	764.0	763.1	762.1	761.2	760.3
145°	794.6	794.7	794.3	793.3	792.4	791.5	790.6
147.5°	820.3	820.5	820.0	819.0	817.8	816.7	815.6
150°	836.9	837.3	836.8	835.5	834.2	833.0	831.8
152.5°	851.4	851.8	851.3	850.2	849.1	848.0	846.9
155°	871.6	872.0	871.7	870.4	869.2	868.0	866.7
157.5°	888.2	888.6	888.3	887.0	885.8	884.6	883.4
160°	898.6	899.2	898.9	897.7	896.5	895.2	893.9
162.5°	908.2	909.2	908.9	907.6	906.2	904.8	903.4
165°	920.5	921.4	921.2	920.0	918.8	917.6	916.2
167.5°	929.8	930.9	930.9	929.4	928.0	926.6	925.2
170°	934.7	935.9	935.9	934.4	933.0	931.6	930.3
172.5°	938.2	939.3	939.1	937.8	936.4	935.0	933.6
175°	942.4	943.6	943.5	942.2	940.8	939.3	937.9
177.5°	943.6	944.5	944.4	943.4	942.4	941.4	940.5
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2

(END OF REPORT)