

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333690

Luminaire Tested: **S125RDIW-S850D1050U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333690  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S850D1050U835-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7441.0 lumens  
Efficiency: N/A  
Efficacy: 141.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333690

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333690

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44					44			
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37					37			
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31					31			
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27					27			
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23					23			
5	68	56	48	42	62	52	45	40	44	38	34	36	32	29	29	26	24	20					20			
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18					18			
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16					16			
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	22	19	17	14					14			
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13					13			
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12					12			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8881	8881	8881
5°	8901	8800	8854
10°	8834	8718	8718
15°	8729	8541	8471
20°	8594	8294	8194
25°	8437	8052	7874
30°	8240	7768	7520
35°	8041	7476	7123
40°	7854	7171	6734
45°	7626	6830	6308
50°	7398	6459	5865
55°	7133	6104	5391
60°	6868	5674	4883
65°	6554	5174	4300
70°	6197	4549	3707
75°	5702	3835	3084
80°	5021	3013	2589
85°	4231	2460	2312



TEST NUMBER: P333690

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.3	1.7
10°-20°	361.3	4.9
20°-30°	524.0	7.0
30°-40°	597.2	8.0
40°-50°	582.1	7.8
50°-60°	490.0	6.6
60°-70°	343.5	4.6
70°-80°	176.6	2.4
80°-90°	47.4	0.6
90°-100°	49.6	0.7
100°-110°	305.6	4.1
110°-120°	554.2	7.4
120°-130°	711.2	9.6
130°-140°	765.0	10.3
140°-150°	718.0	9.6
150°-160°	580.8	7.8
160°-170°	375.7	5.0
170°-180°	129.6	1.7
0°-30°	1014.6	13.6
0°-40°	1611.8	21.7
0°-60°	2683.9	36.1
0°-90°	3251.3	43.7
90°-120°	909.3	12.2
90°-150°	3103.6	41.7
90°-180°	4190.0	56.3
0°-180°	7441.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1373	1368	1357	1367	1366	130
15°	1306	1298	1277	1276	1267	368
25°	1184	1167	1130	1117	1105	545
35°	1020	994	948	919	904	638
45°	835	803	748	708	691	644
55°	634	599	542	497	479	566
65°	429	392	339	298	281	425
75°	228	197	154	132	124	242
85°	57	39	33	32	31	64
90°	1	9	16	21	24	5
95°	58	53	16	21	21	73
105°	297	301	301	301	300	315
115°	558	563	564	560	554	553
125°	794	801	801	797	794	709
135°	990	996	994	992	986	763
145°	1148	1150	1150	1151	1145	718
155°	1264	1259	1260	1263	1255	582
165°	1334	1328	1329	1334	1327	377
175°	1364	1359	1359	1366	1358	130
180°	1364	1364	1364	1364	1364	



TEST NUMBER: P333690

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1377.5	1377.0	1376.4	1375.9	1375.3	1374.1	1372.3	1370.4	1368.6	1366.7	1368.6
5°	1373.0	1372.1	1371.1	1370.2	1369.3	1367.6	1365.0	1362.5	1359.9	1357.4	1359.7
7.5°	1359.5	1358.6	1357.7	1356.8	1356.0	1354.0	1351.0	1347.9	1344.9	1341.8	1343.4
10°	1347.0	1346.3	1345.6	1344.9	1344.2	1342.3	1339.1	1335.8	1332.6	1329.4	1330.0
12.5°	1332.9	1332.0	1331.1	1330.3	1329.4	1326.8	1322.4	1318.1	1313.8	1309.4	1309.9
15°	1305.5	1304.1	1302.7	1301.3	1299.9	1296.8	1292.0	1287.1	1282.3	1277.4	1277.2
17.5°	1274.5	1272.4	1270.3	1268.2	1266.0	1261.9	1255.8	1249.7	1243.6	1237.5	1236.4
20°	1250.4	1248.1	1245.8	1243.5	1241.2	1236.3	1229.0	1221.6	1214.2	1206.8	1205.7
22.5°	1223.8	1221.5	1219.2	1216.9	1214.6	1209.6	1201.8	1194.1	1186.3	1178.6	1176.3
25°	1184.0	1180.5	1177.0	1173.6	1170.1	1164.1	1155.6	1147.0	1138.5	1130.0	1127.0
27.5°	1138.3	1134.1	1129.9	1125.7	1121.5	1114.8	1105.7	1096.5	1087.4	1078.2	1074.0
30°	1105.0	1100.6	1096.3	1091.9	1087.5	1080.4	1070.8	1061.1	1051.4	1041.7	1036.4
32.5°	1072.6	1067.5	1062.4	1057.3	1052.1	1044.6	1034.8	1024.9	1015.0	1005.1	999.3
35°	1019.9	1014.3	1008.8	1003.2	997.7	989.7	979.4	969.0	958.6	948.2	941.5
37.5°	968.1	961.4	954.7	947.9	941.2	932.5	921.8	911.0	900.3	889.6	881.6
40°	931.6	924.7	917.7	910.8	903.9	894.9	883.8	872.7	861.7	850.6	841.8
42.5°	893.4	886.3	879.2	872.0	864.9	855.7	844.2	832.8	821.3	809.9	801.5
45°	835.0	828.3	821.6	814.9	808.2	798.5	785.8	773.2	760.5	747.8	738.5
47.5°	774.6	767.5	760.4	753.4	746.3	736.4	723.6	710.8	698.0	685.2	675.7
50°	736.3	728.7	721.1	713.5	705.9	695.5	682.3	669.2	656.0	642.9	633.2
52.5°	694.8	687.0	679.2	671.4	663.6	653.5	641.1	628.7	616.2	603.8	593.4
55°	633.5	626.1	618.8	611.4	604.0	593.8	580.9	568.0	555.1	542.1	531.7
57.5°	571.6	563.7	555.8	547.9	540.1	529.9	517.4	504.9	492.5	480.0	469.9
60°	531.7	523.7	515.6	507.5	499.4	489.2	476.7	464.2	451.8	439.3	429.2
62.5°	489.4	481.7	474.0	466.2	458.5	448.4	435.7	423.1	410.4	397.8	388.4
65°	428.9	421.1	413.2	405.4	397.5	387.5	375.3	363.0	350.8	338.6	329.3
67.5°	368.9	361.0	353.2	345.4	337.5	327.7	316.0	304.3	292.6	280.8	272.4
70°	328.2	320.3	312.5	304.6	296.8	287.1	275.6	264.0	252.5	240.9	233.8
72.5°	288.3	280.6	273.0	265.3	257.7	248.4	237.6	226.8	216.0	205.2	198.6
75°	228.5	221.6	214.6	207.7	200.8	192.5	182.8	173.1	163.4	153.7	148.6
77.5°	169.1	163.5	158.0	152.5	146.9	140.3	132.5	124.8	117.0	109.3	105.7
80°	135.0	129.5	123.9	118.4	112.9	106.9	100.4	93.9	87.5	81.0	78.9
82.5°	101.8	96.8	91.8	86.8	81.8	77.1	72.7	68.3	63.8	59.4	58.4
85°	57.1	53.0	48.8	44.7	40.5	37.8	36.7	35.5	34.4	33.2	33.0
87.5°	19.3	18.4	17.4	16.5	15.6	15.2	15.3	15.4	15.6	15.7	15.9
90°	1.0	2.8	4.6	6.4	8.2	9.9	11.5	13.0	14.6	16.2	17.3
92.5°	15.6	14.3	13.1	11.8	10.5	10.6	12.0	13.4	14.8	16.2	17.3
95°	57.6	57.0	56.3	55.6	55.0	50.3	41.8	33.3	24.7	16.2	17.3
97.5°	120.4	121.6	122.8	124.0	125.2	117.4	100.5	83.6	66.7	49.8	43.4
100°	168.9	169.6	170.2	170.9	171.6	172.4	173.3	174.2	175.1	176.0	142.5
102.5°	218.3	219.1	220.0	220.8	221.7	222.4	222.9	223.4	224.0	224.5	218.2
105°	297.3	298.2	299.1	300.0	300.9	301.4	301.4	301.4	301.4	301.4	301.4
107.5°	379.5	379.5	379.5	379.5	379.5	379.7	380.1	380.6	381.0	381.5	381.5
110°	432.9	432.9	432.9	432.9	432.9	433.1	433.5	434.0	434.4	434.9	434.2



TEST NUMBER: P333690

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.0	483.6	484.1	484.6	485.2	485.6	485.9	486.1	486.4	486.7	485.8
115°	558.3	559.4	560.5	561.6	562.8	563.4	563.7	563.9	564.1	564.3	563.4
117.5°	636.2	636.1	636.1	636.0	636.0	636.4	637.2	638.1	638.9	639.8	638.6
120°	684.7	684.5	684.2	684.0	683.8	684.0	684.7	685.4	686.0	686.7	686.3
122.5°	727.6	728.4	729.3	730.1	731.0	731.6	731.9	732.2	732.5	732.8	732.4
125°	793.9	795.5	797.1	798.6	800.2	801.0	801.0	801.0	801.0	801.0	800.1
127.5°	857.2	858.4	859.5	860.6	861.7	862.2	862.1	862.0	861.8	861.7	861.2
130°	896.1	897.2	898.3	899.4	900.6	901.2	901.5	901.7	901.9	902.1	901.5
132.5°	934.9	936.2	937.5	938.8	940.1	940.5	940.0	939.5	939.0	938.6	938.4
135°	990.1	991.5	992.8	994.2	995.5	996.0	995.5	995.1	994.6	994.2	993.7
137.5°	1040.9	1042.1	1043.2	1044.4	1045.6	1046.0	1045.6	1045.2	1044.7	1044.3	1044.4
140°	1074.1	1074.5	1075.0	1075.4	1075.9	1076.0	1075.8	1075.5	1075.3	1075.1	1075.5
142.5°	1104.0	1104.3	1104.6	1104.8	1105.1	1105.4	1105.7	1106.0	1106.3	1106.6	1106.7
145°	1147.9	1148.4	1148.8	1149.3	1149.7	1149.9	1149.9	1149.9	1149.9	1149.9	1150.2
147.5°	1186.3	1186.3	1186.2	1186.1	1186.0	1186.1	1186.3	1186.6	1186.9	1187.1	1187.4
150°	1210.6	1210.2	1209.7	1209.3	1208.8	1208.8	1209.3	1209.7	1210.2	1210.6	1211.1
152.5°	1234.1	1233.1	1232.1	1231.1	1230.1	1229.9	1230.3	1230.8	1231.2	1231.6	1232.1
155°	1264.2	1262.9	1261.5	1260.2	1258.8	1258.4	1258.8	1259.3	1259.7	1260.2	1260.8
157.5°	1287.5	1286.7	1285.9	1285.1	1284.2	1283.9	1283.9	1283.9	1284.0	1284.0	1284.8
160°	1303.7	1302.3	1301.0	1299.6	1298.3	1297.7	1297.9	1298.2	1298.4	1298.6	1299.5
162.5°	1316.6	1315.3	1313.9	1312.6	1311.2	1310.6	1310.9	1311.1	1311.3	1311.5	1312.8
165°	1334.0	1332.7	1331.3	1330.0	1328.6	1328.0	1328.3	1328.5	1328.7	1328.9	1330.3
167.5°	1346.9	1345.6	1344.2	1342.8	1341.4	1340.8	1341.0	1341.2	1341.5	1341.7	1343.3
170°	1354.2	1352.7	1351.1	1349.5	1347.9	1347.3	1347.5	1347.7	1347.9	1348.2	1350.0
172.5°	1359.1	1357.5	1355.9	1354.4	1352.8	1352.2	1352.6	1353.0	1353.4	1353.8	1355.4
175°	1364.3	1363.0	1361.6	1360.3	1358.9	1358.4	1358.6	1358.8	1359.1	1359.3	1361.1
177.5°	1366.8	1365.7	1364.6	1363.5	1362.5	1362.0	1362.2	1362.4	1362.5	1362.7	1364.0
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3



TEST NUMBER: P333690

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1370.4	1372.3	1374.1	1375.0	1374.8	1374.6	1374.4	1374.2
5°	1362.0	1364.3	1366.6	1367.6	1367.1	1366.6	1366.2	1365.7
7.5°	1345.1	1346.7	1348.3	1348.8	1348.3	1347.8	1347.3	1346.8
10°	1330.7	1331.4	1332.1	1332.1	1331.4	1330.7	1330.0	1329.4
12.5°	1310.4	1310.9	1311.4	1311.2	1310.1	1309.0	1308.0	1306.9
15°	1277.0	1276.7	1276.5	1275.4	1273.3	1271.2	1269.1	1267.0
17.5°	1235.2	1234.1	1232.9	1231.5	1229.8	1228.1	1226.4	1224.7
20°	1204.5	1203.3	1202.2	1200.6	1198.5	1196.4	1194.3	1192.3
22.5°	1174.0	1171.8	1169.5	1167.5	1165.8	1164.1	1162.4	1160.7
25°	1124.0	1121.0	1118.0	1115.2	1112.6	1110.1	1107.6	1105.0
27.5°	1069.8	1065.6	1061.4	1058.1	1055.7	1053.2	1050.8	1048.3
30°	1031.1	1025.8	1020.4	1016.8	1014.7	1012.6	1010.5	1008.4
32.5°	993.4	987.5	981.7	977.4	974.8	972.2	969.5	966.9
35°	934.8	928.1	921.4	916.5	913.2	910.0	906.8	903.5
37.5°	873.6	865.5	857.5	851.9	848.8	845.6	842.5	839.4
40°	833.0	824.3	815.5	809.7	807.0	804.2	801.4	798.7
42.5°	793.1	784.7	776.3	770.0	766.0	761.9	757.8	753.8
45°	729.3	720.1	710.8	704.5	701.0	697.6	694.1	690.6
47.5°	666.2	656.7	647.2	640.5	636.7	632.9	629.0	625.2
50°	623.5	613.8	604.1	597.5	594.1	590.6	587.1	583.7
52.5°	583.0	572.5	562.1	555.1	551.7	548.2	544.8	541.3
55°	521.4	511.0	500.6	493.5	489.9	486.2	482.5	478.8
57.5°	459.7	449.6	439.4	432.7	429.4	426.1	422.9	419.6
60°	419.0	408.8	398.7	391.9	388.4	385.0	381.5	378.0
62.5°	378.9	369.5	360.1	353.7	350.2	346.7	343.3	339.8
65°	320.1	310.9	301.6	295.3	291.8	288.4	284.9	281.4
67.5°	263.9	255.5	247.0	241.4	238.7	235.9	233.1	230.4
70°	226.6	219.5	212.3	207.4	204.6	201.8	199.1	196.3
72.5°	192.0	185.4	178.8	174.6	172.7	170.9	169.1	167.2
75°	143.6	138.5	133.4	130.1	128.4	126.8	125.2	123.6
77.5°	102.1	98.6	95.0	92.7	91.5	90.3	89.1	87.9
80°	76.9	74.8	72.7	71.4	71.0	70.5	70.0	69.6
82.5°	57.5	56.5	55.5	54.9	54.6	54.4	54.1	53.8
85°	32.8	32.5	32.3	32.1	31.8	31.6	31.4	31.2
87.5°	16.1	16.4	16.6	16.7	16.6	16.6	16.5	16.5
90°	18.4	19.6	20.7	21.6	22.3	22.9	23.6	24.3
92.5°	18.4	19.6	20.7	21.4	21.7	22.0	22.3	22.7
95°	18.4	19.6	20.7	21.2	21.2	21.2	21.2	21.2
97.5°	37.1	30.7	24.4	21.2	21.2	21.2	21.2	21.2
100°	109.0	75.5	42.0	24.8	23.9	23.0	22.1	21.2
102.5°	211.8	205.5	199.2	188.4	173.1	157.8	142.5	127.2
105°	301.4	301.4	301.4	301.3	301.1	300.8	300.6	300.4
107.5°	381.6	381.6	381.7	381.4	380.7	380.0	379.3	378.7
110°	433.5	432.9	432.2	432.0	432.2	432.4	432.6	432.9





TEST NUMBER: P333690

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	485.0	484.1	483.3	482.7	482.4	482.0	481.7	481.4
115°	562.5	561.6	560.7	559.6	558.3	556.9	555.6	554.2
117.5°	637.5	636.3	635.1	634.2	633.7	633.1	632.5	631.9
120°	685.8	685.4	684.9	684.1	683.0	681.9	680.8	679.6
122.5°	731.9	731.5	731.0	730.2	728.9	727.6	726.3	725.0
125°	799.2	798.3	797.4	796.6	796.0	795.3	794.6	793.9
127.5°	860.7	860.2	859.7	858.6	857.0	855.3	853.6	852.0
130°	900.8	900.1	899.4	898.5	897.4	896.3	895.2	894.1
132.5°	938.3	938.1	938.0	937.4	936.3	935.1	934.0	932.9
135°	993.3	992.8	992.4	991.5	990.1	988.8	987.4	986.1
137.5°	1044.5	1044.6	1044.7	1044.2	1043.0	1041.8	1040.7	1039.5
140°	1076.0	1076.4	1076.9	1076.4	1075.1	1073.7	1072.4	1071.0
142.5°	1106.8	1106.9	1107.0	1106.4	1105.0	1103.7	1102.3	1101.0
145°	1150.4	1150.6	1150.8	1150.3	1148.9	1147.6	1146.2	1144.9
147.5°	1187.7	1188.0	1188.2	1187.6	1185.9	1184.3	1182.7	1181.1
150°	1211.5	1212.0	1212.4	1211.7	1209.9	1208.1	1206.3	1204.5
152.5°	1232.5	1233.0	1233.4	1232.9	1231.2	1229.6	1228.0	1226.4
155°	1261.5	1262.2	1262.9	1262.3	1260.5	1258.7	1256.9	1255.1
157.5°	1285.5	1286.2	1286.9	1286.4	1284.6	1282.8	1281.0	1279.2
160°	1300.4	1301.3	1302.2	1301.7	1300.0	1298.2	1296.4	1294.6
162.5°	1314.1	1315.3	1316.6	1316.2	1314.2	1312.3	1310.3	1308.3
165°	1331.6	1333.0	1334.3	1334.1	1332.3	1330.5	1328.7	1326.9
167.5°	1344.9	1346.5	1348.2	1348.0	1345.9	1343.9	1341.9	1339.9
170°	1351.8	1353.6	1355.4	1355.2	1353.2	1351.2	1349.2	1347.1
172.5°	1357.1	1358.7	1360.3	1360.1	1358.1	1356.0	1354.0	1352.0
175°	1362.9	1364.7	1366.5	1366.4	1364.3	1362.3	1360.3	1358.3
177.5°	1365.2	1366.5	1367.8	1367.7	1366.2	1364.8	1363.4	1361.9
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3

(END OF REPORT)