

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333441-830

Luminaire Tested: **S125DIW-S1090D770U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333441-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D770U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6696.0 lumens
Efficiency: N/A
Efficacy: 124.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333441-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333441-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	63
1	101	96	92	88	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	72	85	79	73	69	69	65	61	61	57	54	52	50	48	44
3	83	74	66	60	78	69	63	57	61	56	52	54	49	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	39	42	38	35	32
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	29	24	21	19
9	52	39	32	26	49	37	30	25	33	28	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	28	23	19	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10388	10388	10388
5°	10410	10311	10377
10°	10347	10238	10297
15°	10235	10116	10158
20°	10074	9943	9961
25°	9902	9738	9729
30°	9688	9517	9470
35°	9460	9280	9150
40°	9226	9022	8893
45°	8972	8786	8611
50°	8694	8501	8246
55°	8425	8180	7952
60°	8103	7856	7576
65°	7719	7467	7213
70°	7353	7017	6775
75°	6697	6478	6253
80°	5962	5869	5724
85°	5180	5283	4994



TEST NUMBER: P333441-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.6	2.3
10°-20°	428.4	6.4
20°-30°	632.5	9.4
30°-40°	738.0	11.0
40°-50°	741.2	11.1
50°-60°	650.7	9.7
60°-70°	484.8	7.2
70°-80°	277.2	4.1
80°-90°	82.6	1.2
90°-100°	60.2	0.9
100°-110°	177.8	2.7
110°-120°	301.2	4.5
120°-130°	396.4	5.9
130°-140°	444.2	6.6
140°-150°	435.3	6.5
150°-160°	365.6	5.5
160°-170°	243.1	3.6
170°-180°	85.1	1.3
0°-30°	1212.5	18.1
0°-40°	1950.5	29.1
0°-60°	3342.4	49.9
0°-90°	4187.1	62.5
90°-120°	539.3	8.1
90°-150°	1815.1	27.1
90°-180°	2509.0	37.5
0°-180°	6696.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1608	1608	1608	1608	1608	
5°	1606	1603	1590	1601	1601	152
15°	1531	1526	1513	1519	1519	431
25°	1390	1383	1367	1369	1365	639
35°	1200	1194	1177	1170	1160	750
45°	982	977	962	947	943	757
55°	748	744	726	715	706	668
65°	505	502	489	477	472	501
75°	268	266	260	256	251	286
85°	70	71	71	70	67	78
90°	1	6	11	15	17	6
95°	46	47	54	59	60	49
105°	160	163	167	171	174	170
115°	302	304	306	305	304	298
125°	440	444	445	444	443	394
135°	572	576	577	577	574	441
145°	693	696	698	698	696	433
155°	793	793	794	797	793	365
165°	863	861	862	864	861	243
175°	897	894	894	898	894	85
180°	899	899	899	899	899	



TEST NUMBER: P333441-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1612.4	1611.7	1611.0	1610.3	1609.7	1608.2	1605.9	1603.6	1601.4	1599.1	1601.4
5°	1605.8	1605.2	1604.7	1604.1	1603.5	1601.9	1599.0	1596.2	1593.4	1590.5	1593.1
7.5°	1591.0	1590.4	1589.9	1589.3	1588.7	1586.9	1583.8	1580.6	1577.5	1574.4	1577.0
10°	1577.8	1577.3	1576.7	1576.1	1575.6	1573.7	1570.6	1567.4	1564.3	1561.2	1563.5
12.5°	1561.5	1560.5	1559.4	1558.4	1557.5	1555.5	1552.6	1549.7	1546.8	1543.9	1545.8
15°	1530.7	1529.8	1529.0	1528.1	1527.3	1525.3	1522.2	1519.1	1516.0	1512.9	1514.3
17.5°	1495.3	1494.1	1492.8	1491.6	1490.3	1488.1	1484.9	1481.7	1478.5	1475.2	1477.0
20°	1465.8	1465.3	1464.7	1464.1	1463.6	1461.4	1457.7	1454.1	1450.4	1446.7	1448.7
22.5°	1436.2	1435.3	1434.3	1433.2	1432.2	1429.9	1426.5	1423.1	1419.7	1416.2	1417.5
25°	1389.5	1388.1	1386.7	1385.3	1383.8	1381.3	1377.6	1373.9	1370.3	1366.6	1367.2
27.5°	1334.7	1333.9	1333.0	1332.2	1331.3	1329.1	1325.2	1321.4	1317.7	1313.9	1314.0
30°	1299.1	1298.3	1297.4	1296.6	1295.7	1293.2	1288.9	1284.7	1280.4	1276.2	1275.6
32.5°	1260.5	1259.1	1257.8	1256.5	1255.3	1252.7	1248.9	1245.1	1241.3	1237.6	1236.5
35°	1199.9	1198.7	1197.6	1196.5	1195.3	1192.8	1188.8	1184.9	1180.9	1177.0	1175.5
37.5°	1137.0	1135.6	1134.2	1132.7	1131.3	1128.8	1125.0	1121.3	1117.6	1113.9	1111.7
40°	1094.3	1092.9	1091.5	1090.1	1088.6	1085.9	1081.9	1078.0	1074.0	1070.1	1067.5
42.5°	1048.5	1047.3	1046.1	1044.9	1043.7	1041.1	1037.2	1033.2	1029.3	1025.3	1022.9
45°	982.3	981.2	980.1	978.9	977.8	975.5	972.1	968.7	965.4	962.0	958.6
47.5°	911.1	911.1	911.2	911.3	911.3	909.3	905.2	901.1	897.0	893.0	889.5
50°	865.3	864.4	863.6	862.7	861.9	859.7	856.3	852.9	849.5	846.1	842.4
52.5°	818.4	817.7	817.2	816.5	816.0	813.8	810.2	806.5	803.0	799.3	796.1
55°	748.2	747.3	746.5	745.6	744.8	742.3	738.4	734.4	730.5	726.5	724.0
57.5°	674.1	673.6	673.3	672.8	672.3	670.4	667.0	663.7	660.4	657.0	653.7
60°	627.3	626.1	625.0	623.9	622.7	620.7	617.6	614.4	611.3	608.2	605.4
62.5°	578.4	577.5	576.6	575.7	574.9	573.1	570.3	567.7	565.1	562.4	559.3
65°	505.1	504.5	504.0	503.4	502.8	501.1	497.9	494.8	491.7	488.6	486.1
67.5°	434.1	432.9	431.8	430.6	429.4	427.6	425.3	423.0	420.7	418.4	416.2
70°	389.4	388.0	386.5	385.1	383.7	381.7	379.2	376.6	374.1	371.6	369.9
72.5°	340.5	339.5	338.6	337.6	336.7	335.4	333.8	332.1	330.5	328.8	326.9
75°	268.4	267.9	267.3	266.7	266.2	265.2	263.8	262.4	261.0	259.6	258.7
77.5°	202.1	201.8	201.6	201.4	201.1	200.7	199.8	199.1	198.3	197.5	197.0
80°	160.3	160.3	160.3	160.3	160.3	160.0	159.5	158.9	158.3	157.8	157.5
82.5°	123.7	123.2	122.8	122.3	121.9	121.6	121.5	121.4	121.2	121.1	120.6
85°	69.9	70.2	70.5	70.8	71.1	71.3	71.3	71.3	71.3	71.3	71.0
87.5°	27.6	27.9	28.1	28.4	28.7	28.7	28.7	28.7	28.7	28.7	28.8
90°	0.7	2.0	3.2	4.4	5.7	6.9	7.9	9.0	10.1	11.2	12.0
92.5°	17.0	17.8	18.7	19.5	20.5	21.5	22.9	24.2	25.5	26.9	27.9
95°	45.5	45.8	46.1	46.4	46.8	47.7	49.2	50.8	52.3	53.9	55.0
97.5°	75.6	75.7	75.8	76.0	76.1	77.2	79.4	81.5	83.6	85.8	86.8
100°	97.9	97.9	97.9	97.9	97.9	99.0	100.9	103.0	105.0	107.1	108.5
102.5°	122.1	122.6	123.3	123.9	124.5	125.4	126.4	127.4	128.4	129.4	131.0
105°	159.6	160.3	161.1	161.8	162.7	163.5	164.5	165.3	166.3	167.2	168.1
107.5°	201.0	201.7	202.6	203.3	204.1	204.8	205.6	206.2	207.0	207.6	208.1
110°	229.5	230.3	231.0	231.9	232.6	233.2	233.7	234.1	234.6	235.1	235.5



TEST NUMBER: P333441-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	258.6	259.0	259.4	259.9	260.2	260.7	261.3	261.9	262.5	263.1	263.3
115°	301.6	302.2	302.8	303.4	304.1	304.5	304.8	305.1	305.5	305.8	305.6
117.5°	344.7	345.0	345.3	345.5	345.8	346.1	346.4	346.7	346.9	347.2	347.3
120°	371.6	372.3	373.1	373.9	374.7	375.1	375.2	375.4	375.6	375.7	375.7
122.5°	400.7	401.0	401.2	401.5	401.8	402.1	402.5	402.9	403.3	403.7	403.6
125°	440.1	441.0	442.0	442.9	443.8	444.4	444.5	444.7	444.9	445.0	444.7
127.5°	482.1	482.6	483.1	483.7	484.2	484.6	484.7	484.9	485.1	485.3	485.1
130°	507.3	508.0	508.9	509.6	510.4	511.0	511.2	511.5	511.9	512.2	512.0
132.5°	532.4	533.8	535.0	536.3	537.5	538.2	538.1	538.0	538.0	537.9	537.8
135°	572.3	573.3	574.2	575.1	576.1	576.6	576.7	576.9	577.1	577.2	577.2
137.5°	609.8	610.8	611.6	612.6	613.5	614.1	614.4	614.7	615.1	615.5	615.7
140°	634.0	634.7	635.5	636.2	637.1	637.6	638.1	638.6	639.0	639.5	639.8
142.5°	658.0	658.6	659.3	660.0	660.6	661.2	661.9	662.4	663.0	663.5	663.7
145°	693.4	694.0	694.7	695.2	695.9	696.4	696.9	697.4	697.9	698.3	698.3
147.5°	726.1	726.5	726.8	727.2	727.5	727.8	728.2	728.6	729.0	729.3	729.7
150°	748.0	747.8	747.6	747.5	747.3	747.6	748.2	748.9	749.4	750.1	750.1
152.5°	765.9	766.1	766.3	766.6	766.8	766.9	767.2	767.5	767.7	768.0	768.4
155°	793.4	793.4	793.4	793.4	793.4	793.5	793.7	793.8	794.0	794.2	794.8
157.5°	818.1	817.7	817.4	817.1	816.7	816.6	816.8	816.9	817.1	817.3	817.8
160°	832.6	832.2	831.7	831.2	830.8	830.6	830.8	830.9	831.0	831.2	831.9
162.5°	845.6	845.2	844.8	844.5	844.1	844.0	844.0	844.0	844.0	844.1	844.9
165°	862.7	862.4	862.1	861.8	861.5	861.4	861.6	861.7	861.9	862.0	862.6
167.5°	877.3	876.7	876.0	875.4	874.8	874.5	874.5	874.5	874.5	874.5	875.4
170°	885.1	884.5	883.8	883.3	882.6	882.3	882.3	882.3	882.3	882.3	883.3
172.5°	890.7	890.0	889.5	888.8	888.3	887.9	887.9	887.9	887.9	887.9	888.8
175°	897.0	896.4	895.8	895.1	894.5	894.2	894.2	894.2	894.2	894.2	895.1
177.5°	900.2	899.8	899.2	898.7	898.2	898.0	897.8	897.7	897.6	897.4	898.1
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1



TEST NUMBER: P333441-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4	1608.4
2.5°	1603.6	1605.9	1608.2	1609.2	1609.0	1608.7	1608.5	1608.4
5°	1595.6	1598.2	1600.7	1601.9	1601.6	1601.3	1601.0	1600.7
7.5°	1579.4	1582.0	1584.4	1585.5	1585.3	1585.0	1584.7	1584.4
10°	1565.8	1568.0	1570.3	1571.3	1571.0	1570.7	1570.5	1570.2
12.5°	1547.6	1549.4	1551.1	1552.1	1552.0	1551.9	1551.9	1551.8
15°	1515.7	1517.1	1518.5	1519.3	1519.3	1519.3	1519.3	1519.3
17.5°	1478.8	1480.5	1482.2	1482.4	1481.0	1479.6	1478.2	1476.8
20°	1450.7	1452.6	1454.6	1454.9	1453.5	1452.1	1450.7	1449.3
22.5°	1418.8	1420.1	1421.4	1421.5	1420.6	1419.7	1418.7	1417.7
25°	1367.7	1368.3	1368.9	1368.7	1367.8	1367.0	1366.1	1365.3
27.5°	1314.1	1314.2	1314.4	1314.0	1313.2	1312.3	1311.5	1310.6
30°	1275.1	1274.5	1273.9	1273.3	1272.4	1271.6	1270.7	1269.9
32.5°	1235.5	1234.4	1233.5	1232.2	1230.7	1229.2	1227.6	1226.1
35°	1174.1	1172.7	1171.3	1169.5	1167.2	1165.0	1162.7	1160.5
37.5°	1109.7	1107.6	1105.5	1103.8	1102.5	1101.2	1099.9	1098.6
40°	1065.0	1062.4	1059.9	1058.2	1057.3	1056.5	1055.6	1054.8
42.5°	1020.7	1018.3	1016.1	1014.2	1013.0	1011.6	1010.3	1009.0
45°	955.2	951.8	948.4	946.2	945.4	944.5	943.7	942.8
47.5°	886.1	882.6	879.2	876.5	874.5	872.5	870.5	868.6
50°	838.8	835.1	831.4	828.6	826.6	824.6	822.7	820.7
52.5°	792.9	789.7	786.5	783.7	781.5	779.3	777.1	774.9
55°	721.4	718.9	716.3	714.1	712.1	710.1	708.1	706.2
57.5°	650.5	647.2	643.9	641.8	640.7	639.6	638.6	637.4
60°	602.6	599.7	596.9	594.5	592.5	590.5	588.5	586.5
62.5°	556.3	553.3	550.2	547.9	546.4	544.9	543.3	541.8
65°	483.5	481.0	478.4	476.5	475.4	474.3	473.2	472.0
67.5°	414.1	411.9	409.7	408.3	407.6	407.0	406.3	405.7
70°	368.2	366.5	364.8	363.4	362.2	361.1	360.0	358.8
72.5°	325.0	323.0	321.1	319.6	318.5	317.4	316.2	315.1
75°	257.9	257.0	256.2	255.1	254.0	252.9	251.8	250.6
77.5°	196.4	196.0	195.5	194.8	194.0	193.2	192.4	191.6
80°	157.2	156.9	156.7	156.2	155.6	155.0	154.5	153.9
82.5°	120.1	119.6	119.1	118.8	118.7	118.6	118.5	118.3
85°	70.7	70.4	70.1	69.7	69.1	68.5	68.0	67.4
87.5°	29.0	29.1	29.3	29.2	28.8	28.5	28.2	27.8
90°	12.7	13.6	14.3	14.9	15.4	15.8	16.3	16.8
92.5°	28.9	30.0	31.0	31.7	32.0	32.3	32.7	33.0
95°	56.1	57.1	58.2	58.9	59.3	59.6	59.9	60.1
97.5°	87.8	88.9	89.9	90.5	90.7	90.9	91.0	91.2
100°	109.8	111.2	112.6	113.5	113.9	114.1	114.4	114.7
102.5°	132.5	134.0	135.5	136.5	137.0	137.4	137.8	138.3
105°	169.1	170.0	171.0	171.6	172.1	172.6	173.1	173.5
107.5°	208.6	209.1	209.5	209.7	209.7	209.7	209.6	209.6
110°	236.0	236.5	237.0	237.1	237.0	236.8	236.7	236.5



TEST NUMBER: P333441-830

CATALOG NUMBER: S125DIW-S1090D770U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	263.5	263.7	263.9	263.9	263.6	263.3	263.1	262.8
115°	305.5	305.3	305.1	305.0	304.8	304.7	304.5	304.3
117.5°	347.4	347.5	347.7	347.4	346.9	346.2	345.5	345.0
120°	375.7	375.7	375.7	375.4	374.8	374.2	373.5	373.0
122.5°	403.5	403.3	403.2	402.9	402.4	401.9	401.4	401.0
125°	444.4	444.0	443.7	443.6	443.4	443.2	443.1	442.9
127.5°	485.0	484.8	484.7	484.5	484.2	483.8	483.5	483.2
130°	511.9	511.7	511.5	511.3	511.0	510.7	510.4	510.1
132.5°	537.6	537.4	537.3	537.0	536.6	536.1	535.7	535.3
135°	577.2	577.2	577.2	576.9	576.3	575.7	575.0	574.5
137.5°	615.9	616.0	616.2	615.9	615.1	614.3	613.6	612.7
140°	640.2	640.5	640.7	640.6	639.8	638.9	638.2	637.4
142.5°	663.9	664.1	664.3	664.0	663.3	662.5	661.7	660.9
145°	698.3	698.3	698.3	698.0	697.6	697.1	696.6	696.2
147.5°	730.1	730.5	730.8	730.5	729.4	728.4	727.4	726.3
150°	750.1	750.1	750.1	749.9	749.6	749.3	748.9	748.7
152.5°	768.7	769.1	769.5	769.4	768.8	768.3	767.7	767.1
155°	795.4	796.0	796.6	796.5	795.8	795.0	794.2	793.4
157.5°	818.5	819.1	819.7	819.5	818.5	817.5	816.4	815.4
160°	832.5	833.1	833.7	833.7	832.8	832.1	831.3	830.6
162.5°	845.6	846.3	847.1	847.1	846.1	845.2	844.3	843.4
165°	863.3	863.9	864.5	864.3	863.5	862.5	861.6	860.6
167.5°	876.4	877.3	878.2	878.2	877.2	876.3	875.3	874.3
170°	884.2	885.1	886.1	886.0	884.9	883.8	882.7	881.7
172.5°	889.8	890.7	891.6	891.6	890.7	889.7	888.7	887.8
175°	896.1	897.0	898.0	897.9	896.7	895.7	894.6	893.5
177.5°	898.9	899.7	900.4	900.3	899.5	898.6	897.8	896.8
180°	899.1	899.1	899.1	899.1	899.1	899.1	899.1	899.1

(END OF REPORT)