

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333691

Luminaire Tested: **S125RDIW-S850D1050U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333691
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1050U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6884.6 lumens
Efficiency: N/A
Efficacy: 130.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333691

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333691

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47					47			
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46					40				
2	89	82	76	70	81	75	70	66	63	60	56	52	50	47	42	40	39					34				
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33					29				
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29					25				
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25					22				
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22					19				
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20					17				
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18					15				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16					14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15					13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8881	8881	8881
5°	8901	8800	8854
10°	8834	8718	8718
15°	8729	8541	8471
20°	8594	8294	8194
25°	8437	8052	7874
30°	8240	7768	7520
35°	8041	7476	7123
40°	7854	7171	6734
45°	7626	6830	6308
50°	7398	6459	5865
55°	7133	6104	5391
60°	6868	5674	4883
65°	6554	5174	4300
70°	6197	4549	3707
75°	5702	3835	3084
80°	5021	3013	2589
85°	4231	2460	2312



TEST NUMBER: P333691

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.3	1.9
10°-20°	361.3	5.2
20°-30°	524.0	7.6
30°-40°	597.2	8.7
40°-50°	582.1	8.5
50°-60°	490.0	7.1
60°-70°	343.5	5.0
70°-80°	176.6	2.6
80°-90°	47.4	0.7
90°-100°	87.2	1.3
100°-110°	257.5	3.7
110°-120°	436.2	6.3
120°-130°	574.0	8.3
130°-140°	643.2	9.3
140°-150°	630.4	9.2
150°-160°	529.5	7.7
160°-170°	352.0	5.1
170°-180°	123.2	1.8
0°-30°	1014.6	14.7
0°-40°	1611.8	23.4
0°-60°	2683.9	39.0
0°-90°	3251.3	47.2
90°-120°	780.9	11.3
90°-150°	2628.6	38.2
90°-180°	3633.0	52.8
0°-180°	6884.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1373	1368	1357	1367	1366	130
15°	1306	1298	1277	1276	1267	368
25°	1184	1167	1130	1117	1105	545
35°	1020	994	948	919	904	638
45°	835	803	748	708	691	644
55°	634	599	542	497	479	566
65°	429	392	339	298	281	425
75°	228	197	154	132	124	242
85°	57	39	33	32	31	64
90°	1	9	16	21	24	6
95°	66	68	78	85	87	70
105°	231	236	242	248	251	247
115°	437	441	443	442	441	432
125°	637	643	644	642	641	571
135°	829	835	836	836	832	639
145°	1004	1008	1011	1011	1008	627
155°	1149	1149	1150	1154	1149	529
165°	1249	1247	1248	1252	1246	352
175°	1299	1295	1295	1300	1294	123
180°	1302	1302	1302	1302	1302	



TEST NUMBER: P333691

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1377.5	1377.0	1376.4	1375.9	1375.3	1374.1	1372.3	1370.4	1368.6	1366.7	1368.6
5°	1373.0	1372.1	1371.1	1370.2	1369.3	1367.6	1365.0	1362.5	1359.9	1357.4	1359.7
7.5°	1359.5	1358.6	1357.7	1356.8	1356.0	1354.0	1351.0	1347.9	1344.9	1341.8	1343.4
10°	1347.0	1346.3	1345.6	1344.9	1344.2	1342.3	1339.1	1335.8	1332.6	1329.4	1330.0
12.5°	1332.9	1332.0	1331.1	1330.3	1329.4	1326.8	1322.4	1318.1	1313.8	1309.4	1309.9
15°	1305.5	1304.1	1302.7	1301.3	1299.9	1296.8	1292.0	1287.1	1282.3	1277.4	1277.2
17.5°	1274.5	1272.4	1270.3	1268.2	1266.0	1261.9	1255.8	1249.7	1243.6	1237.5	1236.4
20°	1250.4	1248.1	1245.8	1243.5	1241.2	1236.3	1229.0	1221.6	1214.2	1206.8	1205.7
22.5°	1223.8	1221.5	1219.2	1216.9	1214.6	1209.6	1201.8	1194.1	1186.3	1178.6	1176.3
25°	1184.0	1180.5	1177.0	1173.6	1170.1	1164.1	1155.6	1147.0	1138.5	1130.0	1127.0
27.5°	1138.3	1134.1	1129.9	1125.7	1121.5	1114.8	1105.7	1096.5	1087.4	1078.2	1074.0
30°	1105.0	1100.6	1096.3	1091.9	1087.5	1080.4	1070.8	1061.1	1051.4	1041.7	1036.4
32.5°	1072.6	1067.5	1062.4	1057.3	1052.1	1044.6	1034.8	1024.9	1015.0	1005.1	999.3
35°	1019.9	1014.3	1008.8	1003.2	997.7	989.7	979.4	969.0	958.6	948.2	941.5
37.5°	968.1	961.4	954.7	947.9	941.2	932.5	921.8	911.0	900.3	889.6	881.6
40°	931.6	924.7	917.7	910.8	903.9	894.9	883.8	872.7	861.7	850.6	841.8
42.5°	893.4	886.3	879.2	872.0	864.9	855.7	844.2	832.8	821.3	809.9	801.5
45°	835.0	828.3	821.6	814.9	808.2	798.5	785.8	773.2	760.5	747.8	738.5
47.5°	774.6	767.5	760.4	753.4	746.3	736.4	723.6	710.8	698.0	685.2	675.7
50°	736.3	728.7	721.1	713.5	705.9	695.5	682.3	669.2	656.0	642.9	633.2
52.5°	694.8	687.0	679.2	671.4	663.6	653.5	641.1	628.7	616.2	603.8	593.4
55°	633.5	626.1	618.8	611.4	604.0	593.8	580.9	568.0	555.1	542.1	531.7
57.5°	571.6	563.7	555.8	547.9	540.1	529.9	517.4	504.9	492.5	480.0	469.9
60°	531.7	523.7	515.6	507.5	499.4	489.2	476.7	464.2	451.8	439.3	429.2
62.5°	489.4	481.7	474.0	466.2	458.5	448.4	435.7	423.1	410.4	397.8	388.4
65°	428.9	421.1	413.2	405.4	397.5	387.5	375.3	363.0	350.8	338.6	329.3
67.5°	368.9	361.0	353.2	345.4	337.5	327.7	316.0	304.3	292.6	280.8	272.4
70°	328.2	320.3	312.5	304.6	296.8	287.1	275.6	264.0	252.5	240.9	233.8
72.5°	288.3	280.6	273.0	265.3	257.7	248.4	237.6	226.8	216.0	205.2	198.6
75°	228.5	221.6	214.6	207.7	200.8	192.5	182.8	173.1	163.4	153.7	148.6
77.5°	169.1	163.5	158.0	152.5	146.9	140.3	132.5	124.8	117.0	109.3	105.7
80°	135.0	129.5	123.9	118.4	112.9	106.9	100.4	93.9	87.5	81.0	78.9
82.5°	101.8	96.8	91.8	86.8	81.8	77.1	72.7	68.3	63.8	59.4	58.4
85°	57.1	53.0	48.8	44.7	40.5	37.8	36.7	35.5	34.4	33.2	33.0
87.5°	19.3	18.4	17.4	16.5	15.6	15.2	15.3	15.4	15.6	15.7	15.9
90°	1.0	2.8	4.6	6.4	8.2	9.9	11.5	13.1	14.6	16.2	17.3
92.5°	24.5	25.8	27.0	28.3	29.6	31.2	33.1	35.0	37.0	38.9	40.4
95°	65.9	66.3	66.8	67.2	67.7	69.0	71.3	73.5	75.8	78.0	79.6
97.5°	109.4	109.6	109.8	110.0	110.2	111.8	114.9	118.0	121.1	124.2	125.7
100°	141.9	141.9	141.9	141.9	141.9	143.3	146.2	149.2	152.1	155.0	157.1
102.5°	176.7	177.6	178.5	179.4	180.3	181.5	183.0	184.5	186.0	187.5	189.7
105°	231.0	232.1	233.3	234.4	235.5	236.8	238.1	239.5	240.8	242.2	243.5
107.5°	291.0	292.1	293.3	294.4	295.5	296.6	297.6	298.7	299.7	300.7	301.4
110°	332.3	333.5	334.6	335.7	336.9	337.8	338.4	339.1	339.8	340.5	341.1



TEST NUMBER: P333691

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	374.5	375.1	375.7	376.3	376.8	377.6	378.4	379.3	380.1	381.0	381.3
115°	436.7	437.6	438.5	439.4	440.3	441.0	441.4	441.9	442.3	442.8	442.6
117.5°	499.1	499.5	499.9	500.3	500.8	501.2	501.6	502.0	502.4	502.8	503.0
120°	538.0	539.2	540.3	541.4	542.5	543.2	543.4	543.7	543.9	544.1	544.1
122.5°	580.2	580.6	581.0	581.4	581.8	582.3	582.9	583.5	584.1	584.7	584.5
125°	637.3	638.7	640.0	641.4	642.7	643.5	643.8	644.0	644.2	644.4	644.0
127.5°	698.1	698.9	699.7	700.4	701.2	701.7	702.0	702.3	702.5	702.8	702.6
130°	734.6	735.7	736.9	738.0	739.1	739.9	740.4	740.8	741.3	741.7	741.5
132.5°	771.1	772.9	774.8	776.6	778.5	779.4	779.3	779.2	779.1	779.0	778.8
135°	828.8	830.2	831.5	832.9	834.3	835.0	835.3	835.5	835.7	835.9	835.9
137.5°	883.2	884.5	885.8	887.1	888.4	889.3	889.8	890.3	890.8	891.3	891.5
140°	918.0	919.1	920.3	921.4	922.5	923.4	924.1	924.8	925.4	926.1	926.6
142.5°	952.9	953.8	954.8	955.7	956.7	957.6	958.4	959.3	960.1	961.0	961.2
145°	1004.1	1005.0	1005.9	1006.8	1007.7	1008.5	1009.2	1009.9	1010.6	1011.2	1011.2
147.5°	1051.6	1052.1	1052.6	1053.0	1053.5	1054.1	1054.6	1055.1	1055.7	1056.2	1056.8
150°	1083.2	1083.0	1082.7	1082.5	1082.3	1082.6	1083.5	1084.4	1085.3	1086.2	1086.2
152.5°	1109.1	1109.4	1109.7	1110.1	1110.4	1110.7	1111.1	1111.4	1111.8	1112.2	1112.7
155°	1149.0	1149.0	1149.0	1149.0	1149.0	1149.1	1149.4	1149.6	1149.8	1150.1	1151.0
157.5°	1184.7	1184.2	1183.7	1183.2	1182.7	1182.6	1182.8	1183.0	1183.3	1183.5	1184.4
160°	1205.8	1205.1	1204.4	1203.8	1203.1	1202.9	1203.1	1203.3	1203.5	1203.8	1204.7
162.5°	1224.4	1223.9	1223.4	1222.9	1222.4	1222.2	1222.3	1222.3	1222.4	1222.4	1223.5
165°	1249.4	1248.9	1248.4	1248.0	1247.5	1247.4	1247.7	1247.9	1248.1	1248.3	1249.2
167.5°	1270.4	1269.5	1268.6	1267.7	1266.8	1266.4	1266.4	1266.4	1266.4	1266.4	1267.7
170°	1281.8	1280.9	1280.0	1279.1	1278.2	1277.7	1277.7	1277.7	1277.7	1277.7	1279.1
172.5°	1289.9	1289.0	1288.1	1287.2	1286.3	1285.8	1285.8	1285.8	1285.8	1285.8	1287.2
175°	1299.0	1298.1	1297.2	1296.3	1295.4	1294.9	1294.9	1294.9	1294.9	1294.9	1296.3
177.5°	1303.7	1302.9	1302.2	1301.5	1300.8	1300.3	1300.1	1300.0	1299.8	1299.6	1300.7
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0



TEST NUMBER: P333691

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1370.4	1372.3	1374.1	1375.0	1374.8	1374.6	1374.4	1374.2
5°	1362.0	1364.3	1366.6	1367.6	1367.1	1366.6	1366.2	1365.7
7.5°	1345.1	1346.7	1348.3	1348.8	1348.3	1347.8	1347.3	1346.8
10°	1330.7	1331.4	1332.1	1332.1	1331.4	1330.7	1330.0	1329.4
12.5°	1310.4	1310.9	1311.4	1311.2	1310.1	1309.0	1308.0	1306.9
15°	1277.0	1276.7	1276.5	1275.4	1273.3	1271.2	1269.1	1267.0
17.5°	1235.2	1234.1	1232.9	1231.5	1229.8	1228.1	1226.4	1224.7
20°	1204.5	1203.3	1202.2	1200.6	1198.5	1196.4	1194.3	1192.3
22.5°	1174.0	1171.8	1169.5	1167.5	1165.8	1164.1	1162.4	1160.7
25°	1124.0	1121.0	1118.0	1115.2	1112.6	1110.1	1107.6	1105.0
27.5°	1069.8	1065.6	1061.4	1058.1	1055.7	1053.2	1050.8	1048.3
30°	1031.1	1025.8	1020.4	1016.8	1014.7	1012.6	1010.5	1008.4
32.5°	993.4	987.5	981.7	977.4	974.8	972.2	969.5	966.9
35°	934.8	928.1	921.4	916.5	913.2	910.0	906.8	903.5
37.5°	873.6	865.5	857.5	851.9	848.8	845.6	842.5	839.4
40°	833.0	824.3	815.5	809.7	807.0	804.2	801.4	798.7
42.5°	793.1	784.7	776.3	770.0	766.0	761.9	757.8	753.8
45°	729.3	720.1	710.8	704.5	701.0	697.6	694.1	690.6
47.5°	666.2	656.7	647.2	640.5	636.7	632.9	629.0	625.2
50°	623.5	613.8	604.1	597.5	594.1	590.6	587.1	583.7
52.5°	583.0	572.5	562.1	555.1	551.7	548.2	544.8	541.3
55°	521.4	511.0	500.6	493.5	489.9	486.2	482.5	478.8
57.5°	459.7	449.6	439.4	432.7	429.4	426.1	422.9	419.6
60°	419.0	408.8	398.7	391.9	388.4	385.0	381.5	378.0
62.5°	378.9	369.5	360.1	353.7	350.2	346.7	343.3	339.8
65°	320.1	310.9	301.6	295.3	291.8	288.4	284.9	281.4
67.5°	263.9	255.5	247.0	241.4	238.7	235.9	233.1	230.4
70°	226.6	219.5	212.3	207.4	204.6	201.8	199.1	196.3
72.5°	192.0	185.4	178.8	174.6	172.7	170.9	169.1	167.2
75°	143.6	138.5	133.4	130.1	128.4	126.8	125.2	123.6
77.5°	102.1	98.6	95.0	92.7	91.5	90.3	89.1	87.9
80°	76.9	74.8	72.7	71.4	71.0	70.5	70.0	69.6
82.5°	57.5	56.5	55.5	54.9	54.6	54.4	54.1	53.8
85°	32.8	32.5	32.3	32.1	31.8	31.6	31.4	31.2
87.5°	16.2	16.4	16.6	16.7	16.6	16.6	16.5	16.5
90°	18.5	19.6	20.7	21.6	22.3	23.0	23.6	24.3
92.5°	41.9	43.4	44.9	45.8	46.3	46.8	47.3	47.8
95°	81.2	82.7	84.3	85.3	85.8	86.2	86.7	87.1
97.5°	127.2	128.7	130.2	131.0	131.3	131.6	131.9	132.1
100°	159.1	161.1	163.1	164.4	164.8	165.3	165.7	166.2
102.5°	191.9	194.1	196.3	197.7	198.3	199.0	199.6	200.2
105°	244.9	246.2	247.6	248.6	249.3	249.9	250.6	251.3
107.5°	302.1	302.8	303.4	303.8	303.7	303.7	303.6	303.6
110°	341.8	342.5	343.2	343.4	343.2	342.9	342.7	342.5



TEST NUMBER: P333691

CATALOG NUMBER: S125RDIW-S850D1050U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	381.6	381.9	382.2	382.2	381.8	381.4	381.0	380.6
115°	442.3	442.1	441.9	441.7	441.4	441.2	441.0	440.8
117.5°	503.1	503.3	503.5	503.1	502.2	501.3	500.4	499.5
120°	544.1	544.1	544.1	543.7	542.8	541.9	541.0	540.1
122.5°	584.3	584.1	583.9	583.5	582.8	582.0	581.3	580.6
125°	643.5	643.1	642.6	642.3	642.1	641.8	641.6	641.4
127.5°	702.3	702.1	701.9	701.6	701.1	700.7	700.2	699.8
130°	741.3	741.0	740.8	740.5	740.0	739.6	739.1	738.7
132.5°	778.5	778.3	778.1	777.7	777.0	776.4	775.8	775.1
135°	835.9	835.9	835.9	835.5	834.6	833.7	832.8	831.9
137.5°	891.8	892.1	892.3	891.9	890.8	889.7	888.5	887.4
140°	927.0	927.5	927.9	927.6	926.5	925.3	924.2	923.1
142.5°	961.5	961.8	962.1	961.6	960.5	959.4	958.3	957.1
145°	1011.2	1011.2	1011.2	1010.9	1010.2	1009.5	1008.9	1008.2
147.5°	1057.3	1057.8	1058.4	1057.9	1056.4	1054.8	1053.3	1051.8
150°	1086.2	1086.2	1086.2	1086.0	1085.5	1085.1	1084.6	1084.2
152.5°	1113.2	1113.8	1114.3	1114.2	1113.4	1112.6	1111.7	1110.9
155°	1151.9	1152.8	1153.7	1153.5	1152.4	1151.3	1150.2	1149.0
157.5°	1185.3	1186.2	1187.1	1186.8	1185.3	1183.8	1182.3	1180.9
160°	1205.6	1206.5	1207.4	1207.2	1206.1	1205.0	1203.9	1202.7
162.5°	1224.6	1225.6	1226.7	1226.6	1225.3	1224.0	1222.7	1221.4
165°	1250.1	1251.0	1251.9	1251.7	1250.4	1249.0	1247.7	1246.3
167.5°	1269.1	1270.4	1271.8	1271.8	1270.4	1269.0	1267.6	1266.2
170°	1280.4	1281.8	1283.1	1283.0	1281.4	1279.9	1278.3	1276.7
172.5°	1288.5	1289.9	1291.2	1291.2	1289.8	1288.4	1287.0	1285.6
175°	1297.6	1299.0	1300.4	1300.2	1298.7	1297.1	1295.5	1293.9
177.5°	1301.8	1302.9	1303.9	1303.8	1302.6	1301.3	1300.1	1298.8
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0

(END OF REPORT)