

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333692

Luminaire Tested: **S125RDIW-S850D1340U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333692
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1340U835-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8644.3 lumens
Efficiency: N/A
Efficacy: 140.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38
1	95	91	88	84	86	83	80	77	68	65	63	53	52	51	40	39	39	33
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24
4	73	63	55	49	66	57	51	45	47	42	38	37	34	31	29	26	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	24	21	19	16
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8169	8169	8169	8169
5°	9398	8180	7224	8180
10°	10781	8138	6374	8138
15°	11645	8055	5666	8055
20°	12841	7958	5232	7958
25°	14860	7829	4855	7829
30°	16171	7694	4608	7694
35°	13640	7536	4380	7536
40°	9526	7254	4185	7254
45°	7067	6872	3993	6872
50°	5635	6475	3829	6475
55°	4782	5981	3683	5981
60°	4132	5540	3447	5540
65°	3681	5063	2968	5063
70°	3237	4638	2706	4638
75°	2800	4017	2540	4017
80°	2124	3381	2124	3381
85°	1771	2653	2001	2653



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	1.4
10°-20°	355.5	4.1
20°-30°	563.6	6.5
30°-40°	679.7	7.9
40°-50°	607.0	7.0
50°-60°	465.5	5.4
60°-70°	302.5	3.5
70°-80°	147.1	1.7
80°-90°	38.7	0.4
90°-100°	63.5	0.7
100°-110°	391.2	4.5
110°-120°	709.5	8.2
120°-130°	910.5	10.5
130°-140°	979.3	11.3
140°-150°	919.2	10.6
150°-160°	743.6	8.6
160°-170°	480.9	5.6
170°-180°	165.9	1.9
0°-30°	1040.4	12.0
0°-40°	1720.1	19.9
0°-60°	2792.5	32.3
0°-90°	3280.8	38.0
90°-120°	1164.1	13.5
90°-150°	3973.2	46.0
90°-180°	5364.0	62.1
0°-180°	8644.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1265	1265	1265	1265	1265	
5°	1450	1262	1114	1262	1450	145
15°	1742	1205	847	1205	1742	499
25°	2085	1099	681	1099	2085	957
35°	1730	956	556	956	1730	1045
45°	774	752	437	752	774	617
55°	425	531	327	531	425	385
65°	241	331	194	331	241	240
75°	112	161	102	161	112	119
85°	24	36	27	36	24	28
90°	31	1	31	1	31	15
95°	27	74	27	74	27	22
105°	384	381	384	381	384	348
115°	710	715	710	715	710	704
125°	1016	1016	1016	1016	1016	904
135°	1262	1268	1262	1268	1262	974
145°	1466	1470	1466	1470	1466	916
155°	1607	1618	1607	1618	1607	741
165°	1699	1708	1699	1708	1699	479
175°	1739	1747	1739	1747	1739	165
180°	1747	1747	1747	1747	1747	



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1330.5	1329.7	1331.4	1326.8	1327.2	1320.1	1320.1	1314.7	1307.7	1302.3	1299.8
5°	1449.7	1450.8	1448.7	1440.9	1435.7	1427.9	1419.1	1403.5	1390.5	1378.1	1368.2
7.5°	1572.5	1573.2	1566.4	1564.0	1550.9	1541.3	1521.7	1500.5	1481.7	1457.8	1439.6
10°	1643.9	1643.4	1636.2	1630.4	1619.0	1604.5	1585.3	1560.3	1537.0	1511.0	1486.1
12.5°	1685.5	1684.1	1681.8	1674.9	1664.3	1651.4	1635.1	1610.6	1581.8	1553.4	1524.3
15°	1741.6	1737.9	1731.2	1722.3	1707.3	1692.2	1674.1	1652.3	1624.7	1592.5	1565.5
17.5°	1810.9	1811.0	1800.7	1788.4	1767.9	1741.4	1713.3	1678.1	1640.7	1605.3	1576.5
20°	1868.3	1866.7	1856.3	1832.4	1809.1	1775.8	1743.6	1700.5	1654.8	1608.6	1572.8
22.5°	1950.5	1946.5	1935.7	1904.3	1868.1	1825.3	1776.0	1723.4	1668.1	1615.7	1568.7
25°	2085.3	2082.2	2060.9	2024.6	1973.7	1907.7	1843.3	1771.2	1691.7	1622.7	1565.5
27.5°	2177.5	2174.1	2158.3	2128.1	2081.2	2011.8	1924.6	1828.2	1729.0	1634.0	1551.6
30°	2168.4	2176.2	2174.1	2160.1	2124.8	2062.5	1982.0	1873.5	1755.6	1643.9	1545.8
32.5°	2037.9	2044.9	2063.2	2090.7	2092.8	2067.9	2007.7	1907.5	1785.5	1658.5	1541.2
35°	1730.1	1739.5	1774.8	1830.4	1903.0	1963.8	1976.3	1922.3	1812.7	1676.1	1534.4
37.5°	1330.1	1381.2	1410.9	1469.4	1579.2	1691.0	1798.5	1838.0	1791.4	1668.9	1523.3
40°	1129.9	1142.3	1195.3	1261.3	1353.7	1470.0	1623.2	1733.8	1737.4	1652.3	1505.8
42.5°	967.0	982.8	1019.2	1071.8	1151.0	1267.3	1425.4	1571.4	1639.0	1606.6	1483.0
45°	773.7	785.6	812.1	852.6	913.4	1009.4	1145.5	1314.2	1448.2	1500.6	1421.7
47.5°	635.6	642.0	665.1	695.9	740.9	810.9	916.2	1062.7	1223.4	1336.0	1324.9
50°	560.8	568.1	585.7	609.1	647.0	706.2	790.3	912.3	1078.0	1215.6	1243.1
52.5°	502.6	508.7	519.7	541.8	573.0	618.5	686.4	796.8	945.9	1092.2	1155.8
55°	424.7	428.9	437.7	450.2	475.1	507.8	566.5	642.8	763.3	910.8	1004.2
57.5°	360.6	362.6	368.3	379.8	397.0	420.9	463.3	528.0	614.4	747.2	850.3
60°	319.9	321.9	329.2	337.0	350.5	372.3	405.5	450.7	533.8	643.3	747.7
62.5°	287.5	288.7	291.8	299.6	311.4	328.3	354.4	391.3	457.4	553.6	652.2
65°	240.9	241.5	242.5	248.7	256.0	268.5	285.6	311.5	361.4	434.1	521.3
67.5°	196.3	197.0	200.6	202.8	210.4	216.9	227.0	246.9	282.0	331.0	398.8
70°	171.4	170.8	174.5	177.1	179.7	187.4	194.2	210.3	232.1	269.5	326.1
72.5°	148.1	146.7	148.3	149.2	152.7	158.0	164.7	174.6	191.4	217.1	260.5
75°	112.2	112.7	112.7	113.7	116.3	118.4	120.5	125.7	135.0	152.1	175.5
77.5°	78.7	77.9	80.1	80.4	81.9	84.2	86.0	88.1	91.9	99.0	111.0
80°	57.1	57.1	57.6	59.2	58.7	59.7	62.3	64.4	69.1	73.2	77.4
82.5°	43.8	43.4	43.9	44.2	44.1	45.2	46.1	46.5	48.3	50.4	53.3
85°	23.9	23.9	24.4	24.4	24.9	24.9	25.4	25.4	25.4	26.0	26.5
87.5°	15.4	14.8	14.2	14.0	14.2	14.8	14.1	13.4	13.2	12.9	12.9
90°	31.1	30.2	29.3	28.5	27.6	26.5	25.0	23.6	22.2	20.7	18.7
92.5°	29.0	28.6	28.2	27.8	27.4	26.5	25.0	23.6	22.2	20.7	18.9
95°	27.2	27.2	27.2	27.2	27.2	26.5	25.0	23.6	22.2	20.7	31.6
97.5°	27.2	27.2	27.2	27.2	27.2	31.2	39.4	47.5	55.6	63.7	85.3
100°	27.2	28.3	29.5	30.6	31.8	53.8	96.7	139.5	182.4	225.3	224.1
102.5°	162.9	182.4	202.0	221.6	241.1	255.0	263.1	271.2	279.3	287.4	286.7
105°	384.5	384.8	385.1	385.4	385.7	385.8	385.8	385.8	385.8	385.8	385.8
107.5°	484.8	485.6	486.5	487.3	488.2	488.6	488.6	488.5	488.4	488.4	487.8
110°	554.2	553.9	553.6	553.3	553.0	553.3	554.2	555.0	555.9	556.7	556.2



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	616.3	616.7	617.1	617.5	617.9	618.7	619.8	620.8	621.9	623.0	622.7
115°	709.5	711.2	713.0	714.7	716.4	717.9	719.0	720.2	721.3	722.5	722.2
117.5°	809.0	809.7	810.5	811.2	811.9	813.1	814.6	816.1	817.6	819.1	818.0
120°	870.1	871.5	872.9	874.4	875.8	876.8	877.4	878.0	878.6	879.1	878.3
122.5°	928.1	929.7	931.4	933.1	934.7	935.9	936.4	937.0	937.6	938.2	937.8
125°	1016.4	1017.2	1018.1	1019.0	1019.8	1020.8	1022.0	1023.1	1024.3	1025.4	1025.4
127.5°	1090.7	1092.8	1095.0	1097.1	1099.2	1100.6	1101.2	1101.9	1102.5	1103.1	1103.3
130°	1144.6	1146.0	1147.4	1148.9	1150.3	1151.5	1152.3	1153.2	1154.1	1154.9	1154.6
132.5°	1194.3	1195.7	1197.2	1198.6	1200.0	1200.8	1201.0	1201.2	1201.4	1201.5	1202.2
135°	1262.4	1264.1	1265.8	1267.6	1269.3	1270.4	1271.0	1271.6	1272.2	1272.7	1273.3
137.5°	1330.7	1332.2	1333.7	1335.2	1336.7	1337.4	1337.3	1337.2	1337.1	1337.0	1337.5
140°	1371.1	1372.9	1374.6	1376.3	1378.0	1378.6	1378.0	1377.5	1376.9	1376.3	1376.6
142.5°	1409.5	1411.2	1412.9	1414.6	1416.4	1417.2	1417.1	1416.9	1416.8	1416.7	1416.3
145°	1465.7	1467.4	1469.1	1470.8	1472.6	1473.3	1473.0	1472.7	1472.4	1472.1	1472.1
147.5°	1512.0	1514.1	1516.1	1518.2	1520.3	1521.2	1520.8	1520.5	1520.1	1519.8	1519.4
150°	1542.0	1544.3	1546.6	1548.9	1551.2	1552.1	1551.5	1551.0	1550.4	1549.8	1549.2
152.5°	1570.0	1572.1	1574.2	1576.2	1578.3	1579.0	1578.5	1577.9	1577.3	1576.7	1576.2
155°	1606.8	1609.1	1611.4	1613.7	1616.0	1616.7	1615.8	1615.0	1614.1	1613.3	1612.7
157.5°	1637.6	1639.9	1642.2	1644.5	1646.8	1647.5	1646.6	1645.7	1644.7	1643.8	1643.8
160°	1657.3	1659.6	1661.9	1664.2	1666.5	1667.1	1665.9	1664.8	1663.6	1662.5	1662.2
162.5°	1674.9	1677.4	1679.9	1682.5	1685.0	1685.5	1683.9	1682.2	1680.6	1679.0	1678.7
165°	1698.7	1701.0	1703.3	1705.6	1707.9	1708.2	1706.5	1704.7	1703.0	1701.3	1701.0
167.5°	1715.3	1717.9	1720.5	1723.0	1725.6	1725.9	1723.8	1721.8	1719.7	1717.6	1717.3
170°	1724.6	1727.2	1729.8	1732.4	1735.0	1735.1	1732.8	1730.5	1728.2	1725.9	1725.6
172.5°	1730.8	1733.4	1736.0	1738.6	1741.2	1741.4	1739.4	1737.3	1735.2	1733.1	1732.6
175°	1738.8	1741.4	1744.0	1746.6	1749.2	1749.3	1747.0	1744.7	1742.4	1740.1	1739.9
177.5°	1743.5	1745.3	1747.2	1749.0	1750.9	1751.0	1749.4	1747.8	1746.2	1744.5	1744.3
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1299.8	1296.9	1291.5	1286.5	1280.3	1274.9	1271.1	1266.6	1260.7	1253.7	1247.9
5°	1357.3	1345.9	1330.8	1317.9	1301.2	1288.3	1274.8	1261.8	1248.8	1232.2	1217.6
7.5°	1421.1	1397.5	1374.6	1345.7	1319.5	1296.1	1273.7	1251.0	1228.8	1205.2	1182.4
10°	1460.1	1431.6	1399.9	1363.5	1330.3	1298.6	1269.6	1241.0	1210.9	1184.4	1155.8
12.5°	1496.7	1459.8	1423.6	1377.7	1337.8	1299.1	1262.1	1226.5	1194.3	1159.9	1129.3
15°	1529.7	1493.4	1452.9	1396.8	1341.2	1294.5	1250.9	1204.7	1164.7	1126.3	1092.0
17.5°	1542.5	1504.4	1457.3	1403.4	1342.7	1283.9	1227.7	1177.0	1130.0	1085.2	1046.7
20°	1537.5	1500.6	1452.3	1400.9	1336.0	1274.8	1214.0	1157.9	1105.5	1058.2	1017.2
22.5°	1525.4	1487.3	1440.7	1386.4	1324.8	1259.8	1194.9	1135.1	1080.1	1031.2	986.5
25°	1507.4	1455.5	1407.7	1354.7	1296.0	1231.7	1164.7	1098.7	1040.1	990.2	941.4
27.5°	1488.6	1423.8	1363.0	1310.4	1248.4	1190.9	1126.4	1058.7	997.1	946.3	896.2
30°	1471.6	1398.9	1331.9	1272.2	1213.5	1159.0	1097.7	1031.7	968.4	916.0	865.1
32.5°	1450.4	1373.1	1299.5	1230.6	1174.0	1119.9	1064.5	1001.4	939.7	885.6	833.9
35°	1423.8	1325.1	1245.2	1171.9	1109.1	1056.7	1006.8	955.9	894.1	838.1	787.7
37.5°	1388.9	1276.9	1184.4	1104.7	1038.4	985.7	946.4	899.9	843.5	789.8	743.0
40°	1367.7	1242.0	1140.8	1061.9	992.3	936.7	899.9	860.4	809.0	758.6	711.9
42.5°	1339.5	1210.1	1096.8	1014.5	944.5	891.0	853.7	819.3	776.2	728.7	678.7
45°	1284.1	1148.1	1029.2	940.9	870.3	817.8	783.0	752.4	719.7	676.1	632.4
47.5°	1212.0	1083.4	958.9	862.6	793.4	744.7	711.0	686.8	663.4	626.3	583.9
50°	1154.3	1030.2	908.7	815.2	741.5	695.3	663.6	644.4	623.1	589.3	554.0
52.5°	1086.2	975.4	856.3	760.8	691.2	647.9	617.5	598.3	580.7	553.2	519.6
55°	978.8	881.7	772.6	685.9	622.1	578.4	549.4	531.2	520.8	497.4	471.0
57.5°	854.9	785.3	689.1	605.5	549.1	506.0	484.7	469.2	457.5	440.9	422.3
60°	768.5	719.7	633.5	554.0	502.1	461.1	441.9	428.9	418.0	404.0	389.4
62.5°	680.8	645.3	570.3	502.1	454.3	420.0	402.0	390.3	377.7	368.3	354.1
65°	563.4	531.7	479.8	426.3	382.2	354.6	341.7	331.3	323.5	313.1	303.2
67.5°	438.2	425.4	389.5	352.7	321.0	296.5	285.3	278.0	268.7	262.4	255.7
70°	361.4	355.2	329.7	305.3	275.7	259.1	248.7	245.6	234.2	228.0	223.3
72.5°	293.3	290.4	275.7	258.8	237.9	223.4	213.8	210.3	203.0	198.0	195.0
75°	200.9	202.0	199.4	188.5	180.7	171.4	163.0	161.0	155.8	151.6	149.0
77.5°	127.1	132.4	132.6	132.1	129.0	123.3	119.8	118.3	113.2	111.6	111.0
80°	87.2	92.9	98.1	97.6	96.6	95.0	92.4	90.9	88.3	86.7	85.7
82.5°	58.2	63.5	67.8	70.6	70.4	68.9	67.1	66.4	65.8	64.7	64.5
85°	27.5	28.6	30.1	33.8	36.3	36.9	36.3	35.8	34.3	34.8	35.3
87.5°	12.9	12.5	12.5	12.1	11.2	12.8	13.6	13.6	13.2	12.8	12.4
90°	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	17.1	15.4	13.6	13.5	15.1	16.7	18.3	19.9	18.3	16.7	15.1
95°	42.6	53.5	64.4	70.3	71.2	72.1	72.9	73.8	72.9	72.1	71.2
97.5°	107.0	128.6	150.2	160.3	158.7	157.2	155.6	154.1	155.6	157.2	158.7
100°	223.0	221.8	220.7	219.7	218.8	217.9	217.1	216.2	217.1	217.9	218.8
102.5°	286.1	285.4	284.7	283.8	282.7	281.6	280.5	279.4	280.5	281.6	282.7
105°	385.8	385.8	385.8	385.3	384.1	383.0	381.8	380.7	381.8	383.0	384.1
107.5°	487.2	486.7	486.1	485.8	485.8	485.8	485.8	485.8	485.8	485.8	485.8
110°	555.6	555.0	554.4	554.2	554.2	554.2	554.2	554.2	554.2	554.2	554.2



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	622.3	622.0	621.7	621.1	620.4	619.8	619.1	618.4	619.1	619.8	620.4
115°	721.9	721.6	721.3	720.5	719.0	717.6	716.1	714.7	716.1	717.6	719.0
117.5°	816.9	815.8	814.7	814.2	814.2	814.3	814.3	814.4	814.3	814.3	814.2
120°	877.4	876.5	875.7	875.4	875.7	876.0	876.3	876.5	876.3	876.0	875.7
122.5°	937.4	937.0	936.6	935.8	934.7	933.6	932.5	931.4	932.5	933.6	934.7
125°	1025.4	1025.4	1025.4	1024.4	1022.4	1020.4	1018.4	1016.4	1018.4	1020.4	1022.4
127.5°	1103.5	1103.6	1103.8	1103.2	1101.7	1100.3	1098.9	1097.4	1098.9	1100.3	1101.7
130°	1154.3	1154.1	1153.8	1152.9	1151.5	1150.0	1148.6	1147.1	1148.6	1150.0	1151.5
132.5°	1202.8	1203.4	1204.1	1203.5	1201.9	1200.2	1198.5	1196.9	1198.5	1200.2	1201.9
135°	1273.9	1274.5	1275.0	1274.5	1272.7	1271.0	1269.3	1267.6	1269.3	1271.0	1272.7
137.5°	1338.0	1338.5	1339.0	1338.5	1337.0	1335.5	1334.0	1332.6	1334.0	1335.5	1337.0
140°	1376.9	1377.2	1377.5	1377.3	1376.7	1376.2	1375.6	1375.0	1375.6	1376.2	1376.7
142.5°	1415.9	1415.5	1415.1	1414.7	1414.4	1414.0	1413.7	1413.3	1413.7	1414.0	1414.4
145°	1472.1	1472.1	1472.1	1471.8	1471.3	1470.7	1470.1	1469.5	1470.1	1470.7	1471.3
147.5°	1519.1	1518.7	1518.4	1518.3	1518.4	1518.5	1518.6	1518.7	1518.6	1518.5	1518.4
150°	1548.7	1548.1	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8	1549.2	1548.7	1548.1
152.5°	1575.6	1575.0	1574.4	1574.8	1576.1	1577.3	1578.6	1579.8	1578.6	1577.3	1576.1
155°	1612.1	1611.5	1611.0	1611.5	1613.3	1615.0	1616.7	1618.4	1616.7	1615.0	1613.3
157.5°	1643.7	1643.6	1643.6	1644.1	1645.1	1646.1	1647.2	1648.2	1647.2	1646.1	1645.1
160°	1661.9	1661.6	1661.3	1662.0	1663.7	1665.5	1667.2	1668.9	1667.2	1665.5	1663.7
162.5°	1678.5	1678.2	1677.9	1678.6	1680.3	1682.0	1683.8	1685.5	1683.8	1682.0	1680.3
165°	1700.7	1700.4	1700.1	1700.9	1702.6	1704.3	1706.0	1707.8	1706.0	1704.3	1702.6
167.5°	1717.0	1716.7	1716.5	1717.2	1719.0	1720.8	1722.6	1724.3	1722.6	1720.8	1719.0
170°	1725.3	1725.0	1724.7	1725.6	1727.6	1729.6	1731.7	1733.7	1731.7	1729.6	1727.6
172.5°	1732.1	1731.6	1731.1	1731.8	1733.8	1735.9	1737.9	1739.9	1737.9	1735.9	1733.8
175°	1739.6	1739.3	1739.0	1739.7	1741.4	1743.2	1744.9	1746.6	1744.9	1743.2	1741.4
177.5°	1744.1	1743.9	1743.6	1744.2	1745.6	1747.0	1748.3	1749.7	1748.3	1747.0	1745.6
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1243.7	1237.9	1233.7	1225.4	1219.6	1217.1	1212.6	1211.3	1215.9	1212.6	1212.1
5°	1206.7	1191.7	1179.7	1167.8	1154.8	1146.5	1134.0	1132.0	1128.8	1124.2	1123.1
7.5°	1162.4	1142.8	1127.4	1107.7	1090.5	1076.7	1061.1	1053.8	1049.7	1043.7	1035.6
10°	1132.5	1109.1	1088.3	1068.6	1047.3	1030.2	1014.6	1002.7	994.9	987.6	984.5
12.5°	1103.0	1079.2	1052.6	1028.7	1005.0	985.7	968.5	960.7	952.1	943.6	936.3
15°	1057.2	1025.5	996.4	968.9	948.7	927.9	911.3	899.9	886.9	883.2	869.2
17.5°	1008.6	977.5	943.5	914.5	891.0	868.2	849.9	836.9	827.2	813.8	807.3
20°	978.3	941.4	908.2	881.7	855.7	828.7	810.0	799.1	789.8	778.9	773.7
22.5°	945.9	909.8	875.8	844.7	818.3	791.8	778.5	767.1	756.5	746.5	739.6
25°	898.3	862.0	826.1	793.9	766.4	747.2	731.6	718.6	712.9	703.1	695.8
27.5°	851.3	812.6	775.4	743.4	721.8	702.8	690.0	679.7	669.4	660.8	654.5
30°	820.9	781.5	741.0	715.5	692.7	674.5	660.5	650.6	642.8	635.0	630.4
32.5°	790.6	749.9	714.0	686.4	664.8	649.2	634.7	625.3	617.1	608.5	603.0
35°	742.0	700.5	671.4	644.4	623.1	608.6	598.7	585.2	578.4	572.2	566.5
37.5°	696.8	658.2	626.7	603.1	584.6	570.1	557.4	550.1	541.8	536.2	531.4
40°	663.6	628.3	599.7	574.8	561.3	545.2	533.3	523.9	517.7	510.4	505.2
42.5°	633.7	600.9	573.1	550.7	533.9	520.3	508.8	499.4	491.5	486.3	482.0
45°	591.4	558.7	531.7	510.9	495.4	482.4	470.4	465.8	455.4	449.2	447.1
47.5°	547.7	518.4	492.4	473.2	457.3	445.0	433.8	424.2	418.5	412.4	409.1
50°	518.2	490.2	465.8	447.1	431.5	418.0	407.6	401.4	393.6	387.9	383.7
52.5°	488.7	462.8	438.4	420.5	407.0	393.5	381.9	375.6	368.3	364.6	361.7
55°	446.6	419.0	398.3	380.6	366.6	354.1	343.2	337.0	332.3	328.7	327.6
57.5°	398.8	377.0	357.7	341.8	327.2	315.5	305.9	300.0	295.9	295.3	292.2
60°	367.6	347.9	330.2	313.1	300.6	289.7	281.4	274.7	270.5	270.0	269.0
62.5°	336.5	317.6	301.2	286.1	274.9	264.4	256.5	248.9	246.4	243.8	241.6
65°	290.3	273.1	259.6	247.7	235.7	226.9	219.1	214.4	208.7	205.6	199.9
67.5°	244.9	231.6	218.6	208.5	199.2	190.8	184.3	177.4	173.5	171.0	166.9
70°	215.0	204.6	191.6	180.7	173.4	166.7	161.5	153.7	151.1	149.0	146.9
72.5°	186.7	177.6	166.7	157.9	150.6	144.2	138.2	134.6	132.0	129.9	128.7
75°	146.9	138.1	128.8	122.5	117.4	112.2	109.0	106.4	105.4	104.9	102.8
77.5°	107.9	103.2	95.7	90.8	87.3	85.3	82.5	81.1	81.0	78.7	78.0
80°	82.6	80.0	73.7	71.7	69.1	67.0	65.4	62.8	60.2	59.2	57.6
82.5°	61.4	58.8	56.3	53.0	50.8	49.5	48.0	47.0	47.4	45.9	45.2
85°	32.7	30.1	29.1	28.6	27.5	28.6	28.0	27.5	27.0	26.5	27.0
87.5°	12.5	12.9	12.9	14.1	13.3	14.1	14.4	14.3	14.6	14.8	14.7
90°	10.5	12.7	14.7	16.7	18.7	20.7	22.2	23.6	25.0	26.5	27.6
92.5°	13.5	13.6	15.4	17.1	18.9	20.7	22.2	23.6	25.0	26.5	27.4
95°	70.3	64.4	53.5	42.6	31.6	20.7	22.2	23.6	25.0	26.5	27.2
97.5°	160.3	150.2	128.6	107.0	85.3	63.7	55.6	47.5	39.4	31.2	27.2
100°	219.7	220.7	221.8	223.0	224.1	225.3	182.4	139.5	96.7	53.8	31.8
102.5°	283.8	284.7	285.4	286.1	286.7	287.4	279.3	271.2	263.1	255.0	241.1
105°	385.3	385.8	385.8	385.8	385.8	385.8	385.8	385.8	385.8	385.8	385.7
107.5°	485.8	486.1	486.7	487.2	487.8	488.4	488.4	488.5	488.6	488.6	488.2
110°	554.2	554.4	555.0	555.6	556.2	556.7	555.9	555.0	554.2	553.3	553.0



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	621.1	621.7	622.0	622.3	622.7	623.0	621.9	620.8	619.8	618.7	617.9
115°	720.5	721.3	721.6	721.9	722.2	722.5	721.3	720.2	719.0	717.9	716.4
117.5°	814.2	814.7	815.8	816.9	818.0	819.1	817.6	816.1	814.6	813.1	811.9
120°	875.4	875.7	876.5	877.4	878.3	879.1	878.6	878.0	877.4	876.8	875.8
122.5°	935.8	936.6	937.0	937.4	937.8	938.2	937.6	937.0	936.4	935.9	934.7
125°	1024.4	1025.4	1025.4	1025.4	1025.4	1025.4	1024.3	1023.1	1022.0	1020.8	1019.8
127.5°	1103.2	1103.8	1103.6	1103.5	1103.3	1103.1	1102.5	1101.9	1101.2	1100.6	1099.2
130°	1152.9	1153.8	1154.1	1154.3	1154.6	1154.9	1154.1	1153.2	1152.3	1151.5	1150.3
132.5°	1203.5	1204.1	1203.4	1202.8	1202.2	1201.5	1201.4	1201.2	1201.0	1200.8	1200.0
135°	1274.5	1275.0	1274.5	1273.9	1273.3	1272.7	1272.2	1271.6	1271.0	1270.4	1269.3
137.5°	1338.5	1339.0	1338.5	1338.0	1337.5	1337.0	1337.1	1337.2	1337.3	1337.4	1336.7
140°	1377.3	1377.5	1377.2	1376.9	1376.6	1376.3	1376.9	1377.5	1378.0	1378.6	1378.0
142.5°	1414.7	1415.1	1415.5	1415.9	1416.3	1416.7	1416.8	1416.9	1417.1	1417.2	1416.4
145°	1471.8	1472.1	1472.1	1472.1	1472.1	1472.1	1472.4	1472.7	1473.0	1473.3	1472.6
147.5°	1518.3	1518.4	1518.7	1519.1	1519.4	1519.8	1520.1	1520.5	1520.8	1521.2	1520.3
150°	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8	1550.4	1551.0	1551.5	1552.1	1551.2
152.5°	1574.8	1574.4	1575.0	1575.6	1576.2	1576.7	1577.3	1577.9	1578.5	1579.0	1578.3
155°	1611.5	1611.0	1611.5	1612.1	1612.7	1613.3	1614.1	1615.0	1615.8	1616.7	1616.0
157.5°	1644.1	1643.6	1643.6	1643.7	1643.8	1643.8	1644.7	1645.7	1646.6	1647.5	1646.8
160°	1662.0	1661.3	1661.6	1661.9	1662.2	1662.5	1663.6	1664.8	1665.9	1667.1	1666.5
162.5°	1678.6	1677.9	1678.2	1678.5	1678.7	1679.0	1680.6	1682.2	1683.9	1685.5	1685.0
165°	1700.9	1700.1	1700.4	1700.7	1701.0	1701.3	1703.0	1704.7	1706.5	1708.2	1707.9
167.5°	1717.2	1716.5	1716.7	1717.0	1717.3	1717.6	1719.7	1721.8	1723.8	1725.9	1725.6
170°	1725.6	1724.7	1725.0	1725.3	1725.6	1725.9	1728.2	1730.5	1732.8	1735.1	1735.0
172.5°	1731.8	1731.1	1731.6	1732.1	1732.6	1733.1	1735.2	1737.3	1739.4	1741.4	1741.2
175°	1739.7	1739.0	1739.3	1739.6	1739.9	1740.1	1742.4	1744.7	1747.0	1749.3	1749.2
177.5°	1744.2	1743.6	1743.9	1744.1	1744.3	1744.5	1746.2	1747.8	1749.4	1751.0	1750.9
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1211.7	1207.2	1205.9	1207.6	1205.9	1207.2	1211.7	1212.1	1212.6	1215.9	1211.3
5°	1117.9	1112.8	1115.3	1114.3	1115.3	1112.8	1117.9	1123.1	1124.2	1128.8	1132.0
7.5°	1035.5	1029.0	1022.2	1024.4	1022.2	1029.0	1035.5	1035.6	1043.7	1049.7	1053.8
10°	977.7	972.6	969.4	972.0	969.4	972.6	977.7	984.5	987.6	994.9	1002.7
12.5°	929.1	926.0	923.3	922.2	923.3	926.0	929.1	936.3	943.6	952.1	960.7
15°	863.0	856.8	854.2	847.4	854.2	856.8	863.0	869.2	883.2	886.9	899.9
17.5°	802.0	800.0	793.2	790.3	793.2	800.0	802.0	807.3	813.8	827.2	836.9
20°	765.9	763.8	757.1	761.2	757.1	763.8	765.9	773.7	778.9	789.8	799.1
22.5°	736.0	731.4	729.2	728.0	729.2	731.4	736.0	739.6	746.5	756.5	767.1
25°	693.7	687.0	684.4	681.3	684.4	687.0	693.7	695.8	703.1	712.9	718.6
27.5°	651.6	647.9	644.5	643.7	644.5	647.9	651.6	654.5	660.8	669.4	679.7
30°	624.1	620.5	617.9	617.9	617.9	620.5	624.1	630.4	635.0	642.8	650.6
32.5°	599.6	596.8	594.2	593.8	594.2	596.8	599.6	603.0	608.5	617.1	625.3
35°	563.9	559.8	558.7	555.6	558.7	559.8	563.9	566.5	572.2	578.4	585.2
37.5°	526.8	523.4	523.3	523.0	523.3	523.4	526.8	531.4	536.2	541.8	550.1
40°	503.2	500.6	500.0	496.4	500.0	500.6	503.2	505.2	510.4	517.7	523.9
42.5°	477.8	476.5	474.7	473.1	474.7	476.5	477.8	482.0	486.3	491.5	499.4
45°	443.4	439.8	439.8	437.2	439.8	439.8	443.4	447.1	449.2	455.4	465.8
47.5°	407.9	405.1	405.4	402.7	405.4	405.1	407.9	409.1	412.4	418.5	424.2
50°	384.2	382.7	382.2	381.1	382.2	382.7	384.2	383.7	387.9	393.6	401.4
52.5°	360.6	359.8	361.8	359.5	361.8	359.8	360.6	361.7	364.6	368.3	375.6
55°	328.7	327.1	330.2	327.1	330.2	327.1	328.7	327.6	328.7	332.3	337.0
57.5°	292.0	290.6	293.4	291.8	293.4	290.6	292.0	292.2	295.3	295.9	300.0
60°	267.9	264.8	266.4	266.9	266.4	264.8	267.9	269.0	270.0	270.5	274.7
62.5°	239.3	237.4	238.5	236.2	238.5	237.4	239.3	241.6	243.8	246.4	248.9
65°	198.9	197.3	195.2	194.2	195.2	197.3	198.9	199.9	205.6	208.7	214.4
67.5°	167.1	163.4	163.3	164.1	163.3	163.4	167.1	166.9	171.0	173.5	177.4
70°	143.8	143.8	143.3	143.3	143.3	143.8	143.8	146.9	149.0	151.1	153.7
72.5°	127.6	127.2	126.3	125.9	126.3	127.2	127.6	128.7	129.9	132.0	134.6
75°	102.8	103.3	102.3	101.8	102.3	103.3	102.8	102.8	104.9	105.4	106.4
77.5°	75.9	73.7	74.9	73.7	74.9	73.7	75.9	78.0	78.7	81.0	81.1
80°	57.6	57.1	58.7	57.1	58.7	57.1	57.6	57.6	59.2	60.2	62.8
82.5°	45.6	45.1	45.8	44.7	45.8	45.1	45.6	45.2	45.9	47.4	47.0
85°	27.5	27.0	26.5	27.0	26.5	27.0	27.5	27.0	26.5	27.0	27.5
87.5°	15.3	15.0	15.2	15.4	15.2	15.0	15.3	14.7	14.8	14.6	14.3
90°	28.5	29.3	30.2	31.1	30.2	29.3	28.5	27.6	26.5	25.0	23.6
92.5°	27.8	28.2	28.6	29.0	28.6	28.2	27.8	27.4	26.5	25.0	23.6
95°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	26.5	25.0	23.6
97.5°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	31.2	39.4	47.5
100°	30.6	29.5	28.3	27.2	28.3	29.5	30.6	31.8	53.8	96.7	139.5
102.5°	221.6	202.0	182.4	162.9	182.4	202.0	221.6	241.1	255.0	263.1	271.2
105°	385.4	385.1	384.8	384.5	384.8	385.1	385.4	385.7	385.8	385.8	385.8
107.5°	487.3	486.5	485.6	484.8	485.6	486.5	487.3	488.2	488.6	488.6	488.5
110°	553.3	553.6	553.9	554.2	553.9	553.6	553.3	553.0	553.3	554.2	555.0



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	617.5	617.1	616.7	616.3	616.7	617.1	617.5	617.9	618.7	619.8	620.8
115°	714.7	713.0	711.2	709.5	711.2	713.0	714.7	716.4	717.9	719.0	720.2
117.5°	811.2	810.5	809.7	809.0	809.7	810.5	811.2	811.9	813.1	814.6	816.1
120°	874.4	872.9	871.5	870.1	871.5	872.9	874.4	875.8	876.8	877.4	878.0
122.5°	933.1	931.4	929.7	928.1	929.7	931.4	933.1	934.7	935.9	936.4	937.0
125°	1019.0	1018.1	1017.2	1016.4	1017.2	1018.1	1019.0	1019.8	1020.8	1022.0	1023.1
127.5°	1097.1	1095.0	1092.8	1090.7	1092.8	1095.0	1097.1	1099.2	1100.6	1101.2	1101.9
130°	1148.9	1147.4	1146.0	1144.6	1146.0	1147.4	1148.9	1150.3	1151.5	1152.3	1153.2
132.5°	1198.6	1197.2	1195.7	1194.3	1195.7	1197.2	1198.6	1200.0	1200.8	1201.0	1201.2
135°	1267.6	1265.8	1264.1	1262.4	1264.1	1265.8	1267.6	1269.3	1270.4	1271.0	1271.6
137.5°	1335.2	1333.7	1332.2	1330.7	1332.2	1333.7	1335.2	1336.7	1337.4	1337.3	1337.2
140°	1376.3	1374.6	1372.9	1371.1	1372.9	1374.6	1376.3	1378.0	1378.6	1378.0	1377.5
142.5°	1414.6	1412.9	1411.2	1409.5	1411.2	1412.9	1414.6	1416.4	1417.2	1417.1	1416.9
145°	1470.8	1469.1	1467.4	1465.7	1467.4	1469.1	1470.8	1472.6	1473.3	1473.0	1472.7
147.5°	1518.2	1516.1	1514.1	1512.0	1514.1	1516.1	1518.2	1520.3	1521.2	1520.8	1520.5
150°	1548.9	1546.6	1544.3	1542.0	1544.3	1546.6	1548.9	1551.2	1552.1	1551.5	1551.0
152.5°	1576.2	1574.2	1572.1	1570.0	1572.1	1574.2	1576.2	1578.3	1579.0	1578.5	1577.9
155°	1613.7	1611.4	1609.1	1606.8	1609.1	1611.4	1613.7	1616.0	1616.7	1615.8	1615.0
157.5°	1644.5	1642.2	1639.9	1637.6	1639.9	1642.2	1644.5	1646.8	1647.5	1646.6	1645.7
160°	1664.2	1661.9	1659.6	1657.3	1659.6	1661.9	1664.2	1666.5	1667.1	1665.9	1664.8
162.5°	1682.5	1679.9	1677.4	1674.9	1677.4	1679.9	1682.5	1685.0	1685.5	1683.9	1682.2
165°	1705.6	1703.3	1701.0	1698.7	1701.0	1703.3	1705.6	1707.9	1708.2	1706.5	1704.7
167.5°	1723.0	1720.5	1717.9	1715.3	1717.9	1720.5	1723.0	1725.6	1725.9	1723.8	1721.8
170°	1732.4	1729.8	1727.2	1724.6	1727.2	1729.8	1732.4	1735.0	1735.1	1732.8	1730.5
172.5°	1738.6	1736.0	1733.4	1730.8	1733.4	1736.0	1738.6	1741.2	1741.4	1739.4	1737.3
175°	1746.6	1744.0	1741.4	1738.8	1741.4	1744.0	1746.6	1749.2	1749.3	1747.0	1744.7
177.5°	1749.0	1747.2	1745.3	1743.5	1745.3	1747.2	1749.0	1750.9	1751.0	1749.4	1747.8
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1212.6	1217.1	1219.6	1225.4	1233.7	1237.9	1243.7	1247.9	1253.7	1260.7	1266.6
5°	1134.0	1146.5	1154.8	1167.8	1179.7	1191.7	1206.7	1217.6	1232.2	1248.8	1261.8
7.5°	1061.1	1076.7	1090.5	1107.7	1127.4	1142.8	1162.4	1182.4	1205.2	1228.8	1251.0
10°	1014.6	1030.2	1047.3	1068.6	1088.3	1109.1	1132.5	1155.8	1184.4	1210.9	1241.0
12.5°	968.5	985.7	1005.0	1028.7	1052.6	1079.2	1103.0	1129.3	1159.9	1194.3	1226.5
15°	911.3	927.9	948.7	968.9	996.4	1025.5	1057.2	1092.0	1126.3	1164.7	1204.7
17.5°	849.9	868.2	891.0	914.5	943.5	977.5	1008.6	1046.7	1085.2	1130.0	1177.0
20°	810.0	828.7	855.7	881.7	908.2	941.4	978.3	1017.2	1058.2	1105.5	1157.9
22.5°	778.5	791.8	818.3	844.7	875.8	909.8	945.9	986.5	1031.2	1080.1	1135.1
25°	731.6	747.2	766.4	793.9	826.1	862.0	898.3	941.4	990.2	1040.1	1098.7
27.5°	690.0	702.8	721.8	743.4	775.4	812.6	851.3	896.2	946.3	997.1	1058.7
30°	660.5	674.5	692.7	715.5	741.0	781.5	820.9	865.1	916.0	968.4	1031.7
32.5°	634.7	649.2	664.8	686.4	714.0	749.9	790.6	833.9	885.6	939.7	1001.4
35°	598.7	608.6	623.1	644.4	671.4	700.5	742.0	787.7	838.1	894.1	955.9
37.5°	557.4	570.1	584.6	603.1	626.7	658.2	696.8	743.0	789.8	843.5	899.9
40°	533.3	545.2	561.3	574.8	599.7	628.3	663.6	711.9	758.6	809.0	860.4
42.5°	508.8	520.3	533.9	550.7	573.1	600.9	633.7	678.7	728.7	776.2	819.3
45°	470.4	482.4	495.4	510.9	531.7	558.7	591.4	632.4	676.1	719.7	752.4
47.5°	433.8	445.0	457.3	473.2	492.4	518.4	547.7	583.9	626.3	663.4	686.8
50°	407.6	418.0	431.5	447.1	465.8	490.2	518.2	554.0	589.3	623.1	644.4
52.5°	381.9	393.5	407.0	420.5	438.4	462.8	488.7	519.6	553.2	580.7	598.3
55°	343.2	354.1	366.6	380.6	398.3	419.0	446.6	471.0	497.4	520.8	531.2
57.5°	305.9	315.5	327.2	341.8	357.7	377.0	398.8	422.3	440.9	457.5	469.2
60°	281.4	289.7	300.6	313.1	330.2	347.9	367.6	389.4	404.0	418.0	428.9
62.5°	256.5	264.4	274.9	286.1	301.2	317.6	336.5	354.1	368.3	377.7	390.3
65°	219.1	226.9	235.7	247.7	259.6	273.1	290.3	303.2	313.1	323.5	331.3
67.5°	184.3	190.8	199.2	208.5	218.6	231.6	244.9	255.7	262.4	268.7	278.0
70°	161.5	166.7	173.4	180.7	191.6	204.6	215.0	223.3	228.0	234.2	245.6
72.5°	138.2	144.2	150.6	157.9	166.7	177.6	186.7	195.0	198.0	203.0	210.3
75°	109.0	112.2	117.4	122.5	128.8	138.1	146.9	149.0	151.6	155.8	161.0
77.5°	82.5	85.3	87.3	90.8	95.7	103.2	107.9	111.0	111.6	113.2	118.3
80°	65.4	67.0	69.1	71.7	73.7	80.0	82.6	85.7	86.7	88.3	90.9
82.5°	48.0	49.5	50.8	53.0	56.3	58.8	61.4	64.5	64.7	65.8	66.4
85°	28.0	28.6	27.5	28.6	29.1	30.1	32.7	35.3	34.8	34.3	35.8
87.5°	14.4	14.1	13.3	14.1	12.9	12.9	12.5	12.4	12.8	13.2	13.6
90°	22.2	20.7	18.7	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3
92.5°	22.2	20.7	18.9	17.1	15.4	13.6	13.5	15.1	16.7	18.3	19.9
95°	22.2	20.7	31.6	42.6	53.5	64.4	70.3	71.2	72.1	72.9	73.8
97.5°	55.6	63.7	85.3	107.0	128.6	150.2	160.3	158.7	157.2	155.6	154.1
100°	182.4	225.3	224.1	223.0	221.8	220.7	219.7	218.8	217.9	217.1	216.2
102.5°	279.3	287.4	286.7	286.1	285.4	284.7	283.8	282.7	281.6	280.5	279.4
105°	385.8	385.8	385.8	385.8	385.8	385.8	385.3	384.1	383.0	381.8	380.7
107.5°	488.4	488.4	487.8	487.2	486.7	486.1	485.8	485.8	485.8	485.8	485.8
110°	555.9	556.7	556.2	555.6	555.0	554.4	554.2	554.2	554.2	554.2	554.2



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	621.9	623.0	622.7	622.3	622.0	621.7	621.1	620.4	619.8	619.1	618.4
115°	721.3	722.5	722.2	721.9	721.6	721.3	720.5	719.0	717.6	716.1	714.7
117.5°	817.6	819.1	818.0	816.9	815.8	814.7	814.2	814.2	814.3	814.3	814.4
120°	878.6	879.1	878.3	877.4	876.5	875.7	875.4	875.7	876.0	876.3	876.5
122.5°	937.6	938.2	937.8	937.4	937.0	936.6	935.8	934.7	933.6	932.5	931.4
125°	1024.3	1025.4	1025.4	1025.4	1025.4	1025.4	1024.4	1022.4	1020.4	1018.4	1016.4
127.5°	1102.5	1103.1	1103.3	1103.5	1103.6	1103.8	1103.2	1101.7	1100.3	1098.9	1097.4
130°	1154.1	1154.9	1154.6	1154.3	1154.1	1153.8	1152.9	1151.5	1150.0	1148.6	1147.1
132.5°	1201.4	1201.5	1202.2	1202.8	1203.4	1204.1	1203.5	1201.9	1200.2	1198.5	1196.9
135°	1272.2	1272.7	1273.3	1273.9	1274.5	1275.0	1274.5	1272.7	1271.0	1269.3	1267.6
137.5°	1337.1	1337.0	1337.5	1338.0	1338.5	1339.0	1338.5	1337.0	1335.5	1334.0	1332.6
140°	1376.9	1376.3	1376.6	1376.9	1377.2	1377.5	1377.3	1376.7	1376.2	1375.6	1375.0
142.5°	1416.8	1416.7	1416.3	1415.9	1415.5	1415.1	1414.7	1414.4	1414.0	1413.7	1413.3
145°	1472.4	1472.1	1472.1	1472.1	1472.1	1472.1	1471.8	1471.3	1470.7	1470.1	1469.5
147.5°	1520.1	1519.8	1519.4	1519.1	1518.7	1518.4	1518.3	1518.4	1518.5	1518.6	1518.7
150°	1550.4	1549.8	1549.2	1548.7	1548.1	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8
152.5°	1577.3	1576.7	1576.2	1575.6	1575.0	1574.4	1574.8	1576.1	1577.3	1578.6	1579.8
155°	1614.1	1613.3	1612.7	1612.1	1611.5	1611.0	1611.5	1613.3	1615.0	1616.7	1618.4
157.5°	1644.7	1643.8	1643.8	1643.7	1643.6	1643.6	1644.1	1645.1	1646.1	1647.2	1648.2
160°	1663.6	1662.5	1662.2	1661.9	1661.6	1661.3	1662.0	1663.7	1665.5	1667.2	1668.9
162.5°	1680.6	1679.0	1678.7	1678.5	1678.2	1677.9	1678.6	1680.3	1682.0	1683.8	1685.5
165°	1703.0	1701.3	1701.0	1700.7	1700.4	1700.1	1700.9	1702.6	1704.3	1706.0	1707.8
167.5°	1719.7	1717.6	1717.3	1717.0	1716.7	1716.5	1717.2	1719.0	1720.8	1722.6	1724.3
170°	1728.2	1725.9	1725.6	1725.3	1725.0	1724.7	1725.6	1727.6	1729.6	1731.7	1733.7
172.5°	1735.2	1733.1	1732.6	1732.1	1731.6	1731.1	1731.8	1733.8	1735.9	1737.9	1739.9
175°	1742.4	1740.1	1739.9	1739.6	1739.3	1739.0	1739.7	1741.4	1743.2	1744.9	1746.6
177.5°	1746.2	1744.5	1744.3	1744.1	1743.9	1743.6	1744.2	1745.6	1747.0	1748.3	1749.7
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1271.1	1274.9	1280.3	1286.5	1291.5	1296.9	1299.8	1299.8	1302.3	1307.7	1314.7
5°	1274.8	1288.3	1301.2	1317.9	1330.8	1345.9	1357.3	1368.2	1378.1	1390.5	1403.5
7.5°	1273.7	1296.1	1319.5	1345.7	1374.6	1397.5	1421.1	1439.6	1457.8	1481.7	1500.5
10°	1269.6	1298.6	1330.3	1363.5	1399.9	1431.6	1460.1	1486.1	1511.0	1537.0	1560.3
12.5°	1262.1	1299.1	1337.8	1377.7	1423.6	1459.8	1496.7	1524.3	1553.4	1581.8	1610.6
15°	1250.9	1294.5	1341.2	1396.8	1452.9	1493.4	1529.7	1565.5	1592.5	1624.7	1652.3
17.5°	1227.7	1283.9	1342.7	1403.4	1457.3	1504.4	1542.5	1576.5	1605.3	1640.7	1678.1
20°	1214.0	1274.8	1336.0	1400.9	1452.3	1500.6	1537.5	1572.8	1608.6	1654.8	1700.5
22.5°	1194.9	1259.8	1324.8	1386.4	1440.7	1487.3	1525.4	1568.7	1615.7	1668.1	1723.4
25°	1164.7	1231.7	1296.0	1354.7	1407.7	1455.5	1507.4	1565.5	1622.7	1691.7	1771.2
27.5°	1126.4	1190.9	1248.4	1310.4	1363.0	1423.8	1488.6	1551.6	1634.0	1729.0	1828.2
30°	1097.7	1159.0	1213.5	1272.2	1331.9	1398.9	1471.6	1545.8	1643.9	1755.6	1873.5
32.5°	1064.5	1119.9	1174.0	1230.6	1299.5	1373.1	1450.4	1541.2	1658.5	1785.5	1907.5
35°	1006.8	1056.7	1109.1	1171.9	1245.2	1325.1	1423.8	1534.4	1676.1	1812.7	1922.3
37.5°	946.4	985.7	1038.4	1104.7	1184.4	1276.9	1388.9	1523.3	1668.9	1791.4	1838.0
40°	899.9	936.7	992.3	1061.9	1140.8	1242.0	1367.7	1505.8	1652.3	1737.4	1733.8
42.5°	853.7	891.0	944.5	1014.5	1096.8	1210.1	1339.5	1483.0	1606.6	1639.0	1571.4
45°	783.0	817.8	870.3	940.9	1029.2	1148.1	1284.1	1421.7	1500.6	1448.2	1314.2
47.5°	711.0	744.7	793.4	862.6	958.9	1083.4	1212.0	1324.9	1336.0	1223.4	1062.7
50°	663.6	695.3	741.5	815.2	908.7	1030.2	1154.3	1243.1	1215.6	1078.0	912.3
52.5°	617.5	647.9	691.2	760.8	856.3	975.4	1086.2	1155.8	1092.2	945.9	796.8
55°	549.4	578.4	622.1	685.9	772.6	881.7	978.8	1004.2	910.8	763.3	642.8
57.5°	484.7	506.0	549.1	605.5	689.1	785.3	854.9	850.3	747.2	614.4	528.0
60°	441.9	461.1	502.1	554.0	633.5	719.7	768.5	747.7	643.3	533.8	450.7
62.5°	402.0	420.0	454.3	502.1	570.3	645.3	680.8	652.2	553.6	457.4	391.3
65°	341.7	354.6	382.2	426.3	479.8	531.7	563.4	521.3	434.1	361.4	311.5
67.5°	285.3	296.5	321.0	352.7	389.5	425.4	438.2	398.8	331.0	282.0	246.9
70°	248.7	259.1	275.7	305.3	329.7	355.2	361.4	326.1	269.5	232.1	210.3
72.5°	213.8	223.4	237.9	258.8	275.7	290.4	293.3	260.5	217.1	191.4	174.6
75°	163.0	171.4	180.7	188.5	199.4	202.0	200.9	175.5	152.1	135.0	125.7
77.5°	119.8	123.3	129.0	132.1	132.6	132.4	127.1	111.0	99.0	91.9	88.1
80°	92.4	95.0	96.6	97.6	98.1	92.9	87.2	77.4	73.2	69.1	64.4
82.5°	67.1	68.9	70.4	70.6	67.8	63.5	58.2	53.3	50.4	48.3	46.5
85°	36.3	36.9	36.3	33.8	30.1	28.6	27.5	26.5	26.0	25.4	25.4
87.5°	13.6	12.8	11.2	12.1	12.5	12.5	12.9	12.9	12.9	13.2	13.4
90°	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.7	22.2	23.6
92.5°	18.3	16.7	15.1	13.5	13.6	15.4	17.1	18.9	20.7	22.2	23.6
95°	72.9	72.1	71.2	70.3	64.4	53.5	42.6	31.6	20.7	22.2	23.6
97.5°	155.6	157.2	158.7	160.3	150.2	128.6	107.0	85.3	63.7	55.6	47.5
100°	217.1	217.9	218.8	219.7	220.7	221.8	223.0	224.1	225.3	182.4	139.5
102.5°	280.5	281.6	282.7	283.8	284.7	285.4	286.1	286.7	287.4	279.3	271.2
105°	381.8	383.0	384.1	385.3	385.8	385.8	385.8	385.8	385.8	385.8	385.8
107.5°	485.8	485.8	485.8	485.8	486.1	486.7	487.2	487.8	488.4	488.4	488.5
110°	554.2	554.2	554.2	554.2	554.4	555.0	555.6	556.2	556.7	555.9	555.0



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	619.1	619.8	620.4	621.1	621.7	622.0	622.3	622.7	623.0	621.9	620.8
115°	716.1	717.6	719.0	720.5	721.3	721.6	721.9	722.2	722.5	721.3	720.2
117.5°	814.3	814.3	814.2	814.2	814.7	815.8	816.9	818.0	819.1	817.6	816.1
120°	876.3	876.0	875.7	875.4	875.7	876.5	877.4	878.3	879.1	878.6	878.0
122.5°	932.5	933.6	934.7	935.8	936.6	937.0	937.4	937.8	938.2	937.6	937.0
125°	1018.4	1020.4	1022.4	1024.4	1025.4	1025.4	1025.4	1025.4	1025.4	1024.3	1023.1
127.5°	1098.9	1100.3	1101.7	1103.2	1103.8	1103.6	1103.5	1103.3	1103.1	1102.5	1101.9
130°	1148.6	1150.0	1151.5	1152.9	1153.8	1154.1	1154.3	1154.6	1154.9	1154.1	1153.2
132.5°	1198.5	1200.2	1201.9	1203.5	1204.1	1203.4	1202.8	1202.2	1201.5	1201.4	1201.2
135°	1269.3	1271.0	1272.7	1274.5	1275.0	1274.5	1273.9	1273.3	1272.7	1272.2	1271.6
137.5°	1334.0	1335.5	1337.0	1338.5	1339.0	1338.5	1338.0	1337.5	1337.0	1337.1	1337.2
140°	1375.6	1376.2	1376.7	1377.3	1377.5	1377.2	1376.9	1376.6	1376.3	1376.9	1377.5
142.5°	1413.7	1414.0	1414.4	1414.7	1415.1	1415.5	1415.9	1416.3	1416.7	1416.8	1416.9
145°	1470.1	1470.7	1471.3	1471.8	1472.1	1472.1	1472.1	1472.1	1472.1	1472.4	1472.7
147.5°	1518.6	1518.5	1518.4	1518.3	1518.4	1518.7	1519.1	1519.4	1519.8	1520.1	1520.5
150°	1549.2	1548.7	1548.1	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8	1550.4	1551.0
152.5°	1578.6	1577.3	1576.1	1574.8	1574.4	1575.0	1575.6	1576.2	1576.7	1577.3	1577.9
155°	1616.7	1615.0	1613.3	1611.5	1611.0	1611.5	1612.1	1612.7	1613.3	1614.1	1615.0
157.5°	1647.2	1646.1	1645.1	1644.1	1643.6	1643.6	1643.7	1643.8	1643.8	1644.7	1645.7
160°	1667.2	1665.5	1663.7	1662.0	1661.3	1661.6	1661.9	1662.2	1662.5	1663.6	1664.8
162.5°	1683.8	1682.0	1680.3	1678.6	1677.9	1678.2	1678.5	1678.7	1679.0	1680.6	1682.2
165°	1706.0	1704.3	1702.6	1700.9	1700.1	1700.4	1700.7	1701.0	1701.3	1703.0	1704.7
167.5°	1722.6	1720.8	1719.0	1717.2	1716.5	1716.7	1717.0	1717.3	1717.6	1719.7	1721.8
170°	1731.7	1729.6	1727.6	1725.6	1724.7	1725.0	1725.3	1725.6	1725.9	1728.2	1730.5
172.5°	1737.9	1735.9	1733.8	1731.8	1731.1	1731.6	1732.1	1732.6	1733.1	1735.2	1737.3
175°	1744.9	1743.2	1741.4	1739.7	1739.0	1739.3	1739.6	1739.9	1740.1	1742.4	1744.7
177.5°	1748.3	1747.0	1745.6	1744.2	1743.6	1743.9	1744.1	1744.3	1744.5	1746.2	1747.8
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1320.1	1320.1	1327.2	1326.8	1331.4	1329.7	1330.5
5°	1419.1	1427.9	1435.7	1440.9	1448.7	1450.8	1449.7
7.5°	1521.7	1541.3	1550.9	1564.0	1566.4	1573.2	1572.5
10°	1585.3	1604.5	1619.0	1630.4	1636.2	1643.4	1643.9
12.5°	1635.1	1651.4	1664.3	1674.9	1681.8	1684.1	1685.5
15°	1674.1	1692.2	1707.3	1722.3	1731.2	1737.9	1741.6
17.5°	1713.3	1741.4	1767.9	1788.4	1800.7	1811.0	1810.9
20°	1743.6	1775.8	1809.1	1832.4	1856.3	1866.7	1868.3
22.5°	1776.0	1825.3	1868.1	1904.3	1935.7	1946.5	1950.5
25°	1843.3	1907.7	1973.7	2024.6	2060.9	2082.2	2085.3
27.5°	1924.6	2011.8	2081.2	2128.1	2158.3	2174.1	2177.5
30°	1982.0	2062.5	2124.8	2160.1	2174.1	2176.2	2168.4
32.5°	2007.7	2067.9	2092.8	2090.7	2063.2	2044.9	2037.9
35°	1976.3	1963.8	1903.0	1830.4	1774.8	1739.5	1730.1
37.5°	1798.5	1691.0	1579.2	1469.4	1410.9	1381.2	1330.1
40°	1623.2	1470.0	1353.7	1261.3	1195.3	1142.3	1129.9
42.5°	1425.4	1267.3	1151.0	1071.8	1019.2	982.8	967.0
45°	1145.5	1009.4	913.4	852.6	812.1	785.6	773.7
47.5°	916.2	810.9	740.9	695.9	665.1	642.0	635.6
50°	790.3	706.2	647.0	609.1	585.7	568.1	560.8
52.5°	686.4	618.5	573.0	541.8	519.7	508.7	502.6
55°	566.5	507.8	475.1	450.2	437.7	428.9	424.7
57.5°	463.3	420.9	397.0	379.8	368.3	362.6	360.6
60°	405.5	372.3	350.5	337.0	329.2	321.9	319.9
62.5°	354.4	328.3	311.4	299.6	291.8	288.7	287.5
65°	285.6	268.5	256.0	248.7	242.5	241.5	240.9
67.5°	227.0	216.9	210.4	202.8	200.6	197.0	196.3
70°	194.2	187.4	179.7	177.1	174.5	170.8	171.4
72.5°	164.7	158.0	152.7	149.2	148.3	146.7	148.1
75°	120.5	118.4	116.3	113.7	112.7	112.7	112.2
77.5°	86.0	84.2	81.9	80.4	80.1	77.9	78.7
80°	62.3	59.7	58.7	59.2	57.6	57.1	57.1
82.5°	46.1	45.2	44.1	44.2	43.9	43.4	43.8
85°	25.4	24.9	24.9	24.4	24.4	23.9	23.9
87.5°	14.1	14.8	14.2	14.0	14.2	14.8	15.4
90°	25.0	26.5	27.6	28.5	29.3	30.2	31.1
92.5°	25.0	26.5	27.4	27.8	28.2	28.6	29.0
95°	25.0	26.5	27.2	27.2	27.2	27.2	27.2
97.5°	39.4	31.2	27.2	27.2	27.2	27.2	27.2
100°	96.7	53.8	31.8	30.6	29.5	28.3	27.2
102.5°	263.1	255.0	241.1	221.6	202.0	182.4	162.9
105°	385.8	385.8	385.7	385.4	385.1	384.8	384.5
107.5°	488.6	488.6	488.2	487.3	486.5	485.6	484.8
110°	554.2	553.3	553.0	553.3	553.6	553.9	554.2



TEST NUMBER: P333692

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	619.8	618.7	617.9	617.5	617.1	616.7	616.3
115°	719.0	717.9	716.4	714.7	713.0	711.2	709.5
117.5°	814.6	813.1	811.9	811.2	810.5	809.7	809.0
120°	877.4	876.8	875.8	874.4	872.9	871.5	870.1
122.5°	936.4	935.9	934.7	933.1	931.4	929.7	928.1
125°	1022.0	1020.8	1019.8	1019.0	1018.1	1017.2	1016.4
127.5°	1101.2	1100.6	1099.2	1097.1	1095.0	1092.8	1090.7
130°	1152.3	1151.5	1150.3	1148.9	1147.4	1146.0	1144.6
132.5°	1201.0	1200.8	1200.0	1198.6	1197.2	1195.7	1194.3
135°	1271.0	1270.4	1269.3	1267.6	1265.8	1264.1	1262.4
137.5°	1337.3	1337.4	1336.7	1335.2	1333.7	1332.2	1330.7
140°	1378.0	1378.6	1378.0	1376.3	1374.6	1372.9	1371.1
142.5°	1417.1	1417.2	1416.4	1414.6	1412.9	1411.2	1409.5
145°	1473.0	1473.3	1472.6	1470.8	1469.1	1467.4	1465.7
147.5°	1520.8	1521.2	1520.3	1518.2	1516.1	1514.1	1512.0
150°	1551.5	1552.1	1551.2	1548.9	1546.6	1544.3	1542.0
152.5°	1578.5	1579.0	1578.3	1576.2	1574.2	1572.1	1570.0
155°	1615.8	1616.7	1616.0	1613.7	1611.4	1609.1	1606.8
157.5°	1646.6	1647.5	1646.8	1644.5	1642.2	1639.9	1637.6
160°	1665.9	1667.1	1666.5	1664.2	1661.9	1659.6	1657.3
162.5°	1683.9	1685.5	1685.0	1682.5	1679.9	1677.4	1674.9
165°	1706.5	1708.2	1707.9	1705.6	1703.3	1701.0	1698.7
167.5°	1723.8	1725.9	1725.6	1723.0	1720.5	1717.9	1715.3
170°	1732.8	1735.1	1735.0	1732.4	1729.8	1727.2	1724.6
172.5°	1739.4	1741.4	1741.2	1738.6	1736.0	1733.4	1730.8
175°	1747.0	1749.3	1749.2	1746.6	1744.0	1741.4	1738.8
177.5°	1749.4	1751.0	1750.9	1749.0	1747.2	1745.3	1743.5
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6

(END OF REPORT)