

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333479-830

Luminaire Tested: **S125DIW-S1270D1340U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333479-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D1340U830-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9272.1 lumens  
Efficiency: N/A  
Efficacy: 121.7 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45
2	90	83	77	72	83	77	72	67	66	62	58	56	53	50	46	44	42	38
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	32
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	37	34	31	28
5	69	58	50	44	64	54	47	41	46	41	37	40	35	32	33	30	27	24
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21
7	59	47	39	33	54	44	37	31	38	32	28	33	28	25	28	24	22	19
8	55	42	35	29	51	40	33	28	35	29	25	30	25	22	25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15
10	48	36	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	11180	11180	11180	11180
5°	12947	11218	9822	11218
10°	15062	11160	8605	11160
15°	16673	11078	7938	11078
20°	18664	10948	7403	10948
25°	21865	10802	7142	10802
30°	23616	10657	6915	10657
35°	19418	10387	6766	10387
40°	13801	10010	6604	10010
45°	10602	9502	6509	9502
50°	9051	8874	6497	8874
55°	8059	8257	6552	8257
60°	7270	7582	6719	7582
65°	6715	6906	6894	6906
70°	6105	6201	6992	6201
75°	5390	5465	6932	5465
80°	4537	4456	6338	4456
85°	3586	3216	5120	3216



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.6	1.8
10°-20°	496.2	5.4
20°-30°	805.7	8.7
30°-40°	982.8	10.6
40°-50°	894.0	9.6
50°-60°	712.1	7.7
60°-70°	496.0	5.3
70°-80°	264.5	2.9
80°-90°	70.2	0.8
90°-100°	105.2	1.1
100°-110°	310.7	3.4
110°-120°	526.3	5.7
120°-130°	692.7	7.5
130°-140°	776.1	8.4
140°-150°	760.7	8.2
150°-160°	638.9	6.9
160°-170°	424.7	4.6
170°-180°	148.6	1.6
0°-30°	1468.5	15.8
0°-40°	2451.2	26.4
0°-60°	4057.4	43.8
0°-90°	4888.1	52.7
90°-120°	942.3	10.2
90°-150°	3171.8	34.2
90°-180°	4384.0	47.3
0°-180°	9272.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1731	1731	1731	1731	1731	
5°	1997	1730	1515	1730	1997	201
15°	2494	1657	1187	1657	2494	714
25°	3068	1516	1002	1516	3068	1401
35°	2463	1317	858	1317	2463	1507
45°	1161	1040	713	1040	1161	929
55°	716	733	582	733	716	645
65°	439	452	451	452	439	436
75°	216	219	278	219	216	233
85°	48	43	69	43	48	57
90°	29	1	29	1	29	19
95°	105	80	105	80	105	107
105°	303	279	303	279	303	321
115°	532	527	532	527	532	526
125°	774	769	774	769	774	691
135°	1004	1000	1004	1000	1004	774
145°	1216	1212	1216	1212	1216	759
155°	1386	1386	1386	1386	1386	638
165°	1504	1508	1504	1508	1504	424
175°	1561	1567	1561	1567	1561	148
180°	1571	1571	1571	1571	1571	



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1831.0	1828.6	1826.3	1821.6	1825.0	1815.1	1810.3	1802.1	1792.2	1788.7	1784.5
5°	1997.0	2000.6	2004.3	1989.0	1990.4	1980.1	1956.6	1937.5	1922.0	1902.2	1888.3
7.5°	2196.9	2188.2	2187.5	2177.5	2160.3	2146.5	2121.8	2090.3	2059.9	2025.2	1996.6
10°	2296.8	2297.5	2290.9	2279.2	2260.8	2247.6	2215.3	2184.3	2146.9	2102.8	2071.2
12.5°	2372.0	2375.1	2366.7	2350.9	2341.8	2312.2	2286.9	2250.2	2205.6	2170.4	2122.3
15°	2493.7	2485.6	2479.7	2459.8	2444.5	2413.6	2373.2	2335.0	2286.5	2241.6	2196.9
17.5°	2610.9	2617.4	2606.4	2588.3	2540.4	2504.4	2450.2	2397.8	2337.5	2277.4	2223.9
20°	2715.6	2721.5	2704.5	2673.0	2615.6	2579.6	2508.4	2440.8	2371.0	2293.9	2235.1
22.5°	2846.1	2841.4	2818.6	2770.5	2720.8	2654.3	2577.2	2494.8	2407.4	2320.3	2242.1
25°	3068.3	3037.3	3023.4	2963.9	2898.5	2800.8	2695.0	2574.5	2465.8	2350.4	2250.5
27.5°	3191.4	3181.6	3166.1	3124.7	3055.9	2951.4	2826.7	2679.8	2526.5	2380.9	2250.0
30°	3166.7	3168.2	3169.7	3156.4	3112.4	3033.7	2909.5	2751.6	2569.4	2405.6	2254.2
32.5°	2948.1	2974.8	3000.4	3030.7	3043.0	3027.8	2950.1	2807.5	2619.9	2433.7	2251.8
35°	2462.9	2470.9	2553.9	2636.2	2747.9	2834.6	2892.7	2829.4	2671.4	2457.7	2249.0
37.5°	1920.3	1960.0	2017.4	2110.4	2271.6	2415.9	2601.5	2686.9	2635.9	2465.5	2243.9
40°	1637.0	1673.8	1711.2	1806.0	1941.9	2116.8	2327.6	2507.6	2549.5	2440.8	2226.3
42.5°	1418.3	1447.5	1489.0	1560.3	1673.9	1828.7	2030.2	2265.5	2410.2	2369.1	2189.2
45°	1160.8	1179.2	1211.5	1268.2	1350.5	1471.7	1649.4	1906.7	2130.7	2204.9	2101.3
47.5°	993.6	993.5	1018.6	1057.7	1117.1	1220.1	1351.6	1553.1	1792.4	1969.5	1961.3
50°	900.8	897.1	916.9	950.7	997.8	1066.1	1191.8	1352.6	1582.6	1783.2	1839.0
52.5°	820.9	821.2	833.5	858.5	897.9	956.2	1050.1	1195.1	1391.6	1597.4	1702.7
55°	715.7	712.7	726.6	743.6	772.2	810.4	878.0	988.9	1148.4	1351.1	1487.8
57.5°	619.3	627.4	632.9	644.7	668.5	694.0	751.0	832.5	958.9	1132.9	1277.4
60°	562.8	570.9	575.3	587.0	606.1	628.2	672.3	738.4	845.0	994.9	1138.1
62.5°	512.3	518.6	520.0	530.7	546.2	567.7	602.4	657.9	742.1	873.2	1013.5
65°	439.4	439.4	442.3	453.4	460.7	479.8	506.2	546.7	614.3	716.3	836.1
67.5°	369.1	372.7	371.9	376.7	383.5	398.4	417.4	450.7	500.8	575.3	671.1
70°	323.3	326.2	325.5	329.1	336.5	346.1	361.5	393.0	429.0	493.0	575.3
72.5°	282.1	283.3	281.4	286.3	290.7	299.1	316.2	333.1	366.7	420.8	488.3
75°	216.0	217.4	219.0	221.9	226.3	230.7	239.5	256.5	278.4	318.9	362.2
77.5°	161.9	159.1	162.7	162.2	164.8	168.1	175.9	184.8	202.9	228.5	262.0
80°	122.0	122.7	122.7	123.5	127.1	129.3	135.9	142.5	156.5	175.6	199.2
82.5°	89.1	91.0	89.8	91.1	94.2	95.8	99.4	104.9	113.0	128.0	145.1
85°	48.4	44.9	46.3	47.8	47.8	48.4	51.5	53.6	58.1	63.9	70.5
87.5°	20.0	21.0	21.4	21.2	21.7	21.5	23.6	23.3	24.8	26.2	28.2
90°	29.3	28.6	27.7	26.9	26.1	25.0	23.7	22.2	20.9	19.6	17.6
92.5°	57.7	57.1	56.6	55.9	55.3	54.1	52.3	50.5	48.7	46.9	44.6
95°	105.2	104.6	104.1	103.5	102.9	101.8	99.8	97.9	96.0	94.2	91.4
97.5°	159.5	159.1	158.8	158.4	158.2	157.0	155.2	153.4	151.7	149.9	146.2
100°	200.5	200.0	199.4	198.9	198.3	196.8	194.4	192.0	189.5	187.1	183.5
102.5°	241.6	240.8	240.1	239.3	238.6	236.9	234.1	231.5	228.8	226.2	224.4
105°	303.2	302.4	301.6	300.8	299.9	298.7	297.1	295.5	293.9	292.2	290.6
107.5°	366.3	366.4	366.4	366.5	366.6	366.2	365.3	364.5	363.7	362.9	361.7
110°	413.2	413.5	413.8	414.1	414.3	414.1	413.2	412.5	411.6	410.8	410.0



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	459.2	459.7	460.2	460.7	461.2	461.2	460.8	460.4	460.1	459.7	458.6
115°	531.9	532.2	532.3	532.6	532.9	533.2	533.5	533.8	534.0	534.3	533.8
117.5°	602.8	603.9	604.9	606.1	607.1	607.6	607.3	607.1	606.9	606.7	606.1
120°	651.7	652.7	653.8	654.9	656.0	656.6	656.6	656.6	656.6	656.6	656.3
122.5°	700.6	701.4	702.3	703.1	704.1	704.6	704.8	705.0	705.2	705.5	704.7
125°	773.9	774.2	774.5	774.8	775.1	775.4	776.0	776.5	777.0	777.6	777.3
127.5°	844.3	844.9	845.5	846.0	846.5	847.0	847.2	847.4	847.7	848.0	847.7
130°	891.3	891.8	892.4	893.0	893.4	893.9	894.2	894.4	894.7	894.9	894.4
132.5°	935.3	936.0	936.8	937.6	938.4	938.9	939.1	939.4	939.7	940.0	940.1
135°	1003.8	1004.8	1006.0	1007.0	1008.1	1008.7	1008.7	1008.7	1008.7	1008.7	1008.4
137.5°	1070.8	1072.1	1073.5	1074.9	1076.2	1076.8	1076.4	1076.1	1075.7	1075.4	1074.9
140°	1113.8	1115.2	1116.5	1117.9	1119.3	1119.6	1119.1	1118.6	1118.0	1117.5	1116.6
142.5°	1154.9	1156.2	1157.6	1159.0	1160.4	1160.8	1160.6	1160.2	1159.9	1159.5	1158.5
145°	1216.5	1217.3	1218.1	1219.0	1219.7	1220.2	1220.2	1220.2	1220.2	1220.2	1219.4
147.5°	1269.1	1270.9	1272.8	1274.6	1276.5	1277.1	1276.4	1275.7	1275.2	1274.5	1273.8
150°	1308.2	1308.7	1309.3	1309.9	1310.4	1310.7	1310.7	1310.7	1310.7	1310.7	1309.6
152.5°	1340.5	1341.4	1342.5	1343.4	1344.4	1344.5	1343.9	1343.2	1342.7	1342.0	1341.5
155°	1386.5	1387.8	1389.2	1390.5	1391.9	1392.0	1390.9	1389.9	1388.7	1387.7	1387.4
157.5°	1424.8	1426.6	1428.4	1430.2	1432.0	1432.4	1431.3	1430.2	1429.1	1428.0	1427.8
160°	1451.2	1452.6	1454.0	1455.4	1456.7	1456.8	1455.8	1454.6	1453.6	1452.5	1452.2
162.5°	1473.8	1475.4	1476.9	1478.5	1480.1	1480.2	1478.8	1477.6	1476.3	1475.0	1474.9
165°	1503.8	1505.4	1507.1	1508.7	1510.3	1510.6	1509.6	1508.4	1507.4	1506.3	1506.0
167.5°	1527.8	1529.5	1531.2	1532.9	1534.6	1534.6	1533.0	1531.3	1529.7	1528.0	1528.0
170°	1540.5	1542.4	1544.4	1546.2	1548.1	1548.2	1546.6	1545.0	1543.4	1541.7	1541.7
172.5°	1551.2	1552.9	1554.6	1556.3	1558.0	1558.0	1556.4	1554.8	1553.1	1551.5	1551.5
175°	1561.3	1563.2	1565.1	1567.0	1568.9	1569.1	1567.4	1565.8	1564.1	1562.5	1562.5
177.5°	1567.2	1568.7	1570.2	1571.7	1573.3	1573.4	1572.1	1570.7	1569.4	1568.1	1568.4
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1781.0	1776.9	1772.2	1764.0	1754.0	1748.7	1740.4	1735.1	1724.6	1715.7	1706.4
5°	1871.3	1852.3	1834.7	1811.8	1786.9	1770.7	1751.6	1730.3	1708.3	1685.5	1660.5
7.5°	1965.0	1931.2	1894.4	1854.9	1816.3	1780.7	1746.7	1713.4	1682.2	1644.6	1612.8
10°	2027.9	1985.3	1939.7	1886.0	1833.9	1788.4	1742.0	1701.7	1660.5	1616.4	1577.4
12.5°	2090.7	2034.0	1969.6	1910.7	1848.0	1793.0	1738.5	1687.0	1635.2	1586.4	1541.1
15°	2135.1	2085.2	2025.6	1941.9	1871.3	1795.7	1723.7	1656.8	1594.4	1540.0	1482.7
17.5°	2164.4	2100.0	2036.1	1955.7	1863.3	1778.7	1697.0	1620.5	1550.1	1481.2	1426.0
20°	2169.6	2103.6	2036.6	1958.0	1863.3	1766.3	1684.7	1592.9	1517.2	1446.0	1378.4
22.5°	2167.9	2092.9	2020.2	1939.3	1846.8	1757.5	1658.9	1565.3	1483.1	1413.1	1342.5
25°	2151.3	2071.2	1980.1	1898.6	1807.4	1712.7	1612.8	1515.8	1432.0	1351.9	1282.1
27.5°	2137.5	2033.6	1930.4	1835.3	1747.4	1660.5	1564.8	1465.5	1372.6	1291.5	1225.7
30°	2120.4	2006.6	1890.5	1791.3	1700.9	1616.4	1526.1	1429.1	1332.1	1252.7	1182.2
32.5°	2105.2	1972.5	1849.9	1741.9	1646.2	1564.1	1480.7	1388.5	1293.3	1212.8	1142.2
35°	2075.7	1922.0	1781.7	1659.7	1557.6	1473.1	1403.4	1317.4	1229.9	1152.1	1084.5
37.5°	2038.2	1856.0	1705.3	1577.4	1465.5	1376.5	1311.5	1245.5	1161.6	1086.6	1025.4
40°	2008.7	1808.9	1649.4	1518.7	1402.6	1310.0	1249.8	1187.3	1117.6	1047.7	983.1
42.5°	1971.7	1766.6	1593.1	1452.3	1337.4	1247.2	1183.9	1130.9	1069.3	1004.3	944.2
45°	1903.7	1689.9	1501.8	1350.5	1234.4	1145.5	1080.1	1040.4	994.1	932.4	881.7
47.5°	1803.6	1597.7	1403.2	1247.0	1127.2	1044.8	983.5	945.5	912.9	867.0	821.0
50°	1714.9	1529.0	1332.1	1177.0	1057.2	974.2	917.7	883.2	855.3	819.9	781.0
52.5°	1615.5	1442.6	1262.2	1108.9	990.2	908.4	853.0	822.7	799.4	774.1	735.7
55°	1457.7	1310.8	1143.2	997.8	888.3	808.2	759.7	733.3	714.2	695.0	671.6
57.5°	1283.8	1168.9	1020.6	887.6	786.7	713.9	668.6	642.9	628.0	618.2	604.4
60°	1161.6	1063.2	935.3	814.1	715.7	651.0	606.9	587.0	574.6	566.5	556.2
62.5°	1048.2	967.3	848.9	738.3	652.1	591.0	551.7	532.3	520.5	516.5	508.0
65°	880.9	818.5	720.8	629.0	555.4	503.3	470.2	451.9	444.5	440.1	440.8
67.5°	716.2	678.2	599.6	521.3	462.7	419.0	392.5	378.4	374.8	368.8	368.7
70°	615.7	587.0	520.9	452.6	400.4	366.6	343.1	328.4	324.7	321.8	321.1
72.5°	527.0	501.8	444.5	389.7	342.8	313.1	293.8	284.9	278.9	277.1	277.0
75°	396.1	382.1	336.5	293.1	260.8	240.3	227.1	219.0	214.5	213.8	214.5
77.5°	281.5	269.4	240.4	209.7	189.3	173.7	162.5	159.8	154.8	154.9	154.1
80°	211.6	203.5	185.1	160.9	144.0	130.8	124.9	119.8	118.3	116.1	118.3
82.5°	153.4	144.8	132.2	116.8	102.8	94.9	89.1	87.5	86.5	85.5	86.0
85°	75.7	76.4	69.1	57.3	51.5	47.0	43.4	43.4	42.6	41.8	42.6
87.5°	29.0	27.4	24.7	22.5	19.2	17.0	15.9	16.1	14.8	14.6	15.6
90°	15.7	13.9	12.0	9.9	7.7	5.6	3.4	1.2	3.4	5.6	7.7
92.5°	42.3	40.0	37.6	35.6	34.1	32.6	31.1	29.6	31.1	32.6	34.1
95°	88.7	86.0	83.3	81.6	81.1	80.6	80.0	79.5	80.0	80.6	81.1
97.5°	142.4	138.6	134.9	132.9	132.7	132.5	132.2	132.1	132.2	132.5	132.7
100°	180.0	176.4	173.0	171.2	171.2	171.2	171.2	171.2	171.2	171.2	171.2
102.5°	222.6	220.8	219.0	217.5	216.5	215.4	214.3	213.2	214.3	215.4	216.5
105°	289.0	287.3	285.7	284.2	282.9	281.4	280.1	278.8	280.1	281.4	282.9
107.5°	360.3	359.1	357.9	356.6	355.2	353.8	352.5	351.1	352.5	353.8	355.2
110°	409.2	408.4	407.6	406.4	405.1	403.8	402.4	401.1	402.4	403.8	405.1





TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	457.6	456.6	455.6	454.7	454.0	453.3	452.6	451.9	452.6	453.3	454.0
115°	533.2	532.6	532.2	531.3	530.2	529.1	528.0	527.0	528.0	529.1	530.2
117.5°	605.7	605.2	604.7	604.3	603.7	603.2	602.8	602.3	602.8	603.2	603.7
120°	656.0	655.7	655.4	654.7	653.3	652.0	650.5	649.2	650.5	652.0	653.3
122.5°	704.1	703.3	702.7	702.0	701.5	701.1	700.6	700.1	700.6	701.1	701.5
125°	777.0	776.7	776.5	775.5	773.9	772.3	770.6	769.0	770.6	772.3	773.9
127.5°	847.3	847.1	846.7	846.1	845.2	844.2	843.3	842.4	843.3	844.2	845.2
130°	893.9	893.3	892.8	891.8	890.5	889.1	887.8	886.4	887.8	889.1	890.5
132.5°	940.2	940.3	940.4	939.3	937.1	934.9	932.6	930.4	932.6	934.9	937.1
135°	1008.1	1007.9	1007.6	1006.6	1005.0	1003.3	1001.7	1000.1	1001.7	1003.3	1005.0
137.5°	1074.2	1073.7	1073.0	1072.0	1070.4	1068.8	1067.2	1065.6	1067.2	1068.8	1070.4
140°	1115.9	1115.0	1114.2	1113.1	1111.8	1110.4	1109.1	1107.7	1109.1	1110.4	1111.8
142.5°	1157.4	1156.4	1155.4	1154.3	1153.2	1152.1	1150.9	1149.8	1150.9	1152.1	1153.2
145°	1218.5	1217.8	1216.9	1216.0	1214.8	1213.8	1212.7	1211.6	1212.7	1213.8	1214.8
147.5°	1273.2	1272.5	1271.9	1271.2	1270.6	1270.1	1269.4	1268.9	1269.4	1270.1	1270.6
150°	1308.5	1307.4	1306.3	1305.9	1306.2	1306.5	1306.7	1307.0	1306.7	1306.5	1306.2
152.5°	1341.0	1340.7	1340.2	1339.8	1339.4	1339.1	1338.7	1338.3	1338.7	1339.1	1339.4
155°	1387.1	1386.9	1386.6	1386.5	1386.5	1386.5	1386.5	1386.5	1386.5	1386.5	1386.5
157.5°	1427.5	1427.2	1426.9	1427.1	1427.7	1428.3	1428.9	1429.5	1428.9	1428.3	1427.7
160°	1452.0	1451.7	1451.4	1451.7	1452.5	1453.3	1454.2	1454.9	1454.2	1453.3	1452.5
162.5°	1474.9	1474.8	1474.8	1475.1	1475.6	1476.2	1476.9	1477.4	1476.9	1476.2	1475.6
165°	1505.7	1505.4	1505.2	1505.3	1505.9	1506.4	1506.9	1507.5	1506.9	1506.4	1505.9
167.5°	1528.0	1528.0	1528.0	1528.6	1529.7	1530.8	1531.8	1533.0	1531.8	1530.8	1529.7
170°	1541.7	1541.7	1541.7	1542.3	1543.4	1544.5	1545.6	1546.6	1545.6	1544.5	1543.4
172.5°	1551.5	1551.5	1551.5	1552.1	1553.1	1554.3	1555.3	1556.4	1555.3	1554.3	1553.1
175°	1562.5	1562.5	1562.5	1563.1	1564.1	1565.3	1566.3	1567.4	1566.3	1565.3	1564.1
177.5°	1568.6	1568.8	1569.1	1569.5	1570.5	1571.3	1572.2	1573.0	1572.2	1571.3	1570.5
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1701.0	1694.6	1689.3	1677.5	1671.0	1662.3	1655.2	1662.8	1654.6	1658.1	1652.8
5°	1648.0	1627.4	1612.8	1591.4	1573.1	1556.1	1543.7	1541.4	1535.6	1532.7	1523.8
7.5°	1584.2	1558.5	1533.2	1505.3	1481.8	1457.8	1442.6	1429.9	1421.5	1410.5	1403.1
10°	1546.6	1512.1	1482.7	1448.9	1419.5	1393.8	1373.2	1362.9	1353.4	1339.4	1334.3
12.5°	1500.2	1464.4	1428.6	1392.5	1364.2	1335.6	1318.0	1302.4	1295.8	1280.1	1278.5
15°	1444.4	1390.8	1355.6	1318.8	1279.9	1256.4	1241.7	1224.8	1217.5	1206.5	1198.3
17.5°	1378.1	1330.1	1286.1	1248.0	1214.7	1194.9	1176.6	1165.0	1152.4	1145.2	1131.9
20°	1329.8	1284.3	1240.2	1199.9	1174.1	1151.3	1136.6	1125.6	1112.4	1108.7	1095.5
22.5°	1289.3	1239.1	1196.7	1162.8	1134.7	1109.0	1093.2	1085.6	1076.6	1065.3	1062.5
25°	1223.3	1171.2	1135.2	1101.4	1076.4	1052.9	1041.9	1032.3	1023.5	1015.4	1012.5
27.5°	1166.3	1119.7	1076.9	1046.4	1024.6	1003.2	993.5	981.9	975.4	968.9	961.0
30°	1126.3	1078.6	1041.1	1011.7	988.3	969.1	958.8	950.7	944.9	939.0	934.6
32.5°	1085.2	1040.9	1004.7	975.9	952.3	937.9	928.9	923.1	916.6	909.6	904.0
35°	1030.9	982.3	947.1	922.1	903.7	892.7	882.4	877.2	870.0	870.0	864.0
37.5°	969.6	927.7	896.5	873.7	857.2	847.4	836.3	832.7	828.0	824.9	822.9
40°	933.1	894.2	864.8	842.0	824.3	816.2	807.5	801.6	798.6	794.9	793.5
42.5°	895.5	858.3	830.1	809.1	793.8	786.9	778.6	774.6	768.6	763.8	763.0
45°	838.3	802.3	776.7	759.7	746.5	738.4	733.3	724.4	721.5	715.7	714.9
47.5°	784.1	749.6	724.3	710.5	698.9	692.3	684.2	675.3	672.0	669.0	668.7
50°	743.6	712.0	688.4	675.2	664.2	654.7	646.6	640.6	638.5	638.5	640.0
52.5°	702.4	675.5	655.5	639.3	629.0	618.8	611.3	607.8	604.4	607.9	610.6
55°	642.2	615.0	600.3	584.8	574.6	562.8	559.1	557.7	555.4	561.4	564.3
57.5°	578.3	559.3	542.1	526.8	517.6	510.8	505.8	504.9	509.1	511.8	521.3
60°	537.8	515.8	500.4	488.6	477.6	473.2	471.7	470.2	473.2	481.3	493.7
62.5°	493.1	475.2	458.6	449.8	441.7	434.4	434.0	435.0	440.8	450.1	462.6
65°	427.6	412.2	401.1	390.9	384.3	379.8	381.4	384.3	390.9	403.4	417.4
67.5°	361.1	350.4	340.6	332.2	325.9	325.9	327.4	331.8	339.6	354.0	366.7
70°	318.1	306.4	298.3	294.6	289.5	286.5	291.0	298.3	304.9	318.1	329.1
72.5°	275.2	265.2	258.9	256.5	254.2	251.8	253.4	261.3	270.2	283.4	296.2
75°	211.6	207.9	203.5	200.6	198.4	199.8	201.3	208.7	216.0	230.0	244.7
77.5°	154.5	150.6	148.0	147.2	146.1	146.8	150.9	156.4	163.5	173.7	184.8
80°	116.8	115.4	113.9	113.1	113.1	113.9	119.8	123.5	130.1	139.6	148.5
82.5°	85.1	84.2	83.9	83.8	84.4	84.5	88.0	92.8	98.3	105.5	113.1
85°	44.9	43.4	45.5	46.3	44.9	47.0	48.4	51.5	53.6	57.3	61.0
87.5°	16.7	18.3	18.1	19.0	19.4	20.9	20.6	23.3	24.7	26.2	25.8
90°	9.9	12.0	13.9	15.7	17.6	19.6	20.9	22.2	23.7	25.0	26.1
92.5°	35.6	37.6	40.0	42.3	44.6	46.9	48.7	50.5	52.3	54.1	55.3
95°	81.6	83.3	86.0	88.7	91.4	94.2	96.0	97.9	99.8	101.8	102.9
97.5°	132.9	134.9	138.6	142.4	146.2	149.9	151.7	153.4	155.2	157.0	158.2
100°	171.2	173.0	176.4	180.0	183.5	187.1	189.5	192.0	194.4	196.8	198.3
102.5°	217.5	219.0	220.8	222.6	224.4	226.2	228.8	231.5	234.1	236.9	238.6
105°	284.2	285.7	287.3	289.0	290.6	292.2	293.9	295.5	297.1	298.7	299.9
107.5°	356.6	357.9	359.1	360.3	361.7	362.9	363.7	364.5	365.3	366.2	366.6
110°	406.4	407.6	408.4	409.2	410.0	410.8	411.6	412.5	413.2	414.1	414.3



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	454.7	455.6	456.6	457.6	458.6	459.7	460.1	460.4	460.8	461.2	461.2
115°	531.3	532.2	532.6	533.2	533.8	534.3	534.0	533.8	533.5	533.2	532.9
117.5°	604.3	604.7	605.2	605.7	606.1	606.7	606.9	607.1	607.3	607.6	607.1
120°	654.7	655.4	655.7	656.0	656.3	656.6	656.6	656.6	656.6	656.6	656.0
122.5°	702.0	702.7	703.3	704.1	704.7	705.5	705.2	705.0	704.8	704.6	704.1
125°	775.5	776.5	776.7	777.0	777.3	777.6	777.0	776.5	776.0	775.4	775.1
127.5°	846.1	846.7	847.1	847.3	847.7	848.0	847.7	847.4	847.2	847.0	846.5
130°	891.8	892.8	893.3	893.9	894.4	894.9	894.7	894.4	894.2	893.9	893.4
132.5°	939.3	940.4	940.3	940.2	940.1	940.0	939.7	939.4	939.1	938.9	938.4
135°	1006.6	1007.6	1007.9	1008.1	1008.4	1008.7	1008.7	1008.7	1008.7	1008.7	1008.1
137.5°	1072.0	1073.0	1073.7	1074.2	1074.9	1075.4	1075.7	1076.1	1076.4	1076.8	1076.2
140°	1113.1	1114.2	1115.0	1115.9	1116.6	1117.5	1118.0	1118.6	1119.1	1119.6	1119.3
142.5°	1154.3	1155.4	1156.4	1157.4	1158.5	1159.5	1159.9	1160.2	1160.6	1160.8	1160.4
145°	1216.0	1216.9	1217.8	1218.5	1219.4	1220.2	1220.2	1220.2	1220.2	1220.2	1219.7
147.5°	1271.2	1271.9	1272.5	1273.2	1273.8	1274.5	1275.2	1275.7	1276.4	1277.1	1276.5
150°	1305.9	1306.3	1307.4	1308.5	1309.6	1310.7	1310.7	1310.7	1310.7	1310.7	1310.4
152.5°	1339.8	1340.2	1340.7	1341.0	1341.5	1342.0	1342.7	1343.2	1343.9	1344.5	1344.4
155°	1386.5	1386.6	1386.9	1387.1	1387.4	1387.7	1388.7	1389.9	1390.9	1392.0	1391.9
157.5°	1427.1	1426.9	1427.2	1427.5	1427.8	1428.0	1429.1	1430.2	1431.3	1432.4	1432.0
160°	1451.7	1451.4	1451.7	1452.0	1452.2	1452.5	1453.6	1454.6	1455.8	1456.8	1456.7
162.5°	1475.1	1474.8	1474.8	1474.9	1474.9	1475.0	1476.3	1477.6	1478.8	1480.2	1480.1
165°	1505.3	1505.2	1505.4	1505.7	1506.0	1506.3	1507.4	1508.4	1509.6	1510.6	1510.3
167.5°	1528.6	1528.0	1528.0	1528.0	1528.0	1528.0	1529.7	1531.3	1533.0	1534.6	1534.6
170°	1542.3	1541.7	1541.7	1541.7	1541.7	1541.7	1543.4	1545.0	1546.6	1548.2	1548.1
172.5°	1552.1	1551.5	1551.5	1551.5	1551.5	1551.5	1553.1	1554.8	1556.4	1558.0	1558.0
175°	1563.1	1562.5	1562.5	1562.5	1562.5	1562.5	1564.1	1565.8	1567.4	1569.1	1568.9
177.5°	1569.5	1569.1	1568.8	1568.6	1568.4	1568.1	1569.4	1570.7	1572.1	1573.4	1573.3
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1649.4	1653.4	1649.9	1654.6	1649.9	1653.4	1649.4	1652.8	1658.1	1654.6	1662.8
5°	1520.1	1513.5	1518.0	1515.0	1518.0	1513.5	1520.1	1523.8	1532.7	1535.6	1541.4
7.5°	1400.8	1394.5	1387.3	1383.9	1387.3	1394.5	1400.8	1403.1	1410.5	1421.5	1429.9
10°	1326.2	1318.1	1317.4	1312.2	1317.4	1318.1	1326.2	1334.3	1339.4	1353.4	1362.9
12.5°	1271.5	1264.0	1255.7	1253.5	1255.7	1264.0	1271.5	1278.5	1280.1	1295.8	1302.4
15°	1193.9	1188.1	1182.9	1187.3	1182.9	1188.1	1193.9	1198.3	1206.5	1217.5	1224.8
17.5°	1129.4	1124.5	1123.7	1118.2	1123.7	1124.5	1129.4	1131.9	1145.2	1152.4	1165.0
20°	1088.9	1085.2	1086.7	1077.1	1086.7	1085.2	1088.9	1095.5	1108.7	1112.4	1125.6
22.5°	1056.6	1049.3	1048.5	1046.6	1048.5	1049.3	1056.6	1062.5	1065.3	1076.6	1085.6
25°	1005.9	1002.2	998.5	1002.2	998.5	1002.2	1005.9	1012.5	1015.4	1023.5	1032.3
27.5°	961.6	957.2	956.2	956.6	956.2	957.2	961.6	961.0	968.9	975.4	981.9
30°	934.6	927.3	927.9	927.3	927.9	927.3	934.6	934.6	939.0	944.9	950.7
32.5°	905.2	900.2	899.2	897.9	899.2	900.2	905.2	904.0	909.6	916.6	923.1
35°	861.9	861.9	858.2	858.2	858.2	861.9	861.9	864.0	870.0	870.0	877.2
37.5°	821.1	820.4	818.2	818.5	818.2	820.4	821.1	822.9	824.9	828.0	832.7
40°	790.6	789.9	787.6	783.3	787.6	789.9	790.6	793.5	794.9	798.6	801.6
42.5°	761.2	758.7	757.6	756.2	757.6	758.7	761.2	763.0	763.8	768.6	774.6
45°	714.9	714.9	713.4	712.7	713.4	714.9	714.9	714.9	715.7	721.5	724.4
47.5°	670.0	671.3	674.0	673.6	674.0	671.3	670.0	668.7	669.0	672.0	675.3
50°	642.9	643.7	645.8	646.6	645.8	643.7	642.9	640.0	638.5	638.5	640.6
52.5°	612.9	617.2	620.0	619.5	620.0	617.2	612.9	610.6	607.9	604.4	607.8
55°	570.9	576.0	581.2	581.9	581.2	576.0	570.9	564.3	561.4	555.4	557.7
57.5°	529.3	536.5	542.0	543.7	542.0	536.5	529.3	521.3	511.8	509.1	504.9
60°	501.1	510.7	517.3	520.2	517.3	510.7	501.1	493.7	481.3	473.2	470.2
62.5°	474.0	484.7	491.3	492.0	491.3	484.7	474.0	462.6	450.1	440.8	435.0
65°	429.8	440.8	446.7	451.1	446.7	440.8	429.8	417.4	403.4	390.9	384.3
67.5°	382.2	393.2	399.7	403.2	399.7	393.2	382.2	366.7	354.0	339.6	331.8
70°	347.5	358.5	367.4	370.3	367.4	358.5	347.5	329.1	318.1	304.9	298.3
72.5°	313.4	323.3	330.4	333.8	330.4	323.3	313.4	296.2	283.4	270.2	261.3
75°	254.2	267.4	274.1	277.8	274.1	267.4	254.2	244.7	230.0	216.0	208.7
77.5°	196.0	208.1	212.1	214.0	212.1	208.1	196.0	184.8	173.7	163.5	156.4
80°	157.2	164.6	169.8	170.4	169.8	164.6	157.2	148.5	139.6	130.1	123.5
82.5°	120.8	127.0	128.6	130.4	128.6	127.0	120.8	113.1	105.5	98.3	92.8
85°	66.2	69.1	69.8	69.1	69.8	69.1	66.2	61.0	57.3	53.6	51.5
87.5°	27.1	26.7	26.9	28.2	26.9	26.7	27.1	25.8	26.2	24.7	23.3
90°	26.9	27.7	28.6	29.3	28.6	27.7	26.9	26.1	25.0	23.7	22.2
92.5°	55.9	56.6	57.1	57.7	57.1	56.6	55.9	55.3	54.1	52.3	50.5
95°	103.5	104.1	104.6	105.2	104.6	104.1	103.5	102.9	101.8	99.8	97.9
97.5°	158.4	158.8	159.1	159.5	159.1	158.8	158.4	158.2	157.0	155.2	153.4
100°	198.9	199.4	200.0	200.5	200.0	199.4	198.9	198.3	196.8	194.4	192.0
102.5°	239.3	240.1	240.8	241.6	240.8	240.1	239.3	238.6	236.9	234.1	231.5
105°	300.8	301.6	302.4	303.2	302.4	301.6	300.8	299.9	298.7	297.1	295.5
107.5°	366.5	366.4	366.4	366.3	366.4	366.4	366.5	366.6	366.2	365.3	364.5
110°	414.1	413.8	413.5	413.2	413.5	413.8	414.1	414.3	414.1	413.2	412.5



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	460.7	460.2	459.7	459.2	459.7	460.2	460.7	461.2	461.2	460.8	460.4
115°	532.6	532.3	532.2	531.9	532.2	532.3	532.6	532.9	533.2	533.5	533.8
117.5°	606.1	604.9	603.9	602.8	603.9	604.9	606.1	607.1	607.6	607.3	607.1
120°	654.9	653.8	652.7	651.7	652.7	653.8	654.9	656.0	656.6	656.6	656.6
122.5°	703.1	702.3	701.4	700.6	701.4	702.3	703.1	704.1	704.6	704.8	705.0
125°	774.8	774.5	774.2	773.9	774.2	774.5	774.8	775.1	775.4	776.0	776.5
127.5°	846.0	845.5	844.9	844.3	844.9	845.5	846.0	846.5	847.0	847.2	847.4
130°	893.0	892.4	891.8	891.3	891.8	892.4	893.0	893.4	893.9	894.2	894.4
132.5°	937.6	936.8	936.0	935.3	936.0	936.8	937.6	938.4	938.9	939.1	939.4
135°	1007.0	1006.0	1004.8	1003.8	1004.8	1006.0	1007.0	1008.1	1008.7	1008.7	1008.7
137.5°	1074.9	1073.5	1072.1	1070.8	1072.1	1073.5	1074.9	1076.2	1076.8	1076.4	1076.1
140°	1117.9	1116.5	1115.2	1113.8	1115.2	1116.5	1117.9	1119.3	1119.6	1119.1	1118.6
142.5°	1159.0	1157.6	1156.2	1154.9	1156.2	1157.6	1159.0	1160.4	1160.8	1160.6	1160.2
145°	1219.0	1218.1	1217.3	1216.5	1217.3	1218.1	1219.0	1219.7	1220.2	1220.2	1220.2
147.5°	1274.6	1272.8	1270.9	1269.1	1270.9	1272.8	1274.6	1276.5	1277.1	1276.4	1275.7
150°	1309.9	1309.3	1308.7	1308.2	1308.7	1309.3	1309.9	1310.4	1310.7	1310.7	1310.7
152.5°	1343.4	1342.5	1341.4	1340.5	1341.4	1342.5	1343.4	1344.4	1344.5	1343.9	1343.2
155°	1390.5	1389.2	1387.8	1386.5	1387.8	1389.2	1390.5	1391.9	1392.0	1390.9	1389.9
157.5°	1430.2	1428.4	1426.6	1424.8	1426.6	1428.4	1430.2	1432.0	1432.4	1431.3	1430.2
160°	1455.4	1454.0	1452.6	1451.2	1452.6	1454.0	1455.4	1456.7	1456.8	1455.8	1454.6
162.5°	1478.5	1476.9	1475.4	1473.8	1475.4	1476.9	1478.5	1480.1	1480.2	1478.8	1477.6
165°	1508.7	1507.1	1505.4	1503.8	1505.4	1507.1	1508.7	1510.3	1510.6	1509.6	1508.4
167.5°	1532.9	1531.2	1529.5	1527.8	1529.5	1531.2	1532.9	1534.6	1534.6	1533.0	1531.3
170°	1546.2	1544.4	1542.4	1540.5	1542.4	1544.4	1546.2	1548.1	1548.2	1546.6	1545.0
172.5°	1556.3	1554.6	1552.9	1551.2	1552.9	1554.6	1556.3	1558.0	1558.0	1556.4	1554.8
175°	1567.0	1565.1	1563.2	1561.3	1563.2	1565.1	1567.0	1568.9	1569.1	1567.4	1565.8
177.5°	1571.7	1570.2	1568.7	1567.2	1568.7	1570.2	1571.7	1573.3	1573.4	1572.1	1570.7
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1655.2	1662.3	1671.0	1677.5	1689.3	1694.6	1701.0	1706.4	1715.7	1724.6	1735.1
5°	1543.7	1556.1	1573.1	1591.4	1612.8	1627.4	1648.0	1660.5	1685.5	1708.3	1730.3
7.5°	1442.6	1457.8	1481.8	1505.3	1533.2	1558.5	1584.2	1612.8	1644.6	1682.2	1713.4
10°	1373.2	1393.8	1419.5	1448.9	1482.7	1512.1	1546.6	1577.4	1616.4	1660.5	1701.7
12.5°	1318.0	1335.6	1364.2	1392.5	1428.6	1464.4	1500.2	1541.1	1586.4	1635.2	1687.0
15°	1241.7	1256.4	1279.9	1318.8	1355.6	1390.8	1444.4	1482.7	1540.0	1594.4	1656.8
17.5°	1176.6	1194.9	1214.7	1248.0	1286.1	1330.1	1378.1	1426.0	1481.2	1550.1	1620.5
20°	1136.6	1151.3	1174.1	1199.9	1240.2	1284.3	1329.8	1378.4	1446.0	1517.2	1592.9
22.5°	1093.2	1109.0	1134.7	1162.8	1196.7	1239.1	1289.3	1342.5	1413.1	1483.1	1565.3
25°	1041.9	1052.9	1076.4	1101.4	1135.2	1171.2	1223.3	1282.1	1351.9	1432.0	1515.8
27.5°	993.5	1003.2	1024.6	1046.4	1076.9	1119.7	1166.3	1225.7	1291.5	1372.6	1465.5
30°	958.8	969.1	988.3	1011.7	1041.1	1078.6	1126.3	1182.2	1252.7	1332.1	1429.1
32.5°	928.9	937.9	952.3	975.9	1004.7	1040.9	1085.2	1142.2	1212.8	1293.3	1388.5
35°	882.4	892.7	903.7	922.1	947.1	982.3	1030.9	1084.5	1152.1	1229.9	1317.4
37.5°	836.3	847.4	857.2	873.7	896.5	927.7	969.6	1025.4	1086.6	1161.6	1245.5
40°	807.5	816.2	824.3	842.0	864.8	894.2	933.1	983.1	1047.7	1117.6	1187.3
42.5°	778.6	786.9	793.8	809.1	830.1	858.3	895.5	944.2	1004.3	1069.3	1130.9
45°	733.3	738.4	746.5	759.7	776.7	802.3	838.3	881.7	932.4	994.1	1040.4
47.5°	684.2	692.3	698.9	710.5	724.3	749.6	784.1	821.0	867.0	912.9	945.5
50°	646.6	654.7	664.2	675.2	688.4	712.0	743.6	781.0	819.9	855.3	883.2
52.5°	611.3	618.8	629.0	639.3	655.5	675.5	702.4	735.7	774.1	799.4	822.7
55°	559.1	562.8	574.6	584.8	600.3	615.0	642.2	671.6	695.0	714.2	733.3
57.5°	505.8	510.8	517.6	526.8	542.1	559.3	578.3	604.4	618.2	628.0	642.9
60°	471.7	473.2	477.6	488.6	500.4	515.8	537.8	556.2	566.5	574.6	587.0
62.5°	434.0	434.4	441.7	449.8	458.6	475.2	493.1	508.0	516.5	520.5	532.3
65°	381.4	379.8	384.3	390.9	401.1	412.2	427.6	440.8	440.1	444.5	451.9
67.5°	327.4	325.9	325.9	332.2	340.6	350.4	361.1	368.7	368.8	374.8	378.4
70°	291.0	286.5	289.5	294.6	298.3	306.4	318.1	321.1	321.8	324.7	328.4
72.5°	253.4	251.8	254.2	256.5	258.9	265.2	275.2	277.0	277.1	278.9	284.9
75°	201.3	199.8	198.4	200.6	203.5	207.9	211.6	214.5	213.8	214.5	219.0
77.5°	150.9	146.8	146.1	147.2	148.0	150.6	154.5	154.1	154.9	154.8	159.8
80°	119.8	113.9	113.1	113.1	113.9	115.4	116.8	118.3	116.1	118.3	119.8
82.5°	88.0	84.5	84.4	83.8	83.9	84.2	85.1	86.0	85.5	86.5	87.5
85°	48.4	47.0	44.9	46.3	45.5	43.4	44.9	42.6	41.8	42.6	43.4
87.5°	20.6	20.9	19.4	19.0	18.1	18.3	16.7	15.6	14.6	14.8	16.1
90°	20.9	19.6	17.6	15.7	13.9	12.0	9.9	7.7	5.6	3.4	1.2
92.5°	48.7	46.9	44.6	42.3	40.0	37.6	35.6	34.1	32.6	31.1	29.6
95°	96.0	94.2	91.4	88.7	86.0	83.3	81.6	81.1	80.6	80.0	79.5
97.5°	151.7	149.9	146.2	142.4	138.6	134.9	132.9	132.7	132.5	132.2	132.1
100°	189.5	187.1	183.5	180.0	176.4	173.0	171.2	171.2	171.2	171.2	171.2
102.5°	228.8	226.2	224.4	222.6	220.8	219.0	217.5	216.5	215.4	214.3	213.2
105°	293.9	292.2	290.6	289.0	287.3	285.7	284.2	282.9	281.4	280.1	278.8
107.5°	363.7	362.9	361.7	360.3	359.1	357.9	356.6	355.2	353.8	352.5	351.1
110°	411.6	410.8	410.0	409.2	408.4	407.6	406.4	405.1	403.8	402.4	401.1



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	460.1	459.7	458.6	457.6	456.6	455.6	454.7	454.0	453.3	452.6	451.9
115°	534.0	534.3	533.8	533.2	532.6	532.2	531.3	530.2	529.1	528.0	527.0
117.5°	606.9	606.7	606.1	605.7	605.2	604.7	604.3	603.7	603.2	602.8	602.3
120°	656.6	656.6	656.3	656.0	655.7	655.4	654.7	653.3	652.0	650.5	649.2
122.5°	705.2	705.5	704.7	704.1	703.3	702.7	702.0	701.5	701.1	700.6	700.1
125°	777.0	777.6	777.3	777.0	776.7	776.5	775.5	773.9	772.3	770.6	769.0
127.5°	847.7	848.0	847.7	847.3	847.1	846.7	846.1	845.2	844.2	843.3	842.4
130°	894.7	894.9	894.4	893.9	893.3	892.8	891.8	890.5	889.1	887.8	886.4
132.5°	939.7	940.0	940.1	940.2	940.3	940.4	939.3	937.1	934.9	932.6	930.4
135°	1008.7	1008.7	1008.4	1008.1	1007.9	1007.6	1006.6	1005.0	1003.3	1001.7	1000.1
137.5°	1075.7	1075.4	1074.9	1074.2	1073.7	1073.0	1072.0	1070.4	1068.8	1067.2	1065.6
140°	1118.0	1117.5	1116.6	1115.9	1115.0	1114.2	1113.1	1111.8	1110.4	1109.1	1107.7
142.5°	1159.9	1159.5	1158.5	1157.4	1156.4	1155.4	1154.3	1153.2	1152.1	1150.9	1149.8
145°	1220.2	1220.2	1219.4	1218.5	1217.8	1216.9	1216.0	1214.8	1213.8	1212.7	1211.6
147.5°	1275.2	1274.5	1273.8	1273.2	1272.5	1271.9	1271.2	1270.6	1270.1	1269.4	1268.9
150°	1310.7	1310.7	1309.6	1308.5	1307.4	1306.3	1305.9	1306.2	1306.5	1306.7	1307.0
152.5°	1342.7	1342.0	1341.5	1341.0	1340.7	1340.2	1339.8	1339.4	1339.1	1338.7	1338.3
155°	1388.7	1387.7	1387.4	1387.1	1386.9	1386.6	1386.5	1386.5	1386.5	1386.5	1386.5
157.5°	1429.1	1428.0	1427.8	1427.5	1427.2	1426.9	1427.1	1427.7	1428.3	1428.9	1429.5
160°	1453.6	1452.5	1452.2	1452.0	1451.7	1451.4	1451.7	1452.5	1453.3	1454.2	1454.9
162.5°	1476.3	1475.0	1474.9	1474.9	1474.8	1474.8	1475.1	1475.6	1476.2	1476.9	1477.4
165°	1507.4	1506.3	1506.0	1505.7	1505.4	1505.2	1505.3	1505.9	1506.4	1506.9	1507.5
167.5°	1529.7	1528.0	1528.0	1528.0	1528.0	1528.0	1528.6	1529.7	1530.8	1531.8	1533.0
170°	1543.4	1541.7	1541.7	1541.7	1541.7	1541.7	1542.3	1543.4	1544.5	1545.6	1546.6
172.5°	1553.1	1551.5	1551.5	1551.5	1551.5	1551.5	1552.1	1553.1	1554.3	1555.3	1556.4
175°	1564.1	1562.5	1562.5	1562.5	1562.5	1562.5	1563.1	1564.1	1565.3	1566.3	1567.4
177.5°	1569.4	1568.1	1568.4	1568.6	1568.8	1569.1	1569.5	1570.5	1571.3	1572.2	1573.0
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1740.4	1748.7	1754.0	1764.0	1772.2	1776.9	1781.0	1784.5	1788.7	1792.2	1802.1
5°	1751.6	1770.7	1786.9	1811.8	1834.7	1852.3	1871.3	1888.3	1902.2	1922.0	1937.5
7.5°	1746.7	1780.7	1816.3	1854.9	1894.4	1931.2	1965.0	1996.6	2025.2	2059.9	2090.3
10°	1742.0	1788.4	1833.9	1886.0	1939.7	1985.3	2027.9	2071.2	2102.8	2146.9	2184.3
12.5°	1738.5	1793.0	1848.0	1910.7	1969.6	2034.0	2090.7	2122.3	2170.4	2205.6	2250.2
15°	1723.7	1795.7	1871.3	1941.9	2025.6	2085.2	2135.1	2196.9	2241.6	2286.5	2335.0
17.5°	1697.0	1778.7	1863.3	1955.7	2036.1	2100.0	2164.4	2223.9	2277.4	2337.5	2397.8
20°	1684.7	1766.3	1863.3	1958.0	2036.6	2103.6	2169.6	2235.1	2293.9	2371.0	2440.8
22.5°	1658.9	1757.5	1846.8	1939.3	2020.2	2092.9	2167.9	2242.1	2320.3	2407.4	2494.8
25°	1612.8	1712.7	1807.4	1898.6	1980.1	2071.2	2151.3	2250.5	2350.4	2465.8	2574.5
27.5°	1564.8	1660.5	1747.4	1835.3	1930.4	2033.6	2137.5	2250.0	2380.9	2526.5	2679.8
30°	1526.1	1616.4	1700.9	1791.3	1890.5	2006.6	2120.4	2254.2	2405.6	2569.4	2751.6
32.5°	1480.7	1564.1	1646.2	1741.9	1849.9	1972.5	2105.2	2251.8	2433.7	2619.9	2807.5
35°	1403.4	1473.1	1557.6	1659.7	1781.7	1922.0	2075.7	2249.0	2457.7	2671.4	2829.4
37.5°	1311.5	1376.5	1465.5	1577.4	1705.3	1856.0	2038.2	2243.9	2465.5	2635.9	2686.9
40°	1249.8	1310.0	1402.6	1518.7	1649.4	1808.9	2008.7	2226.3	2440.8	2549.5	2507.6
42.5°	1183.9	1247.2	1337.4	1452.3	1593.1	1766.6	1971.7	2189.2	2369.1	2410.2	2265.5
45°	1080.1	1145.5	1234.4	1350.5	1501.8	1689.9	1903.7	2101.3	2204.9	2130.7	1906.7
47.5°	983.5	1044.8	1127.2	1247.0	1403.2	1597.7	1803.6	1961.3	1969.5	1792.4	1553.1
50°	917.7	974.2	1057.2	1177.0	1332.1	1529.0	1714.9	1839.0	1783.2	1582.6	1352.6
52.5°	853.0	908.4	990.2	1108.9	1262.2	1442.6	1615.5	1702.7	1597.4	1391.6	1195.1
55°	759.7	808.2	888.3	997.8	1143.2	1310.8	1457.7	1487.8	1351.1	1148.4	988.9
57.5°	668.6	713.9	786.7	887.6	1020.6	1168.9	1283.8	1277.4	1132.9	958.9	832.5
60°	606.9	651.0	715.7	814.1	935.3	1063.2	1161.6	1138.1	994.9	845.0	738.4
62.5°	551.7	591.0	652.1	738.3	848.9	967.3	1048.2	1013.5	873.2	742.1	657.9
65°	470.2	503.3	555.4	629.0	720.8	818.5	880.9	836.1	716.3	614.3	546.7
67.5°	392.5	419.0	462.7	521.3	599.6	678.2	716.2	671.1	575.3	500.8	450.7
70°	343.1	366.6	400.4	452.6	520.9	587.0	615.7	575.3	493.0	429.0	393.0
72.5°	293.8	313.1	342.8	389.7	444.5	501.8	527.0	488.3	420.8	366.7	333.1
75°	227.1	240.3	260.8	293.1	336.5	382.1	396.1	362.2	318.9	278.4	256.5
77.5°	162.5	173.7	189.3	209.7	240.4	269.4	281.5	262.0	228.5	202.9	184.8
80°	124.9	130.8	144.0	160.9	185.1	203.5	211.6	199.2	175.6	156.5	142.5
82.5°	89.1	94.9	102.8	116.8	132.2	144.8	153.4	145.1	128.0	113.0	104.9
85°	43.4	47.0	51.5	57.3	69.1	76.4	75.7	70.5	63.9	58.1	53.6
87.5°	15.9	17.0	19.2	22.5	24.7	27.4	29.0	28.2	26.2	24.8	23.3
90°	3.4	5.6	7.7	9.9	12.0	13.9	15.7	17.6	19.6	20.9	22.2
92.5°	31.1	32.6	34.1	35.6	37.6	40.0	42.3	44.6	46.9	48.7	50.5
95°	80.0	80.6	81.1	81.6	83.3	86.0	88.7	91.4	94.2	96.0	97.9
97.5°	132.2	132.5	132.7	132.9	134.9	138.6	142.4	146.2	149.9	151.7	153.4
100°	171.2	171.2	171.2	171.2	173.0	176.4	180.0	183.5	187.1	189.5	192.0
102.5°	214.3	215.4	216.5	217.5	219.0	220.8	222.6	224.4	226.2	228.8	231.5
105°	280.1	281.4	282.9	284.2	285.7	287.3	289.0	290.6	292.2	293.9	295.5
107.5°	352.5	353.8	355.2	356.6	357.9	359.1	360.3	361.7	362.9	363.7	364.5
110°	402.4	403.8	405.1	406.4	407.6	408.4	409.2	410.0	410.8	411.6	412.5





TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	452.6	453.3	454.0	454.7	455.6	456.6	457.6	458.6	459.7	460.1	460.4
115°	528.0	529.1	530.2	531.3	532.2	532.6	533.2	533.8	534.3	534.0	533.8
117.5°	602.8	603.2	603.7	604.3	604.7	605.2	605.7	606.1	606.7	606.9	607.1
120°	650.5	652.0	653.3	654.7	655.4	655.7	656.0	656.3	656.6	656.6	656.6
122.5°	700.6	701.1	701.5	702.0	702.7	703.3	704.1	704.7	705.5	705.2	705.0
125°	770.6	772.3	773.9	775.5	776.5	776.7	777.0	777.3	777.6	777.0	776.5
127.5°	843.3	844.2	845.2	846.1	846.7	847.1	847.3	847.7	848.0	847.7	847.4
130°	887.8	889.1	890.5	891.8	892.8	893.3	893.9	894.4	894.9	894.7	894.4
132.5°	932.6	934.9	937.1	939.3	940.4	940.3	940.2	940.1	940.0	939.7	939.4
135°	1001.7	1003.3	1005.0	1006.6	1007.6	1007.9	1008.1	1008.4	1008.7	1008.7	1008.7
137.5°	1067.2	1068.8	1070.4	1072.0	1073.0	1073.7	1074.2	1074.9	1075.4	1075.7	1076.1
140°	1109.1	1110.4	1111.8	1113.1	1114.2	1115.0	1115.9	1116.6	1117.5	1118.0	1118.6
142.5°	1150.9	1152.1	1153.2	1154.3	1155.4	1156.4	1157.4	1158.5	1159.5	1159.9	1160.2
145°	1212.7	1213.8	1214.8	1216.0	1216.9	1217.8	1218.5	1219.4	1220.2	1220.2	1220.2
147.5°	1269.4	1270.1	1270.6	1271.2	1271.9	1272.5	1273.2	1273.8	1274.5	1275.2	1275.7
150°	1306.7	1306.5	1306.2	1305.9	1306.3	1307.4	1308.5	1309.6	1310.7	1310.7	1310.7
152.5°	1338.7	1339.1	1339.4	1339.8	1340.2	1340.7	1341.0	1341.5	1342.0	1342.7	1343.2
155°	1386.5	1386.5	1386.5	1386.5	1386.6	1386.9	1387.1	1387.4	1387.7	1388.7	1389.9
157.5°	1428.9	1428.3	1427.7	1427.1	1426.9	1427.2	1427.5	1427.8	1428.0	1429.1	1430.2
160°	1454.2	1453.3	1452.5	1451.7	1451.4	1451.7	1452.0	1452.2	1452.5	1453.6	1454.6
162.5°	1476.9	1476.2	1475.6	1475.1	1474.8	1474.8	1474.9	1474.9	1475.0	1476.3	1477.6
165°	1506.9	1506.4	1505.9	1505.3	1505.2	1505.4	1505.7	1506.0	1506.3	1507.4	1508.4
167.5°	1531.8	1530.8	1529.7	1528.6	1528.0	1528.0	1528.0	1528.0	1528.0	1529.7	1531.3
170°	1545.6	1544.5	1543.4	1542.3	1541.7	1541.7	1541.7	1541.7	1541.7	1543.4	1545.0
172.5°	1555.3	1554.3	1553.1	1552.1	1551.5	1551.5	1551.5	1551.5	1551.5	1553.1	1554.8
175°	1566.3	1565.3	1564.1	1563.1	1562.5	1562.5	1562.5	1562.5	1562.5	1564.1	1565.8
177.5°	1572.2	1571.3	1570.5	1569.5	1569.1	1568.8	1568.6	1568.4	1568.1	1569.4	1570.7
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1	1731.1
2.5°	1810.3	1815.1	1825.0	1821.6	1826.3	1828.6	1831.0
5°	1956.6	1980.1	1990.4	1989.0	2004.3	2000.6	1997.0
7.5°	2121.8	2146.5	2160.3	2177.5	2187.5	2188.2	2196.9
10°	2215.3	2247.6	2260.8	2279.2	2290.9	2297.5	2296.8
12.5°	2286.9	2312.2	2341.8	2350.9	2366.7	2375.1	2372.0
15°	2373.2	2413.6	2444.5	2459.8	2479.7	2485.6	2493.7
17.5°	2450.2	2504.4	2540.4	2588.3	2606.4	2617.4	2610.9
20°	2508.4	2579.6	2615.6	2673.0	2704.5	2721.5	2715.6
22.5°	2577.2	2654.3	2720.8	2770.5	2818.6	2841.4	2846.1
25°	2695.0	2800.8	2898.5	2963.9	3023.4	3037.3	3068.3
27.5°	2826.7	2951.4	3055.9	3124.7	3166.1	3181.6	3191.4
30°	2909.5	3033.7	3112.4	3156.4	3169.7	3168.2	3166.7
32.5°	2950.1	3027.8	3043.0	3030.7	3000.4	2974.8	2948.1
35°	2892.7	2834.6	2747.9	2636.2	2553.9	2470.9	2462.9
37.5°	2601.5	2415.9	2271.6	2110.4	2017.4	1960.0	1920.3
40°	2327.6	2116.8	1941.9	1806.0	1711.2	1673.8	1637.0
42.5°	2030.2	1828.7	1673.9	1560.3	1489.0	1447.5	1418.3
45°	1649.4	1471.7	1350.5	1268.2	1211.5	1179.2	1160.8
47.5°	1351.6	1220.1	1117.1	1057.7	1018.6	993.5	993.6
50°	1191.8	1066.1	997.8	950.7	916.9	897.1	900.8
52.5°	1050.1	956.2	897.9	858.5	833.5	821.2	820.9
55°	878.0	810.4	772.2	743.6	726.6	712.7	715.7
57.5°	751.0	694.0	668.5	644.7	632.9	627.4	619.3
60°	672.3	628.2	606.1	587.0	575.3	570.9	562.8
62.5°	602.4	567.7	546.2	530.7	520.0	518.6	512.3
65°	506.2	479.8	460.7	453.4	442.3	439.4	439.4
67.5°	417.4	398.4	383.5	376.7	371.9	372.7	369.1
70°	361.5	346.1	336.5	329.1	325.5	326.2	323.3
72.5°	316.2	299.1	290.7	286.3	281.4	283.3	282.1
75°	239.5	230.7	226.3	221.9	219.0	217.4	216.0
77.5°	175.9	168.1	164.8	162.2	162.7	159.1	161.9
80°	135.9	129.3	127.1	123.5	122.7	122.7	122.0
82.5°	99.4	95.8	94.2	91.1	89.8	91.0	89.1
85°	51.5	48.4	47.8	47.8	46.3	44.9	48.4
87.5°	23.6	21.5	21.7	21.2	21.4	21.0	20.0
90°	23.7	25.0	26.1	26.9	27.7	28.6	29.3
92.5°	52.3	54.1	55.3	55.9	56.6	57.1	57.7
95°	99.8	101.8	102.9	103.5	104.1	104.6	105.2
97.5°	155.2	157.0	158.2	158.4	158.8	159.1	159.5
100°	194.4	196.8	198.3	198.9	199.4	200.0	200.5
102.5°	234.1	236.9	238.6	239.3	240.1	240.8	241.6
105°	297.1	298.7	299.9	300.8	301.6	302.4	303.2
107.5°	365.3	366.2	366.6	366.5	366.4	366.4	366.3
110°	413.2	414.1	414.3	414.1	413.8	413.5	413.2



TEST NUMBER: P333479-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	460.8	461.2	461.2	460.7	460.2	459.7	459.2
115°	533.5	533.2	532.9	532.6	532.3	532.2	531.9
117.5°	607.3	607.6	607.1	606.1	604.9	603.9	602.8
120°	656.6	656.6	656.0	654.9	653.8	652.7	651.7
122.5°	704.8	704.6	704.1	703.1	702.3	701.4	700.6
125°	776.0	775.4	775.1	774.8	774.5	774.2	773.9
127.5°	847.2	847.0	846.5	846.0	845.5	844.9	844.3
130°	894.2	893.9	893.4	893.0	892.4	891.8	891.3
132.5°	939.1	938.9	938.4	937.6	936.8	936.0	935.3
135°	1008.7	1008.7	1008.1	1007.0	1006.0	1004.8	1003.8
137.5°	1076.4	1076.8	1076.2	1074.9	1073.5	1072.1	1070.8
140°	1119.1	1119.6	1119.3	1117.9	1116.5	1115.2	1113.8
142.5°	1160.6	1160.8	1160.4	1159.0	1157.6	1156.2	1154.9
145°	1220.2	1220.2	1219.7	1219.0	1218.1	1217.3	1216.5
147.5°	1276.4	1277.1	1276.5	1274.6	1272.8	1270.9	1269.1
150°	1310.7	1310.7	1310.4	1309.9	1309.3	1308.7	1308.2
152.5°	1343.9	1344.5	1344.4	1343.4	1342.5	1341.4	1340.5
155°	1390.9	1392.0	1391.9	1390.5	1389.2	1387.8	1386.5
157.5°	1431.3	1432.4	1432.0	1430.2	1428.4	1426.6	1424.8
160°	1455.8	1456.8	1456.7	1455.4	1454.0	1452.6	1451.2
162.5°	1478.8	1480.2	1480.1	1478.5	1476.9	1475.4	1473.8
165°	1509.6	1510.6	1510.3	1508.7	1507.1	1505.4	1503.8
167.5°	1533.0	1534.6	1534.6	1532.9	1531.2	1529.5	1527.8
170°	1546.6	1548.2	1548.1	1546.2	1544.4	1542.4	1540.5
172.5°	1556.4	1558.0	1558.0	1556.3	1554.6	1552.9	1551.2
175°	1567.4	1569.1	1568.9	1567.0	1565.1	1563.2	1561.3
177.5°	1572.1	1573.4	1573.3	1571.7	1570.2	1568.7	1567.2
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1

(END OF REPORT)