

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333693

Luminaire Tested: **S125RDIW-S850D1340U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333693
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1340U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7932.0 lumens
Efficiency: N/A
Efficacy: 129.2 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41				
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36				
2	88	81	75	70	80	74	69	65	61	58	54	49	47	45	38	37	35	30				
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26				
4	74	63	56	50	67	58	51	46	48	43	39	39	36	33	31	28	26	23				
5	68	56	48	43	61	52	45	40	43	38	34	35	31	29	28	25	23	20				
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	20	17				
7	58	46	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15				
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	21	18	16	14				
9	50	38	30	25	45	35	28	24	29	24	21	24	21	18	20	17	15	13				
10	46	35	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8169	8169	8169	8169
5°	9398	8180	7224	8180
10°	10781	8138	6374	8138
15°	11645	8055	5666	8055
20°	12841	7958	5232	7958
25°	14860	7829	4855	7829
30°	16171	7694	4608	7694
35°	13640	7536	4380	7536
40°	9526	7254	4185	7254
45°	7067	6872	3993	6872
50°	5635	6475	3829	6475
55°	4782	5981	3683	5981
60°	4132	5540	3447	5540
65°	3681	5063	2968	5063
70°	3237	4638	2706	4638
75°	2800	4017	2540	4017
80°	2124	3381	2124	3381
85°	1771	2653	2001	2653



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	1.5
10°-20°	355.5	4.5
20°-30°	563.6	7.1
30°-40°	679.7	8.6
40°-50°	607.0	7.7
50°-60°	465.5	5.9
60°-70°	302.5	3.8
70°-80°	147.1	1.9
80°-90°	38.7	0.5
90°-100°	111.6	1.4
100°-110°	329.7	4.2
110°-120°	558.4	7.0
120°-130°	734.9	9.3
130°-140°	823.5	10.4
140°-150°	807.1	10.2
150°-160°	677.9	8.5
160°-170°	450.6	5.7
170°-180°	157.7	2.0
0°-30°	1040.4	13.1
0°-40°	1720.1	21.7
0°-60°	2792.5	35.2
0°-90°	3280.8	41.4
90°-120°	999.7	12.6
90°-150°	3365.1	42.4
90°-180°	4651.0	58.6
0°-180°	7932.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1265	1265	1265	1265	1265	
5°	1450	1262	1114	1262	1450	145
15°	1742	1205	847	1205	1742	499
25°	2085	1099	681	1099	2085	957
35°	1730	956	556	956	1730	1045
45°	774	752	437	752	774	617
55°	425	531	327	531	425	385
65°	241	331	194	331	241	240
75°	112	161	102	161	112	119
85°	24	36	27	36	24	28
90°	31	1	31	1	31	19
95°	112	84	112	84	112	114
105°	322	296	322	296	322	341
115°	564	559	564	559	564	558
125°	821	816	821	816	821	733
135°	1065	1061	1065	1061	1065	822
145°	1291	1286	1291	1286	1291	806
155°	1471	1471	1471	1471	1471	677
165°	1596	1599	1596	1599	1596	450
175°	1656	1663	1656	1663	1656	157
180°	1667	1667	1667	1667	1667	



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1330.5	1329.7	1331.4	1326.8	1327.2	1320.1	1320.1	1314.7	1307.7	1302.3	1299.8
5°	1449.7	1450.8	1448.7	1440.9	1435.7	1427.9	1419.1	1403.5	1390.5	1378.1	1368.2
7.5°	1572.5	1573.2	1566.4	1564.0	1550.9	1541.3	1521.7	1500.5	1481.7	1457.8	1439.6
10°	1643.9	1643.4	1636.2	1630.4	1619.0	1604.5	1585.3	1560.3	1537.0	1511.0	1486.1
12.5°	1685.5	1684.1	1681.8	1674.9	1664.3	1651.4	1635.1	1610.6	1581.8	1553.4	1524.3
15°	1741.6	1737.9	1731.2	1722.3	1707.3	1692.2	1674.1	1652.3	1624.7	1592.5	1565.5
17.5°	1810.9	1811.0	1800.7	1788.4	1767.9	1741.4	1713.3	1678.1	1640.7	1605.3	1576.5
20°	1868.3	1866.7	1856.3	1832.4	1809.1	1775.8	1743.6	1700.5	1654.8	1608.6	1572.8
22.5°	1950.5	1946.5	1935.7	1904.3	1868.1	1825.3	1776.0	1723.4	1668.1	1615.7	1568.7
25°	2085.3	2082.2	2060.9	2024.6	1973.7	1907.7	1843.3	1771.2	1691.7	1622.7	1565.5
27.5°	2177.5	2174.1	2158.3	2128.1	2081.2	2011.8	1924.6	1828.2	1729.0	1634.0	1551.6
30°	2168.4	2176.2	2174.1	2160.1	2124.8	2062.5	1982.0	1873.5	1755.6	1643.9	1545.8
32.5°	2037.9	2044.9	2063.2	2090.7	2092.8	2067.9	2007.7	1907.5	1785.5	1658.5	1541.2
35°	1730.1	1739.5	1774.8	1830.4	1903.0	1963.8	1976.3	1922.3	1812.7	1676.1	1534.4
37.5°	1330.1	1381.2	1410.9	1469.4	1579.2	1691.0	1798.5	1838.0	1791.4	1668.9	1523.3
40°	1129.9	1142.3	1195.3	1261.3	1353.7	1470.0	1623.2	1733.8	1737.4	1652.3	1505.8
42.5°	967.0	982.8	1019.2	1071.8	1151.0	1267.3	1425.4	1571.4	1639.0	1606.6	1483.0
45°	773.7	785.6	812.1	852.6	913.4	1009.4	1145.5	1314.2	1448.2	1500.6	1421.7
47.5°	635.6	642.0	665.1	695.9	740.9	810.9	916.2	1062.7	1223.4	1336.0	1324.9
50°	560.8	568.1	585.7	609.1	647.0	706.2	790.3	912.3	1078.0	1215.6	1243.1
52.5°	502.6	508.7	519.7	541.8	573.0	618.5	686.4	796.8	945.9	1092.2	1155.8
55°	424.7	428.9	437.7	450.2	475.1	507.8	566.5	642.8	763.3	910.8	1004.2
57.5°	360.6	362.6	368.3	379.8	397.0	420.9	463.3	528.0	614.4	747.2	850.3
60°	319.9	321.9	329.2	337.0	350.5	372.3	405.5	450.7	533.8	643.3	747.7
62.5°	287.5	288.7	291.8	299.6	311.4	328.3	354.4	391.3	457.4	553.6	652.2
65°	240.9	241.5	242.5	248.7	256.0	268.5	285.6	311.5	361.4	434.1	521.3
67.5°	196.3	197.0	200.6	202.8	210.4	216.9	227.0	246.9	282.0	331.0	398.8
70°	171.4	170.8	174.5	177.1	179.7	187.4	194.2	210.3	232.1	269.5	326.1
72.5°	148.1	146.7	148.3	149.2	152.7	158.0	164.7	174.6	191.4	217.1	260.5
75°	112.2	112.7	112.7	113.7	116.3	118.4	120.5	125.7	135.0	152.1	175.5
77.5°	78.7	77.9	80.1	80.4	81.9	84.2	86.0	88.1	91.9	99.0	111.0
80°	57.1	57.1	57.6	59.2	58.7	59.7	62.3	64.4	69.1	73.2	77.4
82.5°	43.8	43.4	43.9	44.2	44.1	45.2	46.1	46.5	48.3	50.4	53.3
85°	23.9	23.9	24.4	24.4	24.9	24.9	25.4	25.4	25.4	26.0	26.5
87.5°	15.4	14.8	14.2	14.0	14.3	14.9	14.2	13.5	13.2	12.9	12.9
90°	31.1	30.3	29.4	28.5	27.7	26.5	25.1	23.6	22.2	20.8	18.7
92.5°	61.2	60.6	60.0	59.3	58.7	57.4	55.5	53.6	51.7	49.8	47.3
95°	111.6	111.0	110.4	109.8	109.2	108.0	105.9	103.9	101.9	99.9	97.0
97.5°	169.2	168.8	168.5	168.1	167.8	166.6	164.7	162.8	160.9	159.0	155.1
100°	212.7	212.2	211.6	211.0	210.4	208.8	206.2	203.7	201.1	198.5	194.7
102.5°	256.3	255.5	254.7	253.9	253.1	251.3	248.4	245.6	242.8	240.0	238.1
105°	321.7	320.8	320.0	319.1	318.2	316.9	315.2	313.5	311.8	310.0	308.3
107.5°	388.6	388.7	388.7	388.8	388.9	388.5	387.6	386.7	385.9	385.0	383.7
110°	438.4	438.7	439.0	439.3	439.6	439.3	438.4	437.6	436.7	435.8	435.0



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.2	487.7	488.3	488.8	489.3	489.3	488.9	488.5	488.1	487.7	486.6
115°	564.3	564.6	564.8	565.1	565.4	565.7	566.0	566.3	566.6	566.9	566.3
117.5°	639.5	640.7	641.8	643.0	644.1	644.6	644.3	644.1	643.9	643.7	643.1
120°	691.4	692.5	693.7	694.8	696.0	696.6	696.6	696.6	696.6	696.6	696.3
122.5°	743.3	744.2	745.1	746.0	747.0	747.5	747.8	748.0	748.2	748.5	747.7
125°	821.1	821.4	821.7	822.0	822.3	822.7	823.3	823.8	824.4	825.0	824.7
127.5°	895.8	896.4	897.0	897.6	898.1	898.6	898.8	899.1	899.4	899.7	899.4
130°	945.6	946.2	946.8	947.4	947.9	948.4	948.7	948.9	949.2	949.5	948.9
132.5°	992.3	993.1	993.9	994.8	995.6	996.1	996.4	996.7	997.0	997.3	997.4
135°	1065.0	1066.1	1067.3	1068.4	1069.6	1070.2	1070.2	1070.2	1070.2	1070.2	1069.9
137.5°	1136.1	1137.5	1138.9	1140.4	1141.8	1142.4	1142.0	1141.7	1141.3	1141.0	1140.4
140°	1181.7	1183.2	1184.6	1186.0	1187.5	1187.9	1187.3	1186.8	1186.2	1185.6	1184.7
142.5°	1225.3	1226.7	1228.2	1229.6	1231.1	1231.6	1231.3	1230.9	1230.6	1230.2	1229.1
145°	1290.7	1291.5	1292.4	1293.3	1294.1	1294.6	1294.6	1294.6	1294.6	1294.6	1293.7
147.5°	1346.5	1348.4	1350.4	1352.3	1354.3	1354.9	1354.2	1353.5	1352.9	1352.2	1351.5
150°	1388.0	1388.5	1389.1	1389.7	1390.3	1390.6	1390.6	1390.6	1390.6	1390.6	1389.4
152.5°	1422.2	1423.2	1424.3	1425.3	1426.4	1426.5	1425.8	1425.1	1424.5	1423.8	1423.3
155°	1471.0	1472.4	1473.9	1475.3	1476.7	1476.9	1475.7	1474.6	1473.4	1472.3	1472.0
157.5°	1511.7	1513.6	1515.5	1517.4	1519.3	1519.7	1518.5	1517.4	1516.2	1515.1	1514.8
160°	1539.7	1541.2	1542.6	1544.1	1545.5	1545.6	1544.5	1543.3	1542.2	1541.0	1540.7
162.5°	1563.6	1565.3	1566.9	1568.6	1570.3	1570.4	1569.0	1567.7	1566.3	1564.9	1564.8
165°	1595.5	1597.2	1599.0	1600.7	1602.4	1602.7	1601.6	1600.4	1599.3	1598.1	1597.8
167.5°	1620.9	1622.7	1624.5	1626.3	1628.1	1628.1	1626.4	1624.7	1622.9	1621.2	1621.2
170°	1634.4	1636.4	1638.5	1640.5	1642.5	1642.6	1640.9	1639.2	1637.5	1635.7	1635.7
172.5°	1645.8	1647.6	1649.4	1651.2	1653.0	1653.0	1651.3	1649.6	1647.8	1646.1	1646.1
175°	1656.5	1658.5	1660.5	1662.5	1664.5	1664.7	1663.0	1661.2	1659.5	1657.8	1657.8
177.5°	1662.7	1664.3	1665.9	1667.5	1669.2	1669.3	1667.9	1666.5	1665.1	1663.7	1664.0
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1299.8	1296.9	1291.5	1286.5	1280.3	1274.9	1271.1	1266.6	1260.7	1253.7	1247.9
5°	1357.3	1345.9	1330.8	1317.9	1301.2	1288.3	1274.8	1261.8	1248.8	1232.2	1217.6
7.5°	1421.1	1397.5	1374.6	1345.7	1319.5	1296.1	1273.7	1251.0	1228.8	1205.2	1182.4
10°	1460.1	1431.6	1399.9	1363.5	1330.3	1298.6	1269.6	1241.0	1210.9	1184.4	1155.8
12.5°	1496.7	1459.8	1423.6	1377.7	1337.8	1299.1	1262.1	1226.5	1194.3	1159.9	1129.3
15°	1529.7	1493.4	1452.9	1396.8	1341.2	1294.5	1250.9	1204.7	1164.7	1126.3	1092.0
17.5°	1542.5	1504.4	1457.3	1403.4	1342.7	1283.9	1227.7	1177.0	1130.0	1085.2	1046.7
20°	1537.5	1500.6	1452.3	1400.9	1336.0	1274.8	1214.0	1157.9	1105.5	1058.2	1017.2
22.5°	1525.4	1487.3	1440.7	1386.4	1324.8	1259.8	1194.9	1135.1	1080.1	1031.2	986.5
25°	1507.4	1455.5	1407.7	1354.7	1296.0	1231.7	1164.7	1098.7	1040.1	990.2	941.4
27.5°	1488.6	1423.8	1363.0	1310.4	1248.4	1190.9	1126.4	1058.7	997.1	946.3	896.2
30°	1471.6	1398.9	1331.9	1272.2	1213.5	1159.0	1097.7	1031.7	968.4	916.0	865.1
32.5°	1450.4	1373.1	1299.5	1230.6	1174.0	1119.9	1064.5	1001.4	939.7	885.6	833.9
35°	1423.8	1325.1	1245.2	1171.9	1109.1	1056.7	1006.8	955.9	894.1	838.1	787.7
37.5°	1388.9	1276.9	1184.4	1104.7	1038.4	985.7	946.4	899.9	843.5	789.8	743.0
40°	1367.7	1242.0	1140.8	1061.9	992.3	936.7	899.9	860.4	809.0	758.6	711.9
42.5°	1339.5	1210.1	1096.8	1014.5	944.5	891.0	853.7	819.3	776.2	728.7	678.7
45°	1284.1	1148.1	1029.2	940.9	870.3	817.8	783.0	752.4	719.7	676.1	632.4
47.5°	1212.0	1083.4	958.9	862.6	793.4	744.7	711.0	686.8	663.4	626.3	583.9
50°	1154.3	1030.2	908.7	815.2	741.5	695.3	663.6	644.4	623.1	589.3	554.0
52.5°	1086.2	975.4	856.3	760.8	691.2	647.9	617.5	598.3	580.7	553.2	519.6
55°	978.8	881.7	772.6	685.9	622.1	578.4	549.4	531.2	520.8	497.4	471.0
57.5°	854.9	785.3	689.1	605.5	549.1	506.0	484.7	469.2	457.5	440.9	422.3
60°	768.5	719.7	633.5	554.0	502.1	461.1	441.9	428.9	418.0	404.0	389.4
62.5°	680.8	645.3	570.3	502.1	454.3	420.0	402.0	390.3	377.7	368.3	354.1
65°	563.4	531.7	479.8	426.3	382.2	354.6	341.7	331.3	323.5	313.1	303.2
67.5°	438.2	425.4	389.5	352.7	321.0	296.5	285.3	278.0	268.7	262.4	255.7
70°	361.4	355.2	329.7	305.3	275.7	259.1	248.7	245.6	234.2	228.0	223.3
72.5°	293.3	290.4	275.7	258.8	237.9	223.4	213.8	210.3	203.0	198.0	195.0
75°	200.9	202.0	199.4	188.5	180.7	171.4	163.0	161.0	155.8	151.6	149.0
77.5°	127.1	132.4	132.6	132.1	129.0	123.3	119.8	118.3	113.2	111.6	111.0
80°	87.2	92.9	98.1	97.6	96.6	95.0	92.4	90.9	88.3	86.7	85.7
82.5°	58.2	63.5	67.8	70.6	70.4	68.9	67.1	66.4	65.8	64.7	64.5
85°	27.5	28.6	30.1	33.8	36.3	36.9	36.3	35.8	34.3	34.8	35.3
87.5°	12.9	12.5	12.5	12.1	11.2	12.8	13.6	13.6	13.2	12.8	12.4
90°	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	44.9	42.4	39.9	37.8	36.2	34.6	33.0	31.4	33.0	34.6	36.2
95°	94.1	91.2	88.4	86.6	86.0	85.5	84.9	84.3	84.9	85.5	86.0
97.5°	151.1	147.1	143.1	141.0	140.8	140.6	140.3	140.1	140.3	140.6	140.8
100°	191.0	187.2	183.5	181.6	181.6	181.6	181.6	181.6	181.6	181.6	181.6
102.5°	236.2	234.3	232.4	230.8	229.7	228.5	227.4	226.2	227.4	228.5	229.7
105°	306.6	304.8	303.1	301.5	300.1	298.6	297.2	295.8	297.2	298.6	300.1
107.5°	382.3	381.0	379.7	378.3	376.9	375.4	374.0	372.5	374.0	375.4	376.9
110°	434.1	433.3	432.4	431.2	429.8	428.4	426.9	425.5	426.9	428.4	429.8



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	485.5	484.4	483.4	482.4	481.7	480.9	480.2	479.4	480.2	480.9	481.7
115°	565.7	565.1	564.6	563.7	562.5	561.4	560.2	559.1	560.2	561.4	562.5
117.5°	642.6	642.1	641.6	641.1	640.5	640.0	639.5	639.0	639.5	640.0	640.5
120°	696.0	695.7	695.4	694.6	693.1	691.7	690.2	688.8	690.2	691.7	693.1
122.5°	747.0	746.2	745.5	744.8	744.3	743.8	743.3	742.8	743.3	743.8	744.3
125°	824.4	824.1	823.8	822.8	821.1	819.4	817.6	815.9	817.6	819.4	821.1
127.5°	899.0	898.7	898.3	897.7	896.7	895.7	894.7	893.7	894.7	895.7	896.7
130°	948.4	947.8	947.2	946.2	944.8	943.3	941.9	940.4	941.9	943.3	944.8
132.5°	997.5	997.6	997.7	996.6	994.2	991.9	989.5	987.1	989.5	991.9	994.2
135°	1069.6	1069.3	1069.0	1068.0	1066.3	1064.5	1062.8	1061.1	1062.8	1064.5	1066.3
137.5°	1139.7	1139.1	1138.4	1137.3	1135.6	1134.0	1132.3	1130.6	1132.3	1134.0	1135.6
140°	1183.9	1183.0	1182.1	1181.0	1179.6	1178.1	1176.7	1175.2	1176.7	1178.1	1179.6
142.5°	1228.0	1226.9	1225.8	1224.7	1223.5	1222.3	1221.1	1219.9	1221.1	1222.3	1223.5
145°	1292.8	1292.0	1291.1	1290.1	1288.9	1287.8	1286.6	1285.5	1286.6	1287.8	1288.9
147.5°	1350.8	1350.1	1349.4	1348.7	1348.1	1347.5	1346.8	1346.2	1346.8	1347.5	1348.1
150°	1388.3	1387.1	1385.9	1385.5	1385.8	1386.1	1386.4	1386.7	1386.4	1386.1	1385.8
152.5°	1422.8	1422.4	1421.9	1421.5	1421.1	1420.7	1420.3	1419.9	1420.3	1420.7	1421.1
155°	1471.7	1471.4	1471.1	1471.0	1471.0	1471.0	1471.0	1471.0	1471.0	1471.0	1471.0
157.5°	1514.5	1514.2	1513.9	1514.1	1514.7	1515.4	1516.0	1516.6	1516.0	1515.4	1514.7
160°	1540.5	1540.2	1539.9	1540.2	1541.0	1541.9	1542.8	1543.6	1542.8	1541.9	1541.0
162.5°	1564.8	1564.7	1564.7	1565.0	1565.6	1566.2	1566.9	1567.5	1566.9	1566.2	1565.6
165°	1597.5	1597.2	1597.0	1597.1	1597.7	1598.2	1598.8	1599.4	1598.8	1598.2	1597.7
167.5°	1621.2	1621.2	1621.2	1621.8	1622.9	1624.1	1625.2	1626.4	1625.2	1624.1	1622.9
170°	1635.7	1635.7	1635.7	1636.3	1637.5	1638.6	1639.8	1640.9	1639.8	1638.6	1637.5
172.5°	1646.1	1646.1	1646.1	1646.7	1647.8	1649.0	1650.1	1651.3	1650.1	1649.0	1647.8
175°	1657.8	1657.8	1657.8	1658.4	1659.5	1660.7	1661.8	1663.0	1661.8	1660.7	1659.5
177.5°	1664.2	1664.4	1664.7	1665.2	1666.2	1667.1	1668.0	1668.9	1668.0	1667.1	1666.2
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1243.7	1237.9	1233.7	1225.4	1219.6	1217.1	1212.6	1211.3	1215.9	1212.6	1212.1
5°	1206.7	1191.7	1179.7	1167.8	1154.8	1146.5	1134.0	1132.0	1128.8	1124.2	1123.1
7.5°	1162.4	1142.8	1127.4	1107.7	1090.5	1076.7	1061.1	1053.8	1049.7	1043.7	1035.6
10°	1132.5	1109.1	1088.3	1068.6	1047.3	1030.2	1014.6	1002.7	994.9	987.6	984.5
12.5°	1103.0	1079.2	1052.6	1028.7	1005.0	985.7	968.5	960.7	952.1	943.6	936.3
15°	1057.2	1025.5	996.4	968.9	948.7	927.9	911.3	899.9	886.9	883.2	869.2
17.5°	1008.6	977.5	943.5	914.5	891.0	868.2	849.9	836.9	827.2	813.8	807.3
20°	978.3	941.4	908.2	881.7	855.7	828.7	810.0	799.1	789.8	778.9	773.7
22.5°	945.9	909.8	875.8	844.7	818.3	791.8	778.5	767.1	756.5	746.5	739.6
25°	898.3	862.0	826.1	793.9	766.4	747.2	731.6	718.6	712.9	703.1	695.8
27.5°	851.3	812.6	775.4	743.4	721.8	702.8	690.0	679.7	669.4	660.8	654.5
30°	820.9	781.5	741.0	715.5	692.7	674.5	660.5	650.6	642.8	635.0	630.4
32.5°	790.6	749.9	714.0	686.4	664.8	649.2	634.7	625.3	617.1	608.5	603.0
35°	742.0	700.5	671.4	644.4	623.1	608.6	598.7	585.2	578.4	572.2	566.5
37.5°	696.8	658.2	626.7	603.1	584.6	570.1	557.4	550.1	541.8	536.2	531.4
40°	663.6	628.3	599.7	574.8	561.3	545.2	533.3	523.9	517.7	510.4	505.2
42.5°	633.7	600.9	573.1	550.7	533.9	520.3	508.8	499.4	491.5	486.3	482.0
45°	591.4	558.7	531.7	510.9	495.4	482.4	470.4	465.8	455.4	449.2	447.1
47.5°	547.7	518.4	492.4	473.2	457.3	445.0	433.8	424.2	418.5	412.4	409.1
50°	518.2	490.2	465.8	447.1	431.5	418.0	407.6	401.4	393.6	387.9	383.7
52.5°	488.7	462.8	438.4	420.5	407.0	393.5	381.9	375.6	368.3	364.6	361.7
55°	446.6	419.0	398.3	380.6	366.6	354.1	343.2	337.0	332.3	328.7	327.6
57.5°	398.8	377.0	357.7	341.8	327.2	315.5	305.9	300.0	295.9	295.3	292.2
60°	367.6	347.9	330.2	313.1	300.6	289.7	281.4	274.7	270.5	270.0	269.0
62.5°	336.5	317.6	301.2	286.1	274.9	264.4	256.5	248.9	246.4	243.8	241.6
65°	290.3	273.1	259.6	247.7	235.7	226.9	219.1	214.4	208.7	205.6	199.9
67.5°	244.9	231.6	218.6	208.5	199.2	190.8	184.3	177.4	173.5	171.0	166.9
70°	215.0	204.6	191.6	180.7	173.4	166.7	161.5	153.7	151.1	149.0	146.9
72.5°	186.7	177.6	166.7	157.9	150.6	144.2	138.2	134.6	132.0	129.9	128.7
75°	146.9	138.1	128.8	122.5	117.4	112.2	109.0	106.4	105.4	104.9	102.8
77.5°	107.9	103.2	95.7	90.8	87.3	85.3	82.5	81.1	81.0	78.7	78.0
80°	82.6	80.0	73.7	71.7	69.1	67.0	65.4	62.8	60.2	59.2	57.6
82.5°	61.4	58.8	56.3	53.0	50.8	49.5	48.0	47.0	47.4	45.9	45.2
85°	32.7	30.1	29.1	28.6	27.5	28.6	28.0	27.5	27.0	26.5	27.0
87.5°	12.5	12.9	12.9	14.1	13.3	14.1	14.4	14.3	14.6	14.9	14.7
90°	10.5	12.7	14.7	16.7	18.7	20.8	22.2	23.6	25.1	26.5	27.7
92.5°	37.8	39.9	42.4	44.9	47.3	49.8	51.7	53.6	55.5	57.4	58.7
95°	86.6	88.4	91.2	94.1	97.0	99.9	101.9	103.9	105.9	108.0	109.2
97.5°	141.0	143.1	147.1	151.1	155.1	159.0	160.9	162.8	164.7	166.6	167.8
100°	181.6	183.5	187.2	191.0	194.7	198.5	201.1	203.7	206.2	208.8	210.4
102.5°	230.8	232.4	234.3	236.2	238.1	240.0	242.8	245.6	248.4	251.3	253.1
105°	301.5	303.1	304.8	306.6	308.3	310.0	311.8	313.5	315.2	316.9	318.2
107.5°	378.3	379.7	381.0	382.3	383.7	385.0	385.9	386.7	387.6	388.5	388.9
110°	431.2	432.4	433.3	434.1	435.0	435.8	436.7	437.6	438.4	439.3	439.6



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	482.4	483.4	484.4	485.5	486.6	487.7	488.1	488.5	488.9	489.3	489.3
115°	563.7	564.6	565.1	565.7	566.3	566.9	566.6	566.3	566.0	565.7	565.4
117.5°	641.1	641.6	642.1	642.6	643.1	643.7	643.9	644.1	644.3	644.6	644.1
120°	694.6	695.4	695.7	696.0	696.3	696.6	696.6	696.6	696.6	696.6	696.0
122.5°	744.8	745.5	746.2	747.0	747.7	748.5	748.2	748.0	747.8	747.5	747.0
125°	822.8	823.8	824.1	824.4	824.7	825.0	824.4	823.8	823.3	822.7	822.3
127.5°	897.7	898.3	898.7	899.0	899.4	899.7	899.4	899.1	898.8	898.6	898.1
130°	946.2	947.2	947.8	948.4	948.9	949.5	949.2	948.9	948.7	948.4	947.9
132.5°	996.6	997.7	997.6	997.5	997.4	997.3	997.0	996.7	996.4	996.1	995.6
135°	1068.0	1069.0	1069.3	1069.6	1069.9	1070.2	1070.2	1070.2	1070.2	1070.2	1069.6
137.5°	1137.3	1138.4	1139.1	1139.7	1140.4	1141.0	1141.3	1141.7	1142.0	1142.4	1141.8
140°	1181.0	1182.1	1183.0	1183.9	1184.7	1185.6	1186.2	1186.8	1187.3	1187.9	1187.5
142.5°	1224.7	1225.8	1226.9	1228.0	1229.1	1230.2	1230.6	1230.9	1231.3	1231.6	1231.1
145°	1290.1	1291.1	1292.0	1292.8	1293.7	1294.6	1294.6	1294.6	1294.6	1294.6	1294.1
147.5°	1348.7	1349.4	1350.1	1350.8	1351.5	1352.2	1352.9	1353.5	1354.2	1354.9	1354.3
150°	1385.5	1385.9	1387.1	1388.3	1389.4	1390.6	1390.6	1390.6	1390.6	1390.6	1390.3
152.5°	1421.5	1421.9	1422.4	1422.8	1423.3	1423.8	1424.5	1425.1	1425.8	1426.5	1426.4
155°	1471.0	1471.1	1471.4	1471.7	1472.0	1472.3	1473.4	1474.6	1475.7	1476.9	1476.7
157.5°	1514.1	1513.9	1514.2	1514.5	1514.8	1515.1	1516.2	1517.4	1518.5	1519.7	1519.3
160°	1540.2	1539.9	1540.2	1540.5	1540.7	1541.0	1542.2	1543.3	1544.5	1545.6	1545.5
162.5°	1565.0	1564.7	1564.7	1564.8	1564.8	1564.9	1566.3	1567.7	1569.0	1570.4	1570.3
165°	1597.1	1597.0	1597.2	1597.5	1597.8	1598.1	1599.3	1600.4	1601.6	1602.7	1602.4
167.5°	1621.8	1621.2	1621.2	1621.2	1621.2	1621.2	1622.9	1624.7	1626.4	1628.1	1628.1
170°	1636.3	1635.7	1635.7	1635.7	1635.7	1635.7	1637.5	1639.2	1640.9	1642.6	1642.5
172.5°	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.8	1649.6	1651.3	1653.0	1653.0
175°	1658.4	1657.8	1657.8	1657.8	1657.8	1657.8	1659.5	1661.2	1663.0	1664.7	1664.5
177.5°	1665.2	1664.7	1664.4	1664.2	1664.0	1663.7	1665.1	1666.5	1667.9	1669.3	1669.2
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1211.7	1207.2	1205.9	1207.6	1205.9	1207.2	1211.7	1212.1	1212.6	1215.9	1211.3
5°	1117.9	1112.8	1115.3	1114.3	1115.3	1112.8	1117.9	1123.1	1124.2	1128.8	1132.0
7.5°	1035.5	1029.0	1022.2	1024.4	1022.2	1029.0	1035.5	1035.6	1043.7	1049.7	1053.8
10°	977.7	972.6	969.4	972.0	969.4	972.6	977.7	984.5	987.6	994.9	1002.7
12.5°	929.1	926.0	923.3	922.2	923.3	926.0	929.1	936.3	943.6	952.1	960.7
15°	863.0	856.8	854.2	847.4	854.2	856.8	863.0	869.2	883.2	886.9	899.9
17.5°	802.0	800.0	793.2	790.3	793.2	800.0	802.0	807.3	813.8	827.2	836.9
20°	765.9	763.8	757.1	761.2	757.1	763.8	765.9	773.7	778.9	789.8	799.1
22.5°	736.0	731.4	729.2	728.0	729.2	731.4	736.0	739.6	746.5	756.5	767.1
25°	693.7	687.0	684.4	681.3	684.4	687.0	693.7	695.8	703.1	712.9	718.6
27.5°	651.6	647.9	644.5	643.7	644.5	647.9	651.6	654.5	660.8	669.4	679.7
30°	624.1	620.5	617.9	617.9	617.9	620.5	624.1	630.4	635.0	642.8	650.6
32.5°	599.6	596.8	594.2	593.8	594.2	596.8	599.6	603.0	608.5	617.1	625.3
35°	563.9	559.8	558.7	555.6	558.7	559.8	563.9	566.5	572.2	578.4	585.2
37.5°	526.8	523.4	523.3	523.0	523.3	523.4	526.8	531.4	536.2	541.8	550.1
40°	503.2	500.6	500.0	496.4	500.0	500.6	503.2	505.2	510.4	517.7	523.9
42.5°	477.8	476.5	474.7	473.1	474.7	476.5	477.8	482.0	486.3	491.5	499.4
45°	443.4	439.8	439.8	437.2	439.8	439.8	443.4	447.1	449.2	455.4	465.8
47.5°	407.9	405.1	405.4	402.7	405.4	405.1	407.9	409.1	412.4	418.5	424.2
50°	384.2	382.7	382.2	381.1	382.2	382.7	384.2	383.7	387.9	393.6	401.4
52.5°	360.6	359.8	361.8	359.5	361.8	359.8	360.6	361.7	364.6	368.3	375.6
55°	328.7	327.1	330.2	327.1	330.2	327.1	328.7	327.6	328.7	332.3	337.0
57.5°	292.0	290.6	293.4	291.8	293.4	290.6	292.0	292.2	295.3	295.9	300.0
60°	267.9	264.8	266.4	266.9	266.4	264.8	267.9	269.0	270.0	270.5	274.7
62.5°	239.3	237.4	238.5	236.2	238.5	237.4	239.3	241.6	243.8	246.4	248.9
65°	198.9	197.3	195.2	194.2	195.2	197.3	198.9	199.9	205.6	208.7	214.4
67.5°	167.1	163.4	163.3	164.1	163.3	163.4	167.1	166.9	171.0	173.5	177.4
70°	143.8	143.8	143.3	143.3	143.3	143.8	143.8	146.9	149.0	151.1	153.7
72.5°	127.6	127.2	126.3	125.9	126.3	127.2	127.6	128.7	129.9	132.0	134.6
75°	102.8	103.3	102.3	101.8	102.3	103.3	102.8	102.8	104.9	105.4	106.4
77.5°	75.9	73.7	74.9	73.7	74.9	73.7	75.9	78.0	78.7	81.0	81.1
80°	57.6	57.1	58.7	57.1	58.7	57.1	57.6	57.6	59.2	60.2	62.8
82.5°	45.6	45.1	45.8	44.7	45.8	45.1	45.6	45.2	45.9	47.4	47.0
85°	27.5	27.0	26.5	27.0	26.5	27.0	27.5	27.0	26.5	27.0	27.5
87.5°	15.3	15.0	15.2	15.4	15.2	15.0	15.3	14.7	14.9	14.6	14.3
90°	28.5	29.4	30.3	31.1	30.3	29.4	28.5	27.7	26.5	25.1	23.6
92.5°	59.3	60.0	60.6	61.2	60.6	60.0	59.3	58.7	57.4	55.5	53.6
95°	109.8	110.4	111.0	111.6	111.0	110.4	109.8	109.2	108.0	105.9	103.9
97.5°	168.1	168.5	168.8	169.2	168.8	168.5	168.1	167.8	166.6	164.7	162.8
100°	211.0	211.6	212.2	212.7	212.2	211.6	211.0	210.4	208.8	206.2	203.7
102.5°	253.9	254.7	255.5	256.3	255.5	254.7	253.9	253.1	251.3	248.4	245.6
105°	319.1	320.0	320.8	321.7	320.8	320.0	319.1	318.2	316.9	315.2	313.5
107.5°	388.8	388.7	388.7	388.6	388.7	388.7	388.8	388.9	388.5	387.6	386.7
110°	439.3	439.0	438.7	438.4	438.7	439.0	439.3	439.6	439.3	438.4	437.6



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	488.8	488.3	487.7	487.2	487.7	488.3	488.8	489.3	489.3	488.9	488.5
115°	565.1	564.8	564.6	564.3	564.6	564.8	565.1	565.4	565.7	566.0	566.3
117.5°	643.0	641.8	640.7	639.5	640.7	641.8	643.0	644.1	644.6	644.3	644.1
120°	694.8	693.7	692.5	691.4	692.5	693.7	694.8	696.0	696.6	696.6	696.6
122.5°	746.0	745.1	744.2	743.3	744.2	745.1	746.0	747.0	747.5	747.8	748.0
125°	822.0	821.7	821.4	821.1	821.4	821.7	822.0	822.3	822.7	823.3	823.8
127.5°	897.6	897.0	896.4	895.8	896.4	897.0	897.6	898.1	898.6	898.8	899.1
130°	947.4	946.8	946.2	945.6	946.2	946.8	947.4	947.9	948.4	948.7	948.9
132.5°	994.8	993.9	993.1	992.3	993.1	993.9	994.8	995.6	996.1	996.4	996.7
135°	1068.4	1067.3	1066.1	1065.0	1066.1	1067.3	1068.4	1069.6	1070.2	1070.2	1070.2
137.5°	1140.4	1138.9	1137.5	1136.1	1137.5	1138.9	1140.4	1141.8	1142.4	1142.0	1141.7
140°	1186.0	1184.6	1183.2	1181.7	1183.2	1184.6	1186.0	1187.5	1187.9	1187.3	1186.8
142.5°	1229.6	1228.2	1226.7	1225.3	1226.7	1228.2	1229.6	1231.1	1231.6	1231.3	1230.9
145°	1293.3	1292.4	1291.5	1290.7	1291.5	1292.4	1293.3	1294.1	1294.6	1294.6	1294.6
147.5°	1352.3	1350.4	1348.4	1346.5	1348.4	1350.4	1352.3	1354.3	1354.9	1354.2	1353.5
150°	1389.7	1389.1	1388.5	1388.0	1388.5	1389.1	1389.7	1390.3	1390.6	1390.6	1390.6
152.5°	1425.3	1424.3	1423.2	1422.2	1423.2	1424.3	1425.3	1426.4	1426.5	1425.8	1425.1
155°	1475.3	1473.9	1472.4	1471.0	1472.4	1473.9	1475.3	1476.7	1476.9	1475.7	1474.6
157.5°	1517.4	1515.5	1513.6	1511.7	1513.6	1515.5	1517.4	1519.3	1519.7	1518.5	1517.4
160°	1544.1	1542.6	1541.2	1539.7	1541.2	1542.6	1544.1	1545.5	1545.6	1544.5	1543.3
162.5°	1568.6	1566.9	1565.3	1563.6	1565.3	1566.9	1568.6	1570.3	1570.4	1569.0	1567.7
165°	1600.7	1599.0	1597.2	1595.5	1597.2	1599.0	1600.7	1602.4	1602.7	1601.6	1600.4
167.5°	1626.3	1624.5	1622.7	1620.9	1622.7	1624.5	1626.3	1628.1	1628.1	1626.4	1624.7
170°	1640.5	1638.5	1636.4	1634.4	1636.4	1638.5	1640.5	1642.5	1642.6	1640.9	1639.2
172.5°	1651.2	1649.4	1647.6	1645.8	1647.6	1649.4	1651.2	1653.0	1653.0	1651.3	1649.6
175°	1662.5	1660.5	1658.5	1656.5	1658.5	1660.5	1662.5	1664.5	1664.7	1663.0	1661.2
177.5°	1667.5	1665.9	1664.3	1662.7	1664.3	1665.9	1667.5	1669.2	1669.3	1667.9	1666.5
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1212.6	1217.1	1219.6	1225.4	1233.7	1237.9	1243.7	1247.9	1253.7	1260.7	1266.6
5°	1134.0	1146.5	1154.8	1167.8	1179.7	1191.7	1206.7	1217.6	1232.2	1248.8	1261.8
7.5°	1061.1	1076.7	1090.5	1107.7	1127.4	1142.8	1162.4	1182.4	1205.2	1228.8	1251.0
10°	1014.6	1030.2	1047.3	1068.6	1088.3	1109.1	1132.5	1155.8	1184.4	1210.9	1241.0
12.5°	968.5	985.7	1005.0	1028.7	1052.6	1079.2	1103.0	1129.3	1159.9	1194.3	1226.5
15°	911.3	927.9	948.7	968.9	996.4	1025.5	1057.2	1092.0	1126.3	1164.7	1204.7
17.5°	849.9	868.2	891.0	914.5	943.5	977.5	1008.6	1046.7	1085.2	1130.0	1177.0
20°	810.0	828.7	855.7	881.7	908.2	941.4	978.3	1017.2	1058.2	1105.5	1157.9
22.5°	778.5	791.8	818.3	844.7	875.8	909.8	945.9	986.5	1031.2	1080.1	1135.1
25°	731.6	747.2	766.4	793.9	826.1	862.0	898.3	941.4	990.2	1040.1	1098.7
27.5°	690.0	702.8	721.8	743.4	775.4	812.6	851.3	896.2	946.3	997.1	1058.7
30°	660.5	674.5	692.7	715.5	741.0	781.5	820.9	865.1	916.0	968.4	1031.7
32.5°	634.7	649.2	664.8	686.4	714.0	749.9	790.6	833.9	885.6	939.7	1001.4
35°	598.7	608.6	623.1	644.4	671.4	700.5	742.0	787.7	838.1	894.1	955.9
37.5°	557.4	570.1	584.6	603.1	626.7	658.2	696.8	743.0	789.8	843.5	899.9
40°	533.3	545.2	561.3	574.8	599.7	628.3	663.6	711.9	758.6	809.0	860.4
42.5°	508.8	520.3	533.9	550.7	573.1	600.9	633.7	678.7	728.7	776.2	819.3
45°	470.4	482.4	495.4	510.9	531.7	558.7	591.4	632.4	676.1	719.7	752.4
47.5°	433.8	445.0	457.3	473.2	492.4	518.4	547.7	583.9	626.3	663.4	686.8
50°	407.6	418.0	431.5	447.1	465.8	490.2	518.2	554.0	589.3	623.1	644.4
52.5°	381.9	393.5	407.0	420.5	438.4	462.8	488.7	519.6	553.2	580.7	598.3
55°	343.2	354.1	366.6	380.6	398.3	419.0	446.6	471.0	497.4	520.8	531.2
57.5°	305.9	315.5	327.2	341.8	357.7	377.0	398.8	422.3	440.9	457.5	469.2
60°	281.4	289.7	300.6	313.1	330.2	347.9	367.6	389.4	404.0	418.0	428.9
62.5°	256.5	264.4	274.9	286.1	301.2	317.6	336.5	354.1	368.3	377.7	390.3
65°	219.1	226.9	235.7	247.7	259.6	273.1	290.3	303.2	313.1	323.5	331.3
67.5°	184.3	190.8	199.2	208.5	218.6	231.6	244.9	255.7	262.4	268.7	278.0
70°	161.5	166.7	173.4	180.7	191.6	204.6	215.0	223.3	228.0	234.2	245.6
72.5°	138.2	144.2	150.6	157.9	166.7	177.6	186.7	195.0	198.0	203.0	210.3
75°	109.0	112.2	117.4	122.5	128.8	138.1	146.9	149.0	151.6	155.8	161.0
77.5°	82.5	85.3	87.3	90.8	95.7	103.2	107.9	111.0	111.6	113.2	118.3
80°	65.4	67.0	69.1	71.7	73.7	80.0	82.6	85.7	86.7	88.3	90.9
82.5°	48.0	49.5	50.8	53.0	56.3	58.8	61.4	64.5	64.7	65.8	66.4
85°	28.0	28.6	27.5	28.6	29.1	30.1	32.7	35.3	34.8	34.3	35.8
87.5°	14.4	14.1	13.3	14.1	12.9	12.9	12.5	12.4	12.8	13.2	13.6
90°	22.2	20.8	18.7	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3
92.5°	51.7	49.8	47.3	44.9	42.4	39.9	37.8	36.2	34.6	33.0	31.4
95°	101.9	99.9	97.0	94.1	91.2	88.4	86.6	86.0	85.5	84.9	84.3
97.5°	160.9	159.0	155.1	151.1	147.1	143.1	141.0	140.8	140.6	140.3	140.1
100°	201.1	198.5	194.7	191.0	187.2	183.5	181.6	181.6	181.6	181.6	181.6
102.5°	242.8	240.0	238.1	236.2	234.3	232.4	230.8	229.7	228.5	227.4	226.2
105°	311.8	310.0	308.3	306.6	304.8	303.1	301.5	300.1	298.6	297.2	295.8
107.5°	385.9	385.0	383.7	382.3	381.0	379.7	378.3	376.9	375.4	374.0	372.5
110°	436.7	435.8	435.0	434.1	433.3	432.4	431.2	429.8	428.4	426.9	425.5



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	488.1	487.7	486.6	485.5	484.4	483.4	482.4	481.7	480.9	480.2	479.4
115°	566.6	566.9	566.3	565.7	565.1	564.6	563.7	562.5	561.4	560.2	559.1
117.5°	643.9	643.7	643.1	642.6	642.1	641.6	641.1	640.5	640.0	639.5	639.0
120°	696.6	696.6	696.3	696.0	695.7	695.4	694.6	693.1	691.7	690.2	688.8
122.5°	748.2	748.5	747.7	747.0	746.2	745.5	744.8	744.3	743.8	743.3	742.8
125°	824.4	825.0	824.7	824.4	824.1	823.8	822.8	821.1	819.4	817.6	815.9
127.5°	899.4	899.7	899.4	899.0	898.7	898.3	897.7	896.7	895.7	894.7	893.7
130°	949.2	949.5	948.9	948.4	947.8	947.2	946.2	944.8	943.3	941.9	940.4
132.5°	997.0	997.3	997.4	997.5	997.6	997.7	996.6	994.2	991.9	989.5	987.1
135°	1070.2	1070.2	1069.9	1069.6	1069.3	1069.0	1068.0	1066.3	1064.5	1062.8	1061.1
137.5°	1141.3	1141.0	1140.4	1139.7	1139.1	1138.4	1137.3	1135.6	1134.0	1132.3	1130.6
140°	1186.2	1185.6	1184.7	1183.9	1183.0	1182.1	1181.0	1179.6	1178.1	1176.7	1175.2
142.5°	1230.6	1230.2	1229.1	1228.0	1226.9	1225.8	1224.7	1223.5	1222.3	1221.1	1219.9
145°	1294.6	1294.6	1293.7	1292.8	1292.0	1291.1	1290.1	1288.9	1287.8	1286.6	1285.5
147.5°	1352.9	1352.2	1351.5	1350.8	1350.1	1349.4	1348.7	1348.1	1347.5	1346.8	1346.2
150°	1390.6	1390.6	1389.4	1388.3	1387.1	1385.9	1385.5	1385.8	1386.1	1386.4	1386.7
152.5°	1424.5	1423.8	1423.3	1422.8	1422.4	1421.9	1421.5	1421.1	1420.7	1420.3	1419.9
155°	1473.4	1472.3	1472.0	1471.7	1471.4	1471.1	1471.0	1471.0	1471.0	1471.0	1471.0
157.5°	1516.2	1515.1	1514.8	1514.5	1514.2	1513.9	1514.1	1514.7	1515.4	1516.0	1516.6
160°	1542.2	1541.0	1540.7	1540.5	1540.2	1539.9	1540.2	1541.0	1541.9	1542.8	1543.6
162.5°	1566.3	1564.9	1564.8	1564.8	1564.7	1564.7	1565.0	1565.6	1566.2	1566.9	1567.5
165°	1599.3	1598.1	1597.8	1597.5	1597.2	1597.0	1597.1	1597.7	1598.2	1598.8	1599.4
167.5°	1622.9	1621.2	1621.2	1621.2	1621.2	1621.2	1621.8	1622.9	1624.1	1625.2	1626.4
170°	1637.5	1635.7	1635.7	1635.7	1635.7	1635.7	1636.3	1637.5	1638.6	1639.8	1640.9
172.5°	1647.8	1646.1	1646.1	1646.1	1646.1	1646.1	1646.7	1647.8	1649.0	1650.1	1651.3
175°	1659.5	1657.8	1657.8	1657.8	1657.8	1657.8	1658.4	1659.5	1660.7	1661.8	1663.0
177.5°	1665.1	1663.7	1664.0	1664.2	1664.4	1664.7	1665.2	1666.2	1667.1	1668.0	1668.9
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1271.1	1274.9	1280.3	1286.5	1291.5	1296.9	1299.8	1299.8	1302.3	1307.7	1314.7
5°	1274.8	1288.3	1301.2	1317.9	1330.8	1345.9	1357.3	1368.2	1378.1	1390.5	1403.5
7.5°	1273.7	1296.1	1319.5	1345.7	1374.6	1397.5	1421.1	1439.6	1457.8	1481.7	1500.5
10°	1269.6	1298.6	1330.3	1363.5	1399.9	1431.6	1460.1	1486.1	1511.0	1537.0	1560.3
12.5°	1262.1	1299.1	1337.8	1377.7	1423.6	1459.8	1496.7	1524.3	1553.4	1581.8	1610.6
15°	1250.9	1294.5	1341.2	1396.8	1452.9	1493.4	1529.7	1565.5	1592.5	1624.7	1652.3
17.5°	1227.7	1283.9	1342.7	1403.4	1457.3	1504.4	1542.5	1576.5	1605.3	1640.7	1678.1
20°	1214.0	1274.8	1336.0	1400.9	1452.3	1500.6	1537.5	1572.8	1608.6	1654.8	1700.5
22.5°	1194.9	1259.8	1324.8	1386.4	1440.7	1487.3	1525.4	1568.7	1615.7	1668.1	1723.4
25°	1164.7	1231.7	1296.0	1354.7	1407.7	1455.5	1507.4	1565.5	1622.7	1691.7	1771.2
27.5°	1126.4	1190.9	1248.4	1310.4	1363.0	1423.8	1488.6	1551.6	1634.0	1729.0	1828.2
30°	1097.7	1159.0	1213.5	1272.2	1331.9	1398.9	1471.6	1545.8	1643.9	1755.6	1873.5
32.5°	1064.5	1119.9	1174.0	1230.6	1299.5	1373.1	1450.4	1541.2	1658.5	1785.5	1907.5
35°	1006.8	1056.7	1109.1	1171.9	1245.2	1325.1	1423.8	1534.4	1676.1	1812.7	1922.3
37.5°	946.4	985.7	1038.4	1104.7	1184.4	1276.9	1388.9	1523.3	1668.9	1791.4	1838.0
40°	899.9	936.7	992.3	1061.9	1140.8	1242.0	1367.7	1505.8	1652.3	1737.4	1733.8
42.5°	853.7	891.0	944.5	1014.5	1096.8	1210.1	1339.5	1483.0	1606.6	1639.0	1571.4
45°	783.0	817.8	870.3	940.9	1029.2	1148.1	1284.1	1421.7	1500.6	1448.2	1314.2
47.5°	711.0	744.7	793.4	862.6	958.9	1083.4	1212.0	1324.9	1336.0	1223.4	1062.7
50°	663.6	695.3	741.5	815.2	908.7	1030.2	1154.3	1243.1	1215.6	1078.0	912.3
52.5°	617.5	647.9	691.2	760.8	856.3	975.4	1086.2	1155.8	1092.2	945.9	796.8
55°	549.4	578.4	622.1	685.9	772.6	881.7	978.8	1004.2	910.8	763.3	642.8
57.5°	484.7	506.0	549.1	605.5	689.1	785.3	854.9	850.3	747.2	614.4	528.0
60°	441.9	461.1	502.1	554.0	633.5	719.7	768.5	747.7	643.3	533.8	450.7
62.5°	402.0	420.0	454.3	502.1	570.3	645.3	680.8	652.2	553.6	457.4	391.3
65°	341.7	354.6	382.2	426.3	479.8	531.7	563.4	521.3	434.1	361.4	311.5
67.5°	285.3	296.5	321.0	352.7	389.5	425.4	438.2	398.8	331.0	282.0	246.9
70°	248.7	259.1	275.7	305.3	329.7	355.2	361.4	326.1	269.5	232.1	210.3
72.5°	213.8	223.4	237.9	258.8	275.7	290.4	293.3	260.5	217.1	191.4	174.6
75°	163.0	171.4	180.7	188.5	199.4	202.0	200.9	175.5	152.1	135.0	125.7
77.5°	119.8	123.3	129.0	132.1	132.6	132.4	127.1	111.0	99.0	91.9	88.1
80°	92.4	95.0	96.6	97.6	98.1	92.9	87.2	77.4	73.2	69.1	64.4
82.5°	67.1	68.9	70.4	70.6	67.8	63.5	58.2	53.3	50.4	48.3	46.5
85°	36.3	36.9	36.3	33.8	30.1	28.6	27.5	26.5	26.0	25.4	25.4
87.5°	13.6	12.8	11.2	12.1	12.5	12.5	12.9	12.9	12.9	13.2	13.5
90°	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.8	22.2	23.6
92.5°	33.0	34.6	36.2	37.8	39.9	42.4	44.9	47.3	49.8	51.7	53.6
95°	84.9	85.5	86.0	86.6	88.4	91.2	94.1	97.0	99.9	101.9	103.9
97.5°	140.3	140.6	140.8	141.0	143.1	147.1	151.1	155.1	159.0	160.9	162.8
100°	181.6	181.6	181.6	181.6	183.5	187.2	191.0	194.7	198.5	201.1	203.7
102.5°	227.4	228.5	229.7	230.8	232.4	234.3	236.2	238.1	240.0	242.8	245.6
105°	297.2	298.6	300.1	301.5	303.1	304.8	306.6	308.3	310.0	311.8	313.5
107.5°	374.0	375.4	376.9	378.3	379.7	381.0	382.3	383.7	385.0	385.9	386.7
110°	426.9	428.4	429.8	431.2	432.4	433.3	434.1	435.0	435.8	436.7	437.6



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	480.2	480.9	481.7	482.4	483.4	484.4	485.5	486.6	487.7	488.1	488.5
115°	560.2	561.4	562.5	563.7	564.6	565.1	565.7	566.3	566.9	566.6	566.3
117.5°	639.5	640.0	640.5	641.1	641.6	642.1	642.6	643.1	643.7	643.9	644.1
120°	690.2	691.7	693.1	694.6	695.4	695.7	696.0	696.3	696.6	696.6	696.6
122.5°	743.3	743.8	744.3	744.8	745.5	746.2	747.0	747.7	748.5	748.2	748.0
125°	817.6	819.4	821.1	822.8	823.8	824.1	824.4	824.7	825.0	824.4	823.8
127.5°	894.7	895.7	896.7	897.7	898.3	898.7	899.0	899.4	899.7	899.4	899.1
130°	941.9	943.3	944.8	946.2	947.2	947.8	948.4	948.9	949.5	949.2	948.9
132.5°	989.5	991.9	994.2	996.6	997.7	997.6	997.5	997.4	997.3	997.0	996.7
135°	1062.8	1064.5	1066.3	1068.0	1069.0	1069.3	1069.6	1069.9	1070.2	1070.2	1070.2
137.5°	1132.3	1134.0	1135.6	1137.3	1138.4	1139.1	1139.7	1140.4	1141.0	1141.3	1141.7
140°	1176.7	1178.1	1179.6	1181.0	1182.1	1183.0	1183.9	1184.7	1185.6	1186.2	1186.8
142.5°	1221.1	1222.3	1223.5	1224.7	1225.8	1226.9	1228.0	1229.1	1230.2	1230.6	1230.9
145°	1286.6	1287.8	1288.9	1290.1	1291.1	1292.0	1292.8	1293.7	1294.6	1294.6	1294.6
147.5°	1346.8	1347.5	1348.1	1348.7	1349.4	1350.1	1350.8	1351.5	1352.2	1352.9	1353.5
150°	1386.4	1386.1	1385.8	1385.5	1385.9	1387.1	1388.3	1389.4	1390.6	1390.6	1390.6
152.5°	1420.3	1420.7	1421.1	1421.5	1421.9	1422.4	1422.8	1423.3	1423.8	1424.5	1425.1
155°	1471.0	1471.0	1471.0	1471.0	1471.1	1471.4	1471.7	1472.0	1472.3	1473.4	1474.6
157.5°	1516.0	1515.4	1514.7	1514.1	1513.9	1514.2	1514.5	1514.8	1515.1	1516.2	1517.4
160°	1542.8	1541.9	1541.0	1540.2	1539.9	1540.2	1540.5	1540.7	1541.0	1542.2	1543.3
162.5°	1566.9	1566.2	1565.6	1565.0	1564.7	1564.7	1564.8	1564.8	1564.9	1566.3	1567.7
165°	1598.8	1598.2	1597.7	1597.1	1597.0	1597.2	1597.5	1597.8	1598.1	1599.3	1600.4
167.5°	1625.2	1624.1	1622.9	1621.8	1621.2	1621.2	1621.2	1621.2	1621.2	1622.9	1624.7
170°	1639.8	1638.6	1637.5	1636.3	1635.7	1635.7	1635.7	1635.7	1635.7	1637.5	1639.2
172.5°	1650.1	1649.0	1647.8	1646.7	1646.1	1646.1	1646.1	1646.1	1646.1	1647.8	1649.6
175°	1661.8	1660.7	1659.5	1658.4	1657.8	1657.8	1657.8	1657.8	1657.8	1659.5	1661.2
177.5°	1668.0	1667.1	1666.2	1665.2	1664.7	1664.4	1664.2	1664.0	1663.7	1665.1	1666.5
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1320.1	1320.1	1327.2	1326.8	1331.4	1329.7	1330.5
5°	1419.1	1427.9	1435.7	1440.9	1448.7	1450.8	1449.7
7.5°	1521.7	1541.3	1550.9	1564.0	1566.4	1573.2	1572.5
10°	1585.3	1604.5	1619.0	1630.4	1636.2	1643.4	1643.9
12.5°	1635.1	1651.4	1664.3	1674.9	1681.8	1684.1	1685.5
15°	1674.1	1692.2	1707.3	1722.3	1731.2	1737.9	1741.6
17.5°	1713.3	1741.4	1767.9	1788.4	1800.7	1811.0	1810.9
20°	1743.6	1775.8	1809.1	1832.4	1856.3	1866.7	1868.3
22.5°	1776.0	1825.3	1868.1	1904.3	1935.7	1946.5	1950.5
25°	1843.3	1907.7	1973.7	2024.6	2060.9	2082.2	2085.3
27.5°	1924.6	2011.8	2081.2	2128.1	2158.3	2174.1	2177.5
30°	1982.0	2062.5	2124.8	2160.1	2174.1	2176.2	2168.4
32.5°	2007.7	2067.9	2092.8	2090.7	2063.2	2044.9	2037.9
35°	1976.3	1963.8	1903.0	1830.4	1774.8	1739.5	1730.1
37.5°	1798.5	1691.0	1579.2	1469.4	1410.9	1381.2	1330.1
40°	1623.2	1470.0	1353.7	1261.3	1195.3	1142.3	1129.9
42.5°	1425.4	1267.3	1151.0	1071.8	1019.2	982.8	967.0
45°	1145.5	1009.4	913.4	852.6	812.1	785.6	773.7
47.5°	916.2	810.9	740.9	695.9	665.1	642.0	635.6
50°	790.3	706.2	647.0	609.1	585.7	568.1	560.8
52.5°	686.4	618.5	573.0	541.8	519.7	508.7	502.6
55°	566.5	507.8	475.1	450.2	437.7	428.9	424.7
57.5°	463.3	420.9	397.0	379.8	368.3	362.6	360.6
60°	405.5	372.3	350.5	337.0	329.2	321.9	319.9
62.5°	354.4	328.3	311.4	299.6	291.8	288.7	287.5
65°	285.6	268.5	256.0	248.7	242.5	241.5	240.9
67.5°	227.0	216.9	210.4	202.8	200.6	197.0	196.3
70°	194.2	187.4	179.7	177.1	174.5	170.8	171.4
72.5°	164.7	158.0	152.7	149.2	148.3	146.7	148.1
75°	120.5	118.4	116.3	113.7	112.7	112.7	112.2
77.5°	86.0	84.2	81.9	80.4	80.1	77.9	78.7
80°	62.3	59.7	58.7	59.2	57.6	57.1	57.1
82.5°	46.1	45.2	44.1	44.2	43.9	43.4	43.8
85°	25.4	24.9	24.9	24.4	24.4	23.9	23.9
87.5°	14.2	14.9	14.3	14.0	14.2	14.8	15.4
90°	25.1	26.5	27.7	28.5	29.4	30.3	31.1
92.5°	55.5	57.4	58.7	59.3	60.0	60.6	61.2
95°	105.9	108.0	109.2	109.8	110.4	111.0	111.6
97.5°	164.7	166.6	167.8	168.1	168.5	168.8	169.2
100°	206.2	208.8	210.4	211.0	211.6	212.2	212.7
102.5°	248.4	251.3	253.1	253.9	254.7	255.5	256.3
105°	315.2	316.9	318.2	319.1	320.0	320.8	321.7
107.5°	387.6	388.5	388.9	388.8	388.7	388.7	388.6
110°	438.4	439.3	439.6	439.3	439.0	438.7	438.4



TEST NUMBER: P333693

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	488.9	489.3	489.3	488.8	488.3	487.7	487.2
115°	566.0	565.7	565.4	565.1	564.8	564.6	564.3
117.5°	644.3	644.6	644.1	643.0	641.8	640.7	639.5
120°	696.6	696.6	696.0	694.8	693.7	692.5	691.4
122.5°	747.8	747.5	747.0	746.0	745.1	744.2	743.3
125°	823.3	822.7	822.3	822.0	821.7	821.4	821.1
127.5°	898.8	898.6	898.1	897.6	897.0	896.4	895.8
130°	948.7	948.4	947.9	947.4	946.8	946.2	945.6
132.5°	996.4	996.1	995.6	994.8	993.9	993.1	992.3
135°	1070.2	1070.2	1069.6	1068.4	1067.3	1066.1	1065.0
137.5°	1142.0	1142.4	1141.8	1140.4	1138.9	1137.5	1136.1
140°	1187.3	1187.9	1187.5	1186.0	1184.6	1183.2	1181.7
142.5°	1231.3	1231.6	1231.1	1229.6	1228.2	1226.7	1225.3
145°	1294.6	1294.6	1294.1	1293.3	1292.4	1291.5	1290.7
147.5°	1354.2	1354.9	1354.3	1352.3	1350.4	1348.4	1346.5
150°	1390.6	1390.6	1390.3	1389.7	1389.1	1388.5	1388.0
152.5°	1425.8	1426.5	1426.4	1425.3	1424.3	1423.2	1422.2
155°	1475.7	1476.9	1476.7	1475.3	1473.9	1472.4	1471.0
157.5°	1518.5	1519.7	1519.3	1517.4	1515.5	1513.6	1511.7
160°	1544.5	1545.6	1545.5	1544.1	1542.6	1541.2	1539.7
162.5°	1569.0	1570.4	1570.3	1568.6	1566.9	1565.3	1563.6
165°	1601.6	1602.7	1602.4	1600.7	1599.0	1597.2	1595.5
167.5°	1626.4	1628.1	1628.1	1626.3	1624.5	1622.7	1620.9
170°	1640.9	1642.6	1642.5	1640.5	1638.5	1636.4	1634.4
172.5°	1651.3	1653.0	1653.0	1651.2	1649.4	1647.6	1645.8
175°	1663.0	1664.7	1664.5	1662.5	1660.5	1658.5	1656.5
177.5°	1667.9	1669.3	1669.2	1667.5	1665.9	1664.3	1662.7
180°	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9	1666.9

(END OF REPORT)