

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333482-830

Luminaire Tested: **S125DIW-S1270D1340U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333482-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1340U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9892.3 lumens
Efficiency: N/A
Efficacy: 129.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333482-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333482-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39	34
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33	29
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	29	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22
6	63	50	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19	17
8	54	41	34	28	49	38	32	27	33	28	24	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11996	11996	11996
5°	12023	11909	11985
10°	11950	11825	11893
15°	11820	11683	11732
20°	11635	11483	11504
25°	11436	11247	11236
30°	11189	10992	10937
35°	10925	10717	10566
40°	10655	10420	10270
45°	10361	10147	9945
50°	10040	9818	9523
55°	9730	9448	9183
60°	9357	9074	8751
65°	8915	8623	8332
70°	8492	8103	7825
75°	7738	7481	7224
80°	6884	6776	6616
85°	5995	6099	5772



TEST NUMBER: P333482-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.1	1.8
10°-20°	494.7	5.0
20°-30°	730.5	7.4
30°-40°	852.4	8.6
40°-50°	856.1	8.7
50°-60°	751.5	7.6
60°-70°	559.9	5.7
70°-80°	320.2	3.2
80°-90°	96.6	1.0
90°-100°	59.8	0.6
100°-110°	368.7	3.7
110°-120°	668.7	6.8
120°-130°	858.2	8.7
130°-140°	923.1	9.3
140°-150°	866.4	8.8
150°-160°	700.9	7.1
160°-170°	453.3	4.6
170°-180°	156.3	1.6
0°-30°	1400.3	14.2
0°-40°	2252.7	22.8
0°-60°	3860.3	39.0
0°-90°	4836.9	48.9
90°-120°	1097.2	11.1
90°-150°	3744.9	37.9
90°-180°	5055.0	51.1
0°-180°	9892.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1858	1858	1858	1858	1858	
5°	1854	1851	1837	1849	1849	176
15°	1768	1763	1747	1754	1755	498
25°	1605	1597	1578	1581	1577	738
35°	1386	1379	1359	1352	1340	866
45°	1134	1128	1111	1094	1089	874
55°	864	859	839	826	816	771
65°	583	580	564	551	545	579
75°	310	307	300	295	290	331
85°	81	82	82	81	78	90
90°	1	11	20	26	29	7
95°	70	64	20	25	26	89
105°	359	363	364	364	362	380
115°	674	680	681	676	669	668
125°	958	966	966	962	958	855
135°	1195	1202	1200	1197	1190	921
145°	1385	1387	1388	1388	1382	866
155°	1525	1519	1521	1523	1514	703
165°	1610	1603	1604	1610	1601	455
175°	1646	1639	1640	1649	1639	157
180°	1646	1646	1646	1646	1646	



TEST NUMBER: P333482-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1862.2	1861.4	1860.7	1859.8	1859.1	1857.4	1854.7	1852.1	1849.6	1846.9	1849.6
5°	1854.5	1853.9	1853.2	1852.6	1851.9	1850.0	1846.7	1843.4	1840.2	1836.9	1839.8
7.5°	1837.5	1836.8	1836.2	1835.5	1834.8	1832.8	1829.2	1825.6	1822.0	1818.4	1821.3
10°	1822.2	1821.6	1820.9	1820.2	1819.6	1817.5	1813.9	1810.3	1806.7	1803.1	1805.7
12.5°	1803.4	1802.2	1801.1	1799.9	1798.7	1796.5	1793.1	1789.8	1786.5	1783.1	1785.3
15°	1767.8	1766.9	1765.9	1764.9	1764.0	1761.6	1758.0	1754.4	1750.9	1747.3	1748.9
17.5°	1727.0	1725.6	1724.1	1722.7	1721.3	1718.6	1715.0	1711.2	1707.5	1703.7	1705.8
20°	1692.9	1692.2	1691.6	1690.9	1690.3	1687.8	1683.6	1679.3	1675.1	1670.8	1673.1
22.5°	1658.8	1657.6	1656.4	1655.3	1654.1	1651.5	1647.6	1643.6	1639.6	1635.6	1637.1
25°	1604.8	1603.1	1601.5	1599.9	1598.2	1595.3	1591.0	1586.8	1582.5	1578.3	1578.9
27.5°	1541.5	1540.6	1539.5	1538.6	1537.7	1534.9	1530.6	1526.2	1521.8	1517.4	1517.6
30°	1500.4	1499.4	1498.5	1497.4	1496.5	1493.6	1488.7	1483.8	1478.8	1473.9	1473.3
32.5°	1455.8	1454.2	1452.7	1451.2	1449.7	1446.8	1442.4	1438.0	1433.6	1429.3	1428.1
35°	1385.7	1384.5	1383.2	1381.9	1380.5	1377.6	1373.0	1368.5	1363.9	1359.3	1357.7
37.5°	1313.2	1311.5	1309.9	1308.2	1306.6	1303.6	1299.4	1295.1	1290.7	1286.5	1284.0
40°	1263.8	1262.2	1260.6	1258.9	1257.3	1254.1	1249.6	1245.0	1240.5	1235.9	1232.9
42.5°	1210.9	1209.6	1208.2	1206.7	1205.4	1202.4	1197.9	1193.3	1188.7	1184.1	1181.5
45°	1134.4	1133.2	1131.9	1130.6	1129.3	1126.6	1122.8	1118.8	1114.9	1111.0	1107.0
47.5°	1052.2	1052.3	1052.3	1052.3	1052.4	1050.1	1045.5	1040.8	1036.0	1031.3	1027.4
50°	999.3	998.3	997.3	996.4	995.3	992.9	989.0	985.1	981.2	977.2	973.0
52.5°	945.2	944.5	943.8	943.0	942.4	939.9	935.7	931.5	927.4	923.1	919.5
55°	864.1	863.1	862.1	861.1	860.2	857.4	852.8	848.3	843.7	839.1	836.1
57.5°	778.5	778.1	777.5	777.0	776.5	774.3	770.4	766.6	762.7	758.8	755.1
60°	724.4	723.2	721.9	720.6	719.3	716.8	713.2	709.6	706.1	702.5	699.2
62.5°	668.1	667.0	666.0	664.9	663.8	661.9	658.7	655.6	652.6	649.5	646.0
65°	583.4	582.8	582.1	581.5	580.8	578.6	575.0	571.5	567.9	564.3	561.4
67.5°	501.4	500.0	498.7	497.3	496.0	493.9	491.3	488.5	485.9	483.1	480.7
70°	449.7	448.1	446.4	444.8	443.2	440.8	437.9	435.0	432.1	429.1	427.2
72.5°	393.2	392.1	391.1	389.9	388.8	387.3	385.4	383.5	381.6	379.8	377.5
75°	310.1	309.4	308.8	308.1	307.5	306.3	304.7	303.0	301.4	299.8	298.8
77.5°	233.4	233.1	232.8	232.6	232.3	231.8	230.8	229.9	228.9	228.1	227.5
80°	185.1	185.1	185.1	185.1	185.1	184.8	184.2	183.5	182.9	182.2	181.9
82.5°	142.8	142.3	141.8	141.3	140.7	140.4	140.3	140.2	140.1	139.9	139.3
85°	80.9	81.2	81.4	81.8	82.1	82.3	82.3	82.3	82.3	82.3	82.0
87.5°	32.0	32.4	32.9	33.3	33.7	34.0	34.1	34.2	34.3	34.5	34.8
90°	1.2	3.4	5.6	7.7	9.9	12.0	13.9	15.7	17.6	19.5	20.9
92.5°	18.8	17.2	15.7	14.2	12.7	12.8	14.5	16.1	17.8	19.5	20.9
95°	69.6	68.7	68.0	67.1	66.3	60.7	50.4	40.2	29.8	19.5	20.9
97.5°	145.2	146.7	148.2	149.6	151.1	141.6	121.2	100.9	80.4	60.0	52.4
100°	203.8	204.6	205.4	206.2	207.1	208.0	209.1	210.2	211.2	212.4	171.9
102.5°	263.3	264.4	265.4	266.5	267.5	268.3	269.0	269.7	270.2	270.9	263.3
105°	358.8	359.9	361.0	362.0	363.2	363.6	363.6	363.6	363.6	363.6	363.6
107.5°	457.9	457.9	457.9	457.9	457.9	458.2	458.7	459.2	459.8	460.3	460.3
110°	522.4	522.4	522.4	522.4	522.4	522.5	523.1	523.7	524.2	524.7	524.0



TEST NUMBER: P333482-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	582.9	583.5	584.2	584.8	585.4	586.0	586.3	586.5	586.9	587.2	586.2
115°	673.6	675.0	676.4	677.7	679.1	679.9	680.1	680.4	680.7	681.0	679.9
117.5°	767.6	767.5	767.5	767.4	767.4	767.9	768.9	770.0	771.0	772.0	770.6
120°	826.1	826.0	825.7	825.4	825.1	825.4	826.1	827.0	827.8	828.6	828.1
122.5°	877.9	878.9	880.0	881.0	882.0	882.8	883.2	883.5	883.9	884.3	883.7
125°	958.0	959.9	961.8	963.7	965.5	966.5	966.5	966.5	966.5	966.5	965.4
127.5°	1034.3	1035.8	1037.1	1038.4	1039.8	1040.4	1040.2	1040.1	1039.9	1039.7	1039.2
130°	1081.2	1082.6	1083.9	1085.3	1086.7	1087.5	1087.8	1088.0	1088.3	1088.5	1087.8
132.5°	1128.1	1129.6	1131.2	1132.8	1134.3	1134.9	1134.3	1133.7	1133.1	1132.5	1132.4
135°	1194.8	1196.4	1198.0	1199.6	1201.3	1201.7	1201.3	1200.7	1200.1	1199.6	1199.1
137.5°	1256.0	1257.4	1258.8	1260.2	1261.6	1262.1	1261.6	1261.1	1260.7	1260.2	1260.3
140°	1296.0	1296.6	1297.1	1297.6	1298.2	1298.4	1298.1	1297.8	1297.5	1297.2	1297.8
142.5°	1332.1	1332.5	1332.8	1333.1	1333.4	1333.8	1334.2	1334.5	1334.9	1335.3	1335.4
145°	1385.1	1385.6	1386.2	1386.8	1387.2	1387.5	1387.5	1387.5	1387.5	1387.5	1387.8
147.5°	1431.4	1431.3	1431.3	1431.2	1431.1	1431.2	1431.4	1431.8	1432.1	1432.5	1432.8
150°	1460.8	1460.2	1459.7	1459.2	1458.6	1458.6	1459.2	1459.7	1460.2	1460.8	1461.3
152.5°	1489.0	1487.9	1486.7	1485.5	1484.3	1483.9	1484.5	1485.1	1485.6	1486.1	1486.7
155°	1525.4	1523.8	1522.2	1520.6	1518.9	1518.4	1518.9	1519.5	1520.0	1520.6	1521.4
157.5°	1553.5	1552.6	1551.5	1550.6	1549.6	1549.2	1549.2	1549.3	1549.4	1549.4	1550.2
160°	1573.0	1571.4	1569.8	1568.1	1566.5	1565.8	1566.1	1566.4	1566.7	1567.0	1568.0
162.5°	1588.7	1587.1	1585.4	1583.8	1582.2	1581.5	1581.8	1582.1	1582.2	1582.5	1584.0
165°	1609.7	1608.0	1606.4	1604.8	1603.2	1602.4	1602.7	1603.0	1603.3	1603.5	1605.1
167.5°	1625.2	1623.6	1621.9	1620.2	1618.5	1617.9	1618.1	1618.3	1618.6	1618.9	1620.9
170°	1634.1	1632.2	1630.2	1628.3	1626.5	1625.6	1625.9	1626.2	1626.5	1626.7	1628.9
172.5°	1639.9	1638.0	1636.2	1634.2	1632.3	1631.6	1632.1	1632.6	1633.0	1633.5	1635.5
175°	1646.2	1644.6	1643.0	1641.3	1639.7	1639.1	1639.4	1639.6	1639.9	1640.1	1642.3
177.5°	1649.2	1647.8	1646.6	1645.3	1644.0	1643.4	1643.7	1643.9	1644.1	1644.3	1645.9
180°	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2



TEST NUMBER: P333482-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1852.1	1854.7	1857.4	1858.5	1858.3	1858.0	1857.8	1857.5
5°	1842.8	1845.8	1848.7	1850.0	1849.6	1849.4	1849.0	1848.7
7.5°	1824.1	1827.0	1829.9	1831.2	1830.9	1830.5	1830.2	1829.9
10°	1808.4	1811.0	1813.5	1814.7	1814.4	1814.0	1813.7	1813.5
12.5°	1787.3	1789.4	1791.5	1792.5	1792.4	1792.3	1792.3	1792.2
15°	1750.6	1752.2	1753.8	1754.6	1754.6	1754.6	1754.6	1754.6
17.5°	1707.8	1709.9	1711.8	1712.0	1710.4	1708.8	1707.1	1705.5
20°	1675.5	1677.7	1680.0	1680.4	1678.7	1677.1	1675.5	1673.8
22.5°	1638.6	1640.1	1641.6	1641.8	1640.7	1639.6	1638.4	1637.4
25°	1579.6	1580.3	1580.9	1580.7	1579.8	1578.8	1577.8	1576.8
27.5°	1517.7	1517.9	1518.0	1517.5	1516.6	1515.6	1514.6	1513.6
30°	1472.6	1472.0	1471.3	1470.6	1469.5	1468.6	1467.5	1466.6
32.5°	1426.9	1425.8	1424.6	1423.1	1421.4	1419.6	1417.8	1416.1
35°	1356.0	1354.4	1352.8	1350.7	1348.0	1345.5	1342.8	1340.2
37.5°	1281.6	1279.2	1276.8	1274.8	1273.3	1271.8	1270.3	1268.8
40°	1230.0	1227.1	1224.1	1222.2	1221.2	1220.2	1219.2	1218.2
42.5°	1178.8	1176.1	1173.5	1171.4	1169.9	1168.4	1166.9	1165.4
45°	1103.2	1099.2	1095.3	1092.9	1091.8	1090.9	1089.9	1088.9
47.5°	1023.3	1019.4	1015.4	1012.3	1009.9	1007.7	1005.4	1003.1
50°	968.7	964.5	960.3	957.0	954.7	952.4	950.2	947.8
52.5°	915.7	912.0	908.2	905.1	902.6	900.0	897.5	894.9
55°	833.2	830.3	827.4	824.7	822.5	820.2	817.8	815.6
57.5°	751.3	747.5	743.8	741.2	740.0	738.8	737.4	736.2
60°	695.9	692.7	689.4	686.6	684.3	682.0	679.8	677.5
62.5°	642.4	638.9	635.5	632.8	631.0	629.2	627.5	625.8
65°	558.5	555.4	552.5	550.4	549.1	547.8	546.5	545.2
67.5°	478.2	475.7	473.3	471.6	470.8	470.0	469.3	468.4
70°	425.2	423.2	421.2	419.6	418.3	417.0	415.8	414.4
72.5°	375.3	373.1	370.9	369.1	367.8	366.5	365.1	363.8
75°	297.8	296.8	295.9	294.7	293.4	292.1	290.8	289.5
77.5°	226.9	226.3	225.7	225.0	224.0	223.1	222.3	221.3
80°	181.5	181.3	180.9	180.4	179.7	179.1	178.4	177.9
82.5°	138.7	138.2	137.5	137.2	137.0	137.0	136.8	136.7
85°	81.6	81.3	81.0	80.5	79.8	79.2	78.5	77.9
87.5°	35.0	35.3	35.5	35.5	35.2	34.8	34.4	34.0
90°	22.2	23.6	25.0	26.0	26.9	27.6	28.5	29.3
92.5°	22.2	23.6	25.0	25.8	26.2	26.6	27.0	27.3
95°	22.2	23.6	25.0	25.6	25.6	25.6	25.6	25.6
97.5°	44.8	37.1	29.4	25.6	25.6	25.6	25.6	25.6
100°	131.5	91.1	50.7	30.0	28.8	27.8	26.7	25.6
102.5°	255.6	248.0	240.3	227.2	208.9	190.4	171.9	153.5
105°	363.6	363.6	363.6	363.5	363.3	363.0	362.7	362.4
107.5°	460.4	460.5	460.5	460.1	459.3	458.5	457.7	456.9
110°	523.1	522.4	521.5	521.2	521.5	521.8	522.1	522.4



TEST NUMBER: P333482-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	585.1	584.2	583.2	582.4	582.0	581.6	581.3	580.9
115°	678.8	677.7	676.7	675.2	673.6	672.0	670.3	668.7
117.5°	769.2	767.8	766.4	765.3	764.6	763.9	763.2	762.5
120°	827.6	827.0	826.4	825.5	824.2	822.7	821.4	820.1
122.5°	883.2	882.6	882.1	881.0	879.5	877.9	876.3	874.8
125°	964.3	963.3	962.1	961.2	960.5	959.6	958.8	958.0
127.5°	1038.6	1037.9	1037.4	1036.0	1034.1	1032.1	1030.0	1028.0
130°	1086.9	1086.1	1085.3	1084.2	1082.9	1081.5	1080.2	1078.8
132.5°	1132.2	1132.0	1131.8	1131.1	1129.7	1128.4	1127.0	1125.7
135°	1198.5	1198.0	1197.4	1196.4	1194.8	1193.1	1191.5	1189.9
137.5°	1260.4	1260.5	1260.6	1259.9	1258.5	1257.1	1255.7	1254.2
140°	1298.4	1298.8	1299.4	1298.8	1297.2	1295.6	1294.0	1292.3
142.5°	1335.5	1335.7	1335.8	1335.0	1333.3	1331.7	1330.1	1328.5
145°	1388.1	1388.4	1388.6	1388.0	1386.3	1384.7	1383.1	1381.5
147.5°	1433.1	1433.4	1433.8	1432.9	1431.0	1429.0	1427.1	1425.1
150°	1461.9	1462.4	1462.9	1462.1	1459.9	1457.7	1455.6	1453.4
152.5°	1487.2	1487.8	1488.3	1487.6	1485.6	1483.8	1481.8	1479.8
155°	1522.2	1523.0	1523.8	1523.1	1521.0	1518.8	1516.6	1514.5
157.5°	1551.1	1552.0	1552.8	1552.2	1550.0	1547.8	1545.7	1543.5
160°	1569.1	1570.2	1571.3	1570.7	1568.6	1566.4	1564.2	1562.1
162.5°	1585.5	1587.1	1588.7	1588.2	1585.8	1583.4	1581.0	1578.7
165°	1606.8	1608.4	1610.1	1609.8	1607.6	1605.4	1603.3	1601.1
167.5°	1622.9	1624.8	1626.7	1626.5	1624.0	1621.6	1619.2	1616.7
170°	1631.1	1633.2	1635.4	1635.3	1632.9	1630.4	1628.0	1625.5
172.5°	1637.5	1639.5	1641.3	1641.2	1638.7	1636.3	1633.8	1631.4
175°	1644.5	1646.6	1648.8	1648.7	1646.2	1643.8	1641.3	1638.9
177.5°	1647.4	1648.9	1650.4	1650.3	1648.5	1646.8	1645.0	1643.3
180°	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2	1646.2

(END OF REPORT)