

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333694

Luminaire Tested: **S125RDIW-S850D1340U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333694
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D1340U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8615.7 lumens
Efficiency: N/A
Efficacy: 140.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333694

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333694

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38																				
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32																				
2	87	80	74	69	79	72	67	63	59	56	52	47	44	42	35	34	32	27																				
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23																				
4	73	62	54	49	66	57	50	45	46	42	38	37	34	31	28	26	24	20																				
5	67	55	47	42	60	51	44	39	42	36	33	33	30	27	25	23	21	17																				
6	61	50	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15																				
7	57	45	37	32	51	41	34	29	34	29	25	27	23	21	21	18	16	14																				
8	52	41	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12																				
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11																				
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8881	8881	8881
5°	8901	8800	8854
10°	8834	8718	8718
15°	8729	8541	8471
20°	8594	8294	8194
25°	8437	8052	7874
30°	8240	7768	7520
35°	8041	7476	7123
40°	7854	7171	6734
45°	7626	6830	6308
50°	7398	6459	5865
55°	7133	6104	5391
60°	6868	5674	4883
65°	6554	5174	4300
70°	6197	4549	3707
75°	5702	3835	3084
80°	5021	3013	2589
85°	4231	2460	2312



TEST NUMBER: P333694

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.3	1.5
10°-20°	361.3	4.2
20°-30°	524.0	6.1
30°-40°	597.2	6.9
40°-50°	582.1	6.8
50°-60°	490.0	5.7
60°-70°	343.5	4.0
70°-80°	176.6	2.0
80°-90°	48.2	0.6
90°-100°	63.5	0.7
100°-110°	391.2	4.5
110°-120°	709.5	8.2
120°-130°	910.5	10.6
130°-140°	979.3	11.4
140°-150°	919.2	10.7
150°-160°	743.6	8.6
160°-170°	480.9	5.6
170°-180°	165.9	1.9
0°-30°	1014.6	11.8
0°-40°	1611.8	18.7
0°-60°	2683.9	31.2
0°-90°	3252.1	37.7
90°-120°	1164.1	13.5
90°-150°	3973.2	46.1
90°-180°	5364.0	62.3
0°-180°	8615.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1373	1368	1357	1367	1366	130
15°	1306	1298	1277	1276	1267	368
25°	1184	1167	1130	1117	1105	545
35°	1020	994	948	919	904	638
45°	835	803	748	708	691	644
55°	634	599	542	497	479	566
65°	429	392	339	298	281	425
75°	228	197	154	132	124	242
85°	57	39	33	32	31	64
90°	1	12	21	27	31	6
95°	74	67	21	27	27	94
105°	381	386	386	386	384	404
115°	715	721	722	717	710	708
125°	1016	1025	1025	1020	1016	907
135°	1268	1275	1273	1270	1262	977
145°	1470	1472	1472	1473	1466	919
155°	1618	1611	1613	1616	1607	745
165°	1708	1700	1701	1708	1699	482
175°	1747	1739	1740	1749	1739	166
180°	1747	1747	1747	1747	1747	



TEST NUMBER: P333694

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1377.5	1377.0	1376.4	1375.9	1375.3	1374.1	1372.3	1370.4	1368.6	1366.7	1368.6
5°	1373.0	1372.1	1371.1	1370.2	1369.3	1367.6	1365.0	1362.5	1359.9	1357.4	1359.7
7.5°	1359.5	1358.6	1357.7	1356.8	1356.0	1354.0	1351.0	1347.9	1344.9	1341.8	1343.4
10°	1347.0	1346.3	1345.6	1344.9	1344.2	1342.3	1339.1	1335.8	1332.6	1329.4	1330.0
12.5°	1332.9	1332.0	1331.1	1330.3	1329.4	1326.8	1322.4	1318.1	1313.8	1309.4	1309.9
15°	1305.5	1304.1	1302.7	1301.3	1299.9	1296.8	1292.0	1287.1	1282.3	1277.4	1277.2
17.5°	1274.5	1272.4	1270.3	1268.2	1266.0	1261.9	1255.8	1249.7	1243.6	1237.5	1236.4
20°	1250.4	1248.1	1245.8	1243.5	1241.2	1236.3	1229.0	1221.6	1214.2	1206.8	1205.7
22.5°	1223.8	1221.5	1219.2	1216.9	1214.6	1209.6	1201.8	1194.1	1186.3	1178.6	1176.3
25°	1184.0	1180.5	1177.0	1173.6	1170.1	1164.1	1155.6	1147.0	1138.5	1130.0	1127.0
27.5°	1138.3	1134.1	1129.9	1125.7	1121.5	1114.8	1105.7	1096.5	1087.4	1078.2	1074.0
30°	1105.0	1100.6	1096.3	1091.9	1087.5	1080.4	1070.8	1061.1	1051.4	1041.7	1036.4
32.5°	1072.6	1067.5	1062.4	1057.3	1052.1	1044.6	1034.8	1024.9	1015.0	1005.1	999.3
35°	1019.9	1014.3	1008.8	1003.2	997.7	989.7	979.4	969.0	958.6	948.2	941.5
37.5°	968.1	961.4	954.7	947.9	941.2	932.5	921.8	911.0	900.3	889.6	881.6
40°	931.6	924.7	917.7	910.8	903.9	894.9	883.8	872.7	861.7	850.6	841.8
42.5°	893.4	886.3	879.2	872.0	864.9	855.7	844.2	832.8	821.3	809.9	801.5
45°	835.0	828.3	821.6	814.9	808.2	798.5	785.8	773.2	760.5	747.8	738.5
47.5°	774.6	767.5	760.4	753.4	746.3	736.4	723.6	710.8	698.0	685.2	675.7
50°	736.3	728.7	721.1	713.5	705.9	695.5	682.3	669.2	656.0	642.9	633.2
52.5°	694.8	687.0	679.2	671.4	663.6	653.5	641.1	628.7	616.2	603.8	593.4
55°	633.5	626.1	618.8	611.4	604.0	593.8	580.9	568.0	555.1	542.1	531.7
57.5°	571.6	563.7	555.8	547.9	540.1	529.9	517.4	504.9	492.5	480.0	469.9
60°	531.7	523.7	515.6	507.5	499.4	489.2	476.7	464.2	451.8	439.3	429.2
62.5°	489.4	481.7	474.0	466.2	458.5	448.4	435.7	423.1	410.4	397.8	388.4
65°	428.9	421.1	413.2	405.4	397.5	387.5	375.3	363.0	350.8	338.6	329.3
67.5°	368.9	361.0	353.2	345.4	337.5	327.7	316.0	304.3	292.6	280.8	272.4
70°	328.2	320.3	312.5	304.6	296.8	287.1	275.6	264.0	252.5	240.9	233.8
72.5°	288.3	280.6	273.0	265.3	257.7	248.4	237.6	226.8	216.0	205.2	198.6
75°	228.5	221.6	214.6	207.7	200.8	192.5	182.8	173.1	163.4	153.7	148.6
77.5°	169.1	163.5	158.0	152.5	146.9	140.3	132.5	124.8	117.0	109.3	105.7
80°	135.0	129.5	123.9	118.4	112.9	106.9	100.4	93.9	87.5	81.0	78.9
82.5°	101.8	96.8	91.8	86.8	81.8	77.1	72.7	68.3	63.8	59.4	58.4
85°	57.1	53.0	48.8	44.7	40.5	37.8	36.7	35.5	34.4	33.2	33.0
87.5°	19.4	18.5	17.7	16.9	16.0	15.7	16.0	16.2	16.4	16.6	16.9
90°	1.3	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.7	22.2
92.5°	19.9	18.3	16.7	15.1	13.5	13.6	15.4	17.1	18.9	20.7	22.2
95°	73.8	72.9	72.1	71.2	70.3	64.4	53.5	42.6	31.6	20.7	22.2
97.5°	154.1	155.6	157.2	158.7	160.3	150.2	128.6	107.0	85.3	63.7	55.6
100°	216.2	217.1	217.9	218.8	219.7	220.7	221.8	223.0	224.1	225.3	182.4
102.5°	279.4	280.5	281.6	282.7	283.8	284.7	285.4	286.1	286.7	287.4	279.3
105°	380.7	381.8	383.0	384.1	385.3	385.8	385.8	385.8	385.8	385.8	385.8
107.5°	485.8	485.8	485.8	485.8	485.8	486.1	486.7	487.2	487.8	488.4	488.4
110°	554.2	554.2	554.2	554.2	554.2	554.4	555.0	555.6	556.2	556.7	555.9



TEST NUMBER: P333694

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	618.4	619.1	619.8	620.4	621.1	621.7	622.0	622.3	622.7	623.0	621.9
115°	714.7	716.1	717.6	719.0	720.5	721.3	721.6	721.9	722.2	722.5	721.3
117.5°	814.4	814.3	814.3	814.2	814.2	814.7	815.8	816.9	818.0	819.1	817.6
120°	876.5	876.3	876.0	875.7	875.4	875.7	876.5	877.4	878.3	879.1	878.6
122.5°	931.4	932.5	933.6	934.7	935.8	936.6	937.0	937.4	937.8	938.2	937.6
125°	1016.4	1018.4	1020.4	1022.4	1024.4	1025.4	1025.4	1025.4	1025.4	1025.4	1024.3
127.5°	1097.4	1098.9	1100.3	1101.7	1103.2	1103.8	1103.6	1103.5	1103.3	1103.1	1102.5
130°	1147.1	1148.6	1150.0	1151.5	1152.9	1153.8	1154.1	1154.3	1154.6	1154.9	1154.1
132.5°	1196.9	1198.5	1200.2	1201.9	1203.5	1204.1	1203.4	1202.8	1202.2	1201.5	1201.4
135°	1267.6	1269.3	1271.0	1272.7	1274.5	1275.0	1274.5	1273.9	1273.3	1272.7	1272.2
137.5°	1332.6	1334.0	1335.5	1337.0	1338.5	1339.0	1338.5	1338.0	1337.5	1337.0	1337.1
140°	1375.0	1375.6	1376.2	1376.7	1377.3	1377.5	1377.2	1376.9	1376.6	1376.3	1376.9
142.5°	1413.3	1413.7	1414.0	1414.4	1414.7	1415.1	1415.5	1415.9	1416.3	1416.7	1416.8
145°	1469.5	1470.1	1470.7	1471.3	1471.8	1472.1	1472.1	1472.1	1472.1	1472.1	1472.4
147.5°	1518.7	1518.6	1518.5	1518.4	1518.3	1518.4	1518.7	1519.1	1519.4	1519.8	1520.1
150°	1549.8	1549.2	1548.7	1548.1	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8	1550.4
152.5°	1579.8	1578.6	1577.3	1576.1	1574.8	1574.4	1575.0	1575.6	1576.2	1576.7	1577.3
155°	1618.4	1616.7	1615.0	1613.3	1611.5	1611.0	1611.5	1612.1	1612.7	1613.3	1614.1
157.5°	1648.2	1647.2	1646.1	1645.1	1644.1	1643.6	1643.6	1643.7	1643.8	1643.8	1644.7
160°	1668.9	1667.2	1665.5	1663.7	1662.0	1661.3	1661.6	1661.9	1662.2	1662.5	1663.6
162.5°	1685.5	1683.8	1682.0	1680.3	1678.6	1677.9	1678.2	1678.5	1678.7	1679.0	1680.6
165°	1707.8	1706.0	1704.3	1702.6	1700.9	1700.1	1700.4	1700.7	1701.0	1701.3	1703.0
167.5°	1724.3	1722.6	1720.8	1719.0	1717.2	1716.5	1716.7	1717.0	1717.3	1717.6	1719.7
170°	1733.7	1731.7	1729.6	1727.6	1725.6	1724.7	1725.0	1725.3	1725.6	1725.9	1728.2
172.5°	1739.9	1737.9	1735.9	1733.8	1731.8	1731.1	1731.6	1732.1	1732.6	1733.1	1735.2
175°	1746.6	1744.9	1743.2	1741.4	1739.7	1739.0	1739.3	1739.6	1739.9	1740.1	1742.4
177.5°	1749.7	1748.3	1747.0	1745.6	1744.2	1743.6	1743.9	1744.1	1744.3	1744.5	1746.2
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333694

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1370.4	1372.3	1374.1	1375.0	1374.8	1374.6	1374.4	1374.2
5°	1362.0	1364.3	1366.6	1367.6	1367.1	1366.6	1366.2	1365.7
7.5°	1345.1	1346.7	1348.3	1348.8	1348.3	1347.8	1347.3	1346.8
10°	1330.7	1331.4	1332.1	1332.1	1331.4	1330.7	1330.0	1329.4
12.5°	1310.4	1310.9	1311.4	1311.2	1310.1	1309.0	1308.0	1306.9
15°	1277.0	1276.7	1276.5	1275.4	1273.3	1271.2	1269.1	1267.0
17.5°	1235.2	1234.1	1232.9	1231.5	1229.8	1228.1	1226.4	1224.7
20°	1204.5	1203.3	1202.2	1200.6	1198.5	1196.4	1194.3	1192.3
22.5°	1174.0	1171.8	1169.5	1167.5	1165.8	1164.1	1162.4	1160.7
25°	1124.0	1121.0	1118.0	1115.2	1112.6	1110.1	1107.6	1105.0
27.5°	1069.8	1065.6	1061.4	1058.1	1055.7	1053.2	1050.8	1048.3
30°	1031.1	1025.8	1020.4	1016.8	1014.7	1012.6	1010.5	1008.4
32.5°	993.4	987.5	981.7	977.4	974.8	972.2	969.5	966.9
35°	934.8	928.1	921.4	916.5	913.2	910.0	906.8	903.5
37.5°	873.6	865.5	857.5	851.9	848.8	845.6	842.5	839.4
40°	833.0	824.3	815.5	809.7	807.0	804.2	801.4	798.7
42.5°	793.1	784.7	776.3	770.0	766.0	761.9	757.8	753.8
45°	729.3	720.1	710.8	704.5	701.0	697.6	694.1	690.6
47.5°	666.2	656.7	647.2	640.5	636.7	632.9	629.0	625.2
50°	623.5	613.8	604.1	597.5	594.1	590.6	587.1	583.7
52.5°	583.0	572.5	562.1	555.1	551.7	548.2	544.8	541.3
55°	521.4	511.0	500.6	493.5	489.9	486.2	482.5	478.8
57.5°	459.7	449.6	439.4	432.7	429.4	426.1	422.9	419.6
60°	419.0	408.8	398.7	391.9	388.4	385.0	381.5	378.0
62.5°	378.9	369.5	360.1	353.7	350.2	346.7	343.3	339.8
65°	320.1	310.9	301.6	295.3	291.8	288.4	284.9	281.4
67.5°	263.9	255.5	247.0	241.4	238.7	235.9	233.1	230.4
70°	226.6	219.5	212.3	207.4	204.6	201.8	199.1	196.3
72.5°	192.0	185.4	178.8	174.6	172.7	170.9	169.1	167.2
75°	143.6	138.5	133.4	130.1	128.4	126.8	125.2	123.6
77.5°	102.1	98.6	95.0	92.7	91.5	90.3	89.1	87.9
80°	76.9	74.8	72.7	71.4	71.0	70.5	70.0	69.6
82.5°	57.5	56.5	55.5	54.9	54.6	54.4	54.1	53.8
85°	32.8	32.5	32.3	32.1	31.8	31.6	31.4	31.2
87.5°	17.2	17.5	17.8	17.9	17.9	17.9	17.9	17.8
90°	23.6	25.0	26.5	27.6	28.5	29.3	30.2	31.1
92.5°	23.6	25.0	26.5	27.4	27.8	28.2	28.6	29.0
95°	23.6	25.0	26.5	27.2	27.2	27.2	27.2	27.2
97.5°	47.5	39.4	31.2	27.2	27.2	27.2	27.2	27.2
100°	139.5	96.7	53.8	31.8	30.6	29.5	28.3	27.2
102.5°	271.2	263.1	255.0	241.1	221.6	202.0	182.4	162.9
105°	385.8	385.8	385.8	385.7	385.4	385.1	384.8	384.5
107.5°	488.5	488.6	488.6	488.2	487.3	486.5	485.6	484.8
110°	555.0	554.2	553.3	553.0	553.3	553.6	553.9	554.2



TEST NUMBER: P333694

CATALOG NUMBER: S125RDIW-S850D1340U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	620.8	619.8	618.7	617.9	617.5	617.1	616.7	616.3
115°	720.2	719.0	717.9	716.4	714.7	713.0	711.2	709.5
117.5°	816.1	814.6	813.1	811.9	811.2	810.5	809.7	809.0
120°	878.0	877.4	876.8	875.8	874.4	872.9	871.5	870.1
122.5°	937.0	936.4	935.9	934.7	933.1	931.4	929.7	928.1
125°	1023.1	1022.0	1020.8	1019.8	1019.0	1018.1	1017.2	1016.4
127.5°	1101.9	1101.2	1100.6	1099.2	1097.1	1095.0	1092.8	1090.7
130°	1153.2	1152.3	1151.5	1150.3	1148.9	1147.4	1146.0	1144.6
132.5°	1201.2	1201.0	1200.8	1200.0	1198.6	1197.2	1195.7	1194.3
135°	1271.6	1271.0	1270.4	1269.3	1267.6	1265.8	1264.1	1262.4
137.5°	1337.2	1337.3	1337.4	1336.7	1335.2	1333.7	1332.2	1330.7
140°	1377.5	1378.0	1378.6	1378.0	1376.3	1374.6	1372.9	1371.1
142.5°	1416.9	1417.1	1417.2	1416.4	1414.6	1412.9	1411.2	1409.5
145°	1472.7	1473.0	1473.3	1472.6	1470.8	1469.1	1467.4	1465.7
147.5°	1520.5	1520.8	1521.2	1520.3	1518.2	1516.1	1514.1	1512.0
150°	1551.0	1551.5	1552.1	1551.2	1548.9	1546.6	1544.3	1542.0
152.5°	1577.9	1578.5	1579.0	1578.3	1576.2	1574.2	1572.1	1570.0
155°	1615.0	1615.8	1616.7	1616.0	1613.7	1611.4	1609.1	1606.8
157.5°	1645.7	1646.6	1647.5	1646.8	1644.5	1642.2	1639.9	1637.6
160°	1664.8	1665.9	1667.1	1666.5	1664.2	1661.9	1659.6	1657.3
162.5°	1682.2	1683.9	1685.5	1685.0	1682.5	1679.9	1677.4	1674.9
165°	1704.7	1706.5	1708.2	1707.9	1705.6	1703.3	1701.0	1698.7
167.5°	1721.8	1723.8	1725.9	1725.6	1723.0	1720.5	1717.9	1715.3
170°	1730.5	1732.8	1735.1	1735.0	1732.4	1729.8	1727.2	1724.6
172.5°	1737.3	1739.4	1741.4	1741.2	1738.6	1736.0	1733.4	1730.8
175°	1744.7	1747.0	1749.3	1749.2	1746.6	1744.0	1741.4	1738.8
177.5°	1747.8	1749.4	1751.0	1750.9	1749.0	1747.2	1745.3	1743.5
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6

(END OF REPORT)