

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333483-830

Luminaire Tested: **S125DIW-S1270D1340U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333483-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D1340U830-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9220.9 lumens  
Efficiency: N/A  
Efficacy: 121.0 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333483-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333483-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	51	50	49	44
2	89	82	76	71	83	76	71	66	65	61	57	55	52	49	45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	37	35	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	36	36	33	30	27
5	68	57	49	43	63	53	46	40	46	40	35	39	34	31	32	29	26	23
6	63	51	43	37	58	48	40	35	41	35	31	35	30	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	18	16
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11996	11996	11996
5°	12023	11909	11985
10°	11950	11825	11893
15°	11820	11683	11732
20°	11635	11483	11504
25°	11436	11247	11236
30°	11189	10992	10937
35°	10925	10717	10566
40°	10655	10420	10270
45°	10361	10147	9945
50°	10040	9818	9523
55°	9730	9448	9183
60°	9357	9074	8751
65°	8915	8623	8332
70°	8492	8103	7825
75°	7738	7481	7224
80°	6884	6776	6616
85°	5995	6099	5772



TEST NUMBER: P333483-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	175.1	1.9
10°-20°	494.7	5.4
20°-30°	730.5	7.9
30°-40°	852.4	9.2
40°-50°	856.1	9.3
50°-60°	751.5	8.1
60°-70°	559.9	6.1
70°-80°	320.2	3.5
80°-90°	96.6	1.0
90°-100°	105.2	1.1
100°-110°	310.7	3.4
110°-120°	526.3	5.7
120°-130°	692.7	7.5
130°-140°	776.1	8.4
140°-150°	760.7	8.2
150°-160°	638.9	6.9
160°-170°	424.7	4.6
170°-180°	148.6	1.6
0°-30°	1400.3	15.2
0°-40°	2252.7	24.4
0°-60°	3860.3	41.9
0°-90°	4837.0	52.5
90°-120°	942.3	10.2
90°-150°	3171.8	34.4
90°-180°	4384.0	47.5
0°-180°	9220.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1858	1858	1858	1858	1858	
5°	1854	1851	1837	1849	1849	176
15°	1768	1763	1747	1754	1755	498
25°	1605	1597	1578	1581	1577	738
35°	1386	1379	1359	1352	1340	866
45°	1134	1128	1111	1094	1089	874
55°	864	859	839	826	816	771
65°	583	580	564	551	545	579
75°	310	307	300	295	290	331
85°	81	82	82	81	78	90
90°	1	11	20	26	29	9
95°	80	82	94	102	105	85
105°	279	285	292	299	303	298
115°	527	532	534	533	532	521
125°	769	776	778	775	774	688
135°	1000	1007	1009	1008	1004	771
145°	1212	1216	1220	1220	1216	757
155°	1386	1387	1388	1392	1386	638
165°	1508	1505	1506	1510	1504	425
175°	1567	1563	1562	1569	1561	149
180°	1571	1571	1571	1571	1571	



TEST NUMBER: P333483-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1862.2	1861.4	1860.7	1859.8	1859.1	1857.4	1854.7	1852.1	1849.6	1846.9	1849.6
5°	1854.5	1853.9	1853.2	1852.6	1851.9	1850.0	1846.7	1843.4	1840.2	1836.9	1839.8
7.5°	1837.5	1836.8	1836.2	1835.5	1834.8	1832.8	1829.2	1825.6	1822.0	1818.4	1821.3
10°	1822.2	1821.6	1820.9	1820.2	1819.6	1817.5	1813.9	1810.3	1806.7	1803.1	1805.7
12.5°	1803.4	1802.2	1801.1	1799.9	1798.7	1796.5	1793.1	1789.8	1786.5	1783.1	1785.3
15°	1767.8	1766.9	1765.9	1764.9	1764.0	1761.6	1758.0	1754.4	1750.9	1747.3	1748.9
17.5°	1727.0	1725.6	1724.1	1722.7	1721.3	1718.6	1715.0	1711.2	1707.5	1703.7	1705.8
20°	1692.9	1692.2	1691.6	1690.9	1690.3	1687.8	1683.6	1679.3	1675.1	1670.8	1673.1
22.5°	1658.8	1657.6	1656.4	1655.3	1654.1	1651.5	1647.6	1643.6	1639.6	1635.6	1637.1
25°	1604.8	1603.1	1601.5	1599.9	1598.2	1595.3	1591.0	1586.8	1582.5	1578.3	1578.9
27.5°	1541.5	1540.6	1539.5	1538.6	1537.7	1534.9	1530.6	1526.2	1521.8	1517.4	1517.6
30°	1500.4	1499.4	1498.5	1497.4	1496.5	1493.6	1488.7	1483.8	1478.8	1473.9	1473.3
32.5°	1455.8	1454.2	1452.7	1451.2	1449.7	1446.8	1442.4	1438.0	1433.6	1429.3	1428.1
35°	1385.7	1384.5	1383.2	1381.9	1380.5	1377.6	1373.0	1368.5	1363.9	1359.3	1357.7
37.5°	1313.2	1311.5	1309.9	1308.2	1306.6	1303.6	1299.4	1295.1	1290.7	1286.5	1284.0
40°	1263.8	1262.2	1260.6	1258.9	1257.3	1254.1	1249.6	1245.0	1240.5	1235.9	1232.9
42.5°	1210.9	1209.6	1208.2	1206.7	1205.4	1202.4	1197.9	1193.3	1188.7	1184.1	1181.5
45°	1134.4	1133.2	1131.9	1130.6	1129.3	1126.6	1122.8	1118.8	1114.9	1111.0	1107.0
47.5°	1052.2	1052.3	1052.3	1052.3	1052.4	1050.1	1045.5	1040.8	1036.0	1031.3	1027.4
50°	999.3	998.3	997.3	996.4	995.3	992.9	989.0	985.1	981.2	977.2	973.0
52.5°	945.2	944.5	943.8	943.0	942.4	939.9	935.7	931.5	927.4	923.1	919.5
55°	864.1	863.1	862.1	861.1	860.2	857.4	852.8	848.3	843.7	839.1	836.1
57.5°	778.5	778.1	777.5	777.0	776.5	774.3	770.4	766.6	762.7	758.8	755.1
60°	724.4	723.2	721.9	720.6	719.3	716.8	713.2	709.6	706.1	702.5	699.2
62.5°	668.1	667.0	666.0	664.9	663.8	661.9	658.7	655.6	652.6	649.5	646.0
65°	583.4	582.8	582.1	581.5	580.8	578.6	575.0	571.5	567.9	564.3	561.4
67.5°	501.4	500.0	498.7	497.3	496.0	493.9	491.3	488.5	485.9	483.1	480.7
70°	449.7	448.1	446.4	444.8	443.2	440.8	437.9	435.0	432.1	429.1	427.2
72.5°	393.2	392.1	391.1	389.9	388.8	387.3	385.4	383.5	381.6	379.8	377.5
75°	310.1	309.4	308.8	308.1	307.5	306.3	304.7	303.0	301.4	299.8	298.8
77.5°	233.4	233.1	232.8	232.6	232.3	231.8	230.8	229.9	228.9	228.1	227.5
80°	185.1	185.1	185.1	185.1	185.1	184.8	184.2	183.5	182.9	182.2	181.9
82.5°	142.8	142.3	141.8	141.3	140.7	140.4	140.3	140.2	140.1	139.9	139.3
85°	80.9	81.2	81.4	81.8	82.1	82.3	82.3	82.3	82.3	82.3	82.0
87.5°	32.0	32.4	32.9	33.3	33.7	34.0	34.1	34.2	34.4	34.5	34.8
90°	1.2	3.4	5.6	7.7	9.9	12.0	13.9	15.7	17.6	19.6	20.9
92.5°	29.6	31.1	32.6	34.1	35.6	37.6	40.0	42.3	44.6	46.9	48.7
95°	79.5	80.0	80.6	81.1	81.6	83.3	86.0	88.7	91.4	94.2	96.0
97.5°	132.1	132.2	132.5	132.7	132.9	134.9	138.6	142.4	146.2	149.9	151.7
100°	171.2	171.2	171.2	171.2	171.2	173.0	176.4	180.0	183.5	187.1	189.5
102.5°	213.2	214.3	215.4	216.5	217.5	219.0	220.8	222.6	224.4	226.2	228.8
105°	278.8	280.1	281.4	282.9	284.2	285.7	287.3	289.0	290.6	292.2	293.9
107.5°	351.1	352.5	353.8	355.2	356.6	357.9	359.1	360.3	361.7	362.9	363.7
110°	401.1	402.4	403.8	405.1	406.4	407.6	408.4	409.2	410.0	410.8	411.6



TEST NUMBER: P333483-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	451.9	452.6	453.3	454.0	454.7	455.6	456.6	457.6	458.6	459.7	460.1
115°	527.0	528.0	529.1	530.2	531.3	532.2	532.6	533.2	533.8	534.3	534.0
117.5°	602.3	602.8	603.2	603.7	604.3	604.7	605.2	605.7	606.1	606.7	606.9
120°	649.2	650.5	652.0	653.3	654.7	655.4	655.7	656.0	656.3	656.6	656.6
122.5°	700.1	700.6	701.1	701.5	702.0	702.7	703.3	704.1	704.7	705.5	705.2
125°	769.0	770.6	772.3	773.9	775.5	776.5	776.7	777.0	777.3	777.6	777.0
127.5°	842.4	843.3	844.2	845.2	846.1	846.7	847.1	847.3	847.7	848.0	847.7
130°	886.4	887.8	889.1	890.5	891.8	892.8	893.3	893.9	894.4	894.9	894.7
132.5°	930.4	932.6	934.9	937.1	939.3	940.4	940.3	940.2	940.1	940.0	939.7
135°	1000.1	1001.7	1003.3	1005.0	1006.6	1007.6	1007.9	1008.1	1008.4	1008.7	1008.7
137.5°	1065.6	1067.2	1068.8	1070.4	1072.0	1073.0	1073.7	1074.2	1074.9	1075.4	1075.7
140°	1107.7	1109.1	1110.4	1111.8	1113.1	1114.2	1115.0	1115.9	1116.6	1117.5	1118.0
142.5°	1149.8	1150.9	1152.1	1153.2	1154.3	1155.4	1156.4	1157.4	1158.5	1159.5	1159.9
145°	1211.6	1212.7	1213.8	1214.8	1216.0	1216.9	1217.8	1218.5	1219.4	1220.2	1220.2
147.5°	1268.9	1269.4	1270.1	1270.6	1271.2	1271.9	1272.5	1273.2	1273.8	1274.5	1275.2
150°	1307.0	1306.7	1306.5	1306.2	1305.9	1306.3	1307.4	1308.5	1309.6	1310.7	1310.7
152.5°	1338.3	1338.7	1339.1	1339.4	1339.8	1340.2	1340.7	1341.0	1341.5	1342.0	1342.7
155°	1386.5	1386.5	1386.5	1386.5	1386.5	1386.6	1386.9	1387.1	1387.4	1387.7	1388.7
157.5°	1429.5	1428.9	1428.3	1427.7	1427.1	1426.9	1427.2	1427.5	1427.8	1428.0	1429.1
160°	1454.9	1454.2	1453.3	1452.5	1451.7	1451.4	1451.7	1452.0	1452.2	1452.5	1453.6
162.5°	1477.4	1476.9	1476.2	1475.6	1475.1	1474.8	1474.8	1474.9	1474.9	1475.0	1476.3
165°	1507.5	1506.9	1506.4	1505.9	1505.3	1505.2	1505.4	1505.7	1506.0	1506.3	1507.4
167.5°	1533.0	1531.8	1530.8	1529.7	1528.6	1528.0	1528.0	1528.0	1528.0	1528.0	1529.7
170°	1546.6	1545.6	1544.5	1543.4	1542.3	1541.7	1541.7	1541.7	1541.7	1541.7	1543.4
172.5°	1556.4	1555.3	1554.3	1553.1	1552.1	1551.5	1551.5	1551.5	1551.5	1551.5	1553.1
175°	1567.4	1566.3	1565.3	1564.1	1563.1	1562.5	1562.5	1562.5	1562.5	1562.5	1564.1
177.5°	1573.0	1572.2	1571.3	1570.5	1569.5	1569.1	1568.8	1568.6	1568.4	1568.1	1569.4
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333483-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5	1857.5
2.5°	1852.1	1854.7	1857.4	1858.5	1858.3	1858.0	1857.8	1857.5
5°	1842.8	1845.8	1848.7	1850.0	1849.6	1849.4	1849.0	1848.7
7.5°	1824.1	1827.0	1829.9	1831.2	1830.9	1830.5	1830.2	1829.9
10°	1808.4	1811.0	1813.5	1814.7	1814.4	1814.0	1813.7	1813.5
12.5°	1787.3	1789.4	1791.5	1792.5	1792.4	1792.3	1792.3	1792.2
15°	1750.6	1752.2	1753.8	1754.6	1754.6	1754.6	1754.6	1754.6
17.5°	1707.8	1709.9	1711.8	1712.0	1710.4	1708.8	1707.1	1705.5
20°	1675.5	1677.7	1680.0	1680.4	1678.7	1677.1	1675.5	1673.8
22.5°	1638.6	1640.1	1641.6	1641.8	1640.7	1639.6	1638.4	1637.4
25°	1579.6	1580.3	1580.9	1580.7	1579.8	1578.8	1577.8	1576.8
27.5°	1517.7	1517.9	1518.0	1517.5	1516.6	1515.6	1514.6	1513.6
30°	1472.6	1472.0	1471.3	1470.6	1469.5	1468.6	1467.5	1466.6
32.5°	1426.9	1425.8	1424.6	1423.1	1421.4	1419.6	1417.8	1416.1
35°	1356.0	1354.4	1352.8	1350.7	1348.0	1345.5	1342.8	1340.2
37.5°	1281.6	1279.2	1276.8	1274.8	1273.3	1271.8	1270.3	1268.8
40°	1230.0	1227.1	1224.1	1222.2	1221.2	1220.2	1219.2	1218.2
42.5°	1178.8	1176.1	1173.5	1171.4	1169.9	1168.4	1166.9	1165.4
45°	1103.2	1099.2	1095.3	1092.9	1091.8	1090.9	1089.9	1088.9
47.5°	1023.3	1019.4	1015.4	1012.3	1009.9	1007.7	1005.4	1003.1
50°	968.7	964.5	960.3	957.0	954.7	952.4	950.2	947.8
52.5°	915.7	912.0	908.2	905.1	902.6	900.0	897.5	894.9
55°	833.2	830.3	827.4	824.7	822.5	820.2	817.8	815.6
57.5°	751.3	747.5	743.8	741.2	740.0	738.8	737.4	736.2
60°	695.9	692.7	689.4	686.6	684.3	682.0	679.8	677.5
62.5°	642.4	638.9	635.5	632.8	631.0	629.2	627.5	625.8
65°	558.5	555.4	552.5	550.4	549.1	547.8	546.5	545.2
67.5°	478.2	475.7	473.3	471.6	470.8	470.0	469.3	468.4
70°	425.2	423.2	421.2	419.6	418.3	417.0	415.8	414.4
72.5°	375.3	373.1	370.9	369.1	367.8	366.5	365.1	363.8
75°	297.8	296.8	295.9	294.7	293.4	292.1	290.8	289.5
77.5°	226.9	226.3	225.7	225.0	224.0	223.1	222.3	221.3
80°	181.5	181.3	180.9	180.4	179.7	179.1	178.4	177.9
82.5°	138.7	138.2	137.5	137.2	137.0	137.0	136.8	136.7
85°	81.6	81.3	81.0	80.5	79.8	79.2	78.5	77.9
87.5°	35.1	35.3	35.5	35.5	35.2	34.8	34.4	34.1
90°	22.2	23.7	25.0	26.1	26.9	27.7	28.6	29.3
92.5°	50.5	52.3	54.1	55.3	55.9	56.6	57.1	57.7
95°	97.9	99.8	101.8	102.9	103.5	104.1	104.6	105.2
97.5°	153.4	155.2	157.0	158.2	158.4	158.8	159.1	159.5
100°	192.0	194.4	196.8	198.3	198.9	199.4	200.0	200.5
102.5°	231.5	234.1	236.9	238.6	239.3	240.1	240.8	241.6
105°	295.5	297.1	298.7	299.9	300.8	301.6	302.4	303.2
107.5°	364.5	365.3	366.2	366.6	366.5	366.4	366.4	366.3
110°	412.5	413.2	414.1	414.3	414.1	413.8	413.5	413.2





TEST NUMBER: P333483-830

CATALOG NUMBER: S125DIW-S1270D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	460.4	460.8	461.2	461.2	460.7	460.2	459.7	459.2
115°	533.8	533.5	533.2	532.9	532.6	532.3	532.2	531.9
117.5°	607.1	607.3	607.6	607.1	606.1	604.9	603.9	602.8
120°	656.6	656.6	656.6	656.0	654.9	653.8	652.7	651.7
122.5°	705.0	704.8	704.6	704.1	703.1	702.3	701.4	700.6
125°	776.5	776.0	775.4	775.1	774.8	774.5	774.2	773.9
127.5°	847.4	847.2	847.0	846.5	846.0	845.5	844.9	844.3
130°	894.4	894.2	893.9	893.4	893.0	892.4	891.8	891.3
132.5°	939.4	939.1	938.9	938.4	937.6	936.8	936.0	935.3
135°	1008.7	1008.7	1008.7	1008.1	1007.0	1006.0	1004.8	1003.8
137.5°	1076.1	1076.4	1076.8	1076.2	1074.9	1073.5	1072.1	1070.8
140°	1118.6	1119.1	1119.6	1119.3	1117.9	1116.5	1115.2	1113.8
142.5°	1160.2	1160.6	1160.8	1160.4	1159.0	1157.6	1156.2	1154.9
145°	1220.2	1220.2	1220.2	1219.7	1219.0	1218.1	1217.3	1216.5
147.5°	1275.7	1276.4	1277.1	1276.5	1274.6	1272.8	1270.9	1269.1
150°	1310.7	1310.7	1310.7	1310.4	1309.9	1309.3	1308.7	1308.2
152.5°	1343.2	1343.9	1344.5	1344.4	1343.4	1342.5	1341.4	1340.5
155°	1389.9	1390.9	1392.0	1391.9	1390.5	1389.2	1387.8	1386.5
157.5°	1430.2	1431.3	1432.4	1432.0	1430.2	1428.4	1426.6	1424.8
160°	1454.6	1455.8	1456.8	1456.7	1455.4	1454.0	1452.6	1451.2
162.5°	1477.6	1478.8	1480.2	1480.1	1478.5	1476.9	1475.4	1473.8
165°	1508.4	1509.6	1510.6	1510.3	1508.7	1507.1	1505.4	1503.8
167.5°	1531.3	1533.0	1534.6	1534.6	1532.9	1531.2	1529.5	1527.8
170°	1545.0	1546.6	1548.2	1548.1	1546.2	1544.4	1542.4	1540.5
172.5°	1554.8	1556.4	1558.0	1558.0	1556.3	1554.6	1552.9	1551.2
175°	1565.8	1567.4	1569.1	1568.9	1567.0	1565.1	1563.2	1561.3
177.5°	1570.7	1572.1	1573.4	1573.3	1571.7	1570.2	1568.7	1567.2
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1

(END OF REPORT)