

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333699

Luminaire Tested: **S125RDIW-S850D1560U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333699  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S850D1560U835-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8660.6 lumens  
Efficiency: N/A  
Efficacy: 127.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333699

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333699

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38																				
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	40	39	38	32																				
2	87	80	74	69	78	72	67	63	59	55	52	47	44	42	35	34	32	27																				
3	79	70	63	57	72	64	58	53	52	48	44	41	38	36	31	29	28	23																				
4	72	62	54	49	65	57	50	45	46	42	38	37	33	31	28	26	24	20																				
5	66	55	47	42	60	50	44	38	41	36	32	33	29	27	25	23	21	17																				
6	61	50	42	36	55	45	38	33	37	32	28	30	26	23	23	20	18	15																				
7	57	45	37	31	51	41	34	29	34	29	25	27	23	21	21	18	16	14																				
8	52	40	33	28	48	37	31	26	31	26	22	25	21	18	19	17	15	12																				
9	49	37	30	25	44	34	27	23	28	23	20	23	19	17	18	15	13	11																				
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	17	14	12	10																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8881	8881	8881
5°	8901	8800	8854
10°	8834	8718	8718
15°	8729	8541	8471
20°	8594	8294	8194
25°	8437	8052	7874
30°	8240	7768	7520
35°	8041	7476	7123
40°	7854	7171	6734
45°	7626	6830	6308
50°	7398	6459	5865
55°	7133	6104	5391
60°	6868	5674	4883
65°	6554	5174	4300
70°	6197	4549	3707
75°	5702	3835	3084
80°	5021	3013	2589
85°	4231	2460	2312



TEST NUMBER: P333699

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.3	1.5
10°-20°	361.3	4.2
20°-30°	524.0	6.1
30°-40°	597.2	6.9
40°-50°	582.1	6.7
50°-60°	490.0	5.7
60°-70°	343.5	4.0
70°-80°	176.6	2.0
80°-90°	48.8	0.6
90°-100°	129.8	1.5
100°-110°	383.3	4.4
110°-120°	649.2	7.5
120°-130°	854.4	9.9
130°-140°	957.4	11.1
140°-150°	938.3	10.8
150°-160°	788.1	9.1
160°-170°	523.9	6.0
170°-180°	183.3	2.1
0°-30°	1014.6	11.7
0°-40°	1611.8	18.6
0°-60°	2683.9	31.0
0°-90°	3252.7	37.6
90°-120°	1162.3	13.4
90°-150°	3912.5	45.2
90°-180°	5408.0	62.4
0°-180°	8660.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1375	1375	1375	1375	1375	
5°	1373	1368	1357	1367	1366	130
15°	1306	1298	1277	1276	1267	368
25°	1184	1167	1130	1117	1105	545
35°	1020	994	948	919	904	638
45°	835	803	748	708	691	644
55°	634	599	542	497	479	566
65°	429	392	339	298	281	425
75°	228	197	154	132	124	242
85°	57	39	33	32	31	64
90°	2	13	24	32	36	8
95°	98	102	116	126	130	105
105°	344	352	360	369	374	367
115°	650	656	659	658	656	643
125°	949	957	959	956	955	849
135°	1234	1242	1244	1244	1238	951
145°	1495	1501	1505	1505	1501	934
155°	1710	1710	1712	1717	1710	787
165°	1860	1857	1858	1863	1855	524
175°	1934	1928	1927	1935	1926	184
180°	1938	1938	1938	1938	1938	



TEST NUMBER: P333699

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1377.5	1377.0	1376.4	1375.9	1375.3	1374.1	1372.3	1370.4	1368.6	1366.7	1368.6
5°	1373.0	1372.1	1371.1	1370.2	1369.3	1367.6	1365.0	1362.5	1359.9	1357.4	1359.7
7.5°	1359.5	1358.6	1357.7	1356.8	1356.0	1354.0	1351.0	1347.9	1344.9	1341.8	1343.4
10°	1347.0	1346.3	1345.6	1344.9	1344.2	1342.3	1339.1	1335.8	1332.6	1329.4	1330.0
12.5°	1332.9	1332.0	1331.1	1330.3	1329.4	1326.8	1322.4	1318.1	1313.8	1309.4	1309.9
15°	1305.5	1304.1	1302.7	1301.3	1299.9	1296.8	1292.0	1287.1	1282.3	1277.4	1277.2
17.5°	1274.5	1272.4	1270.3	1268.2	1266.0	1261.9	1255.8	1249.7	1243.6	1237.5	1236.4
20°	1250.4	1248.1	1245.8	1243.5	1241.2	1236.3	1229.0	1221.6	1214.2	1206.8	1205.7
22.5°	1223.8	1221.5	1219.2	1216.9	1214.6	1209.6	1201.8	1194.1	1186.3	1178.6	1176.3
25°	1184.0	1180.5	1177.0	1173.6	1170.1	1164.1	1155.6	1147.0	1138.5	1130.0	1127.0
27.5°	1138.3	1134.1	1129.9	1125.7	1121.5	1114.8	1105.7	1096.5	1087.4	1078.2	1074.0
30°	1105.0	1100.6	1096.3	1091.9	1087.5	1080.4	1070.8	1061.1	1051.4	1041.7	1036.4
32.5°	1072.6	1067.5	1062.4	1057.3	1052.1	1044.6	1034.8	1024.9	1015.0	1005.1	999.3
35°	1019.9	1014.3	1008.8	1003.2	997.7	989.7	979.4	969.0	958.6	948.2	941.5
37.5°	968.1	961.4	954.7	947.9	941.2	932.5	921.8	911.0	900.3	889.6	881.6
40°	931.6	924.7	917.7	910.8	903.9	894.9	883.8	872.7	861.7	850.6	841.8
42.5°	893.4	886.3	879.2	872.0	864.9	855.7	844.2	832.8	821.3	809.9	801.5
45°	835.0	828.3	821.6	814.9	808.2	798.5	785.8	773.2	760.5	747.8	738.5
47.5°	774.6	767.5	760.4	753.4	746.3	736.4	723.6	710.8	698.0	685.2	675.7
50°	736.3	728.7	721.1	713.5	705.9	695.5	682.3	669.2	656.0	642.9	633.2
52.5°	694.8	687.0	679.2	671.4	663.6	653.5	641.1	628.7	616.2	603.8	593.4
55°	633.5	626.1	618.8	611.4	604.0	593.8	580.9	568.0	555.1	542.1	531.7
57.5°	571.6	563.7	555.8	547.9	540.1	529.9	517.4	504.9	492.5	480.0	469.9
60°	531.7	523.7	515.6	507.5	499.4	489.2	476.7	464.2	451.8	439.3	429.2
62.5°	489.4	481.7	474.0	466.2	458.5	448.4	435.7	423.1	410.4	397.8	388.4
65°	428.9	421.1	413.2	405.4	397.5	387.5	375.3	363.0	350.8	338.6	329.3
67.5°	368.9	361.0	353.2	345.4	337.5	327.7	316.0	304.3	292.6	280.8	272.4
70°	328.2	320.3	312.5	304.6	296.8	287.1	275.6	264.0	252.5	240.9	233.8
72.5°	288.3	280.6	273.0	265.3	257.7	248.4	237.6	226.8	216.0	205.2	198.6
75°	228.5	221.6	214.6	207.7	200.8	192.5	182.8	173.1	163.4	153.7	148.6
77.5°	169.1	163.5	158.0	152.5	146.9	140.3	132.5	124.8	117.0	109.3	105.7
80°	135.0	129.5	123.9	118.4	112.9	106.9	100.4	93.9	87.5	81.0	78.9
82.5°	101.8	96.8	91.8	86.8	81.8	77.1	72.7	68.3	63.8	59.4	58.4
85°	57.1	53.0	48.8	44.7	40.5	37.8	36.7	35.5	34.4	33.2	33.0
87.5°	19.4	18.7	17.9	17.1	16.4	16.2	16.4	16.7	17.0	17.3	17.6
90°	1.5	4.2	6.9	9.6	12.2	14.7	17.1	19.4	21.8	24.1	25.8
92.5°	36.5	38.4	40.3	42.1	44.0	46.4	49.3	52.1	55.0	57.9	60.1
95°	98.0	98.7	99.4	100.0	100.7	102.7	106.1	109.4	112.8	116.1	118.5
97.5°	162.9	163.1	163.4	163.7	164.0	166.4	171.0	175.7	180.3	184.9	187.1
100°	211.1	211.1	211.1	211.1	211.1	213.3	217.7	222.0	226.4	230.7	233.8
102.5°	263.0	264.4	265.7	267.0	268.4	270.2	272.4	274.6	276.8	279.0	282.3
105°	343.9	345.5	347.2	348.9	350.6	352.4	354.4	356.4	358.4	360.5	362.5
107.5°	433.1	434.8	436.5	438.2	439.8	441.5	443.0	444.5	446.1	447.6	448.6
110°	494.7	496.4	498.0	499.7	501.4	502.7	503.7	504.7	505.7	506.7	507.7



TEST NUMBER: P333699

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	557.4	558.3	559.2	560.0	560.9	562.0	563.2	564.5	565.8	567.1	567.5
115°	650.0	651.4	652.7	654.0	655.4	656.4	657.1	657.7	658.4	659.1	658.7
117.5°	742.9	743.5	744.1	744.7	745.3	745.9	746.5	747.1	747.7	748.4	748.6
120°	800.8	802.5	804.2	805.9	807.5	808.5	808.9	809.2	809.5	809.9	809.9
122.5°	863.6	864.2	864.8	865.4	866.0	866.7	867.6	868.5	869.3	870.2	869.9
125°	948.6	950.6	952.7	954.7	956.7	957.9	958.2	958.5	958.9	959.2	958.5
127.5°	1039.1	1040.3	1041.4	1042.5	1043.7	1044.5	1044.9	1045.3	1045.7	1046.1	1045.7
130°	1093.4	1095.1	1096.8	1098.4	1100.1	1101.3	1102.0	1102.6	1103.3	1104.0	1103.6
132.5°	1147.7	1150.5	1153.2	1156.0	1158.7	1160.0	1159.9	1159.7	1159.6	1159.5	1159.1
135°	1233.7	1235.7	1237.7	1239.7	1241.7	1242.9	1243.2	1243.6	1243.9	1244.2	1244.2
137.5°	1314.5	1316.5	1318.4	1320.3	1322.3	1323.6	1324.4	1325.1	1325.8	1326.6	1327.0
140°	1366.4	1368.1	1369.7	1371.4	1373.1	1374.4	1375.4	1376.5	1377.5	1378.5	1379.1
142.5°	1418.3	1419.7	1421.1	1422.5	1423.9	1425.2	1426.5	1427.8	1429.1	1430.3	1430.7
145°	1494.6	1495.9	1497.3	1498.6	1500.0	1501.1	1502.1	1503.1	1504.1	1505.1	1505.1
147.5°	1565.2	1565.9	1566.6	1567.4	1568.1	1568.9	1569.7	1570.5	1571.3	1572.1	1572.9
150°	1612.2	1611.9	1611.6	1611.2	1610.9	1611.4	1612.7	1614.1	1615.4	1616.8	1616.8
152.5°	1650.8	1651.3	1651.8	1652.2	1652.7	1653.2	1653.8	1654.3	1654.8	1655.4	1656.2
155°	1710.3	1710.3	1710.3	1710.3	1710.3	1710.4	1710.8	1711.1	1711.4	1711.8	1713.1
157.5°	1763.3	1762.6	1761.9	1761.1	1760.4	1760.2	1760.5	1760.9	1761.2	1761.5	1762.9
160°	1794.7	1793.7	1792.7	1791.7	1790.7	1790.4	1790.7	1791.0	1791.4	1791.7	1793.0
162.5°	1822.5	1821.7	1821.0	1820.3	1819.5	1819.2	1819.2	1819.3	1819.4	1819.4	1821.1
165°	1859.6	1858.9	1858.2	1857.6	1856.9	1856.7	1857.1	1857.4	1857.7	1858.1	1859.4
167.5°	1890.9	1889.6	1888.3	1886.9	1885.6	1884.9	1884.9	1884.9	1884.9	1884.9	1886.9
170°	1907.8	1906.5	1905.1	1903.8	1902.5	1901.8	1901.8	1901.8	1901.8	1901.8	1903.8
172.5°	1919.9	1918.6	1917.2	1915.9	1914.5	1913.9	1913.9	1913.9	1913.9	1913.9	1915.9
175°	1933.5	1932.1	1930.8	1929.4	1928.1	1927.4	1927.4	1927.4	1927.4	1927.4	1929.4
177.5°	1940.4	1939.3	1938.3	1937.2	1936.1	1935.4	1935.2	1934.9	1934.6	1934.4	1936.0
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333699

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1	1375.1
2.5°	1370.4	1372.3	1374.1	1375.0	1374.8	1374.6	1374.4	1374.2
5°	1362.0	1364.3	1366.6	1367.6	1367.1	1366.6	1366.2	1365.7
7.5°	1345.1	1346.7	1348.3	1348.8	1348.3	1347.8	1347.3	1346.8
10°	1330.7	1331.4	1332.1	1332.1	1331.4	1330.7	1330.0	1329.4
12.5°	1310.4	1310.9	1311.4	1311.2	1310.1	1309.0	1308.0	1306.9
15°	1277.0	1276.7	1276.5	1275.4	1273.3	1271.2	1269.1	1267.0
17.5°	1235.2	1234.1	1232.9	1231.5	1229.8	1228.1	1226.4	1224.7
20°	1204.5	1203.3	1202.2	1200.6	1198.5	1196.4	1194.3	1192.3
22.5°	1174.0	1171.8	1169.5	1167.5	1165.8	1164.1	1162.4	1160.7
25°	1124.0	1121.0	1118.0	1115.2	1112.6	1110.1	1107.6	1105.0
27.5°	1069.8	1065.6	1061.4	1058.1	1055.7	1053.2	1050.8	1048.3
30°	1031.1	1025.8	1020.4	1016.8	1014.7	1012.6	1010.5	1008.4
32.5°	993.4	987.5	981.7	977.4	974.8	972.2	969.5	966.9
35°	934.8	928.1	921.4	916.5	913.2	910.0	906.8	903.5
37.5°	873.6	865.5	857.5	851.9	848.8	845.6	842.5	839.4
40°	833.0	824.3	815.5	809.7	807.0	804.2	801.4	798.7
42.5°	793.1	784.7	776.3	770.0	766.0	761.9	757.8	753.8
45°	729.3	720.1	710.8	704.5	701.0	697.6	694.1	690.6
47.5°	666.2	656.7	647.2	640.5	636.7	632.9	629.0	625.2
50°	623.5	613.8	604.1	597.5	594.1	590.6	587.1	583.7
52.5°	583.0	572.5	562.1	555.1	551.7	548.2	544.8	541.3
55°	521.4	511.0	500.6	493.5	489.9	486.2	482.5	478.8
57.5°	459.7	449.6	439.4	432.7	429.4	426.1	422.9	419.6
60°	419.0	408.8	398.7	391.9	388.4	385.0	381.5	378.0
62.5°	378.9	369.5	360.1	353.7	350.2	346.7	343.3	339.8
65°	320.1	310.9	301.6	295.3	291.8	288.4	284.9	281.4
67.5°	263.9	255.5	247.0	241.4	238.7	235.9	233.1	230.4
70°	226.6	219.5	212.3	207.4	204.6	201.8	199.1	196.3
72.5°	192.0	185.4	178.8	174.6	172.7	170.9	169.1	167.2
75°	143.6	138.5	133.4	130.1	128.4	126.8	125.2	123.6
77.5°	102.1	98.6	95.0	92.7	91.5	90.3	89.1	87.9
80°	76.9	74.8	72.7	71.4	71.0	70.5	70.0	69.6
82.5°	57.5	56.5	55.5	54.9	54.6	54.4	54.1	53.8
85°	32.8	32.5	32.3	32.1	31.8	31.6	31.4	31.2
87.5°	18.0	18.3	18.6	18.8	18.8	18.8	18.9	18.9
90°	27.5	29.2	30.8	32.2	33.2	34.2	35.2	36.2
92.5°	62.3	64.5	66.8	68.2	69.0	69.7	70.4	71.2
95°	120.8	123.2	125.5	127.0	127.7	128.4	129.0	129.7
97.5°	189.3	191.5	193.7	195.1	195.5	195.9	196.3	196.7
100°	236.8	239.8	242.8	244.7	245.3	246.0	246.7	247.3
102.5°	285.6	288.9	292.1	294.3	295.2	296.1	297.1	298.0
105°	364.5	366.5	368.5	370.0	371.0	372.0	373.0	374.0
107.5°	449.6	450.6	451.6	452.1	452.0	452.0	451.9	451.8
110°	508.8	509.8	510.8	511.1	510.8	510.4	510.1	509.8





TEST NUMBER: P333699

CATALOG NUMBER: S125RDIW-S850D1560U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	568.0	568.5	568.9	568.9	568.3	567.7	567.1	566.5
115°	658.4	658.1	657.7	657.4	657.1	656.7	656.4	656.1
117.5°	748.9	749.2	749.4	748.9	747.5	746.2	744.9	743.5
120°	809.9	809.9	809.9	809.2	807.9	806.5	805.2	803.9
122.5°	869.7	869.4	869.1	868.5	867.4	866.3	865.2	864.2
125°	957.9	957.2	956.5	956.0	955.7	955.3	955.0	954.7
127.5°	1045.4	1045.1	1044.7	1044.2	1043.5	1042.9	1042.2	1041.5
130°	1103.3	1103.0	1102.6	1102.1	1101.5	1100.8	1100.1	1099.5
132.5°	1158.8	1158.5	1158.1	1157.5	1156.6	1155.6	1154.7	1153.7
135°	1244.2	1244.2	1244.2	1243.6	1242.2	1240.9	1239.5	1238.2
137.5°	1327.4	1327.8	1328.2	1327.6	1325.9	1324.2	1322.5	1320.8
140°	1379.8	1380.5	1381.1	1380.6	1379.0	1377.3	1375.6	1373.9
142.5°	1431.1	1431.5	1432.0	1431.3	1429.6	1428.0	1426.3	1424.6
145°	1505.1	1505.1	1505.1	1504.6	1503.6	1502.6	1501.6	1500.6
147.5°	1573.7	1574.5	1575.3	1574.6	1572.3	1570.0	1567.8	1565.5
150°	1616.8	1616.8	1616.8	1616.4	1615.7	1615.1	1614.4	1613.7
152.5°	1657.0	1657.8	1658.6	1658.4	1657.2	1656.0	1654.8	1653.6
155°	1714.4	1715.8	1717.1	1717.0	1715.3	1713.6	1711.9	1710.3
157.5°	1764.2	1765.6	1766.9	1766.5	1764.2	1762.0	1759.8	1757.6
160°	1794.4	1795.7	1797.1	1796.9	1795.2	1793.5	1791.9	1790.2
162.5°	1822.7	1824.3	1825.9	1825.7	1823.8	1821.8	1819.9	1817.9
165°	1860.7	1862.1	1863.4	1863.1	1861.1	1859.1	1857.1	1855.0
167.5°	1888.9	1890.9	1892.9	1892.9	1890.8	1888.8	1886.7	1884.6
170°	1905.8	1907.8	1909.8	1909.7	1907.3	1905.0	1902.6	1900.3
172.5°	1917.9	1919.9	1921.9	1921.9	1919.8	1917.7	1915.6	1913.6
175°	1931.5	1933.5	1935.5	1935.3	1933.0	1930.6	1928.3	1925.9
177.5°	1937.6	1939.2	1940.8	1940.7	1938.8	1936.9	1935.0	1933.2
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0

(END OF REPORT)