

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333356-830

Luminaire Tested: **S125DIW-S375D1050U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333356-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1050U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5384.4 lumens
Efficiency: N/A
Efficacy: 141.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333356-830

CATALOG NUMBER: S125DIW-S375D1050U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333356-830

CATALOG NUMBER: S125DIW-S375D1050U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	88	85	81	82	79	76	73	61	59	57	45	44	43	31	30	29	22
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	26	24	19
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18	14
5	64	53	45	39	57	48	41	36	37	33	29	28	25	22	19	17	16	12
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14	10
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12	9
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3556	3556	3556
5°	3564	3530	3553
10°	3543	3505	3525
15°	3504	3463	3477
20°	3449	3404	3410
25°	3390	3334	3331
30°	3317	3258	3242
35°	3239	3177	3132
40°	3159	3089	3044
45°	3072	3008	2948
50°	2976	2910	2823
55°	2884	2800	2723
60°	2773	2689	2595
65°	2644	2557	2470
70°	2517	2402	2319
75°	2293	2218	2141
80°	2042	2008	1960
85°	1771	1808	1712



TEST NUMBER: P333356-830

CATALOG NUMBER: S125DIW-S375D1050U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.9	1.0
10°-20°	146.6	2.7
20°-30°	216.5	4.0
30°-40°	252.7	4.7
40°-50°	253.8	4.7
50°-60°	222.8	4.1
60°-70°	166.0	3.1
70°-80°	94.9	1.8
80°-90°	30.3	0.6
90°-100°	46.7	0.9
100°-110°	288.0	5.3
110°-120°	522.3	9.7
120°-130°	670.4	12.5
130°-140°	721.0	13.4
140°-150°	676.8	12.6
150°-160°	547.5	10.2
160°-170°	354.1	6.6
170°-180°	122.1	2.3
0°-30°	415.1	7.7
0°-40°	667.8	12.4
0°-60°	1144.3	21.3
0°-90°	1435.4	26.7
90°-120°	857.1	15.9
90°-150°	2925.3	54.3
90°-180°	3949.0	73.3
0°-180°	5384.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	551	551	551	551	551	
5°	550	549	544	548	548	52
15°	524	522	518	520	520	148
25°	476	473	468	469	467	219
35°	411	409	403	401	397	257
45°	336	334	329	324	323	259
55°	256	255	249	245	242	229
65°	173	172	167	164	162	172
75°	92	91	89	88	86	98
85°	24	24	24	24	23	27
90°	1	8	15	20	23	4
95°	54	50	15	20	20	69
105°	280	284	284	284	283	297
115°	526	531	532	528	522	521
125°	748	755	755	751	748	668
135°	933	939	937	935	929	719
145°	1082	1084	1084	1084	1079	676
155°	1192	1186	1188	1190	1183	549
165°	1257	1252	1252	1258	1251	355
175°	1286	1281	1281	1288	1280	122
180°	1286	1286	1286	1286	1286	



TEST NUMBER: P333356-830

CATALOG NUMBER: S125DIW-S375D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	552.0	551.8	551.6	551.3	551.1	550.5	549.8	549.0	548.3	547.4	548.3
5°	549.7	549.5	549.3	549.1	548.9	548.4	547.4	546.5	545.4	544.5	545.4
7.5°	544.7	544.5	544.3	544.1	543.9	543.3	542.2	541.1	540.1	539.0	539.9
10°	540.2	540.0	539.8	539.6	539.4	538.8	537.7	536.6	535.6	534.5	535.3
12.5°	534.6	534.2	533.9	533.6	533.2	532.5	531.5	530.6	529.5	528.6	529.1
15°	524.1	523.8	523.5	523.2	522.8	522.2	521.1	520.1	519.0	517.9	518.4
17.5°	511.9	511.5	511.0	510.7	510.2	509.4	508.3	507.3	506.1	505.0	505.7
20°	501.8	501.6	501.4	501.2	501.1	500.3	499.1	497.8	496.5	495.3	496.0
22.5°	491.7	491.3	491.0	490.7	490.3	489.6	488.3	487.2	486.0	484.8	485.3
25°	475.7	475.2	474.7	474.2	473.7	472.9	471.6	470.3	469.1	467.9	468.1
27.5°	456.9	456.7	456.4	456.1	455.8	455.0	453.7	452.4	451.1	449.8	449.9
30°	444.8	444.5	444.1	443.8	443.6	442.7	441.3	439.8	438.4	436.9	436.7
32.5°	431.5	431.0	430.6	430.2	429.7	428.9	427.5	426.2	425.0	423.7	423.3
35°	410.8	410.4	410.0	409.6	409.3	408.3	407.0	405.7	404.3	402.9	402.5
37.5°	389.3	388.8	388.3	387.8	387.3	386.4	385.1	383.9	382.6	381.4	380.6
40°	374.7	374.1	373.6	373.2	372.7	371.7	370.4	369.1	367.7	366.4	365.5
42.5°	358.9	358.5	358.2	357.7	357.3	356.5	355.1	353.7	352.3	351.0	350.2
45°	336.3	335.9	335.5	335.2	334.7	333.9	332.8	331.7	330.5	329.3	328.2
47.5°	311.9	311.9	311.9	312.0	312.0	311.3	309.9	308.5	307.1	305.7	304.5
50°	296.2	296.0	295.7	295.3	295.0	294.4	293.1	292.0	290.9	289.6	288.4
52.5°	280.2	279.9	279.7	279.6	279.4	278.6	277.4	276.2	274.8	273.6	272.6
55°	256.1	255.8	255.5	255.2	255.0	254.1	252.8	251.5	250.1	248.7	247.9
57.5°	230.8	230.6	230.5	230.4	230.2	229.5	228.4	227.2	226.1	225.0	223.9
60°	214.7	214.3	214.0	213.6	213.2	212.4	211.4	210.4	209.2	208.2	207.3
62.5°	198.0	197.7	197.4	197.1	196.8	196.1	195.3	194.4	193.4	192.6	191.5
65°	173.0	172.8	172.6	172.4	172.2	171.5	170.5	169.4	168.3	167.3	166.4
67.5°	148.6	148.3	147.8	147.4	147.0	146.4	145.6	144.8	144.0	143.3	142.5
70°	133.3	132.8	132.3	131.9	131.4	130.6	129.8	128.9	128.1	127.2	126.6
72.5°	116.6	116.2	115.9	115.6	115.3	114.8	114.2	113.7	113.1	112.5	111.9
75°	91.9	91.7	91.5	91.3	91.1	90.8	90.3	89.8	89.4	88.9	88.6
77.5°	69.2	69.1	69.0	68.9	68.9	68.7	68.4	68.1	67.9	67.6	67.4
80°	54.9	54.9	54.9	54.9	54.9	54.8	54.6	54.4	54.2	54.0	53.9
82.5°	42.3	42.2	42.0	41.8	41.8	41.7	41.6	41.6	41.5	41.5	41.3
85°	23.9	24.0	24.1	24.2	24.3	24.4	24.4	24.4	24.4	24.4	24.3
87.5°	9.6	9.9	10.3	10.7	10.9	11.2	11.5	11.7	11.9	12.1	12.3
90°	0.9	2.6	4.3	6.0	7.7	9.3	10.8	12.3	13.8	15.3	16.3
92.5°	14.7	13.5	12.3	11.1	9.9	10.0	11.3	12.6	13.9	15.3	16.3
95°	54.3	53.7	53.1	52.4	51.8	47.4	39.4	31.4	23.3	15.3	16.3
97.5°	113.5	114.6	115.7	116.9	118.0	110.7	94.7	78.8	62.9	46.9	40.9
100°	159.2	159.9	160.4	161.1	161.7	162.5	163.3	164.2	165.0	165.9	134.3
102.5°	205.8	206.5	207.4	208.1	209.0	209.6	210.1	210.6	211.1	211.6	205.7
105°	280.2	281.1	281.9	282.8	283.6	284.1	284.1	284.1	284.1	284.1	284.1
107.5°	357.7	357.7	357.7	357.7	357.7	357.9	358.3	358.7	359.1	359.6	359.6
110°	408.0	408.0	408.0	408.0	408.0	408.2	408.6	409.1	409.4	409.9	409.3



TEST NUMBER: P333356-830

CATALOG NUMBER: S125DIW-S375D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	455.2	455.8	456.3	456.8	457.3	457.7	458.0	458.2	458.5	458.7	457.9
115°	526.2	527.3	528.3	529.3	530.5	531.0	531.3	531.5	531.7	531.9	531.0
117.5°	599.6	599.6	599.6	599.5	599.5	599.8	600.6	601.4	602.2	603.0	601.9
120°	645.4	645.2	644.9	644.7	644.5	644.7	645.4	646.0	646.6	647.2	646.9
122.5°	685.8	686.5	687.4	688.2	689.0	689.6	689.8	690.1	690.4	690.7	690.3
125°	748.3	749.8	751.3	752.7	754.2	755.0	755.0	755.0	755.0	755.0	754.1
127.5°	807.9	809.1	810.1	811.2	812.2	812.7	812.6	812.5	812.3	812.2	811.7
130°	844.6	845.6	846.7	847.7	848.9	849.4	849.7	849.9	850.1	850.3	849.7
132.5°	881.2	882.4	883.6	884.9	886.1	886.5	886.0	885.5	885.0	884.7	884.5
135°	933.2	934.5	935.8	937.1	938.3	938.8	938.3	937.9	937.5	937.1	936.6
137.5°	981.1	982.2	983.3	984.4	985.5	985.9	985.5	985.1	984.7	984.3	984.4
140°	1012.4	1012.8	1013.2	1013.6	1014.1	1014.2	1014.0	1013.7	1013.5	1013.3	1013.7
142.5°	1040.6	1040.8	1041.1	1041.3	1041.6	1041.9	1042.2	1042.5	1042.7	1043.0	1043.1
145°	1081.9	1082.4	1082.8	1083.3	1083.6	1083.8	1083.8	1083.8	1083.8	1083.8	1084.1
147.5°	1118.1	1118.1	1118.0	1117.9	1117.9	1117.9	1118.1	1118.4	1118.7	1118.9	1119.2
150°	1141.0	1140.7	1140.2	1139.8	1139.3	1139.3	1139.8	1140.2	1140.7	1141.0	1141.5
152.5°	1163.2	1162.2	1161.3	1160.4	1159.4	1159.2	1159.6	1160.1	1160.5	1160.8	1161.3
155°	1191.6	1190.3	1189.0	1187.8	1186.5	1186.1	1186.5	1186.9	1187.3	1187.8	1188.4
157.5°	1213.5	1212.8	1212.0	1211.3	1210.4	1210.1	1210.1	1210.1	1210.2	1210.2	1211.0
160°	1228.8	1227.5	1226.2	1224.9	1223.7	1223.1	1223.3	1223.6	1223.8	1224.0	1224.8
162.5°	1241.0	1239.7	1238.4	1237.2	1235.9	1235.3	1235.6	1235.8	1236.0	1236.1	1237.4
165°	1257.4	1256.1	1254.8	1253.6	1252.3	1251.7	1252.0	1252.2	1252.4	1252.5	1253.9
167.5°	1269.5	1268.3	1267.0	1265.6	1264.3	1263.8	1263.9	1264.1	1264.4	1264.6	1266.1
170°	1276.4	1275.0	1273.5	1272.0	1270.5	1269.9	1270.1	1270.3	1270.5	1270.7	1272.4
172.5°	1281.0	1279.5	1278.0	1276.6	1275.1	1274.5	1274.9	1275.3	1275.6	1276.0	1277.5
175°	1285.9	1284.7	1283.4	1282.1	1280.8	1280.3	1280.5	1280.7	1281.0	1281.2	1282.9
177.5°	1288.3	1287.2	1286.2	1285.2	1284.2	1283.7	1283.9	1284.1	1284.2	1284.4	1285.6
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9



TEST NUMBER: P333356-830

CATALOG NUMBER: S125DIW-S375D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	550.6	550.6	550.6	550.6	550.6	550.6	550.6	550.6
2.5°	549.0	549.8	550.5	550.9	550.8	550.7	550.7	550.6
5°	546.2	547.1	548.0	548.4	548.3	548.2	548.1	548.0
7.5°	540.7	541.6	542.4	542.8	542.7	542.6	542.5	542.4
10°	536.0	536.8	537.6	537.9	537.8	537.7	537.6	537.5
12.5°	529.8	530.5	531.0	531.3	531.3	531.3	531.3	531.2
15°	518.9	519.3	519.9	520.1	520.1	520.1	520.1	520.1
17.5°	506.2	506.8	507.5	507.5	507.0	506.5	506.1	505.6
20°	496.6	497.3	497.9	498.1	497.6	497.1	496.6	496.2
22.5°	485.7	486.2	486.6	486.6	486.4	486.0	485.7	485.3
25°	468.3	468.4	468.6	468.5	468.3	468.0	467.7	467.4
27.5°	449.9	449.9	450.0	449.9	449.5	449.2	448.9	448.7
30°	436.5	436.3	436.1	435.9	435.6	435.4	435.0	434.7
32.5°	423.0	422.6	422.3	421.9	421.3	420.8	420.3	419.7
35°	402.0	401.5	401.0	400.4	399.6	398.8	398.0	397.3
37.5°	379.9	379.2	378.4	377.9	377.4	377.0	376.5	376.1
40°	364.6	363.7	362.9	362.3	362.0	361.7	361.4	361.1
42.5°	349.4	348.6	347.8	347.2	346.8	346.3	345.9	345.4
45°	327.0	325.8	324.7	324.0	323.7	323.4	323.1	322.8
47.5°	303.3	302.2	301.0	300.0	299.4	298.7	298.0	297.4
50°	287.2	285.9	284.6	283.7	283.0	282.3	281.6	281.0
52.5°	271.5	270.3	269.2	268.3	267.6	266.8	266.1	265.3
55°	246.9	246.1	245.2	244.5	243.8	243.1	242.4	241.8
57.5°	222.7	221.6	220.5	219.7	219.3	219.0	218.6	218.2
60°	206.3	205.3	204.3	203.5	202.8	202.2	201.5	200.9
62.5°	190.5	189.4	188.3	187.6	187.1	186.5	186.0	185.5
65°	165.5	164.7	163.8	163.2	162.8	162.4	162.0	161.6
67.5°	141.8	141.0	140.3	139.8	139.6	139.3	139.1	138.8
70°	126.0	125.5	124.9	124.4	124.0	123.7	123.2	122.8
72.5°	111.2	110.6	109.9	109.4	109.1	108.7	108.2	107.8
75°	88.3	88.0	87.7	87.4	87.0	86.6	86.2	85.8
77.5°	67.3	67.1	66.9	66.7	66.4	66.2	65.9	65.6
80°	53.8	53.7	53.6	53.4	53.3	53.1	52.9	52.7
82.5°	41.1	40.9	40.8	40.6	40.6	40.6	40.5	40.5
85°	24.2	24.1	24.0	23.8	23.7	23.5	23.3	23.1
87.5°	12.5	12.7	12.9	13.0	13.0	13.0	13.0	12.9
90°	17.3	18.5	19.5	20.4	21.0	21.6	22.2	22.9
92.5°	17.3	18.5	19.5	20.2	20.5	20.7	21.0	21.4
95°	17.3	18.5	19.5	20.0	20.0	20.0	20.0	20.0
97.5°	35.0	28.9	23.0	20.0	20.0	20.0	20.0	20.0
100°	102.7	71.2	39.6	23.4	22.5	21.7	20.8	20.0
102.5°	199.6	193.7	187.8	177.6	163.2	148.7	134.3	119.9
105°	284.1	284.1	284.1	284.0	283.8	283.5	283.3	283.1
107.5°	359.7	359.7	359.8	359.5	358.8	358.2	357.5	356.9
110°	408.6	408.0	407.4	407.2	407.4	407.6	407.7	408.0



TEST NUMBER: P333356-830

CATALOG NUMBER: S125DIW-S375D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	457.1	456.3	455.5	455.0	454.7	454.3	454.0	453.7
115°	530.2	529.3	528.5	527.4	526.2	524.9	523.7	522.4
117.5°	600.9	599.7	598.6	597.8	597.3	596.7	596.2	595.6
120°	646.4	646.0	645.5	644.8	643.8	642.7	641.7	640.6
122.5°	689.8	689.5	689.0	688.2	687.0	685.8	684.6	683.3
125°	753.3	752.4	751.6	750.8	750.3	749.6	748.9	748.3
127.5°	811.2	810.8	810.3	809.3	807.8	806.2	804.6	803.0
130°	849.0	848.4	847.7	846.9	845.8	844.8	843.8	842.7
132.5°	884.4	884.2	884.1	883.5	882.5	881.4	880.3	879.3
135°	936.2	935.8	935.4	934.5	933.2	932.0	930.7	929.4
137.5°	984.5	984.6	984.7	984.2	983.1	981.9	980.9	979.8
140°	1014.2	1014.6	1015.0	1014.6	1013.3	1012.0	1010.8	1009.5
142.5°	1043.2	1043.3	1043.4	1042.8	1041.5	1040.3	1039.0	1037.7
145°	1084.3	1084.5	1084.7	1084.2	1082.9	1081.7	1080.3	1079.1
147.5°	1119.5	1119.7	1119.9	1119.4	1117.8	1116.3	1114.7	1113.2
150°	1141.9	1142.4	1142.7	1142.1	1140.4	1138.7	1137.0	1135.3
152.5°	1161.7	1162.2	1162.5	1162.1	1160.5	1159.0	1157.4	1155.9
155°	1189.0	1189.7	1190.3	1189.8	1188.1	1186.4	1184.7	1183.0
157.5°	1211.6	1212.3	1213.0	1212.5	1210.8	1209.1	1207.4	1205.7
160°	1225.7	1226.5	1227.4	1226.9	1225.3	1223.6	1221.9	1220.2
162.5°	1238.6	1239.7	1241.0	1240.6	1238.7	1236.9	1235.0	1233.1
165°	1255.1	1256.4	1257.6	1257.4	1255.7	1254.1	1252.4	1250.7
167.5°	1267.6	1269.1	1270.7	1270.5	1268.6	1266.7	1264.8	1262.9
170°	1274.1	1275.8	1277.5	1277.3	1275.4	1273.6	1271.7	1269.7
172.5°	1279.1	1280.6	1282.1	1282.0	1280.1	1278.1	1276.2	1274.3
175°	1284.6	1286.3	1288.0	1287.9	1285.9	1284.0	1282.1	1280.3
177.5°	1286.8	1288.0	1289.2	1289.1	1287.7	1286.4	1285.1	1283.6
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9

(END OF REPORT)