

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333685

Luminaire Tested: **S125RDIW-S850D770U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333685
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S850D770U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5941.1 lumens
Efficiency: N/A
Efficacy: 132.0 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	95	92	88	92	89	85	83	76	74	72	65	63	62	55	53	52	47
2	91	84	78	73	84	78	73	68	67	64	60	58	55	52	49	47	45	40
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39	35
4	76	66	58	52	71	61	55	49	53	48	44	46	42	39	39	36	34	30
5	70	59	51	45	65	55	48	42	48	42	38	41	37	34	35	32	29	26
6	65	53	45	39	60	49	42	37	43	38	33	37	33	30	32	29	26	23
7	60	48	40	34	56	45	38	33	39	34	29	34	30	26	29	26	23	21
8	56	43	36	30	52	41	34	29	36	30	26	31	27	24	27	23	21	19
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8169	8169	8169	8169
5°	9398	8180	7224	8180
10°	10781	8138	6374	8138
15°	11645	8055	5666	8055
20°	12841	7958	5232	7958
25°	14860	7829	4855	7829
30°	16171	7694	4608	7694
35°	13640	7536	4380	7536
40°	9526	7254	4185	7254
45°	7067	6872	3993	6872
50°	5635	6475	3829	6475
55°	4782	5981	3683	5981
60°	4132	5540	3447	5540
65°	3681	5063	2968	5063
70°	3237	4638	2706	4638
75°	2800	4017	2540	4017
80°	2124	3381	2124	3381
85°	1771	2653	2001	2653



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	2.0
10°-20°	355.5	6.0
20°-30°	563.6	9.5
30°-40°	679.7	11.4
40°-50°	607.0	10.2
50°-60°	465.5	7.8
60°-70°	302.5	5.1
70°-80°	147.1	2.5
80°-90°	37.2	0.6
90°-100°	63.9	1.1
100°-110°	188.7	3.2
110°-120°	319.6	5.4
120°-130°	420.6	7.1
130°-140°	471.2	7.9
140°-150°	461.9	7.8
150°-160°	387.9	6.5
160°-170°	257.9	4.3
170°-180°	90.2	1.5
0°-30°	1040.4	17.5
0°-40°	1720.1	29.0
0°-60°	2792.5	47.0
0°-90°	3279.2	55.2
90°-120°	572.1	9.6
90°-150°	1925.8	32.4
90°-180°	2662.0	44.8
0°-180°	5941.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1265	1265	1265	1265	1265	
5°	1450	1262	1114	1262	1450	145
15°	1742	1205	847	1205	1742	499
25°	2085	1099	681	1099	2085	957
35°	1730	956	556	956	1730	1045
45°	774	752	437	752	774	617
55°	425	531	327	531	425	385
65°	241	331	194	331	241	240
75°	112	161	102	161	112	119
85°	24	36	27	36	24	28
90°	18	1	18	1	18	11
95°	64	48	64	48	64	65
105°	184	169	184	169	184	195
115°	323	320	323	320	323	319
125°	470	467	470	467	470	420
135°	610	607	610	607	610	470
145°	739	736	739	736	739	461
155°	842	842	842	842	842	387
165°	913	915	913	915	913	257
175°	948	952	948	952	948	90
180°	954	954	954	954	954	



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1330.5	1329.7	1331.4	1326.8	1327.2	1320.1	1320.1	1314.7	1307.7	1302.3	1299.8
5°	1449.7	1450.8	1448.7	1440.9	1435.7	1427.9	1419.1	1403.5	1390.5	1378.1	1368.2
7.5°	1572.5	1573.2	1566.4	1564.0	1550.9	1541.3	1521.7	1500.5	1481.7	1457.8	1439.6
10°	1643.9	1643.4	1636.2	1630.4	1619.0	1604.5	1585.3	1560.3	1537.0	1511.0	1486.1
12.5°	1685.5	1684.1	1681.8	1674.9	1664.3	1651.4	1635.1	1610.6	1581.8	1553.4	1524.3
15°	1741.6	1737.9	1731.2	1722.3	1707.3	1692.2	1674.1	1652.3	1624.7	1592.5	1565.5
17.5°	1810.9	1811.0	1800.7	1788.4	1767.9	1741.4	1713.3	1678.1	1640.7	1605.3	1576.5
20°	1868.3	1866.7	1856.3	1832.4	1809.1	1775.8	1743.6	1700.5	1654.8	1608.6	1572.8
22.5°	1950.5	1946.5	1935.7	1904.3	1868.1	1825.3	1776.0	1723.4	1668.1	1615.7	1568.7
25°	2085.3	2082.2	2060.9	2024.6	1973.7	1907.7	1843.3	1771.2	1691.7	1622.7	1565.5
27.5°	2177.5	2174.1	2158.3	2128.1	2081.2	2011.8	1924.6	1828.2	1729.0	1634.0	1551.6
30°	2168.4	2176.2	2174.1	2160.1	2124.8	2062.5	1982.0	1873.5	1755.6	1643.9	1545.8
32.5°	2037.9	2044.9	2063.2	2090.7	2092.8	2067.9	2007.7	1907.5	1785.5	1658.5	1541.2
35°	1730.1	1739.5	1774.8	1830.4	1903.0	1963.8	1976.3	1922.3	1812.7	1676.1	1534.4
37.5°	1330.1	1381.2	1410.9	1469.4	1579.2	1691.0	1798.5	1838.0	1791.4	1668.9	1523.3
40°	1129.9	1142.3	1195.3	1261.3	1353.7	1470.0	1623.2	1733.8	1737.4	1652.3	1505.8
42.5°	967.0	982.8	1019.2	1071.8	1151.0	1267.3	1425.4	1571.4	1639.0	1606.6	1483.0
45°	773.7	785.6	812.1	852.6	913.4	1009.4	1145.5	1314.2	1448.2	1500.6	1421.7
47.5°	635.6	642.0	665.1	695.9	740.9	810.9	916.2	1062.7	1223.4	1336.0	1324.9
50°	560.8	568.1	585.7	609.1	647.0	706.2	790.3	912.3	1078.0	1215.6	1243.1
52.5°	502.6	508.7	519.7	541.8	573.0	618.5	686.4	796.8	945.9	1092.2	1155.8
55°	424.7	428.9	437.7	450.2	475.1	507.8	566.5	642.8	763.3	910.8	1004.2
57.5°	360.6	362.6	368.3	379.8	397.0	420.9	463.3	528.0	614.4	747.2	850.3
60°	319.9	321.9	329.2	337.0	350.5	372.3	405.5	450.7	533.8	643.3	747.7
62.5°	287.5	288.7	291.8	299.6	311.4	328.3	354.4	391.3	457.4	553.6	652.2
65°	240.9	241.5	242.5	248.7	256.0	268.5	285.6	311.5	361.4	434.1	521.3
67.5°	196.3	197.0	200.6	202.8	210.4	216.9	227.0	246.9	282.0	331.0	398.8
70°	171.4	170.8	174.5	177.1	179.7	187.4	194.2	210.3	232.1	269.5	326.1
72.5°	148.1	146.7	148.3	149.2	152.7	158.0	164.7	174.6	191.4	217.1	260.5
75°	112.2	112.7	112.7	113.7	116.3	118.4	120.5	125.7	135.0	152.1	175.5
77.5°	78.7	77.9	80.1	80.4	81.9	84.2	86.0	88.1	91.9	99.0	111.0
80°	57.1	57.1	57.6	59.2	58.7	59.7	62.3	64.4	69.1	73.2	77.4
82.5°	43.8	43.4	43.9	44.2	44.1	45.2	46.1	46.5	48.3	50.4	53.3
85°	23.9	23.9	24.4	24.4	24.9	24.9	25.4	25.4	25.4	26.0	26.5
87.5°	12.7	12.2	11.7	11.6	11.9	12.6	12.0	11.4	11.3	11.1	11.3
90°	17.8	17.3	16.8	16.3	15.8	15.2	14.4	13.5	12.7	11.9	10.7
92.5°	35.0	34.7	34.3	34.0	33.6	32.9	31.8	30.7	29.6	28.5	27.1
95°	63.8	63.5	63.2	62.9	62.5	61.8	60.6	59.5	58.3	57.2	55.5
97.5°	96.8	96.6	96.4	96.2	96.0	95.4	94.3	93.2	92.1	91.0	88.7
100°	121.7	121.4	121.1	120.8	120.4	119.5	118.0	116.5	115.1	113.6	111.4
102.5°	146.7	146.2	145.8	145.3	144.8	143.8	142.2	140.6	139.0	137.3	136.2
105°	184.1	183.6	183.1	182.6	182.1	181.4	180.4	179.4	178.4	177.4	176.4
107.5°	222.4	222.4	222.5	222.5	222.5	222.3	221.8	221.3	220.8	220.3	219.6
110°	250.9	251.1	251.2	251.4	251.6	251.4	250.9	250.4	249.9	249.4	248.9



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	278.8	279.1	279.4	279.7	280.0	280.0	279.8	279.6	279.4	279.1	278.5
115°	322.9	323.1	323.3	323.4	323.6	323.7	323.9	324.1	324.2	324.4	324.1
117.5°	366.0	366.6	367.3	368.0	368.6	368.9	368.7	368.6	368.5	368.4	368.1
120°	395.7	396.3	397.0	397.7	398.3	398.6	398.6	398.6	398.6	398.6	398.5
122.5°	425.4	425.9	426.4	426.9	427.5	427.8	427.9	428.1	428.2	428.3	427.9
125°	469.9	470.1	470.2	470.4	470.6	470.8	471.1	471.5	471.8	472.1	472.0
127.5°	512.7	513.0	513.3	513.7	514.0	514.2	514.4	514.6	514.7	514.9	514.7
130°	541.2	541.5	541.8	542.2	542.5	542.7	542.9	543.1	543.2	543.4	543.1
132.5°	567.9	568.4	568.8	569.3	569.7	570.1	570.2	570.4	570.6	570.7	570.8
135°	609.5	610.1	610.8	611.4	612.1	612.4	612.4	612.4	612.4	612.4	612.3
137.5°	650.1	651.0	651.8	652.6	653.4	653.8	653.6	653.4	653.2	653.0	652.6
140°	676.3	677.1	677.9	678.8	679.6	679.8	679.5	679.2	678.8	678.5	678.0
142.5°	701.2	702.0	702.9	703.7	704.5	704.8	704.6	704.4	704.2	704.0	703.4
145°	738.6	739.1	739.6	740.1	740.6	740.9	740.9	740.9	740.9	740.9	740.4
147.5°	770.6	771.7	772.8	773.9	775.0	775.4	775.0	774.6	774.2	773.8	773.4
150°	794.3	794.6	795.0	795.3	795.6	795.8	795.8	795.8	795.8	795.8	795.1
152.5°	813.9	814.5	815.1	815.7	816.3	816.4	816.0	815.6	815.2	814.8	814.5
155°	841.8	842.6	843.5	844.3	845.1	845.2	844.5	843.9	843.2	842.6	842.4
157.5°	865.1	866.2	867.3	868.4	869.5	869.7	869.0	868.4	867.7	867.1	866.9
160°	881.2	882.0	882.8	883.6	884.5	884.5	883.9	883.2	882.6	881.9	881.7
162.5°	894.8	895.8	896.7	897.7	898.7	898.7	897.9	897.2	896.4	895.6	895.5
165°	913.1	914.1	915.1	916.1	917.0	917.2	916.6	915.9	915.2	914.6	914.4
167.5°	927.6	928.7	929.7	930.7	931.7	931.7	930.8	929.8	928.8	927.8	927.8
170°	935.4	936.5	937.7	938.8	940.0	940.1	939.1	938.1	937.1	936.1	936.1
172.5°	941.9	942.9	943.9	945.0	946.0	946.0	945.0	944.0	943.0	942.0	942.0
175°	948.0	949.1	950.3	951.4	952.6	952.7	951.7	950.7	949.7	948.7	948.7
177.5°	951.5	952.5	953.4	954.3	955.2	955.3	954.5	953.7	952.9	952.1	952.3
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1299.8	1296.9	1291.5	1286.5	1280.3	1274.9	1271.1	1266.6	1260.7	1253.7	1247.9
5°	1357.3	1345.9	1330.8	1317.9	1301.2	1288.3	1274.8	1261.8	1248.8	1232.2	1217.6
7.5°	1421.1	1397.5	1374.6	1345.7	1319.5	1296.1	1273.7	1251.0	1228.8	1205.2	1182.4
10°	1460.1	1431.6	1399.9	1363.5	1330.3	1298.6	1269.6	1241.0	1210.9	1184.4	1155.8
12.5°	1496.7	1459.8	1423.6	1377.7	1337.8	1299.1	1262.1	1226.5	1194.3	1159.9	1129.3
15°	1529.7	1493.4	1452.9	1396.8	1341.2	1294.5	1250.9	1204.7	1164.7	1126.3	1092.0
17.5°	1542.5	1504.4	1457.3	1403.4	1342.7	1283.9	1227.7	1177.0	1130.0	1085.2	1046.7
20°	1537.5	1500.6	1452.3	1400.9	1336.0	1274.8	1214.0	1157.9	1105.5	1058.2	1017.2
22.5°	1525.4	1487.3	1440.7	1386.4	1324.8	1259.8	1194.9	1135.1	1080.1	1031.2	986.5
25°	1507.4	1455.5	1407.7	1354.7	1296.0	1231.7	1164.7	1098.7	1040.1	990.2	941.4
27.5°	1488.6	1423.8	1363.0	1310.4	1248.4	1190.9	1126.4	1058.7	997.1	946.3	896.2
30°	1471.6	1398.9	1331.9	1272.2	1213.5	1159.0	1097.7	1031.7	968.4	916.0	865.1
32.5°	1450.4	1373.1	1299.5	1230.6	1174.0	1119.9	1064.5	1001.4	939.7	885.6	833.9
35°	1423.8	1325.1	1245.2	1171.9	1109.1	1056.7	1006.8	955.9	894.1	838.1	787.7
37.5°	1388.9	1276.9	1184.4	1104.7	1038.4	985.7	946.4	899.9	843.5	789.8	743.0
40°	1367.7	1242.0	1140.8	1061.9	992.3	936.7	899.9	860.4	809.0	758.6	711.9
42.5°	1339.5	1210.1	1096.8	1014.5	944.5	891.0	853.7	819.3	776.2	728.7	678.7
45°	1284.1	1148.1	1029.2	940.9	870.3	817.8	783.0	752.4	719.7	676.1	632.4
47.5°	1212.0	1083.4	958.9	862.6	793.4	744.7	711.0	686.8	663.4	626.3	583.9
50°	1154.3	1030.2	908.7	815.2	741.5	695.3	663.6	644.4	623.1	589.3	554.0
52.5°	1086.2	975.4	856.3	760.8	691.2	647.9	617.5	598.3	580.7	553.2	519.6
55°	978.8	881.7	772.6	685.9	622.1	578.4	549.4	531.2	520.8	497.4	471.0
57.5°	854.9	785.3	689.1	605.5	549.1	506.0	484.7	469.2	457.5	440.9	422.3
60°	768.5	719.7	633.5	554.0	502.1	461.1	441.9	428.9	418.0	404.0	389.4
62.5°	680.8	645.3	570.3	502.1	454.3	420.0	402.0	390.3	377.7	368.3	354.1
65°	563.4	531.7	479.8	426.3	382.2	354.6	341.7	331.3	323.5	313.1	303.2
67.5°	438.2	425.4	389.5	352.7	321.0	296.5	285.3	278.0	268.7	262.4	255.7
70°	361.4	355.2	329.7	305.3	275.7	259.1	248.7	245.6	234.2	228.0	223.3
72.5°	293.3	290.4	275.7	258.8	237.9	223.4	213.8	210.3	203.0	198.0	195.0
75°	200.9	202.0	199.4	188.5	180.7	171.4	163.0	161.0	155.8	151.6	149.0
77.5°	127.1	132.4	132.6	132.1	129.0	123.3	119.8	118.3	113.2	111.6	111.0
80°	87.2	92.9	98.1	97.6	96.6	95.0	92.4	90.9	88.3	86.7	85.7
82.5°	58.2	63.5	67.8	70.6	70.4	68.9	67.1	66.4	65.8	64.7	64.5
85°	27.5	28.6	30.1	33.8	36.3	36.9	36.3	35.8	34.3	34.8	35.3
87.5°	11.5	11.2	11.4	11.2	10.5	12.3	13.3	13.4	12.9	12.3	11.7
90°	9.6	8.4	7.3	6.0	4.7	3.4	2.1	0.7	2.1	3.4	4.7
92.5°	25.7	24.3	22.8	21.7	20.7	19.8	18.9	18.0	18.9	19.8	20.7
95°	53.9	52.2	50.6	49.6	49.2	48.9	48.6	48.3	48.6	48.9	49.2
97.5°	86.5	84.2	81.9	80.7	80.6	80.4	80.3	80.2	80.3	80.4	80.6
100°	109.3	107.1	105.0	103.9	103.9	103.9	103.9	103.9	103.9	103.9	103.9
102.5°	135.2	134.1	133.0	132.1	131.4	130.8	130.1	129.5	130.1	130.8	131.4
105°	175.4	174.5	173.5	172.6	171.7	170.9	170.1	169.3	170.1	170.9	171.7
107.5°	218.8	218.1	217.3	216.5	215.7	214.9	214.0	213.2	214.0	214.9	215.7
110°	248.4	247.9	247.4	246.8	246.0	245.1	244.3	243.5	244.3	245.1	246.0



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	277.9	277.2	276.6	276.1	275.7	275.2	274.8	274.4	274.8	275.2	275.7
115°	323.7	323.4	323.1	322.6	321.9	321.3	320.6	320.0	320.6	321.3	321.9
117.5°	367.8	367.5	367.2	366.9	366.6	366.3	366.0	365.7	366.0	366.3	366.6
120°	398.3	398.1	398.0	397.5	396.7	395.8	395.0	394.2	395.0	395.8	396.7
122.5°	427.5	427.0	426.6	426.3	426.0	425.7	425.4	425.1	425.4	425.7	426.0
125°	471.8	471.6	471.5	470.9	469.9	468.9	467.9	466.9	467.9	468.9	469.9
127.5°	514.5	514.3	514.1	513.7	513.2	512.6	512.0	511.5	512.0	512.6	513.2
130°	542.7	542.4	542.1	541.5	540.7	539.9	539.0	538.2	539.0	539.9	540.7
132.5°	570.8	570.9	571.0	570.3	569.0	567.6	566.3	564.9	566.3	567.6	569.0
135°	612.1	611.9	611.8	611.2	610.2	609.2	608.2	607.2	608.2	609.2	610.2
137.5°	652.2	651.9	651.5	650.9	649.9	648.9	648.0	647.0	648.0	648.9	649.9
140°	677.5	677.0	676.5	675.9	675.0	674.2	673.4	672.6	673.4	674.2	675.0
142.5°	702.8	702.2	701.5	700.9	700.2	699.5	698.8	698.1	698.8	699.5	700.2
145°	739.9	739.4	738.9	738.3	737.6	737.0	736.3	735.7	736.3	737.0	737.6
147.5°	773.0	772.6	772.2	771.9	771.5	771.1	770.8	770.4	770.8	771.1	771.5
150°	794.5	793.8	793.2	792.9	793.1	793.2	793.4	793.6	793.4	793.2	793.1
152.5°	814.3	814.0	813.7	813.5	813.3	813.0	812.8	812.6	812.8	813.0	813.3
155°	842.2	842.1	841.9	841.8	841.8	841.8	841.8	841.8	841.8	841.8	841.8
157.5°	866.7	866.6	866.4	866.5	866.9	867.2	867.6	868.0	867.6	867.2	866.9
160°	881.6	881.4	881.2	881.4	881.9	882.4	882.9	883.4	882.9	882.4	881.9
162.5°	895.5	895.5	895.4	895.6	896.0	896.3	896.7	897.1	896.7	896.3	896.0
165°	914.2	914.1	913.9	914.0	914.3	914.7	915.0	915.3	915.0	914.7	914.3
167.5°	927.8	927.8	927.8	928.1	928.8	929.4	930.1	930.8	930.1	929.4	928.8
170°	936.1	936.1	936.1	936.4	937.1	937.7	938.4	939.1	938.4	937.7	937.1
172.5°	942.0	942.0	942.0	942.4	943.0	943.7	944.3	945.0	944.3	943.7	943.0
175°	948.7	948.7	948.7	949.0	949.7	950.4	951.0	951.7	951.0	950.4	949.7
177.5°	952.4	952.5	952.7	953.0	953.5	954.0	954.6	955.1	954.6	954.0	953.5
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1243.7	1237.9	1233.7	1225.4	1219.6	1217.1	1212.6	1211.3	1215.9	1212.6	1212.1
5°	1206.7	1191.7	1179.7	1167.8	1154.8	1146.5	1134.0	1132.0	1128.8	1124.2	1123.1
7.5°	1162.4	1142.8	1127.4	1107.7	1090.5	1076.7	1061.1	1053.8	1049.7	1043.7	1035.6
10°	1132.5	1109.1	1088.3	1068.6	1047.3	1030.2	1014.6	1002.7	994.9	987.6	984.5
12.5°	1103.0	1079.2	1052.6	1028.7	1005.0	985.7	968.5	960.7	952.1	943.6	936.3
15°	1057.2	1025.5	996.4	968.9	948.7	927.9	911.3	899.9	886.9	883.2	869.2
17.5°	1008.6	977.5	943.5	914.5	891.0	868.2	849.9	836.9	827.2	813.8	807.3
20°	978.3	941.4	908.2	881.7	855.7	828.7	810.0	799.1	789.8	778.9	773.7
22.5°	945.9	909.8	875.8	844.7	818.3	791.8	778.5	767.1	756.5	746.5	739.6
25°	898.3	862.0	826.1	793.9	766.4	747.2	731.6	718.6	712.9	703.1	695.8
27.5°	851.3	812.6	775.4	743.4	721.8	702.8	690.0	679.7	669.4	660.8	654.5
30°	820.9	781.5	741.0	715.5	692.7	674.5	660.5	650.6	642.8	635.0	630.4
32.5°	790.6	749.9	714.0	686.4	664.8	649.2	634.7	625.3	617.1	608.5	603.0
35°	742.0	700.5	671.4	644.4	623.1	608.6	598.7	585.2	578.4	572.2	566.5
37.5°	696.8	658.2	626.7	603.1	584.6	570.1	557.4	550.1	541.8	536.2	531.4
40°	663.6	628.3	599.7	574.8	561.3	545.2	533.3	523.9	517.7	510.4	505.2
42.5°	633.7	600.9	573.1	550.7	533.9	520.3	508.8	499.4	491.5	486.3	482.0
45°	591.4	558.7	531.7	510.9	495.4	482.4	470.4	465.8	455.4	449.2	447.1
47.5°	547.7	518.4	492.4	473.2	457.3	445.0	433.8	424.2	418.5	412.4	409.1
50°	518.2	490.2	465.8	447.1	431.5	418.0	407.6	401.4	393.6	387.9	383.7
52.5°	488.7	462.8	438.4	420.5	407.0	393.5	381.9	375.6	368.3	364.6	361.7
55°	446.6	419.0	398.3	380.6	366.6	354.1	343.2	337.0	332.3	328.7	327.6
57.5°	398.8	377.0	357.7	341.8	327.2	315.5	305.9	300.0	295.9	295.3	292.2
60°	367.6	347.9	330.2	313.1	300.6	289.7	281.4	274.7	270.5	270.0	269.0
62.5°	336.5	317.6	301.2	286.1	274.9	264.4	256.5	248.9	246.4	243.8	241.6
65°	290.3	273.1	259.6	247.7	235.7	226.9	219.1	214.4	208.7	205.6	199.9
67.5°	244.9	231.6	218.6	208.5	199.2	190.8	184.3	177.4	173.5	171.0	166.9
70°	215.0	204.6	191.6	180.7	173.4	166.7	161.5	153.7	151.1	149.0	146.9
72.5°	186.7	177.6	166.7	157.9	150.6	144.2	138.2	134.6	132.0	129.9	128.7
75°	146.9	138.1	128.8	122.5	117.4	112.2	109.0	106.4	105.4	104.9	102.8
77.5°	107.9	103.2	95.7	90.8	87.3	85.3	82.5	81.1	81.0	78.7	78.0
80°	82.6	80.0	73.7	71.7	69.1	67.0	65.4	62.8	60.2	59.2	57.6
82.5°	61.4	58.8	56.3	53.0	50.8	49.5	48.0	47.0	47.4	45.9	45.2
85°	32.7	30.1	29.1	28.6	27.5	28.6	28.0	27.5	27.0	26.5	27.0
87.5°	11.6	11.8	11.7	12.7	11.7	12.3	12.5	12.3	12.4	12.6	12.3
90°	6.0	7.3	8.4	9.6	10.7	11.9	12.7	13.5	14.4	15.2	15.8
92.5°	21.7	22.8	24.3	25.7	27.1	28.5	29.6	30.7	31.8	32.9	33.6
95°	49.6	50.6	52.2	53.9	55.5	57.2	58.3	59.5	60.6	61.8	62.5
97.5°	80.7	81.9	84.2	86.5	88.7	91.0	92.1	93.2	94.3	95.4	96.0
100°	103.9	105.0	107.1	109.3	111.4	113.6	115.1	116.5	118.0	119.5	120.4
102.5°	132.1	133.0	134.1	135.2	136.2	137.3	139.0	140.6	142.2	143.8	144.8
105°	172.6	173.5	174.5	175.4	176.4	177.4	178.4	179.4	180.4	181.4	182.1
107.5°	216.5	217.3	218.1	218.8	219.6	220.3	220.8	221.3	221.8	222.3	222.5
110°	246.8	247.4	247.9	248.4	248.9	249.4	249.9	250.4	250.9	251.4	251.6



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	276.1	276.6	277.2	277.9	278.5	279.1	279.4	279.6	279.8	280.0	280.0
115°	322.6	323.1	323.4	323.7	324.1	324.4	324.2	324.1	323.9	323.7	323.6
117.5°	366.9	367.2	367.5	367.8	368.1	368.4	368.5	368.6	368.7	368.9	368.6
120°	397.5	398.0	398.1	398.3	398.5	398.6	398.6	398.6	398.6	398.6	398.3
122.5°	426.3	426.6	427.0	427.5	427.9	428.3	428.2	428.1	427.9	427.8	427.5
125°	470.9	471.5	471.6	471.8	472.0	472.1	471.8	471.5	471.1	470.8	470.6
127.5°	513.7	514.1	514.3	514.5	514.7	514.9	514.7	514.6	514.4	514.2	514.0
130°	541.5	542.1	542.4	542.7	543.1	543.4	543.2	543.1	542.9	542.7	542.5
132.5°	570.3	571.0	570.9	570.8	570.8	570.7	570.6	570.4	570.2	570.1	569.7
135°	611.2	611.8	611.9	612.1	612.3	612.4	612.4	612.4	612.4	612.4	612.1
137.5°	650.9	651.5	651.9	652.2	652.6	653.0	653.2	653.4	653.6	653.8	653.4
140°	675.9	676.5	677.0	677.5	678.0	678.5	678.8	679.2	679.5	679.8	679.6
142.5°	700.9	701.5	702.2	702.8	703.4	704.0	704.2	704.4	704.6	704.8	704.5
145°	738.3	738.9	739.4	739.9	740.4	740.9	740.9	740.9	740.9	740.9	740.6
147.5°	771.9	772.2	772.6	773.0	773.4	773.8	774.2	774.6	775.0	775.4	775.0
150°	792.9	793.2	793.8	794.5	795.1	795.8	795.8	795.8	795.8	795.8	795.6
152.5°	813.5	813.7	814.0	814.3	814.5	814.8	815.2	815.6	816.0	816.4	816.3
155°	841.8	841.9	842.1	842.2	842.4	842.6	843.2	843.9	844.5	845.2	845.1
157.5°	866.5	866.4	866.6	866.7	866.9	867.1	867.7	868.4	869.0	869.7	869.5
160°	881.4	881.2	881.4	881.6	881.7	881.9	882.6	883.2	883.9	884.5	884.5
162.5°	895.6	895.4	895.5	895.5	895.5	895.6	896.4	897.2	897.9	898.7	898.7
165°	914.0	913.9	914.1	914.2	914.4	914.6	915.2	915.9	916.6	917.2	917.0
167.5°	928.1	927.8	927.8	927.8	927.8	927.8	928.8	929.8	930.8	931.7	931.7
170°	936.4	936.1	936.1	936.1	936.1	936.1	937.1	938.1	939.1	940.1	940.0
172.5°	942.4	942.0	942.0	942.0	942.0	942.0	943.0	944.0	945.0	946.0	946.0
175°	949.0	948.7	948.7	948.7	948.7	948.7	949.7	950.7	951.7	952.7	952.6
177.5°	953.0	952.7	952.5	952.4	952.3	952.1	952.9	953.7	954.5	955.3	955.2
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1211.7	1207.2	1205.9	1207.6	1205.9	1207.2	1211.7	1212.1	1212.6	1215.9	1211.3
5°	1117.9	1112.8	1115.3	1114.3	1115.3	1112.8	1117.9	1123.1	1124.2	1128.8	1132.0
7.5°	1035.5	1029.0	1022.2	1024.4	1022.2	1029.0	1035.5	1035.6	1043.7	1049.7	1053.8
10°	977.7	972.6	969.4	972.0	969.4	972.6	977.7	984.5	987.6	994.9	1002.7
12.5°	929.1	926.0	923.3	922.2	923.3	926.0	929.1	936.3	943.6	952.1	960.7
15°	863.0	856.8	854.2	847.4	854.2	856.8	863.0	869.2	883.2	886.9	899.9
17.5°	802.0	800.0	793.2	790.3	793.2	800.0	802.0	807.3	813.8	827.2	836.9
20°	765.9	763.8	757.1	761.2	757.1	763.8	765.9	773.7	778.9	789.8	799.1
22.5°	736.0	731.4	729.2	728.0	729.2	731.4	736.0	739.6	746.5	756.5	767.1
25°	693.7	687.0	684.4	681.3	684.4	687.0	693.7	695.8	703.1	712.9	718.6
27.5°	651.6	647.9	644.5	643.7	644.5	647.9	651.6	654.5	660.8	669.4	679.7
30°	624.1	620.5	617.9	617.9	617.9	620.5	624.1	630.4	635.0	642.8	650.6
32.5°	599.6	596.8	594.2	593.8	594.2	596.8	599.6	603.0	608.5	617.1	625.3
35°	563.9	559.8	558.7	555.6	558.7	559.8	563.9	566.5	572.2	578.4	585.2
37.5°	526.8	523.4	523.3	523.0	523.3	523.4	526.8	531.4	536.2	541.8	550.1
40°	503.2	500.6	500.0	496.4	500.0	500.6	503.2	505.2	510.4	517.7	523.9
42.5°	477.8	476.5	474.7	473.1	474.7	476.5	477.8	482.0	486.3	491.5	499.4
45°	443.4	439.8	439.8	437.2	439.8	439.8	443.4	447.1	449.2	455.4	465.8
47.5°	407.9	405.1	405.4	402.7	405.4	405.1	407.9	409.1	412.4	418.5	424.2
50°	384.2	382.7	382.2	381.1	382.2	382.7	384.2	383.7	387.9	393.6	401.4
52.5°	360.6	359.8	361.8	359.5	361.8	359.8	360.6	361.7	364.6	368.3	375.6
55°	328.7	327.1	330.2	327.1	330.2	327.1	328.7	327.6	328.7	332.3	337.0
57.5°	292.0	290.6	293.4	291.8	293.4	290.6	292.0	292.2	295.3	295.9	300.0
60°	267.9	264.8	266.4	266.9	266.4	264.8	267.9	269.0	270.0	270.5	274.7
62.5°	239.3	237.4	238.5	236.2	238.5	237.4	239.3	241.6	243.8	246.4	248.9
65°	198.9	197.3	195.2	194.2	195.2	197.3	198.9	199.9	205.6	208.7	214.4
67.5°	167.1	163.4	163.3	164.1	163.3	163.4	167.1	166.9	171.0	173.5	177.4
70°	143.8	143.8	143.3	143.3	143.3	143.8	143.8	146.9	149.0	151.1	153.7
72.5°	127.6	127.2	126.3	125.9	126.3	127.2	127.6	128.7	129.9	132.0	134.6
75°	102.8	103.3	102.3	101.8	102.3	103.3	102.8	102.8	104.9	105.4	106.4
77.5°	75.9	73.7	74.9	73.7	74.9	73.7	75.9	78.0	78.7	81.0	81.1
80°	57.6	57.1	58.7	57.1	58.7	57.1	57.6	57.6	59.2	60.2	62.8
82.5°	45.6	45.1	45.8	44.7	45.8	45.1	45.6	45.2	45.9	47.4	47.0
85°	27.5	27.0	26.5	27.0	26.5	27.0	27.5	27.0	26.5	27.0	27.5
87.5°	12.8	12.5	12.6	12.7	12.6	12.5	12.8	12.3	12.6	12.4	12.3
90°	16.3	16.8	17.3	17.8	17.3	16.8	16.3	15.8	15.2	14.4	13.5
92.5°	34.0	34.3	34.7	35.0	34.7	34.3	34.0	33.6	32.9	31.8	30.7
95°	62.9	63.2	63.5	63.8	63.5	63.2	62.9	62.5	61.8	60.6	59.5
97.5°	96.2	96.4	96.6	96.8	96.6	96.4	96.2	96.0	95.4	94.3	93.2
100°	120.8	121.1	121.4	121.7	121.4	121.1	120.8	120.4	119.5	118.0	116.5
102.5°	145.3	145.8	146.2	146.7	146.2	145.8	145.3	144.8	143.8	142.2	140.6
105°	182.6	183.1	183.6	184.1	183.6	183.1	182.6	182.1	181.4	180.4	179.4
107.5°	222.5	222.5	222.4	222.4	222.4	222.5	222.5	222.5	222.3	221.8	221.3
110°	251.4	251.2	251.1	250.9	251.1	251.2	251.4	251.6	251.4	250.9	250.4



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	279.7	279.4	279.1	278.8	279.1	279.4	279.7	280.0	280.0	279.8	279.6
115°	323.4	323.3	323.1	322.9	323.1	323.3	323.4	323.6	323.7	323.9	324.1
117.5°	368.0	367.3	366.6	366.0	366.6	367.3	368.0	368.6	368.9	368.7	368.6
120°	397.7	397.0	396.3	395.7	396.3	397.0	397.7	398.3	398.6	398.6	398.6
122.5°	426.9	426.4	425.9	425.4	425.9	426.4	426.9	427.5	427.8	427.9	428.1
125°	470.4	470.2	470.1	469.9	470.1	470.2	470.4	470.6	470.8	471.1	471.5
127.5°	513.7	513.3	513.0	512.7	513.0	513.3	513.7	514.0	514.2	514.4	514.6
130°	542.2	541.8	541.5	541.2	541.5	541.8	542.2	542.5	542.7	542.9	543.1
132.5°	569.3	568.8	568.4	567.9	568.4	568.8	569.3	569.7	570.1	570.2	570.4
135°	611.4	610.8	610.1	609.5	610.1	610.8	611.4	612.1	612.4	612.4	612.4
137.5°	652.6	651.8	651.0	650.1	651.0	651.8	652.6	653.4	653.8	653.6	653.4
140°	678.8	677.9	677.1	676.3	677.1	677.9	678.8	679.6	679.8	679.5	679.2
142.5°	703.7	702.9	702.0	701.2	702.0	702.9	703.7	704.5	704.8	704.6	704.4
145°	740.1	739.6	739.1	738.6	739.1	739.6	740.1	740.6	740.9	740.9	740.9
147.5°	773.9	772.8	771.7	770.6	771.7	772.8	773.9	775.0	775.4	775.0	774.6
150°	795.3	795.0	794.6	794.3	794.6	795.0	795.3	795.6	795.8	795.8	795.8
152.5°	815.7	815.1	814.5	813.9	814.5	815.1	815.7	816.3	816.4	816.0	815.6
155°	844.3	843.5	842.6	841.8	842.6	843.5	844.3	845.1	845.2	844.5	843.9
157.5°	868.4	867.3	866.2	865.1	866.2	867.3	868.4	869.5	869.7	869.0	868.4
160°	883.6	882.8	882.0	881.2	882.0	882.8	883.6	884.5	884.5	883.9	883.2
162.5°	897.7	896.7	895.8	894.8	895.8	896.7	897.7	898.7	898.7	897.9	897.2
165°	916.1	915.1	914.1	913.1	914.1	915.1	916.1	917.0	917.2	916.6	915.9
167.5°	930.7	929.7	928.7	927.6	928.7	929.7	930.7	931.7	931.7	930.8	929.8
170°	938.8	937.7	936.5	935.4	936.5	937.7	938.8	940.0	940.1	939.1	938.1
172.5°	945.0	943.9	942.9	941.9	942.9	943.9	945.0	946.0	946.0	945.0	944.0
175°	951.4	950.3	949.1	948.0	949.1	950.3	951.4	952.6	952.7	951.7	950.7
177.5°	954.3	953.4	952.5	951.5	952.5	953.4	954.3	955.2	955.3	954.5	953.7
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1212.6	1217.1	1219.6	1225.4	1233.7	1237.9	1243.7	1247.9	1253.7	1260.7	1266.6
5°	1134.0	1146.5	1154.8	1167.8	1179.7	1191.7	1206.7	1217.6	1232.2	1248.8	1261.8
7.5°	1061.1	1076.7	1090.5	1107.7	1127.4	1142.8	1162.4	1182.4	1205.2	1228.8	1251.0
10°	1014.6	1030.2	1047.3	1068.6	1088.3	1109.1	1132.5	1155.8	1184.4	1210.9	1241.0
12.5°	968.5	985.7	1005.0	1028.7	1052.6	1079.2	1103.0	1129.3	1159.9	1194.3	1226.5
15°	911.3	927.9	948.7	968.9	996.4	1025.5	1057.2	1092.0	1126.3	1164.7	1204.7
17.5°	849.9	868.2	891.0	914.5	943.5	977.5	1008.6	1046.7	1085.2	1130.0	1177.0
20°	810.0	828.7	855.7	881.7	908.2	941.4	978.3	1017.2	1058.2	1105.5	1157.9
22.5°	778.5	791.8	818.3	844.7	875.8	909.8	945.9	986.5	1031.2	1080.1	1135.1
25°	731.6	747.2	766.4	793.9	826.1	862.0	898.3	941.4	990.2	1040.1	1098.7
27.5°	690.0	702.8	721.8	743.4	775.4	812.6	851.3	896.2	946.3	997.1	1058.7
30°	660.5	674.5	692.7	715.5	741.0	781.5	820.9	865.1	916.0	968.4	1031.7
32.5°	634.7	649.2	664.8	686.4	714.0	749.9	790.6	833.9	885.6	939.7	1001.4
35°	598.7	608.6	623.1	644.4	671.4	700.5	742.0	787.7	838.1	894.1	955.9
37.5°	557.4	570.1	584.6	603.1	626.7	658.2	696.8	743.0	789.8	843.5	899.9
40°	533.3	545.2	561.3	574.8	599.7	628.3	663.6	711.9	758.6	809.0	860.4
42.5°	508.8	520.3	533.9	550.7	573.1	600.9	633.7	678.7	728.7	776.2	819.3
45°	470.4	482.4	495.4	510.9	531.7	558.7	591.4	632.4	676.1	719.7	752.4
47.5°	433.8	445.0	457.3	473.2	492.4	518.4	547.7	583.9	626.3	663.4	686.8
50°	407.6	418.0	431.5	447.1	465.8	490.2	518.2	554.0	589.3	623.1	644.4
52.5°	381.9	393.5	407.0	420.5	438.4	462.8	488.7	519.6	553.2	580.7	598.3
55°	343.2	354.1	366.6	380.6	398.3	419.0	446.6	471.0	497.4	520.8	531.2
57.5°	305.9	315.5	327.2	341.8	357.7	377.0	398.8	422.3	440.9	457.5	469.2
60°	281.4	289.7	300.6	313.1	330.2	347.9	367.6	389.4	404.0	418.0	428.9
62.5°	256.5	264.4	274.9	286.1	301.2	317.6	336.5	354.1	368.3	377.7	390.3
65°	219.1	226.9	235.7	247.7	259.6	273.1	290.3	303.2	313.1	323.5	331.3
67.5°	184.3	190.8	199.2	208.5	218.6	231.6	244.9	255.7	262.4	268.7	278.0
70°	161.5	166.7	173.4	180.7	191.6	204.6	215.0	223.3	228.0	234.2	245.6
72.5°	138.2	144.2	150.6	157.9	166.7	177.6	186.7	195.0	198.0	203.0	210.3
75°	109.0	112.2	117.4	122.5	128.8	138.1	146.9	149.0	151.6	155.8	161.0
77.5°	82.5	85.3	87.3	90.8	95.7	103.2	107.9	111.0	111.6	113.2	118.3
80°	65.4	67.0	69.1	71.7	73.7	80.0	82.6	85.7	86.7	88.3	90.9
82.5°	48.0	49.5	50.8	53.0	56.3	58.8	61.4	64.5	64.7	65.8	66.4
85°	28.0	28.6	27.5	28.6	29.1	30.1	32.7	35.3	34.8	34.3	35.8
87.5°	12.5	12.3	11.7	12.7	11.7	11.8	11.6	11.7	12.3	12.9	13.4
90°	12.7	11.9	10.7	9.6	8.4	7.3	6.0	4.7	3.4	2.1	0.7
92.5°	29.6	28.5	27.1	25.7	24.3	22.8	21.7	20.7	19.8	18.9	18.0
95°	58.3	57.2	55.5	53.9	52.2	50.6	49.6	49.2	48.9	48.6	48.3
97.5°	92.1	91.0	88.7	86.5	84.2	81.9	80.7	80.6	80.4	80.3	80.2
100°	115.1	113.6	111.4	109.3	107.1	105.0	103.9	103.9	103.9	103.9	103.9
102.5°	139.0	137.3	136.2	135.2	134.1	133.0	132.1	131.4	130.8	130.1	129.5
105°	178.4	177.4	176.4	175.4	174.5	173.5	172.6	171.7	170.9	170.1	169.3
107.5°	220.8	220.3	219.6	218.8	218.1	217.3	216.5	215.7	214.9	214.0	213.2
110°	249.9	249.4	248.9	248.4	247.9	247.4	246.8	246.0	245.1	244.3	243.5



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	279.4	279.1	278.5	277.9	277.2	276.6	276.1	275.7	275.2	274.8	274.4
115°	324.2	324.4	324.1	323.7	323.4	323.1	322.6	321.9	321.3	320.6	320.0
117.5°	368.5	368.4	368.1	367.8	367.5	367.2	366.9	366.6	366.3	366.0	365.7
120°	398.6	398.6	398.5	398.3	398.1	398.0	397.5	396.7	395.8	395.0	394.2
122.5°	428.2	428.3	427.9	427.5	427.0	426.6	426.3	426.0	425.7	425.4	425.1
125°	471.8	472.1	472.0	471.8	471.6	471.5	470.9	469.9	468.9	467.9	466.9
127.5°	514.7	514.9	514.7	514.5	514.3	514.1	513.7	513.2	512.6	512.0	511.5
130°	543.2	543.4	543.1	542.7	542.4	542.1	541.5	540.7	539.9	539.0	538.2
132.5°	570.6	570.7	570.8	570.8	570.9	571.0	570.3	569.0	567.6	566.3	564.9
135°	612.4	612.4	612.3	612.1	611.9	611.8	611.2	610.2	609.2	608.2	607.2
137.5°	653.2	653.0	652.6	652.2	651.9	651.5	650.9	649.9	648.9	648.0	647.0
140°	678.8	678.5	678.0	677.5	677.0	676.5	675.9	675.0	674.2	673.4	672.6
142.5°	704.2	704.0	703.4	702.8	702.2	701.5	700.9	700.2	699.5	698.8	698.1
145°	740.9	740.9	740.4	739.9	739.4	738.9	738.3	737.6	737.0	736.3	735.7
147.5°	774.2	773.8	773.4	773.0	772.6	772.2	771.9	771.5	771.1	770.8	770.4
150°	795.8	795.8	795.1	794.5	793.8	793.2	792.9	793.1	793.2	793.4	793.6
152.5°	815.2	814.8	814.5	814.3	814.0	813.7	813.5	813.3	813.0	812.8	812.6
155°	843.2	842.6	842.4	842.2	842.1	841.9	841.8	841.8	841.8	841.8	841.8
157.5°	867.7	867.1	866.9	866.7	866.6	866.4	866.5	866.9	867.2	867.6	868.0
160°	882.6	881.9	881.7	881.6	881.4	881.2	881.4	881.9	882.4	882.9	883.4
162.5°	896.4	895.6	895.5	895.5	895.5	895.4	895.6	896.0	896.3	896.7	897.1
165°	915.2	914.6	914.4	914.2	914.1	913.9	914.0	914.3	914.7	915.0	915.3
167.5°	928.8	927.8	927.8	927.8	927.8	927.8	928.1	928.8	929.4	930.1	930.8
170°	937.1	936.1	936.1	936.1	936.1	936.1	936.4	937.1	937.7	938.4	939.1
172.5°	943.0	942.0	942.0	942.0	942.0	942.0	942.4	943.0	943.7	944.3	945.0
175°	949.7	948.7	948.7	948.7	948.7	948.7	949.0	949.7	950.4	951.0	951.7
177.5°	952.9	952.1	952.3	952.4	952.5	952.7	953.0	953.5	954.0	954.6	955.1
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1271.1	1274.9	1280.3	1286.5	1291.5	1296.9	1299.8	1299.8	1302.3	1307.7	1314.7
5°	1274.8	1288.3	1301.2	1317.9	1330.8	1345.9	1357.3	1368.2	1378.1	1390.5	1403.5
7.5°	1273.7	1296.1	1319.5	1345.7	1374.6	1397.5	1421.1	1439.6	1457.8	1481.7	1500.5
10°	1269.6	1298.6	1330.3	1363.5	1399.9	1431.6	1460.1	1486.1	1511.0	1537.0	1560.3
12.5°	1262.1	1299.1	1337.8	1377.7	1423.6	1459.8	1496.7	1524.3	1553.4	1581.8	1610.6
15°	1250.9	1294.5	1341.2	1396.8	1452.9	1493.4	1529.7	1565.5	1592.5	1624.7	1652.3
17.5°	1227.7	1283.9	1342.7	1403.4	1457.3	1504.4	1542.5	1576.5	1605.3	1640.7	1678.1
20°	1214.0	1274.8	1336.0	1400.9	1452.3	1500.6	1537.5	1572.8	1608.6	1654.8	1700.5
22.5°	1194.9	1259.8	1324.8	1386.4	1440.7	1487.3	1525.4	1568.7	1615.7	1668.1	1723.4
25°	1164.7	1231.7	1296.0	1354.7	1407.7	1455.5	1507.4	1565.5	1622.7	1691.7	1771.2
27.5°	1126.4	1190.9	1248.4	1310.4	1363.0	1423.8	1488.6	1551.6	1634.0	1729.0	1828.2
30°	1097.7	1159.0	1213.5	1272.2	1331.9	1398.9	1471.6	1545.8	1643.9	1755.6	1873.5
32.5°	1064.5	1119.9	1174.0	1230.6	1299.5	1373.1	1450.4	1541.2	1658.5	1785.5	1907.5
35°	1006.8	1056.7	1109.1	1171.9	1245.2	1325.1	1423.8	1534.4	1676.1	1812.7	1922.3
37.5°	946.4	985.7	1038.4	1104.7	1184.4	1276.9	1388.9	1523.3	1668.9	1791.4	1838.0
40°	899.9	936.7	992.3	1061.9	1140.8	1242.0	1367.7	1505.8	1652.3	1737.4	1733.8
42.5°	853.7	891.0	944.5	1014.5	1096.8	1210.1	1339.5	1483.0	1606.6	1639.0	1571.4
45°	783.0	817.8	870.3	940.9	1029.2	1148.1	1284.1	1421.7	1500.6	1448.2	1314.2
47.5°	711.0	744.7	793.4	862.6	958.9	1083.4	1212.0	1324.9	1336.0	1223.4	1062.7
50°	663.6	695.3	741.5	815.2	908.7	1030.2	1154.3	1243.1	1215.6	1078.0	912.3
52.5°	617.5	647.9	691.2	760.8	856.3	975.4	1086.2	1155.8	1092.2	945.9	796.8
55°	549.4	578.4	622.1	685.9	772.6	881.7	978.8	1004.2	910.8	763.3	642.8
57.5°	484.7	506.0	549.1	605.5	689.1	785.3	854.9	850.3	747.2	614.4	528.0
60°	441.9	461.1	502.1	554.0	633.5	719.7	768.5	747.7	643.3	533.8	450.7
62.5°	402.0	420.0	454.3	502.1	570.3	645.3	680.8	652.2	553.6	457.4	391.3
65°	341.7	354.6	382.2	426.3	479.8	531.7	563.4	521.3	434.1	361.4	311.5
67.5°	285.3	296.5	321.0	352.7	389.5	425.4	438.2	398.8	331.0	282.0	246.9
70°	248.7	259.1	275.7	305.3	329.7	355.2	361.4	326.1	269.5	232.1	210.3
72.5°	213.8	223.4	237.9	258.8	275.7	290.4	293.3	260.5	217.1	191.4	174.6
75°	163.0	171.4	180.7	188.5	199.4	202.0	200.9	175.5	152.1	135.0	125.7
77.5°	119.8	123.3	129.0	132.1	132.6	132.4	127.1	111.0	99.0	91.9	88.1
80°	92.4	95.0	96.6	97.6	98.1	92.9	87.2	77.4	73.2	69.1	64.4
82.5°	67.1	68.9	70.4	70.6	67.8	63.5	58.2	53.3	50.4	48.3	46.5
85°	36.3	36.9	36.3	33.8	30.1	28.6	27.5	26.5	26.0	25.4	25.4
87.5°	13.3	12.3	10.5	11.2	11.4	11.2	11.5	11.3	11.1	11.3	11.4
90°	2.1	3.4	4.7	6.0	7.3	8.4	9.6	10.7	11.9	12.7	13.5
92.5°	18.9	19.8	20.7	21.7	22.8	24.3	25.7	27.1	28.5	29.6	30.7
95°	48.6	48.9	49.2	49.6	50.6	52.2	53.9	55.5	57.2	58.3	59.5
97.5°	80.3	80.4	80.6	80.7	81.9	84.2	86.5	88.7	91.0	92.1	93.2
100°	103.9	103.9	103.9	103.9	105.0	107.1	109.3	111.4	113.6	115.1	116.5
102.5°	130.1	130.8	131.4	132.1	133.0	134.1	135.2	136.2	137.3	139.0	140.6
105°	170.1	170.9	171.7	172.6	173.5	174.5	175.4	176.4	177.4	178.4	179.4
107.5°	214.0	214.9	215.7	216.5	217.3	218.1	218.8	219.6	220.3	220.8	221.3
110°	244.3	245.1	246.0	246.8	247.4	247.9	248.4	248.9	249.4	249.9	250.4



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	274.8	275.2	275.7	276.1	276.6	277.2	277.9	278.5	279.1	279.4	279.6
115°	320.6	321.3	321.9	322.6	323.1	323.4	323.7	324.1	324.4	324.2	324.1
117.5°	366.0	366.3	366.6	366.9	367.2	367.5	367.8	368.1	368.4	368.5	368.6
120°	395.0	395.8	396.7	397.5	398.0	398.1	398.3	398.5	398.6	398.6	398.6
122.5°	425.4	425.7	426.0	426.3	426.6	427.0	427.5	427.9	428.3	428.2	428.1
125°	467.9	468.9	469.9	470.9	471.5	471.6	471.8	472.0	472.1	471.8	471.5
127.5°	512.0	512.6	513.2	513.7	514.1	514.3	514.5	514.7	514.9	514.7	514.6
130°	539.0	539.9	540.7	541.5	542.1	542.4	542.7	543.1	543.4	543.2	543.1
132.5°	566.3	567.6	569.0	570.3	571.0	570.9	570.8	570.8	570.7	570.6	570.4
135°	608.2	609.2	610.2	611.2	611.8	611.9	612.1	612.3	612.4	612.4	612.4
137.5°	648.0	648.9	649.9	650.9	651.5	651.9	652.2	652.6	653.0	653.2	653.4
140°	673.4	674.2	675.0	675.9	676.5	677.0	677.5	678.0	678.5	678.8	679.2
142.5°	698.8	699.5	700.2	700.9	701.5	702.2	702.8	703.4	704.0	704.2	704.4
145°	736.3	737.0	737.6	738.3	738.9	739.4	739.9	740.4	740.9	740.9	740.9
147.5°	770.8	771.1	771.5	771.9	772.2	772.6	773.0	773.4	773.8	774.2	774.6
150°	793.4	793.2	793.1	792.9	793.2	793.8	794.5	795.1	795.8	795.8	795.8
152.5°	812.8	813.0	813.3	813.5	813.7	814.0	814.3	814.5	814.8	815.2	815.6
155°	841.8	841.8	841.8	841.8	841.9	842.1	842.2	842.4	842.6	843.2	843.9
157.5°	867.6	867.2	866.9	866.5	866.4	866.6	866.7	866.9	867.1	867.7	868.4
160°	882.9	882.4	881.9	881.4	881.2	881.4	881.6	881.7	881.9	882.6	883.2
162.5°	896.7	896.3	896.0	895.6	895.4	895.5	895.5	895.5	895.6	896.4	897.2
165°	915.0	914.7	914.3	914.0	913.9	914.1	914.2	914.4	914.6	915.2	915.9
167.5°	930.1	929.4	928.8	928.1	927.8	927.8	927.8	927.8	927.8	928.8	929.8
170°	938.4	937.7	937.1	936.4	936.1	936.1	936.1	936.1	936.1	937.1	938.1
172.5°	944.3	943.7	943.0	942.4	942.0	942.0	942.0	942.0	942.0	943.0	944.0
175°	951.0	950.4	949.7	949.0	948.7	948.7	948.7	948.7	948.7	949.7	950.7
177.5°	954.6	954.0	953.5	953.0	952.7	952.5	952.4	952.3	952.1	952.9	953.7
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9	1264.9
2.5°	1320.1	1320.1	1327.2	1326.8	1331.4	1329.7	1330.5
5°	1419.1	1427.9	1435.7	1440.9	1448.7	1450.8	1449.7
7.5°	1521.7	1541.3	1550.9	1564.0	1566.4	1573.2	1572.5
10°	1585.3	1604.5	1619.0	1630.4	1636.2	1643.4	1643.9
12.5°	1635.1	1651.4	1664.3	1674.9	1681.8	1684.1	1685.5
15°	1674.1	1692.2	1707.3	1722.3	1731.2	1737.9	1741.6
17.5°	1713.3	1741.4	1767.9	1788.4	1800.7	1811.0	1810.9
20°	1743.6	1775.8	1809.1	1832.4	1856.3	1866.7	1868.3
22.5°	1776.0	1825.3	1868.1	1904.3	1935.7	1946.5	1950.5
25°	1843.3	1907.7	1973.7	2024.6	2060.9	2082.2	2085.3
27.5°	1924.6	2011.8	2081.2	2128.1	2158.3	2174.1	2177.5
30°	1982.0	2062.5	2124.8	2160.1	2174.1	2176.2	2168.4
32.5°	2007.7	2067.9	2092.8	2090.7	2063.2	2044.9	2037.9
35°	1976.3	1963.8	1903.0	1830.4	1774.8	1739.5	1730.1
37.5°	1798.5	1691.0	1579.2	1469.4	1410.9	1381.2	1330.1
40°	1623.2	1470.0	1353.7	1261.3	1195.3	1142.3	1129.9
42.5°	1425.4	1267.3	1151.0	1071.8	1019.2	982.8	967.0
45°	1145.5	1009.4	913.4	852.6	812.1	785.6	773.7
47.5°	916.2	810.9	740.9	695.9	665.1	642.0	635.6
50°	790.3	706.2	647.0	609.1	585.7	568.1	560.8
52.5°	686.4	618.5	573.0	541.8	519.7	508.7	502.6
55°	566.5	507.8	475.1	450.2	437.7	428.9	424.7
57.5°	463.3	420.9	397.0	379.8	368.3	362.6	360.6
60°	405.5	372.3	350.5	337.0	329.2	321.9	319.9
62.5°	354.4	328.3	311.4	299.6	291.8	288.7	287.5
65°	285.6	268.5	256.0	248.7	242.5	241.5	240.9
67.5°	227.0	216.9	210.4	202.8	200.6	197.0	196.3
70°	194.2	187.4	179.7	177.1	174.5	170.8	171.4
72.5°	164.7	158.0	152.7	149.2	148.3	146.7	148.1
75°	120.5	118.4	116.3	113.7	112.7	112.7	112.2
77.5°	86.0	84.2	81.9	80.4	80.1	77.9	78.7
80°	62.3	59.7	58.7	59.2	57.6	57.1	57.1
82.5°	46.1	45.2	44.1	44.2	43.9	43.4	43.8
85°	25.4	24.9	24.9	24.4	24.4	23.9	23.9
87.5°	12.0	12.6	11.9	11.6	11.7	12.2	12.7
90°	14.4	15.2	15.8	16.3	16.8	17.3	17.8
92.5°	31.8	32.9	33.6	34.0	34.3	34.7	35.0
95°	60.6	61.8	62.5	62.9	63.2	63.5	63.8
97.5°	94.3	95.4	96.0	96.2	96.4	96.6	96.8
100°	118.0	119.5	120.4	120.8	121.1	121.4	121.7
102.5°	142.2	143.8	144.8	145.3	145.8	146.2	146.7
105°	180.4	181.4	182.1	182.6	183.1	183.6	184.1
107.5°	221.8	222.3	222.5	222.5	222.5	222.4	222.4
110°	250.9	251.4	251.6	251.4	251.2	251.1	250.9



TEST NUMBER: P333685

CATALOG NUMBER: S125RDIW-S850D770U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	279.8	280.0	280.0	279.7	279.4	279.1	278.8
115°	323.9	323.7	323.6	323.4	323.3	323.1	322.9
117.5°	368.7	368.9	368.6	368.0	367.3	366.6	366.0
120°	398.6	398.6	398.3	397.7	397.0	396.3	395.7
122.5°	427.9	427.8	427.5	426.9	426.4	425.9	425.4
125°	471.1	470.8	470.6	470.4	470.2	470.1	469.9
127.5°	514.4	514.2	514.0	513.7	513.3	513.0	512.7
130°	542.9	542.7	542.5	542.2	541.8	541.5	541.2
132.5°	570.2	570.1	569.7	569.3	568.8	568.4	567.9
135°	612.4	612.4	612.1	611.4	610.8	610.1	609.5
137.5°	653.6	653.8	653.4	652.6	651.8	651.0	650.1
140°	679.5	679.8	679.6	678.8	677.9	677.1	676.3
142.5°	704.6	704.8	704.5	703.7	702.9	702.0	701.2
145°	740.9	740.9	740.6	740.1	739.6	739.1	738.6
147.5°	775.0	775.4	775.0	773.9	772.8	771.7	770.6
150°	795.8	795.8	795.6	795.3	795.0	794.6	794.3
152.5°	816.0	816.4	816.3	815.7	815.1	814.5	813.9
155°	844.5	845.2	845.1	844.3	843.5	842.6	841.8
157.5°	869.0	869.7	869.5	868.4	867.3	866.2	865.1
160°	883.9	884.5	884.5	883.6	882.8	882.0	881.2
162.5°	897.9	898.7	898.7	897.7	896.7	895.8	894.8
165°	916.6	917.2	917.0	916.1	915.1	914.1	913.1
167.5°	930.8	931.7	931.7	930.7	929.7	928.7	927.6
170°	939.1	940.1	940.0	938.8	937.7	936.5	935.4
172.5°	945.0	946.0	946.0	945.0	943.9	942.9	941.9
175°	951.7	952.7	952.6	951.4	950.3	949.1	948.0
177.5°	954.5	955.3	955.2	954.3	953.4	952.5	951.5
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9

(END OF REPORT)