

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333478-935

Luminaire Tested: **S125DIW-S1270D1340U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333478-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1340U935-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9083.2 lumens
Efficiency: N/A
Efficacy: 119.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot



51% Up

49% Dn



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49				49
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42				42
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	44	42	40	35				35
3	82	72	65	59	75	67	61	55	57	52	48	47	44	41	39	36	34	30				30
4	75	64	56	50	69	59	52	47	51	45	41	42	38	35	35	32	30	26				26
5	69	57	49	43	63	53	46	41	45	40	36	38	34	31	31	28	26	23				23
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20				20
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				16
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10213	10213	10213	10213
5°	11826	10247	8972	10247
10°	13759	10194	7861	10194
15°	15230	10120	7252	10120
20°	17049	10001	6763	10001
25°	19973	9867	6524	9867
30°	21572	9735	6317	9735
35°	17738	9488	6180	9488
40°	12607	9144	6032	9144
45°	9685	8680	5946	8680
50°	8268	8106	5934	8106
55°	7362	7543	5986	7543
60°	6640	6926	6138	6926
65°	6134	6308	6298	6308
70°	5576	5665	6388	5665
75°	4923	4991	6331	4991
80°	4143	4069	5791	4069
85°	3283	2934	4676	2934



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.2	1.7
10°-20°	453.2	5.0
20°-30°	736.0	8.1
30°-40°	897.7	9.9
40°-50°	816.7	9.0
50°-60°	650.5	7.2
60°-70°	453.1	5.0
70°-80°	241.6	2.7
80°-90°	64.1	0.7
90°-100°	54.6	0.6
100°-110°	336.8	3.7
110°-120°	610.9	6.7
120°-130°	783.9	8.6
130°-140°	843.2	9.3
140°-150°	791.5	8.7
150°-160°	640.2	7.0
160°-170°	414.1	4.6
170°-180°	142.8	1.6
0°-30°	1341.4	14.8
0°-40°	2239.2	24.7
0°-60°	3706.4	40.8
0°-90°	4465.2	49.2
90°-120°	1002.3	11.0
90°-150°	3420.9	37.7
90°-180°	4618.0	50.8
0°-180°	9083.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1824	1581	1384	1581	1824	184
15°	2278	1514	1085	1514	2278	652
25°	2803	1385	916	1385	2803	1280
35°	2250	1203	784	1203	2250	1377
45°	1060	950	651	950	1060	849
55°	654	670	532	670	654	589
65°	401	413	412	413	401	398
75°	197	200	254	200	197	212
85°	44	40	63	40	44	52
90°	27	1	27	1	27	13
95°	23	64	23	64	23	19
105°	331	328	331	328	331	299
115°	611	615	611	615	611	606
125°	875	875	875	875	875	779
135°	1087	1091	1087	1091	1087	839
145°	1262	1265	1262	1265	1262	788
155°	1384	1393	1384	1393	1384	638
165°	1463	1470	1463	1470	1463	413
175°	1497	1504	1497	1504	1497	142
180°	1504	1504	1504	1504	1504	



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1672.6	1670.4	1668.3	1664.0	1667.2	1658.0	1653.7	1646.2	1637.1	1633.9	1630.1
5°	1824.2	1827.6	1830.9	1816.9	1818.2	1808.8	1787.3	1769.9	1755.8	1737.7	1724.9
7.5°	2006.8	1998.9	1998.2	1989.1	1973.4	1960.8	1938.2	1909.4	1881.7	1850.0	1823.9
10°	2098.1	2098.8	2092.7	2082.0	2065.2	2053.1	2023.6	1995.4	1961.2	1920.9	1892.0
12.5°	2166.8	2169.6	2162.0	2147.5	2139.2	2112.2	2089.0	2055.6	2014.8	1982.6	1938.7
15°	2277.9	2270.5	2265.2	2247.0	2233.0	2204.8	2167.9	2133.0	2088.7	2047.7	2006.8
17.5°	2385.1	2391.0	2380.9	2364.4	2320.7	2287.8	2238.3	2190.4	2135.3	2080.3	2031.5
20°	2480.6	2486.1	2470.6	2441.7	2389.4	2356.5	2291.4	2229.6	2165.8	2095.4	2041.7
22.5°	2599.9	2595.6	2574.7	2530.8	2485.4	2424.7	2354.2	2279.0	2199.2	2119.5	2048.1
25°	2802.8	2774.6	2761.8	2707.5	2647.7	2558.5	2461.9	2351.7	2252.5	2147.1	2055.8
27.5°	2915.3	2906.4	2892.2	2854.4	2791.5	2696.0	2582.1	2448.0	2307.9	2174.9	2055.4
30°	2892.7	2894.1	2895.5	2883.3	2843.1	2771.2	2657.8	2513.5	2347.1	2197.4	2059.2
32.5°	2693.0	2717.4	2740.8	2768.5	2779.7	2765.9	2694.8	2564.6	2393.2	2223.2	2057.0
35°	2249.8	2257.1	2333.0	2408.1	2510.2	2589.4	2642.4	2584.6	2440.3	2245.1	2054.4
37.5°	1754.2	1790.4	1842.9	1927.9	2075.1	2206.9	2376.4	2454.5	2407.9	2252.2	2049.8
40°	1495.4	1529.0	1563.1	1649.8	1773.9	1933.6	2126.2	2290.7	2328.9	2229.6	2033.7
42.5°	1295.6	1322.2	1360.2	1425.3	1529.0	1670.5	1854.6	2069.5	2201.7	2164.1	1999.8
45°	1060.4	1077.2	1106.7	1158.5	1233.6	1344.4	1506.8	1741.7	1946.4	2014.1	1919.5
47.5°	907.7	907.6	930.5	966.2	1020.5	1114.6	1234.7	1418.8	1637.4	1799.1	1791.7
50°	822.9	819.5	837.6	868.5	911.5	973.9	1088.6	1235.6	1445.7	1628.9	1679.9
52.5°	749.8	750.2	761.4	784.2	820.2	873.5	959.2	1091.7	1271.2	1459.2	1555.4
55°	653.8	651.0	663.7	679.2	705.4	740.3	802.0	903.4	1049.0	1234.2	1359.1
57.5°	565.7	573.1	578.2	588.9	610.6	634.0	686.0	760.4	876.0	1034.9	1166.9
60°	514.1	521.5	525.6	536.2	553.7	573.9	614.2	674.5	771.9	908.8	1039.7
62.5°	468.0	473.7	475.0	484.7	498.9	518.6	550.3	601.0	677.9	797.6	925.8
65°	401.4	401.4	404.1	414.1	420.9	438.2	462.4	499.4	561.1	654.4	763.8
67.5°	337.2	340.4	339.8	344.1	350.3	363.9	381.3	411.7	457.4	525.6	613.0
70°	295.3	298.0	297.3	300.7	307.4	316.2	330.2	359.0	391.9	450.4	525.6
72.5°	257.7	258.8	257.1	261.5	265.5	273.2	288.9	304.3	335.0	384.4	446.1
75°	197.3	198.6	200.0	202.7	206.7	210.8	218.8	234.3	254.3	291.3	330.9
77.5°	147.9	145.3	148.6	148.2	150.5	153.6	160.7	168.8	185.4	208.7	239.4
80°	111.4	112.1	112.1	112.8	116.1	118.1	124.2	130.2	142.9	160.4	181.9
82.5°	81.4	83.1	82.1	83.3	86.0	87.5	90.8	95.8	103.2	116.9	132.5
85°	44.3	41.0	42.3	43.7	43.7	44.3	47.0	49.0	53.0	58.4	64.4
87.5°	18.3	19.2	19.5	19.4	19.8	19.6	21.5	21.3	22.6	23.9	25.7
90°	26.8	26.0	25.2	24.5	23.8	22.8	21.5	20.3	19.1	17.8	16.1
92.5°	25.0	24.6	24.3	23.9	23.6	22.8	21.5	20.3	19.1	17.8	16.3
95°	23.4	23.4	23.4	23.4	23.4	22.8	21.5	20.3	19.1	17.8	27.2
97.5°	23.4	23.4	23.4	23.4	23.4	26.9	33.9	40.9	47.9	54.8	73.4
100°	23.4	24.4	25.4	26.3	27.4	46.3	83.3	120.1	157.0	194.0	193.0
102.5°	140.3	157.0	173.9	190.8	207.6	219.6	226.5	233.5	240.5	247.5	246.8
105°	331.1	331.3	331.6	331.8	332.1	332.2	332.2	332.2	332.2	332.2	332.2
107.5°	417.4	418.1	418.9	419.6	420.3	420.7	420.7	420.6	420.5	420.5	420.0
110°	477.2	476.9	476.6	476.4	476.1	476.4	477.2	477.9	478.6	479.3	478.9



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	530.6	531.0	531.3	531.7	532.0	532.7	533.6	534.5	535.5	536.4	536.1
115°	610.9	612.3	613.9	615.4	616.8	618.1	619.1	620.1	621.0	622.1	621.8
117.5°	696.5	697.2	697.8	698.4	699.0	700.1	701.4	702.7	704.0	705.2	704.3
120°	749.2	750.4	751.6	752.9	754.1	754.9	755.4	756.0	756.5	756.9	756.2
122.5°	799.1	800.5	801.9	803.4	804.8	805.8	806.2	806.8	807.3	807.8	807.4
125°	875.1	875.8	876.6	877.4	878.0	878.9	879.9	880.9	881.9	882.9	882.9
127.5°	939.1	940.9	942.8	944.6	946.4	947.6	948.1	948.7	949.3	949.8	949.9
130°	985.5	986.7	987.9	989.2	990.4	991.4	992.1	992.9	993.7	994.4	994.1
132.5°	1028.3	1029.5	1030.8	1032.0	1033.2	1033.9	1034.1	1034.2	1034.4	1034.5	1035.1
135°	1086.9	1088.4	1089.9	1091.4	1092.9	1093.8	1094.3	1094.8	1095.4	1095.8	1096.3
137.5°	1145.7	1147.0	1148.3	1149.6	1150.9	1151.5	1151.4	1151.3	1151.2	1151.2	1151.6
140°	1180.5	1182.1	1183.5	1185.0	1186.5	1187.0	1186.5	1186.0	1185.5	1185.0	1185.3
142.5°	1213.6	1215.0	1216.5	1218.0	1219.5	1220.2	1220.1	1220.0	1219.9	1219.8	1219.4
145°	1262.0	1263.4	1264.9	1266.4	1267.9	1268.5	1268.3	1268.0	1267.7	1267.5	1267.5
147.5°	1301.8	1303.6	1305.4	1307.2	1309.0	1309.8	1309.4	1309.2	1308.8	1308.5	1308.2
150°	1327.7	1329.6	1331.6	1333.6	1335.6	1336.4	1335.8	1335.4	1334.9	1334.4	1333.9
152.5°	1351.8	1353.6	1355.4	1357.1	1358.9	1359.5	1359.1	1358.6	1358.1	1357.5	1357.1
155°	1383.5	1385.4	1387.4	1389.4	1391.4	1392.0	1391.2	1390.5	1389.7	1389.1	1388.5
157.5°	1410.0	1412.0	1413.9	1415.9	1417.9	1418.5	1417.7	1416.9	1416.1	1415.3	1415.3
160°	1426.9	1428.9	1430.9	1432.9	1434.9	1435.4	1434.3	1433.4	1432.4	1431.4	1431.2
162.5°	1442.1	1444.2	1446.4	1448.6	1450.8	1451.2	1449.8	1448.4	1447.0	1445.6	1445.4
165°	1462.6	1464.6	1466.5	1468.5	1470.5	1470.8	1469.3	1467.7	1466.3	1464.8	1464.6
167.5°	1476.9	1479.1	1481.4	1483.5	1485.7	1486.0	1484.2	1482.5	1480.7	1478.9	1478.6
170°	1484.9	1487.1	1489.4	1491.6	1493.8	1493.9	1491.9	1490.0	1488.0	1486.0	1485.7
172.5°	1490.2	1492.5	1494.7	1496.9	1499.2	1499.3	1497.6	1495.8	1494.0	1492.2	1491.8
175°	1497.1	1499.3	1501.6	1503.8	1506.1	1506.1	1504.2	1502.2	1500.2	1498.2	1498.1
177.5°	1501.2	1502.7	1504.3	1505.9	1507.5	1507.6	1506.2	1504.9	1503.5	1502.0	1501.8
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1626.9	1623.2	1618.9	1611.4	1602.2	1597.4	1589.8	1585.0	1575.4	1567.3	1558.8
5°	1709.4	1692.0	1675.9	1655.1	1632.3	1617.5	1600.1	1580.6	1560.5	1539.6	1516.8
7.5°	1795.0	1764.1	1730.5	1694.4	1659.1	1626.6	1595.6	1565.1	1536.7	1502.4	1473.3
10°	1852.4	1813.5	1771.9	1722.9	1675.2	1633.7	1591.3	1554.4	1516.8	1476.5	1441.0
12.5°	1909.9	1858.0	1799.2	1745.4	1688.2	1637.9	1588.1	1541.0	1493.7	1449.1	1407.7
15°	1950.4	1904.8	1850.4	1773.9	1709.4	1640.4	1574.6	1513.5	1456.5	1406.8	1354.4
17.5°	1977.1	1918.3	1859.9	1786.5	1702.1	1624.8	1550.2	1480.3	1416.0	1353.1	1302.6
20°	1981.9	1921.6	1860.4	1788.6	1702.1	1613.5	1539.0	1455.1	1386.0	1320.9	1259.1
22.5°	1980.4	1911.9	1845.5	1771.5	1687.0	1605.4	1515.4	1429.9	1354.8	1290.8	1226.3
25°	1965.1	1892.0	1808.8	1734.3	1651.1	1564.5	1473.3	1384.7	1308.1	1234.9	1171.2
27.5°	1952.6	1857.7	1763.4	1676.5	1596.2	1516.8	1429.4	1338.7	1253.9	1179.7	1119.6
30°	1937.0	1833.0	1726.9	1636.3	1553.8	1476.5	1394.0	1305.4	1216.9	1144.4	1080.0
32.5°	1923.0	1801.8	1689.9	1591.2	1503.8	1428.7	1352.6	1268.3	1181.4	1107.8	1043.4
35°	1896.1	1755.8	1627.5	1516.1	1422.9	1345.7	1281.9	1203.4	1123.5	1052.4	990.7
37.5°	1861.8	1695.4	1557.8	1441.0	1338.7	1257.4	1198.0	1137.7	1061.1	992.6	936.7
40°	1835.0	1652.4	1506.8	1387.3	1281.3	1196.7	1141.7	1084.6	1020.9	957.1	898.0
42.5°	1801.1	1613.8	1455.3	1326.6	1221.7	1139.3	1081.5	1033.0	976.8	917.4	862.5
45°	1739.0	1543.7	1371.8	1233.6	1127.6	1046.4	986.6	950.4	908.1	851.7	805.4
47.5°	1647.6	1459.5	1281.8	1139.1	1029.7	954.4	898.5	863.7	833.9	791.9	749.9
50°	1566.5	1396.7	1216.9	1075.2	965.8	889.9	838.3	806.8	781.3	749.0	713.4
52.5°	1475.8	1317.8	1153.0	1013.0	904.6	829.8	779.2	751.5	730.2	707.1	672.1
55°	1331.6	1197.4	1044.3	911.5	811.4	738.3	694.0	669.9	652.4	634.9	613.5
57.5°	1172.8	1067.8	932.3	810.8	718.7	652.1	610.8	587.3	573.7	564.7	552.1
60°	1061.1	971.2	854.4	743.6	653.8	594.7	554.4	536.2	524.9	517.5	508.1
62.5°	957.5	883.6	775.5	674.4	595.7	539.8	503.9	486.3	475.4	471.8	464.1
65°	804.7	747.7	658.4	574.5	507.4	459.8	429.6	412.8	406.0	402.0	402.7
67.5°	654.3	619.5	547.8	476.2	422.7	382.7	358.5	345.7	342.3	336.9	336.8
70°	562.4	536.2	475.9	413.5	365.8	334.9	313.4	300.0	296.6	293.9	293.3
72.5°	481.4	458.4	406.0	356.0	313.1	286.0	268.4	260.3	254.8	253.1	253.0
75°	361.8	349.0	307.4	267.8	238.2	219.5	207.4	200.0	196.0	195.3	196.0
77.5°	257.2	246.1	219.6	191.6	172.9	158.7	148.4	145.9	141.4	141.5	140.8
80°	193.3	185.9	169.1	147.0	131.6	119.5	114.1	109.4	108.1	106.1	108.1
82.5°	140.2	132.2	120.8	106.7	93.9	86.7	81.4	79.9	79.0	78.1	78.5
85°	69.1	69.8	63.1	52.3	47.0	43.0	39.6	39.6	38.9	38.2	38.9
87.5°	26.5	25.1	22.6	20.6	17.5	15.5	14.6	14.7	13.5	13.3	14.3
90°	14.4	12.7	10.9	9.0	7.1	5.1	3.1	1.1	3.1	5.1	7.1
92.5°	14.7	13.3	11.7	11.6	13.0	14.4	15.8	17.1	15.8	14.4	13.0
95°	36.7	46.1	55.4	60.5	61.3	62.1	62.8	63.5	62.8	62.1	61.3
97.5°	92.1	110.7	129.3	138.0	136.6	135.3	134.0	132.7	134.0	135.3	136.6
100°	192.0	191.0	190.0	189.2	188.4	187.6	186.9	186.1	186.9	187.6	188.4
102.5°	246.3	245.7	245.1	244.4	243.4	242.5	241.5	240.6	241.5	242.5	243.4
105°	332.2	332.2	332.2	331.7	330.7	329.8	328.7	327.8	328.7	329.8	330.7
107.5°	419.5	419.0	418.5	418.3	418.3	418.3	418.3	418.3	418.3	418.3	418.3
110°	478.4	477.9	477.3	477.2	477.2	477.2	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	535.8	535.5	535.3	534.8	534.2	533.6	533.0	532.4	533.0	533.6	534.2
115°	621.6	621.3	621.0	620.4	619.1	617.9	616.6	615.4	616.6	617.9	619.1
117.5°	703.4	702.4	701.5	701.0	701.0	701.1	701.1	701.2	701.1	701.1	701.0
120°	755.4	754.7	754.0	753.7	754.0	754.2	754.5	754.7	754.5	754.2	754.0
122.5°	807.1	806.8	806.4	805.7	804.8	803.8	802.9	801.9	802.9	803.8	804.8
125°	882.9	882.9	882.9	882.0	880.3	878.6	876.8	875.1	876.8	878.6	880.3
127.5°	950.1	950.2	950.4	949.9	948.6	947.4	946.2	944.9	946.2	947.4	948.6
130°	993.9	993.7	993.4	992.6	991.4	990.2	988.9	987.7	988.9	990.2	991.4
132.5°	1035.6	1036.1	1036.7	1036.2	1034.8	1033.4	1031.9	1030.5	1031.9	1033.4	1034.8
135°	1096.8	1097.3	1097.8	1097.3	1095.8	1094.3	1092.9	1091.4	1092.9	1094.3	1095.8
137.5°	1152.0	1152.4	1152.9	1152.4	1151.2	1149.9	1148.6	1147.4	1148.6	1149.9	1151.2
140°	1185.5	1185.8	1186.0	1185.9	1185.3	1184.9	1184.4	1183.9	1184.4	1184.9	1185.3
142.5°	1219.1	1218.7	1218.4	1218.1	1217.8	1217.5	1217.2	1216.9	1217.2	1217.5	1217.8
145°	1267.5	1267.5	1267.5	1267.2	1266.8	1266.3	1265.8	1265.2	1265.8	1266.3	1266.8
147.5°	1307.9	1307.6	1307.3	1307.3	1307.3	1307.4	1307.5	1307.6	1307.5	1307.4	1307.3
150°	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1333.9	1333.4	1332.9
152.5°	1356.6	1356.1	1355.6	1355.9	1357.0	1358.1	1359.2	1360.2	1359.2	1358.1	1357.0
155°	1388.0	1387.5	1387.1	1387.5	1389.1	1390.5	1392.0	1393.4	1392.0	1390.5	1389.1
157.5°	1415.2	1415.1	1415.1	1415.6	1416.4	1417.3	1418.2	1419.1	1418.2	1417.3	1416.4
160°	1430.9	1430.6	1430.4	1431.0	1432.4	1434.0	1435.5	1436.9	1435.5	1434.0	1432.4
162.5°	1445.2	1444.9	1444.7	1445.3	1446.7	1448.2	1449.8	1451.2	1449.8	1448.2	1446.7
165°	1464.3	1464.0	1463.8	1464.5	1465.9	1467.4	1468.9	1470.4	1468.9	1467.4	1465.9
167.5°	1478.3	1478.1	1477.9	1478.5	1480.1	1481.6	1483.2	1484.6	1483.2	1481.6	1480.1
170°	1485.5	1485.2	1485.0	1485.7	1487.5	1489.2	1491.0	1492.7	1491.0	1489.2	1487.5
172.5°	1491.3	1490.9	1490.5	1491.1	1492.8	1494.6	1496.3	1498.1	1496.3	1494.6	1492.8
175°	1497.8	1497.5	1497.3	1497.9	1499.3	1500.9	1502.4	1503.8	1502.4	1500.9	1499.3
177.5°	1501.7	1501.5	1501.2	1501.8	1503.0	1504.2	1505.3	1506.5	1505.3	1504.2	1503.0
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1553.8	1548.0	1543.2	1532.4	1526.5	1518.5	1512.0	1519.0	1511.5	1514.7	1509.8
5°	1505.5	1486.6	1473.3	1453.7	1437.0	1421.5	1410.1	1408.1	1402.7	1400.1	1392.0
7.5°	1447.2	1423.7	1400.6	1375.1	1353.6	1331.7	1317.8	1306.2	1298.6	1288.5	1281.7
10°	1412.8	1381.3	1354.4	1323.5	1296.7	1273.2	1254.4	1245.0	1236.3	1223.6	1218.8
12.5°	1370.4	1337.7	1305.0	1272.0	1246.2	1220.0	1203.9	1189.7	1183.7	1169.3	1167.9
15°	1319.5	1270.5	1238.3	1204.7	1169.2	1147.7	1134.3	1118.9	1112.2	1102.1	1094.7
17.5°	1258.9	1215.0	1174.8	1140.1	1109.6	1091.5	1074.8	1064.2	1052.7	1046.1	1034.0
20°	1214.8	1173.2	1132.9	1096.1	1072.5	1051.7	1038.3	1028.2	1016.2	1012.8	1000.7
22.5°	1177.8	1131.9	1093.2	1062.2	1036.6	1013.1	998.6	991.7	983.4	973.1	970.6
25°	1117.5	1069.9	1037.0	1006.1	983.3	961.8	951.7	943.0	935.0	927.6	924.9
27.5°	1065.4	1022.9	983.8	955.9	936.0	916.4	907.6	897.0	891.0	885.1	877.9
30°	1028.9	985.2	951.1	924.2	902.8	885.3	875.9	868.5	863.2	857.7	853.8
32.5°	991.4	950.9	917.7	891.5	870.0	856.8	848.5	843.3	837.3	830.9	825.8
35°	941.7	897.3	865.1	842.3	825.5	815.5	806.1	801.3	794.7	794.7	789.3
37.5°	885.7	847.4	819.0	798.1	783.1	774.1	764.0	760.7	756.4	753.5	751.7
40°	852.4	816.8	790.0	769.1	753.0	745.6	737.6	732.3	729.5	726.2	724.9
42.5°	818.0	784.0	758.3	739.1	725.1	718.8	711.3	707.6	702.1	697.8	697.0
45°	765.8	732.9	709.5	694.0	681.9	674.5	669.9	661.8	659.1	653.8	653.1
47.5°	716.3	684.8	661.7	649.0	638.4	632.4	625.0	616.9	613.9	611.1	610.9
50°	679.2	650.4	628.9	616.8	606.7	598.1	590.6	585.2	583.2	583.2	584.6
52.5°	641.6	617.1	598.8	584.0	574.5	565.2	558.4	555.2	552.1	555.3	557.8
55°	586.6	561.8	548.4	534.3	524.9	514.1	510.7	509.5	507.4	512.8	515.5
57.5°	528.3	510.9	495.2	481.2	472.8	466.6	462.0	461.2	465.0	467.5	476.2
60°	491.3	471.1	457.1	446.3	436.3	432.2	430.9	429.6	432.2	439.6	451.0
62.5°	450.5	434.1	419.0	410.9	403.5	396.8	396.5	397.4	402.7	411.1	422.6
65°	390.6	376.5	366.4	357.1	351.0	347.0	348.4	351.0	357.1	368.5	381.3
67.5°	329.8	320.1	311.2	303.5	297.7	297.7	299.1	303.1	310.2	323.4	335.0
70°	290.6	279.9	272.5	269.1	264.4	261.7	265.8	272.5	278.5	290.6	300.7
72.5°	251.4	242.3	236.5	234.3	232.2	230.1	231.4	238.7	246.8	258.9	270.6
75°	193.3	189.9	185.9	183.2	181.2	182.5	183.9	190.6	197.3	210.1	223.5
77.5°	141.1	137.6	135.2	134.5	133.5	134.1	137.8	142.8	149.4	158.7	168.8
80°	106.7	105.4	104.0	103.3	103.3	104.0	109.4	112.8	118.8	127.5	135.6
82.5°	77.7	76.9	76.6	76.5	77.1	77.1	80.4	84.8	89.8	96.3	103.3
85°	41.0	39.6	41.6	42.3	41.0	43.0	44.3	47.0	49.0	52.3	55.7
87.5°	15.2	16.7	16.4	17.4	17.7	19.1	18.9	21.3	22.6	23.8	23.6
90°	9.0	10.9	12.7	14.4	16.1	17.8	19.1	20.3	21.5	22.8	23.8
92.5°	11.6	11.7	13.3	14.7	16.3	17.8	19.1	20.3	21.5	22.8	23.6
95°	60.5	55.4	46.1	36.7	27.2	17.8	19.1	20.3	21.5	22.8	23.4
97.5°	138.0	129.3	110.7	92.1	73.4	54.8	47.9	40.9	33.9	26.9	23.4
100°	189.2	190.0	191.0	192.0	193.0	194.0	157.0	120.1	83.3	46.3	27.4
102.5°	244.4	245.1	245.7	246.3	246.8	247.5	240.5	233.5	226.5	219.6	207.6
105°	331.7	332.2	332.2	332.2	332.2	332.2	332.2	332.2	332.2	332.2	332.1
107.5°	418.3	418.5	419.0	419.5	420.0	420.5	420.5	420.6	420.7	420.7	420.3
110°	477.2	477.3	477.9	478.4	478.9	479.3	478.6	477.9	477.2	476.4	476.1



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	534.8	535.3	535.5	535.8	536.1	536.4	535.5	534.5	533.6	532.7	532.0
115°	620.4	621.0	621.3	621.6	621.8	622.1	621.0	620.1	619.1	618.1	616.8
117.5°	701.0	701.5	702.4	703.4	704.3	705.2	704.0	702.7	701.4	700.1	699.0
120°	753.7	754.0	754.7	755.4	756.2	756.9	756.5	756.0	755.4	754.9	754.1
122.5°	805.7	806.4	806.8	807.1	807.4	807.8	807.3	806.8	806.2	805.8	804.8
125°	882.0	882.9	882.9	882.9	882.9	882.9	881.9	880.9	879.9	878.9	878.0
127.5°	949.9	950.4	950.2	950.1	949.9	949.8	949.3	948.7	948.1	947.6	946.4
130°	992.6	993.4	993.7	993.9	994.1	994.4	993.7	992.9	992.1	991.4	990.4
132.5°	1036.2	1036.7	1036.1	1035.6	1035.1	1034.5	1034.4	1034.2	1034.1	1033.9	1033.2
135°	1097.3	1097.8	1097.3	1096.8	1096.3	1095.8	1095.4	1094.8	1094.3	1093.8	1092.9
137.5°	1152.4	1152.9	1152.4	1152.0	1151.6	1151.2	1151.2	1151.3	1151.4	1151.5	1150.9
140°	1185.9	1186.0	1185.8	1185.5	1185.3	1185.0	1185.5	1186.0	1186.5	1187.0	1186.5
142.5°	1218.1	1218.4	1218.7	1219.1	1219.4	1219.8	1219.9	1220.0	1220.1	1220.2	1219.5
145°	1267.2	1267.5	1267.5	1267.5	1267.5	1267.5	1267.7	1268.0	1268.3	1268.5	1267.9
147.5°	1307.3	1307.3	1307.6	1307.9	1308.2	1308.5	1308.8	1309.2	1309.4	1309.8	1309.0
150°	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1334.9	1335.4	1335.8	1336.4	1335.6
152.5°	1355.9	1355.6	1356.1	1356.6	1357.1	1357.5	1358.1	1358.6	1359.1	1359.5	1358.9
155°	1387.5	1387.1	1387.5	1388.0	1388.5	1389.1	1389.7	1390.5	1391.2	1392.0	1391.4
157.5°	1415.6	1415.1	1415.1	1415.2	1415.3	1415.3	1416.1	1416.9	1417.7	1418.5	1417.9
160°	1431.0	1430.4	1430.6	1430.9	1431.2	1431.4	1432.4	1433.4	1434.3	1435.4	1434.9
162.5°	1445.3	1444.7	1444.9	1445.2	1445.4	1445.6	1447.0	1448.4	1449.8	1451.2	1450.8
165°	1464.5	1463.8	1464.0	1464.3	1464.6	1464.8	1466.3	1467.7	1469.3	1470.8	1470.5
167.5°	1478.5	1477.9	1478.1	1478.3	1478.6	1478.9	1480.7	1482.5	1484.2	1486.0	1485.7
170°	1485.7	1485.0	1485.2	1485.5	1485.7	1486.0	1488.0	1490.0	1491.9	1493.9	1493.8
172.5°	1491.1	1490.5	1490.9	1491.3	1491.8	1492.2	1494.0	1495.8	1497.6	1499.3	1499.2
175°	1497.9	1497.3	1497.5	1497.8	1498.1	1498.2	1500.2	1502.2	1504.2	1506.1	1506.1
177.5°	1501.8	1501.2	1501.5	1501.7	1501.8	1502.0	1503.5	1504.9	1506.2	1507.6	1507.5
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1506.7	1510.4	1507.2	1511.5	1507.2	1510.4	1506.7	1509.8	1514.7	1511.5	1519.0
5°	1388.6	1382.6	1386.6	1384.0	1386.6	1382.6	1388.6	1392.0	1400.1	1402.7	1408.1
7.5°	1279.6	1273.8	1267.3	1264.2	1267.3	1273.8	1279.6	1281.7	1288.5	1298.6	1306.2
10°	1211.4	1204.1	1203.4	1198.7	1203.4	1204.1	1211.4	1218.8	1223.6	1236.3	1245.0
12.5°	1161.5	1154.7	1147.0	1145.0	1147.0	1154.7	1161.5	1167.9	1169.3	1183.7	1189.7
15°	1090.6	1085.3	1080.6	1084.6	1080.6	1085.3	1090.6	1094.7	1102.1	1112.2	1118.9
17.5°	1031.7	1027.3	1026.5	1021.5	1026.5	1027.3	1031.7	1034.0	1046.1	1052.7	1064.2
20°	994.7	991.4	992.6	984.0	992.6	991.4	994.7	1000.7	1012.8	1016.2	1028.2
22.5°	965.2	958.6	957.8	956.1	957.8	958.6	965.2	970.6	973.1	983.4	991.7
25°	918.9	915.5	912.1	915.5	912.1	915.5	918.9	924.9	927.6	935.0	943.0
27.5°	878.4	874.4	873.5	873.8	873.5	874.4	878.4	877.9	885.1	891.0	897.0
30°	853.8	847.1	847.7	847.1	847.7	847.1	853.8	853.8	857.7	863.2	868.5
32.5°	826.9	822.3	821.4	820.2	821.4	822.3	826.9	825.8	830.9	837.3	843.3
35°	787.3	787.3	783.9	783.9	783.9	787.3	787.3	789.3	794.7	794.7	801.3
37.5°	750.1	749.4	747.4	747.7	747.4	749.4	750.1	751.7	753.5	756.4	760.7
40°	722.2	721.5	719.5	715.5	719.5	721.5	722.2	724.9	726.2	729.5	732.3
42.5°	695.3	693.0	692.1	690.8	692.1	693.0	695.3	697.0	697.8	702.1	707.6
45°	653.1	653.1	651.7	651.0	651.7	653.1	653.1	653.1	653.8	659.1	661.8
47.5°	612.0	613.2	615.7	615.4	615.7	613.2	612.0	610.9	611.1	613.9	616.9
50°	587.3	588.0	590.0	590.6	590.0	588.0	587.3	584.6	583.2	583.2	585.2
52.5°	559.9	563.8	566.4	565.9	566.4	563.8	559.9	557.8	555.3	552.1	555.2
55°	521.5	526.2	530.9	531.6	530.9	526.2	521.5	515.5	512.8	507.4	509.5
57.5°	483.5	490.1	495.1	496.6	495.1	490.1	483.5	476.2	467.5	465.0	461.2
60°	457.7	466.5	472.5	475.2	472.5	466.5	457.7	451.0	439.6	432.2	429.6
62.5°	433.0	442.8	448.8	449.4	448.8	442.8	433.0	422.6	411.1	402.7	397.4
65°	392.6	402.7	408.0	412.1	408.0	402.7	392.6	381.3	368.5	357.1	351.0
67.5°	349.1	359.2	365.2	368.3	365.2	359.2	349.1	335.0	323.4	310.2	303.1
70°	317.5	327.5	335.6	338.3	335.6	327.5	317.5	300.7	290.6	278.5	272.5
72.5°	286.3	295.3	301.8	305.0	301.8	295.3	286.3	270.6	258.9	246.8	238.7
75°	232.2	244.3	250.4	253.7	250.4	244.3	232.2	223.5	210.1	197.3	190.6
77.5°	179.1	190.1	193.7	195.4	193.7	190.1	179.1	168.8	158.7	149.4	142.8
80°	143.6	150.3	155.1	155.7	155.1	150.3	143.6	135.6	127.5	118.8	112.8
82.5°	110.4	116.0	117.4	119.2	117.4	116.0	110.4	103.3	96.3	89.8	84.8
85°	60.4	63.1	63.8	63.1	63.8	63.1	60.4	55.7	52.3	49.0	47.0
87.5°	24.8	24.4	24.5	25.7	24.5	24.4	24.8	23.6	23.8	22.6	21.3
90°	24.5	25.2	26.0	26.8	26.0	25.2	24.5	23.8	22.8	21.5	20.3
92.5°	23.9	24.3	24.6	25.0	24.6	24.3	23.9	23.6	22.8	21.5	20.3
95°	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	22.8	21.5	20.3
97.5°	23.4	23.4	23.4	23.4	23.4	23.4	23.4	23.4	26.9	33.9	40.9
100°	26.3	25.4	24.4	23.4	24.4	25.4	26.3	27.4	46.3	83.3	120.1
102.5°	190.8	173.9	157.0	140.3	157.0	173.9	190.8	207.6	219.6	226.5	233.5
105°	331.8	331.6	331.3	331.1	331.3	331.6	331.8	332.1	332.2	332.2	332.2
107.5°	419.6	418.9	418.1	417.4	418.1	418.9	419.6	420.3	420.7	420.7	420.6
110°	476.4	476.6	476.9	477.2	476.9	476.6	476.4	476.1	476.4	477.2	477.9



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	531.7	531.3	531.0	530.6	531.0	531.3	531.7	532.0	532.7	533.6	534.5
115°	615.4	613.9	612.3	610.9	612.3	613.9	615.4	616.8	618.1	619.1	620.1
117.5°	698.4	697.8	697.2	696.5	697.2	697.8	698.4	699.0	700.1	701.4	702.7
120°	752.9	751.6	750.4	749.2	750.4	751.6	752.9	754.1	754.9	755.4	756.0
122.5°	803.4	801.9	800.5	799.1	800.5	801.9	803.4	804.8	805.8	806.2	806.8
125°	877.4	876.6	875.8	875.1	875.8	876.6	877.4	878.0	878.9	879.9	880.9
127.5°	944.6	942.8	940.9	939.1	940.9	942.8	944.6	946.4	947.6	948.1	948.7
130°	989.2	987.9	986.7	985.5	986.7	987.9	989.2	990.4	991.4	992.1	992.9
132.5°	1032.0	1030.8	1029.5	1028.3	1029.5	1030.8	1032.0	1033.2	1033.9	1034.1	1034.2
135°	1091.4	1089.9	1088.4	1086.9	1088.4	1089.9	1091.4	1092.9	1093.8	1094.3	1094.8
137.5°	1149.6	1148.3	1147.0	1145.7	1147.0	1148.3	1149.6	1150.9	1151.5	1151.4	1151.3
140°	1185.0	1183.5	1182.1	1180.5	1182.1	1183.5	1185.0	1186.5	1187.0	1186.5	1186.0
142.5°	1218.0	1216.5	1215.0	1213.6	1215.0	1216.5	1218.0	1219.5	1220.2	1220.1	1220.0
145°	1266.4	1264.9	1263.4	1262.0	1263.4	1264.9	1266.4	1267.9	1268.5	1268.3	1268.0
147.5°	1307.2	1305.4	1303.6	1301.8	1303.6	1305.4	1307.2	1309.0	1309.8	1309.4	1309.2
150°	1333.6	1331.6	1329.6	1327.7	1329.6	1331.6	1333.6	1335.6	1336.4	1335.8	1335.4
152.5°	1357.1	1355.4	1353.6	1351.8	1353.6	1355.4	1357.1	1358.9	1359.5	1359.1	1358.6
155°	1389.4	1387.4	1385.4	1383.5	1385.4	1387.4	1389.4	1391.4	1392.0	1391.2	1390.5
157.5°	1415.9	1413.9	1412.0	1410.0	1412.0	1413.9	1415.9	1417.9	1418.5	1417.7	1416.9
160°	1432.9	1430.9	1428.9	1426.9	1428.9	1430.9	1432.9	1434.9	1435.4	1434.3	1433.4
162.5°	1448.6	1446.4	1444.2	1442.1	1444.2	1446.4	1448.6	1450.8	1451.2	1449.8	1448.4
165°	1468.5	1466.5	1464.6	1462.6	1464.6	1466.5	1468.5	1470.5	1470.8	1469.3	1467.7
167.5°	1483.5	1481.4	1479.1	1476.9	1479.1	1481.4	1483.5	1485.7	1486.0	1484.2	1482.5
170°	1491.6	1489.4	1487.1	1484.9	1487.1	1489.4	1491.6	1493.8	1493.9	1491.9	1490.0
172.5°	1496.9	1494.7	1492.5	1490.2	1492.5	1494.7	1496.9	1499.2	1499.3	1497.6	1495.8
175°	1503.8	1501.6	1499.3	1497.1	1499.3	1501.6	1503.8	1506.1	1506.1	1504.2	1502.2
177.5°	1505.9	1504.3	1502.7	1501.2	1502.7	1504.3	1505.9	1507.5	1507.6	1506.2	1504.9
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1512.0	1518.5	1526.5	1532.4	1543.2	1548.0	1553.8	1558.8	1567.3	1575.4	1585.0
5°	1410.1	1421.5	1437.0	1453.7	1473.3	1486.6	1505.5	1516.8	1539.6	1560.5	1580.6
7.5°	1317.8	1331.7	1353.6	1375.1	1400.6	1423.7	1447.2	1473.3	1502.4	1536.7	1565.1
10°	1254.4	1273.2	1296.7	1323.5	1354.4	1381.3	1412.8	1441.0	1476.5	1516.8	1554.4
12.5°	1203.9	1220.0	1246.2	1272.0	1305.0	1337.7	1370.4	1407.7	1449.1	1493.7	1541.0
15°	1134.3	1147.7	1169.2	1204.7	1238.3	1270.5	1319.5	1354.4	1406.8	1456.5	1513.5
17.5°	1074.8	1091.5	1109.6	1140.1	1174.8	1215.0	1258.9	1302.6	1353.1	1416.0	1480.3
20°	1038.3	1051.7	1072.5	1096.1	1132.9	1173.2	1214.8	1259.1	1320.9	1386.0	1455.1
22.5°	998.6	1013.1	1036.6	1062.2	1093.2	1131.9	1177.8	1226.3	1290.8	1354.8	1429.9
25°	951.7	961.8	983.3	1006.1	1037.0	1069.9	1117.5	1171.2	1234.9	1308.1	1384.7
27.5°	907.6	916.4	936.0	955.9	983.8	1022.9	1065.4	1119.6	1179.7	1253.9	1338.7
30°	875.9	885.3	902.8	924.2	951.1	985.2	1028.9	1080.0	1144.4	1216.9	1305.4
32.5°	848.5	856.8	870.0	891.5	917.7	950.9	991.4	1043.4	1107.8	1181.4	1268.3
35°	806.1	815.5	825.5	842.3	865.1	897.3	941.7	990.7	1052.4	1123.5	1203.4
37.5°	764.0	774.1	783.1	798.1	819.0	847.4	885.7	936.7	992.6	1061.1	1137.7
40°	737.6	745.6	753.0	769.1	790.0	816.8	852.4	898.0	957.1	1020.9	1084.6
42.5°	711.3	718.8	725.1	739.1	758.3	784.0	818.0	862.5	917.4	976.8	1033.0
45°	669.9	674.5	681.9	694.0	709.5	732.9	765.8	805.4	851.7	908.1	950.4
47.5°	625.0	632.4	638.4	649.0	661.7	684.8	716.3	749.9	791.9	833.9	863.7
50°	590.6	598.1	606.7	616.8	628.9	650.4	679.2	713.4	749.0	781.3	806.8
52.5°	558.4	565.2	574.5	584.0	598.8	617.1	641.6	672.1	707.1	730.2	751.5
55°	510.7	514.1	524.9	534.3	548.4	561.8	586.6	613.5	634.9	652.4	669.9
57.5°	462.0	466.6	472.8	481.2	495.2	510.9	528.3	552.1	564.7	573.7	587.3
60°	430.9	432.2	436.3	446.3	457.1	471.1	491.3	508.1	517.5	524.9	536.2
62.5°	396.5	396.8	403.5	410.9	419.0	434.1	450.5	464.1	471.8	475.4	486.3
65°	348.4	347.0	351.0	357.1	366.4	376.5	390.6	402.7	402.0	406.0	412.8
67.5°	299.1	297.7	297.7	303.5	311.2	320.1	329.8	336.8	336.9	342.3	345.7
70°	265.8	261.7	264.4	269.1	272.5	279.9	290.6	293.3	293.9	296.6	300.0
72.5°	231.4	230.1	232.2	234.3	236.5	242.3	251.4	253.0	253.1	254.8	260.3
75°	183.9	182.5	181.2	183.2	185.9	189.9	193.3	196.0	195.3	196.0	200.0
77.5°	137.8	134.1	133.5	134.5	135.2	137.6	141.1	140.8	141.5	141.4	145.9
80°	109.4	104.0	103.3	103.3	104.0	105.4	106.7	108.1	106.1	108.1	109.4
82.5°	80.4	77.1	77.1	76.5	76.6	76.9	77.7	78.5	78.1	79.0	79.9
85°	44.3	43.0	41.0	42.3	41.6	39.6	41.0	38.9	38.2	38.9	39.6
87.5°	18.9	19.1	17.7	17.4	16.4	16.7	15.2	14.3	13.3	13.5	14.7
90°	19.1	17.8	16.1	14.4	12.7	10.9	9.0	7.1	5.1	3.1	1.1
92.5°	19.1	17.8	16.3	14.7	13.3	11.7	11.6	13.0	14.4	15.8	17.1
95°	19.1	17.8	27.2	36.7	46.1	55.4	60.5	61.3	62.1	62.8	63.5
97.5°	47.9	54.8	73.4	92.1	110.7	129.3	138.0	136.6	135.3	134.0	132.7
100°	157.0	194.0	193.0	192.0	191.0	190.0	189.2	188.4	187.6	186.9	186.1
102.5°	240.5	247.5	246.8	246.3	245.7	245.1	244.4	243.4	242.5	241.5	240.6
105°	332.2	332.2	332.2	332.2	332.2	332.2	331.7	330.7	329.8	328.7	327.8
107.5°	420.5	420.5	420.0	419.5	419.0	418.5	418.3	418.3	418.3	418.3	418.3
110°	478.6	479.3	478.9	478.4	477.9	477.3	477.2	477.2	477.2	477.2	477.2



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	535.5	536.4	536.1	535.8	535.5	535.3	534.8	534.2	533.6	533.0	532.4
115°	621.0	622.1	621.8	621.6	621.3	621.0	620.4	619.1	617.9	616.6	615.4
117.5°	704.0	705.2	704.3	703.4	702.4	701.5	701.0	701.0	701.1	701.1	701.2
120°	756.5	756.9	756.2	755.4	754.7	754.0	753.7	754.0	754.2	754.5	754.7
122.5°	807.3	807.8	807.4	807.1	806.8	806.4	805.7	804.8	803.8	802.9	801.9
125°	881.9	882.9	882.9	882.9	882.9	882.9	882.0	880.3	878.6	876.8	875.1
127.5°	949.3	949.8	949.9	950.1	950.2	950.4	949.9	948.6	947.4	946.2	944.9
130°	993.7	994.4	994.1	993.9	993.7	993.4	992.6	991.4	990.2	988.9	987.7
132.5°	1034.4	1034.5	1035.1	1035.6	1036.1	1036.7	1036.2	1034.8	1033.4	1031.9	1030.5
135°	1095.4	1095.8	1096.3	1096.8	1097.3	1097.8	1097.3	1095.8	1094.3	1092.9	1091.4
137.5°	1151.2	1151.2	1151.6	1152.0	1152.4	1152.9	1152.4	1151.2	1149.9	1148.6	1147.4
140°	1185.5	1185.0	1185.3	1185.5	1185.8	1186.0	1185.9	1185.3	1184.9	1184.4	1183.9
142.5°	1219.9	1219.8	1219.4	1219.1	1218.7	1218.4	1218.1	1217.8	1217.5	1217.2	1216.9
145°	1267.7	1267.5	1267.5	1267.5	1267.5	1267.5	1267.2	1266.8	1266.3	1265.8	1265.2
147.5°	1308.8	1308.5	1308.2	1307.9	1307.6	1307.3	1307.3	1307.3	1307.4	1307.5	1307.6
150°	1334.9	1334.4	1333.9	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4
152.5°	1358.1	1357.5	1357.1	1356.6	1356.1	1355.6	1355.9	1357.0	1358.1	1359.2	1360.2
155°	1389.7	1389.1	1388.5	1388.0	1387.5	1387.1	1387.5	1389.1	1390.5	1392.0	1393.4
157.5°	1416.1	1415.3	1415.3	1415.2	1415.1	1415.1	1415.6	1416.4	1417.3	1418.2	1419.1
160°	1432.4	1431.4	1431.2	1430.9	1430.6	1430.4	1431.0	1432.4	1434.0	1435.5	1436.9
162.5°	1447.0	1445.6	1445.4	1445.2	1444.9	1444.7	1445.3	1446.7	1448.2	1449.8	1451.2
165°	1466.3	1464.8	1464.6	1464.3	1464.0	1463.8	1464.5	1465.9	1467.4	1468.9	1470.4
167.5°	1480.7	1478.9	1478.6	1478.3	1478.1	1477.9	1478.5	1480.1	1481.6	1483.2	1484.6
170°	1488.0	1486.0	1485.7	1485.5	1485.2	1485.0	1485.7	1487.5	1489.2	1491.0	1492.7
172.5°	1494.0	1492.2	1491.8	1491.3	1490.9	1490.5	1491.1	1492.8	1494.6	1496.3	1498.1
175°	1500.2	1498.2	1498.1	1497.8	1497.5	1497.3	1497.9	1499.3	1500.9	1502.4	1503.8
177.5°	1503.5	1502.0	1501.8	1501.7	1501.5	1501.2	1501.8	1503.0	1504.2	1505.3	1506.5
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1589.8	1597.4	1602.2	1611.4	1618.9	1623.2	1626.9	1630.1	1633.9	1637.1	1646.2
5°	1600.1	1617.5	1632.3	1655.1	1675.9	1692.0	1709.4	1724.9	1737.7	1755.8	1769.9
7.5°	1595.6	1626.6	1659.1	1694.4	1730.5	1764.1	1795.0	1823.9	1850.0	1881.7	1909.4
10°	1591.3	1633.7	1675.2	1722.9	1771.9	1813.5	1852.4	1892.0	1920.9	1961.2	1995.4
12.5°	1588.1	1637.9	1688.2	1745.4	1799.2	1858.0	1909.9	1938.7	1982.6	2014.8	2055.6
15°	1574.6	1640.4	1709.4	1773.9	1850.4	1904.8	1950.4	2006.8	2047.7	2088.7	2133.0
17.5°	1550.2	1624.8	1702.1	1786.5	1859.9	1918.3	1977.1	2031.5	2080.3	2135.3	2190.4
20°	1539.0	1613.5	1702.1	1788.6	1860.4	1921.6	1981.9	2041.7	2095.4	2165.8	2229.6
22.5°	1515.4	1605.4	1687.0	1771.5	1845.5	1911.9	1980.4	2048.1	2119.5	2199.2	2279.0
25°	1473.3	1564.5	1651.1	1734.3	1808.8	1892.0	1965.1	2055.8	2147.1	2252.5	2351.7
27.5°	1429.4	1516.8	1596.2	1676.5	1763.4	1857.7	1952.6	2055.4	2174.9	2307.9	2448.0
30°	1394.0	1476.5	1553.8	1636.3	1726.9	1833.0	1937.0	2059.2	2197.4	2347.1	2513.5
32.5°	1352.6	1428.7	1503.8	1591.2	1689.9	1801.8	1923.0	2057.0	2223.2	2393.2	2564.6
35°	1281.9	1345.7	1422.9	1516.1	1627.5	1755.8	1896.1	2054.4	2245.1	2440.3	2584.6
37.5°	1198.0	1257.4	1338.7	1441.0	1557.8	1695.4	1861.8	2049.8	2252.2	2407.9	2454.5
40°	1141.7	1196.7	1281.3	1387.3	1506.8	1652.4	1835.0	2033.7	2229.6	2328.9	2290.7
42.5°	1081.5	1139.3	1221.7	1326.6	1455.3	1613.8	1801.1	1999.8	2164.1	2201.7	2069.5
45°	986.6	1046.4	1127.6	1233.6	1371.8	1543.7	1739.0	1919.5	2014.1	1946.4	1741.7
47.5°	898.5	954.4	1029.7	1139.1	1281.8	1459.5	1647.6	1791.7	1799.1	1637.4	1418.8
50°	838.3	889.9	965.8	1075.2	1216.9	1396.7	1566.5	1679.9	1628.9	1445.7	1235.6
52.5°	779.2	829.8	904.6	1013.0	1153.0	1317.8	1475.8	1555.4	1459.2	1271.2	1091.7
55°	694.0	738.3	811.4	911.5	1044.3	1197.4	1331.6	1359.1	1234.2	1049.0	903.4
57.5°	610.8	652.1	718.7	810.8	932.3	1067.8	1172.8	1166.9	1034.9	876.0	760.4
60°	554.4	594.7	653.8	743.6	854.4	971.2	1061.1	1039.7	908.8	771.9	674.5
62.5°	503.9	539.8	595.7	674.4	775.5	883.6	957.5	925.8	797.6	677.9	601.0
65°	429.6	459.8	507.4	574.5	658.4	747.7	804.7	763.8	654.4	561.1	499.4
67.5°	358.5	382.7	422.7	476.2	547.8	619.5	654.3	613.0	525.6	457.4	411.7
70°	313.4	334.9	365.8	413.5	475.9	536.2	562.4	525.6	450.4	391.9	359.0
72.5°	268.4	286.0	313.1	356.0	406.0	458.4	481.4	446.1	384.4	335.0	304.3
75°	207.4	219.5	238.2	267.8	307.4	349.0	361.8	330.9	291.3	254.3	234.3
77.5°	148.4	158.7	172.9	191.6	219.6	246.1	257.2	239.4	208.7	185.4	168.8
80°	114.1	119.5	131.6	147.0	169.1	185.9	193.3	181.9	160.4	142.9	130.2
82.5°	81.4	86.7	93.9	106.7	120.8	132.2	140.2	132.5	116.9	103.2	95.8
85°	39.6	43.0	47.0	52.3	63.1	69.8	69.1	64.4	58.4	53.0	49.0
87.5°	14.6	15.5	17.5	20.6	22.6	25.1	26.5	25.7	23.9	22.6	21.3
90°	3.1	5.1	7.1	9.0	10.9	12.7	14.4	16.1	17.8	19.1	20.3
92.5°	15.8	14.4	13.0	11.6	11.7	13.3	14.7	16.3	17.8	19.1	20.3
95°	62.8	62.1	61.3	60.5	55.4	46.1	36.7	27.2	17.8	19.1	20.3
97.5°	134.0	135.3	136.6	138.0	129.3	110.7	92.1	73.4	54.8	47.9	40.9
100°	186.9	187.6	188.4	189.2	190.0	191.0	192.0	193.0	194.0	157.0	120.1
102.5°	241.5	242.5	243.4	244.4	245.1	245.7	246.3	246.8	247.5	240.5	233.5
105°	328.7	329.8	330.7	331.7	332.2	332.2	332.2	332.2	332.2	332.2	332.2
107.5°	418.3	418.3	418.3	418.3	418.5	419.0	419.5	420.0	420.5	420.5	420.6
110°	477.2	477.2	477.2	477.2	477.3	477.9	478.4	478.9	479.3	478.6	477.9



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	533.0	533.6	534.2	534.8	535.3	535.5	535.8	536.1	536.4	535.5	534.5
115°	616.6	617.9	619.1	620.4	621.0	621.3	621.6	621.8	622.1	621.0	620.1
117.5°	701.1	701.1	701.0	701.0	701.5	702.4	703.4	704.3	705.2	704.0	702.7
120°	754.5	754.2	754.0	753.7	754.0	754.7	755.4	756.2	756.9	756.5	756.0
122.5°	802.9	803.8	804.8	805.7	806.4	806.8	807.1	807.4	807.8	807.3	806.8
125°	876.8	878.6	880.3	882.0	882.9	882.9	882.9	882.9	882.9	881.9	880.9
127.5°	946.2	947.4	948.6	949.9	950.4	950.2	950.1	949.9	949.8	949.3	948.7
130°	988.9	990.2	991.4	992.6	993.4	993.7	993.9	994.1	994.4	993.7	992.9
132.5°	1031.9	1033.4	1034.8	1036.2	1036.7	1036.1	1035.6	1035.1	1034.5	1034.4	1034.2
135°	1092.9	1094.3	1095.8	1097.3	1097.8	1097.3	1096.8	1096.3	1095.8	1095.4	1094.8
137.5°	1148.6	1149.9	1151.2	1152.4	1152.9	1152.4	1152.0	1151.6	1151.2	1151.2	1151.3
140°	1184.4	1184.9	1185.3	1185.9	1186.0	1185.8	1185.5	1185.3	1185.0	1185.5	1186.0
142.5°	1217.2	1217.5	1217.8	1218.1	1218.4	1218.7	1219.1	1219.4	1219.8	1219.9	1220.0
145°	1265.8	1266.3	1266.8	1267.2	1267.5	1267.5	1267.5	1267.5	1267.5	1267.7	1268.0
147.5°	1307.5	1307.4	1307.3	1307.3	1307.3	1307.6	1307.9	1308.2	1308.5	1308.8	1309.2
150°	1333.9	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1334.9	1335.4
152.5°	1359.2	1358.1	1357.0	1355.9	1355.6	1356.1	1356.6	1357.1	1357.5	1358.1	1358.6
155°	1392.0	1390.5	1389.1	1387.5	1387.1	1387.5	1388.0	1388.5	1389.1	1389.7	1390.5
157.5°	1418.2	1417.3	1416.4	1415.6	1415.1	1415.1	1415.2	1415.3	1415.3	1416.1	1416.9
160°	1435.5	1434.0	1432.4	1431.0	1430.4	1430.6	1430.9	1431.2	1431.4	1432.4	1433.4
162.5°	1449.8	1448.2	1446.7	1445.3	1444.7	1444.9	1445.2	1445.4	1445.6	1447.0	1448.4
165°	1468.9	1467.4	1465.9	1464.5	1463.8	1464.0	1464.3	1464.6	1464.8	1466.3	1467.7
167.5°	1483.2	1481.6	1480.1	1478.5	1477.9	1478.1	1478.3	1478.6	1478.9	1480.7	1482.5
170°	1491.0	1489.2	1487.5	1485.7	1485.0	1485.2	1485.5	1485.7	1486.0	1488.0	1490.0
172.5°	1496.3	1494.6	1492.8	1491.1	1490.5	1490.9	1491.3	1491.8	1492.2	1494.0	1495.8
175°	1502.4	1500.9	1499.3	1497.9	1497.3	1497.5	1497.8	1498.1	1498.2	1500.2	1502.2
177.5°	1505.3	1504.2	1503.0	1501.8	1501.2	1501.5	1501.7	1501.8	1502.0	1503.5	1504.9
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1653.7	1658.0	1667.2	1664.0	1668.3	1670.4	1672.6
5°	1787.3	1808.8	1818.2	1816.9	1830.9	1827.6	1824.2
7.5°	1938.2	1960.8	1973.4	1989.1	1998.2	1998.9	2006.8
10°	2023.6	2053.1	2065.2	2082.0	2092.7	2098.8	2098.1
12.5°	2089.0	2112.2	2139.2	2147.5	2162.0	2169.6	2166.8
15°	2167.9	2204.8	2233.0	2247.0	2265.2	2270.5	2277.9
17.5°	2238.3	2287.8	2320.7	2364.4	2380.9	2391.0	2385.1
20°	2291.4	2356.5	2389.4	2441.7	2470.6	2486.1	2480.6
22.5°	2354.2	2424.7	2485.4	2530.8	2574.7	2595.6	2599.9
25°	2461.9	2558.5	2647.7	2707.5	2761.8	2774.6	2802.8
27.5°	2582.1	2696.0	2791.5	2854.4	2892.2	2906.4	2915.3
30°	2657.8	2771.2	2843.1	2883.3	2895.5	2894.1	2892.7
32.5°	2694.8	2765.9	2779.7	2768.5	2740.8	2717.4	2693.0
35°	2642.4	2589.4	2510.2	2408.1	2333.0	2257.1	2249.8
37.5°	2376.4	2206.9	2075.1	1927.9	1842.9	1790.4	1754.2
40°	2126.2	1933.6	1773.9	1649.8	1563.1	1529.0	1495.4
42.5°	1854.6	1670.5	1529.0	1425.3	1360.2	1322.2	1295.6
45°	1506.8	1344.4	1233.6	1158.5	1106.7	1077.2	1060.4
47.5°	1234.7	1114.6	1020.5	966.2	930.5	907.6	907.7
50°	1088.6	973.9	911.5	868.5	837.6	819.5	822.9
52.5°	959.2	873.5	820.2	784.2	761.4	750.2	749.8
55°	802.0	740.3	705.4	679.2	663.7	651.0	653.8
57.5°	686.0	634.0	610.6	588.9	578.2	573.1	565.7
60°	614.2	573.9	553.7	536.2	525.6	521.5	514.1
62.5°	550.3	518.6	498.9	484.7	475.0	473.7	468.0
65°	462.4	438.2	420.9	414.1	404.1	401.4	401.4
67.5°	381.3	363.9	350.3	344.1	339.8	340.4	337.2
70°	330.2	316.2	307.4	300.7	297.3	298.0	295.3
72.5°	288.9	273.2	265.5	261.5	257.1	258.8	257.7
75°	218.8	210.8	206.7	202.7	200.0	198.6	197.3
77.5°	160.7	153.6	150.5	148.2	148.6	145.3	147.9
80°	124.2	118.1	116.1	112.8	112.1	112.1	111.4
82.5°	90.8	87.5	86.0	83.3	82.1	83.1	81.4
85°	47.0	44.3	43.7	43.7	42.3	41.0	44.3
87.5°	21.5	19.6	19.8	19.4	19.5	19.2	18.3
90°	21.5	22.8	23.8	24.5	25.2	26.0	26.8
92.5°	21.5	22.8	23.6	23.9	24.3	24.6	25.0
95°	21.5	22.8	23.4	23.4	23.4	23.4	23.4
97.5°	33.9	26.9	23.4	23.4	23.4	23.4	23.4
100°	83.3	46.3	27.4	26.3	25.4	24.4	23.4
102.5°	226.5	219.6	207.6	190.8	173.9	157.0	140.3
105°	332.2	332.2	332.1	331.8	331.6	331.3	331.1
107.5°	420.7	420.7	420.3	419.6	418.9	418.1	417.4
110°	477.2	476.4	476.1	476.4	476.6	476.9	477.2



TEST NUMBER: P333478-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	533.6	532.7	532.0	531.7	531.3	531.0	530.6
115°	619.1	618.1	616.8	615.4	613.9	612.3	610.9
117.5°	701.4	700.1	699.0	698.4	697.8	697.2	696.5
120°	755.4	754.9	754.1	752.9	751.6	750.4	749.2
122.5°	806.2	805.8	804.8	803.4	801.9	800.5	799.1
125°	879.9	878.9	878.0	877.4	876.6	875.8	875.1
127.5°	948.1	947.6	946.4	944.6	942.8	940.9	939.1
130°	992.1	991.4	990.4	989.2	987.9	986.7	985.5
132.5°	1034.1	1033.9	1033.2	1032.0	1030.8	1029.5	1028.3
135°	1094.3	1093.8	1092.9	1091.4	1089.9	1088.4	1086.9
137.5°	1151.4	1151.5	1150.9	1149.6	1148.3	1147.0	1145.7
140°	1186.5	1187.0	1186.5	1185.0	1183.5	1182.1	1180.5
142.5°	1220.1	1220.2	1219.5	1218.0	1216.5	1215.0	1213.6
145°	1268.3	1268.5	1267.9	1266.4	1264.9	1263.4	1262.0
147.5°	1309.4	1309.8	1309.0	1307.2	1305.4	1303.6	1301.8
150°	1335.8	1336.4	1335.6	1333.6	1331.6	1329.6	1327.7
152.5°	1359.1	1359.5	1358.9	1357.1	1355.4	1353.6	1351.8
155°	1391.2	1392.0	1391.4	1389.4	1387.4	1385.4	1383.5
157.5°	1417.7	1418.5	1417.9	1415.9	1413.9	1412.0	1410.0
160°	1434.3	1435.4	1434.9	1432.9	1430.9	1428.9	1426.9
162.5°	1449.8	1451.2	1450.8	1448.6	1446.4	1444.2	1442.1
165°	1469.3	1470.8	1470.5	1468.5	1466.5	1464.6	1462.6
167.5°	1484.2	1486.0	1485.7	1483.5	1481.4	1479.1	1476.9
170°	1491.9	1493.9	1493.8	1491.6	1489.4	1487.1	1484.9
172.5°	1497.6	1499.3	1499.2	1496.9	1494.7	1492.5	1490.2
175°	1504.2	1506.1	1506.1	1503.8	1501.6	1499.3	1497.1
177.5°	1506.2	1507.6	1507.5	1505.9	1504.3	1502.7	1501.2
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8

(END OF REPORT)