

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333393-830

Luminaire Tested: **S125DIW-S610D1340U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333393-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D1340U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6742.9 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333393-830

CATALOG NUMBER: S125DIW-S610D1340U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333393-830

CATALOG NUMBER: S125DIW-S610D1340U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35
1	94	90	86	83	85	82	78	75	66	63	61	51	49	48	37	36	36	29
2	86	79	73	68	77	71	66	62	57	54	51	45	42	40	33	31	30	25
3	78	69	62	56	70	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	53	47	64	55	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	40	59	49	42	37	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	27	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5846	5846	5846
5°	5859	5803	5841
10°	5823	5762	5795
15°	5760	5693	5717
20°	5670	5597	5606
25°	5573	5481	5476
30°	5452	5357	5330
35°	5324	5222	5149
40°	5193	5078	5005
45°	5050	4945	4847
50°	4893	4786	4641
55°	4741	4604	4476
60°	4561	4421	4265
65°	4345	4202	4060
70°	4137	3950	3814
75°	3770	3646	3521
80°	3355	3303	3221
85°	2920	2971	2816



TEST NUMBER: P333393-830

CATALOG NUMBER: S125DIW-S610D1340U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.3	1.3
10°-20°	241.1	3.6
20°-30°	356.0	5.3
30°-40°	415.4	6.2
40°-50°	417.2	6.2
50°-60°	366.2	5.4
60°-70°	272.9	4.0
70°-80°	156.0	2.3
80°-90°	48.8	0.7
90°-100°	105.2	1.6
100°-110°	310.7	4.6
110°-120°	526.3	7.8
120°-130°	692.7	10.3
130°-140°	776.1	11.5
140°-150°	760.7	11.3
150°-160°	638.9	9.5
160°-170°	424.7	6.3
170°-180°	148.6	2.2
0°-30°	682.4	10.1
0°-40°	1097.8	16.3
0°-60°	1881.2	27.9
0°-90°	2358.9	35.0
90°-120°	942.3	14.0
90°-150°	3171.8	47.0
90°-180°	4384.0	65.0
0°-180°	6742.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	905	905	905	905	905	
5°	904	902	895	901	901	86
15°	862	859	852	855	855	243
25°	782	778	769	770	768	360
35°	675	672	662	659	653	422
45°	553	550	541	533	531	426
55°	421	418	409	403	398	376
65°	284	282	275	269	266	282
75°	151	150	146	144	141	161
85°	39	40	40	39	38	44
90°	1	11	20	26	29	7
95°	80	82	94	102	105	85
105°	279	285	292	299	303	298
115°	527	532	534	533	532	521
125°	769	776	778	775	774	688
135°	1000	1007	1009	1008	1004	771
145°	1212	1216	1220	1220	1216	757
155°	1386	1387	1388	1392	1386	638
165°	1508	1505	1506	1510	1504	425
175°	1567	1563	1562	1569	1561	149
180°	1571	1571	1571	1571	1571	



TEST NUMBER: P333393-830

CATALOG NUMBER: S125DIW-S610D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2
2.5°	907.5	907.1	906.7	906.3	906.0	905.1	903.9	902.6	901.4	900.0	901.4
5°	903.8	903.4	903.1	902.8	902.5	901.5	899.9	898.3	896.7	895.1	896.6
7.5°	895.4	895.1	894.8	894.5	894.2	893.2	891.4	889.7	887.9	886.2	887.5
10°	888.0	887.7	887.4	887.0	886.7	885.7	883.9	882.2	880.4	878.7	880.0
12.5°	878.8	878.3	877.7	877.1	876.6	875.4	873.8	872.2	870.5	868.9	870.0
15°	861.5	861.0	860.5	860.1	859.6	858.5	856.8	855.0	853.2	851.5	852.2
17.5°	841.6	840.9	840.2	839.5	838.8	837.5	835.8	833.9	832.1	830.3	831.2
20°	825.0	824.6	824.3	824.1	823.7	822.6	820.5	818.4	816.3	814.3	815.4
22.5°	808.3	807.8	807.2	806.6	806.1	804.8	802.9	801.0	799.0	797.0	797.8
25°	782.0	781.2	780.4	779.7	778.8	777.4	775.3	773.3	771.2	769.1	769.5
27.5°	751.2	750.7	750.3	749.8	749.3	748.0	745.8	743.8	741.6	739.5	739.5
30°	731.1	730.7	730.2	729.7	729.2	727.8	725.5	723.0	720.7	718.3	717.9
32.5°	709.4	708.7	707.9	707.2	706.4	705.0	702.9	700.8	698.6	696.5	696.0
35°	675.3	674.7	674.0	673.4	672.8	671.4	669.1	666.8	664.7	662.4	661.7
37.5°	639.9	639.1	638.4	637.5	636.8	635.3	633.2	631.1	629.0	626.9	625.8
40°	615.9	615.1	614.3	613.5	612.7	611.1	609.0	606.7	604.5	602.3	600.9
42.5°	590.1	589.5	588.7	588.1	587.4	586.0	583.7	581.5	579.3	577.0	575.8
45°	552.9	552.2	551.6	550.9	550.4	549.0	547.1	545.3	543.3	541.4	539.5
47.5°	512.7	512.7	512.8	512.8	512.8	511.7	509.4	507.2	504.9	502.6	500.7
50°	487.0	486.4	486.0	485.5	485.0	483.9	481.9	480.0	478.2	476.3	474.2
52.5°	460.6	460.2	460.0	459.6	459.2	458.0	456.0	453.9	451.9	449.9	448.1
55°	421.1	420.6	420.1	419.6	419.1	417.8	415.6	413.4	411.1	408.9	407.5
57.5°	379.4	379.2	378.9	378.6	378.4	377.3	375.4	373.5	371.6	369.9	368.0
60°	353.1	352.4	351.8	351.1	350.5	349.3	347.6	345.8	344.0	342.3	340.7
62.5°	325.6	325.1	324.5	324.0	323.5	322.5	321.0	319.5	318.0	316.5	314.8
65°	284.3	284.0	283.7	283.3	283.0	282.0	280.2	278.5	276.7	275.0	273.5
67.5°	244.3	243.6	243.0	242.3	241.7	240.7	239.4	238.1	236.8	235.4	234.2
70°	219.1	218.4	217.5	216.8	215.9	214.8	213.4	212.0	210.6	209.2	208.1
72.5°	191.6	191.1	190.6	190.0	189.5	188.7	187.8	186.9	186.0	185.0	184.0
75°	151.1	150.8	150.4	150.1	149.9	149.3	148.5	147.7	146.8	146.1	145.6
77.5°	113.8	113.6	113.5	113.3	113.2	112.9	112.4	112.1	111.6	111.1	110.8
80°	90.2	90.2	90.2	90.2	90.2	90.1	89.7	89.4	89.2	88.8	88.6
82.5°	69.7	69.4	69.1	68.8	68.6	68.4	68.3	68.3	68.2	68.1	67.9
85°	39.4	39.6	39.7	39.9	40.1	40.1	40.1	40.1	40.1	40.1	40.0
87.5°	15.7	16.1	16.6	17.1	17.4	17.8	18.0	18.3	18.6	18.9	19.0
90°	1.2	3.4	5.6	7.7	9.9	12.0	13.9	15.7	17.6	19.6	20.9
92.5°	29.6	31.1	32.6	34.1	35.6	37.6	40.0	42.3	44.6	46.9	48.7
95°	79.5	80.0	80.6	81.1	81.6	83.3	86.0	88.7	91.4	94.2	96.0
97.5°	132.1	132.2	132.5	132.7	132.9	134.9	138.6	142.4	146.2	149.9	151.7
100°	171.2	171.2	171.2	171.2	171.2	173.0	176.4	180.0	183.5	187.1	189.5
102.5°	213.2	214.3	215.4	216.5	217.5	219.0	220.8	222.6	224.4	226.2	228.8
105°	278.8	280.1	281.4	282.9	284.2	285.7	287.3	289.0	290.6	292.2	293.9
107.5°	351.1	352.5	353.8	355.2	356.6	357.9	359.1	360.3	361.7	362.9	363.7
110°	401.1	402.4	403.8	405.1	406.4	407.6	408.4	409.2	410.0	410.8	411.6



TEST NUMBER: P333393-830

CATALOG NUMBER: S125DIW-S610D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	451.9	452.6	453.3	454.0	454.7	455.6	456.6	457.6	458.6	459.7	460.1
115°	527.0	528.0	529.1	530.2	531.3	532.2	532.6	533.2	533.8	534.3	534.0
117.5°	602.3	602.8	603.2	603.7	604.3	604.7	605.2	605.7	606.1	606.7	606.9
120°	649.2	650.5	652.0	653.3	654.7	655.4	655.7	656.0	656.3	656.6	656.6
122.5°	700.1	700.6	701.1	701.5	702.0	702.7	703.3	704.1	704.7	705.5	705.2
125°	769.0	770.6	772.3	773.9	775.5	776.5	776.7	777.0	777.3	777.6	777.0
127.5°	842.4	843.3	844.2	845.2	846.1	846.7	847.1	847.3	847.7	848.0	847.7
130°	886.4	887.8	889.1	890.5	891.8	892.8	893.3	893.9	894.4	894.9	894.7
132.5°	930.4	932.6	934.9	937.1	939.3	940.4	940.3	940.2	940.1	940.0	939.7
135°	1000.1	1001.7	1003.3	1005.0	1006.6	1007.6	1007.9	1008.1	1008.4	1008.7	1008.7
137.5°	1065.6	1067.2	1068.8	1070.4	1072.0	1073.0	1073.7	1074.2	1074.9	1075.4	1075.7
140°	1107.7	1109.1	1110.4	1111.8	1113.1	1114.2	1115.0	1115.9	1116.6	1117.5	1118.0
142.5°	1149.8	1150.9	1152.1	1153.2	1154.3	1155.4	1156.4	1157.4	1158.5	1159.5	1159.9
145°	1211.6	1212.7	1213.8	1214.8	1216.0	1216.9	1217.8	1218.5	1219.4	1220.2	1220.2
147.5°	1268.9	1269.4	1270.1	1270.6	1271.2	1271.9	1272.5	1273.2	1273.8	1274.5	1275.2
150°	1307.0	1306.7	1306.5	1306.2	1305.9	1306.3	1307.4	1308.5	1309.6	1310.7	1310.7
152.5°	1338.3	1338.7	1339.1	1339.4	1339.8	1340.2	1340.7	1341.0	1341.5	1342.0	1342.7
155°	1386.5	1386.5	1386.5	1386.5	1386.5	1386.6	1386.9	1387.1	1387.4	1387.7	1388.7
157.5°	1429.5	1428.9	1428.3	1427.7	1427.1	1426.9	1427.2	1427.5	1427.8	1428.0	1429.1
160°	1454.9	1454.2	1453.3	1452.5	1451.7	1451.4	1451.7	1452.0	1452.2	1452.5	1453.6
162.5°	1477.4	1476.9	1476.2	1475.6	1475.1	1474.8	1474.8	1474.9	1474.9	1475.0	1476.3
165°	1507.5	1506.9	1506.4	1505.9	1505.3	1505.2	1505.4	1505.7	1506.0	1506.3	1507.4
167.5°	1533.0	1531.8	1530.8	1529.7	1528.6	1528.0	1528.0	1528.0	1528.0	1528.0	1529.7
170°	1546.6	1545.6	1544.5	1543.4	1542.3	1541.7	1541.7	1541.7	1541.7	1541.7	1543.4
172.5°	1556.4	1555.3	1554.3	1553.1	1552.1	1551.5	1551.5	1551.5	1551.5	1551.5	1553.1
175°	1567.4	1566.3	1565.3	1564.1	1563.1	1562.5	1562.5	1562.5	1562.5	1562.5	1564.1
177.5°	1573.0	1572.2	1571.3	1570.5	1569.5	1569.1	1568.8	1568.6	1568.4	1568.1	1569.4
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333393-830

CATALOG NUMBER: S125DIW-S610D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	905.2	905.2	905.2	905.2	905.2	905.2	905.2	905.2
2.5°	902.6	903.9	905.1	905.7	905.6	905.4	905.3	905.2
5°	898.1	899.5	900.9	901.5	901.4	901.3	901.1	900.9
7.5°	888.9	890.3	891.7	892.4	892.2	892.0	891.9	891.7
10°	881.3	882.5	883.8	884.4	884.2	884.0	883.8	883.7
12.5°	871.0	872.0	873.0	873.5	873.5	873.5	873.5	873.4
15°	853.1	853.8	854.7	855.1	855.1	855.1	855.1	855.1
17.5°	832.3	833.2	834.2	834.3	833.5	832.7	832.0	831.1
20°	816.4	817.6	818.7	818.9	818.0	817.3	816.4	815.7
22.5°	798.5	799.3	800.0	800.1	799.6	799.0	798.4	798.0
25°	769.8	770.1	770.4	770.3	769.9	769.4	768.9	768.5
27.5°	739.6	739.7	739.7	739.5	739.0	738.6	738.1	737.6
30°	717.7	717.4	717.0	716.6	716.1	715.7	715.2	714.7
32.5°	695.4	694.7	694.2	693.5	692.7	691.8	690.9	690.0
35°	660.8	660.1	659.2	658.2	657.0	655.6	654.4	653.1
37.5°	624.5	623.4	622.2	621.2	620.5	619.8	619.1	618.3
40°	599.4	597.9	596.5	595.6	595.1	594.7	594.2	593.7
42.5°	574.5	573.2	571.8	570.8	570.0	569.4	568.6	567.9
45°	537.5	535.6	533.8	532.5	532.1	531.6	531.1	530.7
47.5°	498.7	496.7	494.8	493.3	492.2	491.1	489.9	488.8
50°	472.1	470.0	468.0	466.4	465.2	464.1	463.0	461.9
52.5°	446.2	444.4	442.6	441.1	439.9	438.6	437.3	436.1
55°	406.0	404.6	403.2	401.9	400.8	399.6	398.6	397.5
57.5°	366.1	364.3	362.4	361.2	360.6	360.0	359.4	358.8
60°	339.1	337.5	335.9	334.6	333.5	332.3	331.2	330.2
62.5°	313.1	311.4	309.6	308.4	307.6	306.6	305.8	304.9
65°	272.1	270.7	269.3	268.2	267.6	266.9	266.4	265.7
67.5°	233.1	231.9	230.6	229.8	229.4	229.0	228.7	228.3
70°	207.2	206.2	205.3	204.5	203.9	203.2	202.6	202.0
72.5°	182.9	181.8	180.7	179.8	179.2	178.6	178.0	177.3
75°	145.2	144.7	144.2	143.6	143.0	142.3	141.8	141.1
77.5°	110.6	110.3	110.0	109.6	109.1	108.8	108.3	107.8
80°	88.5	88.3	88.1	87.9	87.6	87.3	87.0	86.6
82.5°	67.6	67.3	67.0	66.8	66.8	66.7	66.6	66.6
85°	39.8	39.6	39.5	39.2	38.9	38.5	38.3	38.0
87.5°	19.3	19.6	19.9	20.0	19.9	19.8	19.7	19.6
90°	22.2	23.7	25.0	26.1	26.9	27.7	28.6	29.3
92.5°	50.5	52.3	54.1	55.3	55.9	56.6	57.1	57.7
95°	97.9	99.8	101.8	102.9	103.5	104.1	104.6	105.2
97.5°	153.4	155.2	157.0	158.2	158.4	158.8	159.1	159.5
100°	192.0	194.4	196.8	198.3	198.9	199.4	200.0	200.5
102.5°	231.5	234.1	236.9	238.6	239.3	240.1	240.8	241.6
105°	295.5	297.1	298.7	299.9	300.8	301.6	302.4	303.2
107.5°	364.5	365.3	366.2	366.6	366.5	366.4	366.4	366.3
110°	412.5	413.2	414.1	414.3	414.1	413.8	413.5	413.2



TEST NUMBER: P333393-830

CATALOG NUMBER: S125DIW-S610D1340U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	460.4	460.8	461.2	461.2	460.7	460.2	459.7	459.2
115°	533.8	533.5	533.2	532.9	532.6	532.3	532.2	531.9
117.5°	607.1	607.3	607.6	607.1	606.1	604.9	603.9	602.8
120°	656.6	656.6	656.6	656.0	654.9	653.8	652.7	651.7
122.5°	705.0	704.8	704.6	704.1	703.1	702.3	701.4	700.6
125°	776.5	776.0	775.4	775.1	774.8	774.5	774.2	773.9
127.5°	847.4	847.2	847.0	846.5	846.0	845.5	844.9	844.3
130°	894.4	894.2	893.9	893.4	893.0	892.4	891.8	891.3
132.5°	939.4	939.1	938.9	938.4	937.6	936.8	936.0	935.3
135°	1008.7	1008.7	1008.7	1008.1	1007.0	1006.0	1004.8	1003.8
137.5°	1076.1	1076.4	1076.8	1076.2	1074.9	1073.5	1072.1	1070.8
140°	1118.6	1119.1	1119.6	1119.3	1117.9	1116.5	1115.2	1113.8
142.5°	1160.2	1160.6	1160.8	1160.4	1159.0	1157.6	1156.2	1154.9
145°	1220.2	1220.2	1220.2	1219.7	1219.0	1218.1	1217.3	1216.5
147.5°	1275.7	1276.4	1277.1	1276.5	1274.6	1272.8	1270.9	1269.1
150°	1310.7	1310.7	1310.7	1310.4	1309.9	1309.3	1308.7	1308.2
152.5°	1343.2	1343.9	1344.5	1344.4	1343.4	1342.5	1341.4	1340.5
155°	1389.9	1390.9	1392.0	1391.9	1390.5	1389.2	1387.8	1386.5
157.5°	1430.2	1431.3	1432.4	1432.0	1430.2	1428.4	1426.6	1424.8
160°	1454.6	1455.8	1456.8	1456.7	1455.4	1454.0	1452.6	1451.2
162.5°	1477.6	1478.8	1480.2	1480.1	1478.5	1476.9	1475.4	1473.8
165°	1508.4	1509.6	1510.6	1510.3	1508.7	1507.1	1505.4	1503.8
167.5°	1531.3	1533.0	1534.6	1534.6	1532.9	1531.2	1529.5	1527.8
170°	1545.0	1546.6	1548.2	1548.1	1546.2	1544.4	1542.4	1540.5
172.5°	1554.8	1556.4	1558.0	1558.0	1556.3	1554.6	1552.9	1551.2
175°	1565.8	1567.4	1569.1	1568.9	1567.0	1565.1	1563.2	1561.3
177.5°	1570.7	1572.1	1573.4	1573.3	1571.7	1570.2	1568.7	1567.2
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1

(END OF REPORT)