

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333412-830

Luminaire Tested: **S125DIW-S850D1050U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333412-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1050U830-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1050 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7205.4 lumens  
Efficiency: N/A  
Efficacy: 137.0 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38				
2	88	81	75	70	81	75	69	65	62	59	55	51	49	46	41	39	37	33				
3	81	71	64	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28				
4	74	63	56	50	67	58	52	46	49	44	40	40	37	34	32	30	28	24				
5	68	56	48	43	62	52	45	40	44	39	34	36	32	29	29	26	24	21				
6	62	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21	18				
7	58	46	38	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16				
8	54	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	15				
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	17	15	13				
10	46	35	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	7447	7447	7447	7447
5°	8624	7472	6543	7472
10°	10033	7433	5732	7433
15°	11106	7379	5288	7379
20°	12432	7292	4931	7292
25°	14564	7195	4757	7195
30°	15731	7099	4606	7099
35°	12934	6918	4507	6918
40°	9193	6668	4398	6668
45°	7063	6330	4337	6330
50°	6028	5910	4326	5910
55°	5368	5499	4365	5499
60°	4841	5052	4476	5052
65°	4473	4600	4592	4600
70°	4067	4132	4658	4132
75°	3591	3638	4616	3638
80°	3020	2964	4225	2964
85°	2393	2134	3409	2134



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	111.0	1.5
10°-20°	330.5	4.6
20°-30°	536.7	7.4
30°-40°	654.6	9.1
40°-50°	595.5	8.3
50°-60°	474.4	6.6
60°-70°	330.4	4.6
70°-80°	176.2	2.4
80°-90°	47.1	0.7
90°-100°	46.7	0.6
100°-110°	288.0	4.0
110°-120°	522.3	7.2
120°-130°	670.4	9.3
130°-140°	721.0	10.0
140°-150°	676.8	9.4
150°-160°	547.5	7.6
160°-170°	354.1	4.9
170°-180°	122.1	1.7
0°-30°	978.2	13.6
0°-40°	1632.8	22.7
0°-60°	2702.7	37.5
0°-90°	3256.4	45.2
90°-120°	857.1	11.9
90°-150°	2925.3	40.6
90°-180°	3949.0	54.8
0°-180°	7205.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1153	1153	1153	1153	1153	
5°	1330	1152	1009	1152	1330	134
15°	1661	1104	791	1104	1661	476
25°	2044	1010	668	1010	2044	934
35°	1640	878	572	878	1640	1004
45°	773	693	475	693	773	619
55°	477	488	388	488	477	429
65°	293	301	300	301	293	290
75°	144	146	185	146	144	155
85°	32	29	46	29	32	38
90°	23	1	23	1	23	11
95°	20	54	20	54	20	17
105°	283	280	283	280	283	256
115°	522	526	522	526	522	519
125°	748	748	748	748	748	666
135°	929	933	929	933	929	717
145°	1079	1082	1079	1082	1079	674
155°	1183	1192	1183	1192	1183	545
165°	1251	1257	1251	1257	1251	353
175°	1280	1286	1280	1286	1280	122
180°	1286	1286	1286	1286	1286	



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1219.7	1218.0	1216.5	1213.3	1215.7	1209.1	1205.9	1200.4	1193.8	1191.5	1188.7
5°	1330.2	1332.7	1335.1	1324.8	1325.9	1319.0	1303.3	1290.6	1280.3	1267.2	1257.8
7.5°	1463.4	1457.5	1457.1	1450.5	1439.0	1429.8	1413.3	1392.4	1372.2	1349.1	1329.9
10°	1529.9	1530.4	1526.0	1518.2	1506.0	1497.1	1475.6	1455.0	1430.1	1400.7	1379.7
12.5°	1580.1	1582.1	1576.5	1565.9	1560.0	1540.2	1523.3	1498.9	1469.2	1445.8	1413.7
15°	1661.1	1655.7	1651.8	1638.6	1628.3	1607.8	1580.8	1555.4	1523.1	1493.2	1463.4
17.5°	1739.2	1743.5	1736.2	1724.1	1692.2	1668.2	1632.1	1597.2	1557.1	1517.0	1481.4
20°	1808.9	1812.8	1801.6	1780.6	1742.4	1718.3	1670.8	1625.9	1579.3	1528.0	1488.8
22.5°	1895.8	1892.7	1877.5	1845.5	1812.4	1768.1	1716.7	1661.9	1603.6	1545.6	1493.6
25°	2043.8	2023.3	2013.9	1974.3	1930.8	1865.7	1795.2	1715.0	1642.5	1565.7	1499.1
27.5°	2125.8	2119.4	2109.0	2081.4	2035.6	1966.0	1882.9	1785.1	1682.9	1585.9	1498.8
30°	2109.4	2110.4	2111.4	2102.5	2073.2	2020.8	1938.2	1832.9	1711.5	1602.3	1501.6
32.5°	1963.8	1981.6	1998.6	2018.7	2026.9	2016.9	1965.1	1870.1	1745.2	1621.2	1500.0
35°	1640.5	1646.0	1701.2	1756.1	1830.4	1888.2	1926.8	1884.8	1779.5	1637.1	1498.1
37.5°	1279.1	1305.6	1343.9	1405.8	1513.2	1609.3	1733.0	1789.8	1755.9	1642.3	1494.7
40°	1090.4	1114.9	1139.8	1203.0	1293.5	1410.0	1550.5	1670.4	1698.3	1625.9	1482.9
42.5°	944.8	964.1	991.8	1039.3	1115.0	1218.1	1352.4	1509.1	1605.5	1578.1	1458.3
45°	773.3	785.5	807.1	844.7	899.6	980.3	1098.7	1270.1	1419.3	1468.8	1399.8
47.5°	661.9	661.8	678.5	704.6	744.1	812.8	900.3	1034.5	1194.0	1311.9	1306.5
50°	600.0	597.6	610.8	633.3	664.6	710.1	793.8	901.0	1054.2	1187.8	1225.0
52.5°	546.8	547.1	555.2	571.8	598.0	637.0	699.5	796.1	927.0	1064.1	1134.2
55°	476.7	474.8	484.0	495.3	514.3	539.8	584.8	658.7	765.0	900.0	991.1
57.5°	412.5	417.8	421.6	429.4	445.3	462.3	500.3	554.5	638.8	754.7	850.9
60°	374.8	380.3	383.2	391.1	403.8	418.5	447.8	491.9	562.8	662.7	758.1
62.5°	341.2	345.4	346.4	353.5	363.8	378.1	401.2	438.2	494.3	581.6	675.1
65°	292.7	292.7	294.6	302.0	306.9	319.6	337.2	364.1	409.2	477.2	556.9
67.5°	245.9	248.3	247.7	251.0	255.5	265.3	278.0	300.2	333.6	383.2	447.0
70°	215.4	217.3	216.8	219.2	224.1	230.5	240.8	261.8	285.8	328.4	383.2
72.5°	187.9	188.7	187.5	190.7	193.6	199.2	210.7	221.9	244.3	280.2	325.3
75°	143.9	144.9	145.8	147.8	150.7	153.6	159.6	170.8	185.5	212.4	241.3
77.5°	107.8	106.0	108.4	108.1	109.7	112.0	117.2	123.1	135.2	152.2	174.6
80°	81.2	81.7	81.7	82.2	84.6	86.1	90.6	94.9	104.2	117.0	132.6
82.5°	59.3	60.6	59.9	60.7	62.8	63.8	66.3	69.8	75.3	85.3	96.6
85°	32.3	29.9	30.8	31.9	31.9	32.3	34.2	35.7	38.6	42.6	46.9
87.5°	13.9	14.6	14.9	14.8	15.0	14.9	16.2	16.0	17.0	17.9	19.2
90°	22.9	22.2	21.6	21.0	20.4	19.5	18.5	17.3	16.3	15.3	13.8
92.5°	21.4	21.0	20.7	20.5	20.2	19.5	18.5	17.3	16.3	15.3	13.9
95°	20.0	20.0	20.0	20.0	20.0	19.5	18.5	17.3	16.3	15.3	23.3
97.5°	20.0	20.0	20.0	20.0	20.0	23.0	28.9	35.0	40.9	46.9	62.9
100°	20.0	20.8	21.7	22.5	23.4	39.6	71.2	102.7	134.3	165.9	165.0
102.5°	119.9	134.3	148.7	163.2	177.6	187.8	193.7	199.6	205.7	211.6	211.1
105°	283.1	283.3	283.5	283.8	284.0	284.1	284.1	284.1	284.1	284.1	284.1
107.5°	356.9	357.5	358.2	358.8	359.5	359.8	359.7	359.7	359.6	359.6	359.1
110°	408.0	407.7	407.6	407.4	407.2	407.4	408.0	408.6	409.3	409.9	409.4



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	453.7	454.0	454.3	454.7	455.0	455.5	456.3	457.1	457.9	458.7	458.5
115°	522.4	523.7	524.9	526.2	527.4	528.5	529.3	530.2	531.0	531.9	531.7
117.5°	595.6	596.2	596.7	597.3	597.8	598.6	599.7	600.9	601.9	603.0	602.2
120°	640.6	641.7	642.7	643.8	644.8	645.5	646.0	646.4	646.9	647.2	646.6
122.5°	683.3	684.6	685.8	687.0	688.2	689.0	689.5	689.8	690.3	690.7	690.4
125°	748.3	748.9	749.6	750.3	750.8	751.6	752.4	753.3	754.1	755.0	755.0
127.5°	803.0	804.6	806.2	807.8	809.3	810.3	810.8	811.2	811.7	812.2	812.3
130°	842.7	843.8	844.8	845.8	846.9	847.7	848.4	849.0	849.7	850.3	850.1
132.5°	879.3	880.3	881.4	882.5	883.5	884.1	884.2	884.4	884.5	884.7	885.0
135°	929.4	930.7	932.0	933.2	934.5	935.4	935.8	936.2	936.6	937.1	937.5
137.5°	979.8	980.9	981.9	983.1	984.2	984.7	984.6	984.5	984.4	984.3	984.7
140°	1009.5	1010.8	1012.0	1013.3	1014.6	1015.0	1014.6	1014.2	1013.7	1013.3	1013.5
142.5°	1037.7	1039.0	1040.3	1041.5	1042.8	1043.4	1043.3	1043.2	1043.1	1043.0	1042.7
145°	1079.1	1080.3	1081.7	1082.9	1084.2	1084.7	1084.5	1084.3	1084.1	1083.8	1083.8
147.5°	1113.2	1114.7	1116.3	1117.8	1119.4	1119.9	1119.7	1119.5	1119.2	1118.9	1118.7
150°	1135.3	1137.0	1138.7	1140.4	1142.1	1142.7	1142.4	1141.9	1141.5	1141.0	1140.7
152.5°	1155.9	1157.4	1159.0	1160.5	1162.1	1162.5	1162.2	1161.7	1161.3	1160.8	1160.5
155°	1183.0	1184.7	1186.4	1188.1	1189.8	1190.3	1189.7	1189.0	1188.4	1187.8	1187.3
157.5°	1205.7	1207.4	1209.1	1210.8	1212.5	1213.0	1212.3	1211.6	1211.0	1210.2	1210.2
160°	1220.2	1221.9	1223.6	1225.3	1226.9	1227.4	1226.5	1225.7	1224.8	1224.0	1223.8
162.5°	1233.1	1235.0	1236.9	1238.7	1240.6	1241.0	1239.7	1238.6	1237.4	1236.1	1236.0
165°	1250.7	1252.4	1254.1	1255.7	1257.4	1257.6	1256.4	1255.1	1253.9	1252.5	1252.4
167.5°	1262.9	1264.8	1266.7	1268.6	1270.5	1270.7	1269.1	1267.6	1266.1	1264.6	1264.4
170°	1269.7	1271.7	1273.6	1275.4	1277.3	1277.5	1275.8	1274.1	1272.4	1270.7	1270.5
172.5°	1274.3	1276.2	1278.1	1280.1	1282.0	1282.1	1280.6	1279.1	1277.5	1276.0	1275.6
175°	1280.3	1282.1	1284.0	1285.9	1287.9	1288.0	1286.3	1284.6	1282.9	1281.2	1281.0
177.5°	1283.6	1285.1	1286.4	1287.7	1289.1	1289.2	1288.0	1286.8	1285.6	1284.4	1284.2
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1186.4	1183.6	1180.4	1175.0	1168.4	1164.8	1159.3	1155.8	1148.8	1142.9	1136.6
5°	1246.5	1233.8	1222.1	1206.9	1190.2	1179.5	1166.8	1152.5	1137.9	1122.8	1106.1
7.5°	1308.9	1286.4	1261.9	1235.6	1209.8	1186.2	1163.6	1141.3	1120.6	1095.5	1074.3
10°	1350.8	1322.4	1292.0	1256.3	1221.6	1191.3	1160.5	1133.5	1106.1	1076.8	1050.7
12.5°	1392.7	1354.9	1312.0	1272.8	1231.0	1194.4	1158.1	1123.7	1089.3	1056.8	1026.5
15°	1422.3	1388.9	1349.3	1293.5	1246.5	1196.2	1148.2	1103.6	1062.1	1025.9	987.7
17.5°	1441.7	1398.8	1356.3	1302.8	1241.1	1184.8	1130.5	1079.5	1032.6	986.7	949.9
20°	1445.3	1401.2	1356.7	1304.3	1241.1	1176.6	1122.3	1061.0	1010.7	963.2	918.1
22.5°	1444.1	1394.2	1345.7	1291.8	1230.2	1170.7	1105.0	1042.6	988.0	941.2	894.3
25°	1433.0	1379.7	1319.0	1264.7	1204.0	1140.9	1074.3	1009.7	953.9	900.5	854.0
27.5°	1423.8	1354.6	1285.9	1222.6	1163.9	1106.1	1042.4	976.2	914.4	860.3	816.4
30°	1412.5	1336.6	1259.2	1193.2	1133.0	1076.8	1016.5	952.0	887.3	834.4	787.5
32.5°	1402.3	1313.9	1232.3	1160.4	1096.6	1041.9	986.4	924.9	861.5	807.9	760.8
35°	1382.6	1280.3	1186.8	1105.6	1037.6	981.3	934.8	877.5	819.3	767.4	722.4
37.5°	1357.6	1236.2	1136.0	1050.7	976.2	916.9	873.6	829.6	773.7	723.8	683.1
40°	1338.0	1204.9	1098.7	1011.6	934.3	872.6	832.5	790.9	744.4	698.0	654.9
42.5°	1313.4	1176.8	1061.2	967.4	890.8	830.8	788.6	753.3	712.3	668.9	629.0
45°	1268.1	1125.7	1000.4	899.6	822.2	763.0	719.4	693.1	662.2	621.0	587.3
47.5°	1201.5	1064.3	934.7	830.7	750.8	696.0	655.2	629.8	608.0	577.5	546.9
50°	1142.3	1018.5	887.3	784.0	704.3	648.9	611.3	588.2	569.7	546.2	520.3
52.5°	1076.1	960.9	840.7	738.7	659.7	605.1	568.3	548.0	532.5	515.7	490.1
55°	971.0	873.2	761.6	664.6	591.7	538.4	506.1	488.4	475.7	463.0	447.3
57.5°	855.2	778.6	679.8	591.3	524.1	475.5	445.4	428.2	418.4	411.8	402.6
60°	773.7	708.2	623.0	542.2	476.7	433.7	404.3	391.1	382.8	377.3	370.5
62.5°	698.2	644.4	565.4	491.7	434.4	393.7	367.5	354.7	346.7	344.0	338.4
65°	586.8	545.3	480.1	419.0	370.0	335.3	313.2	301.0	296.1	293.1	293.7
67.5°	477.1	451.8	399.4	347.3	308.2	279.1	261.5	252.0	249.6	245.7	245.6
70°	410.1	391.1	347.0	301.5	266.7	244.2	228.6	218.8	216.3	214.3	213.9
72.5°	351.0	334.3	296.1	259.6	228.4	208.6	195.7	189.8	185.8	184.6	184.5
75°	263.8	254.5	224.1	195.3	173.7	160.0	151.3	145.8	142.9	142.4	142.9
77.5°	187.6	179.5	160.1	139.7	126.1	115.7	108.3	106.4	103.1	103.2	102.6
80°	140.9	135.5	123.4	107.2	96.0	87.1	83.2	79.7	78.8	77.3	78.8
82.5°	102.2	96.4	88.1	77.9	68.5	63.2	59.3	58.2	57.7	56.9	57.3
85°	50.4	50.9	46.0	38.2	34.2	31.3	28.8	28.8	28.4	27.9	28.4
87.5°	19.7	18.6	16.8	15.3	12.9	11.4	10.7	10.7	9.9	9.9	10.7
90°	12.3	10.8	9.3	7.7	6.0	4.3	2.6	0.9	2.6	4.3	6.0
92.5°	12.6	11.3	10.0	9.9	11.1	12.3	13.5	14.7	13.5	12.3	11.1
95°	31.4	39.4	47.4	51.8	52.4	53.1	53.7	54.3	53.7	53.1	52.4
97.5°	78.8	94.7	110.7	118.0	116.9	115.7	114.6	113.5	114.6	115.7	116.9
100°	164.2	163.3	162.5	161.7	161.1	160.4	159.9	159.2	159.9	160.4	161.1
102.5°	210.6	210.1	209.6	209.0	208.1	207.4	206.5	205.8	206.5	207.4	208.1
105°	284.1	284.1	284.1	283.6	282.8	281.9	281.1	280.2	281.1	281.9	282.8
107.5°	358.7	358.3	357.9	357.7	357.7	357.7	357.7	357.7	357.7	357.7	357.7
110°	409.1	408.6	408.2	408.0	408.0	408.0	408.0	408.0	408.0	408.0	408.0





TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	458.2	458.0	457.7	457.3	456.8	456.3	455.8	455.2	455.8	456.3	456.8
115°	531.5	531.3	531.0	530.5	529.3	528.3	527.3	526.2	527.3	528.3	529.3
117.5°	601.4	600.6	599.8	599.5	599.5	599.6	599.6	599.6	599.6	599.6	599.5
120°	646.0	645.4	644.7	644.5	644.7	644.9	645.2	645.4	645.2	644.9	644.7
122.5°	690.1	689.8	689.6	689.0	688.2	687.4	686.5	685.8	686.5	687.4	688.2
125°	755.0	755.0	755.0	754.2	752.7	751.3	749.8	748.3	749.8	751.3	752.7
127.5°	812.5	812.6	812.7	812.2	811.2	810.1	809.1	807.9	809.1	810.1	811.2
130°	849.9	849.7	849.4	848.9	847.7	846.7	845.6	844.6	845.6	846.7	847.7
132.5°	885.5	886.0	886.5	886.1	884.9	883.6	882.4	881.2	882.4	883.6	884.9
135°	937.9	938.3	938.8	938.3	937.1	935.8	934.5	933.2	934.5	935.8	937.1
137.5°	985.1	985.5	985.9	985.5	984.4	983.3	982.2	981.1	982.2	983.3	984.4
140°	1013.7	1014.0	1014.2	1014.1	1013.6	1013.2	1012.8	1012.4	1012.8	1013.2	1013.6
142.5°	1042.5	1042.2	1041.9	1041.6	1041.3	1041.1	1040.8	1040.6	1040.8	1041.1	1041.3
145°	1083.8	1083.8	1083.8	1083.6	1083.3	1082.8	1082.4	1081.9	1082.4	1082.8	1083.3
147.5°	1118.4	1118.1	1117.9	1117.9	1117.9	1118.0	1118.1	1118.1	1118.1	1118.0	1117.9
150°	1140.2	1139.8	1139.3	1139.3	1139.8	1140.2	1140.7	1141.0	1140.7	1140.2	1139.8
152.5°	1160.1	1159.6	1159.2	1159.4	1160.4	1161.3	1162.2	1163.2	1162.2	1161.3	1160.4
155°	1186.9	1186.5	1186.1	1186.5	1187.8	1189.0	1190.3	1191.6	1190.3	1189.0	1187.8
157.5°	1210.1	1210.1	1210.1	1210.4	1211.3	1212.0	1212.8	1213.5	1212.8	1212.0	1211.3
160°	1223.6	1223.3	1223.1	1223.7	1224.9	1226.2	1227.5	1228.8	1227.5	1226.2	1224.9
162.5°	1235.8	1235.6	1235.3	1235.9	1237.2	1238.4	1239.7	1241.0	1239.7	1238.4	1237.2
165°	1252.2	1252.0	1251.7	1252.3	1253.6	1254.8	1256.1	1257.4	1256.1	1254.8	1253.6
167.5°	1264.1	1263.9	1263.8	1264.3	1265.6	1267.0	1268.3	1269.5	1268.3	1267.0	1265.6
170°	1270.3	1270.1	1269.9	1270.5	1272.0	1273.5	1275.0	1276.4	1275.0	1273.5	1272.0
172.5°	1275.3	1274.9	1274.5	1275.1	1276.6	1278.0	1279.5	1281.0	1279.5	1278.0	1276.6
175°	1280.7	1280.5	1280.3	1280.8	1282.1	1283.4	1284.7	1285.9	1284.7	1283.4	1282.1
177.5°	1284.1	1283.9	1283.7	1284.2	1285.2	1286.2	1287.2	1288.3	1287.2	1286.2	1285.2
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1133.1	1128.8	1125.3	1117.5	1113.1	1107.3	1102.6	1107.7	1102.2	1104.6	1101.0
5°	1097.8	1084.1	1074.3	1060.1	1047.8	1036.6	1028.3	1026.8	1022.8	1021.0	1015.0
7.5°	1055.3	1038.1	1021.3	1002.8	987.0	971.1	960.9	952.5	947.0	939.6	934.6
10°	1030.2	1007.2	987.7	965.2	945.6	928.4	914.7	907.9	901.5	892.2	888.8
12.5°	999.3	975.5	951.6	927.6	908.8	889.7	877.9	867.5	863.2	852.6	851.6
15°	962.2	926.5	903.0	878.5	852.5	836.9	827.1	815.9	811.0	803.6	798.2
17.5°	917.9	886.1	856.7	831.3	809.1	795.9	783.7	776.0	767.6	762.8	754.0
20°	885.9	855.5	826.1	799.2	782.1	766.9	757.1	749.8	741.0	738.6	729.7
22.5°	858.8	825.4	797.2	774.6	755.8	738.8	728.1	723.2	717.1	709.5	707.8
25°	814.9	780.1	756.2	733.7	717.0	701.3	694.0	687.7	681.7	676.4	674.4
27.5°	776.9	745.8	717.4	697.0	682.6	668.3	661.8	654.0	649.8	645.5	640.2
30°	750.3	718.5	693.5	673.9	658.3	645.5	638.7	633.3	629.4	625.5	622.5
32.5°	722.8	693.4	669.2	650.1	634.4	624.8	618.7	614.9	610.6	605.9	602.2
35°	686.6	654.3	630.8	614.3	602.0	594.7	587.8	584.4	579.5	579.5	575.5
37.5°	645.8	617.9	597.2	582.0	571.1	564.5	557.0	554.7	551.6	549.5	548.2
40°	621.6	595.6	576.1	560.9	549.1	543.8	537.9	534.0	532.0	529.5	528.6
42.5°	596.5	571.7	553.0	538.9	528.8	524.1	518.7	515.9	512.0	508.8	508.2
45°	558.5	534.4	517.4	506.1	497.3	491.9	488.4	482.6	480.6	476.7	476.2
47.5°	522.3	499.3	482.5	473.3	465.5	461.1	455.7	449.9	447.6	445.6	445.4
50°	495.3	474.3	458.5	449.8	442.4	436.1	430.6	426.8	425.3	425.3	426.3
52.5°	467.9	450.0	436.7	425.9	419.0	412.2	407.2	404.8	402.6	404.9	406.7
55°	427.7	409.6	399.8	389.6	382.8	374.8	372.5	371.5	370.0	373.9	375.9
57.5°	385.3	372.6	361.1	350.9	344.8	340.3	337.0	336.3	339.0	340.9	347.3
60°	358.3	343.6	333.3	325.5	318.1	315.2	314.2	313.2	315.2	320.6	328.9
62.5°	328.5	316.6	305.5	299.6	294.3	289.4	289.2	289.7	293.7	299.8	308.1
65°	284.8	274.6	267.2	260.3	256.0	253.1	254.0	256.0	260.3	268.7	278.0
67.5°	240.5	233.5	226.9	221.3	217.1	217.1	218.1	221.0	226.2	235.8	244.3
70°	211.9	204.1	198.7	196.2	192.8	190.9	193.8	198.7	203.1	211.9	219.2
72.5°	183.3	176.7	172.5	170.8	169.4	167.8	168.7	174.0	180.0	188.8	197.4
75°	140.9	138.5	135.5	133.7	132.1	133.1	134.1	139.0	143.9	153.2	163.0
77.5°	102.8	100.3	98.6	98.1	97.3	97.7	100.6	104.2	109.0	115.7	123.1
80°	77.9	76.8	75.9	75.4	75.4	75.9	79.7	82.2	86.6	93.0	98.9
82.5°	56.6	56.1	55.9	55.8	56.2	56.3	58.6	61.8	65.5	70.3	75.4
85°	29.9	28.8	30.3	30.8	29.9	31.3	32.3	34.2	35.7	38.2	40.6
87.5°	11.3	12.4	12.3	13.0	13.3	14.4	14.2	16.0	17.0	18.0	17.8
90°	7.7	9.3	10.8	12.3	13.8	15.3	16.3	17.3	18.5	19.5	20.4
92.5°	9.9	10.0	11.3	12.6	13.9	15.3	16.3	17.3	18.5	19.5	20.2
95°	51.8	47.4	39.4	31.4	23.3	15.3	16.3	17.3	18.5	19.5	20.0
97.5°	118.0	110.7	94.7	78.8	62.9	46.9	40.9	35.0	28.9	23.0	20.0
100°	161.7	162.5	163.3	164.2	165.0	165.9	134.3	102.7	71.2	39.6	23.4
102.5°	209.0	209.6	210.1	210.6	211.1	211.6	205.7	199.6	193.7	187.8	177.6
105°	283.6	284.1	284.1	284.1	284.1	284.1	284.1	284.1	284.1	284.1	284.0
107.5°	357.7	357.9	358.3	358.7	359.1	359.6	359.6	359.7	359.7	359.8	359.5
110°	408.0	408.2	408.6	409.1	409.4	409.9	409.3	408.6	408.0	407.4	407.2



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	457.3	457.7	458.0	458.2	458.5	458.7	457.9	457.1	456.3	455.5	455.0
115°	530.5	531.0	531.3	531.5	531.7	531.9	531.0	530.2	529.3	528.5	527.4
117.5°	599.5	599.8	600.6	601.4	602.2	603.0	601.9	600.9	599.7	598.6	597.8
120°	644.5	644.7	645.4	646.0	646.6	647.2	646.9	646.4	646.0	645.5	644.8
122.5°	689.0	689.6	689.8	690.1	690.4	690.7	690.3	689.8	689.5	689.0	688.2
125°	754.2	755.0	755.0	755.0	755.0	755.0	754.1	753.3	752.4	751.6	750.8
127.5°	812.2	812.7	812.6	812.5	812.3	812.2	811.7	811.2	810.8	810.3	809.3
130°	848.9	849.4	849.7	849.9	850.1	850.3	849.7	849.0	848.4	847.7	846.9
132.5°	886.1	886.5	886.0	885.5	885.0	884.7	884.5	884.4	884.2	884.1	883.5
135°	938.3	938.8	938.3	937.9	937.5	937.1	936.6	936.2	935.8	935.4	934.5
137.5°	985.5	985.9	985.5	985.1	984.7	984.3	984.4	984.5	984.6	984.7	984.2
140°	1014.1	1014.2	1014.0	1013.7	1013.5	1013.3	1013.7	1014.2	1014.6	1015.0	1014.6
142.5°	1041.6	1041.9	1042.2	1042.5	1042.7	1043.0	1043.1	1043.2	1043.3	1043.4	1042.8
145°	1083.6	1083.8	1083.8	1083.8	1083.8	1083.8	1084.1	1084.3	1084.5	1084.7	1084.2
147.5°	1117.9	1117.9	1118.1	1118.4	1118.7	1118.9	1119.2	1119.5	1119.7	1119.9	1119.4
150°	1139.3	1139.3	1139.8	1140.2	1140.7	1141.0	1141.5	1141.9	1142.4	1142.7	1142.1
152.5°	1159.4	1159.2	1159.6	1160.1	1160.5	1160.8	1161.3	1161.7	1162.2	1162.5	1162.1
155°	1186.5	1186.1	1186.5	1186.9	1187.3	1187.8	1188.4	1189.0	1189.7	1190.3	1189.8
157.5°	1210.4	1210.1	1210.1	1210.1	1210.2	1210.2	1211.0	1211.6	1212.3	1213.0	1212.5
160°	1223.7	1223.1	1223.3	1223.6	1223.8	1224.0	1224.8	1225.7	1226.5	1227.4	1226.9
162.5°	1235.9	1235.3	1235.6	1235.8	1236.0	1236.1	1237.4	1238.6	1239.7	1241.0	1240.6
165°	1252.3	1251.7	1252.0	1252.2	1252.4	1252.5	1253.9	1255.1	1256.4	1257.6	1257.4
167.5°	1264.3	1263.8	1263.9	1264.1	1264.4	1264.6	1266.1	1267.6	1269.1	1270.7	1270.5
170°	1270.5	1269.9	1270.1	1270.3	1270.5	1270.7	1272.4	1274.1	1275.8	1277.5	1277.3
172.5°	1275.1	1274.5	1274.9	1275.3	1275.6	1276.0	1277.5	1279.1	1280.6	1282.1	1282.0
175°	1280.8	1280.3	1280.5	1280.7	1281.0	1281.2	1282.9	1284.6	1286.3	1288.0	1287.9
177.5°	1284.2	1283.7	1283.9	1284.1	1284.2	1284.4	1285.6	1286.8	1288.0	1289.2	1289.1
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1098.6	1101.4	1099.0	1102.2	1099.0	1101.4	1098.6	1101.0	1104.6	1102.2	1107.7
5°	1012.6	1008.2	1011.2	1009.2	1011.2	1008.2	1012.6	1015.0	1021.0	1022.8	1026.8
7.5°	933.1	928.9	924.2	921.9	924.2	928.9	933.1	934.6	939.6	947.0	952.5
10°	883.4	878.0	877.5	874.1	877.5	878.0	883.4	888.8	892.2	901.5	907.9
12.5°	847.0	842.0	836.4	835.0	836.4	842.0	847.0	851.6	852.6	863.2	867.5
15°	795.3	791.4	788.0	790.9	788.0	791.4	795.3	798.2	803.6	811.0	815.9
17.5°	752.3	749.1	748.5	744.9	748.5	749.1	752.3	754.0	762.8	767.6	776.0
20°	725.3	722.8	723.9	717.5	723.9	722.8	725.3	729.7	738.6	741.0	749.8
22.5°	703.8	699.0	698.4	697.1	698.4	699.0	703.8	707.8	709.5	717.1	723.2
25°	670.1	667.6	665.2	667.6	665.2	667.6	670.1	674.4	676.4	681.7	687.7
27.5°	640.6	637.6	637.0	637.3	637.0	637.6	640.6	640.2	645.5	649.8	654.0
30°	622.5	617.6	618.1	617.6	618.1	617.6	622.5	622.5	625.5	629.4	633.3
32.5°	602.9	599.6	599.0	598.0	599.0	599.6	602.9	602.2	605.9	610.6	614.9
35°	574.1	574.1	571.7	571.7	571.7	574.1	574.1	575.5	579.5	579.5	584.4
37.5°	547.0	546.5	545.0	545.3	545.0	546.5	547.0	548.2	549.5	551.6	554.7
40°	526.6	526.1	524.6	521.7	524.6	526.1	526.6	528.6	529.5	532.0	534.0
42.5°	507.0	505.4	504.7	503.7	504.7	505.4	507.0	508.2	508.8	512.0	515.9
45°	476.2	476.2	475.2	474.8	475.2	476.2	476.2	476.2	476.7	480.6	482.6
47.5°	446.3	447.1	449.0	448.7	449.0	447.1	446.3	445.4	445.6	447.6	449.9
50°	428.2	428.8	430.2	430.6	430.2	428.8	428.2	426.3	425.3	425.3	426.8
52.5°	408.3	411.1	412.9	412.6	412.9	411.1	408.3	406.7	404.9	402.6	404.8
55°	380.3	383.7	387.1	387.7	387.1	383.7	380.3	375.9	373.9	370.0	371.5
57.5°	352.6	357.4	361.0	362.1	361.0	357.4	352.6	347.3	340.9	339.0	336.3
60°	333.8	340.2	344.6	346.5	344.6	340.2	333.8	328.9	320.6	315.2	313.2
62.5°	315.8	322.9	327.3	327.7	327.3	322.9	315.8	308.1	299.8	293.7	289.7
65°	286.3	293.7	297.6	300.5	297.6	293.7	286.3	278.0	268.7	260.3	256.0
67.5°	254.6	261.9	266.3	268.6	266.3	261.9	254.6	244.3	235.8	226.2	221.0
70°	231.5	238.8	244.7	246.7	244.7	238.8	231.5	219.2	211.9	203.1	198.7
72.5°	208.8	215.4	220.1	222.3	220.1	215.4	208.8	197.4	188.8	180.0	174.0
75°	169.4	178.1	182.6	185.0	182.6	178.1	169.4	163.0	153.2	143.9	139.0
77.5°	130.5	138.6	141.3	142.5	141.3	138.6	130.5	123.1	115.7	109.0	104.2
80°	104.7	109.6	113.0	113.6	113.0	109.6	104.7	98.9	93.0	86.6	82.2
82.5°	80.5	84.5	85.7	86.9	85.7	84.5	80.5	75.4	70.3	65.5	61.8
85°	44.0	46.0	46.5	46.0	46.5	46.0	44.0	40.6	38.2	35.7	34.2
87.5°	18.7	18.4	18.6	19.4	18.6	18.4	18.7	17.8	18.0	17.0	16.0
90°	21.0	21.6	22.2	22.9	22.2	21.6	21.0	20.4	19.5	18.5	17.3
92.5°	20.5	20.7	21.0	21.4	21.0	20.7	20.5	20.2	19.5	18.5	17.3
95°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	19.5	18.5	17.3
97.5°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0	23.0	28.9	35.0
100°	22.5	21.7	20.8	20.0	20.8	21.7	22.5	23.4	39.6	71.2	102.7
102.5°	163.2	148.7	134.3	119.9	134.3	148.7	163.2	177.6	187.8	193.7	199.6
105°	283.8	283.5	283.3	283.1	283.3	283.5	283.8	284.0	284.1	284.1	284.1
107.5°	358.8	358.2	357.5	356.9	357.5	358.2	358.8	359.5	359.8	359.7	359.7
110°	407.4	407.6	407.7	408.0	407.7	407.6	407.4	407.2	407.4	408.0	408.6



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	454.7	454.3	454.0	453.7	454.0	454.3	454.7	455.0	455.5	456.3	457.1
115°	526.2	524.9	523.7	522.4	523.7	524.9	526.2	527.4	528.5	529.3	530.2
117.5°	597.3	596.7	596.2	595.6	596.2	596.7	597.3	597.8	598.6	599.7	600.9
120°	643.8	642.7	641.7	640.6	641.7	642.7	643.8	644.8	645.5	646.0	646.4
122.5°	687.0	685.8	684.6	683.3	684.6	685.8	687.0	688.2	689.0	689.5	689.8
125°	750.3	749.6	748.9	748.3	748.9	749.6	750.3	750.8	751.6	752.4	753.3
127.5°	807.8	806.2	804.6	803.0	804.6	806.2	807.8	809.3	810.3	810.8	811.2
130°	845.8	844.8	843.8	842.7	843.8	844.8	845.8	846.9	847.7	848.4	849.0
132.5°	882.5	881.4	880.3	879.3	880.3	881.4	882.5	883.5	884.1	884.2	884.4
135°	933.2	932.0	930.7	929.4	930.7	932.0	933.2	934.5	935.4	935.8	936.2
137.5°	983.1	981.9	980.9	979.8	980.9	981.9	983.1	984.2	984.7	984.6	984.5
140°	1013.3	1012.0	1010.8	1009.5	1010.8	1012.0	1013.3	1014.6	1015.0	1014.6	1014.2
142.5°	1041.5	1040.3	1039.0	1037.7	1039.0	1040.3	1041.5	1042.8	1043.4	1043.3	1043.2
145°	1082.9	1081.7	1080.3	1079.1	1080.3	1081.7	1082.9	1084.2	1084.7	1084.5	1084.3
147.5°	1117.8	1116.3	1114.7	1113.2	1114.7	1116.3	1117.8	1119.4	1119.9	1119.7	1119.5
150°	1140.4	1138.7	1137.0	1135.3	1137.0	1138.7	1140.4	1142.1	1142.7	1142.4	1141.9
152.5°	1160.5	1159.0	1157.4	1155.9	1157.4	1159.0	1160.5	1162.1	1162.5	1162.2	1161.7
155°	1188.1	1186.4	1184.7	1183.0	1184.7	1186.4	1188.1	1189.8	1190.3	1189.7	1189.0
157.5°	1210.8	1209.1	1207.4	1205.7	1207.4	1209.1	1210.8	1212.5	1213.0	1212.3	1211.6
160°	1225.3	1223.6	1221.9	1220.2	1221.9	1223.6	1225.3	1226.9	1227.4	1226.5	1225.7
162.5°	1238.7	1236.9	1235.0	1233.1	1235.0	1236.9	1238.7	1240.6	1241.0	1239.7	1238.6
165°	1255.7	1254.1	1252.4	1250.7	1252.4	1254.1	1255.7	1257.4	1257.6	1256.4	1255.1
167.5°	1268.6	1266.7	1264.8	1262.9	1264.8	1266.7	1268.6	1270.5	1270.7	1269.1	1267.6
170°	1275.4	1273.6	1271.7	1269.7	1271.7	1273.6	1275.4	1277.3	1277.5	1275.8	1274.1
172.5°	1280.1	1278.1	1276.2	1274.3	1276.2	1278.1	1280.1	1282.0	1282.1	1280.6	1279.1
175°	1285.9	1284.0	1282.1	1280.3	1282.1	1284.0	1285.9	1287.9	1288.0	1286.3	1284.6
177.5°	1287.7	1286.4	1285.1	1283.6	1285.1	1286.4	1287.7	1289.1	1289.2	1288.0	1286.8
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1102.6	1107.3	1113.1	1117.5	1125.3	1128.8	1133.1	1136.6	1142.9	1148.8	1155.8
5°	1028.3	1036.6	1047.8	1060.1	1074.3	1084.1	1097.8	1106.1	1122.8	1137.9	1152.5
7.5°	960.9	971.1	987.0	1002.8	1021.3	1038.1	1055.3	1074.3	1095.5	1120.6	1141.3
10°	914.7	928.4	945.6	965.2	987.7	1007.2	1030.2	1050.7	1076.8	1106.1	1133.5
12.5°	877.9	889.7	908.8	927.6	951.6	975.5	999.3	1026.5	1056.8	1089.3	1123.7
15°	827.1	836.9	852.5	878.5	903.0	926.5	962.2	987.7	1025.9	1062.1	1103.6
17.5°	783.7	795.9	809.1	831.3	856.7	886.1	917.9	949.9	986.7	1032.6	1079.5
20°	757.1	766.9	782.1	799.2	826.1	855.5	885.9	918.1	963.2	1010.7	1061.0
22.5°	728.1	738.8	755.8	774.6	797.2	825.4	858.8	894.3	941.2	988.0	1042.6
25°	694.0	701.3	717.0	733.7	756.2	780.1	814.9	854.0	900.5	953.9	1009.7
27.5°	661.8	668.3	682.6	697.0	717.4	745.8	776.9	816.4	860.3	914.4	976.2
30°	638.7	645.5	658.3	673.9	693.5	718.5	750.3	787.5	834.4	887.3	952.0
32.5°	618.7	624.8	634.4	650.1	669.2	693.4	722.8	760.8	807.9	861.5	924.9
35°	587.8	594.7	602.0	614.3	630.8	654.3	686.6	722.4	767.4	819.3	877.5
37.5°	557.0	564.5	571.1	582.0	597.2	617.9	645.8	683.1	723.8	773.7	829.6
40°	537.9	543.8	549.1	560.9	576.1	595.6	621.6	654.9	698.0	744.4	790.9
42.5°	518.7	524.1	528.8	538.9	553.0	571.7	596.5	629.0	668.9	712.3	753.3
45°	488.4	491.9	497.3	506.1	517.4	534.4	558.5	587.3	621.0	662.2	693.1
47.5°	455.7	461.1	465.5	473.3	482.5	499.3	522.3	546.9	577.5	608.0	629.8
50°	430.6	436.1	442.4	449.8	458.5	474.3	495.3	520.3	546.2	569.7	588.2
52.5°	407.2	412.2	419.0	425.9	436.7	450.0	467.9	490.1	515.7	532.5	548.0
55°	372.5	374.8	382.8	389.6	399.8	409.6	427.7	447.3	463.0	475.7	488.4
57.5°	337.0	340.3	344.8	350.9	361.1	372.6	385.3	402.6	411.8	418.4	428.2
60°	314.2	315.2	318.1	325.5	333.3	343.6	358.3	370.5	377.3	382.8	391.1
62.5°	289.2	289.4	294.3	299.6	305.5	316.6	328.5	338.4	344.0	346.7	354.7
65°	254.0	253.1	256.0	260.3	267.2	274.6	284.8	293.7	293.1	296.1	301.0
67.5°	218.1	217.1	217.1	221.3	226.9	233.5	240.5	245.6	245.7	249.6	252.0
70°	193.8	190.9	192.8	196.2	198.7	204.1	211.9	213.9	214.3	216.3	218.8
72.5°	168.7	167.8	169.4	170.8	172.5	176.7	183.3	184.5	184.6	185.8	189.8
75°	134.1	133.1	132.1	133.7	135.5	138.5	140.9	142.9	142.4	142.9	145.8
77.5°	100.6	97.7	97.3	98.1	98.6	100.3	102.8	102.6	103.2	103.1	106.4
80°	79.7	75.9	75.4	75.4	75.9	76.8	77.9	78.8	77.3	78.8	79.7
82.5°	58.6	56.3	56.2	55.8	55.9	56.1	56.6	57.3	56.9	57.7	58.2
85°	32.3	31.3	29.9	30.8	30.3	28.8	29.9	28.4	27.9	28.4	28.8
87.5°	14.2	14.4	13.3	13.0	12.3	12.4	11.3	10.7	9.9	9.9	10.7
90°	16.3	15.3	13.8	12.3	10.8	9.3	7.7	6.0	4.3	2.6	0.9
92.5°	16.3	15.3	13.9	12.6	11.3	10.0	9.9	11.1	12.3	13.5	14.7
95°	16.3	15.3	23.3	31.4	39.4	47.4	51.8	52.4	53.1	53.7	54.3
97.5°	40.9	46.9	62.9	78.8	94.7	110.7	118.0	116.9	115.7	114.6	113.5
100°	134.3	165.9	165.0	164.2	163.3	162.5	161.7	161.1	160.4	159.9	159.2
102.5°	205.7	211.6	211.1	210.6	210.1	209.6	209.0	208.1	207.4	206.5	205.8
105°	284.1	284.1	284.1	284.1	284.1	284.1	283.6	282.8	281.9	281.1	280.2
107.5°	359.6	359.6	359.1	358.7	358.3	357.9	357.7	357.7	357.7	357.7	357.7
110°	409.3	409.9	409.4	409.1	408.6	408.2	408.0	408.0	408.0	408.0	408.0



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	457.9	458.7	458.5	458.2	458.0	457.7	457.3	456.8	456.3	455.8	455.2
115°	531.0	531.9	531.7	531.5	531.3	531.0	530.5	529.3	528.3	527.3	526.2
117.5°	601.9	603.0	602.2	601.4	600.6	599.8	599.5	599.5	599.6	599.6	599.6
120°	646.9	647.2	646.6	646.0	645.4	644.7	644.5	644.7	644.9	645.2	645.4
122.5°	690.3	690.7	690.4	690.1	689.8	689.6	689.0	688.2	687.4	686.5	685.8
125°	754.1	755.0	755.0	755.0	755.0	755.0	754.2	752.7	751.3	749.8	748.3
127.5°	811.7	812.2	812.3	812.5	812.6	812.7	812.2	811.2	810.1	809.1	807.9
130°	849.7	850.3	850.1	849.9	849.7	849.4	848.9	847.7	846.7	845.6	844.6
132.5°	884.5	884.7	885.0	885.5	886.0	886.5	886.1	884.9	883.6	882.4	881.2
135°	936.6	937.1	937.5	937.9	938.3	938.8	938.3	937.1	935.8	934.5	933.2
137.5°	984.4	984.3	984.7	985.1	985.5	985.9	985.5	984.4	983.3	982.2	981.1
140°	1013.7	1013.3	1013.5	1013.7	1014.0	1014.2	1014.1	1013.6	1013.2	1012.8	1012.4
142.5°	1043.1	1043.0	1042.7	1042.5	1042.2	1041.9	1041.6	1041.3	1041.1	1040.8	1040.6
145°	1084.1	1083.8	1083.8	1083.8	1083.8	1083.8	1083.6	1083.3	1082.8	1082.4	1081.9
147.5°	1119.2	1118.9	1118.7	1118.4	1118.1	1117.9	1117.9	1117.9	1118.0	1118.1	1118.1
150°	1141.5	1141.0	1140.7	1140.2	1139.8	1139.3	1139.3	1139.8	1140.2	1140.7	1141.0
152.5°	1161.3	1160.8	1160.5	1160.1	1159.6	1159.2	1159.4	1160.4	1161.3	1162.2	1163.2
155°	1188.4	1187.8	1187.3	1186.9	1186.5	1186.1	1186.5	1187.8	1189.0	1190.3	1191.6
157.5°	1211.0	1210.2	1210.2	1210.1	1210.1	1210.1	1210.4	1211.3	1212.0	1212.8	1213.5
160°	1224.8	1224.0	1223.8	1223.6	1223.3	1223.1	1223.7	1224.9	1226.2	1227.5	1228.8
162.5°	1237.4	1236.1	1236.0	1235.8	1235.6	1235.3	1235.9	1237.2	1238.4	1239.7	1241.0
165°	1253.9	1252.5	1252.4	1252.2	1252.0	1251.7	1252.3	1253.6	1254.8	1256.1	1257.4
167.5°	1266.1	1264.6	1264.4	1264.1	1263.9	1263.8	1264.3	1265.6	1267.0	1268.3	1269.5
170°	1272.4	1270.7	1270.5	1270.3	1270.1	1269.9	1270.5	1272.0	1273.5	1275.0	1276.4
172.5°	1277.5	1276.0	1275.6	1275.3	1274.9	1274.5	1275.1	1276.6	1278.0	1279.5	1281.0
175°	1282.9	1281.2	1281.0	1280.7	1280.5	1280.3	1280.8	1282.1	1283.4	1284.7	1285.9
177.5°	1285.6	1284.4	1284.2	1284.1	1283.9	1283.7	1284.2	1285.2	1286.2	1287.2	1288.3
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1159.3	1164.8	1168.4	1175.0	1180.4	1183.6	1186.4	1188.7	1191.5	1193.8	1200.4
5°	1166.8	1179.5	1190.2	1206.9	1222.1	1233.8	1246.5	1257.8	1267.2	1280.3	1290.6
7.5°	1163.6	1186.2	1209.8	1235.6	1261.9	1286.4	1308.9	1329.9	1349.1	1372.2	1392.4
10°	1160.5	1191.3	1221.6	1256.3	1292.0	1322.4	1350.8	1379.7	1400.7	1430.1	1455.0
12.5°	1158.1	1194.4	1231.0	1272.8	1312.0	1354.9	1392.7	1413.7	1445.8	1469.2	1498.9
15°	1148.2	1196.2	1246.5	1293.5	1349.3	1388.9	1422.3	1463.4	1493.2	1523.1	1555.4
17.5°	1130.5	1184.8	1241.1	1302.8	1356.3	1398.8	1441.7	1481.4	1517.0	1557.1	1597.2
20°	1122.3	1176.6	1241.1	1304.3	1356.7	1401.2	1445.3	1488.8	1528.0	1579.3	1625.9
22.5°	1105.0	1170.7	1230.2	1291.8	1345.7	1394.2	1444.1	1493.6	1545.6	1603.6	1661.9
25°	1074.3	1140.9	1204.0	1264.7	1319.0	1379.7	1433.0	1499.1	1565.7	1642.5	1715.0
27.5°	1042.4	1106.1	1163.9	1222.6	1285.9	1354.6	1423.8	1498.8	1585.9	1682.9	1785.1
30°	1016.5	1076.8	1133.0	1193.2	1259.2	1336.6	1412.5	1501.6	1602.3	1711.5	1832.9
32.5°	986.4	1041.9	1096.6	1160.4	1232.3	1313.9	1402.3	1500.0	1621.2	1745.2	1870.1
35°	934.8	981.3	1037.6	1105.6	1186.8	1280.3	1382.6	1498.1	1637.1	1779.5	1884.8
37.5°	873.6	916.9	976.2	1050.7	1136.0	1236.2	1357.6	1494.7	1642.3	1755.9	1789.8
40°	832.5	872.6	934.3	1011.6	1098.7	1204.9	1338.0	1482.9	1625.9	1698.3	1670.4
42.5°	788.6	830.8	890.8	967.4	1061.2	1176.8	1313.4	1458.3	1578.1	1605.5	1509.1
45°	719.4	763.0	822.2	899.6	1000.4	1125.7	1268.1	1399.8	1468.8	1419.3	1270.1
47.5°	655.2	696.0	750.8	830.7	934.7	1064.3	1201.5	1306.5	1311.9	1194.0	1034.5
50°	611.3	648.9	704.3	784.0	887.3	1018.5	1142.3	1225.0	1187.8	1054.2	901.0
52.5°	568.3	605.1	659.7	738.7	840.7	960.9	1076.1	1134.2	1064.1	927.0	796.1
55°	506.1	538.4	591.7	664.6	761.6	873.2	971.0	991.1	900.0	765.0	658.7
57.5°	445.4	475.5	524.1	591.3	679.8	778.6	855.2	850.9	754.7	638.8	554.5
60°	404.3	433.7	476.7	542.2	623.0	708.2	773.7	758.1	662.7	562.8	491.9
62.5°	367.5	393.7	434.4	491.7	565.4	644.4	698.2	675.1	581.6	494.3	438.2
65°	313.2	335.3	370.0	419.0	480.1	545.3	586.8	556.9	477.2	409.2	364.1
67.5°	261.5	279.1	308.2	347.3	399.4	451.8	477.1	447.0	383.2	333.6	300.2
70°	228.6	244.2	266.7	301.5	347.0	391.1	410.1	383.2	328.4	285.8	261.8
72.5°	195.7	208.6	228.4	259.6	296.1	334.3	351.0	325.3	280.2	244.3	221.9
75°	151.3	160.0	173.7	195.3	224.1	254.5	263.8	241.3	212.4	185.5	170.8
77.5°	108.3	115.7	126.1	139.7	160.1	179.5	187.6	174.6	152.2	135.2	123.1
80°	83.2	87.1	96.0	107.2	123.4	135.5	140.9	132.6	117.0	104.2	94.9
82.5°	59.3	63.2	68.5	77.9	88.1	96.4	102.2	96.6	85.3	75.3	69.8
85°	28.8	31.3	34.2	38.2	46.0	50.9	50.4	46.9	42.6	38.6	35.7
87.5°	10.7	11.4	12.9	15.3	16.8	18.6	19.7	19.2	17.9	17.0	16.0
90°	2.6	4.3	6.0	7.7	9.3	10.8	12.3	13.8	15.3	16.3	17.3
92.5°	13.5	12.3	11.1	9.9	10.0	11.3	12.6	13.9	15.3	16.3	17.3
95°	53.7	53.1	52.4	51.8	47.4	39.4	31.4	23.3	15.3	16.3	17.3
97.5°	114.6	115.7	116.9	118.0	110.7	94.7	78.8	62.9	46.9	40.9	35.0
100°	159.9	160.4	161.1	161.7	162.5	163.3	164.2	165.0	165.9	134.3	102.7
102.5°	206.5	207.4	208.1	209.0	209.6	210.1	210.6	211.1	211.6	205.7	199.6
105°	281.1	281.9	282.8	283.6	284.1	284.1	284.1	284.1	284.1	284.1	284.1
107.5°	357.7	357.7	357.7	357.7	357.9	358.3	358.7	359.1	359.6	359.6	359.7
110°	408.0	408.0	408.0	408.0	408.2	408.6	409.1	409.4	409.9	409.3	408.6





TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	455.8	456.3	456.8	457.3	457.7	458.0	458.2	458.5	458.7	457.9	457.1
115°	527.3	528.3	529.3	530.5	531.0	531.3	531.5	531.7	531.9	531.0	530.2
117.5°	599.6	599.6	599.5	599.5	599.8	600.6	601.4	602.2	603.0	601.9	600.9
120°	645.2	644.9	644.7	644.5	644.7	645.4	646.0	646.6	647.2	646.9	646.4
122.5°	686.5	687.4	688.2	689.0	689.6	689.8	690.1	690.4	690.7	690.3	689.8
125°	749.8	751.3	752.7	754.2	755.0	755.0	755.0	755.0	755.0	754.1	753.3
127.5°	809.1	810.1	811.2	812.2	812.7	812.6	812.5	812.3	812.2	811.7	811.2
130°	845.6	846.7	847.7	848.9	849.4	849.7	849.9	850.1	850.3	849.7	849.0
132.5°	882.4	883.6	884.9	886.1	886.5	886.0	885.5	885.0	884.7	884.5	884.4
135°	934.5	935.8	937.1	938.3	938.8	938.3	937.9	937.5	937.1	936.6	936.2
137.5°	982.2	983.3	984.4	985.5	985.9	985.5	985.1	984.7	984.3	984.4	984.5
140°	1012.8	1013.2	1013.6	1014.1	1014.2	1014.0	1013.7	1013.5	1013.3	1013.7	1014.2
142.5°	1040.8	1041.1	1041.3	1041.6	1041.9	1042.2	1042.5	1042.7	1043.0	1043.1	1043.2
145°	1082.4	1082.8	1083.3	1083.6	1083.8	1083.8	1083.8	1083.8	1083.8	1084.1	1084.3
147.5°	1118.1	1118.0	1117.9	1117.9	1117.9	1118.1	1118.4	1118.7	1118.9	1119.2	1119.5
150°	1140.7	1140.2	1139.8	1139.3	1139.3	1139.8	1140.2	1140.7	1141.0	1141.5	1141.9
152.5°	1162.2	1161.3	1160.4	1159.4	1159.2	1159.6	1160.1	1160.5	1160.8	1161.3	1161.7
155°	1190.3	1189.0	1187.8	1186.5	1186.1	1186.5	1186.9	1187.3	1187.8	1188.4	1189.0
157.5°	1212.8	1212.0	1211.3	1210.4	1210.1	1210.1	1210.1	1210.2	1210.2	1211.0	1211.6
160°	1227.5	1226.2	1224.9	1223.7	1223.1	1223.3	1223.6	1223.8	1224.0	1224.8	1225.7
162.5°	1239.7	1238.4	1237.2	1235.9	1235.3	1235.6	1235.8	1236.0	1236.1	1237.4	1238.6
165°	1256.1	1254.8	1253.6	1252.3	1251.7	1252.0	1252.2	1252.4	1252.5	1253.9	1255.1
167.5°	1268.3	1267.0	1265.6	1264.3	1263.8	1263.9	1264.1	1264.4	1264.6	1266.1	1267.6
170°	1275.0	1273.5	1272.0	1270.5	1269.9	1270.1	1270.3	1270.5	1270.7	1272.4	1274.1
172.5°	1279.5	1278.0	1276.6	1275.1	1274.5	1274.9	1275.3	1275.6	1276.0	1277.5	1279.1
175°	1284.7	1283.4	1282.1	1280.8	1280.3	1280.5	1280.7	1281.0	1281.2	1282.9	1284.6
177.5°	1287.2	1286.2	1285.2	1284.2	1283.7	1283.9	1284.1	1284.2	1284.4	1285.6	1286.8
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1205.9	1209.1	1215.7	1213.3	1216.5	1218.0	1219.7
5°	1303.3	1319.0	1325.9	1324.8	1335.1	1332.7	1330.2
7.5°	1413.3	1429.8	1439.0	1450.5	1457.1	1457.5	1463.4
10°	1475.6	1497.1	1506.0	1518.2	1526.0	1530.4	1529.9
12.5°	1523.3	1540.2	1560.0	1565.9	1576.5	1582.1	1580.1
15°	1580.8	1607.8	1628.3	1638.6	1651.8	1655.7	1661.1
17.5°	1632.1	1668.2	1692.2	1724.1	1736.2	1743.5	1739.2
20°	1670.8	1718.3	1742.4	1780.6	1801.6	1812.8	1808.9
22.5°	1716.7	1768.1	1812.4	1845.5	1877.5	1892.7	1895.8
25°	1795.2	1865.7	1930.8	1974.3	2013.9	2023.3	2043.8
27.5°	1882.9	1966.0	2035.6	2081.4	2109.0	2119.4	2125.8
30°	1938.2	2020.8	2073.2	2102.5	2111.4	2110.4	2109.4
32.5°	1965.1	2016.9	2026.9	2018.7	1998.6	1981.6	1963.8
35°	1926.8	1888.2	1830.4	1756.1	1701.2	1646.0	1640.5
37.5°	1733.0	1609.3	1513.2	1405.8	1343.9	1305.6	1279.1
40°	1550.5	1410.0	1293.5	1203.0	1139.8	1114.9	1090.4
42.5°	1352.4	1218.1	1115.0	1039.3	991.8	964.1	944.8
45°	1098.7	980.3	899.6	844.7	807.1	785.5	773.3
47.5°	900.3	812.8	744.1	704.6	678.5	661.8	661.9
50°	793.8	710.1	664.6	633.3	610.8	597.6	600.0
52.5°	699.5	637.0	598.0	571.8	555.2	547.1	546.8
55°	584.8	539.8	514.3	495.3	484.0	474.8	476.7
57.5°	500.3	462.3	445.3	429.4	421.6	417.8	412.5
60°	447.8	418.5	403.8	391.1	383.2	380.3	374.8
62.5°	401.2	378.1	363.8	353.5	346.4	345.4	341.2
65°	337.2	319.6	306.9	302.0	294.6	292.7	292.7
67.5°	278.0	265.3	255.5	251.0	247.7	248.3	245.9
70°	240.8	230.5	224.1	219.2	216.8	217.3	215.4
72.5°	210.7	199.2	193.6	190.7	187.5	188.7	187.9
75°	159.6	153.6	150.7	147.8	145.8	144.9	143.9
77.5°	117.2	112.0	109.7	108.1	108.4	106.0	107.8
80°	90.6	86.1	84.6	82.2	81.7	81.7	81.2
82.5°	66.3	63.8	62.8	60.7	59.9	60.6	59.3
85°	34.2	32.3	31.9	31.9	30.8	29.9	32.3
87.5°	16.2	14.9	15.0	14.8	14.9	14.6	13.9
90°	18.5	19.5	20.4	21.0	21.6	22.2	22.9
92.5°	18.5	19.5	20.2	20.5	20.7	21.0	21.4
95°	18.5	19.5	20.0	20.0	20.0	20.0	20.0
97.5°	28.9	23.0	20.0	20.0	20.0	20.0	20.0
100°	71.2	39.6	23.4	22.5	21.7	20.8	20.0
102.5°	193.7	187.8	177.6	163.2	148.7	134.3	119.9
105°	284.1	284.1	284.0	283.8	283.5	283.3	283.1
107.5°	359.7	359.8	359.5	358.8	358.2	357.5	356.9
110°	408.0	407.4	407.2	407.4	407.6	407.7	408.0



TEST NUMBER: P333412-830

CATALOG NUMBER: S125DIW-S850D1050U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	456.3	455.5	455.0	454.7	454.3	454.0	453.7
115°	529.3	528.5	527.4	526.2	524.9	523.7	522.4
117.5°	599.7	598.6	597.8	597.3	596.7	596.2	595.6
120°	646.0	645.5	644.8	643.8	642.7	641.7	640.6
122.5°	689.5	689.0	688.2	687.0	685.8	684.6	683.3
125°	752.4	751.6	750.8	750.3	749.6	748.9	748.3
127.5°	810.8	810.3	809.3	807.8	806.2	804.6	803.0
130°	848.4	847.7	846.9	845.8	844.8	843.8	842.7
132.5°	884.2	884.1	883.5	882.5	881.4	880.3	879.3
135°	935.8	935.4	934.5	933.2	932.0	930.7	929.4
137.5°	984.6	984.7	984.2	983.1	981.9	980.9	979.8
140°	1014.6	1015.0	1014.6	1013.3	1012.0	1010.8	1009.5
142.5°	1043.3	1043.4	1042.8	1041.5	1040.3	1039.0	1037.7
145°	1084.5	1084.7	1084.2	1082.9	1081.7	1080.3	1079.1
147.5°	1119.7	1119.9	1119.4	1117.8	1116.3	1114.7	1113.2
150°	1142.4	1142.7	1142.1	1140.4	1138.7	1137.0	1135.3
152.5°	1162.2	1162.5	1162.1	1160.5	1159.0	1157.4	1155.9
155°	1189.7	1190.3	1189.8	1188.1	1186.4	1184.7	1183.0
157.5°	1212.3	1213.0	1212.5	1210.8	1209.1	1207.4	1205.7
160°	1226.5	1227.4	1226.9	1225.3	1223.6	1221.9	1220.2
162.5°	1239.7	1241.0	1240.6	1238.7	1236.9	1235.0	1233.1
165°	1256.4	1257.6	1257.4	1255.7	1254.1	1252.4	1250.7
167.5°	1269.1	1270.7	1270.5	1268.6	1266.7	1264.8	1262.9
170°	1275.8	1277.5	1277.3	1275.4	1273.6	1271.7	1269.7
172.5°	1280.6	1282.1	1282.0	1280.1	1278.1	1276.2	1274.3
175°	1286.3	1288.0	1287.9	1285.9	1284.0	1282.1	1280.3
177.5°	1288.0	1289.2	1289.1	1287.7	1286.4	1285.1	1283.6
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9

(END OF REPORT)