

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333482-935

Luminaire Tested: **S125DIW-S1270D1340U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333482-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D1340U935-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9036.5 lumens  
Efficiency: N/A  
Efficacy: 118.6 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333482-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333482-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	43	41	39
3	81	71	64	58	74	66	60	54	56	51	47	47	43	40	38	35	33
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	29
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25
6	63	50	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	19
8	54	41	34	28	49	38	32	27	33	28	24	28	24	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10959	10959	10959
5°	10983	10878	10949
10°	10916	10802	10864
15°	10797	10672	10717
20°	10628	10490	10509
25°	10446	10274	10264
30°	10221	10041	9991
35°	9980	9790	9653
40°	9732	9517	9382
45°	9465	9270	9085
50°	9171	8969	8699
55°	8888	8631	8389
60°	8548	8289	7994
65°	8145	7878	7610
70°	7757	7402	7149
75°	7069	6835	6598
80°	6289	6189	6044
85°	5476	5572	5269



TEST NUMBER: P333482-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.0	1.8
10°-20°	451.9	5.0
20°-30°	667.3	7.4
30°-40°	778.6	8.6
40°-50°	782.0	8.7
50°-60°	686.5	7.6
60°-70°	511.5	5.7
70°-80°	292.5	3.2
80°-90°	88.2	1.0
90°-100°	54.6	0.6
100°-110°	336.8	3.7
110°-120°	610.9	6.8
120°-130°	783.9	8.7
130°-140°	843.2	9.3
140°-150°	791.5	8.8
150°-160°	640.2	7.1
160°-170°	414.1	4.6
170°-180°	142.8	1.6
0°-30°	1279.2	14.2
0°-40°	2057.8	22.8
0°-60°	3526.3	39.0
0°-90°	4418.5	48.9
90°-120°	1002.3	11.1
90°-150°	3420.9	37.9
90°-180°	4618.0	51.1
0°-180°	9036.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1694	1691	1678	1689	1689	161
15°	1615	1610	1596	1602	1603	455
25°	1466	1459	1442	1444	1440	674
35°	1266	1260	1242	1235	1224	791
45°	1036	1030	1015	999	995	798
55°	789	784	766	755	745	704
65°	533	530	516	504	498	529
75°	283	280	274	270	264	302
85°	74	75	75	74	71	83
90°	1	10	18	23	27	7
95°	64	58	18	23	23	81
105°	328	332	332	332	331	347
115°	615	621	622	617	611	610
125°	875	882	883	878	875	781
135°	1091	1098	1096	1093	1087	841
145°	1265	1267	1268	1268	1262	791
155°	1393	1387	1389	1392	1384	642
165°	1470	1464	1465	1471	1463	415
175°	1504	1498	1498	1506	1497	143
180°	1504	1504	1504	1504	1504	



TEST NUMBER: P333482-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1701.1	1700.4	1699.7	1698.9	1698.2	1696.7	1694.3	1691.9	1689.5	1687.1	1689.5
5°	1694.1	1693.5	1692.9	1692.3	1691.7	1690.0	1687.0	1683.9	1681.0	1678.0	1680.7
7.5°	1678.5	1677.9	1677.3	1676.7	1676.1	1674.2	1670.9	1667.7	1664.4	1661.1	1663.7
10°	1664.6	1664.0	1663.4	1662.8	1662.2	1660.3	1657.0	1653.7	1650.4	1647.1	1649.5
12.5°	1647.4	1646.3	1645.3	1644.2	1643.1	1641.1	1638.0	1635.0	1631.9	1628.8	1630.8
15°	1614.9	1614.0	1613.1	1612.2	1611.4	1609.2	1605.9	1602.7	1599.4	1596.1	1597.6
17.5°	1577.6	1576.3	1574.9	1573.6	1572.4	1569.9	1566.6	1563.1	1559.8	1556.3	1558.2
20°	1546.4	1545.8	1545.2	1544.6	1544.0	1541.8	1537.9	1534.0	1530.2	1526.3	1528.4
22.5°	1515.3	1514.2	1513.1	1512.1	1511.0	1508.6	1505.0	1501.4	1497.7	1494.1	1495.5
25°	1465.9	1464.4	1462.9	1461.5	1459.9	1457.2	1453.4	1449.5	1445.6	1441.7	1442.3
27.5°	1408.2	1407.3	1406.4	1405.5	1404.6	1402.1	1398.2	1394.1	1390.2	1386.1	1386.3
30°	1370.6	1369.7	1368.8	1367.9	1367.0	1364.3	1359.9	1355.4	1350.9	1346.4	1345.8
32.5°	1329.8	1328.4	1327.1	1325.7	1324.3	1321.6	1317.6	1313.6	1309.6	1305.6	1304.6
35°	1265.8	1264.7	1263.5	1262.3	1261.1	1258.4	1254.2	1250.1	1245.9	1241.7	1240.3
37.5°	1199.5	1198.1	1196.6	1195.1	1193.6	1190.8	1187.0	1183.0	1179.1	1175.2	1172.9
40°	1154.4	1153.0	1151.5	1150.0	1148.5	1145.6	1141.5	1137.3	1133.2	1128.9	1126.3
42.5°	1106.1	1104.9	1103.6	1102.3	1101.1	1098.4	1094.2	1090.0	1085.9	1081.7	1079.3
45°	1036.3	1035.2	1034.0	1032.8	1031.6	1029.2	1025.6	1022.0	1018.5	1014.9	1011.2
47.5°	961.1	961.2	961.3	961.3	961.4	959.2	955.0	950.7	946.4	942.1	938.5
50°	912.8	912.0	911.0	910.2	909.2	907.0	903.4	899.8	896.3	892.7	888.8
52.5°	863.4	862.8	862.1	861.4	860.8	858.6	854.7	850.9	847.1	843.3	839.9
55°	789.4	788.4	787.6	786.6	785.7	783.3	779.0	774.9	770.7	766.5	763.8
57.5°	711.2	710.8	710.2	709.8	709.3	707.3	703.8	700.3	696.7	693.2	689.7
60°	661.8	660.6	659.4	658.2	657.0	654.8	651.5	648.2	645.0	641.7	638.7
62.5°	610.3	609.3	608.4	607.3	606.4	604.6	601.8	598.9	596.2	593.3	590.1
65°	533.0	532.4	531.8	531.2	530.5	528.6	525.3	522.0	518.8	515.5	512.8
67.5°	458.1	456.8	455.6	454.3	453.1	451.2	448.8	446.3	443.8	441.3	439.1
70°	410.8	409.3	407.8	406.3	404.8	402.7	400.0	397.4	394.7	392.0	390.2
72.5°	359.2	358.2	357.2	356.2	355.2	353.8	352.1	350.3	348.6	346.9	344.8
75°	283.3	282.7	282.1	281.5	280.9	279.8	278.4	276.8	275.3	273.9	272.9
77.5°	213.2	212.9	212.7	212.5	212.2	211.7	210.9	210.0	209.1	208.4	207.8
80°	169.1	169.1	169.1	169.1	169.1	168.8	168.2	167.6	167.0	166.4	166.2
82.5°	130.4	130.0	129.5	129.1	128.5	128.3	128.1	128.0	127.9	127.8	127.3
85°	73.9	74.1	74.4	74.7	75.0	75.2	75.2	75.2	75.2	75.2	74.9
87.5°	29.2	29.6	30.0	30.4	30.8	31.1	31.2	31.3	31.3	31.5	31.8
90°	1.1	3.1	5.1	7.1	9.0	10.9	12.7	14.4	16.1	17.8	19.1
92.5°	17.1	15.8	14.4	13.0	11.6	11.7	13.3	14.7	16.3	17.8	19.1
95°	63.5	62.8	62.1	61.3	60.5	55.4	46.1	36.7	27.2	17.8	19.1
97.5°	132.7	134.0	135.3	136.6	138.0	129.3	110.7	92.1	73.4	54.8	47.9
100°	186.1	186.9	187.6	188.4	189.2	190.0	191.0	192.0	193.0	194.0	157.0
102.5°	240.6	241.5	242.5	243.4	244.4	245.1	245.7	246.3	246.8	247.5	240.5
105°	327.8	328.7	329.8	330.7	331.7	332.2	332.2	332.2	332.2	332.2	332.2
107.5°	418.3	418.3	418.3	418.3	418.3	418.5	419.0	419.5	420.0	420.5	420.5
110°	477.2	477.2	477.2	477.2	477.2	477.3	477.9	478.4	478.9	479.3	478.6



TEST NUMBER: P333482-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	532.4	533.0	533.6	534.2	534.8	535.3	535.5	535.8	536.1	536.4	535.5
115°	615.4	616.6	617.9	619.1	620.4	621.0	621.3	621.6	621.8	622.1	621.0
117.5°	701.2	701.1	701.1	701.0	701.0	701.5	702.4	703.4	704.3	705.2	704.0
120°	754.7	754.5	754.2	754.0	753.7	754.0	754.7	755.4	756.2	756.9	756.5
122.5°	801.9	802.9	803.8	804.8	805.7	806.4	806.8	807.1	807.4	807.8	807.3
125°	875.1	876.8	878.6	880.3	882.0	882.9	882.9	882.9	882.9	882.9	881.9
127.5°	944.9	946.2	947.4	948.6	949.9	950.4	950.2	950.1	949.9	949.8	949.3
130°	987.7	988.9	990.2	991.4	992.6	993.4	993.7	993.9	994.1	994.4	993.7
132.5°	1030.5	1031.9	1033.4	1034.8	1036.2	1036.7	1036.1	1035.6	1035.1	1034.5	1034.4
135°	1091.4	1092.9	1094.3	1095.8	1097.3	1097.8	1097.3	1096.8	1096.3	1095.8	1095.4
137.5°	1147.4	1148.6	1149.9	1151.2	1152.4	1152.9	1152.4	1152.0	1151.6	1151.2	1151.2
140°	1183.9	1184.4	1184.9	1185.3	1185.9	1186.0	1185.8	1185.5	1185.3	1185.0	1185.5
142.5°	1216.9	1217.2	1217.5	1217.8	1218.1	1218.4	1218.7	1219.1	1219.4	1219.8	1219.9
145°	1265.2	1265.8	1266.3	1266.8	1267.2	1267.5	1267.5	1267.5	1267.5	1267.5	1267.7
147.5°	1307.6	1307.5	1307.4	1307.3	1307.3	1307.3	1307.6	1307.9	1308.2	1308.5	1308.8
150°	1334.4	1333.9	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1334.9
152.5°	1360.2	1359.2	1358.1	1357.0	1355.9	1355.6	1356.1	1356.6	1357.1	1357.5	1358.1
155°	1393.4	1392.0	1390.5	1389.1	1387.5	1387.1	1387.5	1388.0	1388.5	1389.1	1389.7
157.5°	1419.1	1418.2	1417.3	1416.4	1415.6	1415.1	1415.1	1415.2	1415.3	1415.3	1416.1
160°	1436.9	1435.5	1434.0	1432.4	1431.0	1430.4	1430.6	1430.9	1431.2	1431.4	1432.4
162.5°	1451.2	1449.8	1448.2	1446.7	1445.3	1444.7	1444.9	1445.2	1445.4	1445.6	1447.0
165°	1470.4	1468.9	1467.4	1465.9	1464.5	1463.8	1464.0	1464.3	1464.6	1464.8	1466.3
167.5°	1484.6	1483.2	1481.6	1480.1	1478.5	1477.9	1478.1	1478.3	1478.6	1478.9	1480.7
170°	1492.7	1491.0	1489.2	1487.5	1485.7	1485.0	1485.2	1485.5	1485.7	1486.0	1488.0
172.5°	1498.1	1496.3	1494.6	1492.8	1491.1	1490.5	1490.9	1491.3	1491.8	1492.2	1494.0
175°	1503.8	1502.4	1500.9	1499.3	1497.9	1497.3	1497.5	1497.8	1498.1	1498.2	1500.2
177.5°	1506.5	1505.3	1504.2	1503.0	1501.8	1501.2	1501.5	1501.7	1501.8	1502.0	1503.5
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333482-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1691.9	1694.3	1696.7	1697.7	1697.5	1697.3	1697.0	1696.8
5°	1683.3	1686.1	1688.8	1690.0	1689.6	1689.4	1689.0	1688.8
7.5°	1666.3	1669.0	1671.5	1672.8	1672.5	1672.1	1671.9	1671.5
10°	1651.9	1654.3	1656.7	1657.7	1657.4	1657.1	1656.8	1656.6
12.5°	1632.7	1634.6	1636.5	1637.4	1637.4	1637.3	1637.3	1637.2
15°	1599.1	1600.6	1602.1	1602.8	1602.8	1602.8	1602.8	1602.8
17.5°	1560.0	1561.9	1563.7	1563.9	1562.5	1561.0	1559.4	1558.0
20°	1530.5	1532.6	1534.6	1535.0	1533.4	1532.0	1530.5	1529.0
22.5°	1496.8	1498.2	1499.6	1499.8	1498.7	1497.7	1496.7	1495.7
25°	1442.9	1443.6	1444.2	1444.0	1443.1	1442.2	1441.3	1440.4
27.5°	1386.4	1386.6	1386.6	1386.2	1385.3	1384.5	1383.5	1382.7
30°	1345.2	1344.6	1344.0	1343.3	1342.4	1341.5	1340.6	1339.7
32.5°	1303.5	1302.4	1301.3	1299.9	1298.4	1296.8	1295.1	1293.6
35°	1238.7	1237.3	1235.8	1233.8	1231.4	1229.1	1226.7	1224.3
37.5°	1170.7	1168.5	1166.3	1164.5	1163.1	1161.7	1160.4	1159.0
40°	1123.6	1120.9	1118.2	1116.5	1115.5	1114.7	1113.7	1112.8
42.5°	1076.9	1074.4	1071.9	1070.1	1068.7	1067.3	1065.9	1064.5
45°	1007.7	1004.1	1000.6	998.3	997.4	996.5	995.6	994.7
47.5°	934.8	931.2	927.6	924.7	922.6	920.5	918.4	916.4
50°	884.9	881.1	877.2	874.2	872.1	870.0	868.0	865.8
52.5°	836.5	833.1	829.7	826.8	824.5	822.2	819.8	817.5
55°	761.1	758.5	755.8	753.4	751.3	749.2	747.1	745.0
57.5°	686.3	682.9	679.4	677.1	676.0	674.9	673.6	672.5
60°	635.7	632.7	629.7	627.2	625.1	623.0	621.0	618.9
62.5°	586.9	583.7	580.5	578.1	576.4	574.8	573.2	571.6
65°	510.1	507.4	504.7	502.8	501.6	500.4	499.2	498.0
67.5°	436.9	434.5	432.3	430.8	430.1	429.4	428.7	427.9
70°	388.4	386.6	384.8	383.3	382.1	380.9	379.8	378.6
72.5°	342.9	340.8	338.8	337.2	336.0	334.8	333.6	332.3
75°	272.1	271.1	270.3	269.2	268.0	266.8	265.6	264.4
77.5°	207.2	206.7	206.2	205.5	204.7	203.8	203.0	202.2
80°	165.8	165.6	165.2	164.8	164.2	163.6	163.0	162.5
82.5°	126.7	126.2	125.6	125.4	125.2	125.1	124.9	124.8
85°	74.6	74.3	74.0	73.5	72.9	72.3	71.7	71.1
87.5°	31.9	32.2	32.5	32.5	32.1	31.8	31.4	31.1
90°	20.3	21.5	22.8	23.8	24.5	25.2	26.0	26.8
92.5°	20.3	21.5	22.8	23.6	23.9	24.3	24.6	25.0
95°	20.3	21.5	22.8	23.4	23.4	23.4	23.4	23.4
97.5°	40.9	33.9	26.9	23.4	23.4	23.4	23.4	23.4
100°	120.1	83.3	46.3	27.4	26.3	25.4	24.4	23.4
102.5°	233.5	226.5	219.6	207.6	190.8	173.9	157.0	140.3
105°	332.2	332.2	332.2	332.1	331.8	331.6	331.3	331.1
107.5°	420.6	420.7	420.7	420.3	419.6	418.9	418.1	417.4
110°	477.9	477.2	476.4	476.1	476.4	476.6	476.9	477.2





TEST NUMBER: P333482-935

CATALOG NUMBER: S125DIW-S1270D1340U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	534.5	533.6	532.7	532.0	531.7	531.3	531.0	530.6
115°	620.1	619.1	618.1	616.8	615.4	613.9	612.3	610.9
117.5°	702.7	701.4	700.1	699.0	698.4	697.8	697.2	696.5
120°	756.0	755.4	754.9	754.1	752.9	751.6	750.4	749.2
122.5°	806.8	806.2	805.8	804.8	803.4	801.9	800.5	799.1
125°	880.9	879.9	878.9	878.0	877.4	876.6	875.8	875.1
127.5°	948.7	948.1	947.6	946.4	944.6	942.8	940.9	939.1
130°	992.9	992.1	991.4	990.4	989.2	987.9	986.7	985.5
132.5°	1034.2	1034.1	1033.9	1033.2	1032.0	1030.8	1029.5	1028.3
135°	1094.8	1094.3	1093.8	1092.9	1091.4	1089.9	1088.4	1086.9
137.5°	1151.3	1151.4	1151.5	1150.9	1149.6	1148.3	1147.0	1145.7
140°	1186.0	1186.5	1187.0	1186.5	1185.0	1183.5	1182.1	1180.5
142.5°	1220.0	1220.1	1220.2	1219.5	1218.0	1216.5	1215.0	1213.6
145°	1268.0	1268.3	1268.5	1267.9	1266.4	1264.9	1263.4	1262.0
147.5°	1309.2	1309.4	1309.8	1309.0	1307.2	1305.4	1303.6	1301.8
150°	1335.4	1335.8	1336.4	1335.6	1333.6	1331.6	1329.6	1327.7
152.5°	1358.6	1359.1	1359.5	1358.9	1357.1	1355.4	1353.6	1351.8
155°	1390.5	1391.2	1392.0	1391.4	1389.4	1387.4	1385.4	1383.5
157.5°	1416.9	1417.7	1418.5	1417.9	1415.9	1413.9	1412.0	1410.0
160°	1433.4	1434.3	1435.4	1434.9	1432.9	1430.9	1428.9	1426.9
162.5°	1448.4	1449.8	1451.2	1450.8	1448.6	1446.4	1444.2	1442.1
165°	1467.7	1469.3	1470.8	1470.5	1468.5	1466.5	1464.6	1462.6
167.5°	1482.5	1484.2	1486.0	1485.7	1483.5	1481.4	1479.1	1476.9
170°	1490.0	1491.9	1493.9	1493.8	1491.6	1489.4	1487.1	1484.9
172.5°	1495.8	1497.6	1499.3	1499.2	1496.9	1494.7	1492.5	1490.2
175°	1502.2	1504.2	1506.1	1506.1	1503.8	1501.6	1499.3	1497.1
177.5°	1504.9	1506.2	1507.6	1507.5	1505.9	1504.3	1502.7	1501.2
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8

(END OF REPORT)