

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333485-935

Luminaire Tested: **S125DIW-S1270D1560U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333485-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1560U935-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9121.9 lumens
Efficiency: N/A
Efficacy: 110.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49																				
1	98	94	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42																				
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	42	40	35																				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30																				
4	75	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30	26																				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23																				
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20																				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18																				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16																				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14																				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13																				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10213	10213	10213	10213
5°	11826	10247	8972	10247
10°	13759	10194	7861	10194
15°	15230	10120	7252	10120
20°	17049	10001	6763	10001
25°	19973	9867	6524	9867
30°	21572	9735	6317	9735
35°	17738	9488	6180	9488
40°	12607	9144	6032	9144
45°	9685	8680	5946	8680
50°	8268	8106	5934	8106
55°	7362	7543	5986	7543
60°	6640	6926	6138	6926
65°	6134	6308	6298	6308
70°	5576	5665	6388	5665
75°	4923	4991	6331	4991
80°	4143	4069	5791	4069
85°	3283	2934	4676	2934



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.2	1.7
10°-20°	453.2	5.0
20°-30°	736.0	8.1
30°-40°	897.7	9.8
40°-50°	816.7	9.0
50°-60°	650.5	7.1
60°-70°	453.1	5.0
70°-80°	241.6	2.6
80°-90°	64.6	0.7
90°-100°	111.8	1.2
100°-110°	330.0	3.6
110°-120°	559.0	6.1
120°-130°	735.7	8.1
130°-140°	824.3	9.0
140°-150°	807.9	8.9
150°-160°	678.6	7.4
160°-170°	451.1	4.9
170°-180°	157.9	1.7
0°-30°	1341.4	14.7
0°-40°	2239.2	24.5
0°-60°	3706.4	40.6
0°-90°	4465.7	49.0
90°-120°	1000.8	11.0
90°-150°	3368.6	36.9
90°-180°	4656.0	51.0
0°-180°	9121.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1824	1581	1384	1581	1824	184
15°	2278	1514	1085	1514	2278	652
25°	2803	1385	916	1385	2803	1280
35°	2250	1203	784	1203	2250	1377
45°	1060	950	651	950	1060	849
55°	654	670	532	670	654	589
65°	401	413	412	413	401	398
75°	197	200	254	200	197	212
85°	44	40	63	40	44	52
90°	31	1	31	1	31	20
95°	112	84	112	84	112	114
105°	322	296	322	296	322	341
115°	565	560	565	560	565	559
125°	822	817	822	817	822	734
135°	1066	1062	1066	1062	1066	822
145°	1292	1287	1292	1287	1292	807
155°	1473	1473	1473	1473	1473	678
165°	1597	1601	1597	1601	1597	450
175°	1658	1665	1658	1665	1658	158
180°	1669	1669	1669	1669	1669	



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1672.6	1670.4	1668.3	1664.0	1667.2	1658.0	1653.7	1646.2	1637.1	1633.9	1630.1
5°	1824.2	1827.6	1830.9	1816.9	1818.2	1808.8	1787.3	1769.9	1755.8	1737.7	1724.9
7.5°	2006.8	1998.9	1998.2	1989.1	1973.4	1960.8	1938.2	1909.4	1881.7	1850.0	1823.9
10°	2098.1	2098.8	2092.7	2082.0	2065.2	2053.1	2023.6	1995.4	1961.2	1920.9	1892.0
12.5°	2166.8	2169.6	2162.0	2147.5	2139.2	2112.2	2089.0	2055.6	2014.8	1982.6	1938.7
15°	2277.9	2270.5	2265.2	2247.0	2233.0	2204.8	2167.9	2133.0	2088.7	2047.7	2006.8
17.5°	2385.1	2391.0	2380.9	2364.4	2320.7	2287.8	2238.3	2190.4	2135.3	2080.3	2031.5
20°	2480.6	2486.1	2470.6	2441.7	2389.4	2356.5	2291.4	2229.6	2165.8	2095.4	2041.7
22.5°	2599.9	2595.6	2574.7	2530.8	2485.4	2424.7	2354.2	2279.0	2199.2	2119.5	2048.1
25°	2802.8	2774.6	2761.8	2707.5	2647.7	2558.5	2461.9	2351.7	2252.5	2147.1	2055.8
27.5°	2915.3	2906.4	2892.2	2854.4	2791.5	2696.0	2582.1	2448.0	2307.9	2174.9	2055.4
30°	2892.7	2894.1	2895.5	2883.3	2843.1	2771.2	2657.8	2513.5	2347.1	2197.4	2059.2
32.5°	2693.0	2717.4	2740.8	2768.5	2779.7	2765.9	2694.8	2564.6	2393.2	2223.2	2057.0
35°	2249.8	2257.1	2333.0	2408.1	2510.2	2589.4	2642.4	2584.6	2440.3	2245.1	2054.4
37.5°	1754.2	1790.4	1842.9	1927.9	2075.1	2206.9	2376.4	2454.5	2407.9	2252.2	2049.8
40°	1495.4	1529.0	1563.1	1649.8	1773.9	1933.6	2126.2	2290.7	2328.9	2229.6	2033.7
42.5°	1295.6	1322.2	1360.2	1425.3	1529.0	1670.5	1854.6	2069.5	2201.7	2164.1	1999.8
45°	1060.4	1077.2	1106.7	1158.5	1233.6	1344.4	1506.8	1741.7	1946.4	2014.1	1919.5
47.5°	907.7	907.6	930.5	966.2	1020.5	1114.6	1234.7	1418.8	1637.4	1799.1	1791.7
50°	822.9	819.5	837.6	868.5	911.5	973.9	1088.6	1235.6	1445.7	1628.9	1679.9
52.5°	749.8	750.2	761.4	784.2	820.2	873.5	959.2	1091.7	1271.2	1459.2	1555.4
55°	653.8	651.0	663.7	679.2	705.4	740.3	802.0	903.4	1049.0	1234.2	1359.1
57.5°	565.7	573.1	578.2	588.9	610.6	634.0	686.0	760.4	876.0	1034.9	1166.9
60°	514.1	521.5	525.6	536.2	553.7	573.9	614.2	674.5	771.9	908.8	1039.7
62.5°	468.0	473.7	475.0	484.7	498.9	518.6	550.3	601.0	677.9	797.6	925.8
65°	401.4	401.4	404.1	414.1	420.9	438.2	462.4	499.4	561.1	654.4	763.8
67.5°	337.2	340.4	339.8	344.1	350.3	363.9	381.3	411.7	457.4	525.6	613.0
70°	295.3	298.0	297.3	300.7	307.4	316.2	330.2	359.0	391.9	450.4	525.6
72.5°	257.7	258.8	257.1	261.5	265.5	273.2	288.9	304.3	335.0	384.4	446.1
75°	197.3	198.6	200.0	202.7	206.7	210.8	218.8	234.3	254.3	291.3	330.9
77.5°	147.9	145.3	148.6	148.2	150.5	153.6	160.7	168.8	185.4	208.7	239.4
80°	111.4	112.1	112.1	112.8	116.1	118.1	124.2	130.2	142.9	160.4	181.9
82.5°	81.4	83.1	82.1	83.3	86.0	87.5	90.8	95.8	103.2	116.9	132.5
85°	44.3	41.0	42.3	43.7	43.7	44.3	47.0	49.0	53.0	58.4	64.4
87.5°	19.1	20.1	20.4	20.2	20.6	20.3	22.2	22.0	23.2	24.5	26.3
90°	31.2	30.3	29.4	28.6	27.7	26.5	25.1	23.7	22.2	20.8	18.8
92.5°	61.3	60.6	60.0	59.4	58.7	57.5	55.5	53.6	51.7	49.9	47.4
95°	111.7	111.1	110.6	109.9	109.3	108.1	106.1	104.0	102.0	100.0	97.1
97.5°	169.4	169.0	168.7	168.3	168.0	166.8	164.9	163.0	161.1	159.2	155.2
100°	212.9	212.4	211.8	211.2	210.7	209.1	206.5	203.9	201.3	198.6	194.9
102.5°	256.6	255.8	254.9	254.2	253.4	251.5	248.7	245.9	243.1	240.2	238.3
105°	322.0	321.2	320.3	319.4	318.6	317.3	315.6	313.8	312.1	310.4	308.6
107.5°	389.0	389.1	389.2	389.2	389.3	388.8	388.0	387.1	386.2	385.4	384.1
110°	438.9	439.2	439.5	439.8	440.1	439.8	438.9	438.1	437.1	436.3	435.4



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	487.8	488.3	488.8	489.3	489.8	489.8	489.5	489.0	488.6	488.3	487.2
115°	564.9	565.2	565.4	565.8	566.0	566.3	566.6	566.9	567.1	567.5	566.9
117.5°	640.2	641.4	642.5	643.6	644.8	645.2	645.1	644.8	644.5	644.4	643.8
120°	692.2	693.3	694.4	695.6	696.7	697.3	697.3	697.3	697.3	697.3	697.0
122.5°	744.1	744.9	745.9	746.8	747.8	748.3	748.6	748.8	749.0	749.2	748.5
125°	822.0	822.3	822.5	822.9	823.1	823.5	824.1	824.8	825.3	825.9	825.6
127.5°	896.7	897.3	897.9	898.5	899.1	899.5	899.8	900.1	900.3	900.7	900.3
130°	946.7	947.2	947.8	948.4	948.9	949.3	949.7	949.9	950.2	950.5	949.9
132.5°	993.3	994.2	995.0	995.8	996.6	997.1	997.5	997.7	998.0	998.3	998.4
135°	1066.1	1067.2	1068.4	1069.5	1070.7	1071.3	1071.3	1071.3	1071.3	1071.3	1071.0
137.5°	1137.2	1138.7	1140.1	1141.6	1143.1	1143.6	1143.2	1142.9	1142.5	1142.2	1141.5
140°	1182.9	1184.4	1185.9	1187.3	1188.7	1189.1	1188.6	1188.0	1187.4	1186.9	1186.0
142.5°	1226.6	1228.0	1229.5	1230.9	1232.3	1233.0	1232.5	1232.2	1231.8	1231.5	1230.5
145°	1292.0	1292.9	1293.7	1294.6	1295.5	1295.9	1295.9	1295.9	1295.9	1295.9	1295.0
147.5°	1347.9	1349.9	1351.8	1353.8	1355.7	1356.3	1355.6	1355.0	1354.3	1353.6	1352.9
150°	1389.4	1390.0	1390.6	1391.1	1391.7	1392.1	1392.1	1392.1	1392.1	1392.1	1390.9
152.5°	1423.7	1424.8	1425.8	1426.8	1427.9	1428.1	1427.4	1426.7	1426.0	1425.3	1424.8
155°	1472.6	1473.9	1475.4	1476.9	1478.3	1478.4	1477.3	1476.1	1475.0	1473.9	1473.5
157.5°	1513.3	1515.2	1517.1	1519.0	1521.0	1521.3	1520.2	1519.0	1517.9	1516.7	1516.4
160°	1541.4	1542.8	1544.2	1545.7	1547.1	1547.3	1546.1	1545.0	1543.8	1542.7	1542.4
162.5°	1565.2	1566.9	1568.6	1570.3	1571.9	1572.1	1570.7	1569.3	1568.0	1566.5	1566.5
165°	1597.2	1599.0	1600.7	1602.4	1604.1	1604.4	1603.3	1602.1	1600.9	1599.8	1599.5
167.5°	1622.6	1624.4	1626.3	1628.0	1629.8	1629.8	1628.1	1626.3	1624.6	1622.9	1622.9
170°	1636.2	1638.1	1640.2	1642.2	1644.3	1644.3	1642.6	1640.9	1639.2	1637.4	1637.4
172.5°	1647.6	1649.3	1651.1	1652.9	1654.8	1654.8	1653.0	1651.3	1649.6	1647.9	1647.9
175°	1658.2	1660.3	1662.2	1664.3	1666.3	1666.5	1664.7	1663.0	1661.2	1659.5	1659.5
177.5°	1664.5	1666.0	1667.7	1669.3	1670.9	1671.0	1669.7	1668.3	1666.9	1665.5	1665.7
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1626.9	1623.2	1618.9	1611.4	1602.2	1597.4	1589.8	1585.0	1575.4	1567.3	1558.8
5°	1709.4	1692.0	1675.9	1655.1	1632.3	1617.5	1600.1	1580.6	1560.5	1539.6	1516.8
7.5°	1795.0	1764.1	1730.5	1694.4	1659.1	1626.6	1595.6	1565.1	1536.7	1502.4	1473.3
10°	1852.4	1813.5	1771.9	1722.9	1675.2	1633.7	1591.3	1554.4	1516.8	1476.5	1441.0
12.5°	1909.9	1858.0	1799.2	1745.4	1688.2	1637.9	1588.1	1541.0	1493.7	1449.1	1407.7
15°	1950.4	1904.8	1850.4	1773.9	1709.4	1640.4	1574.6	1513.5	1456.5	1406.8	1354.4
17.5°	1977.1	1918.3	1859.9	1786.5	1702.1	1624.8	1550.2	1480.3	1416.0	1353.1	1302.6
20°	1981.9	1921.6	1860.4	1788.6	1702.1	1613.5	1539.0	1455.1	1386.0	1320.9	1259.1
22.5°	1980.4	1911.9	1845.5	1771.5	1687.0	1605.4	1515.4	1429.9	1354.8	1290.8	1226.3
25°	1965.1	1892.0	1808.8	1734.3	1651.1	1564.5	1473.3	1384.7	1308.1	1234.9	1171.2
27.5°	1952.6	1857.7	1763.4	1676.5	1596.2	1516.8	1429.4	1338.7	1253.9	1179.7	1119.6
30°	1937.0	1833.0	1726.9	1636.3	1553.8	1476.5	1394.0	1305.4	1216.9	1144.4	1080.0
32.5°	1923.0	1801.8	1689.9	1591.2	1503.8	1428.7	1352.6	1268.3	1181.4	1107.8	1043.4
35°	1896.1	1755.8	1627.5	1516.1	1422.9	1345.7	1281.9	1203.4	1123.5	1052.4	990.7
37.5°	1861.8	1695.4	1557.8	1441.0	1338.7	1257.4	1198.0	1137.7	1061.1	992.6	936.7
40°	1835.0	1652.4	1506.8	1387.3	1281.3	1196.7	1141.7	1084.6	1020.9	957.1	898.0
42.5°	1801.1	1613.8	1455.3	1326.6	1221.7	1139.3	1081.5	1033.0	976.8	917.4	862.5
45°	1739.0	1543.7	1371.8	1233.6	1127.6	1046.4	986.6	950.4	908.1	851.7	805.4
47.5°	1647.6	1459.5	1281.8	1139.1	1029.7	954.4	898.5	863.7	833.9	791.9	749.9
50°	1566.5	1396.7	1216.9	1075.2	965.8	889.9	838.3	806.8	781.3	749.0	713.4
52.5°	1475.8	1317.8	1153.0	1013.0	904.6	829.8	779.2	751.5	730.2	707.1	672.1
55°	1331.6	1197.4	1044.3	911.5	811.4	738.3	694.0	669.9	652.4	634.9	613.5
57.5°	1172.8	1067.8	932.3	810.8	718.7	652.1	610.8	587.3	573.7	564.7	552.1
60°	1061.1	971.2	854.4	743.6	653.8	594.7	554.4	536.2	524.9	517.5	508.1
62.5°	957.5	883.6	775.5	674.4	595.7	539.8	503.9	486.3	475.4	471.8	464.1
65°	804.7	747.7	658.4	574.5	507.4	459.8	429.6	412.8	406.0	402.0	402.7
67.5°	654.3	619.5	547.8	476.2	422.7	382.7	358.5	345.7	342.3	336.9	336.8
70°	562.4	536.2	475.9	413.5	365.8	334.9	313.4	300.0	296.6	293.9	293.3
72.5°	481.4	458.4	406.0	356.0	313.1	286.0	268.4	260.3	254.8	253.1	253.0
75°	361.8	349.0	307.4	267.8	238.2	219.5	207.4	200.0	196.0	195.3	196.0
77.5°	257.2	246.1	219.6	191.6	172.9	158.7	148.4	145.9	141.4	141.5	140.8
80°	193.3	185.9	169.1	147.0	131.6	119.5	114.1	109.4	108.1	106.1	108.1
82.5°	140.2	132.2	120.8	106.7	93.9	86.7	81.4	79.9	79.0	78.1	78.5
85°	69.1	69.8	63.1	52.3	47.0	43.0	39.6	39.6	38.9	38.2	38.9
87.5°	26.9	25.5	22.9	20.9	17.7	15.7	14.7	14.7	13.6	13.5	14.6
90°	16.7	14.7	12.7	10.5	8.3	5.9	3.6	1.3	3.6	5.9	8.3
92.5°	44.9	42.4	40.0	37.9	36.2	34.7	33.1	31.4	33.1	34.7	36.2
95°	94.2	91.4	88.4	86.7	86.1	85.6	85.0	84.4	85.0	85.6	86.1
97.5°	151.3	147.2	143.3	141.2	140.9	140.7	140.4	140.3	140.4	140.7	140.9
100°	191.1	187.4	183.7	181.8	181.8	181.8	181.8	181.8	181.8	181.8	181.8
102.5°	236.4	234.5	232.6	231.1	229.9	228.8	227.6	226.4	227.6	228.8	229.9
105°	306.9	305.1	303.4	301.9	300.4	298.9	297.5	296.1	297.5	298.9	300.4
107.5°	382.7	381.4	380.1	378.7	377.3	375.8	374.4	372.9	374.4	375.8	377.3
110°	434.5	433.7	432.8	431.7	430.2	428.8	427.4	425.9	427.4	428.8	430.2



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	486.0	484.9	483.9	482.9	482.2	481.5	480.7	479.9	480.7	481.5	482.2
115°	566.3	565.8	565.2	564.3	563.1	562.0	560.9	559.6	560.9	562.0	563.1
117.5°	643.3	642.7	642.2	641.7	641.2	640.7	640.2	639.6	640.2	640.7	641.2
120°	696.7	696.5	696.1	695.3	693.9	692.4	691.0	689.5	691.0	692.4	693.9
122.5°	747.8	747.0	746.2	745.6	745.1	744.6	744.1	743.6	744.1	744.6	745.1
125°	825.3	825.0	824.8	823.7	822.0	820.3	818.5	816.7	818.5	820.3	822.0
127.5°	900.0	899.7	899.3	898.6	897.6	896.6	895.7	894.7	895.7	896.6	897.6
130°	949.3	948.8	948.2	947.2	945.7	944.3	942.9	941.4	942.9	944.3	945.7
132.5°	998.5	998.7	998.8	997.6	995.3	992.9	990.6	988.2	990.6	992.9	995.3
135°	1070.7	1070.4	1070.1	1069.1	1067.4	1065.7	1063.9	1062.2	1063.9	1065.7	1067.4
137.5°	1140.9	1140.3	1139.6	1138.5	1136.8	1135.1	1133.5	1131.8	1133.5	1135.1	1136.8
140°	1185.2	1184.2	1183.4	1182.2	1180.8	1179.3	1177.9	1176.5	1177.9	1179.3	1180.8
142.5°	1229.3	1228.2	1227.1	1226.0	1224.8	1223.6	1222.4	1221.2	1222.4	1223.6	1224.8
145°	1294.2	1293.3	1292.4	1291.5	1290.3	1289.2	1288.0	1286.9	1288.0	1289.2	1290.3
147.5°	1352.2	1351.5	1350.8	1350.1	1349.5	1348.8	1348.2	1347.6	1348.2	1348.8	1349.5
150°	1389.7	1388.5	1387.4	1387.0	1387.2	1387.6	1387.8	1388.1	1387.8	1387.6	1387.2
152.5°	1424.4	1423.9	1423.4	1423.0	1422.5	1422.2	1421.8	1421.3	1421.8	1422.2	1422.5
155°	1473.3	1473.0	1472.7	1472.6	1472.6	1472.6	1472.6	1472.6	1472.6	1472.6	1472.6
157.5°	1516.1	1515.8	1515.5	1515.7	1516.3	1517.0	1517.6	1518.2	1517.6	1517.0	1516.3
160°	1542.1	1541.8	1541.5	1541.8	1542.7	1543.5	1544.4	1545.2	1544.4	1543.5	1542.7
162.5°	1566.4	1566.3	1566.3	1566.6	1567.3	1567.9	1568.5	1569.2	1568.5	1567.9	1567.3
165°	1599.2	1599.0	1598.6	1598.8	1599.4	1599.9	1600.5	1601.1	1600.5	1599.9	1599.4
167.5°	1622.9	1622.9	1622.9	1623.5	1624.6	1625.8	1626.9	1628.1	1626.9	1625.8	1624.6
170°	1637.4	1637.4	1637.4	1638.1	1639.2	1640.3	1641.5	1642.6	1641.5	1640.3	1639.2
172.5°	1647.9	1647.9	1647.9	1648.4	1649.6	1650.7	1651.9	1653.0	1651.9	1650.7	1649.6
175°	1659.5	1659.5	1659.5	1660.1	1661.2	1662.4	1663.5	1664.7	1663.5	1662.4	1661.2
177.5°	1665.9	1666.2	1666.4	1667.0	1667.9	1668.9	1669.7	1670.7	1669.7	1668.9	1667.9
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1553.8	1548.0	1543.2	1532.4	1526.5	1518.5	1512.0	1519.0	1511.5	1514.7	1509.8
5°	1505.5	1486.6	1473.3	1453.7	1437.0	1421.5	1410.1	1408.1	1402.7	1400.1	1392.0
7.5°	1447.2	1423.7	1400.6	1375.1	1353.6	1331.7	1317.8	1306.2	1298.6	1288.5	1281.7
10°	1412.8	1381.3	1354.4	1323.5	1296.7	1273.2	1254.4	1245.0	1236.3	1223.6	1218.8
12.5°	1370.4	1337.7	1305.0	1272.0	1246.2	1220.0	1203.9	1189.7	1183.7	1169.3	1167.9
15°	1319.5	1270.5	1238.3	1204.7	1169.2	1147.7	1134.3	1118.9	1112.2	1102.1	1094.7
17.5°	1258.9	1215.0	1174.8	1140.1	1109.6	1091.5	1074.8	1064.2	1052.7	1046.1	1034.0
20°	1214.8	1173.2	1132.9	1096.1	1072.5	1051.7	1038.3	1028.2	1016.2	1012.8	1000.7
22.5°	1177.8	1131.9	1093.2	1062.2	1036.6	1013.1	998.6	991.7	983.4	973.1	970.6
25°	1117.5	1069.9	1037.0	1006.1	983.3	961.8	951.7	943.0	935.0	927.6	924.9
27.5°	1065.4	1022.9	983.8	955.9	936.0	916.4	907.6	897.0	891.0	885.1	877.9
30°	1028.9	985.2	951.1	924.2	902.8	885.3	875.9	868.5	863.2	857.7	853.8
32.5°	991.4	950.9	917.7	891.5	870.0	856.8	848.5	843.3	837.3	830.9	825.8
35°	941.7	897.3	865.1	842.3	825.5	815.5	806.1	801.3	794.7	794.7	789.3
37.5°	885.7	847.4	819.0	798.1	783.1	774.1	764.0	760.7	756.4	753.5	751.7
40°	852.4	816.8	790.0	769.1	753.0	745.6	737.6	732.3	729.5	726.2	724.9
42.5°	818.0	784.0	758.3	739.1	725.1	718.8	711.3	707.6	702.1	697.8	697.0
45°	765.8	732.9	709.5	694.0	681.9	674.5	669.9	661.8	659.1	653.8	653.1
47.5°	716.3	684.8	661.7	649.0	638.4	632.4	625.0	616.9	613.9	611.1	610.9
50°	679.2	650.4	628.9	616.8	606.7	598.1	590.6	585.2	583.2	583.2	584.6
52.5°	641.6	617.1	598.8	584.0	574.5	565.2	558.4	555.2	552.1	555.3	557.8
55°	586.6	561.8	548.4	534.3	524.9	514.1	510.7	509.5	507.4	512.8	515.5
57.5°	528.3	510.9	495.2	481.2	472.8	466.6	462.0	461.2	465.0	467.5	476.2
60°	491.3	471.1	457.1	446.3	436.3	432.2	430.9	429.6	432.2	439.6	451.0
62.5°	450.5	434.1	419.0	410.9	403.5	396.8	396.5	397.4	402.7	411.1	422.6
65°	390.6	376.5	366.4	357.1	351.0	347.0	348.4	351.0	357.1	368.5	381.3
67.5°	329.8	320.1	311.2	303.5	297.7	297.7	299.1	303.1	310.2	323.4	335.0
70°	290.6	279.9	272.5	269.1	264.4	261.7	265.8	272.5	278.5	290.6	300.7
72.5°	251.4	242.3	236.5	234.3	232.2	230.1	231.4	238.7	246.8	258.9	270.6
75°	193.3	189.9	185.9	183.2	181.2	182.5	183.9	190.6	197.3	210.1	223.5
77.5°	141.1	137.6	135.2	134.5	133.5	134.1	137.8	142.8	149.4	158.7	168.8
80°	106.7	105.4	104.0	103.3	103.3	104.0	109.4	112.8	118.8	127.5	135.6
82.5°	77.7	76.9	76.6	76.5	77.1	77.1	80.4	84.8	89.8	96.3	103.3
85°	41.0	39.6	41.6	42.3	41.0	43.0	44.3	47.0	49.0	52.3	55.7
87.5°	15.5	17.0	16.9	17.8	18.3	19.7	19.5	22.0	23.2	24.6	24.4
90°	10.5	12.7	14.7	16.7	18.8	20.8	22.2	23.7	25.1	26.5	27.7
92.5°	37.9	40.0	42.4	44.9	47.4	49.9	51.7	53.6	55.5	57.5	58.7
95°	86.7	88.4	91.4	94.2	97.1	100.0	102.0	104.0	106.1	108.1	109.3
97.5°	141.2	143.3	147.2	151.3	155.2	159.2	161.1	163.0	164.9	166.8	168.0
100°	181.8	183.7	187.4	191.1	194.9	198.6	201.3	203.9	206.5	209.1	210.7
102.5°	231.1	232.6	234.5	236.4	238.3	240.2	243.1	245.9	248.7	251.5	253.4
105°	301.9	303.4	305.1	306.9	308.6	310.4	312.1	313.8	315.6	317.3	318.6
107.5°	378.7	380.1	381.4	382.7	384.1	385.4	386.2	387.1	388.0	388.8	389.3
110°	431.7	432.8	433.7	434.5	435.4	436.3	437.1	438.1	438.9	439.8	440.1



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	482.9	483.9	484.9	486.0	487.2	488.3	488.6	489.0	489.5	489.8	489.8
115°	564.3	565.2	565.8	566.3	566.9	567.5	567.1	566.9	566.6	566.3	566.0
117.5°	641.7	642.2	642.7	643.3	643.8	644.4	644.5	644.8	645.1	645.2	644.8
120°	695.3	696.1	696.5	696.7	697.0	697.3	697.3	697.3	697.3	697.3	696.7
122.5°	745.6	746.2	747.0	747.8	748.5	749.2	749.0	748.8	748.6	748.3	747.8
125°	823.7	824.8	825.0	825.3	825.6	825.9	825.3	824.8	824.1	823.5	823.1
127.5°	898.6	899.3	899.7	900.0	900.3	900.7	900.3	900.1	899.8	899.5	899.1
130°	947.2	948.2	948.8	949.3	949.9	950.5	950.2	949.9	949.7	949.3	948.9
132.5°	997.6	998.8	998.7	998.5	998.4	998.3	998.0	997.7	997.5	997.1	996.6
135°	1069.1	1070.1	1070.4	1070.7	1071.0	1071.3	1071.3	1071.3	1071.3	1071.3	1070.7
137.5°	1138.5	1139.6	1140.3	1140.9	1141.5	1142.2	1142.5	1142.9	1143.2	1143.6	1143.1
140°	1182.2	1183.4	1184.2	1185.2	1186.0	1186.9	1187.4	1188.0	1188.6	1189.1	1188.7
142.5°	1226.0	1227.1	1228.2	1229.3	1230.5	1231.5	1231.8	1232.2	1232.5	1233.0	1232.3
145°	1291.5	1292.4	1293.3	1294.2	1295.0	1295.9	1295.9	1295.9	1295.9	1295.9	1295.5
147.5°	1350.1	1350.8	1351.5	1352.2	1352.9	1353.6	1354.3	1355.0	1355.6	1356.3	1355.7
150°	1387.0	1387.4	1388.5	1389.7	1390.9	1392.1	1392.1	1392.1	1392.1	1392.1	1391.7
152.5°	1423.0	1423.4	1423.9	1424.4	1424.8	1425.3	1426.0	1426.7	1427.4	1428.1	1427.9
155°	1472.6	1472.7	1473.0	1473.3	1473.5	1473.9	1475.0	1476.1	1477.3	1478.4	1478.3
157.5°	1515.7	1515.5	1515.8	1516.1	1516.4	1516.7	1517.9	1519.0	1520.2	1521.3	1521.0
160°	1541.8	1541.5	1541.8	1542.1	1542.4	1542.7	1543.8	1545.0	1546.1	1547.3	1547.1
162.5°	1566.6	1566.3	1566.3	1566.4	1566.5	1566.5	1568.0	1569.3	1570.7	1572.1	1571.9
165°	1598.8	1598.6	1599.0	1599.2	1599.5	1599.8	1600.9	1602.1	1603.3	1604.4	1604.1
167.5°	1623.5	1622.9	1622.9	1622.9	1622.9	1622.9	1624.6	1626.3	1628.1	1629.8	1629.8
170°	1638.1	1637.4	1637.4	1637.4	1637.4	1637.4	1639.2	1640.9	1642.6	1644.3	1644.3
172.5°	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.6	1651.3	1653.0	1654.8	1654.8
175°	1660.1	1659.5	1659.5	1659.5	1659.5	1659.5	1661.2	1663.0	1664.7	1666.5	1666.3
177.5°	1667.0	1666.4	1666.2	1665.9	1665.7	1665.5	1666.9	1668.3	1669.7	1671.0	1670.9
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1506.7	1510.4	1507.2	1511.5	1507.2	1510.4	1506.7	1509.8	1514.7	1511.5	1519.0
5°	1388.6	1382.6	1386.6	1384.0	1386.6	1382.6	1388.6	1392.0	1400.1	1402.7	1408.1
7.5°	1279.6	1273.8	1267.3	1264.2	1267.3	1273.8	1279.6	1281.7	1288.5	1298.6	1306.2
10°	1211.4	1204.1	1203.4	1198.7	1203.4	1204.1	1211.4	1218.8	1223.6	1236.3	1245.0
12.5°	1161.5	1154.7	1147.0	1145.0	1147.0	1154.7	1161.5	1167.9	1169.3	1183.7	1189.7
15°	1090.6	1085.3	1080.6	1084.6	1080.6	1085.3	1090.6	1094.7	1102.1	1112.2	1118.9
17.5°	1031.7	1027.3	1026.5	1021.5	1026.5	1027.3	1031.7	1034.0	1046.1	1052.7	1064.2
20°	994.7	991.4	992.6	984.0	992.6	991.4	994.7	1000.7	1012.8	1016.2	1028.2
22.5°	965.2	958.6	957.8	956.1	957.8	958.6	965.2	970.6	973.1	983.4	991.7
25°	918.9	915.5	912.1	915.5	912.1	915.5	918.9	924.9	927.6	935.0	943.0
27.5°	878.4	874.4	873.5	873.8	873.5	874.4	878.4	877.9	885.1	891.0	897.0
30°	853.8	847.1	847.7	847.1	847.7	847.1	853.8	853.8	857.7	863.2	868.5
32.5°	826.9	822.3	821.4	820.2	821.4	822.3	826.9	825.8	830.9	837.3	843.3
35°	787.3	787.3	783.9	783.9	783.9	787.3	787.3	789.3	794.7	794.7	801.3
37.5°	750.1	749.4	747.4	747.7	747.4	749.4	750.1	751.7	753.5	756.4	760.7
40°	722.2	721.5	719.5	715.5	719.5	721.5	722.2	724.9	726.2	729.5	732.3
42.5°	695.3	693.0	692.1	690.8	692.1	693.0	695.3	697.0	697.8	702.1	707.6
45°	653.1	653.1	651.7	651.0	651.7	653.1	653.1	653.1	653.8	659.1	661.8
47.5°	612.0	613.2	615.7	615.4	615.7	613.2	612.0	610.9	611.1	613.9	616.9
50°	587.3	588.0	590.0	590.6	590.0	588.0	587.3	584.6	583.2	583.2	585.2
52.5°	559.9	563.8	566.4	565.9	566.4	563.8	559.9	557.8	555.3	552.1	555.2
55°	521.5	526.2	530.9	531.6	530.9	526.2	521.5	515.5	512.8	507.4	509.5
57.5°	483.5	490.1	495.1	496.6	495.1	490.1	483.5	476.2	467.5	465.0	461.2
60°	457.7	466.5	472.5	475.2	472.5	466.5	457.7	451.0	439.6	432.2	429.6
62.5°	433.0	442.8	448.8	449.4	448.8	442.8	433.0	422.6	411.1	402.7	397.4
65°	392.6	402.7	408.0	412.1	408.0	402.7	392.6	381.3	368.5	357.1	351.0
67.5°	349.1	359.2	365.2	368.3	365.2	359.2	349.1	335.0	323.4	310.2	303.1
70°	317.5	327.5	335.6	338.3	335.6	327.5	317.5	300.7	290.6	278.5	272.5
72.5°	286.3	295.3	301.8	305.0	301.8	295.3	286.3	270.6	258.9	246.8	238.7
75°	232.2	244.3	250.4	253.7	250.4	244.3	232.2	223.5	210.1	197.3	190.6
77.5°	179.1	190.1	193.7	195.4	193.7	190.1	179.1	168.8	158.7	149.4	142.8
80°	143.6	150.3	155.1	155.7	155.1	150.3	143.6	135.6	127.5	118.8	112.8
82.5°	110.4	116.0	117.4	119.2	117.4	116.0	110.4	103.3	96.3	89.8	84.8
85°	60.4	63.1	63.8	63.1	63.8	63.1	60.4	55.7	52.3	49.0	47.0
87.5°	25.6	25.2	25.4	26.6	25.4	25.2	25.6	24.4	24.6	23.2	22.0
90°	28.6	29.4	30.3	31.2	30.3	29.4	28.6	27.7	26.5	25.1	23.7
92.5°	59.4	60.0	60.6	61.3	60.6	60.0	59.4	58.7	57.5	55.5	53.6
95°	109.9	110.6	111.1	111.7	111.1	110.6	109.9	109.3	108.1	106.1	104.0
97.5°	168.3	168.7	169.0	169.4	169.0	168.7	168.3	168.0	166.8	164.9	163.0
100°	211.2	211.8	212.4	212.9	212.4	211.8	211.2	210.7	209.1	206.5	203.9
102.5°	254.2	254.9	255.8	256.6	255.8	254.9	254.2	253.4	251.5	248.7	245.9
105°	319.4	320.3	321.2	322.0	321.2	320.3	319.4	318.6	317.3	315.6	313.8
107.5°	389.2	389.2	389.1	389.0	389.1	389.2	389.2	389.3	388.8	388.0	387.1
110°	439.8	439.5	439.2	438.9	439.2	439.5	439.8	440.1	439.8	438.9	438.1



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	489.3	488.8	488.3	487.8	488.3	488.8	489.3	489.8	489.8	489.5	489.0
115°	565.8	565.4	565.2	564.9	565.2	565.4	565.8	566.0	566.3	566.6	566.9
117.5°	643.6	642.5	641.4	640.2	641.4	642.5	643.6	644.8	645.2	645.1	644.8
120°	695.6	694.4	693.3	692.2	693.3	694.4	695.6	696.7	697.3	697.3	697.3
122.5°	746.8	745.9	744.9	744.1	744.9	745.9	746.8	747.8	748.3	748.6	748.8
125°	822.9	822.5	822.3	822.0	822.3	822.5	822.9	823.1	823.5	824.1	824.8
127.5°	898.5	897.9	897.3	896.7	897.3	897.9	898.5	899.1	899.5	899.8	900.1
130°	948.4	947.8	947.2	946.7	947.2	947.8	948.4	948.9	949.3	949.7	949.9
132.5°	995.8	995.0	994.2	993.3	994.2	995.0	995.8	996.6	997.1	997.5	997.7
135°	1069.5	1068.4	1067.2	1066.1	1067.2	1068.4	1069.5	1070.7	1071.3	1071.3	1071.3
137.5°	1141.6	1140.1	1138.7	1137.2	1138.7	1140.1	1141.6	1143.1	1143.6	1143.2	1142.9
140°	1187.3	1185.9	1184.4	1182.9	1184.4	1185.9	1187.3	1188.7	1189.1	1188.6	1188.0
142.5°	1230.9	1229.5	1228.0	1226.6	1228.0	1229.5	1230.9	1232.3	1233.0	1232.5	1232.2
145°	1294.6	1293.7	1292.9	1292.0	1292.9	1293.7	1294.6	1295.5	1295.9	1295.9	1295.9
147.5°	1353.8	1351.8	1349.9	1347.9	1349.9	1351.8	1353.8	1355.7	1356.3	1355.6	1355.0
150°	1391.1	1390.6	1390.0	1389.4	1390.0	1390.6	1391.1	1391.7	1392.1	1392.1	1392.1
152.5°	1426.8	1425.8	1424.8	1423.7	1424.8	1425.8	1426.8	1427.9	1428.1	1427.4	1426.7
155°	1476.9	1475.4	1473.9	1472.6	1473.9	1475.4	1476.9	1478.3	1478.4	1477.3	1476.1
157.5°	1519.0	1517.1	1515.2	1513.3	1515.2	1517.1	1519.0	1521.0	1521.3	1520.2	1519.0
160°	1545.7	1544.2	1542.8	1541.4	1542.8	1544.2	1545.7	1547.1	1547.3	1546.1	1545.0
162.5°	1570.3	1568.6	1566.9	1565.2	1566.9	1568.6	1570.3	1571.9	1572.1	1570.7	1569.3
165°	1602.4	1600.7	1599.0	1597.2	1599.0	1600.7	1602.4	1604.1	1604.4	1603.3	1602.1
167.5°	1628.0	1626.3	1624.4	1622.6	1624.4	1626.3	1628.0	1629.8	1629.8	1628.1	1626.3
170°	1642.2	1640.2	1638.1	1636.2	1638.1	1640.2	1642.2	1644.3	1644.3	1642.6	1640.9
172.5°	1652.9	1651.1	1649.3	1647.6	1649.3	1651.1	1652.9	1654.8	1654.8	1653.0	1651.3
175°	1664.3	1662.2	1660.3	1658.2	1660.3	1662.2	1664.3	1666.3	1666.5	1664.7	1663.0
177.5°	1669.3	1667.7	1666.0	1664.5	1666.0	1667.7	1669.3	1670.9	1671.0	1669.7	1668.3
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1512.0	1518.5	1526.5	1532.4	1543.2	1548.0	1553.8	1558.8	1567.3	1575.4	1585.0
5°	1410.1	1421.5	1437.0	1453.7	1473.3	1486.6	1505.5	1516.8	1539.6	1560.5	1580.6
7.5°	1317.8	1331.7	1353.6	1375.1	1400.6	1423.7	1447.2	1473.3	1502.4	1536.7	1565.1
10°	1254.4	1273.2	1296.7	1323.5	1354.4	1381.3	1412.8	1441.0	1476.5	1516.8	1554.4
12.5°	1203.9	1220.0	1246.2	1272.0	1305.0	1337.7	1370.4	1407.7	1449.1	1493.7	1541.0
15°	1134.3	1147.7	1169.2	1204.7	1238.3	1270.5	1319.5	1354.4	1406.8	1456.5	1513.5
17.5°	1074.8	1091.5	1109.6	1140.1	1174.8	1215.0	1258.9	1302.6	1353.1	1416.0	1480.3
20°	1038.3	1051.7	1072.5	1096.1	1132.9	1173.2	1214.8	1259.1	1320.9	1386.0	1455.1
22.5°	998.6	1013.1	1036.6	1062.2	1093.2	1131.9	1177.8	1226.3	1290.8	1354.8	1429.9
25°	951.7	961.8	983.3	1006.1	1037.0	1069.9	1117.5	1171.2	1234.9	1308.1	1384.7
27.5°	907.6	916.4	936.0	955.9	983.8	1022.9	1065.4	1119.6	1179.7	1253.9	1338.7
30°	875.9	885.3	902.8	924.2	951.1	985.2	1028.9	1080.0	1144.4	1216.9	1305.4
32.5°	848.5	856.8	870.0	891.5	917.7	950.9	991.4	1043.4	1107.8	1181.4	1268.3
35°	806.1	815.5	825.5	842.3	865.1	897.3	941.7	990.7	1052.4	1123.5	1203.4
37.5°	764.0	774.1	783.1	798.1	819.0	847.4	885.7	936.7	992.6	1061.1	1137.7
40°	737.6	745.6	753.0	769.1	790.0	816.8	852.4	898.0	957.1	1020.9	1084.6
42.5°	711.3	718.8	725.1	739.1	758.3	784.0	818.0	862.5	917.4	976.8	1033.0
45°	669.9	674.5	681.9	694.0	709.5	732.9	765.8	805.4	851.7	908.1	950.4
47.5°	625.0	632.4	638.4	649.0	661.7	684.8	716.3	749.9	791.9	833.9	863.7
50°	590.6	598.1	606.7	616.8	628.9	650.4	679.2	713.4	749.0	781.3	806.8
52.5°	558.4	565.2	574.5	584.0	598.8	617.1	641.6	672.1	707.1	730.2	751.5
55°	510.7	514.1	524.9	534.3	548.4	561.8	586.6	613.5	634.9	652.4	669.9
57.5°	462.0	466.6	472.8	481.2	495.2	510.9	528.3	552.1	564.7	573.7	587.3
60°	430.9	432.2	436.3	446.3	457.1	471.1	491.3	508.1	517.5	524.9	536.2
62.5°	396.5	396.8	403.5	410.9	419.0	434.1	450.5	464.1	471.8	475.4	486.3
65°	348.4	347.0	351.0	357.1	366.4	376.5	390.6	402.7	402.0	406.0	412.8
67.5°	299.1	297.7	297.7	303.5	311.2	320.1	329.8	336.8	336.9	342.3	345.7
70°	265.8	261.7	264.4	269.1	272.5	279.9	290.6	293.3	293.9	296.6	300.0
72.5°	231.4	230.1	232.2	234.3	236.5	242.3	251.4	253.0	253.1	254.8	260.3
75°	183.9	182.5	181.2	183.2	185.9	189.9	193.3	196.0	195.3	196.0	200.0
77.5°	137.8	134.1	133.5	134.5	135.2	137.6	141.1	140.8	141.5	141.4	145.9
80°	109.4	104.0	103.3	103.3	104.0	105.4	106.7	108.1	106.1	108.1	109.4
82.5°	80.4	77.1	77.1	76.5	76.6	76.9	77.7	78.5	78.1	79.0	79.9
85°	44.3	43.0	41.0	42.3	41.6	39.6	41.0	38.9	38.2	38.9	39.6
87.5°	19.5	19.7	18.3	17.8	16.9	17.0	15.5	14.6	13.5	13.6	14.7
90°	22.2	20.8	18.8	16.7	14.7	12.7	10.5	8.3	5.9	3.6	1.3
92.5°	51.7	49.9	47.4	44.9	42.4	40.0	37.9	36.2	34.7	33.1	31.4
95°	102.0	100.0	97.1	94.2	91.4	88.4	86.7	86.1	85.6	85.0	84.4
97.5°	161.1	159.2	155.2	151.3	147.2	143.3	141.2	140.9	140.7	140.4	140.3
100°	201.3	198.6	194.9	191.1	187.4	183.7	181.8	181.8	181.8	181.8	181.8
102.5°	243.1	240.2	238.3	236.4	234.5	232.6	231.1	229.9	228.8	227.6	226.4
105°	312.1	310.4	308.6	306.9	305.1	303.4	301.9	300.4	298.9	297.5	296.1
107.5°	386.2	385.4	384.1	382.7	381.4	380.1	378.7	377.3	375.8	374.4	372.9
110°	437.1	436.3	435.4	434.5	433.7	432.8	431.7	430.2	428.8	427.4	425.9



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	488.6	488.3	487.2	486.0	484.9	483.9	482.9	482.2	481.5	480.7	479.9
115°	567.1	567.5	566.9	566.3	565.8	565.2	564.3	563.1	562.0	560.9	559.6
117.5°	644.5	644.4	643.8	643.3	642.7	642.2	641.7	641.2	640.7	640.2	639.6
120°	697.3	697.3	697.0	696.7	696.5	696.1	695.3	693.9	692.4	691.0	689.5
122.5°	749.0	749.2	748.5	747.8	747.0	746.2	745.6	745.1	744.6	744.1	743.6
125°	825.3	825.9	825.6	825.3	825.0	824.8	823.7	822.0	820.3	818.5	816.7
127.5°	900.3	900.7	900.3	900.0	899.7	899.3	898.6	897.6	896.6	895.7	894.7
130°	950.2	950.5	949.9	949.3	948.8	948.2	947.2	945.7	944.3	942.9	941.4
132.5°	998.0	998.3	998.4	998.5	998.7	998.8	997.6	995.3	992.9	990.6	988.2
135°	1071.3	1071.3	1071.0	1070.7	1070.4	1070.1	1069.1	1067.4	1065.7	1063.9	1062.2
137.5°	1142.5	1142.2	1141.5	1140.9	1140.3	1139.6	1138.5	1136.8	1135.1	1133.5	1131.8
140°	1187.4	1186.9	1186.0	1185.2	1184.2	1183.4	1182.2	1180.8	1179.3	1177.9	1176.5
142.5°	1231.8	1231.5	1230.5	1229.3	1228.2	1227.1	1226.0	1224.8	1223.6	1222.4	1221.2
145°	1295.9	1295.9	1295.0	1294.2	1293.3	1292.4	1291.5	1290.3	1289.2	1288.0	1286.9
147.5°	1354.3	1353.6	1352.9	1352.2	1351.5	1350.8	1350.1	1349.5	1348.8	1348.2	1347.6
150°	1392.1	1392.1	1390.9	1389.7	1388.5	1387.4	1387.0	1387.2	1387.6	1387.8	1388.1
152.5°	1426.0	1425.3	1424.8	1424.4	1423.9	1423.4	1423.0	1422.5	1422.2	1421.8	1421.3
155°	1475.0	1473.9	1473.5	1473.3	1473.0	1472.7	1472.6	1472.6	1472.6	1472.6	1472.6
157.5°	1517.9	1516.7	1516.4	1516.1	1515.8	1515.5	1515.7	1516.3	1517.0	1517.6	1518.2
160°	1543.8	1542.7	1542.4	1542.1	1541.8	1541.5	1541.8	1542.7	1543.5	1544.4	1545.2
162.5°	1568.0	1566.5	1566.5	1566.4	1566.3	1566.3	1566.6	1567.3	1567.9	1568.5	1569.2
165°	1600.9	1599.8	1599.5	1599.2	1599.0	1598.6	1598.8	1599.4	1599.9	1600.5	1601.1
167.5°	1624.6	1622.9	1622.9	1622.9	1622.9	1622.9	1623.5	1624.6	1625.8	1626.9	1628.1
170°	1639.2	1637.4	1637.4	1637.4	1637.4	1637.4	1638.1	1639.2	1640.3	1641.5	1642.6
172.5°	1649.6	1647.9	1647.9	1647.9	1647.9	1647.9	1648.4	1649.6	1650.7	1651.9	1653.0
175°	1661.2	1659.5	1659.5	1659.5	1659.5	1659.5	1660.1	1661.2	1662.4	1663.5	1664.7
177.5°	1666.9	1665.5	1665.7	1665.9	1666.2	1666.4	1667.0	1667.9	1668.9	1669.7	1670.7
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1589.8	1597.4	1602.2	1611.4	1618.9	1623.2	1626.9	1630.1	1633.9	1637.1	1646.2
5°	1600.1	1617.5	1632.3	1655.1	1675.9	1692.0	1709.4	1724.9	1737.7	1755.8	1769.9
7.5°	1595.6	1626.6	1659.1	1694.4	1730.5	1764.1	1795.0	1823.9	1850.0	1881.7	1909.4
10°	1591.3	1633.7	1675.2	1722.9	1771.9	1813.5	1852.4	1892.0	1920.9	1961.2	1995.4
12.5°	1588.1	1637.9	1688.2	1745.4	1799.2	1858.0	1909.9	1938.7	1982.6	2014.8	2055.6
15°	1574.6	1640.4	1709.4	1773.9	1850.4	1904.8	1950.4	2006.8	2047.7	2088.7	2133.0
17.5°	1550.2	1624.8	1702.1	1786.5	1859.9	1918.3	1977.1	2031.5	2080.3	2135.3	2190.4
20°	1539.0	1613.5	1702.1	1788.6	1860.4	1921.6	1981.9	2041.7	2095.4	2165.8	2229.6
22.5°	1515.4	1605.4	1687.0	1771.5	1845.5	1911.9	1980.4	2048.1	2119.5	2199.2	2279.0
25°	1473.3	1564.5	1651.1	1734.3	1808.8	1892.0	1965.1	2055.8	2147.1	2252.5	2351.7
27.5°	1429.4	1516.8	1596.2	1676.5	1763.4	1857.7	1952.6	2055.4	2174.9	2307.9	2448.0
30°	1394.0	1476.5	1553.8	1636.3	1726.9	1833.0	1937.0	2059.2	2197.4	2347.1	2513.5
32.5°	1352.6	1428.7	1503.8	1591.2	1689.9	1801.8	1923.0	2057.0	2223.2	2393.2	2564.6
35°	1281.9	1345.7	1422.9	1516.1	1627.5	1755.8	1896.1	2054.4	2245.1	2440.3	2584.6
37.5°	1198.0	1257.4	1338.7	1441.0	1557.8	1695.4	1861.8	2049.8	2252.2	2407.9	2454.5
40°	1141.7	1196.7	1281.3	1387.3	1506.8	1652.4	1835.0	2033.7	2229.6	2328.9	2290.7
42.5°	1081.5	1139.3	1221.7	1326.6	1455.3	1613.8	1801.1	1999.8	2164.1	2201.7	2069.5
45°	986.6	1046.4	1127.6	1233.6	1371.8	1543.7	1739.0	1919.5	2014.1	1946.4	1741.7
47.5°	898.5	954.4	1029.7	1139.1	1281.8	1459.5	1647.6	1791.7	1799.1	1637.4	1418.8
50°	838.3	889.9	965.8	1075.2	1216.9	1396.7	1566.5	1679.9	1628.9	1445.7	1235.6
52.5°	779.2	829.8	904.6	1013.0	1153.0	1317.8	1475.8	1555.4	1459.2	1271.2	1091.7
55°	694.0	738.3	811.4	911.5	1044.3	1197.4	1331.6	1359.1	1234.2	1049.0	903.4
57.5°	610.8	652.1	718.7	810.8	932.3	1067.8	1172.8	1166.9	1034.9	876.0	760.4
60°	554.4	594.7	653.8	743.6	854.4	971.2	1061.1	1039.7	908.8	771.9	674.5
62.5°	503.9	539.8	595.7	674.4	775.5	883.6	957.5	925.8	797.6	677.9	601.0
65°	429.6	459.8	507.4	574.5	658.4	747.7	804.7	763.8	654.4	561.1	499.4
67.5°	358.5	382.7	422.7	476.2	547.8	619.5	654.3	613.0	525.6	457.4	411.7
70°	313.4	334.9	365.8	413.5	475.9	536.2	562.4	525.6	450.4	391.9	359.0
72.5°	268.4	286.0	313.1	356.0	406.0	458.4	481.4	446.1	384.4	335.0	304.3
75°	207.4	219.5	238.2	267.8	307.4	349.0	361.8	330.9	291.3	254.3	234.3
77.5°	148.4	158.7	172.9	191.6	219.6	246.1	257.2	239.4	208.7	185.4	168.8
80°	114.1	119.5	131.6	147.0	169.1	185.9	193.3	181.9	160.4	142.9	130.2
82.5°	81.4	86.7	93.9	106.7	120.8	132.2	140.2	132.5	116.9	103.2	95.8
85°	39.6	43.0	47.0	52.3	63.1	69.8	69.1	64.4	58.4	53.0	49.0
87.5°	14.7	15.7	17.7	20.9	22.9	25.5	26.9	26.3	24.5	23.2	22.0
90°	3.6	5.9	8.3	10.5	12.7	14.7	16.7	18.8	20.8	22.2	23.7
92.5°	33.1	34.7	36.2	37.9	40.0	42.4	44.9	47.4	49.9	51.7	53.6
95°	85.0	85.6	86.1	86.7	88.4	91.4	94.2	97.1	100.0	102.0	104.0
97.5°	140.4	140.7	140.9	141.2	143.3	147.2	151.3	155.2	159.2	161.1	163.0
100°	181.8	181.8	181.8	181.8	183.7	187.4	191.1	194.9	198.6	201.3	203.9
102.5°	227.6	228.8	229.9	231.1	232.6	234.5	236.4	238.3	240.2	243.1	245.9
105°	297.5	298.9	300.4	301.9	303.4	305.1	306.9	308.6	310.4	312.1	313.8
107.5°	374.4	375.8	377.3	378.7	380.1	381.4	382.7	384.1	385.4	386.2	387.1
110°	427.4	428.8	430.2	431.7	432.8	433.7	434.5	435.4	436.3	437.1	438.1



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	480.7	481.5	482.2	482.9	483.9	484.9	486.0	487.2	488.3	488.6	489.0
115°	560.9	562.0	563.1	564.3	565.2	565.8	566.3	566.9	567.5	567.1	566.9
117.5°	640.2	640.7	641.2	641.7	642.2	642.7	643.3	643.8	644.4	644.5	644.8
120°	691.0	692.4	693.9	695.3	696.1	696.5	696.7	697.0	697.3	697.3	697.3
122.5°	744.1	744.6	745.1	745.6	746.2	747.0	747.8	748.5	749.2	749.0	748.8
125°	818.5	820.3	822.0	823.7	824.8	825.0	825.3	825.6	825.9	825.3	824.8
127.5°	895.7	896.6	897.6	898.6	899.3	899.7	900.0	900.3	900.7	900.3	900.1
130°	942.9	944.3	945.7	947.2	948.2	948.8	949.3	949.9	950.5	950.2	949.9
132.5°	990.6	992.9	995.3	997.6	998.8	998.7	998.5	998.4	998.3	998.0	997.7
135°	1063.9	1065.7	1067.4	1069.1	1070.1	1070.4	1070.7	1071.0	1071.3	1071.3	1071.3
137.5°	1133.5	1135.1	1136.8	1138.5	1139.6	1140.3	1140.9	1141.5	1142.2	1142.5	1142.9
140°	1177.9	1179.3	1180.8	1182.2	1183.4	1184.2	1185.2	1186.0	1186.9	1187.4	1188.0
142.5°	1222.4	1223.6	1224.8	1226.0	1227.1	1228.2	1229.3	1230.5	1231.5	1231.8	1232.2
145°	1288.0	1289.2	1290.3	1291.5	1292.4	1293.3	1294.2	1295.0	1295.9	1295.9	1295.9
147.5°	1348.2	1348.8	1349.5	1350.1	1350.8	1351.5	1352.2	1352.9	1353.6	1354.3	1355.0
150°	1387.8	1387.6	1387.2	1387.0	1387.4	1388.5	1389.7	1390.9	1392.1	1392.1	1392.1
152.5°	1421.8	1422.2	1422.5	1423.0	1423.4	1423.9	1424.4	1424.8	1425.3	1426.0	1426.7
155°	1472.6	1472.6	1472.6	1472.6	1472.7	1473.0	1473.3	1473.5	1473.9	1475.0	1476.1
157.5°	1517.6	1517.0	1516.3	1515.7	1515.5	1515.8	1516.1	1516.4	1516.7	1517.9	1519.0
160°	1544.4	1543.5	1542.7	1541.8	1541.5	1541.8	1542.1	1542.4	1542.7	1543.8	1545.0
162.5°	1568.5	1567.9	1567.3	1566.6	1566.3	1566.3	1566.4	1566.5	1566.5	1568.0	1569.3
165°	1600.5	1599.9	1599.4	1598.8	1598.6	1599.0	1599.2	1599.5	1599.8	1600.9	1602.1
167.5°	1626.9	1625.8	1624.6	1623.5	1622.9	1622.9	1622.9	1622.9	1622.9	1624.6	1626.3
170°	1641.5	1640.3	1639.2	1638.1	1637.4	1637.4	1637.4	1637.4	1637.4	1639.2	1640.9
172.5°	1651.9	1650.7	1649.6	1648.4	1647.9	1647.9	1647.9	1647.9	1647.9	1649.6	1651.3
175°	1663.5	1662.4	1661.2	1660.1	1659.5	1659.5	1659.5	1659.5	1659.5	1661.2	1663.0
177.5°	1669.7	1668.9	1667.9	1667.0	1666.4	1666.2	1665.9	1665.7	1665.5	1666.9	1668.3
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1653.7	1658.0	1667.2	1664.0	1668.3	1670.4	1672.6
5°	1787.3	1808.8	1818.2	1816.9	1830.9	1827.6	1824.2
7.5°	1938.2	1960.8	1973.4	1989.1	1998.2	1998.9	2006.8
10°	2023.6	2053.1	2065.2	2082.0	2092.7	2098.8	2098.1
12.5°	2089.0	2112.2	2139.2	2147.5	2162.0	2169.6	2166.8
15°	2167.9	2204.8	2233.0	2247.0	2265.2	2270.5	2277.9
17.5°	2238.3	2287.8	2320.7	2364.4	2380.9	2391.0	2385.1
20°	2291.4	2356.5	2389.4	2441.7	2470.6	2486.1	2480.6
22.5°	2354.2	2424.7	2485.4	2530.8	2574.7	2595.6	2599.9
25°	2461.9	2558.5	2647.7	2707.5	2761.8	2774.6	2802.8
27.5°	2582.1	2696.0	2791.5	2854.4	2892.2	2906.4	2915.3
30°	2657.8	2771.2	2843.1	2883.3	2895.5	2894.1	2892.7
32.5°	2694.8	2765.9	2779.7	2768.5	2740.8	2717.4	2693.0
35°	2642.4	2589.4	2510.2	2408.1	2333.0	2257.1	2249.8
37.5°	2376.4	2206.9	2075.1	1927.9	1842.9	1790.4	1754.2
40°	2126.2	1933.6	1773.9	1649.8	1563.1	1529.0	1495.4
42.5°	1854.6	1670.5	1529.0	1425.3	1360.2	1322.2	1295.6
45°	1506.8	1344.4	1233.6	1158.5	1106.7	1077.2	1060.4
47.5°	1234.7	1114.6	1020.5	966.2	930.5	907.6	907.7
50°	1088.6	973.9	911.5	868.5	837.6	819.5	822.9
52.5°	959.2	873.5	820.2	784.2	761.4	750.2	749.8
55°	802.0	740.3	705.4	679.2	663.7	651.0	653.8
57.5°	686.0	634.0	610.6	588.9	578.2	573.1	565.7
60°	614.2	573.9	553.7	536.2	525.6	521.5	514.1
62.5°	550.3	518.6	498.9	484.7	475.0	473.7	468.0
65°	462.4	438.2	420.9	414.1	404.1	401.4	401.4
67.5°	381.3	363.9	350.3	344.1	339.8	340.4	337.2
70°	330.2	316.2	307.4	300.7	297.3	298.0	295.3
72.5°	288.9	273.2	265.5	261.5	257.1	258.8	257.7
75°	218.8	210.8	206.7	202.7	200.0	198.6	197.3
77.5°	160.7	153.6	150.5	148.2	148.6	145.3	147.9
80°	124.2	118.1	116.1	112.8	112.1	112.1	111.4
82.5°	90.8	87.5	86.0	83.3	82.1	83.1	81.4
85°	47.0	44.3	43.7	43.7	42.3	41.0	44.3
87.5°	22.2	20.3	20.6	20.2	20.4	20.1	19.1
90°	25.1	26.5	27.7	28.6	29.4	30.3	31.2
92.5°	55.5	57.5	58.7	59.4	60.0	60.6	61.3
95°	106.1	108.1	109.3	109.9	110.6	111.1	111.7
97.5°	164.9	166.8	168.0	168.3	168.7	169.0	169.4
100°	206.5	209.1	210.7	211.2	211.8	212.4	212.9
102.5°	248.7	251.5	253.4	254.2	254.9	255.8	256.6
105°	315.6	317.3	318.6	319.4	320.3	321.2	322.0
107.5°	388.0	388.8	389.3	389.2	389.2	389.1	389.0
110°	438.9	439.8	440.1	439.8	439.5	439.2	438.9



TEST NUMBER: P333485-935

CATALOG NUMBER: S125DIW-S1270D1560U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	489.5	489.8	489.8	489.3	488.8	488.3	487.8
115°	566.6	566.3	566.0	565.8	565.4	565.2	564.9
117.5°	645.1	645.2	644.8	643.6	642.5	641.4	640.2
120°	697.3	697.3	696.7	695.6	694.4	693.3	692.2
122.5°	748.6	748.3	747.8	746.8	745.9	744.9	744.1
125°	824.1	823.5	823.1	822.9	822.5	822.3	822.0
127.5°	899.8	899.5	899.1	898.5	897.9	897.3	896.7
130°	949.7	949.3	948.9	948.4	947.8	947.2	946.7
132.5°	997.5	997.1	996.6	995.8	995.0	994.2	993.3
135°	1071.3	1071.3	1070.7	1069.5	1068.4	1067.2	1066.1
137.5°	1143.2	1143.6	1143.1	1141.6	1140.1	1138.7	1137.2
140°	1188.6	1189.1	1188.7	1187.3	1185.9	1184.4	1182.9
142.5°	1232.5	1233.0	1232.3	1230.9	1229.5	1228.0	1226.6
145°	1295.9	1295.9	1295.5	1294.6	1293.7	1292.9	1292.0
147.5°	1355.6	1356.3	1355.7	1353.8	1351.8	1349.9	1347.9
150°	1392.1	1392.1	1391.7	1391.1	1390.6	1390.0	1389.4
152.5°	1427.4	1428.1	1427.9	1426.8	1425.8	1424.8	1423.7
155°	1477.3	1478.4	1478.3	1476.9	1475.4	1473.9	1472.6
157.5°	1520.2	1521.3	1521.0	1519.0	1517.1	1515.2	1513.3
160°	1546.1	1547.3	1547.1	1545.7	1544.2	1542.8	1541.4
162.5°	1570.7	1572.1	1571.9	1570.3	1568.6	1566.9	1565.2
165°	1603.3	1604.4	1604.1	1602.4	1600.7	1599.0	1597.2
167.5°	1628.1	1629.8	1629.8	1628.0	1626.3	1624.4	1622.6
170°	1642.6	1644.3	1644.3	1642.2	1640.2	1638.1	1636.2
172.5°	1653.0	1654.8	1654.8	1652.9	1651.1	1649.3	1647.6
175°	1664.7	1666.5	1666.3	1664.3	1662.2	1660.3	1658.2
177.5°	1669.7	1671.0	1670.9	1669.3	1667.7	1666.0	1664.5
180°	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6	1668.6

(END OF REPORT)