

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333424-830

Luminaire Tested: **S125DIW-S850D1560U830-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333424-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1560U830-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9135.5 lumens
Efficiency: N/A
Efficacy: 134.1 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

Luminous Intensity Polar Plot



64% Up

36% Dn



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36								
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30								
2	86	79	73	68	78	72	67	63	58	55	52	45	43	41	34	32	31	26								
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	27	22								
4	72	62	54	48	65	56	50	44	46	41	37	36	33	30	27	25	23	19								
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16								
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	20	18	14								
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	18	16	13								
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	11								
9	48	37	29	24	44	33	27	23	28	23	19	22	18	16	17	14	13	10								
10	45	33	26	22	41	31	24	20	25	21	17	20	17	14	16	13	11	9								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7447	7447	7447	7447
5°	8624	7472	6543	7472
10°	10033	7433	5732	7433
15°	11106	7379	5288	7379
20°	12432	7292	4931	7292
25°	14564	7195	4757	7195
30°	15731	7099	4606	7099
35°	12934	6918	4507	6918
40°	9193	6668	4398	6668
45°	7063	6330	4337	6330
50°	6028	5910	4326	5910
55°	5368	5499	4365	5499
60°	4841	5052	4476	5052
65°	4473	4600	4592	4600
70°	4067	4132	4658	4132
75°	3591	3638	4616	3638
80°	3020	2964	4225	2964
85°	2393	2134	3409	2134



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	1.2
10°-20°	330.5	3.6
20°-30°	536.7	5.9
30°-40°	654.6	7.2
40°-50°	595.5	6.5
50°-60°	474.4	5.2
60°-70°	330.4	3.6
70°-80°	176.2	1.9
80°-90°	48.4	0.5
90°-100°	69.6	0.8
100°-110°	428.7	4.7
110°-120°	777.5	8.5
120°-130°	997.8	10.9
130°-140°	1073.2	11.7
140°-150°	1007.4	11.0
150°-160°	814.9	8.9
160°-170°	527.0	5.8
170°-180°	181.8	2.0
0°-30°	978.2	10.7
0°-40°	1632.8	17.9
0°-60°	2702.7	29.6
0°-90°	3257.7	35.7
90°-120°	1275.7	14.0
90°-150°	4354.1	47.7
90°-180°	5878.0	64.3
0°-180°	9135.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1153	1153	1153	1153	1153	
5°	1330	1152	1009	1152	1330	134
15°	1661	1104	791	1104	1661	476
25°	2044	1010	668	1010	2044	934
35°	1640	878	572	878	1640	1004
45°	773	693	475	693	773	619
55°	477	488	388	488	477	429
65°	293	301	300	301	293	290
75°	144	146	185	146	144	155
85°	32	29	46	29	32	38
90°	34	1	34	1	34	16
95°	30	81	30	81	30	25
105°	421	417	421	417	421	381
115°	778	783	778	783	778	772
125°	1114	1114	1114	1114	1114	991
135°	1383	1389	1383	1389	1383	1068
145°	1606	1610	1606	1610	1606	1003
155°	1761	1774	1761	1774	1761	812
165°	1862	1872	1862	1872	1862	525
175°	1906	1914	1906	1914	1906	181
180°	1914	1914	1914	1914	1914	



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1219.7	1218.0	1216.5	1213.3	1215.7	1209.1	1205.9	1200.4	1193.8	1191.5	1188.7
5°	1330.2	1332.7	1335.1	1324.8	1325.9	1319.0	1303.3	1290.6	1280.3	1267.2	1257.8
7.5°	1463.4	1457.5	1457.1	1450.5	1439.0	1429.8	1413.3	1392.4	1372.2	1349.1	1329.9
10°	1529.9	1530.4	1526.0	1518.2	1506.0	1497.1	1475.6	1455.0	1430.1	1400.7	1379.7
12.5°	1580.1	1582.1	1576.5	1565.9	1560.0	1540.2	1523.3	1498.9	1469.2	1445.8	1413.7
15°	1661.1	1655.7	1651.8	1638.6	1628.3	1607.8	1580.8	1555.4	1523.1	1493.2	1463.4
17.5°	1739.2	1743.5	1736.2	1724.1	1692.2	1668.2	1632.1	1597.2	1557.1	1517.0	1481.4
20°	1808.9	1812.8	1801.6	1780.6	1742.4	1718.3	1670.8	1625.9	1579.3	1528.0	1488.8
22.5°	1895.8	1892.7	1877.5	1845.5	1812.4	1768.1	1716.7	1661.9	1603.6	1545.6	1493.6
25°	2043.8	2023.3	2013.9	1974.3	1930.8	1865.7	1795.2	1715.0	1642.5	1565.7	1499.1
27.5°	2125.8	2119.4	2109.0	2081.4	2035.6	1966.0	1882.9	1785.1	1682.9	1585.9	1498.8
30°	2109.4	2110.4	2111.4	2102.5	2073.2	2020.8	1938.2	1832.9	1711.5	1602.3	1501.6
32.5°	1963.8	1981.6	1998.6	2018.7	2026.9	2016.9	1965.1	1870.1	1745.2	1621.2	1500.0
35°	1640.5	1646.0	1701.2	1756.1	1830.4	1888.2	1926.8	1884.8	1779.5	1637.1	1498.1
37.5°	1279.1	1305.6	1343.9	1405.8	1513.2	1609.3	1733.0	1789.8	1755.9	1642.3	1494.7
40°	1090.4	1114.9	1139.8	1203.0	1293.5	1410.0	1550.5	1670.4	1698.3	1625.9	1482.9
42.5°	944.8	964.1	991.8	1039.3	1115.0	1218.1	1352.4	1509.1	1605.5	1578.1	1458.3
45°	773.3	785.5	807.1	844.7	899.6	980.3	1098.7	1270.1	1419.3	1468.8	1399.8
47.5°	661.9	661.8	678.5	704.6	744.1	812.8	900.3	1034.5	1194.0	1311.9	1306.5
50°	600.0	597.6	610.8	633.3	664.6	710.1	793.8	901.0	1054.2	1187.8	1225.0
52.5°	546.8	547.1	555.2	571.8	598.0	637.0	699.5	796.1	927.0	1064.1	1134.2
55°	476.7	474.8	484.0	495.3	514.3	539.8	584.8	658.7	765.0	900.0	991.1
57.5°	412.5	417.8	421.6	429.4	445.3	462.3	500.3	554.5	638.8	754.7	850.9
60°	374.8	380.3	383.2	391.1	403.8	418.5	447.8	491.9	562.8	662.7	758.1
62.5°	341.2	345.4	346.4	353.5	363.8	378.1	401.2	438.2	494.3	581.6	675.1
65°	292.7	292.7	294.6	302.0	306.9	319.6	337.2	364.1	409.2	477.2	556.9
67.5°	245.9	248.3	247.7	251.0	255.5	265.3	278.0	300.2	333.6	383.2	447.0
70°	215.4	217.3	216.8	219.2	224.1	230.5	240.8	261.8	285.8	328.4	383.2
72.5°	187.9	188.7	187.5	190.7	193.6	199.2	210.7	221.9	244.3	280.2	325.3
75°	143.9	144.9	145.8	147.8	150.7	153.6	159.6	170.8	185.5	212.4	241.3
77.5°	107.8	106.0	108.4	108.1	109.7	112.0	117.2	123.1	135.2	152.2	174.6
80°	81.2	81.7	81.7	82.2	84.6	86.1	90.6	94.9	104.2	117.0	132.6
82.5°	59.3	60.6	59.9	60.7	62.8	63.8	66.3	69.8	75.3	85.3	96.6
85°	32.3	29.9	30.8	31.9	31.9	32.3	34.2	35.7	38.6	42.6	46.9
87.5°	16.2	16.8	17.0	16.8	17.1	16.8	18.0	17.7	18.6	19.4	20.5
90°	34.0	33.1	32.1	31.2	30.3	29.0	27.4	25.8	24.3	22.7	20.5
92.5°	31.8	31.4	30.9	30.4	30.0	29.0	27.4	25.8	24.3	22.7	20.7
95°	29.8	29.8	29.8	29.8	29.8	29.0	27.4	25.8	24.3	22.7	34.7
97.5°	29.8	29.8	29.8	29.8	29.8	34.2	43.2	52.0	60.9	69.8	93.5
100°	29.8	31.1	32.3	33.6	34.9	59.0	105.9	152.9	199.9	246.9	245.6
102.5°	178.5	199.9	221.4	242.8	264.3	279.5	288.3	297.2	306.1	315.0	314.2
105°	421.4	421.7	422.1	422.4	422.6	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	531.2	532.2	533.1	534.0	535.0	535.5	535.4	535.4	535.3	535.2	534.6
110°	607.3	607.0	606.6	606.3	606.1	606.3	607.3	608.2	609.2	610.1	609.4



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	675.3	675.8	676.3	676.7	677.1	678.0	679.2	680.3	681.6	682.8	682.4
115°	777.5	779.4	781.3	783.3	785.1	786.6	788.0	789.2	790.4	791.7	791.5
117.5°	886.5	887.3	888.2	889.0	889.8	891.0	892.7	894.3	895.9	897.6	896.4
120°	953.5	955.1	956.6	958.2	959.8	960.9	961.5	962.1	962.8	963.4	962.4
122.5°	1017.0	1018.9	1020.7	1022.6	1024.4	1025.6	1026.2	1026.8	1027.5	1028.1	1027.7
125°	1113.8	1114.7	1115.7	1116.6	1117.6	1118.7	1119.9	1121.2	1122.5	1123.7	1123.7
127.5°	1195.2	1197.6	1200.0	1202.2	1204.6	1206.1	1206.8	1207.5	1208.2	1208.9	1209.1
130°	1254.2	1255.8	1257.4	1259.0	1260.6	1261.9	1262.8	1263.8	1264.7	1265.6	1265.3
132.5°	1308.7	1310.3	1311.9	1313.5	1315.0	1316.0	1316.2	1316.4	1316.5	1316.7	1317.4
135°	1383.4	1385.3	1387.1	1389.0	1390.9	1392.2	1392.9	1393.5	1394.1	1394.8	1395.3
137.5°	1458.3	1459.9	1461.6	1463.2	1464.9	1465.7	1465.5	1465.4	1465.3	1465.1	1465.7
140°	1502.6	1504.5	1506.4	1508.3	1510.1	1510.8	1510.1	1509.5	1508.9	1508.3	1508.5
142.5°	1544.5	1546.4	1548.3	1550.2	1552.2	1553.0	1552.9	1552.7	1552.7	1552.6	1552.1
145°	1606.2	1608.1	1610.0	1611.8	1613.7	1614.5	1614.2	1613.9	1613.5	1613.3	1613.3
147.5°	1657.0	1659.3	1661.5	1663.8	1666.0	1667.0	1666.6	1666.2	1665.8	1665.5	1665.1
150°	1689.9	1692.4	1694.9	1697.4	1700.0	1700.9	1700.3	1699.6	1699.0	1698.4	1697.7
152.5°	1720.5	1722.8	1725.0	1727.3	1729.6	1730.4	1729.8	1729.2	1728.5	1727.9	1727.3
155°	1760.8	1763.3	1765.9	1768.4	1770.8	1771.7	1770.8	1769.8	1768.9	1767.9	1767.3
157.5°	1794.6	1797.1	1799.6	1802.1	1804.7	1805.4	1804.4	1803.4	1802.4	1801.4	1801.3
160°	1816.2	1818.6	1821.2	1823.7	1826.3	1826.8	1825.6	1824.3	1823.1	1821.8	1821.5
162.5°	1835.4	1838.2	1841.0	1843.8	1846.5	1847.0	1845.3	1843.5	1841.7	1839.9	1839.7
165°	1861.5	1864.1	1866.6	1869.2	1871.6	1872.0	1870.1	1868.1	1866.2	1864.3	1864.1
167.5°	1879.7	1882.5	1885.4	1888.2	1891.0	1891.3	1889.0	1886.8	1884.5	1882.3	1882.0
170°	1889.9	1892.7	1895.6	1898.5	1901.3	1901.4	1898.9	1896.4	1893.9	1891.3	1891.0
172.5°	1896.8	1899.6	1902.4	1905.3	1908.1	1908.4	1906.1	1903.8	1901.6	1899.3	1898.8
175°	1905.5	1908.4	1911.2	1914.0	1916.8	1917.0	1914.5	1911.9	1909.5	1907.0	1906.7
177.5°	1910.6	1912.6	1914.7	1916.7	1918.7	1918.8	1917.0	1915.3	1913.5	1911.8	1911.5
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1186.4	1183.6	1180.4	1175.0	1168.4	1164.8	1159.3	1155.8	1148.8	1142.9	1136.6
5°	1246.5	1233.8	1222.1	1206.9	1190.2	1179.5	1166.8	1152.5	1137.9	1122.8	1106.1
7.5°	1308.9	1286.4	1261.9	1235.6	1209.8	1186.2	1163.6	1141.3	1120.6	1095.5	1074.3
10°	1350.8	1322.4	1292.0	1256.3	1221.6	1191.3	1160.5	1133.5	1106.1	1076.8	1050.7
12.5°	1392.7	1354.9	1312.0	1272.8	1231.0	1194.4	1158.1	1123.7	1089.3	1056.8	1026.5
15°	1422.3	1388.9	1349.3	1293.5	1246.5	1196.2	1148.2	1103.6	1062.1	1025.9	987.7
17.5°	1441.7	1398.8	1356.3	1302.8	1241.1	1184.8	1130.5	1079.5	1032.6	986.7	949.9
20°	1445.3	1401.2	1356.7	1304.3	1241.1	1176.6	1122.3	1061.0	1010.7	963.2	918.1
22.5°	1444.1	1394.2	1345.7	1291.8	1230.2	1170.7	1105.0	1042.6	988.0	941.2	894.3
25°	1433.0	1379.7	1319.0	1264.7	1204.0	1140.9	1074.3	1009.7	953.9	900.5	854.0
27.5°	1423.8	1354.6	1285.9	1222.6	1163.9	1106.1	1042.4	976.2	914.4	860.3	816.4
30°	1412.5	1336.6	1259.2	1193.2	1133.0	1076.8	1016.5	952.0	887.3	834.4	787.5
32.5°	1402.3	1313.9	1232.3	1160.4	1096.6	1041.9	986.4	924.9	861.5	807.9	760.8
35°	1382.6	1280.3	1186.8	1105.6	1037.6	981.3	934.8	877.5	819.3	767.4	722.4
37.5°	1357.6	1236.2	1136.0	1050.7	976.2	916.9	873.6	829.6	773.7	723.8	683.1
40°	1338.0	1204.9	1098.7	1011.6	934.3	872.6	832.5	790.9	744.4	698.0	654.9
42.5°	1313.4	1176.8	1061.2	967.4	890.8	830.8	788.6	753.3	712.3	668.9	629.0
45°	1268.1	1125.7	1000.4	899.6	822.2	763.0	719.4	693.1	662.2	621.0	587.3
47.5°	1201.5	1064.3	934.7	830.7	750.8	696.0	655.2	629.8	608.0	577.5	546.9
50°	1142.3	1018.5	887.3	784.0	704.3	648.9	611.3	588.2	569.7	546.2	520.3
52.5°	1076.1	960.9	840.7	738.7	659.7	605.1	568.3	548.0	532.5	515.7	490.1
55°	971.0	873.2	761.6	664.6	591.7	538.4	506.1	488.4	475.7	463.0	447.3
57.5°	855.2	778.6	679.8	591.3	524.1	475.5	445.4	428.2	418.4	411.8	402.6
60°	773.7	708.2	623.0	542.2	476.7	433.7	404.3	391.1	382.8	377.3	370.5
62.5°	698.2	644.4	565.4	491.7	434.4	393.7	367.5	354.7	346.7	344.0	338.4
65°	586.8	545.3	480.1	419.0	370.0	335.3	313.2	301.0	296.1	293.1	293.7
67.5°	477.1	451.8	399.4	347.3	308.2	279.1	261.5	252.0	249.6	245.7	245.6
70°	410.1	391.1	347.0	301.5	266.7	244.2	228.6	218.8	216.3	214.3	213.9
72.5°	351.0	334.3	296.1	259.6	228.4	208.6	195.7	189.8	185.8	184.6	184.5
75°	263.8	254.5	224.1	195.3	173.7	160.0	151.3	145.8	142.9	142.4	142.9
77.5°	187.6	179.5	160.1	139.7	126.1	115.7	108.3	106.4	103.1	103.2	102.6
80°	140.9	135.5	123.4	107.2	96.0	87.1	83.2	79.7	78.8	77.3	78.8
82.5°	102.2	96.4	88.1	77.9	68.5	63.2	59.3	58.2	57.7	56.9	57.3
85°	50.4	50.9	46.0	38.2	34.2	31.3	28.8	28.8	28.4	27.9	28.4
87.5°	20.9	19.7	17.6	16.0	13.6	11.9	10.9	10.8	10.2	10.3	11.2
90°	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4	4.0	6.5	9.0
92.5°	18.8	16.9	14.9	14.8	16.6	18.3	20.1	21.9	20.1	18.3	16.6
95°	46.7	58.6	70.6	77.1	78.0	79.0	79.9	80.9	79.9	79.0	78.0
97.5°	117.3	140.9	164.7	175.7	174.0	172.2	170.5	168.8	170.5	172.2	174.0
100°	244.4	243.1	241.9	240.7	239.8	238.8	237.9	237.0	237.9	238.8	239.8
102.5°	313.5	312.7	312.0	310.9	309.8	308.6	307.4	306.2	307.4	308.6	309.8
105°	422.8	422.8	422.8	422.2	420.9	419.7	418.4	417.2	418.4	419.7	420.9
107.5°	534.0	533.3	532.6	532.3	532.3	532.3	532.3	532.3	532.3	532.3	532.3
110°	608.9	608.2	607.6	607.3	607.3	607.3	607.3	607.3	607.3	607.3	607.3



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	682.0	681.6	681.3	680.7	680.0	679.2	678.4	677.7	678.4	679.2	680.0
115°	791.1	790.8	790.4	789.5	788.0	786.4	784.8	783.3	784.8	786.4	788.0
117.5°	895.1	894.0	892.8	892.2	892.3	892.3	892.4	892.5	892.4	892.3	892.3
120°	961.5	960.5	959.6	959.3	959.6	960.0	960.3	960.5	960.3	960.0	959.6
122.5°	1027.2	1026.8	1026.3	1025.5	1024.4	1023.1	1021.9	1020.8	1021.9	1023.1	1024.4
125°	1123.7	1123.7	1123.7	1122.7	1120.4	1118.2	1116.0	1113.8	1116.0	1118.2	1120.4
127.5°	1209.3	1209.5	1209.7	1208.9	1207.4	1205.8	1204.2	1202.6	1204.2	1205.8	1207.4
130°	1265.0	1264.7	1264.3	1263.4	1261.9	1260.3	1258.7	1257.1	1258.7	1260.3	1261.9
132.5°	1318.1	1318.8	1319.5	1318.9	1317.1	1315.2	1313.4	1311.5	1313.4	1315.2	1317.1
135°	1396.0	1396.7	1397.2	1396.7	1394.8	1392.9	1390.9	1389.0	1390.9	1392.9	1394.8
137.5°	1466.2	1466.8	1467.4	1466.9	1465.2	1463.6	1461.9	1460.3	1461.9	1463.6	1465.2
140°	1508.9	1509.2	1509.5	1509.4	1508.7	1508.1	1507.5	1506.8	1507.5	1508.1	1508.7
142.5°	1551.6	1551.2	1550.8	1550.3	1549.9	1549.5	1549.2	1548.8	1549.2	1549.5	1549.9
145°	1613.3	1613.3	1613.3	1613.0	1612.3	1611.7	1611.0	1610.4	1611.0	1611.7	1612.3
147.5°	1664.7	1664.3	1664.0	1663.8	1664.0	1664.1	1664.2	1664.3	1664.2	1664.1	1664.0
150°	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1697.7	1697.1	1696.5
152.5°	1726.6	1726.0	1725.3	1725.7	1727.1	1728.5	1729.9	1731.3	1729.9	1728.5	1727.1
155°	1766.6	1766.0	1765.4	1766.0	1767.9	1769.8	1771.7	1773.6	1771.7	1769.8	1767.9
157.5°	1801.3	1801.2	1801.1	1801.7	1802.8	1803.9	1805.1	1806.2	1805.1	1803.9	1802.8
160°	1821.2	1820.9	1820.5	1821.4	1823.3	1825.1	1827.0	1828.9	1827.0	1825.1	1823.3
162.5°	1839.4	1839.0	1838.7	1839.5	1841.4	1843.3	1845.2	1847.1	1845.2	1843.3	1841.4
165°	1863.8	1863.4	1863.1	1863.9	1865.8	1867.6	1869.6	1871.5	1869.6	1867.6	1865.8
167.5°	1881.6	1881.3	1881.0	1881.8	1883.8	1885.7	1887.7	1889.6	1887.7	1885.7	1883.8
170°	1890.7	1890.4	1890.1	1891.0	1893.2	1895.5	1897.6	1899.9	1897.6	1895.5	1893.2
172.5°	1898.2	1897.6	1897.1	1897.8	1900.1	1902.2	1904.5	1906.7	1904.5	1902.2	1900.1
175°	1906.3	1906.0	1905.7	1906.5	1908.4	1910.3	1912.1	1914.0	1912.1	1910.3	1908.4
177.5°	1911.3	1911.0	1910.7	1911.4	1912.9	1914.4	1915.9	1917.4	1915.9	1914.4	1912.9
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1133.1	1128.8	1125.3	1117.5	1113.1	1107.3	1102.6	1107.7	1102.2	1104.6	1101.0
5°	1097.8	1084.1	1074.3	1060.1	1047.8	1036.6	1028.3	1026.8	1022.8	1021.0	1015.0
7.5°	1055.3	1038.1	1021.3	1002.8	987.0	971.1	960.9	952.5	947.0	939.6	934.6
10°	1030.2	1007.2	987.7	965.2	945.6	928.4	914.7	907.9	901.5	892.2	888.8
12.5°	999.3	975.5	951.6	927.6	908.8	889.7	877.9	867.5	863.2	852.6	851.6
15°	962.2	926.5	903.0	878.5	852.5	836.9	827.1	815.9	811.0	803.6	798.2
17.5°	917.9	886.1	856.7	831.3	809.1	795.9	783.7	776.0	767.6	762.8	754.0
20°	885.9	855.5	826.1	799.2	782.1	766.9	757.1	749.8	741.0	738.6	729.7
22.5°	858.8	825.4	797.2	774.6	755.8	738.8	728.1	723.2	717.1	709.5	707.8
25°	814.9	780.1	756.2	733.7	717.0	701.3	694.0	687.7	681.7	676.4	674.4
27.5°	776.9	745.8	717.4	697.0	682.6	668.3	661.8	654.0	649.8	645.5	640.2
30°	750.3	718.5	693.5	673.9	658.3	645.5	638.7	633.3	629.4	625.5	622.5
32.5°	722.8	693.4	669.2	650.1	634.4	624.8	618.7	614.9	610.6	605.9	602.2
35°	686.6	654.3	630.8	614.3	602.0	594.7	587.8	584.4	579.5	579.5	575.5
37.5°	645.8	617.9	597.2	582.0	571.1	564.5	557.0	554.7	551.6	549.5	548.2
40°	621.6	595.6	576.1	560.9	549.1	543.8	537.9	534.0	532.0	529.5	528.6
42.5°	596.5	571.7	553.0	538.9	528.8	524.1	518.7	515.9	512.0	508.8	508.2
45°	558.5	534.4	517.4	506.1	497.3	491.9	488.4	482.6	480.6	476.7	476.2
47.5°	522.3	499.3	482.5	473.3	465.5	461.1	455.7	449.9	447.6	445.6	445.4
50°	495.3	474.3	458.5	449.8	442.4	436.1	430.6	426.8	425.3	425.3	426.3
52.5°	467.9	450.0	436.7	425.9	419.0	412.2	407.2	404.8	402.6	404.9	406.7
55°	427.7	409.6	399.8	389.6	382.8	374.8	372.5	371.5	370.0	373.9	375.9
57.5°	385.3	372.6	361.1	350.9	344.8	340.3	337.0	336.3	339.0	340.9	347.3
60°	358.3	343.6	333.3	325.5	318.1	315.2	314.2	313.2	315.2	320.6	328.9
62.5°	328.5	316.6	305.5	299.6	294.3	289.4	289.2	289.7	293.7	299.8	308.1
65°	284.8	274.6	267.2	260.3	256.0	253.1	254.0	256.0	260.3	268.7	278.0
67.5°	240.5	233.5	226.9	221.3	217.1	217.1	218.1	221.0	226.2	235.8	244.3
70°	211.9	204.1	198.7	196.2	192.8	190.9	193.8	198.7	203.1	211.9	219.2
72.5°	183.3	176.7	172.5	170.8	169.4	167.8	168.7	174.0	180.0	188.8	197.4
75°	140.9	138.5	135.5	133.7	132.1	133.1	134.1	139.0	143.9	153.2	163.0
77.5°	102.8	100.3	98.6	98.1	97.3	97.7	100.6	104.2	109.0	115.7	123.1
80°	77.9	76.8	75.9	75.4	75.4	75.9	79.7	82.2	86.6	93.0	98.9
82.5°	56.6	56.1	55.9	55.8	56.2	56.3	58.6	61.8	65.5	70.3	75.4
85°	29.9	28.8	30.3	30.8	29.9	31.3	32.3	34.2	35.7	38.2	40.6
87.5°	12.1	13.4	13.4	14.2	14.7	15.9	15.8	17.7	18.8	19.9	19.8
90°	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.8	27.4	29.0	30.3
92.5°	14.8	14.9	16.9	18.8	20.7	22.7	24.3	25.8	27.4	29.0	30.0
95°	77.1	70.6	58.6	46.7	34.7	22.7	24.3	25.8	27.4	29.0	29.8
97.5°	175.7	164.7	140.9	117.3	93.5	69.8	60.9	52.0	43.2	34.2	29.8
100°	240.7	241.9	243.1	244.4	245.6	246.9	199.9	152.9	105.9	59.0	34.9
102.5°	310.9	312.0	312.7	313.5	314.2	315.0	306.1	297.2	288.3	279.5	264.3
105°	422.2	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.8	422.6
107.5°	532.3	532.6	533.3	534.0	534.6	535.2	535.3	535.4	535.4	535.5	535.0
110°	607.3	607.6	608.2	608.9	609.4	610.1	609.2	608.2	607.3	606.3	606.1



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	680.7	681.3	681.6	682.0	682.4	682.8	681.6	680.3	679.2	678.0	677.1
115°	789.5	790.4	790.8	791.1	791.5	791.7	790.4	789.2	788.0	786.6	785.1
117.5°	892.2	892.8	894.0	895.1	896.4	897.6	895.9	894.3	892.7	891.0	889.8
120°	959.3	959.6	960.5	961.5	962.4	963.4	962.8	962.1	961.5	960.9	959.8
122.5°	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5	1026.8	1026.2	1025.6	1024.4
125°	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5	1121.2	1119.9	1118.7	1117.6
127.5°	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2	1207.5	1206.8	1206.1	1204.6
130°	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7	1263.8	1262.8	1261.9	1260.6
132.5°	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5	1316.4	1316.2	1316.0	1315.0
135°	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1	1393.5	1392.9	1392.2	1390.9
137.5°	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3	1465.4	1465.5	1465.7	1464.9
140°	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9	1509.5	1510.1	1510.8	1510.1
142.5°	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7	1552.7	1552.9	1553.0	1552.2
145°	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5	1613.9	1614.2	1614.5	1613.7
147.5°	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8	1666.2	1666.6	1667.0	1666.0
150°	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0	1699.6	1700.3	1700.9	1700.0
152.5°	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5	1729.2	1729.8	1730.4	1729.6
155°	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9	1769.8	1770.8	1771.7	1770.8
157.5°	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4	1803.4	1804.4	1805.4	1804.7
160°	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1	1824.3	1825.6	1826.8	1826.3
162.5°	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7	1843.5	1845.3	1847.0	1846.5
165°	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2	1868.1	1870.1	1872.0	1871.6
167.5°	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5	1886.8	1889.0	1891.3	1891.0
170°	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9	1896.4	1898.9	1901.4	1901.3
172.5°	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6	1903.8	1906.1	1908.4	1908.1
175°	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5	1911.9	1914.5	1917.0	1916.8
177.5°	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5	1915.3	1917.0	1918.8	1918.7
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1098.6	1101.4	1099.0	1102.2	1099.0	1101.4	1098.6	1101.0	1104.6	1102.2	1107.7
5°	1012.6	1008.2	1011.2	1009.2	1011.2	1008.2	1012.6	1015.0	1021.0	1022.8	1026.8
7.5°	933.1	928.9	924.2	921.9	924.2	928.9	933.1	934.6	939.6	947.0	952.5
10°	883.4	878.0	877.5	874.1	877.5	878.0	883.4	888.8	892.2	901.5	907.9
12.5°	847.0	842.0	836.4	835.0	836.4	842.0	847.0	851.6	852.6	863.2	867.5
15°	795.3	791.4	788.0	790.9	788.0	791.4	795.3	798.2	803.6	811.0	815.9
17.5°	752.3	749.1	748.5	744.9	748.5	749.1	752.3	754.0	762.8	767.6	776.0
20°	725.3	722.8	723.9	717.5	723.9	722.8	725.3	729.7	738.6	741.0	749.8
22.5°	703.8	699.0	698.4	697.1	698.4	699.0	703.8	707.8	709.5	717.1	723.2
25°	670.1	667.6	665.2	667.6	665.2	667.6	670.1	674.4	676.4	681.7	687.7
27.5°	640.6	637.6	637.0	637.3	637.0	637.6	640.6	640.2	645.5	649.8	654.0
30°	622.5	617.6	618.1	617.6	618.1	617.6	622.5	622.5	625.5	629.4	633.3
32.5°	602.9	599.6	599.0	598.0	599.0	599.6	602.9	602.2	605.9	610.6	614.9
35°	574.1	574.1	571.7	571.7	571.7	574.1	574.1	575.5	579.5	579.5	584.4
37.5°	547.0	546.5	545.0	545.3	545.0	546.5	547.0	548.2	549.5	551.6	554.7
40°	526.6	526.1	524.6	521.7	524.6	526.1	526.6	528.6	529.5	532.0	534.0
42.5°	507.0	505.4	504.7	503.7	504.7	505.4	507.0	508.2	508.8	512.0	515.9
45°	476.2	476.2	475.2	474.8	475.2	476.2	476.2	476.2	476.7	480.6	482.6
47.5°	446.3	447.1	449.0	448.7	449.0	447.1	446.3	445.4	445.6	447.6	449.9
50°	428.2	428.8	430.2	430.6	430.2	428.8	428.2	426.3	425.3	425.3	426.8
52.5°	408.3	411.1	412.9	412.6	412.9	411.1	408.3	406.7	404.9	402.6	404.8
55°	380.3	383.7	387.1	387.7	387.1	383.7	380.3	375.9	373.9	370.0	371.5
57.5°	352.6	357.4	361.0	362.1	361.0	357.4	352.6	347.3	340.9	339.0	336.3
60°	333.8	340.2	344.6	346.5	344.6	340.2	333.8	328.9	320.6	315.2	313.2
62.5°	315.8	322.9	327.3	327.7	327.3	322.9	315.8	308.1	299.8	293.7	289.7
65°	286.3	293.7	297.6	300.5	297.6	293.7	286.3	278.0	268.7	260.3	256.0
67.5°	254.6	261.9	266.3	268.6	266.3	261.9	254.6	244.3	235.8	226.2	221.0
70°	231.5	238.8	244.7	246.7	244.7	238.8	231.5	219.2	211.9	203.1	198.7
72.5°	208.8	215.4	220.1	222.3	220.1	215.4	208.8	197.4	188.8	180.0	174.0
75°	169.4	178.1	182.6	185.0	182.6	178.1	169.4	163.0	153.2	143.9	139.0
77.5°	130.5	138.6	141.3	142.5	141.3	138.6	130.5	123.1	115.7	109.0	104.2
80°	104.7	109.6	113.0	113.6	113.0	109.6	104.7	98.9	93.0	86.6	82.2
82.5°	80.5	84.5	85.7	86.9	85.7	84.5	80.5	75.4	70.3	65.5	61.8
85°	44.0	46.0	46.5	46.0	46.5	46.0	44.0	40.6	38.2	35.7	34.2
87.5°	20.7	20.5	20.7	21.7	20.7	20.5	20.7	19.8	19.9	18.8	17.7
90°	31.2	32.1	33.1	34.0	33.1	32.1	31.2	30.3	29.0	27.4	25.8
92.5°	30.4	30.9	31.4	31.8	31.4	30.9	30.4	30.0	29.0	27.4	25.8
95°	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.0	27.4	25.8
97.5°	29.8	29.8	29.8	29.8	29.8	29.8	29.8	29.8	34.2	43.2	52.0
100°	33.6	32.3	31.1	29.8	31.1	32.3	33.6	34.9	59.0	105.9	152.9
102.5°	242.8	221.4	199.9	178.5	199.9	221.4	242.8	264.3	279.5	288.3	297.2
105°	422.4	422.1	421.7	421.4	421.7	422.1	422.4	422.6	422.8	422.8	422.8
107.5°	534.0	533.1	532.2	531.2	532.2	533.1	534.0	535.0	535.5	535.4	535.4
110°	606.3	606.6	607.0	607.3	607.0	606.6	606.3	606.1	606.3	607.3	608.2



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	676.7	676.3	675.8	675.3	675.8	676.3	676.7	677.1	678.0	679.2	680.3
115°	783.3	781.3	779.4	777.5	779.4	781.3	783.3	785.1	786.6	788.0	789.2
117.5°	889.0	888.2	887.3	886.5	887.3	888.2	889.0	889.8	891.0	892.7	894.3
120°	958.2	956.6	955.1	953.5	955.1	956.6	958.2	959.8	960.9	961.5	962.1
122.5°	1022.6	1020.7	1018.9	1017.0	1018.9	1020.7	1022.6	1024.4	1025.6	1026.2	1026.8
125°	1116.6	1115.7	1114.7	1113.8	1114.7	1115.7	1116.6	1117.6	1118.7	1119.9	1121.2
127.5°	1202.2	1200.0	1197.6	1195.2	1197.6	1200.0	1202.2	1204.6	1206.1	1206.8	1207.5
130°	1259.0	1257.4	1255.8	1254.2	1255.8	1257.4	1259.0	1260.6	1261.9	1262.8	1263.8
132.5°	1313.5	1311.9	1310.3	1308.7	1310.3	1311.9	1313.5	1315.0	1316.0	1316.2	1316.4
135°	1389.0	1387.1	1385.3	1383.4	1385.3	1387.1	1389.0	1390.9	1392.2	1392.9	1393.5
137.5°	1463.2	1461.6	1459.9	1458.3	1459.9	1461.6	1463.2	1464.9	1465.7	1465.5	1465.4
140°	1508.3	1506.4	1504.5	1502.6	1504.5	1506.4	1508.3	1510.1	1510.8	1510.1	1509.5
142.5°	1550.2	1548.3	1546.4	1544.5	1546.4	1548.3	1550.2	1552.2	1553.0	1552.9	1552.7
145°	1611.8	1610.0	1608.1	1606.2	1608.1	1610.0	1611.8	1613.7	1614.5	1614.2	1613.9
147.5°	1663.8	1661.5	1659.3	1657.0	1659.3	1661.5	1663.8	1666.0	1667.0	1666.6	1666.2
150°	1697.4	1694.9	1692.4	1689.9	1692.4	1694.9	1697.4	1700.0	1700.9	1700.3	1699.6
152.5°	1727.3	1725.0	1722.8	1720.5	1722.8	1725.0	1727.3	1729.6	1730.4	1729.8	1729.2
155°	1768.4	1765.9	1763.3	1760.8	1763.3	1765.9	1768.4	1770.8	1771.7	1770.8	1769.8
157.5°	1802.1	1799.6	1797.1	1794.6	1797.1	1799.6	1802.1	1804.7	1805.4	1804.4	1803.4
160°	1823.7	1821.2	1818.6	1816.2	1818.6	1821.2	1823.7	1826.3	1826.8	1825.6	1824.3
162.5°	1843.8	1841.0	1838.2	1835.4	1838.2	1841.0	1843.8	1846.5	1847.0	1845.3	1843.5
165°	1869.2	1866.6	1864.1	1861.5	1864.1	1866.6	1869.2	1871.6	1872.0	1870.1	1868.1
167.5°	1888.2	1885.4	1882.5	1879.7	1882.5	1885.4	1888.2	1891.0	1891.3	1889.0	1886.8
170°	1898.5	1895.6	1892.7	1889.9	1892.7	1895.6	1898.5	1901.3	1901.4	1898.9	1896.4
172.5°	1905.3	1902.4	1899.6	1896.8	1899.6	1902.4	1905.3	1908.1	1908.4	1906.1	1903.8
175°	1914.0	1911.2	1908.4	1905.5	1908.4	1911.2	1914.0	1916.8	1917.0	1914.5	1911.9
177.5°	1916.7	1914.7	1912.6	1910.6	1912.6	1914.7	1916.7	1918.7	1918.8	1917.0	1915.3
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1102.6	1107.3	1113.1	1117.5	1125.3	1128.8	1133.1	1136.6	1142.9	1148.8	1155.8
5°	1028.3	1036.6	1047.8	1060.1	1074.3	1084.1	1097.8	1106.1	1122.8	1137.9	1152.5
7.5°	960.9	971.1	987.0	1002.8	1021.3	1038.1	1055.3	1074.3	1095.5	1120.6	1141.3
10°	914.7	928.4	945.6	965.2	987.7	1007.2	1030.2	1050.7	1076.8	1106.1	1133.5
12.5°	877.9	889.7	908.8	927.6	951.6	975.5	999.3	1026.5	1056.8	1089.3	1123.7
15°	827.1	836.9	852.5	878.5	903.0	926.5	962.2	987.7	1025.9	1062.1	1103.6
17.5°	783.7	795.9	809.1	831.3	856.7	886.1	917.9	949.9	986.7	1032.6	1079.5
20°	757.1	766.9	782.1	799.2	826.1	855.5	885.9	918.1	963.2	1010.7	1061.0
22.5°	728.1	738.8	755.8	774.6	797.2	825.4	858.8	894.3	941.2	988.0	1042.6
25°	694.0	701.3	717.0	733.7	756.2	780.1	814.9	854.0	900.5	953.9	1009.7
27.5°	661.8	668.3	682.6	697.0	717.4	745.8	776.9	816.4	860.3	914.4	976.2
30°	638.7	645.5	658.3	673.9	693.5	718.5	750.3	787.5	834.4	887.3	952.0
32.5°	618.7	624.8	634.4	650.1	669.2	693.4	722.8	760.8	807.9	861.5	924.9
35°	587.8	594.7	602.0	614.3	630.8	654.3	686.6	722.4	767.4	819.3	877.5
37.5°	557.0	564.5	571.1	582.0	597.2	617.9	645.8	683.1	723.8	773.7	829.6
40°	537.9	543.8	549.1	560.9	576.1	595.6	621.6	654.9	698.0	744.4	790.9
42.5°	518.7	524.1	528.8	538.9	553.0	571.7	596.5	629.0	668.9	712.3	753.3
45°	488.4	491.9	497.3	506.1	517.4	534.4	558.5	587.3	621.0	662.2	693.1
47.5°	455.7	461.1	465.5	473.3	482.5	499.3	522.3	546.9	577.5	608.0	629.8
50°	430.6	436.1	442.4	449.8	458.5	474.3	495.3	520.3	546.2	569.7	588.2
52.5°	407.2	412.2	419.0	425.9	436.7	450.0	467.9	490.1	515.7	532.5	548.0
55°	372.5	374.8	382.8	389.6	399.8	409.6	427.7	447.3	463.0	475.7	488.4
57.5°	337.0	340.3	344.8	350.9	361.1	372.6	385.3	402.6	411.8	418.4	428.2
60°	314.2	315.2	318.1	325.5	333.3	343.6	358.3	370.5	377.3	382.8	391.1
62.5°	289.2	289.4	294.3	299.6	305.5	316.6	328.5	338.4	344.0	346.7	354.7
65°	254.0	253.1	256.0	260.3	267.2	274.6	284.8	293.7	293.1	296.1	301.0
67.5°	218.1	217.1	217.1	221.3	226.9	233.5	240.5	245.6	245.7	249.6	252.0
70°	193.8	190.9	192.8	196.2	198.7	204.1	211.9	213.9	214.3	216.3	218.8
72.5°	168.7	167.8	169.4	170.8	172.5	176.7	183.3	184.5	184.6	185.8	189.8
75°	134.1	133.1	132.1	133.7	135.5	138.5	140.9	142.9	142.4	142.9	145.8
77.5°	100.6	97.7	97.3	98.1	98.6	100.3	102.8	102.6	103.2	103.1	106.4
80°	79.7	75.9	75.4	75.4	75.9	76.8	77.9	78.8	77.3	78.8	79.7
82.5°	58.6	56.3	56.2	55.8	55.9	56.1	56.6	57.3	56.9	57.7	58.2
85°	32.3	31.3	29.9	30.8	30.3	28.8	29.9	28.4	27.9	28.4	28.8
87.5°	15.8	15.9	14.7	14.2	13.4	13.4	12.1	11.2	10.3	10.2	10.8
90°	24.3	22.7	20.5	18.3	16.1	13.9	11.5	9.0	6.5	4.0	1.4
92.5°	24.3	22.7	20.7	18.8	16.9	14.9	14.8	16.6	18.3	20.1	21.9
95°	24.3	22.7	34.7	46.7	58.6	70.6	77.1	78.0	79.0	79.9	80.9
97.5°	60.9	69.8	93.5	117.3	140.9	164.7	175.7	174.0	172.2	170.5	168.8
100°	199.9	246.9	245.6	244.4	243.1	241.9	240.7	239.8	238.8	237.9	237.0
102.5°	306.1	315.0	314.2	313.5	312.7	312.0	310.9	309.8	308.6	307.4	306.2
105°	422.8	422.8	422.8	422.8	422.8	422.8	422.2	420.9	419.7	418.4	417.2
107.5°	535.3	535.2	534.6	534.0	533.3	532.6	532.3	532.3	532.3	532.3	532.3
110°	609.2	610.1	609.4	608.9	608.2	607.6	607.3	607.3	607.3	607.3	607.3



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	681.6	682.8	682.4	682.0	681.6	681.3	680.7	680.0	679.2	678.4	677.7
115°	790.4	791.7	791.5	791.1	790.8	790.4	789.5	788.0	786.4	784.8	783.3
117.5°	895.9	897.6	896.4	895.1	894.0	892.8	892.2	892.3	892.3	892.4	892.5
120°	962.8	963.4	962.4	961.5	960.5	959.6	959.3	959.6	960.0	960.3	960.5
122.5°	1027.5	1028.1	1027.7	1027.2	1026.8	1026.3	1025.5	1024.4	1023.1	1021.9	1020.8
125°	1122.5	1123.7	1123.7	1123.7	1123.7	1123.7	1122.7	1120.4	1118.2	1116.0	1113.8
127.5°	1208.2	1208.9	1209.1	1209.3	1209.5	1209.7	1208.9	1207.4	1205.8	1204.2	1202.6
130°	1264.7	1265.6	1265.3	1265.0	1264.7	1264.3	1263.4	1261.9	1260.3	1258.7	1257.1
132.5°	1316.5	1316.7	1317.4	1318.1	1318.8	1319.5	1318.9	1317.1	1315.2	1313.4	1311.5
135°	1394.1	1394.8	1395.3	1396.0	1396.7	1397.2	1396.7	1394.8	1392.9	1390.9	1389.0
137.5°	1465.3	1465.1	1465.7	1466.2	1466.8	1467.4	1466.9	1465.2	1463.6	1461.9	1460.3
140°	1508.9	1508.3	1508.5	1508.9	1509.2	1509.5	1509.4	1508.7	1508.1	1507.5	1506.8
142.5°	1552.7	1552.6	1552.1	1551.6	1551.2	1550.8	1550.3	1549.9	1549.5	1549.2	1548.8
145°	1613.5	1613.3	1613.3	1613.3	1613.3	1613.3	1613.0	1612.3	1611.7	1611.0	1610.4
147.5°	1665.8	1665.5	1665.1	1664.7	1664.3	1664.0	1663.8	1664.0	1664.1	1664.2	1664.3
150°	1699.0	1698.4	1697.7	1697.1	1696.5	1695.8	1695.8	1695.8	1696.5	1697.1	1697.7
152.5°	1728.5	1727.9	1727.3	1726.6	1726.0	1725.3	1725.7	1727.1	1728.5	1729.9	1731.3
155°	1768.9	1767.9	1767.3	1766.6	1766.0	1765.4	1766.0	1767.9	1769.8	1771.7	1773.6
157.5°	1802.4	1801.4	1801.3	1801.3	1801.2	1801.1	1801.7	1802.8	1803.9	1805.1	1806.2
160°	1823.1	1821.8	1821.5	1821.2	1820.9	1820.5	1821.4	1823.3	1825.1	1827.0	1828.9
162.5°	1841.7	1839.9	1839.7	1839.4	1839.0	1838.7	1839.5	1841.4	1843.3	1845.2	1847.1
165°	1866.2	1864.3	1864.1	1863.8	1863.4	1863.1	1863.9	1865.8	1867.6	1869.6	1871.5
167.5°	1884.5	1882.3	1882.0	1881.6	1881.3	1881.0	1881.8	1883.8	1885.7	1887.7	1889.6
170°	1893.9	1891.3	1891.0	1890.7	1890.4	1890.1	1891.0	1893.2	1895.5	1897.6	1899.9
172.5°	1901.6	1899.3	1898.8	1898.2	1897.6	1897.1	1897.8	1900.1	1902.2	1904.5	1906.7
175°	1909.5	1907.0	1906.7	1906.3	1906.0	1905.7	1906.5	1908.4	1910.3	1912.1	1914.0
177.5°	1913.5	1911.8	1911.5	1911.3	1911.0	1910.7	1911.4	1912.9	1914.4	1915.9	1917.4
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1159.3	1164.8	1168.4	1175.0	1180.4	1183.6	1186.4	1188.7	1191.5	1193.8	1200.4
5°	1166.8	1179.5	1190.2	1206.9	1222.1	1233.8	1246.5	1257.8	1267.2	1280.3	1290.6
7.5°	1163.6	1186.2	1209.8	1235.6	1261.9	1286.4	1308.9	1329.9	1349.1	1372.2	1392.4
10°	1160.5	1191.3	1221.6	1256.3	1292.0	1322.4	1350.8	1379.7	1400.7	1430.1	1455.0
12.5°	1158.1	1194.4	1231.0	1272.8	1312.0	1354.9	1392.7	1413.7	1445.8	1469.2	1498.9
15°	1148.2	1196.2	1246.5	1293.5	1349.3	1388.9	1422.3	1463.4	1493.2	1523.1	1555.4
17.5°	1130.5	1184.8	1241.1	1302.8	1356.3	1398.8	1441.7	1481.4	1517.0	1557.1	1597.2
20°	1122.3	1176.6	1241.1	1304.3	1356.7	1401.2	1445.3	1488.8	1528.0	1579.3	1625.9
22.5°	1105.0	1170.7	1230.2	1291.8	1345.7	1394.2	1444.1	1493.6	1545.6	1603.6	1661.9
25°	1074.3	1140.9	1204.0	1264.7	1319.0	1379.7	1433.0	1499.1	1565.7	1642.5	1715.0
27.5°	1042.4	1106.1	1163.9	1222.6	1285.9	1354.6	1423.8	1498.8	1585.9	1682.9	1785.1
30°	1016.5	1076.8	1133.0	1193.2	1259.2	1336.6	1412.5	1501.6	1602.3	1711.5	1832.9
32.5°	986.4	1041.9	1096.6	1160.4	1232.3	1313.9	1402.3	1500.0	1621.2	1745.2	1870.1
35°	934.8	981.3	1037.6	1105.6	1186.8	1280.3	1382.6	1498.1	1637.1	1779.5	1884.8
37.5°	873.6	916.9	976.2	1050.7	1136.0	1236.2	1357.6	1494.7	1642.3	1755.9	1789.8
40°	832.5	872.6	934.3	1011.6	1098.7	1204.9	1338.0	1482.9	1625.9	1698.3	1670.4
42.5°	788.6	830.8	890.8	967.4	1061.2	1176.8	1313.4	1458.3	1578.1	1605.5	1509.1
45°	719.4	763.0	822.2	899.6	1000.4	1125.7	1268.1	1399.8	1468.8	1419.3	1270.1
47.5°	655.2	696.0	750.8	830.7	934.7	1064.3	1201.5	1306.5	1311.9	1194.0	1034.5
50°	611.3	648.9	704.3	784.0	887.3	1018.5	1142.3	1225.0	1187.8	1054.2	901.0
52.5°	568.3	605.1	659.7	738.7	840.7	960.9	1076.1	1134.2	1064.1	927.0	796.1
55°	506.1	538.4	591.7	664.6	761.6	873.2	971.0	991.1	900.0	765.0	658.7
57.5°	445.4	475.5	524.1	591.3	679.8	778.6	855.2	850.9	754.7	638.8	554.5
60°	404.3	433.7	476.7	542.2	623.0	708.2	773.7	758.1	662.7	562.8	491.9
62.5°	367.5	393.7	434.4	491.7	565.4	644.4	698.2	675.1	581.6	494.3	438.2
65°	313.2	335.3	370.0	419.0	480.1	545.3	586.8	556.9	477.2	409.2	364.1
67.5°	261.5	279.1	308.2	347.3	399.4	451.8	477.1	447.0	383.2	333.6	300.2
70°	228.6	244.2	266.7	301.5	347.0	391.1	410.1	383.2	328.4	285.8	261.8
72.5°	195.7	208.6	228.4	259.6	296.1	334.3	351.0	325.3	280.2	244.3	221.9
75°	151.3	160.0	173.7	195.3	224.1	254.5	263.8	241.3	212.4	185.5	170.8
77.5°	108.3	115.7	126.1	139.7	160.1	179.5	187.6	174.6	152.2	135.2	123.1
80°	83.2	87.1	96.0	107.2	123.4	135.5	140.9	132.6	117.0	104.2	94.9
82.5°	59.3	63.2	68.5	77.9	88.1	96.4	102.2	96.6	85.3	75.3	69.8
85°	28.8	31.3	34.2	38.2	46.0	50.9	50.4	46.9	42.6	38.6	35.7
87.5°	10.9	11.9	13.6	16.0	17.6	19.7	20.9	20.5	19.4	18.6	17.7
90°	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3	25.8
92.5°	20.1	18.3	16.6	14.8	14.9	16.9	18.8	20.7	22.7	24.3	25.8
95°	79.9	79.0	78.0	77.1	70.6	58.6	46.7	34.7	22.7	24.3	25.8
97.5°	170.5	172.2	174.0	175.7	164.7	140.9	117.3	93.5	69.8	60.9	52.0
100°	237.9	238.8	239.8	240.7	241.9	243.1	244.4	245.6	246.9	199.9	152.9
102.5°	307.4	308.6	309.8	310.9	312.0	312.7	313.5	314.2	315.0	306.1	297.2
105°	418.4	419.7	420.9	422.2	422.8	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	532.3	532.3	532.3	532.3	532.6	533.3	534.0	534.6	535.2	535.3	535.4
110°	607.3	607.3	607.3	607.3	607.6	608.2	608.9	609.4	610.1	609.2	608.2



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	678.4	679.2	680.0	680.7	681.3	681.6	682.0	682.4	682.8	681.6	680.3
115°	784.8	786.4	788.0	789.5	790.4	790.8	791.1	791.5	791.7	790.4	789.2
117.5°	892.4	892.3	892.3	892.2	892.8	894.0	895.1	896.4	897.6	895.9	894.3
120°	960.3	960.0	959.6	959.3	959.6	960.5	961.5	962.4	963.4	962.8	962.1
122.5°	1021.9	1023.1	1024.4	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5	1026.8
125°	1116.0	1118.2	1120.4	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5	1121.2
127.5°	1204.2	1205.8	1207.4	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2	1207.5
130°	1258.7	1260.3	1261.9	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7	1263.8
132.5°	1313.4	1315.2	1317.1	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5	1316.4
135°	1390.9	1392.9	1394.8	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1	1393.5
137.5°	1461.9	1463.6	1465.2	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3	1465.4
140°	1507.5	1508.1	1508.7	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9	1509.5
142.5°	1549.2	1549.5	1549.9	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7	1552.7
145°	1611.0	1611.7	1612.3	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5	1613.9
147.5°	1664.2	1664.1	1664.0	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8	1666.2
150°	1697.7	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0	1699.6
152.5°	1729.9	1728.5	1727.1	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5	1729.2
155°	1771.7	1769.8	1767.9	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9	1769.8
157.5°	1805.1	1803.9	1802.8	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4	1803.4
160°	1827.0	1825.1	1823.3	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1	1824.3
162.5°	1845.2	1843.3	1841.4	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7	1843.5
165°	1869.6	1867.6	1865.8	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2	1868.1
167.5°	1887.7	1885.7	1883.8	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5	1886.8
170°	1897.6	1895.5	1893.2	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9	1896.4
172.5°	1904.5	1902.2	1900.1	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6	1903.8
175°	1912.1	1910.3	1908.4	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5	1911.9
177.5°	1915.9	1914.4	1912.9	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5	1915.3
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1	1153.1
2.5°	1205.9	1209.1	1215.7	1213.3	1216.5	1218.0	1219.7
5°	1303.3	1319.0	1325.9	1324.8	1335.1	1332.7	1330.2
7.5°	1413.3	1429.8	1439.0	1450.5	1457.1	1457.5	1463.4
10°	1475.6	1497.1	1506.0	1518.2	1526.0	1530.4	1529.9
12.5°	1523.3	1540.2	1560.0	1565.9	1576.5	1582.1	1580.1
15°	1580.8	1607.8	1628.3	1638.6	1651.8	1655.7	1661.1
17.5°	1632.1	1668.2	1692.2	1724.1	1736.2	1743.5	1739.2
20°	1670.8	1718.3	1742.4	1780.6	1801.6	1812.8	1808.9
22.5°	1716.7	1768.1	1812.4	1845.5	1877.5	1892.7	1895.8
25°	1795.2	1865.7	1930.8	1974.3	2013.9	2023.3	2043.8
27.5°	1882.9	1966.0	2035.6	2081.4	2109.0	2119.4	2125.8
30°	1938.2	2020.8	2073.2	2102.5	2111.4	2110.4	2109.4
32.5°	1965.1	2016.9	2026.9	2018.7	1998.6	1981.6	1963.8
35°	1926.8	1888.2	1830.4	1756.1	1701.2	1646.0	1640.5
37.5°	1733.0	1609.3	1513.2	1405.8	1343.9	1305.6	1279.1
40°	1550.5	1410.0	1293.5	1203.0	1139.8	1114.9	1090.4
42.5°	1352.4	1218.1	1115.0	1039.3	991.8	964.1	944.8
45°	1098.7	980.3	899.6	844.7	807.1	785.5	773.3
47.5°	900.3	812.8	744.1	704.6	678.5	661.8	661.9
50°	793.8	710.1	664.6	633.3	610.8	597.6	600.0
52.5°	699.5	637.0	598.0	571.8	555.2	547.1	546.8
55°	584.8	539.8	514.3	495.3	484.0	474.8	476.7
57.5°	500.3	462.3	445.3	429.4	421.6	417.8	412.5
60°	447.8	418.5	403.8	391.1	383.2	380.3	374.8
62.5°	401.2	378.1	363.8	353.5	346.4	345.4	341.2
65°	337.2	319.6	306.9	302.0	294.6	292.7	292.7
67.5°	278.0	265.3	255.5	251.0	247.7	248.3	245.9
70°	240.8	230.5	224.1	219.2	216.8	217.3	215.4
72.5°	210.7	199.2	193.6	190.7	187.5	188.7	187.9
75°	159.6	153.6	150.7	147.8	145.8	144.9	143.9
77.5°	117.2	112.0	109.7	108.1	108.4	106.0	107.8
80°	90.6	86.1	84.6	82.2	81.7	81.7	81.2
82.5°	66.3	63.8	62.8	60.7	59.9	60.6	59.3
85°	34.2	32.3	31.9	31.9	30.8	29.9	32.3
87.5°	18.0	16.8	17.1	16.8	17.0	16.8	16.2
90°	27.4	29.0	30.3	31.2	32.1	33.1	34.0
92.5°	27.4	29.0	30.0	30.4	30.9	31.4	31.8
95°	27.4	29.0	29.8	29.8	29.8	29.8	29.8
97.5°	43.2	34.2	29.8	29.8	29.8	29.8	29.8
100°	105.9	59.0	34.9	33.6	32.3	31.1	29.8
102.5°	288.3	279.5	264.3	242.8	221.4	199.9	178.5
105°	422.8	422.8	422.6	422.4	422.1	421.7	421.4
107.5°	535.4	535.5	535.0	534.0	533.1	532.2	531.2
110°	607.3	606.3	606.1	606.3	606.6	607.0	607.3



TEST NUMBER: P333424-830

CATALOG NUMBER: S125DIW-S850D1560U830-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	679.2	678.0	677.1	676.7	676.3	675.8	675.3
115°	788.0	786.6	785.1	783.3	781.3	779.4	777.5
117.5°	892.7	891.0	889.8	889.0	888.2	887.3	886.5
120°	961.5	960.9	959.8	958.2	956.6	955.1	953.5
122.5°	1026.2	1025.6	1024.4	1022.6	1020.7	1018.9	1017.0
125°	1119.9	1118.7	1117.6	1116.6	1115.7	1114.7	1113.8
127.5°	1206.8	1206.1	1204.6	1202.2	1200.0	1197.6	1195.2
130°	1262.8	1261.9	1260.6	1259.0	1257.4	1255.8	1254.2
132.5°	1316.2	1316.0	1315.0	1313.5	1311.9	1310.3	1308.7
135°	1392.9	1392.2	1390.9	1389.0	1387.1	1385.3	1383.4
137.5°	1465.5	1465.7	1464.9	1463.2	1461.6	1459.9	1458.3
140°	1510.1	1510.8	1510.1	1508.3	1506.4	1504.5	1502.6
142.5°	1552.9	1553.0	1552.2	1550.2	1548.3	1546.4	1544.5
145°	1614.2	1614.5	1613.7	1611.8	1610.0	1608.1	1606.2
147.5°	1666.6	1667.0	1666.0	1663.8	1661.5	1659.3	1657.0
150°	1700.3	1700.9	1700.0	1697.4	1694.9	1692.4	1689.9
152.5°	1729.8	1730.4	1729.6	1727.3	1725.0	1722.8	1720.5
155°	1770.8	1771.7	1770.8	1768.4	1765.9	1763.3	1760.8
157.5°	1804.4	1805.4	1804.7	1802.1	1799.6	1797.1	1794.6
160°	1825.6	1826.8	1826.3	1823.7	1821.2	1818.6	1816.2
162.5°	1845.3	1847.0	1846.5	1843.8	1841.0	1838.2	1835.4
165°	1870.1	1872.0	1871.6	1869.2	1866.6	1864.1	1861.5
167.5°	1889.0	1891.3	1891.0	1888.2	1885.4	1882.5	1879.7
170°	1898.9	1901.4	1901.3	1898.5	1895.6	1892.7	1889.9
172.5°	1906.1	1908.4	1908.1	1905.3	1902.4	1899.6	1896.8
175°	1914.5	1917.0	1916.8	1914.0	1911.2	1908.4	1905.5
177.5°	1917.0	1918.8	1918.7	1916.7	1914.7	1912.6	1910.6
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0

(END OF REPORT)