

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333466-935

Luminaire Tested: **S125DIW-S1270D770U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333466-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D770U935-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7106.7 lumens  
Efficiency: N/A  
Efficacy: 118.8 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	60	59	58	54
2	92	85	79	73	86	80	74	70	70	66	63	62	58	56	54	51	49	45
3	84	75	67	61	79	70	64	59	62	57	53	55	51	47	48	45	42	39
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	43	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	34	57	46	38	33	41	35	30	36	31	28	32	28	25	23
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10213	10213	10213	10213
5°	11826	10247	8972	10247
10°	13759	10194	7861	10194
15°	15230	10120	7252	10120
20°	17049	10001	6763	10001
25°	19973	9867	6524	9867
30°	21572	9735	6317	9735
35°	17738	9488	6180	9488
40°	12607	9144	6032	9144
45°	9685	8680	5946	8680
50°	8268	8106	5934	8106
55°	7362	7543	5986	7543
60°	6640	6926	6138	6926
65°	6134	6308	6298	6308
70°	5576	5665	6388	5665
75°	4923	4991	6331	4991
80°	4143	4069	5791	4069
85°	3283	2934	4676	2934



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	152.2	2.1
10°-20°	453.2	6.4
20°-30°	736.0	10.4
30°-40°	897.7	12.6
40°-50°	816.7	11.5
50°-60°	650.5	9.2
60°-70°	453.1	6.4
70°-80°	241.6	3.4
80°-90°	62.8	0.9
90°-100°	31.3	0.4
100°-110°	192.7	2.7
110°-120°	349.6	4.9
120°-130°	448.6	6.3
130°-140°	482.6	6.8
140°-150°	452.9	6.4
150°-160°	366.4	5.2
160°-170°	237.0	3.3
170°-180°	81.7	1.2
0°-30°	1341.4	18.9
0°-40°	2239.2	31.5
0°-60°	3706.4	52.2
0°-90°	4463.9	62.8
90°-120°	573.6	8.1
90°-150°	1957.7	27.5
90°-180°	2643.0	37.2
0°-180°	7106.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1581	1581	1581	1581	1581	
5°	1824	1581	1384	1581	1824	184
15°	2278	1514	1085	1514	2278	652
25°	2803	1385	916	1385	2803	1280
35°	2250	1203	784	1203	2250	1377
45°	1060	950	651	950	1060	849
55°	654	670	532	670	654	589
65°	401	413	412	413	401	398
75°	197	200	254	200	197	212
85°	44	40	63	40	44	51
90°	15	1	15	1	15	8
95°	13	36	13	36	13	11
105°	190	188	190	188	190	171
115°	350	352	350	352	350	347
125°	501	501	501	501	501	446
135°	622	625	622	625	622	480
145°	722	724	722	724	722	451
155°	792	798	792	798	792	365
165°	837	842	837	842	837	236
175°	857	861	857	861	857	82
180°	861	861	861	861	861	



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1672.6	1670.4	1668.3	1664.0	1667.2	1658.0	1653.7	1646.2	1637.1	1633.9	1630.1
5°	1824.2	1827.6	1830.9	1816.9	1818.2	1808.8	1787.3	1769.9	1755.8	1737.7	1724.9
7.5°	2006.8	1998.9	1998.2	1989.1	1973.4	1960.8	1938.2	1909.4	1881.7	1850.0	1823.9
10°	2098.1	2098.8	2092.7	2082.0	2065.2	2053.1	2023.6	1995.4	1961.2	1920.9	1892.0
12.5°	2166.8	2169.6	2162.0	2147.5	2139.2	2112.2	2089.0	2055.6	2014.8	1982.6	1938.7
15°	2277.9	2270.5	2265.2	2247.0	2233.0	2204.8	2167.9	2133.0	2088.7	2047.7	2006.8
17.5°	2385.1	2391.0	2380.9	2364.4	2320.7	2287.8	2238.3	2190.4	2135.3	2080.3	2031.5
20°	2480.6	2486.1	2470.6	2441.7	2389.4	2356.5	2291.4	2229.6	2165.8	2095.4	2041.7
22.5°	2599.9	2595.6	2574.7	2530.8	2485.4	2424.7	2354.2	2279.0	2199.2	2119.5	2048.1
25°	2802.8	2774.6	2761.8	2707.5	2647.7	2558.5	2461.9	2351.7	2252.5	2147.1	2055.8
27.5°	2915.3	2906.4	2892.2	2854.4	2791.5	2696.0	2582.1	2448.0	2307.9	2174.9	2055.4
30°	2892.7	2894.1	2895.5	2883.3	2843.1	2771.2	2657.8	2513.5	2347.1	2197.4	2059.2
32.5°	2693.0	2717.4	2740.8	2768.5	2779.7	2765.9	2694.8	2564.6	2393.2	2223.2	2057.0
35°	2249.8	2257.1	2333.0	2408.1	2510.2	2589.4	2642.4	2584.6	2440.3	2245.1	2054.4
37.5°	1754.2	1790.4	1842.9	1927.9	2075.1	2206.9	2376.4	2454.5	2407.9	2252.2	2049.8
40°	1495.4	1529.0	1563.1	1649.8	1773.9	1933.6	2126.2	2290.7	2328.9	2229.6	2033.7
42.5°	1295.6	1322.2	1360.2	1425.3	1529.0	1670.5	1854.6	2069.5	2201.7	2164.1	1999.8
45°	1060.4	1077.2	1106.7	1158.5	1233.6	1344.4	1506.8	1741.7	1946.4	2014.1	1919.5
47.5°	907.7	907.6	930.5	966.2	1020.5	1114.6	1234.7	1418.8	1637.4	1799.1	1791.7
50°	822.9	819.5	837.6	868.5	911.5	973.9	1088.6	1235.6	1445.7	1628.9	1679.9
52.5°	749.8	750.2	761.4	784.2	820.2	873.5	959.2	1091.7	1271.2	1459.2	1555.4
55°	653.8	651.0	663.7	679.2	705.4	740.3	802.0	903.4	1049.0	1234.2	1359.1
57.5°	565.7	573.1	578.2	588.9	610.6	634.0	686.0	760.4	876.0	1034.9	1166.9
60°	514.1	521.5	525.6	536.2	553.7	573.9	614.2	674.5	771.9	908.8	1039.7
62.5°	468.0	473.7	475.0	484.7	498.9	518.6	550.3	601.0	677.9	797.6	925.8
65°	401.4	401.4	404.1	414.1	420.9	438.2	462.4	499.4	561.1	654.4	763.8
67.5°	337.2	340.4	339.8	344.1	350.3	363.9	381.3	411.7	457.4	525.6	613.0
70°	295.3	298.0	297.3	300.7	307.4	316.2	330.2	359.0	391.9	450.4	525.6
72.5°	257.7	258.8	257.1	261.5	265.5	273.2	288.9	304.3	335.0	384.4	446.1
75°	197.3	198.6	200.0	202.7	206.7	210.8	218.8	234.3	254.3	291.3	330.9
77.5°	147.9	145.3	148.6	148.2	150.5	153.6	160.7	168.8	185.4	208.7	239.4
80°	111.4	112.1	112.1	112.8	116.1	118.1	124.2	130.2	142.9	160.4	181.9
82.5°	81.4	83.1	82.1	83.3	86.0	87.5	90.8	95.8	103.2	116.9	132.5
85°	44.3	41.0	42.3	43.7	43.7	44.3	47.0	49.0	53.0	58.4	64.4
87.5°	15.9	17.0	17.4	17.3	17.7	17.7	19.6	19.5	21.0	22.5	24.4
90°	15.3	14.9	14.5	14.0	13.6	13.0	12.3	11.6	10.9	10.2	9.2
92.5°	14.3	14.1	13.9	13.7	13.5	13.0	12.3	11.6	10.9	10.2	9.3
95°	13.4	13.4	13.4	13.4	13.4	13.0	12.3	11.6	10.9	10.2	15.6
97.5°	13.4	13.4	13.4	13.4	13.4	15.4	19.4	23.4	27.4	31.4	42.0
100°	13.4	13.9	14.6	15.1	15.7	26.5	47.6	68.8	89.9	111.0	110.5
102.5°	80.2	89.9	99.5	109.2	118.8	125.6	129.7	133.6	137.7	141.6	141.3
105°	189.5	189.6	189.8	189.9	190.0	190.1	190.1	190.1	190.1	190.1	190.1
107.5°	238.8	239.3	239.7	240.1	240.6	240.7	240.7	240.7	240.6	240.6	240.4
110°	273.0	272.9	272.8	272.6	272.5	272.6	273.0	273.5	273.9	274.3	274.1



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	303.7	303.8	304.1	304.3	304.4	304.8	305.4	305.9	306.4	307.0	306.9
115°	349.6	350.4	351.3	352.1	353.0	353.7	354.3	354.8	355.4	356.0	355.9
117.5°	398.6	399.0	399.3	399.7	400.1	400.6	401.4	402.1	402.9	403.6	403.0
120°	428.7	429.5	430.2	430.8	431.5	432.0	432.3	432.7	432.9	433.2	432.7
122.5°	457.3	458.1	458.9	459.8	460.5	461.2	461.4	461.7	462.0	462.3	462.1
125°	500.8	501.3	501.6	502.0	502.5	503.0	503.6	504.1	504.7	505.2	505.2
127.5°	537.4	538.5	539.5	540.5	541.7	542.3	542.6	542.9	543.2	543.5	543.6
130°	564.0	564.6	565.4	566.1	566.8	567.4	567.8	568.3	568.6	569.0	568.9
132.5°	588.5	589.2	589.9	590.6	591.3	591.7	591.8	591.9	591.9	592.0	592.4
135°	622.0	622.8	623.7	624.6	625.4	626.0	626.3	626.5	626.8	627.2	627.4
137.5°	655.7	656.4	657.2	657.9	658.7	659.0	658.9	658.9	658.8	658.8	659.0
140°	675.6	676.5	677.3	678.1	679.0	679.3	679.0	678.7	678.5	678.1	678.3
142.5°	694.5	695.3	696.2	697.1	697.9	698.3	698.3	698.2	698.1	698.1	697.8
145°	722.2	723.1	723.8	724.7	725.6	725.9	725.8	725.7	725.5	725.4	725.4
147.5°	745.0	746.1	747.1	748.1	749.1	749.5	749.3	749.2	749.0	748.8	748.6
150°	759.8	761.0	762.1	763.2	764.4	764.8	764.5	764.2	764.0	763.6	763.4
152.5°	773.6	774.6	775.7	776.6	777.7	778.1	777.7	777.5	777.2	776.9	776.6
155°	791.7	792.9	794.0	795.1	796.3	796.6	796.2	795.7	795.3	794.9	794.6
157.5°	806.9	808.0	809.2	810.3	811.4	811.8	811.3	810.9	810.5	809.9	809.9
160°	816.6	817.8	818.9	820.0	821.1	821.4	820.9	820.3	819.8	819.2	819.0
162.5°	825.3	826.6	827.8	829.1	830.3	830.5	829.7	828.9	828.1	827.3	827.2
165°	837.0	838.2	839.3	840.4	841.5	841.7	840.9	840.0	839.1	838.3	838.2
167.5°	845.2	846.4	847.7	849.0	850.3	850.4	849.4	848.3	847.3	846.4	846.2
170°	849.8	851.0	852.3	853.6	854.9	855.0	853.9	852.6	851.5	850.4	850.2
172.5°	852.8	854.1	855.4	856.7	857.9	858.1	857.0	856.0	855.0	854.0	853.8
175°	856.8	858.1	859.4	860.7	861.9	861.9	860.8	859.7	858.6	857.5	857.3
177.5°	859.1	860.0	860.9	861.8	862.7	862.8	861.9	861.2	860.4	859.6	859.5
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1626.9	1623.2	1618.9	1611.4	1602.2	1597.4	1589.8	1585.0	1575.4	1567.3	1558.8
5°	1709.4	1692.0	1675.9	1655.1	1632.3	1617.5	1600.1	1580.6	1560.5	1539.6	1516.8
7.5°	1795.0	1764.1	1730.5	1694.4	1659.1	1626.6	1595.6	1565.1	1536.7	1502.4	1473.3
10°	1852.4	1813.5	1771.9	1722.9	1675.2	1633.7	1591.3	1554.4	1516.8	1476.5	1441.0
12.5°	1909.9	1858.0	1799.2	1745.4	1688.2	1637.9	1588.1	1541.0	1493.7	1449.1	1407.7
15°	1950.4	1904.8	1850.4	1773.9	1709.4	1640.4	1574.6	1513.5	1456.5	1406.8	1354.4
17.5°	1977.1	1918.3	1859.9	1786.5	1702.1	1624.8	1550.2	1480.3	1416.0	1353.1	1302.6
20°	1981.9	1921.6	1860.4	1788.6	1702.1	1613.5	1539.0	1455.1	1386.0	1320.9	1259.1
22.5°	1980.4	1911.9	1845.5	1771.5	1687.0	1605.4	1515.4	1429.9	1354.8	1290.8	1226.3
25°	1965.1	1892.0	1808.8	1734.3	1651.1	1564.5	1473.3	1384.7	1308.1	1234.9	1171.2
27.5°	1952.6	1857.7	1763.4	1676.5	1596.2	1516.8	1429.4	1338.7	1253.9	1179.7	1119.6
30°	1937.0	1833.0	1726.9	1636.3	1553.8	1476.5	1394.0	1305.4	1216.9	1144.4	1080.0
32.5°	1923.0	1801.8	1689.9	1591.2	1503.8	1428.7	1352.6	1268.3	1181.4	1107.8	1043.4
35°	1896.1	1755.8	1627.5	1516.1	1422.9	1345.7	1281.9	1203.4	1123.5	1052.4	990.7
37.5°	1861.8	1695.4	1557.8	1441.0	1338.7	1257.4	1198.0	1137.7	1061.1	992.6	936.7
40°	1835.0	1652.4	1506.8	1387.3	1281.3	1196.7	1141.7	1084.6	1020.9	957.1	898.0
42.5°	1801.1	1613.8	1455.3	1326.6	1221.7	1139.3	1081.5	1033.0	976.8	917.4	862.5
45°	1739.0	1543.7	1371.8	1233.6	1127.6	1046.4	986.6	950.4	908.1	851.7	805.4
47.5°	1647.6	1459.5	1281.8	1139.1	1029.7	954.4	898.5	863.7	833.9	791.9	749.9
50°	1566.5	1396.7	1216.9	1075.2	965.8	889.9	838.3	806.8	781.3	749.0	713.4
52.5°	1475.8	1317.8	1153.0	1013.0	904.6	829.8	779.2	751.5	730.2	707.1	672.1
55°	1331.6	1197.4	1044.3	911.5	811.4	738.3	694.0	669.9	652.4	634.9	613.5
57.5°	1172.8	1067.8	932.3	810.8	718.7	652.1	610.8	587.3	573.7	564.7	552.1
60°	1061.1	971.2	854.4	743.6	653.8	594.7	554.4	536.2	524.9	517.5	508.1
62.5°	957.5	883.6	775.5	674.4	595.7	539.8	503.9	486.3	475.4	471.8	464.1
65°	804.7	747.7	658.4	574.5	507.4	459.8	429.6	412.8	406.0	402.0	402.7
67.5°	654.3	619.5	547.8	476.2	422.7	382.7	358.5	345.7	342.3	336.9	336.8
70°	562.4	536.2	475.9	413.5	365.8	334.9	313.4	300.0	296.6	293.9	293.3
72.5°	481.4	458.4	406.0	356.0	313.1	286.0	268.4	260.3	254.8	253.1	253.0
75°	361.8	349.0	307.4	267.8	238.2	219.5	207.4	200.0	196.0	195.3	196.0
77.5°	257.2	246.1	219.6	191.6	172.9	158.7	148.4	145.9	141.4	141.5	140.8
80°	193.3	185.9	169.1	147.0	131.6	119.5	114.1	109.4	108.1	106.1	108.1
82.5°	140.2	132.2	120.8	106.7	93.9	86.7	81.4	79.9	79.0	78.1	78.5
85°	69.1	69.8	63.1	52.3	47.0	43.0	39.6	39.6	38.9	38.2	38.9
87.5°	25.2	24.0	21.6	19.8	16.9	15.1	14.3	14.6	13.3	12.9	13.7
90°	8.3	7.2	6.2	5.2	4.0	2.9	1.8	0.6	1.8	2.9	4.0
92.5°	8.4	7.6	6.7	6.6	7.4	8.3	9.0	9.8	9.0	8.3	7.4
95°	21.0	26.3	31.8	34.7	35.1	35.5	35.9	36.3	35.9	35.5	35.1
97.5°	52.7	63.4	74.0	79.0	78.2	77.5	76.7	75.9	76.7	77.5	78.2
100°	109.9	109.3	108.7	108.2	107.8	107.4	106.9	106.5	106.9	107.4	107.8
102.5°	140.9	140.6	140.3	139.8	139.3	138.8	138.2	137.7	138.2	138.8	139.3
105°	190.1	190.1	190.1	189.9	189.2	188.7	188.1	187.5	188.1	188.7	189.2
107.5°	240.0	239.8	239.5	239.4	239.4	239.4	239.4	239.4	239.4	239.4	239.4
110°	273.8	273.5	273.2	273.0	273.0	273.0	273.0	273.0	273.0	273.0	273.0





TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	306.7	306.5	306.3	306.1	305.7	305.4	305.1	304.7	305.1	305.4	305.7
115°	355.7	355.6	355.4	355.0	354.3	353.6	352.8	352.1	352.8	353.6	354.3
117.5°	402.5	402.0	401.4	401.1	401.2	401.2	401.2	401.3	401.2	401.2	401.2
120°	432.3	431.9	431.4	431.4	431.4	431.6	431.8	431.9	431.8	431.6	431.4
122.5°	461.8	461.7	461.5	461.2	460.5	460.0	459.5	458.9	459.5	460.0	460.5
125°	505.2	505.2	505.2	504.8	503.8	502.8	501.8	500.8	501.8	502.8	503.8
127.5°	543.7	543.8	543.9	543.5	542.9	542.2	541.5	540.7	541.5	542.2	542.9
130°	568.8	568.6	568.5	568.1	567.4	566.6	565.9	565.2	565.9	566.6	567.4
132.5°	592.6	593.0	593.3	593.1	592.2	591.4	590.6	589.7	590.6	591.4	592.2
135°	627.7	628.0	628.3	628.0	627.2	626.3	625.4	624.6	625.4	626.3	627.2
137.5°	659.3	659.5	659.8	659.5	658.8	658.1	657.4	656.6	657.4	658.1	658.8
140°	678.5	678.6	678.7	678.6	678.4	678.1	677.8	677.5	677.8	678.1	678.4
142.5°	697.7	697.5	697.2	697.1	696.9	696.7	696.5	696.4	696.5	696.7	696.9
145°	725.4	725.4	725.4	725.2	725.0	724.7	724.4	724.1	724.4	724.7	725.0
147.5°	748.5	748.4	748.2	748.1	748.2	748.2	748.3	748.4	748.3	748.2	748.2
150°	763.1	762.8	762.5	762.5	762.8	763.1	763.4	763.6	763.4	763.1	762.8
152.5°	776.4	776.1	775.8	775.9	776.6	777.2	777.8	778.4	777.8	777.2	776.6
155°	794.4	794.1	793.8	794.1	794.9	795.7	796.6	797.5	796.6	795.7	794.9
157.5°	809.9	809.9	809.9	810.1	810.6	811.1	811.7	812.1	811.7	811.1	810.6
160°	818.9	818.7	818.6	819.0	819.8	820.6	821.5	822.3	821.5	820.6	819.8
162.5°	827.1	826.9	826.7	827.1	827.9	828.8	829.7	830.5	829.7	828.8	827.9
165°	838.0	837.8	837.8	838.1	839.0	839.8	840.6	841.5	840.6	839.8	839.0
167.5°	846.0	845.9	845.8	846.1	847.1	847.9	848.8	849.6	848.8	847.9	847.1
170°	850.2	850.0	849.8	850.2	851.3	852.2	853.3	854.3	853.3	852.2	851.3
172.5°	853.5	853.3	853.0	853.3	854.3	855.3	856.4	857.3	856.4	855.3	854.3
175°	857.1	857.0	856.9	857.2	858.1	858.9	859.8	860.7	859.8	858.9	858.1
177.5°	859.4	859.3	859.1	859.5	860.1	860.8	861.4	862.1	861.4	860.8	860.1
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1553.8	1548.0	1543.2	1532.4	1526.5	1518.5	1512.0	1519.0	1511.5	1514.7	1509.8
5°	1505.5	1486.6	1473.3	1453.7	1437.0	1421.5	1410.1	1408.1	1402.7	1400.1	1392.0
7.5°	1447.2	1423.7	1400.6	1375.1	1353.6	1331.7	1317.8	1306.2	1298.6	1288.5	1281.7
10°	1412.8	1381.3	1354.4	1323.5	1296.7	1273.2	1254.4	1245.0	1236.3	1223.6	1218.8
12.5°	1370.4	1337.7	1305.0	1272.0	1246.2	1220.0	1203.9	1189.7	1183.7	1169.3	1167.9
15°	1319.5	1270.5	1238.3	1204.7	1169.2	1147.7	1134.3	1118.9	1112.2	1102.1	1094.7
17.5°	1258.9	1215.0	1174.8	1140.1	1109.6	1091.5	1074.8	1064.2	1052.7	1046.1	1034.0
20°	1214.8	1173.2	1132.9	1096.1	1072.5	1051.7	1038.3	1028.2	1016.2	1012.8	1000.7
22.5°	1177.8	1131.9	1093.2	1062.2	1036.6	1013.1	998.6	991.7	983.4	973.1	970.6
25°	1117.5	1069.9	1037.0	1006.1	983.3	961.8	951.7	943.0	935.0	927.6	924.9
27.5°	1065.4	1022.9	983.8	955.9	936.0	916.4	907.6	897.0	891.0	885.1	877.9
30°	1028.9	985.2	951.1	924.2	902.8	885.3	875.9	868.5	863.2	857.7	853.8
32.5°	991.4	950.9	917.7	891.5	870.0	856.8	848.5	843.3	837.3	830.9	825.8
35°	941.7	897.3	865.1	842.3	825.5	815.5	806.1	801.3	794.7	794.7	789.3
37.5°	885.7	847.4	819.0	798.1	783.1	774.1	764.0	760.7	756.4	753.5	751.7
40°	852.4	816.8	790.0	769.1	753.0	745.6	737.6	732.3	729.5	726.2	724.9
42.5°	818.0	784.0	758.3	739.1	725.1	718.8	711.3	707.6	702.1	697.8	697.0
45°	765.8	732.9	709.5	694.0	681.9	674.5	669.9	661.8	659.1	653.8	653.1
47.5°	716.3	684.8	661.7	649.0	638.4	632.4	625.0	616.9	613.9	611.1	610.9
50°	679.2	650.4	628.9	616.8	606.7	598.1	590.6	585.2	583.2	583.2	584.6
52.5°	641.6	617.1	598.8	584.0	574.5	565.2	558.4	555.2	552.1	555.3	557.8
55°	586.6	561.8	548.4	534.3	524.9	514.1	510.7	509.5	507.4	512.8	515.5
57.5°	528.3	510.9	495.2	481.2	472.8	466.6	462.0	461.2	465.0	467.5	476.2
60°	491.3	471.1	457.1	446.3	436.3	432.2	430.9	429.6	432.2	439.6	451.0
62.5°	450.5	434.1	419.0	410.9	403.5	396.8	396.5	397.4	402.7	411.1	422.6
65°	390.6	376.5	366.4	357.1	351.0	347.0	348.4	351.0	357.1	368.5	381.3
67.5°	329.8	320.1	311.2	303.5	297.7	297.7	299.1	303.1	310.2	323.4	335.0
70°	290.6	279.9	272.5	269.1	264.4	261.7	265.8	272.5	278.5	290.6	300.7
72.5°	251.4	242.3	236.5	234.3	232.2	230.1	231.4	238.7	246.8	258.9	270.6
75°	193.3	189.9	185.9	183.2	181.2	182.5	183.9	190.6	197.3	210.1	223.5
77.5°	141.1	137.6	135.2	134.5	133.5	134.1	137.8	142.8	149.4	158.7	168.8
80°	106.7	105.4	104.0	103.3	103.3	104.0	109.4	112.8	118.8	127.5	135.6
82.5°	77.7	76.9	76.6	76.5	77.1	77.1	80.4	84.8	89.8	96.3	103.3
85°	41.0	39.6	41.6	42.3	41.0	43.0	44.3	47.0	49.0	52.3	55.7
87.5°	14.5	15.8	15.4	16.1	16.4	17.7	17.2	19.5	20.8	22.0	21.5
90°	5.2	6.2	7.2	8.3	9.2	10.2	10.9	11.6	12.3	13.0	13.6
92.5°	6.6	6.7	7.6	8.4	9.3	10.2	10.9	11.6	12.3	13.0	13.5
95°	34.7	31.8	26.3	21.0	15.6	10.2	10.9	11.6	12.3	13.0	13.4
97.5°	79.0	74.0	63.4	52.7	42.0	31.4	27.4	23.4	19.4	15.4	13.4
100°	108.2	108.7	109.3	109.9	110.5	111.0	89.9	68.8	47.6	26.5	15.7
102.5°	139.8	140.3	140.6	140.9	141.3	141.6	137.7	133.6	129.7	125.6	118.8
105°	189.9	190.1	190.1	190.1	190.1	190.1	190.1	190.1	190.1	190.1	190.0
107.5°	239.4	239.5	239.8	240.0	240.4	240.6	240.6	240.7	240.7	240.7	240.6
110°	273.0	273.2	273.5	273.8	274.1	274.3	273.9	273.5	273.0	272.6	272.5



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	306.1	306.3	306.5	306.7	306.9	307.0	306.4	305.9	305.4	304.8	304.4
115°	355.0	355.4	355.6	355.7	355.9	356.0	355.4	354.8	354.3	353.7	353.0
117.5°	401.1	401.4	402.0	402.5	403.0	403.6	402.9	402.1	401.4	400.6	400.1
120°	431.4	431.4	431.9	432.3	432.7	433.2	432.9	432.7	432.3	432.0	431.5
122.5°	461.2	461.5	461.7	461.8	462.1	462.3	462.0	461.7	461.4	461.2	460.5
125°	504.8	505.2	505.2	505.2	505.2	505.2	504.7	504.1	503.6	503.0	502.5
127.5°	543.5	543.9	543.8	543.7	543.6	543.5	543.2	542.9	542.6	542.3	541.7
130°	568.1	568.5	568.6	568.8	568.9	569.0	568.6	568.3	567.8	567.4	566.8
132.5°	593.1	593.3	593.0	592.6	592.4	592.0	591.9	591.9	591.8	591.7	591.3
135°	628.0	628.3	628.0	627.7	627.4	627.2	626.8	626.5	626.3	626.0	625.4
137.5°	659.5	659.8	659.5	659.3	659.0	658.8	658.8	658.9	658.9	659.0	658.7
140°	678.6	678.7	678.6	678.5	678.3	678.1	678.5	678.7	679.0	679.3	679.0
142.5°	697.1	697.2	697.5	697.7	697.8	698.1	698.1	698.2	698.3	698.3	697.9
145°	725.2	725.4	725.4	725.4	725.4	725.4	725.5	725.7	725.8	725.9	725.6
147.5°	748.1	748.2	748.4	748.5	748.6	748.8	749.0	749.2	749.3	749.5	749.1
150°	762.5	762.5	762.8	763.1	763.4	763.6	764.0	764.2	764.5	764.8	764.4
152.5°	775.9	775.8	776.1	776.4	776.6	776.9	777.2	777.5	777.7	778.1	777.7
155°	794.1	793.8	794.1	794.4	794.6	794.9	795.3	795.7	796.2	796.6	796.3
157.5°	810.1	809.9	809.9	809.9	809.9	809.9	810.5	810.9	811.3	811.8	811.4
160°	819.0	818.6	818.7	818.9	819.0	819.2	819.8	820.3	820.9	821.4	821.1
162.5°	827.1	826.7	826.9	827.1	827.2	827.3	828.1	828.9	829.7	830.5	830.3
165°	838.1	837.8	837.8	838.0	838.2	838.3	839.1	840.0	840.9	841.7	841.5
167.5°	846.1	845.8	845.9	846.0	846.2	846.4	847.3	848.3	849.4	850.4	850.3
170°	850.2	849.8	850.0	850.2	850.2	850.4	851.5	852.6	853.9	855.0	854.9
172.5°	853.3	853.0	853.3	853.5	853.8	854.0	855.0	856.0	857.0	858.1	857.9
175°	857.2	856.9	857.0	857.1	857.3	857.5	858.6	859.7	860.8	861.9	861.9
177.5°	859.5	859.1	859.3	859.4	859.5	859.6	860.4	861.2	861.9	862.8	862.7
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1506.7	1510.4	1507.2	1511.5	1507.2	1510.4	1506.7	1509.8	1514.7	1511.5	1519.0
5°	1388.6	1382.6	1386.6	1384.0	1386.6	1382.6	1388.6	1392.0	1400.1	1402.7	1408.1
7.5°	1279.6	1273.8	1267.3	1264.2	1267.3	1273.8	1279.6	1281.7	1288.5	1298.6	1306.2
10°	1211.4	1204.1	1203.4	1198.7	1203.4	1204.1	1211.4	1218.8	1223.6	1236.3	1245.0
12.5°	1161.5	1154.7	1147.0	1145.0	1147.0	1154.7	1161.5	1167.9	1169.3	1183.7	1189.7
15°	1090.6	1085.3	1080.6	1084.6	1080.6	1085.3	1090.6	1094.7	1102.1	1112.2	1118.9
17.5°	1031.7	1027.3	1026.5	1021.5	1026.5	1027.3	1031.7	1034.0	1046.1	1052.7	1064.2
20°	994.7	991.4	992.6	984.0	992.6	991.4	994.7	1000.7	1012.8	1016.2	1028.2
22.5°	965.2	958.6	957.8	956.1	957.8	958.6	965.2	970.6	973.1	983.4	991.7
25°	918.9	915.5	912.1	915.5	912.1	915.5	918.9	924.9	927.6	935.0	943.0
27.5°	878.4	874.4	873.5	873.8	873.5	874.4	878.4	877.9	885.1	891.0	897.0
30°	853.8	847.1	847.7	847.1	847.7	847.1	853.8	853.8	857.7	863.2	868.5
32.5°	826.9	822.3	821.4	820.2	821.4	822.3	826.9	825.8	830.9	837.3	843.3
35°	787.3	787.3	783.9	783.9	783.9	787.3	787.3	789.3	794.7	794.7	801.3
37.5°	750.1	749.4	747.4	747.7	747.4	749.4	750.1	751.7	753.5	756.4	760.7
40°	722.2	721.5	719.5	715.5	719.5	721.5	722.2	724.9	726.2	729.5	732.3
42.5°	695.3	693.0	692.1	690.8	692.1	693.0	695.3	697.0	697.8	702.1	707.6
45°	653.1	653.1	651.7	651.0	651.7	653.1	653.1	653.1	653.8	659.1	661.8
47.5°	612.0	613.2	615.7	615.4	615.7	613.2	612.0	610.9	611.1	613.9	616.9
50°	587.3	588.0	590.0	590.6	590.0	588.0	587.3	584.6	583.2	583.2	585.2
52.5°	559.9	563.8	566.4	565.9	566.4	563.8	559.9	557.8	555.3	552.1	555.2
55°	521.5	526.2	530.9	531.6	530.9	526.2	521.5	515.5	512.8	507.4	509.5
57.5°	483.5	490.1	495.1	496.6	495.1	490.1	483.5	476.2	467.5	465.0	461.2
60°	457.7	466.5	472.5	475.2	472.5	466.5	457.7	451.0	439.6	432.2	429.6
62.5°	433.0	442.8	448.8	449.4	448.8	442.8	433.0	422.6	411.1	402.7	397.4
65°	392.6	402.7	408.0	412.1	408.0	402.7	392.6	381.3	368.5	357.1	351.0
67.5°	349.1	359.2	365.2	368.3	365.2	359.2	349.1	335.0	323.4	310.2	303.1
70°	317.5	327.5	335.6	338.3	335.6	327.5	317.5	300.7	290.6	278.5	272.5
72.5°	286.3	295.3	301.8	305.0	301.8	295.3	286.3	270.6	258.9	246.8	238.7
75°	232.2	244.3	250.4	253.7	250.4	244.3	232.2	223.5	210.1	197.3	190.6
77.5°	179.1	190.1	193.7	195.4	193.7	190.1	179.1	168.8	158.7	149.4	142.8
80°	143.6	150.3	155.1	155.7	155.1	150.3	143.6	135.6	127.5	118.8	112.8
82.5°	110.4	116.0	117.4	119.2	117.4	116.0	110.4	103.3	96.3	89.8	84.8
85°	60.4	63.1	63.8	63.1	63.8	63.1	60.4	55.7	52.3	49.0	47.0
87.5°	22.6	22.2	22.3	23.5	22.3	22.2	22.6	21.5	22.0	20.8	19.5
90°	14.0	14.5	14.9	15.3	14.9	14.5	14.0	13.6	13.0	12.3	11.6
92.5°	13.7	13.9	14.1	14.3	14.1	13.9	13.7	13.5	13.0	12.3	11.6
95°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.0	12.3	11.6
97.5°	13.4	13.4	13.4	13.4	13.4	13.4	13.4	13.4	15.4	19.4	23.4
100°	15.1	14.6	13.9	13.4	13.9	14.6	15.1	15.7	26.5	47.6	68.8
102.5°	109.2	99.5	89.9	80.2	89.9	99.5	109.2	118.8	125.6	129.7	133.6
105°	189.9	189.8	189.6	189.5	189.6	189.8	189.9	190.0	190.1	190.1	190.1
107.5°	240.1	239.7	239.3	238.8	239.3	239.7	240.1	240.6	240.7	240.7	240.7
110°	272.6	272.8	272.9	273.0	272.9	272.8	272.6	272.5	272.6	273.0	273.5



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	304.3	304.1	303.8	303.7	303.8	304.1	304.3	304.4	304.8	305.4	305.9
115°	352.1	351.3	350.4	349.6	350.4	351.3	352.1	353.0	353.7	354.3	354.8
117.5°	399.7	399.3	399.0	398.6	399.0	399.3	399.7	400.1	400.6	401.4	402.1
120°	430.8	430.2	429.5	428.7	429.5	430.2	430.8	431.5	432.0	432.3	432.7
122.5°	459.8	458.9	458.1	457.3	458.1	458.9	459.8	460.5	461.2	461.4	461.7
125°	502.0	501.6	501.3	500.8	501.3	501.6	502.0	502.5	503.0	503.6	504.1
127.5°	540.5	539.5	538.5	537.4	538.5	539.5	540.5	541.7	542.3	542.6	542.9
130°	566.1	565.4	564.6	564.0	564.6	565.4	566.1	566.8	567.4	567.8	568.3
132.5°	590.6	589.9	589.2	588.5	589.2	589.9	590.6	591.3	591.7	591.8	591.9
135°	624.6	623.7	622.8	622.0	622.8	623.7	624.6	625.4	626.0	626.3	626.5
137.5°	657.9	657.2	656.4	655.7	656.4	657.2	657.9	658.7	659.0	658.9	658.9
140°	678.1	677.3	676.5	675.6	676.5	677.3	678.1	679.0	679.3	679.0	678.7
142.5°	697.1	696.2	695.3	694.5	695.3	696.2	697.1	697.9	698.3	698.3	698.2
145°	724.7	723.8	723.1	722.2	723.1	723.8	724.7	725.6	725.9	725.8	725.7
147.5°	748.1	747.1	746.1	745.0	746.1	747.1	748.1	749.1	749.5	749.3	749.2
150°	763.2	762.1	761.0	759.8	761.0	762.1	763.2	764.4	764.8	764.5	764.2
152.5°	776.6	775.7	774.6	773.6	774.6	775.7	776.6	777.7	778.1	777.7	777.5
155°	795.1	794.0	792.9	791.7	792.9	794.0	795.1	796.3	796.6	796.2	795.7
157.5°	810.3	809.2	808.0	806.9	808.0	809.2	810.3	811.4	811.8	811.3	810.9
160°	820.0	818.9	817.8	816.6	817.8	818.9	820.0	821.1	821.4	820.9	820.3
162.5°	829.1	827.8	826.6	825.3	826.6	827.8	829.1	830.3	830.5	829.7	828.9
165°	840.4	839.3	838.2	837.0	838.2	839.3	840.4	841.5	841.7	840.9	840.0
167.5°	849.0	847.7	846.4	845.2	846.4	847.7	849.0	850.3	850.4	849.4	848.3
170°	853.6	852.3	851.0	849.8	851.0	852.3	853.6	854.9	855.0	853.9	852.6
172.5°	856.7	855.4	854.1	852.8	854.1	855.4	856.7	857.9	858.1	857.0	856.0
175°	860.7	859.4	858.1	856.8	858.1	859.4	860.7	861.9	861.9	860.8	859.7
177.5°	861.8	860.9	860.0	859.1	860.0	860.9	861.8	862.7	862.8	861.9	861.2
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1512.0	1518.5	1526.5	1532.4	1543.2	1548.0	1553.8	1558.8	1567.3	1575.4	1585.0
5°	1410.1	1421.5	1437.0	1453.7	1473.3	1486.6	1505.5	1516.8	1539.6	1560.5	1580.6
7.5°	1317.8	1331.7	1353.6	1375.1	1400.6	1423.7	1447.2	1473.3	1502.4	1536.7	1565.1
10°	1254.4	1273.2	1296.7	1323.5	1354.4	1381.3	1412.8	1441.0	1476.5	1516.8	1554.4
12.5°	1203.9	1220.0	1246.2	1272.0	1305.0	1337.7	1370.4	1407.7	1449.1	1493.7	1541.0
15°	1134.3	1147.7	1169.2	1204.7	1238.3	1270.5	1319.5	1354.4	1406.8	1456.5	1513.5
17.5°	1074.8	1091.5	1109.6	1140.1	1174.8	1215.0	1258.9	1302.6	1353.1	1416.0	1480.3
20°	1038.3	1051.7	1072.5	1096.1	1132.9	1173.2	1214.8	1259.1	1320.9	1386.0	1455.1
22.5°	998.6	1013.1	1036.6	1062.2	1093.2	1131.9	1177.8	1226.3	1290.8	1354.8	1429.9
25°	951.7	961.8	983.3	1006.1	1037.0	1069.9	1117.5	1171.2	1234.9	1308.1	1384.7
27.5°	907.6	916.4	936.0	955.9	983.8	1022.9	1065.4	1119.6	1179.7	1253.9	1338.7
30°	875.9	885.3	902.8	924.2	951.1	985.2	1028.9	1080.0	1144.4	1216.9	1305.4
32.5°	848.5	856.8	870.0	891.5	917.7	950.9	991.4	1043.4	1107.8	1181.4	1268.3
35°	806.1	815.5	825.5	842.3	865.1	897.3	941.7	990.7	1052.4	1123.5	1203.4
37.5°	764.0	774.1	783.1	798.1	819.0	847.4	885.7	936.7	992.6	1061.1	1137.7
40°	737.6	745.6	753.0	769.1	790.0	816.8	852.4	898.0	957.1	1020.9	1084.6
42.5°	711.3	718.8	725.1	739.1	758.3	784.0	818.0	862.5	917.4	976.8	1033.0
45°	669.9	674.5	681.9	694.0	709.5	732.9	765.8	805.4	851.7	908.1	950.4
47.5°	625.0	632.4	638.4	649.0	661.7	684.8	716.3	749.9	791.9	833.9	863.7
50°	590.6	598.1	606.7	616.8	628.9	650.4	679.2	713.4	749.0	781.3	806.8
52.5°	558.4	565.2	574.5	584.0	598.8	617.1	641.6	672.1	707.1	730.2	751.5
55°	510.7	514.1	524.9	534.3	548.4	561.8	586.6	613.5	634.9	652.4	669.9
57.5°	462.0	466.6	472.8	481.2	495.2	510.9	528.3	552.1	564.7	573.7	587.3
60°	430.9	432.2	436.3	446.3	457.1	471.1	491.3	508.1	517.5	524.9	536.2
62.5°	396.5	396.8	403.5	410.9	419.0	434.1	450.5	464.1	471.8	475.4	486.3
65°	348.4	347.0	351.0	357.1	366.4	376.5	390.6	402.7	402.0	406.0	412.8
67.5°	299.1	297.7	297.7	303.5	311.2	320.1	329.8	336.8	336.9	342.3	345.7
70°	265.8	261.7	264.4	269.1	272.5	279.9	290.6	293.3	293.9	296.6	300.0
72.5°	231.4	230.1	232.2	234.3	236.5	242.3	251.4	253.0	253.1	254.8	260.3
75°	183.9	182.5	181.2	183.2	185.9	189.9	193.3	196.0	195.3	196.0	200.0
77.5°	137.8	134.1	133.5	134.5	135.2	137.6	141.1	140.8	141.5	141.4	145.9
80°	109.4	104.0	103.3	103.3	104.0	105.4	106.7	108.1	106.1	108.1	109.4
82.5°	80.4	77.1	77.1	76.5	76.6	76.9	77.7	78.5	78.1	79.0	79.9
85°	44.3	43.0	41.0	42.3	41.6	39.6	41.0	38.9	38.2	38.9	39.6
87.5°	17.2	17.7	16.4	16.1	15.4	15.8	14.5	13.7	12.9	13.3	14.6
90°	10.9	10.2	9.2	8.3	7.2	6.2	5.2	4.0	2.9	1.8	0.6
92.5°	10.9	10.2	9.3	8.4	7.6	6.7	6.6	7.4	8.3	9.0	9.8
95°	10.9	10.2	15.6	21.0	26.3	31.8	34.7	35.1	35.5	35.9	36.3
97.5°	27.4	31.4	42.0	52.7	63.4	74.0	79.0	78.2	77.5	76.7	75.9
100°	89.9	111.0	110.5	109.9	109.3	108.7	108.2	107.8	107.4	106.9	106.5
102.5°	137.7	141.6	141.3	140.9	140.6	140.3	139.8	139.3	138.8	138.2	137.7
105°	190.1	190.1	190.1	190.1	190.1	190.1	189.9	189.2	188.7	188.1	187.5
107.5°	240.6	240.6	240.4	240.0	239.8	239.5	239.4	239.4	239.4	239.4	239.4
110°	273.9	274.3	274.1	273.8	273.5	273.2	273.0	273.0	273.0	273.0	273.0



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	306.4	307.0	306.9	306.7	306.5	306.3	306.1	305.7	305.4	305.1	304.7
115°	355.4	356.0	355.9	355.7	355.6	355.4	355.0	354.3	353.6	352.8	352.1
117.5°	402.9	403.6	403.0	402.5	402.0	401.4	401.1	401.2	401.2	401.2	401.3
120°	432.9	433.2	432.7	432.3	431.9	431.4	431.4	431.4	431.6	431.8	431.9
122.5°	462.0	462.3	462.1	461.8	461.7	461.5	461.2	460.5	460.0	459.5	458.9
125°	504.7	505.2	505.2	505.2	505.2	505.2	504.8	503.8	502.8	501.8	500.8
127.5°	543.2	543.5	543.6	543.7	543.8	543.9	543.5	542.9	542.2	541.5	540.7
130°	568.6	569.0	568.9	568.8	568.6	568.5	568.1	567.4	566.6	565.9	565.2
132.5°	591.9	592.0	592.4	592.6	593.0	593.3	593.1	592.2	591.4	590.6	589.7
135°	626.8	627.2	627.4	627.7	628.0	628.3	628.0	627.2	626.3	625.4	624.6
137.5°	658.8	658.8	659.0	659.3	659.5	659.8	659.5	658.8	658.1	657.4	656.6
140°	678.5	678.1	678.3	678.5	678.6	678.7	678.6	678.4	678.1	677.8	677.5
142.5°	698.1	698.1	697.8	697.7	697.5	697.2	697.1	696.9	696.7	696.5	696.4
145°	725.5	725.4	725.4	725.4	725.4	725.4	725.2	725.0	724.7	724.4	724.1
147.5°	749.0	748.8	748.6	748.5	748.4	748.2	748.1	748.2	748.2	748.3	748.4
150°	764.0	763.6	763.4	763.1	762.8	762.5	762.5	762.8	763.1	763.4	763.6
152.5°	777.2	776.9	776.6	776.4	776.1	775.8	775.9	776.6	777.2	777.8	778.4
155°	795.3	794.9	794.6	794.4	794.1	793.8	794.1	794.9	795.7	796.6	797.5
157.5°	810.5	809.9	809.9	809.9	809.9	809.9	810.1	810.6	811.1	811.7	812.1
160°	819.8	819.2	819.0	818.9	818.7	818.6	819.0	819.8	820.6	821.5	822.3
162.5°	828.1	827.3	827.2	827.1	826.9	826.7	827.1	827.9	828.8	829.7	830.5
165°	839.1	838.3	838.2	838.0	837.8	837.8	838.1	839.0	839.8	840.6	841.5
167.5°	847.3	846.4	846.2	846.0	845.9	845.8	846.1	847.1	847.9	848.8	849.6
170°	851.5	850.4	850.2	850.2	850.0	849.8	850.2	851.3	852.2	853.3	854.3
172.5°	855.0	854.0	853.8	853.5	853.3	853.0	853.3	854.3	855.3	856.4	857.3
175°	858.6	857.5	857.3	857.1	857.0	856.9	857.2	858.1	858.9	859.8	860.7
177.5°	860.4	859.6	859.5	859.4	859.3	859.1	859.5	860.1	860.8	861.4	862.1
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1589.8	1597.4	1602.2	1611.4	1618.9	1623.2	1626.9	1630.1	1633.9	1637.1	1646.2
5°	1600.1	1617.5	1632.3	1655.1	1675.9	1692.0	1709.4	1724.9	1737.7	1755.8	1769.9
7.5°	1595.6	1626.6	1659.1	1694.4	1730.5	1764.1	1795.0	1823.9	1850.0	1881.7	1909.4
10°	1591.3	1633.7	1675.2	1722.9	1771.9	1813.5	1852.4	1892.0	1920.9	1961.2	1995.4
12.5°	1588.1	1637.9	1688.2	1745.4	1799.2	1858.0	1909.9	1938.7	1982.6	2014.8	2055.6
15°	1574.6	1640.4	1709.4	1773.9	1850.4	1904.8	1950.4	2006.8	2047.7	2088.7	2133.0
17.5°	1550.2	1624.8	1702.1	1786.5	1859.9	1918.3	1977.1	2031.5	2080.3	2135.3	2190.4
20°	1539.0	1613.5	1702.1	1788.6	1860.4	1921.6	1981.9	2041.7	2095.4	2165.8	2229.6
22.5°	1515.4	1605.4	1687.0	1771.5	1845.5	1911.9	1980.4	2048.1	2119.5	2199.2	2279.0
25°	1473.3	1564.5	1651.1	1734.3	1808.8	1892.0	1965.1	2055.8	2147.1	2252.5	2351.7
27.5°	1429.4	1516.8	1596.2	1676.5	1763.4	1857.7	1952.6	2055.4	2174.9	2307.9	2448.0
30°	1394.0	1476.5	1553.8	1636.3	1726.9	1833.0	1937.0	2059.2	2197.4	2347.1	2513.5
32.5°	1352.6	1428.7	1503.8	1591.2	1689.9	1801.8	1923.0	2057.0	2223.2	2393.2	2564.6
35°	1281.9	1345.7	1422.9	1516.1	1627.5	1755.8	1896.1	2054.4	2245.1	2440.3	2584.6
37.5°	1198.0	1257.4	1338.7	1441.0	1557.8	1695.4	1861.8	2049.8	2252.2	2407.9	2454.5
40°	1141.7	1196.7	1281.3	1387.3	1506.8	1652.4	1835.0	2033.7	2229.6	2328.9	2290.7
42.5°	1081.5	1139.3	1221.7	1326.6	1455.3	1613.8	1801.1	1999.8	2164.1	2201.7	2069.5
45°	986.6	1046.4	1127.6	1233.6	1371.8	1543.7	1739.0	1919.5	2014.1	1946.4	1741.7
47.5°	898.5	954.4	1029.7	1139.1	1281.8	1459.5	1647.6	1791.7	1799.1	1637.4	1418.8
50°	838.3	889.9	965.8	1075.2	1216.9	1396.7	1566.5	1679.9	1628.9	1445.7	1235.6
52.5°	779.2	829.8	904.6	1013.0	1153.0	1317.8	1475.8	1555.4	1459.2	1271.2	1091.7
55°	694.0	738.3	811.4	911.5	1044.3	1197.4	1331.6	1359.1	1234.2	1049.0	903.4
57.5°	610.8	652.1	718.7	810.8	932.3	1067.8	1172.8	1166.9	1034.9	876.0	760.4
60°	554.4	594.7	653.8	743.6	854.4	971.2	1061.1	1039.7	908.8	771.9	674.5
62.5°	503.9	539.8	595.7	674.4	775.5	883.6	957.5	925.8	797.6	677.9	601.0
65°	429.6	459.8	507.4	574.5	658.4	747.7	804.7	763.8	654.4	561.1	499.4
67.5°	358.5	382.7	422.7	476.2	547.8	619.5	654.3	613.0	525.6	457.4	411.7
70°	313.4	334.9	365.8	413.5	475.9	536.2	562.4	525.6	450.4	391.9	359.0
72.5°	268.4	286.0	313.1	356.0	406.0	458.4	481.4	446.1	384.4	335.0	304.3
75°	207.4	219.5	238.2	267.8	307.4	349.0	361.8	330.9	291.3	254.3	234.3
77.5°	148.4	158.7	172.9	191.6	219.6	246.1	257.2	239.4	208.7	185.4	168.8
80°	114.1	119.5	131.6	147.0	169.1	185.9	193.3	181.9	160.4	142.9	130.2
82.5°	81.4	86.7	93.9	106.7	120.8	132.2	140.2	132.5	116.9	103.2	95.8
85°	39.6	43.0	47.0	52.3	63.1	69.8	69.1	64.4	58.4	53.0	49.0
87.5°	14.3	15.1	16.9	19.8	21.6	24.0	25.2	24.4	22.5	21.0	19.5
90°	1.8	2.9	4.0	5.2	6.2	7.2	8.3	9.2	10.2	10.9	11.6
92.5°	9.0	8.3	7.4	6.6	6.7	7.6	8.4	9.3	10.2	10.9	11.6
95°	35.9	35.5	35.1	34.7	31.8	26.3	21.0	15.6	10.2	10.9	11.6
97.5°	76.7	77.5	78.2	79.0	74.0	63.4	52.7	42.0	31.4	27.4	23.4
100°	106.9	107.4	107.8	108.2	108.7	109.3	109.9	110.5	111.0	89.9	68.8
102.5°	138.2	138.8	139.3	139.8	140.3	140.6	140.9	141.3	141.6	137.7	133.6
105°	188.1	188.7	189.2	189.9	190.1	190.1	190.1	190.1	190.1	190.1	190.1
107.5°	239.4	239.4	239.4	239.4	239.5	239.8	240.0	240.4	240.6	240.6	240.7
110°	273.0	273.0	273.0	273.0	273.2	273.5	273.8	274.1	274.3	273.9	273.5





TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	305.1	305.4	305.7	306.1	306.3	306.5	306.7	306.9	307.0	306.4	305.9
115°	352.8	353.6	354.3	355.0	355.4	355.6	355.7	355.9	356.0	355.4	354.8
117.5°	401.2	401.2	401.2	401.1	401.4	402.0	402.5	403.0	403.6	402.9	402.1
120°	431.8	431.6	431.4	431.4	431.4	431.9	432.3	432.7	433.2	432.9	432.7
122.5°	459.5	460.0	460.5	461.2	461.5	461.7	461.8	462.1	462.3	462.0	461.7
125°	501.8	502.8	503.8	504.8	505.2	505.2	505.2	505.2	505.2	504.7	504.1
127.5°	541.5	542.2	542.9	543.5	543.9	543.8	543.7	543.6	543.5	543.2	542.9
130°	565.9	566.6	567.4	568.1	568.5	568.6	568.8	568.9	569.0	568.6	568.3
132.5°	590.6	591.4	592.2	593.1	593.3	593.0	592.6	592.4	592.0	591.9	591.9
135°	625.4	626.3	627.2	628.0	628.3	628.0	627.7	627.4	627.2	626.8	626.5
137.5°	657.4	658.1	658.8	659.5	659.8	659.5	659.3	659.0	658.8	658.8	658.9
140°	677.8	678.1	678.4	678.6	678.7	678.6	678.5	678.3	678.1	678.5	678.7
142.5°	696.5	696.7	696.9	697.1	697.2	697.5	697.7	697.8	698.1	698.1	698.2
145°	724.4	724.7	725.0	725.2	725.4	725.4	725.4	725.4	725.4	725.5	725.7
147.5°	748.3	748.2	748.2	748.1	748.2	748.4	748.5	748.6	748.8	749.0	749.2
150°	763.4	763.1	762.8	762.5	762.5	762.8	763.1	763.4	763.6	764.0	764.2
152.5°	777.8	777.2	776.6	775.9	775.8	776.1	776.4	776.6	776.9	777.2	777.5
155°	796.6	795.7	794.9	794.1	793.8	794.1	794.4	794.6	794.9	795.3	795.7
157.5°	811.7	811.1	810.6	810.1	809.9	809.9	809.9	809.9	809.9	810.5	810.9
160°	821.5	820.6	819.8	819.0	818.6	818.7	818.9	819.0	819.2	819.8	820.3
162.5°	829.7	828.8	827.9	827.1	826.7	826.9	827.1	827.2	827.3	828.1	828.9
165°	840.6	839.8	839.0	838.1	837.8	837.8	838.0	838.2	838.3	839.1	840.0
167.5°	848.8	847.9	847.1	846.1	845.8	845.9	846.0	846.2	846.4	847.3	848.3
170°	853.3	852.2	851.3	850.2	849.8	850.0	850.2	850.2	850.4	851.5	852.6
172.5°	856.4	855.3	854.3	853.3	853.0	853.3	853.5	853.8	854.0	855.0	856.0
175°	859.8	858.9	858.1	857.2	856.9	857.0	857.1	857.3	857.5	858.6	859.7
177.5°	861.4	860.8	860.1	859.5	859.1	859.3	859.4	859.5	859.6	860.4	861.2
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3	1581.3
2.5°	1653.7	1658.0	1667.2	1664.0	1668.3	1670.4	1672.6
5°	1787.3	1808.8	1818.2	1816.9	1830.9	1827.6	1824.2
7.5°	1938.2	1960.8	1973.4	1989.1	1998.2	1998.9	2006.8
10°	2023.6	2053.1	2065.2	2082.0	2092.7	2098.8	2098.1
12.5°	2089.0	2112.2	2139.2	2147.5	2162.0	2169.6	2166.8
15°	2167.9	2204.8	2233.0	2247.0	2265.2	2270.5	2277.9
17.5°	2238.3	2287.8	2320.7	2364.4	2380.9	2391.0	2385.1
20°	2291.4	2356.5	2389.4	2441.7	2470.6	2486.1	2480.6
22.5°	2354.2	2424.7	2485.4	2530.8	2574.7	2595.6	2599.9
25°	2461.9	2558.5	2647.7	2707.5	2761.8	2774.6	2802.8
27.5°	2582.1	2696.0	2791.5	2854.4	2892.2	2906.4	2915.3
30°	2657.8	2771.2	2843.1	2883.3	2895.5	2894.1	2892.7
32.5°	2694.8	2765.9	2779.7	2768.5	2740.8	2717.4	2693.0
35°	2642.4	2589.4	2510.2	2408.1	2333.0	2257.1	2249.8
37.5°	2376.4	2206.9	2075.1	1927.9	1842.9	1790.4	1754.2
40°	2126.2	1933.6	1773.9	1649.8	1563.1	1529.0	1495.4
42.5°	1854.6	1670.5	1529.0	1425.3	1360.2	1322.2	1295.6
45°	1506.8	1344.4	1233.6	1158.5	1106.7	1077.2	1060.4
47.5°	1234.7	1114.6	1020.5	966.2	930.5	907.6	907.7
50°	1088.6	973.9	911.5	868.5	837.6	819.5	822.9
52.5°	959.2	873.5	820.2	784.2	761.4	750.2	749.8
55°	802.0	740.3	705.4	679.2	663.7	651.0	653.8
57.5°	686.0	634.0	610.6	588.9	578.2	573.1	565.7
60°	614.2	573.9	553.7	536.2	525.6	521.5	514.1
62.5°	550.3	518.6	498.9	484.7	475.0	473.7	468.0
65°	462.4	438.2	420.9	414.1	404.1	401.4	401.4
67.5°	381.3	363.9	350.3	344.1	339.8	340.4	337.2
70°	330.2	316.2	307.4	300.7	297.3	298.0	295.3
72.5°	288.9	273.2	265.5	261.5	257.1	258.8	257.7
75°	218.8	210.8	206.7	202.7	200.0	198.6	197.3
77.5°	160.7	153.6	150.5	148.2	148.6	145.3	147.9
80°	124.2	118.1	116.1	112.8	112.1	112.1	111.4
82.5°	90.8	87.5	86.0	83.3	82.1	83.1	81.4
85°	47.0	44.3	43.7	43.7	42.3	41.0	44.3
87.5°	19.6	17.7	17.7	17.3	17.4	17.0	15.9
90°	12.3	13.0	13.6	14.0	14.5	14.9	15.3
92.5°	12.3	13.0	13.5	13.7	13.9	14.1	14.3
95°	12.3	13.0	13.4	13.4	13.4	13.4	13.4
97.5°	19.4	15.4	13.4	13.4	13.4	13.4	13.4
100°	47.6	26.5	15.7	15.1	14.6	13.9	13.4
102.5°	129.7	125.6	118.8	109.2	99.5	89.9	80.2
105°	190.1	190.1	190.0	189.9	189.8	189.6	189.5
107.5°	240.7	240.7	240.6	240.1	239.7	239.3	238.8
110°	273.0	272.6	272.5	272.6	272.8	272.9	273.0



TEST NUMBER: P333466-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	305.4	304.8	304.4	304.3	304.1	303.8	303.7
115°	354.3	353.7	353.0	352.1	351.3	350.4	349.6
117.5°	401.4	400.6	400.1	399.7	399.3	399.0	398.6
120°	432.3	432.0	431.5	430.8	430.2	429.5	428.7
122.5°	461.4	461.2	460.5	459.8	458.9	458.1	457.3
125°	503.6	503.0	502.5	502.0	501.6	501.3	500.8
127.5°	542.6	542.3	541.7	540.5	539.5	538.5	537.4
130°	567.8	567.4	566.8	566.1	565.4	564.6	564.0
132.5°	591.8	591.7	591.3	590.6	589.9	589.2	588.5
135°	626.3	626.0	625.4	624.6	623.7	622.8	622.0
137.5°	658.9	659.0	658.7	657.9	657.2	656.4	655.7
140°	679.0	679.3	679.0	678.1	677.3	676.5	675.6
142.5°	698.3	698.3	697.9	697.1	696.2	695.3	694.5
145°	725.8	725.9	725.6	724.7	723.8	723.1	722.2
147.5°	749.3	749.5	749.1	748.1	747.1	746.1	745.0
150°	764.5	764.8	764.4	763.2	762.1	761.0	759.8
152.5°	777.7	778.1	777.7	776.6	775.7	774.6	773.6
155°	796.2	796.6	796.3	795.1	794.0	792.9	791.7
157.5°	811.3	811.8	811.4	810.3	809.2	808.0	806.9
160°	820.9	821.4	821.1	820.0	818.9	817.8	816.6
162.5°	829.7	830.5	830.3	829.1	827.8	826.6	825.3
165°	840.9	841.7	841.5	840.4	839.3	838.2	837.0
167.5°	849.4	850.4	850.3	849.0	847.7	846.4	845.2
170°	853.9	855.0	854.9	853.6	852.3	851.0	849.8
172.5°	857.0	858.1	857.9	856.7	855.4	854.1	852.8
175°	860.8	861.9	861.9	860.7	859.4	858.1	856.8
177.5°	861.9	862.8	862.7	861.8	860.9	860.0	859.1
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7

(END OF REPORT)