

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333470-935

Luminaire Tested: **S125DIW-S1270D770U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333470-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D770U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7059.9 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333470-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333470-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	96	92	88	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	72	85	79	73	69	69	65	61	61	57	54	53	50	48	44
3	83	74	66	60	78	69	63	57	61	56	52	54	49	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	39	42	38	35	32
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	29	25	22	19
9	52	39	32	26	49	37	30	25	33	28	23	30	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	28	23	19	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10959	10959	10959
5°	10983	10878	10949
10°	10916	10802	10864
15°	10797	10672	10717
20°	10628	10490	10509
25°	10446	10274	10264
30°	10221	10041	9991
35°	9980	9790	9653
40°	9732	9517	9382
45°	9465	9270	9085
50°	9171	8969	8699
55°	8888	8631	8389
60°	8548	8289	7994
65°	8145	7878	7610
70°	7757	7402	7149
75°	7069	6835	6598
80°	6289	6189	6044
85°	5476	5572	5269



TEST NUMBER: P333470-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.0	2.3
10°-20°	451.9	6.4
20°-30°	667.3	9.5
30°-40°	778.6	11.0
40°-50°	782.0	11.1
50°-60°	686.5	9.7
60°-70°	511.5	7.2
70°-80°	292.5	4.1
80°-90°	86.9	1.2
90°-100°	31.3	0.4
100°-110°	192.7	2.7
110°-120°	349.6	5.0
120°-130°	448.6	6.4
130°-140°	482.6	6.8
140°-150°	452.9	6.4
150°-160°	366.4	5.2
160°-170°	237.0	3.4
170°-180°	81.7	1.2
0°-30°	1279.2	18.1
0°-40°	2057.8	29.1
0°-60°	3526.3	49.9
0°-90°	4417.1	62.6
90°-120°	573.6	8.1
90°-150°	1957.7	27.7
90°-180°	2643.0	37.4
0°-180°	7059.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1697	1697	1697	1697	1697	
5°	1694	1691	1678	1689	1689	161
15°	1615	1610	1596	1602	1603	455
25°	1466	1459	1442	1444	1440	674
35°	1266	1260	1242	1235	1224	791
45°	1036	1030	1015	999	995	798
55°	789	784	766	755	745	704
65°	533	530	516	504	498	529
75°	283	280	274	270	264	302
85°	74	75	75	74	71	82
90°	1	6	10	13	15	5
95°	36	33	10	13	13	46
105°	188	190	190	190	190	199
115°	352	355	356	353	350	349
125°	501	505	505	503	501	447
135°	625	628	627	626	622	481
145°	724	725	725	726	722	453
155°	798	794	795	796	792	367
165°	842	838	838	842	837	238
175°	861	857	858	862	857	82
180°	861	861	861	861	861	



TEST NUMBER: P333470-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1701.1	1700.4	1699.7	1698.9	1698.2	1696.7	1694.3	1691.9	1689.5	1687.1	1689.5
5°	1694.1	1693.5	1692.9	1692.3	1691.7	1690.0	1687.0	1683.9	1681.0	1678.0	1680.7
7.5°	1678.5	1677.9	1677.3	1676.7	1676.1	1674.2	1670.9	1667.7	1664.4	1661.1	1663.7
10°	1664.6	1664.0	1663.4	1662.8	1662.2	1660.3	1657.0	1653.7	1650.4	1647.1	1649.5
12.5°	1647.4	1646.3	1645.3	1644.2	1643.1	1641.1	1638.0	1635.0	1631.9	1628.8	1630.8
15°	1614.9	1614.0	1613.1	1612.2	1611.4	1609.2	1605.9	1602.7	1599.4	1596.1	1597.6
17.5°	1577.6	1576.3	1574.9	1573.6	1572.4	1569.9	1566.6	1563.1	1559.8	1556.3	1558.2
20°	1546.4	1545.8	1545.2	1544.6	1544.0	1541.8	1537.9	1534.0	1530.2	1526.3	1528.4
22.5°	1515.3	1514.2	1513.1	1512.1	1511.0	1508.6	1505.0	1501.4	1497.7	1494.1	1495.5
25°	1465.9	1464.4	1462.9	1461.5	1459.9	1457.2	1453.4	1449.5	1445.6	1441.7	1442.3
27.5°	1408.2	1407.3	1406.4	1405.5	1404.6	1402.1	1398.2	1394.1	1390.2	1386.1	1386.3
30°	1370.6	1369.7	1368.8	1367.9	1367.0	1364.3	1359.9	1355.4	1350.9	1346.4	1345.8
32.5°	1329.8	1328.4	1327.1	1325.7	1324.3	1321.6	1317.6	1313.6	1309.6	1305.6	1304.6
35°	1265.8	1264.7	1263.5	1262.3	1261.1	1258.4	1254.2	1250.1	1245.9	1241.7	1240.3
37.5°	1199.5	1198.1	1196.6	1195.1	1193.6	1190.8	1187.0	1183.0	1179.1	1175.2	1172.9
40°	1154.4	1153.0	1151.5	1150.0	1148.5	1145.6	1141.5	1137.3	1133.2	1128.9	1126.3
42.5°	1106.1	1104.9	1103.6	1102.3	1101.1	1098.4	1094.2	1090.0	1085.9	1081.7	1079.3
45°	1036.3	1035.2	1034.0	1032.8	1031.6	1029.2	1025.6	1022.0	1018.5	1014.9	1011.2
47.5°	961.1	961.2	961.3	961.3	961.4	959.2	955.0	950.7	946.4	942.1	938.5
50°	912.8	912.0	911.0	910.2	909.2	907.0	903.4	899.8	896.3	892.7	888.8
52.5°	863.4	862.8	862.1	861.4	860.8	858.6	854.7	850.9	847.1	843.3	839.9
55°	789.4	788.4	787.6	786.6	785.7	783.3	779.0	774.9	770.7	766.5	763.8
57.5°	711.2	710.8	710.2	709.8	709.3	707.3	703.8	700.3	696.7	693.2	689.7
60°	661.8	660.6	659.4	658.2	657.0	654.8	651.5	648.2	645.0	641.7	638.7
62.5°	610.3	609.3	608.4	607.3	606.4	604.6	601.8	598.9	596.2	593.3	590.1
65°	533.0	532.4	531.8	531.2	530.5	528.6	525.3	522.0	518.8	515.5	512.8
67.5°	458.1	456.8	455.6	454.3	453.1	451.2	448.8	446.3	443.8	441.3	439.1
70°	410.8	409.3	407.8	406.3	404.8	402.7	400.0	397.4	394.7	392.0	390.2
72.5°	359.2	358.2	357.2	356.2	355.2	353.8	352.1	350.3	348.6	346.9	344.8
75°	283.3	282.7	282.1	281.5	280.9	279.8	278.4	276.8	275.3	273.9	272.9
77.5°	213.2	212.9	212.7	212.5	212.2	211.7	210.9	210.0	209.1	208.4	207.8
80°	169.1	169.1	169.1	169.1	169.1	168.8	168.2	167.6	167.0	166.4	166.2
82.5°	130.4	130.0	129.5	129.1	128.5	128.3	128.1	128.0	127.9	127.8	127.3
85°	73.9	74.1	74.4	74.7	75.0	75.2	75.2	75.2	75.2	75.2	74.9
87.5°	29.1	29.4	29.6	29.8	30.0	30.1	30.0	30.0	30.0	30.0	30.1
90°	0.6	1.8	2.9	4.0	5.2	6.2	7.2	8.3	9.2	10.2	10.9
92.5°	9.8	9.0	8.3	7.4	6.6	6.7	7.6	8.4	9.3	10.2	10.9
95°	36.3	35.9	35.5	35.1	34.7	31.8	26.3	21.0	15.6	10.2	10.9
97.5°	75.9	76.7	77.5	78.2	79.0	74.0	63.4	52.7	42.0	31.4	27.4
100°	106.5	106.9	107.4	107.8	108.2	108.7	109.3	109.9	110.5	111.0	89.9
102.5°	137.7	138.2	138.8	139.3	139.8	140.3	140.6	140.9	141.3	141.6	137.7
105°	187.5	188.1	188.7	189.2	189.9	190.1	190.1	190.1	190.1	190.1	190.1
107.5°	239.4	239.4	239.4	239.4	239.4	239.5	239.8	240.0	240.4	240.6	240.6
110°	273.0	273.0	273.0	273.0	273.0	273.2	273.5	273.8	274.1	274.3	273.9



TEST NUMBER: P333470-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	304.7	305.1	305.4	305.7	306.1	306.3	306.5	306.7	306.9	307.0	306.4
115°	352.1	352.8	353.6	354.3	355.0	355.4	355.6	355.7	355.9	356.0	355.4
117.5°	401.3	401.2	401.2	401.2	401.1	401.4	402.0	402.5	403.0	403.6	402.9
120°	431.9	431.8	431.6	431.4	431.4	431.4	431.9	432.3	432.7	433.2	432.9
122.5°	458.9	459.5	460.0	460.5	461.2	461.5	461.7	461.8	462.1	462.3	462.0
125°	500.8	501.8	502.8	503.8	504.8	505.2	505.2	505.2	505.2	505.2	504.7
127.5°	540.7	541.5	542.2	542.9	543.5	543.9	543.8	543.7	543.6	543.5	543.2
130°	565.2	565.9	566.6	567.4	568.1	568.5	568.6	568.8	568.9	569.0	568.6
132.5°	589.7	590.6	591.4	592.2	593.1	593.3	593.0	592.6	592.4	592.0	591.9
135°	624.6	625.4	626.3	627.2	628.0	628.3	628.0	627.7	627.4	627.2	626.8
137.5°	656.6	657.4	658.1	658.8	659.5	659.8	659.5	659.3	659.0	658.8	658.8
140°	677.5	677.8	678.1	678.4	678.6	678.7	678.6	678.5	678.3	678.1	678.5
142.5°	696.4	696.5	696.7	696.9	697.1	697.2	697.5	697.7	697.8	698.1	698.1
145°	724.1	724.4	724.7	725.0	725.2	725.4	725.4	725.4	725.4	725.4	725.5
147.5°	748.4	748.3	748.2	748.2	748.1	748.2	748.4	748.5	748.6	748.8	749.0
150°	763.6	763.4	763.1	762.8	762.5	762.5	762.8	763.1	763.4	763.6	764.0
152.5°	778.4	777.8	777.2	776.6	775.9	775.8	776.1	776.4	776.6	776.9	777.2
155°	797.5	796.6	795.7	794.9	794.1	793.8	794.1	794.4	794.6	794.9	795.3
157.5°	812.1	811.7	811.1	810.6	810.1	809.9	809.9	809.9	809.9	809.9	810.5
160°	822.3	821.5	820.6	819.8	819.0	818.6	818.7	818.9	819.0	819.2	819.8
162.5°	830.5	829.7	828.8	827.9	827.1	826.7	826.9	827.1	827.2	827.3	828.1
165°	841.5	840.6	839.8	839.0	838.1	837.8	837.8	838.0	838.2	838.3	839.1
167.5°	849.6	848.8	847.9	847.1	846.1	845.8	845.9	846.0	846.2	846.4	847.3
170°	854.3	853.3	852.2	851.3	850.2	849.8	850.0	850.2	850.2	850.4	851.5
172.5°	857.3	856.4	855.3	854.3	853.3	853.0	853.3	853.5	853.8	854.0	855.0
175°	860.7	859.8	858.9	858.1	857.2	856.9	857.0	857.1	857.3	857.5	858.6
177.5°	862.1	861.4	860.8	860.1	859.5	859.1	859.3	859.4	859.5	859.6	860.4
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7



TEST NUMBER: P333470-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8	1696.8
2.5°	1691.9	1694.3	1696.7	1697.7	1697.5	1697.3	1697.0	1696.8
5°	1683.3	1686.1	1688.8	1690.0	1689.6	1689.4	1689.0	1688.8
7.5°	1666.3	1669.0	1671.5	1672.8	1672.5	1672.1	1671.9	1671.5
10°	1651.9	1654.3	1656.7	1657.7	1657.4	1657.1	1656.8	1656.6
12.5°	1632.7	1634.6	1636.5	1637.4	1637.4	1637.3	1637.3	1637.2
15°	1599.1	1600.6	1602.1	1602.8	1602.8	1602.8	1602.8	1602.8
17.5°	1560.0	1561.9	1563.7	1563.9	1562.5	1561.0	1559.4	1558.0
20°	1530.5	1532.6	1534.6	1535.0	1533.4	1532.0	1530.5	1529.0
22.5°	1496.8	1498.2	1499.6	1499.8	1498.7	1497.7	1496.7	1495.7
25°	1442.9	1443.6	1444.2	1444.0	1443.1	1442.2	1441.3	1440.4
27.5°	1386.4	1386.6	1386.6	1386.2	1385.3	1384.5	1383.5	1382.7
30°	1345.2	1344.6	1344.0	1343.3	1342.4	1341.5	1340.6	1339.7
32.5°	1303.5	1302.4	1301.3	1299.9	1298.4	1296.8	1295.1	1293.6
35°	1238.7	1237.3	1235.8	1233.8	1231.4	1229.1	1226.7	1224.3
37.5°	1170.7	1168.5	1166.3	1164.5	1163.1	1161.7	1160.4	1159.0
40°	1123.6	1120.9	1118.2	1116.5	1115.5	1114.7	1113.7	1112.8
42.5°	1076.9	1074.4	1071.9	1070.1	1068.7	1067.3	1065.9	1064.5
45°	1007.7	1004.1	1000.6	998.3	997.4	996.5	995.6	994.7
47.5°	934.8	931.2	927.6	924.7	922.6	920.5	918.4	916.4
50°	884.9	881.1	877.2	874.2	872.1	870.0	868.0	865.8
52.5°	836.5	833.1	829.7	826.8	824.5	822.2	819.8	817.5
55°	761.1	758.5	755.8	753.4	751.3	749.2	747.1	745.0
57.5°	686.3	682.9	679.4	677.1	676.0	674.9	673.6	672.5
60°	635.7	632.7	629.7	627.2	625.1	623.0	621.0	618.9
62.5°	586.9	583.7	580.5	578.1	576.4	574.8	573.2	571.6
65°	510.1	507.4	504.7	502.8	501.6	500.4	499.2	498.0
67.5°	436.9	434.5	432.3	430.8	430.1	429.4	428.7	427.9
70°	388.4	386.6	384.8	383.3	382.1	380.9	379.8	378.6
72.5°	342.9	340.8	338.8	337.2	336.0	334.8	333.6	332.3
75°	272.1	271.1	270.3	269.2	268.0	266.8	265.6	264.4
77.5°	207.2	206.7	206.2	205.5	204.7	203.8	203.0	202.2
80°	165.8	165.6	165.2	164.8	164.2	163.6	163.0	162.5
82.5°	126.7	126.2	125.6	125.4	125.2	125.1	124.9	124.8
85°	74.6	74.3	74.0	73.5	72.9	72.3	71.7	71.1
87.5°	30.2	30.4	30.6	30.4	30.0	29.6	29.2	28.8
90°	11.6	12.3	13.0	13.6	14.0	14.5	14.9	15.3
92.5°	11.6	12.3	13.0	13.5	13.7	13.9	14.1	14.3
95°	11.6	12.3	13.0	13.4	13.4	13.4	13.4	13.4
97.5°	23.4	19.4	15.4	13.4	13.4	13.4	13.4	13.4
100°	68.8	47.6	26.5	15.7	15.1	14.6	13.9	13.4
102.5°	133.6	129.7	125.6	118.8	109.2	99.5	89.9	80.2
105°	190.1	190.1	190.1	190.0	189.9	189.8	189.6	189.5
107.5°	240.7	240.7	240.7	240.6	240.1	239.7	239.3	238.8
110°	273.5	273.0	272.6	272.5	272.6	272.8	272.9	273.0



TEST NUMBER: P333470-935

CATALOG NUMBER: S125DIW-S1270D770U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	305.9	305.4	304.8	304.4	304.3	304.1	303.8	303.7
115°	354.8	354.3	353.7	353.0	352.1	351.3	350.4	349.6
117.5°	402.1	401.4	400.6	400.1	399.7	399.3	399.0	398.6
120°	432.7	432.3	432.0	431.5	430.8	430.2	429.5	428.7
122.5°	461.7	461.4	461.2	460.5	459.8	458.9	458.1	457.3
125°	504.1	503.6	503.0	502.5	502.0	501.6	501.3	500.8
127.5°	542.9	542.6	542.3	541.7	540.5	539.5	538.5	537.4
130°	568.3	567.8	567.4	566.8	566.1	565.4	564.6	564.0
132.5°	591.9	591.8	591.7	591.3	590.6	589.9	589.2	588.5
135°	626.5	626.3	626.0	625.4	624.6	623.7	622.8	622.0
137.5°	658.9	658.9	659.0	658.7	657.9	657.2	656.4	655.7
140°	678.7	679.0	679.3	679.0	678.1	677.3	676.5	675.6
142.5°	698.2	698.3	698.3	697.9	697.1	696.2	695.3	694.5
145°	725.7	725.8	725.9	725.6	724.7	723.8	723.1	722.2
147.5°	749.2	749.3	749.5	749.1	748.1	747.1	746.1	745.0
150°	764.2	764.5	764.8	764.4	763.2	762.1	761.0	759.8
152.5°	777.5	777.7	778.1	777.7	776.6	775.7	774.6	773.6
155°	795.7	796.2	796.6	796.3	795.1	794.0	792.9	791.7
157.5°	810.9	811.3	811.8	811.4	810.3	809.2	808.0	806.9
160°	820.3	820.9	821.4	821.1	820.0	818.9	817.8	816.6
162.5°	828.9	829.7	830.5	830.3	829.1	827.8	826.6	825.3
165°	840.0	840.9	841.7	841.5	840.4	839.3	838.2	837.0
167.5°	848.3	849.4	850.4	850.3	849.0	847.7	846.4	845.2
170°	852.6	853.9	855.0	854.9	853.6	852.3	851.0	849.8
172.5°	856.0	857.0	858.1	857.9	856.7	855.4	854.1	852.8
175°	859.7	860.8	861.9	861.9	860.7	859.4	858.1	856.8
177.5°	861.2	861.9	862.8	862.7	861.8	860.9	860.0	859.1
180°	860.7	860.7	860.7	860.7	860.7	860.7	860.7	860.7

(END OF REPORT)