

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333715-830

Luminaire Tested: **S125RDIW-S1090D1340U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333715-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D1340U830-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8367.4 lumens  
Efficiency: N/A  
Efficacy: 119.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333715-830

CATALOG NUMBER: S125RDIW-S1090D1340U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333715-830

CATALOG NUMBER: S125RDIW-S1090D1340U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	82	76	71	82	75	70	66	63	60	56	53	50	47	42	41	39
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	22
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333715-830

CATALOG NUMBER: S125RDIW-S1090D1340U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.4	1.9
10°-20°	442.7	5.3
20°-30°	642.0	7.7
30°-40°	731.6	8.7
40°-50°	713.2	8.5
50°-60°	600.3	7.2
60°-70°	420.8	5.0
70°-80°	216.3	2.6
80°-90°	58.1	0.7
90°-100°	105.2	1.3
100°-110°	310.7	3.7
110°-120°	526.3	6.3
120°-130°	692.7	8.3
130°-140°	776.1	9.3
140°-150°	760.7	9.1
150°-160°	638.9	7.6
160°-170°	424.7	5.1
170°-180°	148.6	1.8
0°-30°	1243.1	14.9
0°-40°	1974.7	23.6
0°-60°	3288.2	39.3
0°-90°	3983.4	47.6
90°-120°	942.3	11.3
90°-150°	3171.8	37.9
90°-180°	4384.0	52.4
0°-180°	8367.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	1	11	20	26	29	8
95°	80	82	94	102	105	85
105°	279	285	292	299	303	298
115°	527	532	534	533	532	521
125°	769	776	778	775	774	688
135°	1000	1007	1009	1008	1004	771
145°	1212	1216	1220	1220	1216	757
155°	1386	1387	1388	1392	1386	638
165°	1508	1505	1506	1510	1504	425
175°	1567	1563	1562	1569	1561	149
180°	1571	1571	1571	1571	1571	



TEST NUMBER: P333715-830

CATALOG NUMBER: S125RDIW-S1090D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.7	22.5	21.4	20.2	19.0	18.6	18.8	18.9	19.0	19.2	19.4
90°	1.2	3.4	5.6	7.7	9.9	12.0	13.9	15.7	17.6	19.6	20.9
92.5°	29.6	31.1	32.6	34.1	35.6	37.6	40.0	42.3	44.6	46.9	48.7
95°	79.5	80.0	80.6	81.1	81.6	83.3	86.0	88.7	91.4	94.2	96.0
97.5°	132.1	132.2	132.5	132.7	132.9	134.9	138.6	142.4	146.2	149.9	151.7
100°	171.2	171.2	171.2	171.2	171.2	173.0	176.4	180.0	183.5	187.1	189.5
102.5°	213.2	214.3	215.4	216.5	217.5	219.0	220.8	222.6	224.4	226.2	228.8
105°	278.8	280.1	281.4	282.9	284.2	285.7	287.3	289.0	290.6	292.2	293.9
107.5°	351.1	352.5	353.8	355.2	356.6	357.9	359.1	360.3	361.7	362.9	363.7
110°	401.1	402.4	403.8	405.1	406.4	407.6	408.4	409.2	410.0	410.8	411.6



TEST NUMBER: P333715-830

CATALOG NUMBER: S125RDIW-S1090D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	451.9	452.6	453.3	454.0	454.7	455.6	456.6	457.6	458.6	459.7	460.1
115°	527.0	528.0	529.1	530.2	531.3	532.2	532.6	533.2	533.8	534.3	534.0
117.5°	602.3	602.8	603.2	603.7	604.3	604.7	605.2	605.7	606.1	606.7	606.9
120°	649.2	650.5	652.0	653.3	654.7	655.4	655.7	656.0	656.3	656.6	656.6
122.5°	700.1	700.6	701.1	701.5	702.0	702.7	703.3	704.1	704.7	705.5	705.2
125°	769.0	770.6	772.3	773.9	775.5	776.5	776.7	777.0	777.3	777.6	777.0
127.5°	842.4	843.3	844.2	845.2	846.1	846.7	847.1	847.3	847.7	848.0	847.7
130°	886.4	887.8	889.1	890.5	891.8	892.8	893.3	893.9	894.4	894.9	894.7
132.5°	930.4	932.6	934.9	937.1	939.3	940.4	940.3	940.2	940.1	940.0	939.7
135°	1000.1	1001.7	1003.3	1005.0	1006.6	1007.6	1007.9	1008.1	1008.4	1008.7	1008.7
137.5°	1065.6	1067.2	1068.8	1070.4	1072.0	1073.0	1073.7	1074.2	1074.9	1075.4	1075.7
140°	1107.7	1109.1	1110.4	1111.8	1113.1	1114.2	1115.0	1115.9	1116.6	1117.5	1118.0
142.5°	1149.8	1150.9	1152.1	1153.2	1154.3	1155.4	1156.4	1157.4	1158.5	1159.5	1159.9
145°	1211.6	1212.7	1213.8	1214.8	1216.0	1216.9	1217.8	1218.5	1219.4	1220.2	1220.2
147.5°	1268.9	1269.4	1270.1	1270.6	1271.2	1271.9	1272.5	1273.2	1273.8	1274.5	1275.2
150°	1307.0	1306.7	1306.5	1306.2	1305.9	1306.3	1307.4	1308.5	1309.6	1310.7	1310.7
152.5°	1338.3	1338.7	1339.1	1339.4	1339.8	1340.2	1340.7	1341.0	1341.5	1342.0	1342.7
155°	1386.5	1386.5	1386.5	1386.5	1386.5	1386.6	1386.9	1387.1	1387.4	1387.7	1388.7
157.5°	1429.5	1428.9	1428.3	1427.7	1427.1	1426.9	1427.2	1427.5	1427.8	1428.0	1429.1
160°	1454.9	1454.2	1453.3	1452.5	1451.7	1451.4	1451.7	1452.0	1452.2	1452.5	1453.6
162.5°	1477.4	1476.9	1476.2	1475.6	1475.1	1474.8	1474.8	1474.9	1474.9	1475.0	1476.3
165°	1507.5	1506.9	1506.4	1505.9	1505.3	1505.2	1505.4	1505.7	1506.0	1506.3	1507.4
167.5°	1533.0	1531.8	1530.8	1529.7	1528.6	1528.0	1528.0	1528.0	1528.0	1528.0	1529.7
170°	1546.6	1545.6	1544.5	1543.4	1542.3	1541.7	1541.7	1541.7	1541.7	1541.7	1543.4
172.5°	1556.4	1555.3	1554.3	1553.1	1552.1	1551.5	1551.5	1551.5	1551.5	1551.5	1553.1
175°	1567.4	1566.3	1565.3	1564.1	1563.1	1562.5	1562.5	1562.5	1562.5	1562.5	1564.1
177.5°	1573.0	1572.2	1571.3	1570.5	1569.5	1569.1	1568.8	1568.6	1568.4	1568.1	1569.4
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1



TEST NUMBER: P333715-830

CATALOG NUMBER: S125RDIW-S1090D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	19.7	20.0	20.3	20.4	20.3	20.3	20.2	20.1
90°	22.2	23.7	25.0	26.1	26.9	27.7	28.6	29.3
92.5°	50.5	52.3	54.1	55.3	55.9	56.6	57.1	57.7
95°	97.9	99.8	101.8	102.9	103.5	104.1	104.6	105.2
97.5°	153.4	155.2	157.0	158.2	158.4	158.8	159.1	159.5
100°	192.0	194.4	196.8	198.3	198.9	199.4	200.0	200.5
102.5°	231.5	234.1	236.9	238.6	239.3	240.1	240.8	241.6
105°	295.5	297.1	298.7	299.9	300.8	301.6	302.4	303.2
107.5°	364.5	365.3	366.2	366.6	366.5	366.4	366.4	366.3
110°	412.5	413.2	414.1	414.3	414.1	413.8	413.5	413.2





TEST NUMBER: P333715-830

CATALOG NUMBER: S125RDIW-S1090D1340U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	460.4	460.8	461.2	461.2	460.7	460.2	459.7	459.2
115°	533.8	533.5	533.2	532.9	532.6	532.3	532.2	531.9
117.5°	607.1	607.3	607.6	607.1	606.1	604.9	603.9	602.8
120°	656.6	656.6	656.6	656.0	654.9	653.8	652.7	651.7
122.5°	705.0	704.8	704.6	704.1	703.1	702.3	701.4	700.6
125°	776.5	776.0	775.4	775.1	774.8	774.5	774.2	773.9
127.5°	847.4	847.2	847.0	846.5	846.0	845.5	844.9	844.3
130°	894.4	894.2	893.9	893.4	893.0	892.4	891.8	891.3
132.5°	939.4	939.1	938.9	938.4	937.6	936.8	936.0	935.3
135°	1008.7	1008.7	1008.7	1008.1	1007.0	1006.0	1004.8	1003.8
137.5°	1076.1	1076.4	1076.8	1076.2	1074.9	1073.5	1072.1	1070.8
140°	1118.6	1119.1	1119.6	1119.3	1117.9	1116.5	1115.2	1113.8
142.5°	1160.2	1160.6	1160.8	1160.4	1159.0	1157.6	1156.2	1154.9
145°	1220.2	1220.2	1220.2	1219.7	1219.0	1218.1	1217.3	1216.5
147.5°	1275.7	1276.4	1277.1	1276.5	1274.6	1272.8	1270.9	1269.1
150°	1310.7	1310.7	1310.7	1310.4	1309.9	1309.3	1308.7	1308.2
152.5°	1343.2	1343.9	1344.5	1344.4	1343.4	1342.5	1341.4	1340.5
155°	1389.9	1390.9	1392.0	1391.9	1390.5	1389.2	1387.8	1386.5
157.5°	1430.2	1431.3	1432.4	1432.0	1430.2	1428.4	1426.6	1424.8
160°	1454.6	1455.8	1456.8	1456.7	1455.4	1454.0	1452.6	1451.2
162.5°	1477.6	1478.8	1480.2	1480.1	1478.5	1476.9	1475.4	1473.8
165°	1508.4	1509.6	1510.6	1510.3	1508.7	1507.1	1505.4	1503.8
167.5°	1531.3	1533.0	1534.6	1534.6	1532.9	1531.2	1529.5	1527.8
170°	1545.0	1546.6	1548.2	1548.1	1546.2	1544.4	1542.4	1540.5
172.5°	1554.8	1556.4	1558.0	1558.0	1556.3	1554.6	1552.9	1551.2
175°	1565.8	1567.4	1569.1	1568.9	1567.0	1565.1	1563.2	1561.3
177.5°	1570.7	1572.1	1573.4	1573.3	1571.7	1570.2	1568.7	1567.2
180°	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1	1571.1

(END OF REPORT)