

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333718-830

Luminaire Tested: **S125RDIW-S1090D1560U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333718-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D1560U830-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9861.6 lumens  
Efficiency: N/A  
Efficacy: 128.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333718-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333718-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40
1	96	92	88	84	87	84	80	78	69	66	64	55	53	52	42	41	40	34
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	36	34	29
3	80	71	63	58	72	65	58	53	53	49	45	43	40	37	33	31	29	25
4	73	63	55	49	66	57	51	45	47	42	39	38	35	32	30	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	22	20	16
7	57	45	37	32	52	41	35	30	35	29	26	28	24	21	22	19	17	15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	20	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333718-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.4	1.6
10°-20°	442.7	4.5
20°-30°	642.0	6.5
30°-40°	731.6	7.4
40°-50°	713.2	7.2
50°-60°	600.3	6.1
60°-70°	420.8	4.3
70°-80°	216.3	2.2
80°-90°	58.6	0.6
90°-100°	69.6	0.7
100°-110°	428.7	4.3
110°-120°	777.5	7.9
120°-130°	997.8	10.1
130°-140°	1073.2	10.9
140°-150°	1007.4	10.2
150°-160°	814.9	8.3
160°-170°	527.0	5.3
170°-180°	181.8	1.8
0°-30°	1243.1	12.6
0°-40°	1974.7	20.0
0°-60°	3288.2	33.3
0°-90°	3983.9	40.4
90°-120°	1275.7	12.9
90°-150°	4354.1	44.2
90°-180°	5878.0	59.6
0°-180°	9861.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	1	13	23	30	34	7
95°	81	74	23	29	30	103
105°	417	422	423	423	421	442
115°	783	790	792	786	778	776
125°	1114	1123	1124	1118	1114	994
135°	1389	1397	1395	1392	1383	1070
145°	1610	1613	1613	1614	1606	1007
155°	1774	1766	1768	1771	1761	817
165°	1872	1864	1864	1872	1862	528
175°	1914	1906	1907	1917	1906	182
180°	1914	1914	1914	1914	1914	



TEST NUMBER: P333718-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.7	22.6	21.6	20.5	19.4	18.9	19.1	19.4	19.6	19.8	20.2
90°	1.4	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3
92.5°	21.9	20.1	18.3	16.6	14.8	14.9	16.9	18.8	20.7	22.7	24.3
95°	80.9	79.9	79.0	78.0	77.1	70.6	58.6	46.7	34.7	22.7	24.3
97.5°	168.8	170.5	172.2	174.0	175.7	164.7	140.9	117.3	93.5	69.8	60.9
100°	237.0	237.9	238.8	239.8	240.7	241.9	243.1	244.4	245.6	246.9	199.9
102.5°	306.2	307.4	308.6	309.8	310.9	312.0	312.7	313.5	314.2	315.0	306.1
105°	417.2	418.4	419.7	420.9	422.2	422.8	422.8	422.8	422.8	422.8	422.8
107.5°	532.3	532.3	532.3	532.3	532.3	532.6	533.3	534.0	534.6	535.2	535.3
110°	607.3	607.3	607.3	607.3	607.3	607.6	608.2	608.9	609.4	610.1	609.2



TEST NUMBER: P333718-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	677.7	678.4	679.2	680.0	680.7	681.3	681.6	682.0	682.4	682.8	681.6
115°	783.3	784.8	786.4	788.0	789.5	790.4	790.8	791.1	791.5	791.7	790.4
117.5°	892.5	892.4	892.3	892.3	892.2	892.8	894.0	895.1	896.4	897.6	895.9
120°	960.5	960.3	960.0	959.6	959.3	959.6	960.5	961.5	962.4	963.4	962.8
122.5°	1020.8	1021.9	1023.1	1024.4	1025.5	1026.3	1026.8	1027.2	1027.7	1028.1	1027.5
125°	1113.8	1116.0	1118.2	1120.4	1122.7	1123.7	1123.7	1123.7	1123.7	1123.7	1122.5
127.5°	1202.6	1204.2	1205.8	1207.4	1208.9	1209.7	1209.5	1209.3	1209.1	1208.9	1208.2
130°	1257.1	1258.7	1260.3	1261.9	1263.4	1264.3	1264.7	1265.0	1265.3	1265.6	1264.7
132.5°	1311.5	1313.4	1315.2	1317.1	1318.9	1319.5	1318.8	1318.1	1317.4	1316.7	1316.5
135°	1389.0	1390.9	1392.9	1394.8	1396.7	1397.2	1396.7	1396.0	1395.3	1394.8	1394.1
137.5°	1460.3	1461.9	1463.6	1465.2	1466.9	1467.4	1466.8	1466.2	1465.7	1465.1	1465.3
140°	1506.8	1507.5	1508.1	1508.7	1509.4	1509.5	1509.2	1508.9	1508.5	1508.3	1508.9
142.5°	1548.8	1549.2	1549.5	1549.9	1550.3	1550.8	1551.2	1551.6	1552.1	1552.6	1552.7
145°	1610.4	1611.0	1611.7	1612.3	1613.0	1613.3	1613.3	1613.3	1613.3	1613.3	1613.5
147.5°	1664.3	1664.2	1664.1	1664.0	1663.8	1664.0	1664.3	1664.7	1665.1	1665.5	1665.8
150°	1698.4	1697.7	1697.1	1696.5	1695.8	1695.8	1696.5	1697.1	1697.7	1698.4	1699.0
152.5°	1731.3	1729.9	1728.5	1727.1	1725.7	1725.3	1726.0	1726.6	1727.3	1727.9	1728.5
155°	1773.6	1771.7	1769.8	1767.9	1766.0	1765.4	1766.0	1766.6	1767.3	1767.9	1768.9
157.5°	1806.2	1805.1	1803.9	1802.8	1801.7	1801.1	1801.2	1801.3	1801.3	1801.4	1802.4
160°	1828.9	1827.0	1825.1	1823.3	1821.4	1820.5	1820.9	1821.2	1821.5	1821.8	1823.1
162.5°	1847.1	1845.2	1843.3	1841.4	1839.5	1838.7	1839.0	1839.4	1839.7	1839.9	1841.7
165°	1871.5	1869.6	1867.6	1865.8	1863.9	1863.1	1863.4	1863.8	1864.1	1864.3	1866.2
167.5°	1889.6	1887.7	1885.7	1883.8	1881.8	1881.0	1881.3	1881.6	1882.0	1882.3	1884.5
170°	1899.9	1897.6	1895.5	1893.2	1891.0	1890.1	1890.4	1890.7	1891.0	1891.3	1893.9
172.5°	1906.7	1904.5	1902.2	1900.1	1897.8	1897.1	1897.6	1898.2	1898.8	1899.3	1901.6
175°	1914.0	1912.1	1910.3	1908.4	1906.5	1905.7	1906.0	1906.3	1906.7	1907.0	1909.5
177.5°	1917.4	1915.9	1914.4	1912.9	1911.4	1910.7	1911.0	1911.3	1911.5	1911.8	1913.5
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0



TEST NUMBER: P333718-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	20.5	20.7	21.1	21.2	21.2	21.1	21.1	21.0
90°	25.8	27.4	29.0	30.3	31.2	32.1	33.1	34.0
92.5°	25.8	27.4	29.0	30.0	30.4	30.9	31.4	31.8
95°	25.8	27.4	29.0	29.8	29.8	29.8	29.8	29.8
97.5°	52.0	43.2	34.2	29.8	29.8	29.8	29.8	29.8
100°	152.9	105.9	59.0	34.9	33.6	32.3	31.1	29.8
102.5°	297.2	288.3	279.5	264.3	242.8	221.4	199.9	178.5
105°	422.8	422.8	422.8	422.6	422.4	422.1	421.7	421.4
107.5°	535.4	535.4	535.5	535.0	534.0	533.1	532.2	531.2
110°	608.2	607.3	606.3	606.1	606.3	606.6	607.0	607.3





TEST NUMBER: P333718-830

CATALOG NUMBER: S125RDIW-S1090D1560U830-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	680.3	679.2	678.0	677.1	676.7	676.3	675.8	675.3
115°	789.2	788.0	786.6	785.1	783.3	781.3	779.4	777.5
117.5°	894.3	892.7	891.0	889.8	889.0	888.2	887.3	886.5
120°	962.1	961.5	960.9	959.8	958.2	956.6	955.1	953.5
122.5°	1026.8	1026.2	1025.6	1024.4	1022.6	1020.7	1018.9	1017.0
125°	1121.2	1119.9	1118.7	1117.6	1116.6	1115.7	1114.7	1113.8
127.5°	1207.5	1206.8	1206.1	1204.6	1202.2	1200.0	1197.6	1195.2
130°	1263.8	1262.8	1261.9	1260.6	1259.0	1257.4	1255.8	1254.2
132.5°	1316.4	1316.2	1316.0	1315.0	1313.5	1311.9	1310.3	1308.7
135°	1393.5	1392.9	1392.2	1390.9	1389.0	1387.1	1385.3	1383.4
137.5°	1465.4	1465.5	1465.7	1464.9	1463.2	1461.6	1459.9	1458.3
140°	1509.5	1510.1	1510.8	1510.1	1508.3	1506.4	1504.5	1502.6
142.5°	1552.7	1552.9	1553.0	1552.2	1550.2	1548.3	1546.4	1544.5
145°	1613.9	1614.2	1614.5	1613.7	1611.8	1610.0	1608.1	1606.2
147.5°	1666.2	1666.6	1667.0	1666.0	1663.8	1661.5	1659.3	1657.0
150°	1699.6	1700.3	1700.9	1700.0	1697.4	1694.9	1692.4	1689.9
152.5°	1729.2	1729.8	1730.4	1729.6	1727.3	1725.0	1722.8	1720.5
155°	1769.8	1770.8	1771.7	1770.8	1768.4	1765.9	1763.3	1760.8
157.5°	1803.4	1804.4	1805.4	1804.7	1802.1	1799.6	1797.1	1794.6
160°	1824.3	1825.6	1826.8	1826.3	1823.7	1821.2	1818.6	1816.2
162.5°	1843.5	1845.3	1847.0	1846.5	1843.8	1841.0	1838.2	1835.4
165°	1868.1	1870.1	1872.0	1871.6	1869.2	1866.6	1864.1	1861.5
167.5°	1886.8	1889.0	1891.3	1891.0	1888.2	1885.4	1882.5	1879.7
170°	1896.4	1898.9	1901.4	1901.3	1898.5	1895.6	1892.7	1889.9
172.5°	1903.8	1906.1	1908.4	1908.1	1905.3	1902.4	1899.6	1896.8
175°	1911.9	1914.5	1917.0	1916.8	1914.0	1911.2	1908.4	1905.5
177.5°	1915.3	1917.0	1918.8	1918.7	1916.7	1914.7	1912.6	1910.6
180°	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0	1914.0

(END OF REPORT)