

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333703-830

Luminaire Tested: **S125RDIW-S1090D470U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333703-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D470U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5513.0 lumens
Efficiency: N/A
Efficacy: 119.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333703-830

CATALOG NUMBER: S125RDIW-S1090D470U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333703-830

CATALOG NUMBER: S125RDIW-S1090D470U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	99	95	91	98	94	90	87	85	82	79	76	74	72	68	67	65	62
2	94	87	80	75	89	82	77	72	74	70	66	67	64	61	60	58	55	52
3	86	76	69	63	81	73	66	61	66	61	56	60	55	52	54	50	48	44
4	79	68	60	54	75	65	57	52	59	53	48	53	49	45	48	44	41	38
5	73	61	52	46	69	58	51	45	53	47	42	48	43	39	44	39	36	33
6	67	55	46	41	64	52	45	39	48	42	37	44	38	34	40	35	32	29
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26
8	58	45	37	32	55	43	36	31	40	34	29	37	31	27	33	29	26	24
9	54	42	34	29	51	40	33	28	37	31	26	34	29	25	31	27	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10880	10880	10880
5°	10906	10781	10847
10°	10823	10681	10681
15°	10694	10465	10380
20°	10529	10162	10040
25°	10337	9865	9648
30°	10097	9517	9214
35°	9851	9159	8728
40°	9622	8786	8250
45°	9344	8368	7728
50°	9064	7913	7185
55°	8740	7479	6604
60°	8415	6952	5983
65°	8031	6339	5269
70°	7593	5574	4539
75°	6984	4699	3778
80°	6152	3689	3169
85°	5180	3016	2831



TEST NUMBER: P333703-830

CATALOG NUMBER: S125RDIW-S1090D470U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.4	2.9
10°-20°	442.7	8.0
20°-30°	642.0	11.6
30°-40°	731.6	13.3
40°-50°	713.2	12.9
50°-60°	600.3	10.9
60°-70°	420.8	7.6
70°-80°	216.3	3.9
80°-90°	55.8	1.0
90°-100°	36.8	0.7
100°-110°	108.6	2.0
110°-120°	183.9	3.3
120°-130°	242.0	4.4
130°-140°	271.2	4.9
140°-150°	265.8	4.8
150°-160°	223.2	4.0
160°-170°	148.4	2.7
170°-180°	51.9	0.9
0°-30°	1243.1	22.5
0°-40°	1974.7	35.8
0°-60°	3288.2	59.6
0°-90°	3981.1	72.2
90°-120°	329.3	6.0
90°-150°	1108.3	20.1
90°-180°	1532.0	27.8
0°-180°	5513.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1685	1685	1685	1685	1685	
5°	1682	1677	1663	1675	1673	159
15°	1599	1591	1565	1563	1552	451
25°	1451	1430	1384	1368	1354	667
35°	1250	1218	1162	1126	1107	782
45°	1023	984	916	867	846	789
55°	776	734	664	609	586	694
65°	526	481	415	366	345	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	0	4	7	9	10	5
95°	28	29	33	36	37	30
105°	97	100	102	105	106	104
115°	184	186	187	186	186	182
125°	269	271	272	271	270	241
135°	349	352	352	352	351	269
145°	423	425	426	426	425	265
155°	484	484	485	486	484	223
165°	527	526	526	528	526	149
175°	548	546	546	548	546	52
180°	549	549	549	549	549	



TEST NUMBER: P333703-830

CATALOG NUMBER: S125RDIW-S1090D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1687.7	1687.1	1686.4	1685.6	1685.0	1683.6	1681.3	1679.0	1676.8	1674.5	1676.8
5°	1682.2	1681.0	1679.9	1678.8	1677.6	1675.5	1672.4	1669.2	1666.1	1663.0	1665.8
7.5°	1665.6	1664.5	1663.4	1662.4	1661.2	1658.9	1655.1	1651.4	1647.7	1644.0	1646.0
10°	1650.3	1649.4	1648.6	1647.8	1646.9	1644.5	1640.6	1636.6	1632.7	1628.7	1629.6
12.5°	1633.0	1631.9	1630.9	1629.8	1628.7	1625.5	1620.2	1614.9	1609.6	1604.2	1604.9
15°	1599.4	1597.7	1596.0	1594.3	1592.6	1588.8	1582.9	1577.0	1571.0	1565.1	1564.8
17.5°	1561.5	1558.9	1556.3	1553.7	1551.0	1546.1	1538.6	1531.2	1523.6	1516.2	1514.8
20°	1532.0	1529.2	1526.4	1523.5	1520.7	1514.8	1505.7	1496.7	1487.6	1478.6	1477.2
22.5°	1499.4	1496.6	1493.7	1490.9	1488.1	1482.0	1472.4	1462.9	1453.4	1443.9	1441.1
25°	1450.6	1446.3	1442.1	1437.8	1433.6	1426.3	1415.8	1405.3	1394.9	1384.4	1380.7
27.5°	1394.6	1389.4	1384.2	1379.1	1373.9	1365.8	1354.6	1343.4	1332.2	1321.0	1315.9
30°	1353.9	1348.5	1343.1	1337.8	1332.4	1323.7	1311.8	1300.0	1288.1	1276.2	1269.7
32.5°	1314.1	1307.9	1301.6	1295.3	1289.0	1279.9	1267.7	1255.7	1243.5	1231.4	1224.3
35°	1249.5	1242.7	1236.0	1229.2	1222.4	1212.6	1199.9	1187.1	1174.4	1161.7	1153.5
37.5°	1186.1	1177.9	1169.6	1161.4	1153.1	1142.5	1129.3	1116.2	1103.1	1090.0	1080.1
40°	1141.3	1132.8	1124.4	1115.9	1107.4	1096.4	1082.8	1069.2	1055.6	1042.1	1031.3
42.5°	1094.5	1085.8	1077.1	1068.4	1059.7	1048.3	1034.3	1020.3	1006.3	992.2	981.9
45°	1023.0	1014.8	1006.6	998.4	990.2	978.4	962.8	947.3	931.7	916.2	904.8
47.5°	949.0	940.3	931.6	923.0	914.4	902.2	886.6	870.8	855.2	839.5	827.8
50°	902.1	892.8	883.4	874.1	864.8	852.1	835.9	819.8	803.7	787.6	775.7
52.5°	851.2	841.7	832.1	822.6	813.0	800.6	785.4	770.2	755.0	739.8	727.0
55°	776.2	767.1	758.1	749.0	740.0	727.5	711.7	695.9	680.0	664.2	651.5
57.5°	700.3	690.7	681.0	671.3	661.7	649.2	634.0	618.7	603.4	588.1	575.7
60°	651.5	641.6	631.7	621.8	611.9	599.3	584.0	568.7	553.5	538.2	525.8
62.5°	599.6	590.1	580.7	571.2	561.8	549.3	533.9	518.3	502.8	487.3	475.8
65°	525.5	515.9	506.2	496.6	487.0	474.8	459.8	444.8	429.8	414.8	403.5
67.5°	451.9	442.3	432.7	423.1	413.5	401.5	387.1	372.8	358.4	344.0	333.8
70°	402.1	392.5	382.9	373.2	363.6	351.8	337.6	323.5	309.3	295.2	286.4
72.5°	353.3	343.8	334.4	325.1	315.7	304.3	291.2	277.9	264.7	251.5	243.4
75°	279.9	271.5	263.0	254.5	246.0	235.8	223.9	212.1	200.2	188.3	182.1
77.5°	207.2	200.4	193.6	186.8	180.0	171.8	162.4	152.9	143.4	133.8	129.5
80°	165.4	158.6	151.8	145.1	138.3	130.9	123.0	115.1	107.2	99.2	96.7
82.5°	124.7	118.6	112.4	106.4	100.3	94.5	89.1	83.6	78.2	72.8	71.6
85°	69.9	64.8	59.8	54.7	49.6	46.4	45.0	43.5	42.1	40.7	40.4
87.5°	23.5	22.1	20.6	19.2	17.8	17.0	16.9	16.8	16.7	16.6	16.8
90°	0.5	1.2	2.0	2.7	3.5	4.1	4.8	5.5	6.1	6.9	7.4
92.5°	10.4	10.8	11.4	12.0	12.4	13.1	13.9	14.8	15.6	16.4	17.1
95°	27.8	28.0	28.2	28.4	28.6	29.1	30.1	31.0	32.0	32.9	33.6
97.5°	46.1	46.2	46.3	46.4	46.5	47.1	48.4	49.8	51.1	52.4	53.0
100°	59.9	59.9	59.9	59.9	59.9	60.4	61.6	62.9	64.1	65.3	66.3
102.5°	74.5	74.8	75.3	75.7	76.1	76.5	77.2	77.8	78.4	79.0	79.9
105°	97.4	97.8	98.3	98.8	99.3	99.8	100.4	100.9	101.5	102.1	102.6
107.5°	122.7	123.2	123.7	124.1	124.6	125.1	125.5	125.9	126.4	126.8	127.1
110°	140.2	140.6	141.1	141.6	142.0	142.4	142.7	143.0	143.3	143.5	143.8



TEST NUMBER: P333703-830

CATALOG NUMBER: S125RDIW-S1090D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	157.9	158.2	158.3	158.6	158.9	159.2	159.6	159.9	160.2	160.6	160.8
115°	184.1	184.5	184.9	185.3	185.7	186.0	186.2	186.3	186.5	186.7	186.6
117.5°	210.5	210.6	210.8	210.9	211.1	211.3	211.5	211.6	211.8	212.0	212.1
120°	226.9	227.3	227.8	228.3	228.8	229.0	229.1	229.2	229.3	229.4	229.4
122.5°	244.6	244.8	245.0	245.2	245.2	245.5	245.7	246.0	246.3	246.5	246.4
125°	268.7	269.3	269.8	270.4	271.0	271.4	271.5	271.5	271.6	271.7	271.5
127.5°	294.4	294.6	295.0	295.3	295.7	295.9	296.0	296.1	296.1	296.3	296.2
130°	309.7	310.2	310.7	311.1	311.6	312.0	312.2	312.4	312.5	312.7	312.6
132.5°	325.1	325.8	326.7	327.4	328.2	328.6	328.6	328.5	328.5	328.4	328.3
135°	349.4	350.1	350.6	351.2	351.8	352.0	352.1	352.2	352.3	352.4	352.4
137.5°	372.3	372.9	373.4	374.0	374.6	374.9	375.1	375.3	375.5	375.8	375.9
140°	387.0	387.5	388.0	388.4	388.9	389.4	389.6	389.9	390.2	390.5	390.7
142.5°	401.7	402.1	402.6	402.9	403.3	403.7	404.1	404.4	404.8	405.2	405.3
145°	423.4	423.8	424.1	424.5	424.9	425.2	425.5	425.7	426.0	426.3	426.3
147.5°	443.4	443.6	443.7	443.9	444.2	444.4	444.6	444.9	445.1	445.4	445.5
150°	456.7	456.6	456.5	456.4	456.3	456.5	456.9	457.2	457.6	458.0	458.0
152.5°	467.6	467.8	467.9	468.0	468.2	468.3	468.4	468.6	468.7	468.9	469.1
155°	484.5	484.5	484.5	484.5	484.5	484.5	484.6	484.7	484.7	484.8	485.2
157.5°	499.5	499.3	499.1	498.9	498.6	498.6	498.7	498.8	498.9	499.0	499.4
160°	508.4	508.1	507.7	507.5	507.2	507.1	507.2	507.3	507.4	507.5	507.9
162.5°	516.2	516.0	515.9	515.6	515.4	515.3	515.3	515.3	515.4	515.4	515.9
165°	526.7	526.5	526.3	526.1	525.9	525.9	526.0	526.1	526.2	526.3	526.7
167.5°	535.6	535.3	534.9	534.5	534.1	534.0	534.0	534.0	534.0	534.0	534.5
170°	540.4	540.0	539.6	539.2	538.9	538.7	538.7	538.7	538.7	538.7	539.2
172.5°	543.8	543.5	543.1	542.7	542.3	542.2	542.2	542.2	542.2	542.2	542.7
175°	547.7	547.2	546.9	546.5	546.1	545.9	545.9	545.9	545.9	545.9	546.5
177.5°	549.6	549.3	549.0	548.7	548.4	548.2	548.2	548.1	548.0	547.9	548.4
180°	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9



TEST NUMBER: P333703-830

CATALOG NUMBER: S125RDIW-S1090D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7	1684.7
2.5°	1679.0	1681.3	1683.6	1684.5	1684.3	1684.1	1683.9	1683.7
5°	1668.7	1671.5	1674.3	1675.5	1674.9	1674.3	1673.8	1673.2
7.5°	1647.9	1649.9	1651.9	1652.6	1651.9	1651.3	1650.7	1650.0
10°	1630.4	1631.3	1632.1	1632.1	1631.3	1630.4	1629.6	1628.7
12.5°	1605.5	1606.1	1606.8	1606.4	1605.1	1603.8	1602.5	1601.2
15°	1564.5	1564.2	1564.0	1562.5	1560.0	1557.5	1554.9	1552.4
17.5°	1513.3	1511.9	1510.5	1508.8	1506.7	1504.6	1502.5	1500.4
20°	1475.7	1474.3	1472.9	1470.9	1468.4	1465.8	1463.3	1460.8
22.5°	1438.4	1435.6	1432.9	1430.4	1428.3	1426.3	1424.1	1422.0
25°	1377.1	1373.4	1369.7	1366.3	1363.2	1360.1	1357.0	1353.9
27.5°	1310.7	1305.6	1300.4	1296.4	1293.4	1290.3	1287.3	1284.4
30°	1263.2	1256.7	1250.2	1245.7	1243.1	1240.6	1238.0	1235.5
32.5°	1217.1	1209.8	1202.7	1197.5	1194.3	1191.1	1187.8	1184.6
35°	1145.3	1137.1	1128.9	1122.9	1118.9	1114.9	1111.0	1107.0
37.5°	1070.3	1060.5	1050.6	1043.8	1039.9	1036.0	1032.2	1028.3
40°	1020.6	1009.8	999.1	992.0	988.6	985.2	981.8	978.5
42.5°	971.7	961.3	951.0	943.4	938.4	933.5	928.5	923.5
45°	893.5	882.2	870.9	863.1	858.8	854.6	850.4	846.1
47.5°	816.2	804.6	793.0	784.8	780.0	775.3	770.7	766.0
50°	763.8	752.0	740.1	732.1	727.8	723.6	719.3	715.1
52.5°	714.3	701.4	688.6	680.1	675.9	671.7	667.4	663.2
55°	638.8	626.0	613.3	604.6	600.1	595.6	591.1	586.5
57.5°	563.3	550.8	538.4	530.1	526.1	522.1	518.0	514.1
60°	513.3	500.9	488.4	480.1	475.9	471.6	467.4	463.2
62.5°	464.3	452.7	441.2	433.3	429.0	424.8	420.6	416.3
65°	392.2	380.9	369.6	361.7	357.5	353.3	349.0	344.8
67.5°	323.4	313.0	302.7	295.8	292.4	289.0	285.6	282.2
70°	277.7	268.9	260.1	254.0	250.6	247.2	243.8	240.4
72.5°	235.3	227.2	219.0	213.9	211.6	209.3	207.1	204.8
75°	175.9	169.7	163.4	159.3	157.3	155.3	153.4	151.4
77.5°	125.2	120.8	116.4	113.5	112.1	110.6	109.1	107.6
80°	94.2	91.6	89.1	87.5	86.9	86.3	85.8	85.2
82.5°	70.4	69.2	68.1	67.3	66.9	66.5	66.3	65.9
85°	40.2	39.9	39.6	39.3	39.0	38.7	38.5	38.2
87.5°	16.9	17.0	17.1	17.0	16.8	16.7	16.5	16.3
90°	7.8	8.3	8.8	9.1	9.4	9.7	10.0	10.3
92.5°	17.6	18.3	18.9	19.3	19.5	19.7	20.0	20.2
95°	34.2	34.9	35.5	36.0	36.2	36.4	36.6	36.8
97.5°	53.6	54.3	54.9	55.2	55.3	55.5	55.6	55.7
100°	67.1	68.0	68.8	69.3	69.5	69.7	69.8	70.0
102.5°	80.9	81.8	82.8	83.3	83.6	83.9	84.2	84.5
105°	103.2	103.8	104.3	104.8	105.1	105.4	105.7	105.9
107.5°	127.3	127.6	127.9	128.1	128.1	128.0	128.0	128.0
110°	144.1	144.4	144.7	144.8	144.7	144.6	144.5	144.4



TEST NUMBER: P333703-830

CATALOG NUMBER: S125RDIW-S1090D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	160.9	161.0	161.2	161.2	161.0	160.8	160.6	160.4
115°	186.5	186.4	186.3	186.2	186.2	186.1	186.0	185.9
117.5°	212.2	212.2	212.3	212.2	211.8	211.4	210.9	210.6
120°	229.4	229.4	229.4	229.2	228.8	228.5	228.1	227.7
122.5°	246.4	246.3	246.2	246.0	245.7	245.4	245.1	244.8
125°	271.4	271.2	271.0	270.8	270.7	270.6	270.5	270.4
127.5°	296.1	296.1	296.0	295.8	295.6	295.4	295.2	295.0
130°	312.5	312.5	312.4	312.2	312.0	311.8	311.6	311.4
132.5°	328.2	328.1	328.0	327.9	327.6	327.3	327.1	326.8
135°	352.4	352.4	352.4	352.2	351.9	351.5	351.1	350.7
137.5°	376.0	376.1	376.3	376.1	375.6	375.1	374.6	374.1
140°	390.9	391.1	391.2	391.1	390.6	390.1	389.6	389.2
142.5°	405.4	405.5	405.6	405.4	404.9	404.4	404.0	403.5
145°	426.3	426.3	426.3	426.2	425.9	425.7	425.4	425.1
147.5°	445.7	446.0	446.2	446.0	445.4	444.7	444.0	443.5
150°	458.0	458.0	458.0	457.9	457.7	457.5	457.3	457.1
152.5°	469.4	469.6	469.8	469.8	469.4	469.1	468.7	468.3
155°	485.6	486.0	486.4	486.4	485.9	485.4	484.9	484.5
157.5°	499.7	500.1	500.5	500.4	499.7	499.1	498.5	497.9
160°	508.3	508.7	509.1	509.0	508.5	508.0	507.6	507.1
162.5°	516.3	516.7	517.2	517.2	516.6	516.0	515.5	514.9
165°	527.1	527.4	527.8	527.7	527.2	526.6	526.0	525.5
167.5°	535.1	535.6	536.2	536.2	535.6	535.0	534.4	533.9
170°	539.8	540.4	541.0	540.9	540.3	539.6	538.9	538.3
172.5°	543.3	543.8	544.4	544.4	543.8	543.2	542.6	542.1
175°	547.1	547.7	548.3	548.2	547.5	546.9	546.2	545.5
177.5°	548.8	549.3	549.8	549.7	549.2	548.7	548.1	547.6
180°	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9

(END OF REPORT)