

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333389-935

Luminaire Tested: **S125DIW-S610D1340U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333389-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S610D1340U935-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6182.3 lumens  
Efficiency: N/A  
Efficacy: 114.9 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	90	87	83	85	82	79	76	66	64	62	51	50	49	38	37	36	30
2	86	79	73	68	78	72	67	63	58	54	51	45	43	41	33	32	31	25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22
4	72	62	54	48	65	56	49	44	45	41	37	36	32	30	27	24	23	19
5	66	55	47	41	59	50	43	38	41	36	32	32	28	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	31	28	29	25	22	22	19	17	14
7	56	44	36	31	51	40	34	29	33	28	24	26	23	20	20	17	15	13
8	52	40	33	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11
9	48	36	29	24	44	33	27	23	28	23	19	22	18	16	17	14	12	10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	16	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	4977	4977	4977	4977
5°	5763	4994	4372	4994
10°	6705	4968	3831	4968
15°	7422	4931	3534	4931
20°	8308	4874	3296	4874
25°	9733	4809	3180	4809
30°	10513	4744	3078	4744
35°	8643	4623	3012	4623
40°	6144	4457	2939	4457
45°	4720	4230	2898	4230
50°	4029	3950	2892	3950
55°	3587	3675	2917	3675
60°	3237	3375	2992	3375
65°	2989	3073	3069	3073
70°	2717	2761	3114	2761
75°	2400	2433	3084	2433
80°	2020	1982	2823	1982
85°	1601	1430	2275	1430



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	74.2	1.2
10°-20°	220.9	3.6
20°-30°	358.6	5.8
30°-40°	437.5	7.1
40°-50°	398.0	6.4
50°-60°	317.0	5.1
60°-70°	220.8	3.6
70°-80°	117.7	1.9
80°-90°	32.8	0.5
90°-100°	96.1	1.6
100°-110°	283.9	4.6
110°-120°	480.8	7.8
120°-130°	632.7	10.2
130°-140°	709.0	11.5
140°-150°	694.9	11.2
150°-160°	583.6	9.4
160°-170°	388.0	6.3
170°-180°	135.8	2.2
0°-30°	653.7	10.6
0°-40°	1091.2	17.7
0°-60°	1806.2	29.2
0°-90°	2177.6	35.2
90°-120°	860.8	13.9
90°-150°	2897.4	46.9
90°-180°	4005.0	64.8
0°-180°	6182.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	771	771	771	771	771	
5°	889	770	674	770	889	90
15°	1110	738	529	738	1110	318
25°	1366	675	446	675	1366	624
35°	1096	586	382	586	1096	671
45°	517	463	317	463	517	414
55°	319	326	259	326	319	287
65°	196	201	201	201	196	194
75°	96	98	124	98	96	104
85°	22	19	31	19	22	26
90°	27	1	27	1	27	16
95°	96	73	96	73	96	98
105°	277	255	277	255	277	293
115°	486	481	486	481	486	481
125°	707	702	707	702	707	631
135°	917	914	917	914	917	707
145°	1111	1107	1111	1107	1111	694
155°	1266	1266	1266	1266	1266	583
165°	1374	1377	1374	1377	1374	387
175°	1426	1432	1426	1432	1426	136
180°	1435	1435	1435	1435	1435	



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	815.1	814.0	813.0	810.9	812.4	808.0	805.9	802.3	797.8	796.3	794.4
5°	889.0	890.6	892.3	885.4	886.1	881.5	871.0	862.5	855.7	846.8	840.6
7.5°	977.9	974.0	973.8	969.3	961.7	955.5	944.5	930.5	917.0	901.6	888.8
10°	1022.4	1022.8	1019.9	1014.6	1006.4	1000.5	986.1	972.4	955.7	936.1	922.0
12.5°	1055.9	1057.3	1053.6	1046.5	1042.5	1029.3	1018.0	1001.7	981.9	966.2	944.8
15°	1110.1	1106.5	1103.9	1095.0	1088.1	1074.4	1056.4	1039.4	1017.9	997.9	977.9
17.5°	1162.3	1165.2	1160.3	1152.2	1130.9	1114.8	1090.7	1067.5	1040.5	1013.8	990.0
20°	1208.8	1211.5	1203.9	1189.9	1164.4	1148.3	1116.6	1086.5	1055.5	1021.1	995.0
22.5°	1267.0	1264.9	1254.7	1233.3	1211.3	1181.6	1147.3	1110.6	1071.7	1032.9	998.1
25°	1365.9	1352.1	1345.9	1319.4	1290.3	1246.8	1199.7	1146.1	1097.7	1046.3	1001.9
27.5°	1420.6	1416.3	1409.5	1390.9	1360.4	1313.9	1258.4	1193.0	1124.6	1059.9	1001.6
30°	1409.7	1410.3	1411.0	1405.1	1385.5	1350.5	1295.2	1224.9	1143.8	1070.8	1003.5
32.5°	1312.3	1324.2	1335.7	1349.1	1354.6	1347.9	1313.3	1249.7	1166.3	1083.4	1002.4
35°	1096.3	1099.9	1137.0	1173.5	1223.2	1261.9	1287.7	1259.6	1189.2	1094.1	1001.2
37.5°	854.8	872.5	898.1	939.5	1011.2	1075.5	1158.1	1196.1	1173.4	1097.5	998.8
40°	728.8	745.1	761.7	803.9	864.4	942.3	1036.1	1116.3	1135.0	1086.5	991.0
42.5°	631.4	644.4	662.9	694.6	745.1	814.1	903.8	1008.5	1072.9	1054.6	974.6
45°	516.8	525.0	539.3	564.6	601.2	655.1	734.3	848.8	948.5	981.5	935.4
47.5°	442.3	442.3	453.5	470.9	497.3	543.1	601.7	691.4	797.9	876.8	873.1
50°	401.0	399.3	408.2	423.3	444.2	474.6	530.5	602.2	704.6	793.8	818.6
52.5°	365.4	365.6	371.0	382.1	399.7	425.7	467.4	532.0	619.5	711.1	757.9
55°	318.6	317.3	323.5	331.0	343.8	360.8	390.9	440.2	511.2	601.5	662.3
57.5°	275.7	279.2	281.7	287.0	297.6	308.9	334.3	370.6	426.9	504.4	568.7
60°	250.6	254.2	256.1	261.3	269.8	279.7	299.3	328.7	376.2	442.9	506.6
62.5°	228.0	230.8	231.5	236.2	243.1	252.7	268.1	292.8	330.4	388.7	451.2
65°	195.6	195.6	196.9	201.8	205.1	213.6	225.3	243.3	273.5	318.9	372.2
67.5°	164.3	165.9	165.6	167.7	170.7	177.4	185.8	200.6	222.9	256.1	298.8
70°	143.9	145.3	144.9	146.5	149.8	154.0	160.9	175.0	191.0	219.5	256.1
72.5°	125.6	126.1	125.3	127.4	129.4	133.1	140.8	148.3	163.2	187.3	217.4
75°	96.2	96.8	97.5	98.8	100.7	102.7	106.6	114.2	124.0	142.0	161.3
77.5°	72.1	70.9	72.4	72.2	73.4	74.8	78.3	82.3	90.3	101.7	116.7
80°	54.3	54.6	54.6	54.9	56.6	57.6	60.5	63.5	69.7	78.2	88.6
82.5°	39.6	40.5	40.0	40.6	41.9	42.6	44.3	46.7	50.3	57.0	64.6
85°	21.6	20.0	20.6	21.3	21.3	21.6	22.9	23.8	25.8	28.4	31.4
87.5°	11.6	12.1	12.1	12.0	12.1	11.9	12.7	12.5	13.0	13.5	14.2
90°	26.8	26.1	25.3	24.5	23.8	22.8	21.6	20.3	19.1	17.9	16.1
92.5°	52.7	52.2	51.7	51.1	50.5	49.4	47.8	46.1	44.5	42.9	40.7
95°	96.1	95.6	95.1	94.5	94.0	93.0	91.2	89.5	87.7	86.0	83.5
97.5°	145.7	145.3	145.1	144.7	144.5	143.4	141.8	140.2	138.5	136.9	133.5
100°	183.1	182.7	182.2	181.7	181.2	179.8	177.5	175.4	173.1	170.9	167.6
102.5°	220.7	220.0	219.3	218.6	217.9	216.4	213.9	211.5	209.1	206.6	205.0
105°	277.0	276.2	275.5	274.7	274.0	272.9	271.4	269.9	268.5	266.9	265.4
107.5°	334.6	334.7	334.7	334.8	334.8	334.5	333.7	332.9	332.3	331.5	330.4
110°	377.5	377.7	378.0	378.2	378.5	378.2	377.5	376.8	376.0	375.2	374.5



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	419.5	419.9	420.4	420.9	421.3	421.3	420.9	420.6	420.3	419.9	419.0
115°	485.9	486.1	486.3	486.6	486.8	487.1	487.3	487.6	487.8	488.1	487.6
117.5°	550.6	551.6	552.6	553.6	554.6	555.0	554.7	554.6	554.4	554.2	553.7
120°	595.3	596.2	597.3	598.2	599.3	599.8	599.8	599.8	599.8	599.8	599.5
122.5°	640.0	640.8	641.5	642.3	643.2	643.6	643.9	644.0	644.2	644.5	643.8
125°	707.0	707.2	707.5	707.7	708.0	708.3	708.9	709.3	709.8	710.3	710.1
127.5°	771.3	771.8	772.3	772.8	773.3	773.7	773.9	774.1	774.4	774.6	774.4
130°	814.2	814.7	815.2	815.7	816.1	816.6	816.8	817.0	817.3	817.5	817.0
132.5°	854.4	855.1	855.7	856.5	857.2	857.6	857.9	858.2	858.4	858.7	858.8
135°	917.0	917.9	918.9	919.9	920.9	921.4	921.4	921.4	921.4	921.4	921.2
137.5°	978.2	979.4	980.6	981.9	983.1	983.6	983.3	983.0	982.7	982.4	981.9
140°	1017.4	1018.7	1019.9	1021.1	1022.4	1022.8	1022.3	1021.8	1021.3	1020.8	1020.0
142.5°	1055.0	1056.2	1057.5	1058.7	1060.0	1060.4	1060.1	1059.8	1059.5	1059.2	1058.3
145°	1111.3	1112.0	1112.8	1113.5	1114.2	1114.7	1114.7	1114.7	1114.7	1114.7	1113.9
147.5°	1159.3	1161.0	1162.7	1164.3	1166.1	1166.6	1166.0	1165.4	1164.8	1164.2	1163.6
150°	1195.1	1195.5	1196.0	1196.5	1197.0	1197.3	1197.3	1197.3	1197.3	1197.3	1196.3
152.5°	1224.5	1225.4	1226.3	1227.2	1228.1	1228.2	1227.6	1227.0	1226.5	1225.9	1225.5
155°	1266.5	1267.7	1269.0	1270.2	1271.4	1271.6	1270.6	1269.6	1268.6	1267.7	1267.4
157.5°	1301.6	1303.2	1304.8	1306.5	1308.1	1308.5	1307.4	1306.5	1305.4	1304.5	1304.2
160°	1325.7	1327.0	1328.2	1329.5	1330.7	1330.8	1329.8	1328.8	1327.8	1326.8	1326.5
162.5°	1346.3	1347.7	1349.1	1350.6	1352.0	1352.1	1350.9	1349.8	1348.6	1347.4	1347.3
165°	1373.7	1375.2	1376.7	1378.2	1379.7	1379.9	1379.0	1377.9	1377.0	1376.0	1375.7
167.5°	1395.6	1397.1	1398.7	1400.2	1401.8	1401.8	1400.3	1398.9	1397.3	1395.9	1395.9
170°	1407.2	1408.9	1410.7	1412.5	1414.2	1414.3	1412.8	1411.4	1409.9	1408.3	1408.3
172.5°	1417.0	1418.6	1420.1	1421.7	1423.2	1423.2	1421.8	1420.3	1418.8	1417.3	1417.3
175°	1426.2	1428.0	1429.7	1431.4	1433.1	1433.3	1431.8	1430.3	1428.8	1427.4	1427.4
177.5°	1431.6	1433.0	1434.3	1435.7	1437.2	1437.3	1436.1	1434.9	1433.7	1432.4	1432.7
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	792.8	791.0	788.9	785.2	780.8	778.4	774.8	772.4	767.7	763.8	759.6
5°	833.0	824.6	816.7	806.6	795.5	788.2	779.7	770.3	760.4	750.3	739.2
7.5°	874.7	859.7	843.3	825.7	808.6	792.7	777.6	762.8	748.9	732.1	717.9
10°	902.8	883.7	863.5	839.6	816.4	796.1	775.5	757.5	739.2	719.5	702.2
12.5°	930.7	905.4	876.8	850.6	822.7	798.2	774.0	751.0	728.0	706.2	686.0
15°	950.5	928.2	901.7	864.4	833.0	799.4	767.3	737.5	709.7	685.5	660.0
17.5°	963.5	934.9	906.4	870.6	829.5	791.8	755.4	721.4	690.1	659.4	634.8
20°	965.9	936.4	906.6	871.7	829.5	786.3	750.0	709.1	675.4	643.7	613.5
22.5°	965.1	931.7	899.3	863.2	822.2	782.4	738.5	696.8	660.2	629.0	597.6
25°	957.7	922.0	881.5	845.2	804.6	762.4	717.9	674.8	637.5	601.8	570.8
27.5°	951.5	905.3	859.4	817.0	777.8	739.2	696.6	652.4	611.1	574.9	545.6
30°	943.9	893.2	841.5	797.4	757.2	719.5	679.3	636.2	593.0	557.7	526.2
32.5°	937.1	878.0	823.5	775.4	732.9	696.3	659.2	618.1	575.8	539.8	508.5
35°	924.0	855.7	793.2	738.8	693.4	655.8	624.7	586.4	547.5	512.8	482.8
37.5°	907.3	826.2	759.1	702.2	652.4	612.8	583.8	554.5	517.1	483.7	456.5
40°	894.2	805.3	734.3	676.1	624.4	583.2	556.4	528.6	497.5	466.4	437.6
42.5°	877.7	786.4	709.1	646.5	595.4	555.2	527.0	503.4	476.0	447.0	420.3
45°	847.5	752.3	668.6	601.2	549.5	509.9	480.8	463.1	442.6	415.1	392.5
47.5°	802.9	711.3	624.7	555.1	501.8	465.1	437.8	420.9	406.4	386.0	365.5
50°	763.4	680.6	593.0	524.0	470.6	433.7	408.5	393.1	380.7	365.0	347.7
52.5°	719.2	642.1	561.9	493.6	440.8	404.4	379.7	366.2	355.9	344.6	327.5
55°	648.9	583.5	508.9	444.2	395.5	359.8	338.2	326.4	317.9	309.4	298.9
57.5°	571.5	520.4	454.3	395.1	350.3	317.8	297.6	286.2	279.6	275.2	269.1
60°	517.1	473.3	416.4	362.4	318.6	289.8	270.2	261.3	255.8	252.2	247.6
62.5°	466.6	430.6	377.9	328.6	290.3	263.1	245.6	237.0	231.7	230.0	226.1
65°	392.2	364.4	320.9	280.0	247.3	224.0	209.3	201.1	197.9	195.9	196.2
67.5°	318.8	301.9	267.0	232.1	206.0	186.5	174.7	168.4	166.8	164.2	164.1
70°	274.1	261.3	231.9	201.5	178.2	163.2	152.7	146.2	144.6	143.3	142.9
72.5°	234.5	223.4	197.9	173.5	152.7	139.4	130.8	126.8	124.2	123.4	123.3
75°	176.3	170.0	149.8	130.5	116.1	106.9	101.1	97.5	95.5	95.1	95.5
77.5°	125.4	119.9	107.0	93.3	84.3	77.3	72.3	71.1	68.9	69.0	68.6
80°	94.2	90.6	82.4	71.6	64.1	58.2	55.6	53.3	52.7	51.7	52.7
82.5°	68.3	64.4	58.9	52.0	45.8	42.3	39.6	38.9	38.5	38.1	38.2
85°	33.7	34.0	30.7	25.5	22.9	20.9	19.3	19.3	18.9	18.7	18.9
87.5°	14.4	13.5	12.1	10.9	9.3	8.1	7.4	7.3	6.9	7.1	7.7
90°	14.4	12.7	10.9	9.0	7.1	5.1	3.1	1.1	3.1	5.1	7.1
92.5°	38.7	36.5	34.4	32.5	31.2	29.8	28.4	27.0	28.4	29.8	31.2
95°	81.0	78.5	76.1	74.6	74.0	73.6	73.1	72.6	73.1	73.6	74.0
97.5°	130.1	126.7	123.2	121.4	121.2	121.1	120.8	120.6	120.8	121.1	121.2
100°	164.5	161.2	158.0	156.4	156.4	156.4	156.4	156.4	156.4	156.4	156.4
102.5°	203.4	201.7	200.1	198.7	197.8	196.7	195.8	194.8	195.8	196.7	197.8
105°	264.0	262.4	261.0	259.6	258.4	257.1	255.9	254.7	255.9	257.1	258.4
107.5°	329.2	328.0	326.9	325.7	324.5	323.2	322.0	320.7	322.0	323.2	324.5
110°	373.8	373.1	372.3	371.3	370.1	368.9	367.6	366.4	367.6	368.9	370.1





TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	418.0	417.1	416.2	415.3	414.7	414.1	413.5	412.8	413.5	414.1	414.7
115°	487.1	486.6	486.1	485.3	484.3	483.4	482.3	481.4	482.3	483.4	484.3
117.5°	553.3	552.8	552.4	552.0	551.5	551.0	550.6	550.2	550.6	551.0	551.5
120°	599.3	599.0	598.7	598.1	596.8	595.6	594.3	593.1	594.3	595.6	596.8
122.5°	643.2	642.5	641.9	641.3	640.8	640.4	640.0	639.6	640.0	640.4	640.8
125°	709.8	709.6	709.3	708.4	707.0	705.5	704.0	702.5	704.0	705.5	707.0
127.5°	774.0	773.8	773.4	772.9	772.1	771.2	770.3	769.5	770.3	771.2	772.1
130°	816.6	816.1	815.5	814.7	813.5	812.2	811.0	809.7	811.0	812.2	813.5
132.5°	858.8	858.9	859.0	858.1	856.0	854.0	852.0	849.9	852.0	854.0	856.0
135°	920.9	920.7	920.4	919.5	918.1	916.5	915.1	913.6	915.1	916.5	918.1
137.5°	981.3	980.8	980.2	979.2	977.8	976.4	974.9	973.4	974.9	976.4	977.8
140°	1019.3	1018.6	1017.8	1016.8	1015.6	1014.3	1013.1	1011.8	1013.1	1014.3	1015.6
142.5°	1057.3	1056.4	1055.4	1054.5	1053.4	1052.4	1051.4	1050.3	1051.4	1052.4	1053.4
145°	1113.1	1112.4	1111.6	1110.8	1109.7	1108.8	1107.8	1106.8	1107.8	1108.8	1109.7
147.5°	1163.0	1162.4	1161.8	1161.2	1160.7	1160.2	1159.6	1159.1	1159.6	1160.2	1160.7
150°	1195.3	1194.3	1193.3	1192.9	1193.2	1193.4	1193.7	1193.9	1193.7	1193.4	1193.2
152.5°	1225.0	1224.7	1224.3	1223.9	1223.6	1223.2	1222.9	1222.5	1222.9	1223.2	1223.6
155°	1267.1	1266.9	1266.6	1266.5	1266.5	1266.5	1266.5	1266.5	1266.5	1266.5	1266.5
157.5°	1304.0	1303.7	1303.5	1303.6	1304.2	1304.8	1305.3	1305.8	1305.3	1304.8	1304.2
160°	1326.4	1326.1	1325.9	1326.1	1326.8	1327.6	1328.4	1329.0	1328.4	1327.6	1326.8
162.5°	1347.3	1347.2	1347.2	1347.5	1348.0	1348.5	1349.1	1349.6	1349.1	1348.5	1348.0
165°	1375.4	1375.2	1375.0	1375.1	1375.6	1376.1	1376.6	1377.1	1376.6	1376.1	1375.6
167.5°	1395.9	1395.9	1395.9	1396.4	1397.3	1398.4	1399.3	1400.3	1399.3	1398.4	1397.3
170°	1408.3	1408.3	1408.3	1408.9	1409.9	1410.8	1411.9	1412.8	1411.9	1410.8	1409.9
172.5°	1417.3	1417.3	1417.3	1417.8	1418.8	1419.8	1420.7	1421.8	1420.7	1419.8	1418.8
175°	1427.4	1427.4	1427.4	1427.9	1428.8	1429.9	1430.8	1431.8	1430.8	1429.9	1428.8
177.5°	1432.9	1433.0	1433.3	1433.7	1434.6	1435.4	1436.1	1436.9	1436.1	1435.4	1434.6
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	757.2	754.3	752.0	746.7	743.9	739.9	736.8	740.2	736.6	738.1	735.8
5°	733.7	724.4	717.9	708.4	700.3	692.8	687.2	686.2	683.5	682.3	678.4
7.5°	705.2	693.8	682.5	670.1	659.6	649.0	642.1	636.5	632.8	627.9	624.6
10°	688.5	673.1	660.0	645.0	631.9	620.4	611.3	606.7	602.4	596.2	594.0
12.5°	667.8	651.9	635.9	619.8	607.3	594.5	586.7	579.8	576.9	569.8	569.1
15°	643.0	619.1	603.5	587.1	569.7	559.3	552.8	545.3	542.0	537.1	533.5
17.5°	613.5	592.1	572.5	555.6	540.7	531.9	523.7	518.6	513.0	509.8	503.9
20°	592.0	571.7	552.1	534.1	522.6	512.6	506.0	501.1	495.2	493.5	487.7
22.5°	573.9	551.6	532.7	517.6	505.1	493.7	486.6	483.3	479.2	474.2	473.0
25°	544.6	521.3	505.3	490.3	479.1	468.7	463.8	459.5	455.6	452.0	450.7
27.5°	519.2	498.4	479.4	465.8	456.2	446.6	442.3	437.1	434.2	431.4	427.8
30°	501.4	480.2	463.5	450.4	439.9	431.4	426.8	423.3	420.6	418.0	416.0
32.5°	483.1	463.4	447.2	434.5	424.0	417.6	413.5	411.0	408.0	404.9	402.4
35°	458.9	437.3	421.6	410.4	402.3	397.4	392.8	390.5	387.3	387.3	384.6
37.5°	431.6	412.9	399.1	388.9	381.6	377.2	372.3	370.7	368.6	367.2	366.4
40°	415.3	398.0	385.0	374.8	367.0	363.3	359.5	356.8	355.5	353.9	353.3
42.5°	398.6	382.1	369.5	360.2	353.4	350.3	346.6	344.8	342.2	340.0	339.7
45°	373.2	357.1	345.7	338.2	332.3	328.7	326.4	322.5	321.2	318.6	318.2
47.5°	349.0	333.6	322.4	316.2	311.1	308.2	304.5	300.7	299.1	297.8	297.7
50°	331.0	316.9	306.4	300.6	295.7	291.4	287.8	285.2	284.2	284.2	284.9
52.5°	312.7	300.7	291.8	284.6	280.0	275.4	272.2	270.5	269.1	270.6	271.8
55°	285.9	273.8	267.3	260.4	255.8	250.6	248.9	248.2	247.3	249.9	251.2
57.5°	257.4	249.0	241.3	234.5	230.4	227.4	225.2	224.8	226.6	227.8	232.1
60°	239.4	229.6	222.7	217.5	212.6	210.6	210.0	209.3	210.6	214.2	219.8
62.5°	219.6	211.5	204.1	200.3	196.7	193.4	193.2	193.6	196.2	200.4	206.0
65°	190.4	183.5	178.6	174.0	171.1	169.1	169.8	171.1	174.0	179.6	185.8
67.5°	160.7	156.0	151.6	147.9	145.1	145.1	145.8	147.7	151.2	157.6	163.2
70°	141.6	136.4	132.8	131.1	128.9	127.6	129.5	132.8	135.7	141.6	146.5
72.5°	122.5	118.0	115.3	114.2	113.1	112.1	112.8	116.3	120.3	126.2	131.9
75°	94.2	92.6	90.6	89.3	88.3	88.9	89.6	92.9	96.2	102.4	108.9
77.5°	68.8	67.1	65.9	65.5	65.0	65.3	67.2	69.6	72.8	77.3	82.3
80°	52.0	51.3	50.7	50.4	50.4	50.7	53.3	54.9	57.9	62.2	66.0
82.5°	37.9	37.5	37.4	37.3	37.5	37.6	39.2	41.3	43.7	47.0	50.4
85°	20.0	19.3	20.3	20.6	20.0	20.9	21.6	22.9	23.8	25.5	27.1
87.5°	8.4	9.2	9.3	9.9	10.3	11.2	11.1	12.5	13.2	13.9	13.9
90°	9.0	10.9	12.7	14.4	16.1	17.9	19.1	20.3	21.6	22.8	23.8
92.5°	32.5	34.4	36.5	38.7	40.7	42.9	44.5	46.1	47.8	49.4	50.5
95°	74.6	76.1	78.5	81.0	83.5	86.0	87.7	89.5	91.2	93.0	94.0
97.5°	121.4	123.2	126.7	130.1	133.5	136.9	138.5	140.2	141.8	143.4	144.5
100°	156.4	158.0	161.2	164.5	167.6	170.9	173.1	175.4	177.5	179.8	181.2
102.5°	198.7	200.1	201.7	203.4	205.0	206.6	209.1	211.5	213.9	216.4	217.9
105°	259.6	261.0	262.4	264.0	265.4	266.9	268.5	269.9	271.4	272.9	274.0
107.5°	325.7	326.9	328.0	329.2	330.4	331.5	332.3	332.9	333.7	334.5	334.8
110°	371.3	372.3	373.1	373.8	374.5	375.2	376.0	376.8	377.5	378.2	378.5



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	415.3	416.2	417.1	418.0	419.0	419.9	420.3	420.6	420.9	421.3	421.3
115°	485.3	486.1	486.6	487.1	487.6	488.1	487.8	487.6	487.3	487.1	486.8
117.5°	552.0	552.4	552.8	553.3	553.7	554.2	554.4	554.6	554.7	555.0	554.6
120°	598.1	598.7	599.0	599.3	599.5	599.8	599.8	599.8	599.8	599.8	599.3
122.5°	641.3	641.9	642.5	643.2	643.8	644.5	644.2	644.0	643.9	643.6	643.2
125°	708.4	709.3	709.6	709.8	710.1	710.3	709.8	709.3	708.9	708.3	708.0
127.5°	772.9	773.4	773.8	774.0	774.4	774.6	774.4	774.1	773.9	773.7	773.3
130°	814.7	815.5	816.1	816.6	817.0	817.5	817.3	817.0	816.8	816.6	816.1
132.5°	858.1	859.0	858.9	858.8	858.8	858.7	858.4	858.2	857.9	857.6	857.2
135°	919.5	920.4	920.7	920.9	921.2	921.4	921.4	921.4	921.4	921.4	920.9
137.5°	979.2	980.2	980.8	981.3	981.9	982.4	982.7	983.0	983.3	983.6	983.1
140°	1016.8	1017.8	1018.6	1019.3	1020.0	1020.8	1021.3	1021.8	1022.3	1022.8	1022.4
142.5°	1054.5	1055.4	1056.4	1057.3	1058.3	1059.2	1059.5	1059.8	1060.1	1060.4	1060.0
145°	1110.8	1111.6	1112.4	1113.1	1113.9	1114.7	1114.7	1114.7	1114.7	1114.7	1114.2
147.5°	1161.2	1161.8	1162.4	1163.0	1163.6	1164.2	1164.8	1165.4	1166.0	1166.6	1166.1
150°	1192.9	1193.3	1194.3	1195.3	1196.3	1197.3	1197.3	1197.3	1197.3	1197.3	1197.0
152.5°	1223.9	1224.3	1224.7	1225.0	1225.5	1225.9	1226.5	1227.0	1227.6	1228.2	1228.1
155°	1266.5	1266.6	1266.9	1267.1	1267.4	1267.7	1268.6	1269.6	1270.6	1271.6	1271.4
157.5°	1303.6	1303.5	1303.7	1304.0	1304.2	1304.5	1305.4	1306.5	1307.4	1308.5	1308.1
160°	1326.1	1325.9	1326.1	1326.4	1326.5	1326.8	1327.8	1328.8	1329.8	1330.8	1330.7
162.5°	1347.5	1347.2	1347.2	1347.3	1347.3	1347.4	1348.6	1349.8	1350.9	1352.1	1352.0
165°	1375.1	1375.0	1375.2	1375.4	1375.7	1376.0	1377.0	1377.9	1379.0	1379.9	1379.7
167.5°	1396.4	1395.9	1395.9	1395.9	1395.9	1395.9	1397.3	1398.9	1400.3	1401.8	1401.8
170°	1408.9	1408.3	1408.3	1408.3	1408.3	1408.3	1409.9	1411.4	1412.8	1414.3	1414.2
172.5°	1417.8	1417.3	1417.3	1417.3	1417.3	1417.3	1418.8	1420.3	1421.8	1423.2	1423.2
175°	1427.9	1427.4	1427.4	1427.4	1427.4	1427.4	1428.8	1430.3	1431.8	1433.3	1433.1
177.5°	1433.7	1433.3	1433.0	1432.9	1432.7	1432.4	1433.7	1434.9	1436.1	1437.3	1437.2
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	734.2	736.1	734.5	736.6	734.5	736.1	734.2	735.8	738.1	736.6	740.2
5°	676.7	673.7	675.7	674.4	675.7	673.7	676.7	678.4	682.3	683.5	686.2
7.5°	623.6	620.8	617.6	616.0	617.6	620.8	623.6	624.6	627.9	632.8	636.5
10°	590.4	586.8	586.4	584.2	586.4	586.8	590.4	594.0	596.2	602.4	606.7
12.5°	566.0	562.7	559.0	558.0	559.0	562.7	566.0	569.1	569.8	576.9	579.8
15°	531.5	528.9	526.6	528.6	526.6	528.9	531.5	533.5	537.1	542.0	545.3
17.5°	502.7	500.6	500.2	497.8	500.2	500.6	502.7	503.9	509.8	513.0	518.6
20°	484.7	483.1	483.7	479.5	483.7	483.1	484.7	487.7	493.5	495.2	501.1
22.5°	470.4	467.1	466.7	465.9	466.7	467.1	470.4	473.0	474.2	479.2	483.3
25°	447.8	446.2	444.5	446.2	444.5	446.2	447.8	450.7	452.0	455.6	459.5
27.5°	428.1	426.1	425.7	425.9	425.7	426.1	428.1	427.8	431.4	434.2	437.1
30°	416.0	412.8	413.1	412.8	413.1	412.8	416.0	416.0	418.0	420.6	423.3
32.5°	402.9	400.7	400.3	399.7	400.3	400.7	402.9	402.4	404.9	408.0	411.0
35°	383.7	383.7	382.0	382.0	382.0	383.7	383.7	384.6	387.3	387.3	390.5
37.5°	365.5	365.2	364.2	364.4	364.2	365.2	365.5	366.4	367.2	368.6	370.7
40°	351.9	351.6	350.6	348.6	350.6	351.6	351.9	353.3	353.9	355.5	356.8
42.5°	338.9	337.8	337.3	336.7	337.3	337.8	338.9	339.7	340.0	342.2	344.8
45°	318.2	318.2	317.6	317.3	317.6	318.2	318.2	318.2	318.6	321.2	322.5
47.5°	298.3	298.9	300.1	299.9	300.1	298.9	298.3	297.7	297.8	299.1	300.7
50°	286.2	286.5	287.5	287.8	287.5	286.5	286.2	284.9	284.2	284.2	285.2
52.5°	272.9	274.7	276.0	275.8	276.0	274.7	272.9	271.8	270.6	269.1	270.5
55°	254.2	256.4	258.7	259.1	258.7	256.4	254.2	251.2	249.9	247.3	248.2
57.5°	235.7	238.8	241.3	242.0	241.3	238.8	235.7	232.1	227.8	226.6	224.8
60°	223.1	227.3	230.2	231.6	230.2	227.3	223.1	219.8	214.2	210.6	209.3
62.5°	211.0	215.8	218.8	219.0	218.8	215.8	211.0	206.0	200.4	196.2	193.6
65°	191.3	196.2	198.9	200.8	198.9	196.2	191.3	185.8	179.6	174.0	171.1
67.5°	170.1	175.0	178.0	179.5	178.0	175.0	170.1	163.2	157.6	151.2	147.7
70°	154.7	159.6	163.5	164.9	163.5	159.6	154.7	146.5	141.6	135.7	132.8
72.5°	139.6	143.9	147.1	148.6	147.1	143.9	139.6	131.9	126.2	120.3	116.3
75°	113.1	119.1	122.0	123.6	122.0	119.1	113.1	108.9	102.4	96.2	92.9
77.5°	87.3	92.6	94.4	95.2	94.4	92.6	87.3	82.3	77.3	72.8	69.6
80°	70.0	73.3	75.6	75.9	75.6	73.3	70.0	66.0	62.2	57.9	54.9
82.5°	53.8	56.5	57.3	58.1	57.3	56.5	53.8	50.4	47.0	43.7	41.3
85°	29.4	30.7	31.1	30.7	31.1	30.7	29.4	27.1	25.5	23.8	22.9
87.5°	14.6	14.5	14.6	15.3	14.6	14.5	14.6	13.9	13.9	13.2	12.5
90°	24.5	25.3	26.1	26.8	26.1	25.3	24.5	23.8	22.8	21.6	20.3
92.5°	51.1	51.7	52.2	52.7	52.2	51.7	51.1	50.5	49.4	47.8	46.1
95°	94.5	95.1	95.6	96.1	95.6	95.1	94.5	94.0	93.0	91.2	89.5
97.5°	144.7	145.1	145.3	145.7	145.3	145.1	144.7	144.5	143.4	141.8	140.2
100°	181.7	182.2	182.7	183.1	182.7	182.2	181.7	181.2	179.8	177.5	175.4
102.5°	218.6	219.3	220.0	220.7	220.0	219.3	218.6	217.9	216.4	213.9	211.5
105°	274.7	275.5	276.2	277.0	276.2	275.5	274.7	274.0	272.9	271.4	269.9
107.5°	334.8	334.7	334.7	334.6	334.7	334.7	334.8	334.8	334.5	333.7	332.9
110°	378.2	378.0	377.7	377.5	377.7	378.0	378.2	378.5	378.2	377.5	376.8



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	420.9	420.4	419.9	419.5	419.9	420.4	420.9	421.3	421.3	420.9	420.6
115°	486.6	486.3	486.1	485.9	486.1	486.3	486.6	486.8	487.1	487.3	487.6
117.5°	553.6	552.6	551.6	550.6	551.6	552.6	553.6	554.6	555.0	554.7	554.6
120°	598.2	597.3	596.2	595.3	596.2	597.3	598.2	599.3	599.8	599.8	599.8
122.5°	642.3	641.5	640.8	640.0	640.8	641.5	642.3	643.2	643.6	643.9	644.0
125°	707.7	707.5	707.2	707.0	707.2	707.5	707.7	708.0	708.3	708.9	709.3
127.5°	772.8	772.3	771.8	771.3	771.8	772.3	772.8	773.3	773.7	773.9	774.1
130°	815.7	815.2	814.7	814.2	814.7	815.2	815.7	816.1	816.6	816.8	817.0
132.5°	856.5	855.7	855.1	854.4	855.1	855.7	856.5	857.2	857.6	857.9	858.2
135°	919.9	918.9	917.9	917.0	917.9	918.9	919.9	920.9	921.4	921.4	921.4
137.5°	981.9	980.6	979.4	978.2	979.4	980.6	981.9	983.1	983.6	983.3	983.0
140°	1021.1	1019.9	1018.7	1017.4	1018.7	1019.9	1021.1	1022.4	1022.8	1022.3	1021.8
142.5°	1058.7	1057.5	1056.2	1055.0	1056.2	1057.5	1058.7	1060.0	1060.4	1060.1	1059.8
145°	1113.5	1112.8	1112.0	1111.3	1112.0	1112.8	1113.5	1114.2	1114.7	1114.7	1114.7
147.5°	1164.3	1162.7	1161.0	1159.3	1161.0	1162.7	1164.3	1166.1	1166.6	1166.0	1165.4
150°	1196.5	1196.0	1195.5	1195.1	1195.5	1196.0	1196.5	1197.0	1197.3	1197.3	1197.3
152.5°	1227.2	1226.3	1225.4	1224.5	1225.4	1226.3	1227.2	1228.1	1228.2	1227.6	1227.0
155°	1270.2	1269.0	1267.7	1266.5	1267.7	1269.0	1270.2	1271.4	1271.6	1270.6	1269.6
157.5°	1306.5	1304.8	1303.2	1301.6	1303.2	1304.8	1306.5	1308.1	1308.5	1307.4	1306.5
160°	1329.5	1328.2	1327.0	1325.7	1327.0	1328.2	1329.5	1330.7	1330.8	1329.8	1328.8
162.5°	1350.6	1349.1	1347.7	1346.3	1347.7	1349.1	1350.6	1352.0	1352.1	1350.9	1349.8
165°	1378.2	1376.7	1375.2	1373.7	1375.2	1376.7	1378.2	1379.7	1379.9	1379.0	1377.9
167.5°	1400.2	1398.7	1397.1	1395.6	1397.1	1398.7	1400.2	1401.8	1401.8	1400.3	1398.9
170°	1412.5	1410.7	1408.9	1407.2	1408.9	1410.7	1412.5	1414.2	1414.3	1412.8	1411.4
172.5°	1421.7	1420.1	1418.6	1417.0	1418.6	1420.1	1421.7	1423.2	1423.2	1421.8	1420.3
175°	1431.4	1429.7	1428.0	1426.2	1428.0	1429.7	1431.4	1433.1	1433.3	1431.8	1430.3
177.5°	1435.7	1434.3	1433.0	1431.6	1433.0	1434.3	1435.7	1437.2	1437.3	1436.1	1434.9
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	736.8	739.9	743.9	746.7	752.0	754.3	757.2	759.6	763.8	767.7	772.4
5°	687.2	692.8	700.3	708.4	717.9	724.4	733.7	739.2	750.3	760.4	770.3
7.5°	642.1	649.0	659.6	670.1	682.5	693.8	705.2	717.9	732.1	748.9	762.8
10°	611.3	620.4	631.9	645.0	660.0	673.1	688.5	702.2	719.5	739.2	757.5
12.5°	586.7	594.5	607.3	619.8	635.9	651.9	667.8	686.0	706.2	728.0	751.0
15°	552.8	559.3	569.7	587.1	603.5	619.1	643.0	660.0	685.5	709.7	737.5
17.5°	523.7	531.9	540.7	555.6	572.5	592.1	613.5	634.8	659.4	690.1	721.4
20°	506.0	512.6	522.6	534.1	552.1	571.7	592.0	613.5	643.7	675.4	709.1
22.5°	486.6	493.7	505.1	517.6	532.7	551.6	573.9	597.6	629.0	660.2	696.8
25°	463.8	468.7	479.1	490.3	505.3	521.3	544.6	570.8	601.8	637.5	674.8
27.5°	442.3	446.6	456.2	465.8	479.4	498.4	519.2	545.6	574.9	611.1	652.4
30°	426.8	431.4	439.9	450.4	463.5	480.2	501.4	526.2	557.7	593.0	636.2
32.5°	413.5	417.6	424.0	434.5	447.2	463.4	483.1	508.5	539.8	575.8	618.1
35°	392.8	397.4	402.3	410.4	421.6	437.3	458.9	482.8	512.8	547.5	586.4
37.5°	372.3	377.2	381.6	388.9	399.1	412.9	431.6	456.5	483.7	517.1	554.5
40°	359.5	363.3	367.0	374.8	385.0	398.0	415.3	437.6	466.4	497.5	528.6
42.5°	346.6	350.3	353.4	360.2	369.5	382.1	398.6	420.3	447.0	476.0	503.4
45°	326.4	328.7	332.3	338.2	345.7	357.1	373.2	392.5	415.1	442.6	463.1
47.5°	304.5	308.2	311.1	316.2	322.4	333.6	349.0	365.5	386.0	406.4	420.9
50°	287.8	291.4	295.7	300.6	306.4	316.9	331.0	347.7	365.0	380.7	393.1
52.5°	272.2	275.4	280.0	284.6	291.8	300.7	312.7	327.5	344.6	355.9	366.2
55°	248.9	250.6	255.8	260.4	267.3	273.8	285.9	298.9	309.4	317.9	326.4
57.5°	225.2	227.4	230.4	234.5	241.3	249.0	257.4	269.1	275.2	279.6	286.2
60°	210.0	210.6	212.6	217.5	222.7	229.6	239.4	247.6	252.2	255.8	261.3
62.5°	193.2	193.4	196.7	200.3	204.1	211.5	219.6	226.1	230.0	231.7	237.0
65°	169.8	169.1	171.1	174.0	178.6	183.5	190.4	196.2	195.9	197.9	201.1
67.5°	145.8	145.1	145.1	147.9	151.6	156.0	160.7	164.1	164.2	166.8	168.4
70°	129.5	127.6	128.9	131.1	132.8	136.4	141.6	142.9	143.3	144.6	146.2
72.5°	112.8	112.1	113.1	114.2	115.3	118.0	122.5	123.3	123.4	124.2	126.8
75°	89.6	88.9	88.3	89.3	90.6	92.6	94.2	95.5	95.1	95.5	97.5
77.5°	67.2	65.3	65.0	65.5	65.9	67.1	68.8	68.6	69.0	68.9	71.1
80°	53.3	50.7	50.4	50.4	50.7	51.3	52.0	52.7	51.7	52.7	53.3
82.5°	39.2	37.6	37.5	37.3	37.4	37.5	37.9	38.2	38.1	38.5	38.9
85°	21.6	20.9	20.0	20.6	20.3	19.3	20.0	18.9	18.7	18.9	19.3
87.5°	11.1	11.2	10.3	9.9	9.3	9.2	8.4	7.7	7.1	6.9	7.3
90°	19.1	17.9	16.1	14.4	12.7	10.9	9.0	7.1	5.1	3.1	1.1
92.5°	44.5	42.9	40.7	38.7	36.5	34.4	32.5	31.2	29.8	28.4	27.0
95°	87.7	86.0	83.5	81.0	78.5	76.1	74.6	74.0	73.6	73.1	72.6
97.5°	138.5	136.9	133.5	130.1	126.7	123.2	121.4	121.2	121.1	120.8	120.6
100°	173.1	170.9	167.6	164.5	161.2	158.0	156.4	156.4	156.4	156.4	156.4
102.5°	209.1	206.6	205.0	203.4	201.7	200.1	198.7	197.8	196.7	195.8	194.8
105°	268.5	266.9	265.4	264.0	262.4	261.0	259.6	258.4	257.1	255.9	254.7
107.5°	332.3	331.5	330.4	329.2	328.0	326.9	325.7	324.5	323.2	322.0	320.7
110°	376.0	375.2	374.5	373.8	373.1	372.3	371.3	370.1	368.9	367.6	366.4



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	420.3	419.9	419.0	418.0	417.1	416.2	415.3	414.7	414.1	413.5	412.8
115°	487.8	488.1	487.6	487.1	486.6	486.1	485.3	484.3	483.4	482.3	481.4
117.5°	554.4	554.2	553.7	553.3	552.8	552.4	552.0	551.5	551.0	550.6	550.2
120°	599.8	599.8	599.5	599.3	599.0	598.7	598.1	596.8	595.6	594.3	593.1
122.5°	644.2	644.5	643.8	643.2	642.5	641.9	641.3	640.8	640.4	640.0	639.6
125°	709.8	710.3	710.1	709.8	709.6	709.3	708.4	707.0	705.5	704.0	702.5
127.5°	774.4	774.6	774.4	774.0	773.8	773.4	772.9	772.1	771.2	770.3	769.5
130°	817.3	817.5	817.0	816.6	816.1	815.5	814.7	813.5	812.2	811.0	809.7
132.5°	858.4	858.7	858.8	858.8	858.9	859.0	858.1	856.0	854.0	852.0	849.9
135°	921.4	921.4	921.2	920.9	920.7	920.4	919.5	918.1	916.5	915.1	913.6
137.5°	982.7	982.4	981.9	981.3	980.8	980.2	979.2	977.8	976.4	974.9	973.4
140°	1021.3	1020.8	1020.0	1019.3	1018.6	1017.8	1016.8	1015.6	1014.3	1013.1	1011.8
142.5°	1059.5	1059.2	1058.3	1057.3	1056.4	1055.4	1054.5	1053.4	1052.4	1051.4	1050.3
145°	1114.7	1114.7	1113.9	1113.1	1112.4	1111.6	1110.8	1109.7	1108.8	1107.8	1106.8
147.5°	1164.8	1164.2	1163.6	1163.0	1162.4	1161.8	1161.2	1160.7	1160.2	1159.6	1159.1
150°	1197.3	1197.3	1196.3	1195.3	1194.3	1193.3	1192.9	1193.2	1193.4	1193.7	1193.9
152.5°	1226.5	1225.9	1225.5	1225.0	1224.7	1224.3	1223.9	1223.6	1223.2	1222.9	1222.5
155°	1268.6	1267.7	1267.4	1267.1	1266.9	1266.6	1266.5	1266.5	1266.5	1266.5	1266.5
157.5°	1305.4	1304.5	1304.2	1304.0	1303.7	1303.5	1303.6	1304.2	1304.8	1305.3	1305.8
160°	1327.8	1326.8	1326.5	1326.4	1326.1	1325.9	1326.1	1326.8	1327.6	1328.4	1329.0
162.5°	1348.6	1347.4	1347.3	1347.3	1347.2	1347.2	1347.5	1348.0	1348.5	1349.1	1349.6
165°	1377.0	1376.0	1375.7	1375.4	1375.2	1375.0	1375.1	1375.6	1376.1	1376.6	1377.1
167.5°	1397.3	1395.9	1395.9	1395.9	1395.9	1395.9	1396.4	1397.3	1398.4	1399.3	1400.3
170°	1409.9	1408.3	1408.3	1408.3	1408.3	1408.3	1408.9	1409.9	1410.8	1411.9	1412.8
172.5°	1418.8	1417.3	1417.3	1417.3	1417.3	1417.3	1417.8	1418.8	1419.8	1420.7	1421.8
175°	1428.8	1427.4	1427.4	1427.4	1427.4	1427.4	1427.9	1428.8	1429.9	1430.8	1431.8
177.5°	1433.7	1432.4	1432.7	1432.9	1433.0	1433.3	1433.7	1434.6	1435.4	1436.1	1436.9
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	774.8	778.4	780.8	785.2	788.9	791.0	792.8	794.4	796.3	797.8	802.3
5°	779.7	788.2	795.5	806.6	816.7	824.6	833.0	840.6	846.8	855.7	862.5
7.5°	777.6	792.7	808.6	825.7	843.3	859.7	874.7	888.8	901.6	917.0	930.5
10°	775.5	796.1	816.4	839.6	863.5	883.7	902.8	922.0	936.1	955.7	972.4
12.5°	774.0	798.2	822.7	850.6	876.8	905.4	930.7	944.8	966.2	981.9	1001.7
15°	767.3	799.4	833.0	864.4	901.7	928.2	950.5	977.9	997.9	1017.9	1039.4
17.5°	755.4	791.8	829.5	870.6	906.4	934.9	963.5	990.0	1013.8	1040.5	1067.5
20°	750.0	786.3	829.5	871.7	906.6	936.4	965.9	995.0	1021.1	1055.5	1086.5
22.5°	738.5	782.4	822.2	863.2	899.3	931.7	965.1	998.1	1032.9	1071.7	1110.6
25°	717.9	762.4	804.6	845.2	881.5	922.0	957.7	1001.9	1046.3	1097.7	1146.1
27.5°	696.6	739.2	777.8	817.0	859.4	905.3	951.5	1001.6	1059.9	1124.6	1193.0
30°	679.3	719.5	757.2	797.4	841.5	893.2	943.9	1003.5	1070.8	1143.8	1224.9
32.5°	659.2	696.3	732.9	775.4	823.5	878.0	937.1	1002.4	1083.4	1166.3	1249.7
35°	624.7	655.8	693.4	738.8	793.2	855.7	924.0	1001.2	1094.1	1189.2	1259.6
37.5°	583.8	612.8	652.4	702.2	759.1	826.2	907.3	998.8	1097.5	1173.4	1196.1
40°	556.4	583.2	624.4	676.1	734.3	805.3	894.2	991.0	1086.5	1135.0	1116.3
42.5°	527.0	555.2	595.4	646.5	709.1	786.4	877.7	974.6	1054.6	1072.9	1008.5
45°	480.8	509.9	549.5	601.2	668.6	752.3	847.5	935.4	981.5	948.5	848.8
47.5°	437.8	465.1	501.8	555.1	624.7	711.3	802.9	873.1	876.8	797.9	691.4
50°	408.5	433.7	470.6	524.0	593.0	680.6	763.4	818.6	793.8	704.6	602.2
52.5°	379.7	404.4	440.8	493.6	561.9	642.1	719.2	757.9	711.1	619.5	532.0
55°	338.2	359.8	395.5	444.2	508.9	583.5	648.9	662.3	601.5	511.2	440.2
57.5°	297.6	317.8	350.3	395.1	454.3	520.4	571.5	568.7	504.4	426.9	370.6
60°	270.2	289.8	318.6	362.4	416.4	473.3	517.1	506.6	442.9	376.2	328.7
62.5°	245.6	263.1	290.3	328.6	377.9	430.6	466.6	451.2	388.7	330.4	292.8
65°	209.3	224.0	247.3	280.0	320.9	364.4	392.2	372.2	318.9	273.5	243.3
67.5°	174.7	186.5	206.0	232.1	267.0	301.9	318.8	298.8	256.1	222.9	200.6
70°	152.7	163.2	178.2	201.5	231.9	261.3	274.1	256.1	219.5	191.0	175.0
72.5°	130.8	139.4	152.7	173.5	197.9	223.4	234.5	217.4	187.3	163.2	148.3
75°	101.1	106.9	116.1	130.5	149.8	170.0	176.3	161.3	142.0	124.0	114.2
77.5°	72.3	77.3	84.3	93.3	107.0	119.9	125.4	116.7	101.7	90.3	82.3
80°	55.6	58.2	64.1	71.6	82.4	90.6	94.2	88.6	78.2	69.7	63.5
82.5°	39.6	42.3	45.8	52.0	58.9	64.4	68.3	64.6	57.0	50.3	46.7
85°	19.3	20.9	22.9	25.5	30.7	34.0	33.7	31.4	28.4	25.8	23.8
87.5°	7.4	8.1	9.3	10.9	12.1	13.5	14.4	14.2	13.5	13.0	12.5
90°	3.1	5.1	7.1	9.0	10.9	12.7	14.4	16.1	17.9	19.1	20.3
92.5°	28.4	29.8	31.2	32.5	34.4	36.5	38.7	40.7	42.9	44.5	46.1
95°	73.1	73.6	74.0	74.6	76.1	78.5	81.0	83.5	86.0	87.7	89.5
97.5°	120.8	121.1	121.2	121.4	123.2	126.7	130.1	133.5	136.9	138.5	140.2
100°	156.4	156.4	156.4	156.4	158.0	161.2	164.5	167.6	170.9	173.1	175.4
102.5°	195.8	196.7	197.8	198.7	200.1	201.7	203.4	205.0	206.6	209.1	211.5
105°	255.9	257.1	258.4	259.6	261.0	262.4	264.0	265.4	266.9	268.5	269.9
107.5°	322.0	323.2	324.5	325.7	326.9	328.0	329.2	330.4	331.5	332.3	332.9
110°	367.6	368.9	370.1	371.3	372.3	373.1	373.8	374.5	375.2	376.0	376.8





TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	413.5	414.1	414.7	415.3	416.2	417.1	418.0	419.0	419.9	420.3	420.6
115°	482.3	483.4	484.3	485.3	486.1	486.6	487.1	487.6	488.1	487.8	487.6
117.5°	550.6	551.0	551.5	552.0	552.4	552.8	553.3	553.7	554.2	554.4	554.6
120°	594.3	595.6	596.8	598.1	598.7	599.0	599.3	599.5	599.8	599.8	599.8
122.5°	640.0	640.4	640.8	641.3	641.9	642.5	643.2	643.8	644.5	644.2	644.0
125°	704.0	705.5	707.0	708.4	709.3	709.6	709.8	710.1	710.3	709.8	709.3
127.5°	770.3	771.2	772.1	772.9	773.4	773.8	774.0	774.4	774.6	774.4	774.1
130°	811.0	812.2	813.5	814.7	815.5	816.1	816.6	817.0	817.5	817.3	817.0
132.5°	852.0	854.0	856.0	858.1	859.0	858.9	858.8	858.8	858.7	858.4	858.2
135°	915.1	916.5	918.1	919.5	920.4	920.7	920.9	921.2	921.4	921.4	921.4
137.5°	974.9	976.4	977.8	979.2	980.2	980.8	981.3	981.9	982.4	982.7	983.0
140°	1013.1	1014.3	1015.6	1016.8	1017.8	1018.6	1019.3	1020.0	1020.8	1021.3	1021.8
142.5°	1051.4	1052.4	1053.4	1054.5	1055.4	1056.4	1057.3	1058.3	1059.2	1059.5	1059.8
145°	1107.8	1108.8	1109.7	1110.8	1111.6	1112.4	1113.1	1113.9	1114.7	1114.7	1114.7
147.5°	1159.6	1160.2	1160.7	1161.2	1161.8	1162.4	1163.0	1163.6	1164.2	1164.8	1165.4
150°	1193.7	1193.4	1193.2	1192.9	1193.3	1194.3	1195.3	1196.3	1197.3	1197.3	1197.3
152.5°	1222.9	1223.2	1223.6	1223.9	1224.3	1224.7	1225.0	1225.5	1225.9	1226.5	1227.0
155°	1266.5	1266.5	1266.5	1266.5	1266.6	1266.9	1267.1	1267.4	1267.7	1268.6	1269.6
157.5°	1305.3	1304.8	1304.2	1303.6	1303.5	1303.7	1304.0	1304.2	1304.5	1305.4	1306.5
160°	1328.4	1327.6	1326.8	1326.1	1325.9	1326.1	1326.4	1326.5	1326.8	1327.8	1328.8
162.5°	1349.1	1348.5	1348.0	1347.5	1347.2	1347.2	1347.3	1347.3	1347.4	1348.6	1349.8
165°	1376.6	1376.1	1375.6	1375.1	1375.0	1375.2	1375.4	1375.7	1376.0	1377.0	1377.9
167.5°	1399.3	1398.4	1397.3	1396.4	1395.9	1395.9	1395.9	1395.9	1395.9	1397.3	1398.9
170°	1411.9	1410.8	1409.9	1408.9	1408.3	1408.3	1408.3	1408.3	1408.3	1409.9	1411.4
172.5°	1420.7	1419.8	1418.8	1417.8	1417.3	1417.3	1417.3	1417.3	1417.3	1418.8	1420.3
175°	1430.8	1429.9	1428.8	1427.9	1427.4	1427.4	1427.4	1427.4	1427.4	1428.8	1430.3
177.5°	1436.1	1435.4	1434.6	1433.7	1433.3	1433.0	1432.9	1432.7	1432.4	1433.7	1434.9
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	770.6	770.6	770.6	770.6	770.6	770.6	770.6
2.5°	805.9	808.0	812.4	810.9	813.0	814.0	815.1
5°	871.0	881.5	886.1	885.4	892.3	890.6	889.0
7.5°	944.5	955.5	961.7	969.3	973.8	974.0	977.9
10°	986.1	1000.5	1006.4	1014.6	1019.9	1022.8	1022.4
12.5°	1018.0	1029.3	1042.5	1046.5	1053.6	1057.3	1055.9
15°	1056.4	1074.4	1088.1	1095.0	1103.9	1106.5	1110.1
17.5°	1090.7	1114.8	1130.9	1152.2	1160.3	1165.2	1162.3
20°	1116.6	1148.3	1164.4	1189.9	1203.9	1211.5	1208.8
22.5°	1147.3	1181.6	1211.3	1233.3	1254.7	1264.9	1267.0
25°	1199.7	1246.8	1290.3	1319.4	1345.9	1352.1	1365.9
27.5°	1258.4	1313.9	1360.4	1390.9	1409.5	1416.3	1420.6
30°	1295.2	1350.5	1385.5	1405.1	1411.0	1410.3	1409.7
32.5°	1313.3	1347.9	1354.6	1349.1	1335.7	1324.2	1312.3
35°	1287.7	1261.9	1223.2	1173.5	1137.0	1099.9	1096.3
37.5°	1158.1	1075.5	1011.2	939.5	898.1	872.5	854.8
40°	1036.1	942.3	864.4	803.9	761.7	745.1	728.8
42.5°	903.8	814.1	745.1	694.6	662.9	644.4	631.4
45°	734.3	655.1	601.2	564.6	539.3	525.0	516.8
47.5°	601.7	543.1	497.3	470.9	453.5	442.3	442.3
50°	530.5	474.6	444.2	423.3	408.2	399.3	401.0
52.5°	467.4	425.7	399.7	382.1	371.0	365.6	365.4
55°	390.9	360.8	343.8	331.0	323.5	317.3	318.6
57.5°	334.3	308.9	297.6	287.0	281.7	279.2	275.7
60°	299.3	279.7	269.8	261.3	256.1	254.2	250.6
62.5°	268.1	252.7	243.1	236.2	231.5	230.8	228.0
65°	225.3	213.6	205.1	201.8	196.9	195.6	195.6
67.5°	185.8	177.4	170.7	167.7	165.6	165.9	164.3
70°	160.9	154.0	149.8	146.5	144.9	145.3	143.9
72.5°	140.8	133.1	129.4	127.4	125.3	126.1	125.6
75°	106.6	102.7	100.7	98.8	97.5	96.8	96.2
77.5°	78.3	74.8	73.4	72.2	72.4	70.9	72.1
80°	60.5	57.6	56.6	54.9	54.6	54.6	54.3
82.5°	44.3	42.6	41.9	40.6	40.0	40.5	39.6
85°	22.9	21.6	21.3	21.3	20.6	20.0	21.6
87.5°	12.7	11.9	12.1	12.0	12.1	12.1	11.6
90°	21.6	22.8	23.8	24.5	25.3	26.1	26.8
92.5°	47.8	49.4	50.5	51.1	51.7	52.2	52.7
95°	91.2	93.0	94.0	94.5	95.1	95.6	96.1
97.5°	141.8	143.4	144.5	144.7	145.1	145.3	145.7
100°	177.5	179.8	181.2	181.7	182.2	182.7	183.1
102.5°	213.9	216.4	217.9	218.6	219.3	220.0	220.7
105°	271.4	272.9	274.0	274.7	275.5	276.2	277.0
107.5°	333.7	334.5	334.8	334.8	334.7	334.7	334.6
110°	377.5	378.2	378.5	378.2	378.0	377.7	377.5



TEST NUMBER: P333389-935

CATALOG NUMBER: S125DIW-S610D1340U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	420.9	421.3	421.3	420.9	420.4	419.9	419.5
115°	487.3	487.1	486.8	486.6	486.3	486.1	485.9
117.5°	554.7	555.0	554.6	553.6	552.6	551.6	550.6
120°	599.8	599.8	599.3	598.2	597.3	596.2	595.3
122.5°	643.9	643.6	643.2	642.3	641.5	640.8	640.0
125°	708.9	708.3	708.0	707.7	707.5	707.2	707.0
127.5°	773.9	773.7	773.3	772.8	772.3	771.8	771.3
130°	816.8	816.6	816.1	815.7	815.2	814.7	814.2
132.5°	857.9	857.6	857.2	856.5	855.7	855.1	854.4
135°	921.4	921.4	920.9	919.9	918.9	917.9	917.0
137.5°	983.3	983.6	983.1	981.9	980.6	979.4	978.2
140°	1022.3	1022.8	1022.4	1021.1	1019.9	1018.7	1017.4
142.5°	1060.1	1060.4	1060.0	1058.7	1057.5	1056.2	1055.0
145°	1114.7	1114.7	1114.2	1113.5	1112.8	1112.0	1111.3
147.5°	1166.0	1166.6	1166.1	1164.3	1162.7	1161.0	1159.3
150°	1197.3	1197.3	1197.0	1196.5	1196.0	1195.5	1195.1
152.5°	1227.6	1228.2	1228.1	1227.2	1226.3	1225.4	1224.5
155°	1270.6	1271.6	1271.4	1270.2	1269.0	1267.7	1266.5
157.5°	1307.4	1308.5	1308.1	1306.5	1304.8	1303.2	1301.6
160°	1329.8	1330.8	1330.7	1329.5	1328.2	1327.0	1325.7
162.5°	1350.9	1352.1	1352.0	1350.6	1349.1	1347.7	1346.3
165°	1379.0	1379.9	1379.7	1378.2	1376.7	1375.2	1373.7
167.5°	1400.3	1401.8	1401.8	1400.2	1398.7	1397.1	1395.6
170°	1412.8	1414.3	1414.2	1412.5	1410.7	1408.9	1407.2
172.5°	1421.8	1423.2	1423.2	1421.7	1420.1	1418.6	1417.0
175°	1431.8	1433.3	1433.1	1431.4	1429.7	1428.0	1426.2
177.5°	1436.1	1437.3	1437.2	1435.7	1434.3	1433.0	1431.6
180°	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2	1435.2

(END OF REPORT)