

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333739-830

Luminaire Tested: **S125RDIW-S1270D1560U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333739-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1560U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9697.6 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333739-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333739-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	41	39
3	81	72	65	59	74	66	60	55	56	51	48	47	43	40	38	35	33
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333739-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	1.9
10°-20°	511.3	5.3
20°-30°	741.4	7.6
30°-40°	845.0	8.7
40°-50°	823.6	8.5
50°-60°	693.3	7.1
60°-70°	486.0	5.0
70°-80°	249.8	2.6
80°-90°	67.1	0.7
90°-100°	122.3	1.3
100°-110°	361.3	3.7
110°-120°	611.9	6.3
120°-130°	805.3	8.3
130°-140°	902.4	9.3
140°-150°	884.4	9.1
150°-160°	742.8	7.7
160°-170°	493.8	5.1
170°-180°	172.8	1.8
0°-30°	1435.7	14.8
0°-40°	2280.6	23.5
0°-60°	3797.6	39.2
0°-90°	4600.5	47.4
90°-120°	1095.5	11.3
90°-150°	3687.7	38.0
90°-180°	5097.0	52.6
0°-180°	9697.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	1	13	23	30	34	9
95°	92	96	109	119	122	99
105°	324	331	340	348	352	346
115°	613	618	621	620	618	606
125°	894	902	904	901	900	800
135°	1163	1171	1173	1172	1167	896
145°	1409	1414	1419	1418	1414	880
155°	1612	1612	1613	1618	1612	742
165°	1753	1750	1751	1756	1748	494
175°	1822	1817	1817	1824	1815	173
180°	1827	1827	1827	1827	1827	



TEST NUMBER: P333739-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.3	26.0	24.7	23.4	22.1	21.5	21.7	21.9	22.0	22.1	22.5
90°	1.4	4.0	6.5	9.0	11.5	13.9	16.1	18.3	20.5	22.7	24.3
92.5°	34.4	36.2	38.0	39.7	41.5	43.7	46.5	49.1	51.8	54.6	56.6
95°	92.4	93.0	93.7	94.3	94.9	96.8	100.0	103.1	106.3	109.4	111.7
97.5°	153.5	153.7	154.0	154.3	154.6	156.8	161.2	165.6	169.9	174.3	176.3
100°	199.0	199.0	199.0	199.0	199.0	201.0	205.2	209.2	213.4	217.4	220.4
102.5°	247.9	249.2	250.4	251.7	253.0	254.7	256.7	258.8	260.9	263.0	266.1
105°	324.1	325.6	327.3	328.9	330.5	332.2	334.0	335.9	337.8	339.8	341.7
107.5°	408.2	409.8	411.4	413.0	414.5	416.1	417.5	419.0	420.5	421.9	422.8
110°	466.3	467.9	469.4	471.0	472.6	473.8	474.8	475.7	476.6	477.6	478.5



TEST NUMBER: P333739-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	525.4	526.2	527.1	527.8	528.7	529.7	530.8	532.1	533.3	534.5	534.9
115°	612.7	614.0	615.2	616.4	617.7	618.7	619.3	619.9	620.6	621.2	620.9
117.5°	700.2	700.8	701.3	701.9	702.5	703.0	703.6	704.2	704.7	705.4	705.6
120°	754.8	756.4	758.0	759.6	761.1	762.0	762.4	762.7	763.0	763.4	763.4
122.5°	814.0	814.5	815.1	815.7	816.2	816.9	817.7	818.6	819.4	820.2	819.9
125°	894.1	896.0	898.0	899.8	901.7	902.9	903.1	903.4	903.8	904.1	903.4
127.5°	979.4	980.5	981.6	982.6	983.7	984.5	984.9	985.2	985.6	986.0	985.6
130°	1030.6	1032.2	1033.8	1035.3	1036.9	1038.0	1038.7	1039.2	1039.9	1040.6	1040.2
132.5°	1081.8	1084.4	1086.9	1089.6	1092.1	1093.3	1093.3	1093.1	1093.0	1092.9	1092.5
135°	1162.8	1164.7	1166.6	1168.5	1170.4	1171.5	1171.8	1172.1	1172.4	1172.7	1172.7
137.5°	1239.0	1240.9	1242.6	1244.4	1246.3	1247.5	1248.3	1249.0	1249.6	1250.4	1250.8
140°	1287.9	1289.5	1291.0	1292.6	1294.2	1295.4	1296.4	1297.4	1298.4	1299.3	1299.9
142.5°	1336.8	1338.1	1339.4	1340.8	1342.1	1343.3	1344.5	1345.8	1347.0	1348.1	1348.5
145°	1408.7	1409.9	1411.3	1412.5	1413.8	1414.9	1415.8	1416.7	1417.7	1418.6	1418.6
147.5°	1475.3	1475.9	1476.6	1477.3	1478.0	1478.8	1479.5	1480.3	1481.0	1481.8	1482.5
150°	1519.6	1519.3	1519.0	1518.6	1518.3	1518.8	1520.0	1521.4	1522.6	1523.9	1523.9
152.5°	1555.9	1556.4	1556.9	1557.3	1557.7	1558.2	1558.8	1559.2	1559.7	1560.3	1561.0
155°	1612.0	1612.0	1612.0	1612.0	1612.0	1612.1	1612.5	1612.8	1613.1	1613.4	1614.7
157.5°	1662.0	1661.3	1660.7	1659.9	1659.3	1659.1	1659.3	1659.7	1660.0	1660.3	1661.6
160°	1691.6	1690.6	1689.7	1688.8	1687.8	1687.5	1687.8	1688.1	1688.5	1688.8	1690.0
162.5°	1717.8	1717.0	1716.4	1715.7	1715.0	1714.7	1714.7	1714.8	1714.9	1714.9	1716.5
165°	1752.8	1752.1	1751.4	1750.9	1750.2	1750.0	1750.4	1750.7	1751.0	1751.3	1752.6
167.5°	1782.3	1781.0	1779.8	1778.5	1777.3	1776.6	1776.6	1776.6	1776.6	1776.6	1778.5
170°	1798.2	1797.0	1795.6	1794.4	1793.2	1792.5	1792.5	1792.5	1792.5	1792.5	1794.4
172.5°	1809.6	1808.4	1807.0	1805.8	1804.5	1803.9	1803.9	1803.9	1803.9	1803.9	1805.8
175°	1822.4	1821.1	1819.9	1818.5	1817.3	1816.7	1816.7	1816.7	1816.7	1816.7	1818.5
177.5°	1828.9	1827.9	1826.9	1825.9	1824.9	1824.2	1824.0	1823.7	1823.4	1823.3	1824.8
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6



TEST NUMBER: P333739-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	22.8	23.1	23.5	23.6	23.5	23.5	23.4	23.3
90°	25.9	27.5	29.0	30.3	31.3	32.2	33.2	34.1
92.5°	58.7	60.8	63.0	64.3	65.0	65.7	66.4	67.1
95°	113.9	116.1	118.3	119.7	120.4	121.0	121.6	122.2
97.5°	178.4	180.5	182.6	183.9	184.3	184.6	185.0	185.4
100°	223.2	226.0	228.8	230.6	231.2	231.9	232.5	233.1
102.5°	269.2	272.3	275.3	277.4	278.2	279.1	280.0	280.9
105°	343.6	345.4	347.3	348.7	349.7	350.6	351.6	352.5
107.5°	423.8	424.7	425.7	426.1	426.0	426.0	425.9	425.8
110°	479.6	480.5	481.5	481.7	481.5	481.1	480.8	480.5



TEST NUMBER: P333739-830

CATALOG NUMBER: S125RDIW-S1270D1560U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	535.4	535.8	536.2	536.2	535.6	535.1	534.5	534.0
115°	620.6	620.3	619.9	619.6	619.3	619.0	618.7	618.4
117.5°	705.9	706.2	706.3	705.9	704.6	703.3	702.1	700.8
120°	763.4	763.4	763.4	762.7	761.5	760.2	758.9	757.7
122.5°	819.7	819.4	819.2	818.6	817.6	816.5	815.5	814.5
125°	902.9	902.2	901.5	901.1	900.8	900.4	900.1	899.8
127.5°	985.3	985.1	984.7	984.2	983.5	983.0	982.3	981.7
130°	1039.9	1039.6	1039.2	1038.8	1038.2	1037.6	1036.9	1036.3
132.5°	1092.2	1091.9	1091.6	1091.0	1090.1	1089.2	1088.4	1087.4
135°	1172.7	1172.7	1172.7	1172.1	1170.8	1169.6	1168.3	1167.1
137.5°	1251.1	1251.5	1251.9	1251.3	1249.7	1248.1	1246.5	1244.9
140°	1300.5	1301.2	1301.7	1301.3	1299.8	1298.2	1296.6	1295.0
142.5°	1348.9	1349.2	1349.7	1349.1	1347.5	1346.0	1344.3	1342.7
145°	1418.6	1418.6	1418.6	1418.1	1417.2	1416.3	1415.3	1414.4
147.5°	1483.3	1484.0	1484.8	1484.1	1482.0	1479.8	1477.7	1475.6
150°	1523.9	1523.9	1523.9	1523.5	1522.9	1522.3	1521.6	1521.0
152.5°	1561.8	1562.5	1563.3	1563.1	1562.0	1560.9	1559.7	1558.6
155°	1615.9	1617.2	1618.4	1618.3	1616.7	1615.1	1613.5	1612.0
157.5°	1662.8	1664.2	1665.4	1665.0	1662.8	1660.8	1658.7	1656.6
160°	1691.3	1692.5	1693.8	1693.7	1692.1	1690.5	1688.9	1687.3
162.5°	1718.0	1719.5	1721.0	1720.8	1719.0	1717.1	1715.3	1713.4
165°	1753.8	1755.1	1756.3	1756.1	1754.2	1752.3	1750.4	1748.4
167.5°	1780.4	1782.3	1784.1	1784.1	1782.2	1780.3	1778.3	1776.3
170°	1796.3	1798.2	1800.1	1800.0	1797.7	1795.5	1793.3	1791.1
172.5°	1807.7	1809.6	1811.5	1811.5	1809.5	1807.5	1805.5	1803.6
175°	1820.5	1822.4	1824.3	1824.1	1821.9	1819.7	1817.5	1815.2
177.5°	1826.3	1827.8	1829.3	1829.2	1827.4	1825.6	1823.8	1822.1
180°	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6	1826.6

(END OF REPORT)