

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333375-935

Luminaire Tested: **S125DIW-S610D470U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333375-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D470U935-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3552.1 lumens
Efficiency: N/A
Efficacy: 117.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333375-935

CATALOG NUMBER: S125DIW-S610D470U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333375-935

CATALOG NUMBER: S125DIW-S610D470U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	55	51
2	91	83	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47	43
3	83	73	66	60	77	69	62	57	60	55	51	53	49	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	41	48	42	37	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5340	5340	5340
5°	5352	5301	5335
10°	5319	5264	5294
15°	5262	5201	5223
20°	5179	5112	5121
25°	5091	5007	5002
30°	4981	4894	4869
35°	4864	4771	4704
40°	4743	4639	4572
45°	4613	4517	4427
50°	4470	4372	4240
55°	4332	4206	4088
60°	4166	4039	3896
65°	3969	3839	3709
70°	3780	3609	3484
75°	3444	3331	3216
80°	3065	3016	2942
85°	2668	2712	2571



TEST NUMBER: P333375-935

CATALOG NUMBER: S125DIW-S610D470U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.0	2.2
10°-20°	220.2	6.2
20°-30°	325.2	9.2
30°-40°	379.4	10.7
40°-50°	381.1	10.7
50°-60°	334.5	9.4
60°-70°	249.3	7.0
70°-80°	142.5	4.0
80°-90°	42.6	1.2
90°-100°	33.6	0.9
100°-110°	99.2	2.8
110°-120°	168.0	4.7
120°-130°	221.1	6.2
130°-140°	247.7	7.0
140°-150°	242.8	6.8
150°-160°	203.9	5.7
160°-170°	135.6	3.8
170°-180°	47.4	1.3
0°-30°	623.4	17.5
0°-40°	1002.8	28.2
0°-60°	1718.4	48.4
0°-90°	2152.8	60.6
90°-120°	300.8	8.5
90°-150°	1012.4	28.5
90°-180°	1399.0	39.4
0°-180°	3552.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	827	827	827	827	827	
5°	826	824	818	823	823	78
15°	787	785	778	781	781	222
25°	714	711	703	704	702	329
35°	617	614	605	602	597	386
45°	505	502	495	487	485	389
55°	385	382	374	368	363	343
65°	260	258	251	246	243	258
75°	138	137	134	131	129	147
85°	36	37	37	36	35	40
90°	0	4	6	8	9	3
95°	25	26	30	33	34	27
105°	89	91	93	96	97	95
115°	168	170	171	170	170	166
125°	246	248	248	247	247	220
135°	319	321	322	322	320	246
145°	387	388	389	389	388	242
155°	443	443	443	444	443	204
165°	481	480	481	482	480	136
175°	500	499	499	501	498	48
180°	501	501	501	501	501	



TEST NUMBER: P333375-935

CATALOG NUMBER: S125DIW-S610D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	829.0	828.6	828.3	827.9	827.6	826.8	825.7	824.5	823.4	822.2	823.4
5°	825.6	825.3	825.0	824.7	824.4	823.5	822.1	820.6	819.2	817.7	819.1
7.5°	817.9	817.7	817.4	817.1	816.8	815.9	814.2	812.7	811.1	809.5	810.7
10°	811.1	810.9	810.6	810.3	810.0	809.1	807.4	805.9	804.3	802.7	803.8
12.5°	802.8	802.3	801.8	801.2	800.7	799.7	798.2	796.8	795.2	793.8	794.7
15°	787.0	786.5	786.1	785.7	785.2	784.2	782.6	781.0	779.4	777.8	778.5
17.5°	768.8	768.2	767.5	766.9	766.2	765.1	763.4	761.7	760.1	758.5	759.3
20°	753.6	753.3	753.0	752.8	752.4	751.4	749.5	747.6	745.7	743.8	744.9
22.5°	738.4	737.9	737.4	736.8	736.3	735.2	733.4	731.7	729.9	728.1	728.8
25°	714.4	713.6	712.9	712.2	711.4	710.2	708.3	706.4	704.5	702.6	702.9
27.5°	686.2	685.8	685.4	684.9	684.5	683.3	681.3	679.4	677.4	675.5	675.5
30°	667.9	667.4	667.0	666.6	666.2	664.9	662.7	660.5	658.3	656.2	655.8
32.5°	648.0	647.4	646.7	646.0	645.3	644.0	642.1	640.2	638.2	636.3	635.8
35°	616.9	616.3	615.7	615.2	614.6	613.3	611.2	609.2	607.2	605.1	604.4
37.5°	584.5	583.8	583.2	582.4	581.7	580.3	578.4	576.5	574.5	572.7	571.6
40°	562.6	561.9	561.1	560.4	559.6	558.3	556.3	554.2	552.2	550.2	548.9
42.5°	539.1	538.5	537.8	537.2	536.6	535.3	533.2	531.2	529.2	527.1	526.0
45°	505.1	504.5	503.9	503.3	502.7	501.5	499.8	498.1	496.3	494.6	492.8
47.5°	468.4	468.4	468.5	468.5	468.5	467.4	465.4	463.3	461.2	459.1	457.4
50°	444.9	444.4	443.9	443.5	443.1	442.0	440.2	438.5	436.8	435.1	433.2
52.5°	420.8	420.4	420.2	419.8	419.5	418.4	416.6	414.7	412.8	411.0	409.3
55°	384.7	384.2	383.7	383.3	382.9	381.7	379.6	377.6	375.6	373.5	372.2
57.5°	346.6	346.4	346.1	345.9	345.7	344.7	342.9	341.2	339.5	337.9	336.1
60°	322.5	321.9	321.3	320.7	320.2	319.1	317.5	315.9	314.3	312.7	311.3
62.5°	297.4	297.0	296.4	296.0	295.5	294.6	293.3	291.9	290.5	289.1	287.6
65°	259.7	259.4	259.2	258.8	258.6	257.6	256.0	254.4	252.8	251.2	249.9
67.5°	223.2	222.6	222.0	221.4	220.8	219.9	218.7	217.5	216.3	215.1	214.0
70°	200.2	199.5	198.7	198.0	197.3	196.2	194.9	193.6	192.3	191.1	190.1
72.5°	175.0	174.5	174.1	173.6	173.1	172.4	171.6	170.7	169.9	169.0	168.1
75°	138.0	137.8	137.4	137.2	136.9	136.4	135.6	134.9	134.1	133.5	133.0
77.5°	103.9	103.8	103.7	103.5	103.4	103.1	102.7	102.4	101.9	101.5	101.3
80°	82.4	82.4	82.4	82.4	82.4	82.3	82.0	81.7	81.5	81.1	80.9
82.5°	63.6	63.4	63.1	62.9	62.7	62.5	62.4	62.4	62.3	62.3	62.0
85°	36.0	36.2	36.2	36.4	36.6	36.6	36.6	36.6	36.6	36.6	36.5
87.5°	14.2	14.4	14.5	14.6	14.7	14.8	14.8	14.8	14.8	14.9	15.0
90°	0.4	1.1	1.8	2.5	3.2	3.8	4.4	5.0	5.6	6.3	6.7
92.5°	9.5	9.9	10.4	10.9	11.4	12.0	12.7	13.5	14.2	15.0	15.6
95°	25.4	25.6	25.7	25.9	26.1	26.6	27.5	28.3	29.2	30.0	30.7
97.5°	42.1	42.2	42.3	42.4	42.4	43.0	44.3	45.5	46.7	47.9	48.4
100°	54.7	54.7	54.7	54.7	54.7	55.2	56.3	57.4	58.5	59.7	60.5
102.5°	68.0	68.4	68.8	69.1	69.5	69.9	70.5	71.0	71.6	72.2	73.0
105°	88.9	89.4	89.8	90.2	90.7	91.2	91.7	92.2	92.7	93.2	93.8
107.5°	112.1	112.5	113.0	113.4	113.8	114.3	114.6	115.0	115.5	115.8	116.1
110°	128.0	128.5	128.9	129.3	129.8	130.1	130.4	130.6	130.9	131.1	131.4



TEST NUMBER: P333375-935

CATALOG NUMBER: S125DIW-S610D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	144.2	144.5	144.6	144.9	145.2	145.4	145.8	146.1	146.4	146.7	146.9
115°	168.2	168.5	168.9	169.3	169.6	169.9	170.0	170.2	170.4	170.6	170.5
117.5°	192.3	192.3	192.5	192.7	192.9	193.0	193.2	193.3	193.5	193.6	193.7
120°	207.2	207.7	208.1	208.5	209.0	209.2	209.3	209.4	209.5	209.6	209.6
122.5°	223.4	223.6	223.8	223.9	224.0	224.3	224.5	224.7	225.0	225.2	225.1
125°	245.5	246.0	246.5	247.0	247.5	247.9	248.0	248.1	248.1	248.2	248.1
127.5°	268.9	269.1	269.5	269.8	270.1	270.3	270.4	270.4	270.5	270.7	270.6
130°	282.9	283.4	283.8	284.2	284.6	285.0	285.2	285.3	285.5	285.7	285.6
132.5°	297.0	297.6	298.4	299.1	299.8	300.1	300.1	300.1	300.1	300.0	299.9
135°	319.2	319.8	320.3	320.8	321.3	321.6	321.7	321.8	321.8	321.9	321.9
137.5°	340.1	340.6	341.1	341.6	342.2	342.5	342.7	342.9	343.0	343.3	343.4
140°	353.5	354.0	354.4	354.8	355.2	355.7	355.9	356.2	356.5	356.7	356.9
142.5°	367.0	367.3	367.7	368.1	368.4	368.8	369.1	369.5	369.8	370.1	370.2
145°	386.8	387.1	387.4	387.8	388.1	388.4	388.7	388.9	389.2	389.4	389.4
147.5°	405.0	405.2	405.4	405.5	405.8	406.0	406.1	406.4	406.6	406.8	407.0
150°	417.2	417.1	417.0	416.9	416.8	417.0	417.3	417.7	418.0	418.4	418.4
152.5°	427.1	427.3	427.4	427.5	427.7	427.7	427.9	428.1	428.2	428.3	428.5
155°	442.6	442.6	442.6	442.6	442.6	442.6	442.6	442.7	442.8	442.9	443.2
157.5°	456.2	456.1	455.9	455.7	455.5	455.5	455.6	455.6	455.7	455.8	456.2
160°	464.4	464.2	463.8	463.6	463.3	463.2	463.3	463.4	463.5	463.6	464.0
162.5°	471.6	471.4	471.2	471.0	470.8	470.7	470.7	470.7	470.8	470.8	471.2
165°	481.1	481.0	480.8	480.6	480.4	480.4	480.5	480.6	480.7	480.8	481.1
167.5°	489.3	489.0	488.6	488.3	487.9	487.8	487.8	487.8	487.8	487.8	488.3
170°	493.6	493.3	492.9	492.6	492.2	492.1	492.1	492.1	492.1	492.1	492.6
172.5°	496.8	496.5	496.1	495.8	495.4	495.2	495.2	495.2	495.2	495.2	495.8
175°	500.3	499.9	499.6	499.2	498.9	498.7	498.7	498.7	498.7	498.7	499.2
177.5°	502.0	501.8	501.5	501.3	500.9	500.8	500.8	500.7	500.6	500.5	500.9
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4



TEST NUMBER: P333375-935

CATALOG NUMBER: S125DIW-S610D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	826.9	826.9	826.9	826.9	826.9	826.9	826.9	826.9
2.5°	824.5	825.7	826.8	827.3	827.2	827.1	827.0	826.9
5°	820.4	821.7	822.9	823.5	823.4	823.3	823.1	822.9
7.5°	812.0	813.3	814.6	815.2	815.0	814.9	814.8	814.6
10°	805.0	806.2	807.4	807.9	807.7	807.5	807.4	807.3
12.5°	795.7	796.6	797.5	798.0	797.9	797.9	797.9	797.8
15°	779.3	780.0	780.8	781.1	781.1	781.1	781.1	781.1
17.5°	760.3	761.1	762.1	762.2	761.4	760.7	760.0	759.2
20°	745.8	746.8	747.9	748.0	747.3	746.6	745.8	745.1
22.5°	729.4	730.1	730.8	730.9	730.4	729.9	729.4	728.9
25°	703.2	703.4	703.8	703.7	703.3	702.8	702.4	702.0
27.5°	675.6	675.7	675.7	675.5	675.1	674.7	674.2	673.8
30°	655.6	655.3	655.0	654.6	654.2	653.8	653.3	652.9
32.5°	635.2	634.6	634.1	633.5	632.7	632.0	631.1	630.3
35°	603.6	603.0	602.2	601.2	600.1	598.9	597.8	596.6
37.5°	570.5	569.5	568.3	567.5	566.8	566.2	565.5	564.8
40°	547.5	546.2	544.9	544.1	543.6	543.2	542.8	542.3
42.5°	524.8	523.6	522.4	521.4	520.7	520.1	519.4	518.8
45°	491.0	489.3	487.6	486.5	486.0	485.6	485.2	484.7
47.5°	455.6	453.7	452.0	450.6	449.6	448.6	447.5	446.5
50°	431.3	429.4	427.5	426.0	425.0	424.0	422.9	422.0
52.5°	407.6	406.0	404.3	402.9	401.8	400.6	399.5	398.4
55°	370.9	369.6	368.3	367.1	366.1	365.1	364.1	363.1
57.5°	334.4	332.8	331.1	329.9	329.4	328.8	328.3	327.8
60°	309.8	308.3	306.9	305.7	304.6	303.6	302.6	301.6
62.5°	286.0	284.5	282.8	281.7	280.9	280.1	279.3	278.5
65°	248.6	247.3	246.0	245.0	244.4	243.8	243.3	242.7
67.5°	212.9	211.8	210.7	209.9	209.6	209.2	208.9	208.5
70°	189.2	188.4	187.5	186.8	186.2	185.6	185.0	184.5
72.5°	167.0	166.1	165.1	164.3	163.7	163.2	162.6	162.0
75°	132.6	132.2	131.7	131.2	130.6	130.0	129.5	128.9
77.5°	101.0	100.7	100.5	100.1	99.7	99.4	98.9	98.5
80°	80.8	80.7	80.5	80.3	80.0	79.7	79.5	79.1
82.5°	61.7	61.5	61.2	61.0	61.0	61.0	60.9	60.9
85°	36.3	36.2	36.1	35.8	35.6	35.2	35.0	34.7
87.5°	15.1	15.2	15.2	15.2	15.0	14.8	14.6	14.5
90°	7.1	7.6	8.0	8.4	8.6	8.9	9.1	9.4
92.5°	16.1	16.7	17.3	17.7	17.8	18.0	18.3	18.4
95°	31.3	31.9	32.5	32.9	33.1	33.2	33.4	33.6
97.5°	49.0	49.6	50.1	50.5	50.5	50.7	50.8	50.9
100°	61.3	62.1	62.9	63.3	63.5	63.6	63.8	64.0
102.5°	73.9	74.7	75.6	76.1	76.4	76.6	76.9	77.1
105°	94.3	94.8	95.3	95.7	96.0	96.3	96.5	96.8
107.5°	116.3	116.6	116.8	117.0	117.0	116.9	116.9	116.9
110°	131.6	131.9	132.2	132.2	132.2	132.1	132.0	131.9



TEST NUMBER: P333375-935

CATALOG NUMBER: S125DIW-S610D470U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	147.0	147.1	147.2	147.2	147.1	146.9	146.7	146.5
115°	170.4	170.3	170.2	170.1	170.0	170.0	169.9	169.8
117.5°	193.8	193.8	193.9	193.8	193.5	193.1	192.7	192.3
120°	209.6	209.6	209.6	209.4	209.1	208.7	208.4	208.0
122.5°	225.1	225.0	224.9	224.7	224.5	224.2	223.9	223.6
125°	247.9	247.7	247.5	247.4	247.3	247.2	247.1	247.0
127.5°	270.5	270.4	270.4	270.2	270.0	269.8	269.7	269.5
130°	285.5	285.4	285.3	285.2	285.0	284.8	284.6	284.5
132.5°	299.8	299.7	299.6	299.5	299.3	299.0	298.8	298.5
135°	321.9	321.9	321.9	321.8	321.4	321.1	320.7	320.4
137.5°	343.5	343.5	343.7	343.5	343.1	342.7	342.2	341.7
140°	357.1	357.2	357.4	357.2	356.8	356.4	355.9	355.5
142.5°	370.3	370.4	370.5	370.3	369.9	369.5	369.0	368.6
145°	389.4	389.4	389.4	389.3	389.1	388.8	388.6	388.3
147.5°	407.2	407.4	407.6	407.4	406.8	406.2	405.6	405.1
150°	418.4	418.4	418.4	418.3	418.1	417.9	417.8	417.6
152.5°	428.8	429.0	429.1	429.1	428.8	428.5	428.2	427.8
155°	443.6	443.9	444.3	444.3	443.8	443.4	443.0	442.6
157.5°	456.5	456.8	457.2	457.1	456.5	455.9	455.4	454.8
160°	464.3	464.7	465.0	464.9	464.5	464.1	463.6	463.2
162.5°	471.7	472.0	472.4	472.4	471.9	471.4	470.9	470.4
165°	481.5	481.8	482.2	482.1	481.6	481.0	480.5	480.0
167.5°	488.8	489.3	489.8	489.8	489.2	488.7	488.2	487.7
170°	493.1	493.6	494.2	494.1	493.5	492.9	492.3	491.7
172.5°	496.3	496.8	497.3	497.3	496.7	496.2	495.7	495.2
175°	499.7	500.3	500.8	500.8	500.2	499.6	498.9	498.3
177.5°	501.4	501.8	502.2	502.1	501.7	501.2	500.7	500.2
180°	501.4	501.4	501.4	501.4	501.4	501.4	501.4	501.4

(END OF REPORT)