

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333422-935

Luminaire Tested: **S125DIW-S850D1340U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333422-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1340U935-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7562.3 lumens
Efficiency: N/A
Efficacy: 123.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333422-935

CATALOG NUMBER: S125DIW-S850D1340U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333422-935

CATALOG NUMBER: S125DIW-S850D1340U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	86	83	80	77	68	65	63	53	52	51	41	40	39	33
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33	27
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	32	29	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	24	27	23	20	21	18	16	13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7299	7299	7299
5°	7316	7247	7293
10°	7271	7195	7237
15°	7192	7109	7138
20°	7080	6988	7000
25°	6959	6844	6837
30°	6809	6689	6655
35°	6649	6522	6430
40°	6483	6340	6250
45°	6305	6175	6052
50°	6109	5974	5795
55°	5920	5749	5588
60°	5694	5521	5324
65°	5425	5248	5069
70°	5166	4930	4762
75°	4706	4551	4397
80°	4192	4125	4024
85°	3646	3712	3512



TEST NUMBER: P333422-935

CATALOG NUMBER: S125DIW-S850D1340U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.6	1.4
10°-20°	301.0	4.0
20°-30°	444.5	5.9
30°-40°	518.7	6.9
40°-50°	520.9	6.9
50°-60°	457.3	6.0
60°-70°	340.7	4.5
70°-80°	194.8	2.6
80°-90°	59.8	0.8
90°-100°	54.6	0.7
100°-110°	336.8	4.5
110°-120°	610.9	8.1
120°-130°	783.9	10.4
130°-140°	843.2	11.2
140°-150°	791.5	10.5
150°-160°	640.2	8.5
160°-170°	414.1	5.5
170°-180°	142.8	1.9
0°-30°	852.1	11.3
0°-40°	1370.8	18.1
0°-60°	2348.9	31.1
0°-90°	2944.3	38.9
90°-120°	1002.3	13.3
90°-150°	3420.9	45.2
90°-180°	4618.0	61.1
0°-180°	7562.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1130	1130	1130	1130	1130	
5°	1128	1126	1118	1125	1125	107
15°	1076	1073	1063	1067	1068	303
25°	976	972	960	962	960	449
35°	843	839	827	823	816	527
45°	690	686	676	666	663	532
55°	526	523	511	503	496	469
65°	355	353	343	336	332	352
75°	189	187	182	180	176	201
85°	49	50	50	49	47	55
90°	1	10	18	23	27	5
95°	64	58	18	23	23	81
105°	328	332	332	332	331	347
115°	615	621	622	617	611	610
125°	875	882	883	878	875	781
135°	1091	1098	1096	1093	1087	841
145°	1265	1267	1268	1268	1262	791
155°	1393	1387	1389	1392	1384	642
165°	1470	1464	1465	1471	1463	415
175°	1504	1498	1498	1506	1497	143
180°	1504	1504	1504	1504	1504	



TEST NUMBER: P333422-935

CATALOG NUMBER: S125DIW-S850D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1133.2	1132.6	1132.2	1131.7	1131.2	1130.1	1128.6	1127.0	1125.4	1123.9	1125.4
5°	1128.5	1128.1	1127.7	1127.3	1126.9	1125.7	1123.7	1121.7	1119.7	1117.8	1119.6
7.5°	1118.1	1117.8	1117.3	1116.9	1116.5	1115.3	1113.0	1110.9	1108.7	1106.5	1108.2
10°	1108.8	1108.5	1108.0	1107.6	1107.2	1106.0	1103.7	1101.6	1099.4	1097.2	1098.8
12.5°	1097.3	1096.7	1096.0	1095.2	1094.5	1093.1	1091.1	1089.1	1087.0	1085.0	1086.3
15°	1075.7	1075.1	1074.5	1073.9	1073.3	1071.9	1069.8	1067.6	1065.4	1063.2	1064.2
17.5°	1050.9	1050.0	1049.1	1048.3	1047.4	1045.8	1043.5	1041.3	1039.0	1036.7	1037.9
20°	1030.1	1029.8	1029.3	1028.9	1028.6	1027.0	1024.4	1021.8	1019.3	1016.7	1018.1
22.5°	1009.4	1008.7	1008.0	1007.2	1006.5	1005.0	1002.5	1000.1	997.6	995.2	996.2
25°	976.5	975.5	974.5	973.4	972.5	970.7	968.1	965.5	962.9	960.4	960.8
27.5°	938.0	937.5	936.9	936.3	935.6	934.0	931.3	928.7	926.0	923.3	923.4
30°	913.0	912.4	911.8	911.2	910.6	908.8	905.9	902.8	899.8	896.9	896.5
32.5°	885.8	884.8	884.0	883.0	882.2	880.4	877.7	875.0	872.4	869.7	869.0
35°	843.3	842.4	841.6	840.9	840.1	838.3	835.5	832.7	829.9	827.2	826.1
37.5°	799.1	798.1	797.0	796.1	795.0	793.2	790.7	788.0	785.4	782.8	781.3
40°	769.0	768.0	767.1	766.0	765.0	763.2	760.3	757.6	754.8	752.0	750.3
42.5°	736.8	736.0	735.1	734.3	733.5	731.7	728.9	726.1	723.3	720.6	718.9
45°	690.3	689.5	688.7	687.9	687.2	685.5	683.2	680.8	678.4	676.1	673.6
47.5°	640.2	640.3	640.3	640.3	640.4	639.0	636.1	633.3	630.4	627.6	625.1
50°	608.0	607.4	606.8	606.2	605.7	604.2	601.8	599.4	597.0	594.6	592.0
52.5°	575.1	574.7	574.3	573.9	573.4	571.9	569.4	566.8	564.3	561.7	559.5
55°	525.8	525.2	524.6	524.0	523.4	521.7	518.9	516.2	513.3	510.6	508.8
57.5°	473.7	473.5	473.1	472.8	472.5	471.1	468.8	466.5	464.1	461.8	459.4
60°	440.8	440.1	439.3	438.4	437.6	436.2	433.9	431.8	429.6	427.4	425.4
62.5°	406.5	405.9	405.3	404.6	404.0	402.7	400.9	399.0	397.1	395.2	393.1
65°	355.0	354.6	354.2	353.8	353.4	352.1	349.9	347.8	345.5	343.4	341.6
67.5°	305.1	304.3	303.4	302.6	301.8	300.5	298.9	297.3	295.7	294.0	292.5
70°	273.6	272.6	271.6	270.6	269.7	268.3	266.5	264.7	262.9	261.1	259.9
72.5°	239.3	238.6	237.9	237.3	236.6	235.7	234.5	233.3	232.2	231.1	229.7
75°	188.6	188.3	187.9	187.5	187.1	186.4	185.4	184.4	183.4	182.4	181.8
77.5°	142.0	141.8	141.7	141.5	141.4	141.0	140.4	139.9	139.3	138.8	138.4
80°	112.7	112.7	112.7	112.7	112.7	112.4	112.1	111.7	111.2	110.9	110.7
82.5°	86.9	86.6	86.3	85.9	85.7	85.4	85.3	85.3	85.2	85.2	84.8
85°	49.2	49.4	49.6	49.8	49.9	50.1	50.1	50.1	50.1	50.1	49.9
87.5°	19.5	20.0	20.3	20.8	21.1	21.4	21.6	21.8	22.0	22.1	22.4
90°	1.1	3.1	5.1	7.1	9.0	10.9	12.7	14.4	16.1	17.8	19.1
92.5°	17.1	15.8	14.4	13.0	11.6	11.7	13.3	14.7	16.3	17.8	19.1
95°	63.5	62.8	62.1	61.3	60.5	55.4	46.1	36.7	27.2	17.8	19.1
97.5°	132.7	134.0	135.3	136.6	138.0	129.3	110.7	92.1	73.4	54.8	47.9
100°	186.1	186.9	187.6	188.4	189.2	190.0	191.0	192.0	193.0	194.0	157.0
102.5°	240.6	241.5	242.5	243.4	244.4	245.1	245.7	246.3	246.8	247.5	240.5
105°	327.8	328.7	329.8	330.7	331.7	332.2	332.2	332.2	332.2	332.2	332.2
107.5°	418.3	418.3	418.3	418.3	418.3	418.5	419.0	419.5	420.0	420.5	420.5
110°	477.2	477.2	477.2	477.2	477.2	477.3	477.9	478.4	478.9	479.3	478.6



TEST NUMBER: P333422-935

CATALOG NUMBER: S125DIW-S850D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	532.4	533.0	533.6	534.2	534.8	535.3	535.5	535.8	536.1	536.4	535.5
115°	615.4	616.6	617.9	619.1	620.4	621.0	621.3	621.6	621.8	622.1	621.0
117.5°	701.2	701.1	701.1	701.0	701.0	701.5	702.4	703.4	704.3	705.2	704.0
120°	754.7	754.5	754.2	754.0	753.7	754.0	754.7	755.4	756.2	756.9	756.5
122.5°	801.9	802.9	803.8	804.8	805.7	806.4	806.8	807.1	807.4	807.8	807.3
125°	875.1	876.8	878.6	880.3	882.0	882.9	882.9	882.9	882.9	882.9	881.9
127.5°	944.9	946.2	947.4	948.6	949.9	950.4	950.2	950.1	949.9	949.8	949.3
130°	987.7	988.9	990.2	991.4	992.6	993.4	993.7	993.9	994.1	994.4	993.7
132.5°	1030.5	1031.9	1033.4	1034.8	1036.2	1036.7	1036.1	1035.6	1035.1	1034.5	1034.4
135°	1091.4	1092.9	1094.3	1095.8	1097.3	1097.8	1097.3	1096.8	1096.3	1095.8	1095.4
137.5°	1147.4	1148.6	1149.9	1151.2	1152.4	1152.9	1152.4	1152.0	1151.6	1151.2	1151.2
140°	1183.9	1184.4	1184.9	1185.3	1185.9	1186.0	1185.8	1185.5	1185.3	1185.0	1185.5
142.5°	1216.9	1217.2	1217.5	1217.8	1218.1	1218.4	1218.7	1219.1	1219.4	1219.8	1219.9
145°	1265.2	1265.8	1266.3	1266.8	1267.2	1267.5	1267.5	1267.5	1267.5	1267.5	1267.7
147.5°	1307.6	1307.5	1307.4	1307.3	1307.3	1307.3	1307.6	1307.9	1308.2	1308.5	1308.8
150°	1334.4	1333.9	1333.4	1332.9	1332.4	1332.4	1332.9	1333.4	1333.9	1334.4	1334.9
152.5°	1360.2	1359.2	1358.1	1357.0	1355.9	1355.6	1356.1	1356.6	1357.1	1357.5	1358.1
155°	1393.4	1392.0	1390.5	1389.1	1387.5	1387.1	1387.5	1388.0	1388.5	1389.1	1389.7
157.5°	1419.1	1418.2	1417.3	1416.4	1415.6	1415.1	1415.1	1415.2	1415.3	1415.3	1416.1
160°	1436.9	1435.5	1434.0	1432.4	1431.0	1430.4	1430.6	1430.9	1431.2	1431.4	1432.4
162.5°	1451.2	1449.8	1448.2	1446.7	1445.3	1444.7	1444.9	1445.2	1445.4	1445.6	1447.0
165°	1470.4	1468.9	1467.4	1465.9	1464.5	1463.8	1464.0	1464.3	1464.6	1464.8	1466.3
167.5°	1484.6	1483.2	1481.6	1480.1	1478.5	1477.9	1478.1	1478.3	1478.6	1478.9	1480.7
170°	1492.7	1491.0	1489.2	1487.5	1485.7	1485.0	1485.2	1485.5	1485.7	1486.0	1488.0
172.5°	1498.1	1496.3	1494.6	1492.8	1491.1	1490.5	1490.9	1491.3	1491.8	1492.2	1494.0
175°	1503.8	1502.4	1500.9	1499.3	1497.9	1497.3	1497.5	1497.8	1498.1	1498.2	1500.2
177.5°	1506.5	1505.3	1504.2	1503.0	1501.8	1501.2	1501.5	1501.7	1501.8	1502.0	1503.5
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8



TEST NUMBER: P333422-935

CATALOG NUMBER: S125DIW-S850D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2	1130.2
2.5°	1127.0	1128.6	1130.1	1130.9	1130.8	1130.6	1130.4	1130.2
5°	1121.4	1123.1	1124.9	1125.7	1125.5	1125.3	1125.1	1124.9
7.5°	1110.0	1111.7	1113.4	1114.2	1114.0	1113.9	1113.6	1113.4
10°	1100.4	1102.0	1103.5	1104.2	1104.1	1103.8	1103.6	1103.5
12.5°	1087.5	1088.8	1090.1	1090.7	1090.7	1090.6	1090.6	1090.5
15°	1065.2	1066.2	1067.2	1067.6	1067.6	1067.6	1067.6	1067.6
17.5°	1039.2	1040.4	1041.6	1041.8	1040.8	1039.8	1038.8	1037.8
20°	1019.5	1020.9	1022.3	1022.4	1021.5	1020.5	1019.5	1018.5
22.5°	997.0	998.0	998.9	999.0	998.3	997.6	997.0	996.3
25°	961.1	961.6	962.0	961.8	961.3	960.7	960.1	959.5
27.5°	923.5	923.6	923.7	923.4	922.8	922.2	921.6	921.0
30°	896.1	895.7	895.3	894.8	894.2	893.6	893.0	892.4
32.5°	868.2	867.5	866.9	865.9	864.9	863.8	862.7	861.7
35°	825.2	824.1	823.2	821.9	820.3	818.7	817.1	815.5
37.5°	779.8	778.3	776.9	775.7	774.8	773.9	773.0	772.1
40°	748.5	746.7	744.9	743.6	743.0	742.5	741.9	741.3
42.5°	717.3	715.7	714.0	712.7	711.9	710.9	710.0	709.1
45°	671.2	668.8	666.5	665.0	664.4	663.8	663.2	662.6
47.5°	622.7	620.3	617.9	616.0	614.6	613.2	611.7	610.4
50°	589.4	586.9	584.3	582.3	580.9	579.5	578.2	576.8
52.5°	557.2	554.9	552.7	550.8	549.2	547.7	546.1	544.6
55°	507.0	505.2	503.4	501.9	500.4	499.0	497.7	496.3
57.5°	457.2	454.9	452.5	451.0	450.2	449.5	448.8	448.0
60°	423.4	421.5	419.5	417.8	416.4	415.0	413.6	412.2
62.5°	391.0	388.8	386.7	385.0	384.0	382.9	381.9	380.7
65°	339.8	338.0	336.2	334.9	334.2	333.4	332.5	331.7
67.5°	291.0	289.5	288.0	287.0	286.5	286.0	285.5	285.1
70°	258.7	257.5	256.3	255.4	254.5	253.7	253.0	252.2
72.5°	228.3	227.0	225.7	224.5	223.8	223.0	222.2	221.4
75°	181.2	180.6	180.0	179.3	178.6	177.7	176.9	176.2
77.5°	138.1	137.7	137.3	136.9	136.3	135.8	135.3	134.7
80°	110.5	110.3	110.1	109.8	109.4	109.0	108.6	108.2
82.5°	84.4	84.0	83.7	83.5	83.4	83.3	83.3	83.2
85°	49.7	49.5	49.2	49.0	48.6	48.2	47.8	47.4
87.5°	22.6	22.9	23.2	23.2	23.0	22.8	22.7	22.6
90°	20.3	21.5	22.8	23.8	24.5	25.2	26.0	26.8
92.5°	20.3	21.5	22.8	23.6	23.9	24.3	24.6	25.0
95°	20.3	21.5	22.8	23.4	23.4	23.4	23.4	23.4
97.5°	40.9	33.9	26.9	23.4	23.4	23.4	23.4	23.4
100°	120.1	83.3	46.3	27.4	26.3	25.4	24.4	23.4
102.5°	233.5	226.5	219.6	207.6	190.8	173.9	157.0	140.3
105°	332.2	332.2	332.2	332.1	331.8	331.6	331.3	331.1
107.5°	420.6	420.7	420.7	420.3	419.6	418.9	418.1	417.4
110°	477.9	477.2	476.4	476.1	476.4	476.6	476.9	477.2



TEST NUMBER: P333422-935

CATALOG NUMBER: S125DIW-S850D1340U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	534.5	533.6	532.7	532.0	531.7	531.3	531.0	530.6
115°	620.1	619.1	618.1	616.8	615.4	613.9	612.3	610.9
117.5°	702.7	701.4	700.1	699.0	698.4	697.8	697.2	696.5
120°	756.0	755.4	754.9	754.1	752.9	751.6	750.4	749.2
122.5°	806.8	806.2	805.8	804.8	803.4	801.9	800.5	799.1
125°	880.9	879.9	878.9	878.0	877.4	876.6	875.8	875.1
127.5°	948.7	948.1	947.6	946.4	944.6	942.8	940.9	939.1
130°	992.9	992.1	991.4	990.4	989.2	987.9	986.7	985.5
132.5°	1034.2	1034.1	1033.9	1033.2	1032.0	1030.8	1029.5	1028.3
135°	1094.8	1094.3	1093.8	1092.9	1091.4	1089.9	1088.4	1086.9
137.5°	1151.3	1151.4	1151.5	1150.9	1149.6	1148.3	1147.0	1145.7
140°	1186.0	1186.5	1187.0	1186.5	1185.0	1183.5	1182.1	1180.5
142.5°	1220.0	1220.1	1220.2	1219.5	1218.0	1216.5	1215.0	1213.6
145°	1268.0	1268.3	1268.5	1267.9	1266.4	1264.9	1263.4	1262.0
147.5°	1309.2	1309.4	1309.8	1309.0	1307.2	1305.4	1303.6	1301.8
150°	1335.4	1335.8	1336.4	1335.6	1333.6	1331.6	1329.6	1327.7
152.5°	1358.6	1359.1	1359.5	1358.9	1357.1	1355.4	1353.6	1351.8
155°	1390.5	1391.2	1392.0	1391.4	1389.4	1387.4	1385.4	1383.5
157.5°	1416.9	1417.7	1418.5	1417.9	1415.9	1413.9	1412.0	1410.0
160°	1433.4	1434.3	1435.4	1434.9	1432.9	1430.9	1428.9	1426.9
162.5°	1448.4	1449.8	1451.2	1450.8	1448.6	1446.4	1444.2	1442.1
165°	1467.7	1469.3	1470.8	1470.5	1468.5	1466.5	1464.6	1462.6
167.5°	1482.5	1484.2	1486.0	1485.7	1483.5	1481.4	1479.1	1476.9
170°	1490.0	1491.9	1493.9	1493.8	1491.6	1489.4	1487.1	1484.9
172.5°	1495.8	1497.6	1499.3	1499.2	1496.9	1494.7	1492.5	1490.2
175°	1502.2	1504.2	1506.1	1506.1	1503.8	1501.6	1499.3	1497.1
177.5°	1504.9	1506.2	1507.6	1507.5	1505.9	1504.3	1502.7	1501.2
180°	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8	1503.8

(END OF REPORT)