

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333723-830

Luminaire Tested: **S125RDIW-S1270D470U830-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333723-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D470U830-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6129.6 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333723-830

CATALOG NUMBER: S125RDIW-S1270D470U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333723-830

CATALOG NUMBER: S125RDIW-S1270D470U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	113	113	113	113	108	108	108	108	97	97	97	88	88	88	79	79	79	75					75			
1	104	99	95	92	99	95	91	88	86	83	81	78	76	74	70	69	68	64					64			
2	95	87	81	76	90	83	78	73	76	71	67	69	65	62	62	60	57	54					54			
3	87	77	69	63	82	74	67	61	67	62	57	61	57	53	56	52	49	46					46			
4	80	68	60	54	75	65	58	52	60	54	49	55	50	46	50	46	43	40					40			
5	73	61	53	47	69	59	51	45	54	47	43	49	44	40	45	41	37	35					35			
6	68	55	47	41	64	53	45	40	49	42	37	45	39	35	41	37	33	31					31			
7	63	50	42	36	60	48	41	35	44	38	33	41	35	31	38	33	30	27					27			
8	58	46	38	32	55	44	37	31	41	34	30	38	32	28	35	30	27	24					24			
9	55	42	34	29	52	40	33	28	37	31	27	35	29	25	32	27	24	22					22			
10	51	39	31	26	49	37	30	26	35	29	24	32	27	23	30	25	22	20					20			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333723-830

CATALOG NUMBER: S125RDIW-S1270D470U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	3.0
10°-20°	511.3	8.3
20°-30°	741.4	12.1
30°-40°	845.0	13.8
40°-50°	823.6	13.4
50°-60°	693.3	11.3
60°-70°	486.0	7.9
70°-80°	249.8	4.1
80°-90°	64.3	1.0
90°-100°	36.8	0.6
100°-110°	108.6	1.8
110°-120°	183.9	3.0
120°-130°	242.0	3.9
130°-140°	271.2	4.4
140°-150°	265.8	4.3
150°-160°	223.2	3.6
160°-170°	148.4	2.4
170°-180°	51.9	0.8
0°-30°	1435.7	23.4
0°-40°	2280.6	37.2
0°-60°	3797.6	62.0
0°-90°	4597.7	75.0
90°-120°	329.3	5.4
90°-150°	1108.3	18.1
90°-180°	1532.0	25.0
0°-180°	6129.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	0	4	7	9	10	5
95°	28	29	33	36	37	30
105°	97	100	102	105	106	104
115°	184	186	187	186	186	182
125°	269	271	272	271	270	241
135°	349	352	352	352	351	269
145°	423	425	426	426	425	265
155°	484	484	485	486	484	223
165°	527	526	526	528	526	149
175°	548	546	546	548	546	52
180°	549	549	549	549	549	



TEST NUMBER: P333723-830

CATALOG NUMBER: S125RDIW-S1270D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.1	25.4	23.8	22.1	20.5	19.5	19.4	19.2	19.1	19.0	19.1
90°	0.5	1.2	2.0	2.7	3.5	4.1	4.8	5.5	6.1	6.9	7.4
92.5°	10.4	10.8	11.4	12.0	12.4	13.1	13.9	14.8	15.6	16.4	17.1
95°	27.8	28.0	28.2	28.4	28.6	29.1	30.1	31.0	32.0	32.9	33.6
97.5°	46.1	46.2	46.3	46.4	46.5	47.1	48.4	49.8	51.1	52.4	53.0
100°	59.9	59.9	59.9	59.9	59.9	60.4	61.6	62.9	64.1	65.3	66.3
102.5°	74.5	74.8	75.3	75.7	76.1	76.5	77.2	77.8	78.4	79.0	79.9
105°	97.4	97.8	98.3	98.8	99.3	99.8	100.4	100.9	101.5	102.1	102.6
107.5°	122.7	123.2	123.7	124.1	124.6	125.1	125.5	125.9	126.4	126.8	127.1
110°	140.2	140.6	141.1	141.6	142.0	142.4	142.7	143.0	143.3	143.5	143.8



TEST NUMBER: P333723-830

CATALOG NUMBER: S125RDIW-S1270D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	157.9	158.2	158.3	158.6	158.9	159.2	159.6	159.9	160.2	160.6	160.8
115°	184.1	184.5	184.9	185.3	185.7	186.0	186.2	186.3	186.5	186.7	186.6
117.5°	210.5	210.6	210.8	210.9	211.1	211.3	211.5	211.6	211.8	212.0	212.1
120°	226.9	227.3	227.8	228.3	228.8	229.0	229.1	229.2	229.3	229.4	229.4
122.5°	244.6	244.8	245.0	245.2	245.2	245.5	245.7	246.0	246.3	246.5	246.4
125°	268.7	269.3	269.8	270.4	271.0	271.4	271.5	271.5	271.6	271.7	271.5
127.5°	294.4	294.6	295.0	295.3	295.7	295.9	296.0	296.1	296.1	296.3	296.2
130°	309.7	310.2	310.7	311.1	311.6	312.0	312.2	312.4	312.5	312.7	312.6
132.5°	325.1	325.8	326.7	327.4	328.2	328.6	328.6	328.5	328.5	328.4	328.3
135°	349.4	350.1	350.6	351.2	351.8	352.0	352.1	352.2	352.3	352.4	352.4
137.5°	372.3	372.9	373.4	374.0	374.6	374.9	375.1	375.3	375.5	375.8	375.9
140°	387.0	387.5	388.0	388.4	388.9	389.4	389.6	389.9	390.2	390.5	390.7
142.5°	401.7	402.1	402.6	402.9	403.3	403.7	404.1	404.4	404.8	405.2	405.3
145°	423.4	423.8	424.1	424.5	424.9	425.2	425.5	425.7	426.0	426.3	426.3
147.5°	443.4	443.6	443.7	443.9	444.2	444.4	444.6	444.9	445.1	445.4	445.5
150°	456.7	456.6	456.5	456.4	456.3	456.5	456.9	457.2	457.6	458.0	458.0
152.5°	467.6	467.8	467.9	468.0	468.2	468.3	468.4	468.6	468.7	468.9	469.1
155°	484.5	484.5	484.5	484.5	484.5	484.5	484.6	484.7	484.7	484.8	485.2
157.5°	499.5	499.3	499.1	498.9	498.6	498.6	498.7	498.8	498.9	499.0	499.4
160°	508.4	508.1	507.7	507.5	507.2	507.1	507.2	507.3	507.4	507.5	507.9
162.5°	516.2	516.0	515.9	515.6	515.4	515.3	515.3	515.3	515.4	515.4	515.9
165°	526.7	526.5	526.3	526.1	525.9	525.9	526.0	526.1	526.2	526.3	526.7
167.5°	535.6	535.3	534.9	534.5	534.1	534.0	534.0	534.0	534.0	534.0	534.5
170°	540.4	540.0	539.6	539.2	538.9	538.7	538.7	538.7	538.7	538.7	539.2
172.5°	543.8	543.5	543.1	542.7	542.3	542.2	542.2	542.2	542.2	542.2	542.7
175°	547.7	547.2	546.9	546.5	546.1	545.9	545.9	545.9	545.9	545.9	546.5
177.5°	549.6	549.3	549.0	548.7	548.4	548.2	548.2	548.1	548.0	547.9	548.4
180°	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9



TEST NUMBER: P333723-830

CATALOG NUMBER: S125RDIW-S1270D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	19.2	19.3	19.4	19.3	19.1	18.9	18.8	18.5
90°	7.8	8.3	8.8	9.1	9.4	9.7	10.0	10.3
92.5°	17.6	18.3	18.9	19.3	19.5	19.7	20.0	20.2
95°	34.2	34.9	35.5	36.0	36.2	36.4	36.6	36.8
97.5°	53.6	54.3	54.9	55.2	55.3	55.5	55.6	55.7
100°	67.1	68.0	68.8	69.3	69.5	69.7	69.8	70.0
102.5°	80.9	81.8	82.8	83.3	83.6	83.9	84.2	84.5
105°	103.2	103.8	104.3	104.8	105.1	105.4	105.7	105.9
107.5°	127.3	127.6	127.9	128.1	128.1	128.0	128.0	128.0
110°	144.1	144.4	144.7	144.8	144.7	144.6	144.5	144.4



TEST NUMBER: P333723-830

CATALOG NUMBER: S125RDIW-S1270D470U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	160.9	161.0	161.2	161.2	161.0	160.8	160.6	160.4
115°	186.5	186.4	186.3	186.2	186.2	186.1	186.0	185.9
117.5°	212.2	212.2	212.3	212.2	211.8	211.4	210.9	210.6
120°	229.4	229.4	229.4	229.2	228.8	228.5	228.1	227.7
122.5°	246.4	246.3	246.2	246.0	245.7	245.4	245.1	244.8
125°	271.4	271.2	271.0	270.8	270.7	270.6	270.5	270.4
127.5°	296.1	296.1	296.0	295.8	295.6	295.4	295.2	295.0
130°	312.5	312.5	312.4	312.2	312.0	311.8	311.6	311.4
132.5°	328.2	328.1	328.0	327.9	327.6	327.3	327.1	326.8
135°	352.4	352.4	352.4	352.2	351.9	351.5	351.1	350.7
137.5°	376.0	376.1	376.3	376.1	375.6	375.1	374.6	374.1
140°	390.9	391.1	391.2	391.1	390.6	390.1	389.6	389.2
142.5°	405.4	405.5	405.6	405.4	404.9	404.4	404.0	403.5
145°	426.3	426.3	426.3	426.2	425.9	425.7	425.4	425.1
147.5°	445.7	446.0	446.2	446.0	445.4	444.7	444.0	443.5
150°	458.0	458.0	458.0	457.9	457.7	457.5	457.3	457.1
152.5°	469.4	469.6	469.8	469.8	469.4	469.1	468.7	468.3
155°	485.6	486.0	486.4	486.4	485.9	485.4	484.9	484.5
157.5°	499.7	500.1	500.5	500.4	499.7	499.1	498.5	497.9
160°	508.3	508.7	509.1	509.0	508.5	508.0	507.6	507.1
162.5°	516.3	516.7	517.2	517.2	516.6	516.0	515.5	514.9
165°	527.1	527.4	527.8	527.7	527.2	526.6	526.0	525.5
167.5°	535.1	535.6	536.2	536.2	535.6	535.0	534.4	533.9
170°	539.8	540.4	541.0	540.9	540.3	539.6	538.9	538.3
172.5°	543.3	543.8	544.4	544.4	543.8	543.2	542.6	542.1
175°	547.1	547.7	548.3	548.2	547.5	546.9	546.2	545.5
177.5°	548.8	549.3	549.8	549.7	549.2	548.7	548.1	547.6
180°	548.9	548.9	548.9	548.9	548.9	548.9	548.9	548.9

(END OF REPORT)