

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333424-935

Luminaire Tested: **S125DIW-S850D1560U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333424-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1560U935-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8345.1 lumens
Efficiency: N/A
Efficacy: 122.5 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot



64% Up

36% Dn



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	36
1	95	91	87	83	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	86	79	73	68	78	72	67	63	58	55	52	45	43	41	34	32	31	26
3	79	70	63	57	71	63	57	52	51	47	43	40	37	35	30	28	27	22
4	72	62	54	48	65	56	50	44	46	41	37	36	33	30	27	25	23	19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	20	18	14
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	18	16	13
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	11
9	48	37	29	24	44	33	27	23	28	23	19	22	18	16	17	14	13	10
10	45	33	26	22	41	31	24	20	25	21	17	20	17	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6803	6803	6803	6803
5°	7878	6825	5977	6825
10°	9165	6790	5237	6790
15°	10146	6740	4831	6740
20°	11357	6661	4504	6661
25°	13304	6572	4345	6572
30°	14370	6485	4207	6485
35°	11815	6320	4117	6320
40°	8398	6091	4018	6091
45°	6452	5782	3961	5782
50°	5507	5399	3953	5399
55°	4904	5024	3987	5024
60°	4423	4614	4088	4614
65°	4085	4201	4195	4201
70°	3714	3773	4254	3773
75°	3281	3324	4217	3324
80°	2760	2708	3861	2708
85°	2186	1949	3112	1949



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.4	1.2
10°-20°	301.9	3.6
20°-30°	490.2	5.9
30°-40°	598.0	7.2
40°-50°	544.0	6.5
50°-60°	433.3	5.2
60°-70°	301.8	3.6
70°-80°	160.9	1.9
80°-90°	44.3	0.5
90°-100°	63.5	0.8
100°-110°	391.6	4.7
110°-120°	710.2	8.5
120°-130°	911.5	10.9
130°-140°	980.4	11.7
140°-150°	920.2	11.0
150°-160°	744.4	8.9
160°-170°	481.4	5.8
170°-180°	166.0	2.0
0°-30°	893.6	10.7
0°-40°	1491.6	17.9
0°-60°	2468.9	29.6
0°-90°	2975.9	35.7
90°-120°	1165.3	14.0
90°-150°	3977.4	47.7
90°-180°	5369.0	64.3
0°-180°	8345.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1053	1053	1053	1053	1053	
5°	1215	1053	922	1053	1215	122
15°	1517	1008	722	1008	1517	434
25°	1867	922	610	922	1867	853
35°	1499	802	522	802	1499	917
45°	706	633	434	633	706	565
55°	436	446	354	446	436	392
65°	267	275	274	275	267	265
75°	132	133	169	133	132	142
85°	30	26	42	26	30	35
90°	31	1	31	1	31	15
95°	27	74	27	74	27	22
105°	385	381	385	381	385	348
115°	710	716	710	716	710	705
125°	1017	1017	1017	1017	1017	905
135°	1264	1269	1264	1269	1264	975
145°	1467	1471	1467	1471	1467	916
155°	1608	1620	1608	1620	1608	741
165°	1700	1710	1700	1710	1700	480
175°	1741	1748	1741	1748	1741	166
180°	1748	1748	1748	1748	1748	



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1114.1	1112.7	1111.3	1108.4	1110.5	1104.5	1101.6	1096.6	1090.5	1088.4	1085.9
5°	1215.1	1217.4	1219.6	1210.2	1211.2	1204.9	1190.6	1179.0	1169.6	1157.5	1149.0
7.5°	1336.8	1331.5	1331.0	1325.0	1314.5	1306.1	1291.1	1272.0	1253.4	1232.3	1214.9
10°	1397.6	1398.0	1394.0	1386.8	1375.7	1367.6	1348.0	1329.1	1306.4	1279.5	1260.3
12.5°	1443.4	1445.2	1440.1	1430.5	1425.0	1407.0	1391.5	1369.2	1342.1	1320.7	1291.4
15°	1517.4	1512.4	1508.9	1496.8	1487.5	1468.7	1444.1	1420.8	1391.3	1364.0	1336.8
17.5°	1588.7	1592.7	1586.0	1574.9	1545.8	1523.9	1490.9	1459.1	1422.4	1385.8	1353.2
20°	1652.4	1656.0	1645.7	1626.5	1591.6	1569.7	1526.3	1485.2	1442.7	1395.8	1360.0
22.5°	1731.8	1729.0	1715.1	1685.8	1655.6	1615.1	1568.1	1518.1	1464.9	1411.9	1364.3
25°	1867.0	1848.2	1839.7	1803.5	1763.8	1704.3	1639.9	1566.6	1500.4	1430.2	1369.4
27.5°	1941.9	1936.0	1926.6	1901.3	1859.5	1796.0	1720.0	1630.6	1537.3	1448.7	1369.2
30°	1926.9	1927.8	1928.7	1920.6	1893.9	1846.0	1770.5	1674.3	1563.4	1463.7	1371.7
32.5°	1793.9	1810.2	1825.7	1844.1	1851.6	1842.5	1795.1	1708.3	1594.2	1480.9	1370.2
35°	1498.6	1503.6	1554.0	1604.1	1672.1	1724.8	1760.1	1721.7	1625.6	1495.5	1368.5
37.5°	1168.5	1192.7	1227.6	1284.2	1382.2	1470.1	1583.0	1635.0	1604.0	1500.2	1365.4
40°	996.1	1018.5	1041.2	1098.9	1181.6	1288.1	1416.3	1525.9	1551.3	1485.2	1354.6
42.5°	863.1	880.7	906.0	949.4	1018.6	1112.8	1235.4	1378.5	1466.6	1441.6	1332.1
45°	706.4	717.6	737.3	771.6	821.7	895.5	1003.7	1160.2	1296.5	1341.7	1278.7
47.5°	604.6	604.5	619.8	643.6	679.8	742.4	822.4	945.0	1090.7	1198.4	1193.4
50°	548.1	545.9	557.9	578.5	607.1	648.7	725.1	823.0	963.0	1085.0	1119.0
52.5°	499.5	499.7	507.1	522.4	546.3	581.9	638.9	727.2	846.8	972.1	1036.0
55°	435.5	433.7	442.1	452.5	469.8	493.1	534.3	601.8	698.8	822.2	905.3
57.5°	376.8	381.7	385.1	392.3	406.7	422.3	457.0	506.5	583.5	689.4	777.3
60°	342.4	347.4	350.1	357.2	368.9	382.3	409.1	449.4	514.1	605.4	692.5
62.5°	311.7	315.6	316.4	322.9	332.3	345.4	366.5	400.3	451.5	531.3	616.7
65°	267.3	267.3	269.1	275.9	280.3	292.0	308.1	332.6	373.8	435.9	508.8
67.5°	224.6	226.8	226.3	229.3	233.4	242.4	253.9	274.2	304.7	350.1	408.4
70°	196.7	198.5	198.0	200.3	204.7	210.6	220.0	239.2	261.1	300.0	350.1
72.5°	171.7	172.4	171.3	174.2	176.8	181.9	192.4	202.7	223.2	256.0	297.1
75°	131.5	132.3	133.2	135.0	137.7	140.3	145.8	156.0	169.4	194.1	220.4
77.5°	98.5	96.9	99.0	98.8	100.2	102.3	107.0	112.4	123.5	139.1	159.5
80°	74.2	74.6	74.6	75.1	77.3	78.7	82.7	86.7	95.2	106.9	121.1
82.5°	54.2	55.4	54.7	55.4	57.3	58.3	60.5	63.8	68.8	77.9	88.3
85°	29.5	27.3	28.2	29.1	29.1	29.5	31.3	32.6	35.3	38.9	42.9
87.5°	14.8	15.3	15.5	15.3	15.6	15.3	16.4	16.2	17.0	17.7	18.8
90°	31.1	30.2	29.4	28.5	27.6	26.5	25.1	23.6	22.2	20.8	18.7
92.5°	29.0	28.7	28.2	27.8	27.4	26.5	25.1	23.6	22.2	20.8	18.9
95°	27.2	27.2	27.2	27.2	27.2	26.5	25.1	23.6	22.2	20.8	31.7
97.5°	27.2	27.2	27.2	27.2	27.2	31.3	39.4	47.5	55.6	63.8	85.4
100°	27.2	28.4	29.5	30.7	31.9	53.9	96.8	139.7	182.6	225.5	224.4
102.5°	163.1	182.6	202.2	221.8	241.4	255.3	263.4	271.5	279.7	287.7	287.1
105°	385.0	385.2	385.6	385.8	386.1	386.2	386.2	386.2	386.2	386.2	386.2
107.5°	485.3	486.1	487.0	487.8	488.7	489.1	489.0	489.0	489.0	488.9	488.4
110°	554.7	554.5	554.1	553.9	553.6	553.9	554.7	555.6	556.5	557.3	556.7



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	616.9	617.3	617.8	618.2	618.5	619.3	620.4	621.5	622.6	623.7	623.4
115°	710.2	712.0	713.7	715.5	717.2	718.6	719.8	720.9	722.0	723.2	723.0
117.5°	809.8	810.5	811.3	812.1	812.8	813.9	815.5	816.9	818.4	819.9	818.8
120°	871.0	872.5	873.8	875.3	876.8	877.8	878.3	878.9	879.5	880.0	879.2
122.5°	929.0	930.7	932.4	934.1	935.7	936.9	937.5	938.0	938.6	939.2	938.7
125°	1017.4	1018.3	1019.2	1020.0	1020.9	1021.9	1023.0	1024.2	1025.4	1026.5	1026.5
127.5°	1091.8	1094.0	1096.1	1098.2	1100.4	1101.7	1102.4	1103.0	1103.6	1104.3	1104.5
130°	1145.7	1147.2	1148.7	1150.1	1151.5	1152.7	1153.6	1154.4	1155.3	1156.2	1155.8
132.5°	1195.5	1197.0	1198.4	1199.9	1201.3	1202.1	1202.3	1202.5	1202.6	1202.8	1203.4
135°	1263.7	1265.4	1267.1	1268.9	1270.6	1271.8	1272.4	1272.9	1273.5	1274.1	1274.6
137.5°	1332.1	1333.6	1335.2	1336.6	1338.2	1338.9	1338.7	1338.6	1338.5	1338.3	1338.9
140°	1372.6	1374.3	1376.1	1377.8	1379.5	1380.1	1379.5	1378.9	1378.4	1377.8	1378.0
142.5°	1410.9	1412.6	1414.4	1416.1	1417.9	1418.7	1418.6	1418.4	1418.3	1418.2	1417.8
145°	1467.2	1469.0	1470.7	1472.4	1474.1	1474.8	1474.5	1474.3	1473.9	1473.7	1473.7
147.5°	1513.6	1515.7	1517.8	1519.8	1521.9	1522.8	1522.4	1522.1	1521.7	1521.4	1521.0
150°	1543.7	1546.0	1548.3	1550.6	1552.9	1553.8	1553.2	1552.6	1552.0	1551.4	1550.8
152.5°	1571.7	1573.7	1575.8	1577.9	1579.9	1580.7	1580.1	1579.6	1579.0	1578.4	1577.9
155°	1608.4	1610.8	1613.1	1615.4	1617.6	1618.4	1617.6	1616.7	1615.8	1615.0	1614.4
157.5°	1639.3	1641.6	1643.9	1646.2	1648.6	1649.2	1648.3	1647.4	1646.5	1645.5	1645.5
160°	1659.1	1661.3	1663.6	1665.9	1668.3	1668.8	1667.7	1666.5	1665.3	1664.2	1663.9
162.5°	1676.6	1679.2	1681.7	1684.3	1686.8	1687.2	1685.7	1684.0	1682.4	1680.8	1680.5
165°	1700.5	1702.8	1705.1	1707.4	1709.7	1710.0	1708.3	1706.5	1704.8	1703.1	1702.8
167.5°	1717.1	1719.7	1722.3	1724.8	1727.4	1727.7	1725.6	1723.5	1721.5	1719.4	1719.2
170°	1726.4	1729.0	1731.6	1734.2	1736.8	1736.9	1734.7	1732.3	1730.0	1727.7	1727.4
172.5°	1732.7	1735.3	1737.8	1740.4	1743.0	1743.3	1741.2	1739.1	1737.1	1735.0	1734.5
175°	1740.7	1743.3	1745.8	1748.4	1751.0	1751.2	1748.9	1746.5	1744.3	1742.0	1741.7
177.5°	1745.3	1747.1	1749.0	1750.8	1752.7	1752.8	1751.2	1749.6	1748.0	1746.4	1746.1
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1083.7	1081.2	1078.3	1073.3	1067.3	1064.0	1059.0	1055.8	1049.4	1044.0	1038.3
5°	1138.7	1127.0	1116.4	1102.5	1087.3	1077.5	1065.8	1052.8	1039.5	1025.6	1010.4
7.5°	1195.7	1175.1	1152.7	1128.7	1105.2	1083.6	1062.9	1042.6	1023.6	1000.7	981.4
10°	1233.9	1208.0	1180.3	1147.6	1115.9	1088.2	1060.1	1035.4	1010.4	983.6	959.8
12.5°	1272.2	1237.7	1198.5	1162.7	1124.5	1091.1	1057.9	1026.5	995.1	965.4	937.7
15°	1299.2	1268.8	1232.6	1181.6	1138.7	1092.7	1048.9	1008.1	970.2	937.1	902.2
17.5°	1317.0	1277.8	1239.0	1190.1	1133.8	1082.3	1032.7	986.1	943.2	901.3	867.7
20°	1320.3	1280.0	1239.3	1191.5	1133.8	1074.8	1025.2	969.2	923.3	879.9	838.7
22.5°	1319.1	1273.6	1229.2	1180.0	1123.8	1069.4	1009.4	952.4	902.5	859.8	816.9
25°	1309.1	1260.3	1204.9	1155.3	1099.8	1042.2	981.4	922.3	871.3	822.6	780.2
27.5°	1300.6	1237.4	1174.7	1116.8	1063.2	1010.4	952.2	891.7	835.3	785.8	745.8
30°	1290.3	1221.0	1150.3	1089.9	1035.0	983.6	928.6	869.6	810.5	762.2	719.4
32.5°	1281.0	1200.2	1125.7	1060.0	1001.7	951.7	901.0	844.9	787.0	738.0	695.0
35°	1263.0	1169.6	1084.2	1010.0	947.8	896.4	853.9	801.6	748.4	701.0	659.9
37.5°	1240.2	1129.3	1037.7	959.8	891.7	837.6	798.1	757.9	706.8	661.2	624.0
40°	1222.3	1100.7	1003.7	924.1	853.5	797.1	760.5	722.5	680.0	637.6	598.2
42.5°	1199.8	1075.0	969.4	883.7	813.7	758.9	720.4	688.1	650.7	611.1	574.5
45°	1158.4	1028.3	913.9	821.7	751.1	697.0	657.2	633.1	604.9	567.3	536.5
47.5°	1097.5	972.2	853.9	758.8	685.9	635.8	598.5	575.3	555.4	527.5	499.6
50°	1043.4	930.4	810.5	716.2	643.3	592.8	558.4	537.4	520.4	498.9	475.3
52.5°	983.0	877.8	768.0	674.8	602.6	552.8	519.1	500.6	486.5	471.1	447.7
55°	887.0	797.6	695.7	607.1	540.5	491.8	462.3	446.2	434.5	422.9	408.6
57.5°	781.2	711.3	621.0	540.1	478.7	434.4	406.8	391.2	382.2	376.2	367.7
60°	706.8	647.0	569.1	495.3	435.5	396.1	369.3	357.2	349.7	344.7	338.5
62.5°	637.8	588.7	516.5	449.2	396.8	359.6	335.7	324.0	316.7	314.3	309.1
65°	536.1	498.1	438.6	382.7	338.0	306.3	286.1	274.9	270.4	267.8	268.3
67.5°	435.8	412.7	364.9	317.3	281.5	254.9	238.8	230.2	228.0	224.5	224.4
70°	374.6	357.2	317.0	275.4	243.7	223.1	208.8	199.8	197.6	195.8	195.4
72.5°	320.6	305.4	270.4	237.1	208.6	190.5	178.7	173.4	169.7	168.7	168.6
75°	241.0	232.5	204.7	178.4	158.7	146.2	138.2	133.2	130.5	130.1	130.5
77.5°	171.3	163.9	146.3	127.6	115.2	105.7	98.9	97.2	94.2	94.3	93.8
80°	128.7	123.8	112.7	97.9	87.6	79.6	76.0	72.8	72.0	70.6	72.0
82.5°	93.3	88.1	80.5	71.1	62.6	57.8	54.2	53.2	52.7	52.0	52.3
85°	46.1	46.5	42.0	34.9	31.3	28.6	26.3	26.3	25.9	25.5	25.9
87.5°	19.1	18.0	16.1	14.6	12.4	10.8	10.0	9.9	9.3	9.4	10.2
90°	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	17.1	15.4	13.6	13.5	15.2	16.7	18.3	20.0	18.3	16.7	15.2
95°	42.6	53.6	64.5	70.4	71.3	72.2	73.0	73.9	73.0	72.2	71.3
97.5°	107.1	128.7	150.4	160.5	158.9	157.3	155.8	154.2	155.8	157.3	158.9
100°	223.3	222.1	220.9	219.9	219.0	218.2	217.3	216.5	217.3	218.2	219.0
102.5°	286.4	285.7	285.0	284.0	283.0	281.9	280.8	279.7	280.8	281.9	283.0
105°	386.2	386.2	386.2	385.6	384.5	383.4	382.2	381.1	382.2	383.4	384.5
107.5°	487.8	487.2	486.6	486.3	486.3	486.3	486.3	486.3	486.3	486.3	486.3
110°	556.2	555.6	555.0	554.7	554.7	554.7	554.7	554.7	554.7	554.7	554.7



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	623.0	622.7	622.3	621.8	621.1	620.4	619.7	619.1	619.7	620.4	621.1
115°	722.6	722.4	722.0	721.2	719.8	718.3	716.9	715.5	716.9	718.3	719.8
117.5°	817.7	816.7	815.5	815.0	815.1	815.1	815.2	815.3	815.2	815.1	815.1
120°	878.3	877.4	876.6	876.3	876.6	876.9	877.2	877.4	877.2	876.9	876.6
122.5°	938.3	938.0	937.5	936.8	935.7	934.6	933.5	932.5	933.5	934.6	935.7
125°	1026.5	1026.5	1026.5	1025.5	1023.5	1021.5	1019.4	1017.4	1019.4	1021.5	1023.5
127.5°	1104.7	1104.8	1105.0	1104.3	1102.9	1101.5	1100.0	1098.5	1100.0	1101.5	1102.9
130°	1155.5	1155.3	1154.9	1154.1	1152.7	1151.2	1149.8	1148.3	1149.8	1151.2	1152.7
132.5°	1204.0	1204.7	1205.3	1204.8	1203.2	1201.4	1199.8	1198.1	1199.8	1201.4	1203.2
135°	1275.2	1275.8	1276.3	1275.8	1274.1	1272.4	1270.6	1268.9	1270.6	1272.4	1274.1
137.5°	1339.4	1339.9	1340.4	1340.0	1338.4	1337.0	1335.4	1333.9	1335.4	1337.0	1338.4
140°	1378.4	1378.6	1378.9	1378.8	1378.2	1377.6	1377.1	1376.5	1377.1	1377.6	1378.2
142.5°	1417.4	1417.0	1416.6	1416.2	1415.8	1415.5	1415.1	1414.8	1415.1	1415.5	1415.8
145°	1473.7	1473.7	1473.7	1473.4	1472.8	1472.2	1471.6	1471.1	1471.6	1472.2	1472.8
147.5°	1520.7	1520.4	1520.0	1519.8	1520.0	1520.1	1520.2	1520.4	1520.2	1520.1	1520.0
150°	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1550.8	1550.3	1549.7
152.5°	1577.3	1576.7	1576.1	1576.4	1577.7	1579.0	1580.3	1581.5	1580.3	1579.0	1577.7
155°	1613.8	1613.3	1612.7	1613.3	1615.0	1616.7	1618.4	1620.1	1618.4	1616.7	1615.0
157.5°	1645.5	1645.4	1645.3	1645.8	1646.8	1647.9	1648.9	1649.9	1648.9	1647.9	1646.8
160°	1663.6	1663.4	1663.0	1663.8	1665.5	1667.2	1669.0	1670.7	1669.0	1667.2	1665.5
162.5°	1680.2	1679.9	1679.6	1680.3	1682.0	1683.9	1685.6	1687.3	1685.6	1683.9	1682.0
165°	1702.5	1702.2	1701.9	1702.6	1704.3	1706.1	1707.9	1709.6	1707.9	1706.1	1704.3
167.5°	1718.8	1718.6	1718.3	1719.0	1720.8	1722.6	1724.4	1726.1	1724.4	1722.6	1720.8
170°	1727.2	1726.8	1726.6	1727.4	1729.4	1731.5	1733.5	1735.5	1733.5	1731.5	1729.4
172.5°	1734.0	1733.5	1732.9	1733.6	1735.7	1737.7	1739.7	1741.7	1739.7	1737.7	1735.7
175°	1741.4	1741.1	1740.9	1741.5	1743.3	1745.0	1746.7	1748.4	1746.7	1745.0	1743.3
177.5°	1745.9	1745.7	1745.4	1746.0	1747.4	1748.8	1750.2	1751.5	1750.2	1748.8	1747.4
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1035.1	1031.1	1027.9	1020.8	1016.8	1011.5	1007.2	1011.8	1006.9	1009.0	1005.7
5°	1002.8	990.3	981.4	968.4	957.2	946.9	939.4	938.0	934.4	932.6	927.2
7.5°	964.0	948.3	933.0	916.0	901.6	887.1	877.8	870.1	865.0	858.3	853.8
10°	941.1	920.1	902.2	881.7	863.8	848.1	835.6	829.3	823.5	815.0	811.9
12.5°	912.8	891.1	869.3	847.3	830.2	812.7	801.9	792.5	788.5	778.9	777.9
15°	879.0	846.4	824.8	802.5	778.8	764.5	755.5	745.3	740.8	734.1	729.2
17.5°	838.5	809.4	782.6	759.4	739.1	727.0	715.9	708.9	701.2	696.8	688.8
20°	809.3	781.5	754.7	730.0	714.5	700.6	691.6	684.9	676.9	674.7	666.6
22.5°	784.5	754.0	728.2	707.6	690.4	674.9	665.1	660.6	655.0	648.2	646.5
25°	744.4	712.6	690.8	670.2	655.0	640.7	634.0	628.2	622.8	617.9	616.0
27.5°	709.7	681.3	655.3	636.7	623.5	610.4	604.5	597.4	593.6	589.6	584.8
30°	685.4	656.3	633.5	615.6	601.3	589.7	583.4	578.5	575.0	571.4	568.7
32.5°	660.3	633.4	611.3	593.8	579.5	570.8	565.2	561.7	557.8	553.5	550.1
35°	627.2	597.7	576.3	561.1	549.9	543.2	536.9	533.8	529.3	529.3	525.7
37.5°	590.0	564.5	545.5	531.7	521.7	515.7	508.9	506.7	503.9	502.0	500.8
40°	567.8	544.1	526.2	512.4	501.6	496.7	491.4	487.8	485.9	483.7	482.8
42.5°	544.9	522.3	505.1	492.3	483.0	478.8	473.8	471.3	467.7	464.8	464.3
45°	510.1	488.2	472.6	462.3	454.3	449.4	446.2	440.8	439.0	435.5	435.0
47.5°	477.1	456.1	440.7	432.3	425.2	421.2	416.3	411.0	408.9	407.1	406.9
50°	452.5	433.3	418.9	410.9	404.2	398.4	393.4	389.9	388.5	388.5	389.4
52.5°	427.4	411.0	398.9	389.1	382.7	376.5	372.0	369.8	367.7	369.9	371.5
55°	390.7	374.2	365.2	355.9	349.7	342.4	340.3	339.3	338.0	341.6	343.4
57.5°	352.0	340.4	329.8	320.6	315.0	310.8	307.8	307.2	309.7	311.4	317.3
60°	327.3	313.8	304.4	297.3	290.6	287.9	287.1	286.1	287.9	292.8	300.4
62.5°	300.1	289.2	279.1	273.7	268.8	264.3	264.2	264.7	268.3	273.9	281.5
65°	260.2	250.8	244.1	237.8	233.8	231.2	232.0	233.8	237.8	245.5	253.9
67.5°	219.7	213.3	207.2	202.2	198.3	198.3	199.2	201.9	206.6	215.4	223.2
70°	193.6	186.4	181.5	179.3	176.2	174.4	177.0	181.5	185.5	193.6	200.3
72.5°	167.5	161.4	157.6	156.0	154.7	153.3	154.1	158.9	164.5	172.5	180.3
75°	128.7	126.5	123.8	122.1	120.7	121.6	122.5	127.0	131.5	139.9	148.9
77.5°	93.9	91.6	90.1	89.6	88.9	89.3	91.9	95.1	99.5	105.7	112.4
80°	71.1	70.2	69.3	68.9	68.9	69.3	72.8	75.1	79.1	85.0	90.3
82.5°	51.7	51.2	51.1	51.0	51.3	51.4	53.6	56.5	59.8	64.2	68.9
85°	27.3	26.3	27.7	28.2	27.3	28.6	29.5	31.3	32.6	34.9	37.1
87.5°	11.0	12.2	12.2	13.0	13.4	14.6	14.5	16.2	17.1	18.2	18.1
90°	10.5	12.7	14.7	16.7	18.7	20.8	22.2	23.6	25.1	26.5	27.6
92.5°	13.5	13.6	15.4	17.1	18.9	20.8	22.2	23.6	25.1	26.5	27.4
95°	70.4	64.5	53.6	42.6	31.7	20.8	22.2	23.6	25.1	26.5	27.2
97.5°	160.5	150.4	128.7	107.1	85.4	63.8	55.6	47.5	39.4	31.3	27.2
100°	219.9	220.9	222.1	223.3	224.4	225.5	182.6	139.7	96.8	53.9	31.9
102.5°	284.0	285.0	285.7	286.4	287.1	287.7	279.7	271.5	263.4	255.3	241.4
105°	385.6	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.1
107.5°	486.3	486.6	487.2	487.8	488.4	488.9	489.0	489.0	489.0	489.1	488.7
110°	554.7	555.0	555.6	556.2	556.7	557.3	556.5	555.6	554.7	553.9	553.6



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	621.8	622.3	622.7	623.0	623.4	623.7	622.6	621.5	620.4	619.3	618.5
115°	721.2	722.0	722.4	722.6	723.0	723.2	722.0	720.9	719.8	718.6	717.2
117.5°	815.0	815.5	816.7	817.7	818.8	819.9	818.4	816.9	815.5	813.9	812.8
120°	876.3	876.6	877.4	878.3	879.2	880.0	879.5	878.9	878.3	877.8	876.8
122.5°	936.8	937.5	938.0	938.3	938.7	939.2	938.6	938.0	937.5	936.9	935.7
125°	1025.5	1026.5	1026.5	1026.5	1026.5	1026.5	1025.4	1024.2	1023.0	1021.9	1020.9
127.5°	1104.3	1105.0	1104.8	1104.7	1104.5	1104.3	1103.6	1103.0	1102.4	1101.7	1100.4
130°	1154.1	1154.9	1155.3	1155.5	1155.8	1156.2	1155.3	1154.4	1153.6	1152.7	1151.5
132.5°	1204.8	1205.3	1204.7	1204.0	1203.4	1202.8	1202.6	1202.5	1202.3	1202.1	1201.3
135°	1275.8	1276.3	1275.8	1275.2	1274.6	1274.1	1273.5	1272.9	1272.4	1271.8	1270.6
137.5°	1340.0	1340.4	1339.9	1339.4	1338.9	1338.3	1338.5	1338.6	1338.7	1338.9	1338.2
140°	1378.8	1378.9	1378.6	1378.4	1378.0	1377.8	1378.4	1378.9	1379.5	1380.1	1379.5
142.5°	1416.2	1416.6	1417.0	1417.4	1417.8	1418.2	1418.3	1418.4	1418.6	1418.7	1417.9
145°	1473.4	1473.7	1473.7	1473.7	1473.7	1473.7	1473.9	1474.3	1474.5	1474.8	1474.1
147.5°	1519.8	1520.0	1520.4	1520.7	1521.0	1521.4	1521.7	1522.1	1522.4	1522.8	1521.9
150°	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1552.0	1552.6	1553.2	1553.8	1552.9
152.5°	1576.4	1576.1	1576.7	1577.3	1577.9	1578.4	1579.0	1579.6	1580.1	1580.7	1579.9
155°	1613.3	1612.7	1613.3	1613.8	1614.4	1615.0	1615.8	1616.7	1617.6	1618.4	1617.6
157.5°	1645.8	1645.3	1645.4	1645.5	1645.5	1645.5	1646.5	1647.4	1648.3	1649.2	1648.6
160°	1663.8	1663.0	1663.4	1663.6	1663.9	1664.2	1665.3	1666.5	1667.7	1668.8	1668.3
162.5°	1680.3	1679.6	1679.9	1680.2	1680.5	1680.8	1682.4	1684.0	1685.7	1687.2	1686.8
165°	1702.6	1701.9	1702.2	1702.5	1702.8	1703.1	1704.8	1706.5	1708.3	1710.0	1709.7
167.5°	1719.0	1718.3	1718.6	1718.8	1719.2	1719.4	1721.5	1723.5	1725.6	1727.7	1727.4
170°	1727.4	1726.6	1726.8	1727.2	1727.4	1727.7	1730.0	1732.3	1734.7	1736.9	1736.8
172.5°	1733.6	1732.9	1733.5	1734.0	1734.5	1735.0	1737.1	1739.1	1741.2	1743.3	1743.0
175°	1741.5	1740.9	1741.1	1741.4	1741.7	1742.0	1744.3	1746.5	1748.9	1751.2	1751.0
177.5°	1746.0	1745.4	1745.7	1745.9	1746.1	1746.4	1748.0	1749.6	1751.2	1752.8	1752.7
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1003.6	1006.1	1003.9	1006.9	1003.9	1006.1	1003.6	1005.7	1009.0	1006.9	1011.8
5°	925.0	921.0	923.7	921.9	923.7	921.0	925.0	927.2	932.6	934.4	938.0
7.5°	852.4	848.5	844.2	842.1	844.2	848.5	852.4	853.8	858.3	865.0	870.1
10°	807.0	802.0	801.6	798.5	801.6	802.0	807.0	811.9	815.0	823.5	829.3
12.5°	773.7	769.1	764.1	762.8	764.1	769.1	773.7	777.9	778.9	788.5	792.5
15°	726.5	722.9	719.8	722.5	719.8	722.9	726.5	729.2	734.1	740.8	745.3
17.5°	687.3	684.3	683.7	680.4	683.7	684.3	687.3	688.8	696.8	701.2	708.9
20°	662.5	660.3	661.2	655.4	661.2	660.3	662.5	666.6	674.7	676.9	684.9
22.5°	642.9	638.5	638.0	636.8	638.0	638.5	642.9	646.5	648.2	655.0	660.6
25°	612.1	609.8	607.6	609.8	607.6	609.8	612.1	616.0	617.9	622.8	628.2
27.5°	585.1	582.5	581.9	582.1	581.9	582.5	585.1	584.8	589.6	593.6	597.4
30°	568.7	564.2	564.6	564.2	564.6	564.2	568.7	568.7	571.4	575.0	578.5
32.5°	550.8	547.8	547.2	546.3	547.2	547.8	550.8	550.1	553.5	557.8	561.7
35°	524.4	524.4	522.2	522.2	522.2	524.4	524.4	525.7	529.3	529.3	533.8
37.5°	499.6	499.2	497.8	498.1	497.8	499.2	499.6	500.8	502.0	503.9	506.7
40°	481.0	480.6	479.2	476.6	479.2	480.6	481.0	482.8	483.7	485.9	487.8
42.5°	463.1	461.7	461.1	460.1	461.1	461.7	463.1	464.3	464.8	467.7	471.3
45°	435.0	435.0	434.1	433.7	434.1	435.0	435.0	435.0	435.5	439.0	440.8
47.5°	407.7	408.5	410.2	409.9	410.2	408.5	407.7	406.9	407.1	408.9	411.0
50°	391.2	391.7	393.0	393.4	393.0	391.7	391.2	389.4	388.5	388.5	389.9
52.5°	373.0	375.6	377.2	376.9	377.2	375.6	373.0	371.5	369.9	367.7	369.8
55°	347.4	350.5	353.6	354.1	353.6	350.5	347.4	343.4	341.6	338.0	339.3
57.5°	322.1	326.5	329.8	330.8	329.8	326.5	322.1	317.3	311.4	309.7	307.2
60°	304.9	310.7	314.8	316.5	314.8	310.7	304.9	300.4	292.8	287.9	286.1
62.5°	288.4	295.0	299.0	299.4	299.0	295.0	288.4	281.5	273.9	268.3	264.7
65°	261.6	268.3	271.8	274.5	271.8	268.3	261.6	253.9	245.5	237.8	233.8
67.5°	232.6	239.3	243.2	245.4	243.2	239.3	232.6	223.2	215.4	206.6	201.9
70°	211.5	218.2	223.5	225.3	223.5	218.2	211.5	200.3	193.6	185.5	181.5
72.5°	190.7	196.7	201.0	203.1	201.0	196.7	190.7	180.3	172.5	164.5	158.9
75°	154.7	162.7	166.8	169.0	166.8	162.7	154.7	148.9	139.9	131.5	127.0
77.5°	119.2	126.7	129.1	130.2	129.1	126.7	119.2	112.4	105.7	99.5	95.1
80°	95.7	100.1	103.2	103.8	103.2	100.1	95.7	90.3	85.0	79.1	75.1
82.5°	73.5	77.2	78.3	79.4	78.3	77.2	73.5	68.9	64.2	59.8	56.5
85°	40.2	42.0	42.4	42.0	42.4	42.0	40.2	37.1	34.9	32.6	31.3
87.5°	18.9	18.8	18.9	19.8	18.9	18.8	18.9	18.1	18.2	17.1	16.2
90°	28.5	29.4	30.2	31.1	30.2	29.4	28.5	27.6	26.5	25.1	23.6
92.5°	27.8	28.2	28.7	29.0	28.7	28.2	27.8	27.4	26.5	25.1	23.6
95°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	26.5	25.1	23.6
97.5°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	31.3	39.4	47.5
100°	30.7	29.5	28.4	27.2	28.4	29.5	30.7	31.9	53.9	96.8	139.7
102.5°	221.8	202.2	182.6	163.1	182.6	202.2	221.8	241.4	255.3	263.4	271.5
105°	385.8	385.6	385.2	385.0	385.2	385.6	385.8	386.1	386.2	386.2	386.2
107.5°	487.8	487.0	486.1	485.3	486.1	487.0	487.8	488.7	489.1	489.0	489.0
110°	553.9	554.1	554.5	554.7	554.5	554.1	553.9	553.6	553.9	554.7	555.6



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	618.2	617.8	617.3	616.9	617.3	617.8	618.2	618.5	619.3	620.4	621.5
115°	715.5	713.7	712.0	710.2	712.0	713.7	715.5	717.2	718.6	719.8	720.9
117.5°	812.1	811.3	810.5	809.8	810.5	811.3	812.1	812.8	813.9	815.5	816.9
120°	875.3	873.8	872.5	871.0	872.5	873.8	875.3	876.8	877.8	878.3	878.9
122.5°	934.1	932.4	930.7	929.0	930.7	932.4	934.1	935.7	936.9	937.5	938.0
125°	1020.0	1019.2	1018.3	1017.4	1018.3	1019.2	1020.0	1020.9	1021.9	1023.0	1024.2
127.5°	1098.2	1096.1	1094.0	1091.8	1094.0	1096.1	1098.2	1100.4	1101.7	1102.4	1103.0
130°	1150.1	1148.7	1147.2	1145.7	1147.2	1148.7	1150.1	1151.5	1152.7	1153.6	1154.4
132.5°	1199.9	1198.4	1197.0	1195.5	1197.0	1198.4	1199.9	1201.3	1202.1	1202.3	1202.5
135°	1268.9	1267.1	1265.4	1263.7	1265.4	1267.1	1268.9	1270.6	1271.8	1272.4	1272.9
137.5°	1336.6	1335.2	1333.6	1332.1	1333.6	1335.2	1336.6	1338.2	1338.9	1338.7	1338.6
140°	1377.8	1376.1	1374.3	1372.6	1374.3	1376.1	1377.8	1379.5	1380.1	1379.5	1378.9
142.5°	1416.1	1414.4	1412.6	1410.9	1412.6	1414.4	1416.1	1417.9	1418.7	1418.6	1418.4
145°	1472.4	1470.7	1469.0	1467.2	1469.0	1470.7	1472.4	1474.1	1474.8	1474.5	1474.3
147.5°	1519.8	1517.8	1515.7	1513.6	1515.7	1517.8	1519.8	1521.9	1522.8	1522.4	1522.1
150°	1550.6	1548.3	1546.0	1543.7	1546.0	1548.3	1550.6	1552.9	1553.8	1553.2	1552.6
152.5°	1577.9	1575.8	1573.7	1571.7	1573.7	1575.8	1577.9	1579.9	1580.7	1580.1	1579.6
155°	1615.4	1613.1	1610.8	1608.4	1610.8	1613.1	1615.4	1617.6	1618.4	1617.6	1616.7
157.5°	1646.2	1643.9	1641.6	1639.3	1641.6	1643.9	1646.2	1648.6	1649.2	1648.3	1647.4
160°	1665.9	1663.6	1661.3	1659.1	1661.3	1663.6	1665.9	1668.3	1668.8	1667.7	1666.5
162.5°	1684.3	1681.7	1679.2	1676.6	1679.2	1681.7	1684.3	1686.8	1687.2	1685.7	1684.0
165°	1707.4	1705.1	1702.8	1700.5	1702.8	1705.1	1707.4	1709.7	1710.0	1708.3	1706.5
167.5°	1724.8	1722.3	1719.7	1717.1	1719.7	1722.3	1724.8	1727.4	1727.7	1725.6	1723.5
170°	1734.2	1731.6	1729.0	1726.4	1729.0	1731.6	1734.2	1736.8	1736.9	1734.7	1732.3
172.5°	1740.4	1737.8	1735.3	1732.7	1735.3	1737.8	1740.4	1743.0	1743.3	1741.2	1739.1
175°	1748.4	1745.8	1743.3	1740.7	1743.3	1745.8	1748.4	1751.0	1751.2	1748.9	1746.5
177.5°	1750.8	1749.0	1747.1	1745.3	1747.1	1749.0	1750.8	1752.7	1752.8	1751.2	1749.6
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1007.2	1011.5	1016.8	1020.8	1027.9	1031.1	1035.1	1038.3	1044.0	1049.4	1055.8
5°	939.4	946.9	957.2	968.4	981.4	990.3	1002.8	1010.4	1025.6	1039.5	1052.8
7.5°	877.8	887.1	901.6	916.0	933.0	948.3	964.0	981.4	1000.7	1023.6	1042.6
10°	835.6	848.1	863.8	881.7	902.2	920.1	941.1	959.8	983.6	1010.4	1035.4
12.5°	801.9	812.7	830.2	847.3	869.3	891.1	912.8	937.7	965.4	995.1	1026.5
15°	755.5	764.5	778.8	802.5	824.8	846.4	879.0	902.2	937.1	970.2	1008.1
17.5°	715.9	727.0	739.1	759.4	782.6	809.4	838.5	867.7	901.3	943.2	986.1
20°	691.6	700.6	714.5	730.0	754.7	781.5	809.3	838.7	879.9	923.3	969.2
22.5°	665.1	674.9	690.4	707.6	728.2	754.0	784.5	816.9	859.8	902.5	952.4
25°	634.0	640.7	655.0	670.2	690.8	712.6	744.4	780.2	822.6	871.3	922.3
27.5°	604.5	610.4	623.5	636.7	655.3	681.3	709.7	745.8	785.8	835.3	891.7
30°	583.4	589.7	601.3	615.6	633.5	656.3	685.4	719.4	762.2	810.5	869.6
32.5°	565.2	570.8	579.5	593.8	611.3	633.4	660.3	695.0	738.0	787.0	844.9
35°	536.9	543.2	549.9	561.1	576.3	597.7	627.2	659.9	701.0	748.4	801.6
37.5°	508.9	515.7	521.7	531.7	545.5	564.5	590.0	624.0	661.2	706.8	757.9
40°	491.4	496.7	501.6	512.4	526.2	544.1	567.8	598.2	637.6	680.0	722.5
42.5°	473.8	478.8	483.0	492.3	505.1	522.3	544.9	574.5	611.1	650.7	688.1
45°	446.2	449.4	454.3	462.3	472.6	488.2	510.1	536.5	567.3	604.9	633.1
47.5°	416.3	421.2	425.2	432.3	440.7	456.1	477.1	499.6	527.5	555.4	575.3
50°	393.4	398.4	404.2	410.9	418.9	433.3	452.5	475.3	498.9	520.4	537.4
52.5°	372.0	376.5	382.7	389.1	398.9	411.0	427.4	447.7	471.1	486.5	500.6
55°	340.3	342.4	349.7	355.9	365.2	374.2	390.7	408.6	422.9	434.5	446.2
57.5°	307.8	310.8	315.0	320.6	329.8	340.4	352.0	367.7	376.2	382.2	391.2
60°	287.1	287.9	290.6	297.3	304.4	313.8	327.3	338.5	344.7	349.7	357.2
62.5°	264.2	264.3	268.8	273.7	279.1	289.2	300.1	309.1	314.3	316.7	324.0
65°	232.0	231.2	233.8	237.8	244.1	250.8	260.2	268.3	267.8	270.4	274.9
67.5°	199.2	198.3	198.3	202.2	207.2	213.3	219.7	224.4	224.5	228.0	230.2
70°	177.0	174.4	176.2	179.3	181.5	186.4	193.6	195.4	195.8	197.6	199.8
72.5°	154.1	153.3	154.7	156.0	157.6	161.4	167.5	168.6	168.7	169.7	173.4
75°	122.5	121.6	120.7	122.1	123.8	126.5	128.7	130.5	130.1	130.5	133.2
77.5°	91.9	89.3	88.9	89.6	90.1	91.6	93.9	93.8	94.3	94.2	97.2
80°	72.8	69.3	68.9	68.9	69.3	70.2	71.1	72.0	70.6	72.0	72.8
82.5°	53.6	51.4	51.3	51.0	51.1	51.2	51.7	52.3	52.0	52.7	53.2
85°	29.5	28.6	27.3	28.2	27.7	26.3	27.3	25.9	25.5	25.9	26.3
87.5°	14.5	14.6	13.4	13.0	12.2	12.2	11.0	10.2	9.4	9.3	9.9
90°	22.2	20.8	18.7	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3
92.5°	22.2	20.8	18.9	17.1	15.4	13.6	13.5	15.2	16.7	18.3	20.0
95°	22.2	20.8	31.7	42.6	53.6	64.5	70.4	71.3	72.2	73.0	73.9
97.5°	55.6	63.8	85.4	107.1	128.7	150.4	160.5	158.9	157.3	155.8	154.2
100°	182.6	225.5	224.4	223.3	222.1	220.9	219.9	219.0	218.2	217.3	216.5
102.5°	279.7	287.7	287.1	286.4	285.7	285.0	284.0	283.0	281.9	280.8	279.7
105°	386.2	386.2	386.2	386.2	386.2	386.2	385.6	384.5	383.4	382.2	381.1
107.5°	489.0	488.9	488.4	487.8	487.2	486.6	486.3	486.3	486.3	486.3	486.3
110°	556.5	557.3	556.7	556.2	555.6	555.0	554.7	554.7	554.7	554.7	554.7



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	622.6	623.7	623.4	623.0	622.7	622.3	621.8	621.1	620.4	619.7	619.1
115°	722.0	723.2	723.0	722.6	722.4	722.0	721.2	719.8	718.3	716.9	715.5
117.5°	818.4	819.9	818.8	817.7	816.7	815.5	815.0	815.1	815.1	815.2	815.3
120°	879.5	880.0	879.2	878.3	877.4	876.6	876.3	876.6	876.9	877.2	877.4
122.5°	938.6	939.2	938.7	938.3	938.0	937.5	936.8	935.7	934.6	933.5	932.5
125°	1025.4	1026.5	1026.5	1026.5	1026.5	1026.5	1025.5	1023.5	1021.5	1019.4	1017.4
127.5°	1103.6	1104.3	1104.5	1104.7	1104.8	1105.0	1104.3	1102.9	1101.5	1100.0	1098.5
130°	1155.3	1156.2	1155.8	1155.5	1155.3	1154.9	1154.1	1152.7	1151.2	1149.8	1148.3
132.5°	1202.6	1202.8	1203.4	1204.0	1204.7	1205.3	1204.8	1203.2	1201.4	1199.8	1198.1
135°	1273.5	1274.1	1274.6	1275.2	1275.8	1276.3	1275.8	1274.1	1272.4	1270.6	1268.9
137.5°	1338.5	1338.3	1338.9	1339.4	1339.9	1340.4	1340.0	1338.4	1337.0	1335.4	1333.9
140°	1378.4	1377.8	1378.0	1378.4	1378.6	1378.9	1378.8	1378.2	1377.6	1377.1	1376.5
142.5°	1418.3	1418.2	1417.8	1417.4	1417.0	1416.6	1416.2	1415.8	1415.5	1415.1	1414.8
145°	1473.9	1473.7	1473.7	1473.7	1473.7	1473.7	1473.4	1472.8	1472.2	1471.6	1471.1
147.5°	1521.7	1521.4	1521.0	1520.7	1520.4	1520.0	1519.8	1520.0	1520.1	1520.2	1520.4
150°	1552.0	1551.4	1550.8	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4
152.5°	1579.0	1578.4	1577.9	1577.3	1576.7	1576.1	1576.4	1577.7	1579.0	1580.3	1581.5
155°	1615.8	1615.0	1614.4	1613.8	1613.3	1612.7	1613.3	1615.0	1616.7	1618.4	1620.1
157.5°	1646.5	1645.5	1645.5	1645.5	1645.4	1645.3	1645.8	1646.8	1647.9	1648.9	1649.9
160°	1665.3	1664.2	1663.9	1663.6	1663.4	1663.0	1663.8	1665.5	1667.2	1669.0	1670.7
162.5°	1682.4	1680.8	1680.5	1680.2	1679.9	1679.6	1680.3	1682.0	1683.9	1685.6	1687.3
165°	1704.8	1703.1	1702.8	1702.5	1702.2	1701.9	1702.6	1704.3	1706.1	1707.9	1709.6
167.5°	1721.5	1719.4	1719.2	1718.8	1718.6	1718.3	1719.0	1720.8	1722.6	1724.4	1726.1
170°	1730.0	1727.7	1727.4	1727.2	1726.8	1726.6	1727.4	1729.4	1731.5	1733.5	1735.5
172.5°	1737.1	1735.0	1734.5	1734.0	1733.5	1732.9	1733.6	1735.7	1737.7	1739.7	1741.7
175°	1744.3	1742.0	1741.7	1741.4	1741.1	1740.9	1741.5	1743.3	1745.0	1746.7	1748.4
177.5°	1748.0	1746.4	1746.1	1745.9	1745.7	1745.4	1746.0	1747.4	1748.8	1750.2	1751.5
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1059.0	1064.0	1067.3	1073.3	1078.3	1081.2	1083.7	1085.9	1088.4	1090.5	1096.6
5°	1065.8	1077.5	1087.3	1102.5	1116.4	1127.0	1138.7	1149.0	1157.5	1169.6	1179.0
7.5°	1062.9	1083.6	1105.2	1128.7	1152.7	1175.1	1195.7	1214.9	1232.3	1253.4	1272.0
10°	1060.1	1088.2	1115.9	1147.6	1180.3	1208.0	1233.9	1260.3	1279.5	1306.4	1329.1
12.5°	1057.9	1091.1	1124.5	1162.7	1198.5	1237.7	1272.2	1291.4	1320.7	1342.1	1369.2
15°	1048.9	1092.7	1138.7	1181.6	1232.6	1268.8	1299.2	1336.8	1364.0	1391.3	1420.8
17.5°	1032.7	1082.3	1133.8	1190.1	1239.0	1277.8	1317.0	1353.2	1385.8	1422.4	1459.1
20°	1025.2	1074.8	1133.8	1191.5	1239.3	1280.0	1320.3	1360.0	1395.8	1442.7	1485.2
22.5°	1009.4	1069.4	1123.8	1180.0	1229.2	1273.6	1319.1	1364.3	1411.9	1464.9	1518.1
25°	981.4	1042.2	1099.8	1155.3	1204.9	1260.3	1309.1	1369.4	1430.2	1500.4	1566.6
27.5°	952.2	1010.4	1063.2	1116.8	1174.7	1237.4	1300.6	1369.2	1448.7	1537.3	1630.6
30°	928.6	983.6	1035.0	1089.9	1150.3	1221.0	1290.3	1371.7	1463.7	1563.4	1674.3
32.5°	901.0	951.7	1001.7	1060.0	1125.7	1200.2	1281.0	1370.2	1480.9	1594.2	1708.3
35°	853.9	896.4	947.8	1010.0	1084.2	1169.6	1263.0	1368.5	1495.5	1625.6	1721.7
37.5°	798.1	837.6	891.7	959.8	1037.7	1129.3	1240.2	1365.4	1500.2	1604.0	1635.0
40°	760.5	797.1	853.5	924.1	1003.7	1100.7	1222.3	1354.6	1485.2	1551.3	1525.9
42.5°	720.4	758.9	813.7	883.7	969.4	1075.0	1199.8	1332.1	1441.6	1466.6	1378.5
45°	657.2	697.0	751.1	821.7	913.9	1028.3	1158.4	1278.7	1341.7	1296.5	1160.2
47.5°	598.5	635.8	685.9	758.8	853.9	972.2	1097.5	1193.4	1198.4	1090.7	945.0
50°	558.4	592.8	643.3	716.2	810.5	930.4	1043.4	1119.0	1085.0	963.0	823.0
52.5°	519.1	552.8	602.6	674.8	768.0	877.8	983.0	1036.0	972.1	846.8	727.2
55°	462.3	491.8	540.5	607.1	695.7	797.6	887.0	905.3	822.2	698.8	601.8
57.5°	406.8	434.4	478.7	540.1	621.0	711.3	781.2	777.3	689.4	583.5	506.5
60°	369.3	396.1	435.5	495.3	569.1	647.0	706.8	692.5	605.4	514.1	449.4
62.5°	335.7	359.6	396.8	449.2	516.5	588.7	637.8	616.7	531.3	451.5	400.3
65°	286.1	306.3	338.0	382.7	438.6	498.1	536.1	508.8	435.9	373.8	332.6
67.5°	238.8	254.9	281.5	317.3	364.9	412.7	435.8	408.4	350.1	304.7	274.2
70°	208.8	223.1	243.7	275.4	317.0	357.2	374.6	350.1	300.0	261.1	239.2
72.5°	178.7	190.5	208.6	237.1	270.4	305.4	320.6	297.1	256.0	223.2	202.7
75°	138.2	146.2	158.7	178.4	204.7	232.5	241.0	220.4	194.1	169.4	156.0
77.5°	98.9	105.7	115.2	127.6	146.3	163.9	171.3	159.5	139.1	123.5	112.4
80°	76.0	79.6	87.6	97.9	112.7	123.8	128.7	121.1	106.9	95.2	86.7
82.5°	54.2	57.8	62.6	71.1	80.5	88.1	93.3	88.3	77.9	68.8	63.8
85°	26.3	28.6	31.3	34.9	42.0	46.5	46.1	42.9	38.9	35.3	32.6
87.5°	10.0	10.8	12.4	14.6	16.1	18.0	19.1	18.8	17.7	17.0	16.2
90°	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.8	22.2	23.6
92.5°	18.3	16.7	15.2	13.5	13.6	15.4	17.1	18.9	20.8	22.2	23.6
95°	73.0	72.2	71.3	70.4	64.5	53.6	42.6	31.7	20.8	22.2	23.6
97.5°	155.8	157.3	158.9	160.5	150.4	128.7	107.1	85.4	63.8	55.6	47.5
100°	217.3	218.2	219.0	219.9	220.9	222.1	223.3	224.4	225.5	182.6	139.7
102.5°	280.8	281.9	283.0	284.0	285.0	285.7	286.4	287.1	287.7	279.7	271.5
105°	382.2	383.4	384.5	385.6	386.2	386.2	386.2	386.2	386.2	386.2	386.2
107.5°	486.3	486.3	486.3	486.3	486.6	487.2	487.8	488.4	488.9	489.0	489.0
110°	554.7	554.7	554.7	554.7	555.0	555.6	556.2	556.7	557.3	556.5	555.6



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	619.7	620.4	621.1	621.8	622.3	622.7	623.0	623.4	623.7	622.6	621.5
115°	716.9	718.3	719.8	721.2	722.0	722.4	722.6	723.0	723.2	722.0	720.9
117.5°	815.2	815.1	815.1	815.0	815.5	816.7	817.7	818.8	819.9	818.4	816.9
120°	877.2	876.9	876.6	876.3	876.6	877.4	878.3	879.2	880.0	879.5	878.9
122.5°	933.5	934.6	935.7	936.8	937.5	938.0	938.3	938.7	939.2	938.6	938.0
125°	1019.4	1021.5	1023.5	1025.5	1026.5	1026.5	1026.5	1026.5	1026.5	1025.4	1024.2
127.5°	1100.0	1101.5	1102.9	1104.3	1105.0	1104.8	1104.7	1104.5	1104.3	1103.6	1103.0
130°	1149.8	1151.2	1152.7	1154.1	1154.9	1155.3	1155.5	1155.8	1156.2	1155.3	1154.4
132.5°	1199.8	1201.4	1203.2	1204.8	1205.3	1204.7	1204.0	1203.4	1202.8	1202.6	1202.5
135°	1270.6	1272.4	1274.1	1275.8	1276.3	1275.8	1275.2	1274.6	1274.1	1273.5	1272.9
137.5°	1335.4	1337.0	1338.4	1340.0	1340.4	1339.9	1339.4	1338.9	1338.3	1338.5	1338.6
140°	1377.1	1377.6	1378.2	1378.8	1378.9	1378.6	1378.4	1378.0	1377.8	1378.4	1378.9
142.5°	1415.1	1415.5	1415.8	1416.2	1416.6	1417.0	1417.4	1417.8	1418.2	1418.3	1418.4
145°	1471.6	1472.2	1472.8	1473.4	1473.7	1473.7	1473.7	1473.7	1473.7	1473.9	1474.3
147.5°	1520.2	1520.1	1520.0	1519.8	1520.0	1520.4	1520.7	1521.0	1521.4	1521.7	1522.1
150°	1550.8	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1552.0	1552.6
152.5°	1580.3	1579.0	1577.7	1576.4	1576.1	1576.7	1577.3	1577.9	1578.4	1579.0	1579.6
155°	1618.4	1616.7	1615.0	1613.3	1612.7	1613.3	1613.8	1614.4	1615.0	1615.8	1616.7
157.5°	1648.9	1647.9	1646.8	1645.8	1645.3	1645.4	1645.5	1645.5	1645.5	1646.5	1647.4
160°	1669.0	1667.2	1665.5	1663.8	1663.0	1663.4	1663.6	1663.9	1664.2	1665.3	1666.5
162.5°	1685.6	1683.9	1682.0	1680.3	1679.6	1679.9	1680.2	1680.5	1680.8	1682.4	1684.0
165°	1707.9	1706.1	1704.3	1702.6	1701.9	1702.2	1702.5	1702.8	1703.1	1704.8	1706.5
167.5°	1724.4	1722.6	1720.8	1719.0	1718.3	1718.6	1718.8	1719.2	1719.4	1721.5	1723.5
170°	1733.5	1731.5	1729.4	1727.4	1726.6	1726.8	1727.2	1727.4	1727.7	1730.0	1732.3
172.5°	1739.7	1737.7	1735.7	1733.6	1732.9	1733.5	1734.0	1734.5	1735.0	1737.1	1739.1
175°	1746.7	1745.0	1743.3	1741.5	1740.9	1741.1	1741.4	1741.7	1742.0	1744.3	1746.5
177.5°	1750.2	1748.8	1747.4	1746.0	1745.4	1745.7	1745.9	1746.1	1746.4	1748.0	1749.6
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3	1053.3
2.5°	1101.6	1104.5	1110.5	1108.4	1111.3	1112.7	1114.1
5°	1190.6	1204.9	1211.2	1210.2	1219.6	1217.4	1215.1
7.5°	1291.1	1306.1	1314.5	1325.0	1331.0	1331.5	1336.8
10°	1348.0	1367.6	1375.7	1386.8	1394.0	1398.0	1397.6
12.5°	1391.5	1407.0	1425.0	1430.5	1440.1	1445.2	1443.4
15°	1444.1	1468.7	1487.5	1496.8	1508.9	1512.4	1517.4
17.5°	1490.9	1523.9	1545.8	1574.9	1586.0	1592.7	1588.7
20°	1526.3	1569.7	1591.6	1626.5	1645.7	1656.0	1652.4
22.5°	1568.1	1615.1	1655.6	1685.8	1715.1	1729.0	1731.8
25°	1639.9	1704.3	1763.8	1803.5	1839.7	1848.2	1867.0
27.5°	1720.0	1796.0	1859.5	1901.3	1926.6	1936.0	1941.9
30°	1770.5	1846.0	1893.9	1920.6	1928.7	1927.8	1926.9
32.5°	1795.1	1842.5	1851.6	1844.1	1825.7	1810.2	1793.9
35°	1760.1	1724.8	1672.1	1604.1	1554.0	1503.6	1498.6
37.5°	1583.0	1470.1	1382.2	1284.2	1227.6	1192.7	1168.5
40°	1416.3	1288.1	1181.6	1098.9	1041.2	1018.5	996.1
42.5°	1235.4	1112.8	1018.6	949.4	906.0	880.7	863.1
45°	1003.7	895.5	821.7	771.6	737.3	717.6	706.4
47.5°	822.4	742.4	679.8	643.6	619.8	604.5	604.6
50°	725.1	648.7	607.1	578.5	557.9	545.9	548.1
52.5°	638.9	581.9	546.3	522.4	507.1	499.7	499.5
55°	534.3	493.1	469.8	452.5	442.1	433.7	435.5
57.5°	457.0	422.3	406.7	392.3	385.1	381.7	376.8
60°	409.1	382.3	368.9	357.2	350.1	347.4	342.4
62.5°	366.5	345.4	332.3	322.9	316.4	315.6	311.7
65°	308.1	292.0	280.3	275.9	269.1	267.3	267.3
67.5°	253.9	242.4	233.4	229.3	226.3	226.8	224.6
70°	220.0	210.6	204.7	200.3	198.0	198.5	196.7
72.5°	192.4	181.9	176.8	174.2	171.3	172.4	171.7
75°	145.8	140.3	137.7	135.0	133.2	132.3	131.5
77.5°	107.0	102.3	100.2	98.8	99.0	96.9	98.5
80°	82.7	78.7	77.3	75.1	74.6	74.6	74.2
82.5°	60.5	58.3	57.3	55.4	54.7	55.4	54.2
85°	31.3	29.5	29.1	29.1	28.2	27.3	29.5
87.5°	16.4	15.3	15.6	15.3	15.5	15.3	14.8
90°	25.1	26.5	27.6	28.5	29.4	30.2	31.1
92.5°	25.1	26.5	27.4	27.8	28.2	28.7	29.0
95°	25.1	26.5	27.2	27.2	27.2	27.2	27.2
97.5°	39.4	31.3	27.2	27.2	27.2	27.2	27.2
100°	96.8	53.9	31.9	30.7	29.5	28.4	27.2
102.5°	263.4	255.3	241.4	221.8	202.2	182.6	163.1
105°	386.2	386.2	386.1	385.8	385.6	385.2	385.0
107.5°	489.0	489.1	488.7	487.8	487.0	486.1	485.3
110°	554.7	553.9	553.6	553.9	554.1	554.5	554.7



TEST NUMBER: P333424-935

CATALOG NUMBER: S125DIW-S850D1560U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	620.4	619.3	618.5	618.2	617.8	617.3	616.9
115°	719.8	718.6	717.2	715.5	713.7	712.0	710.2
117.5°	815.5	813.9	812.8	812.1	811.3	810.5	809.8
120°	878.3	877.8	876.8	875.3	873.8	872.5	871.0
122.5°	937.5	936.9	935.7	934.1	932.4	930.7	929.0
125°	1023.0	1021.9	1020.9	1020.0	1019.2	1018.3	1017.4
127.5°	1102.4	1101.7	1100.4	1098.2	1096.1	1094.0	1091.8
130°	1153.6	1152.7	1151.5	1150.1	1148.7	1147.2	1145.7
132.5°	1202.3	1202.1	1201.3	1199.9	1198.4	1197.0	1195.5
135°	1272.4	1271.8	1270.6	1268.9	1267.1	1265.4	1263.7
137.5°	1338.7	1338.9	1338.2	1336.6	1335.2	1333.6	1332.1
140°	1379.5	1380.1	1379.5	1377.8	1376.1	1374.3	1372.6
142.5°	1418.6	1418.7	1417.9	1416.1	1414.4	1412.6	1410.9
145°	1474.5	1474.8	1474.1	1472.4	1470.7	1469.0	1467.2
147.5°	1522.4	1522.8	1521.9	1519.8	1517.8	1515.7	1513.6
150°	1553.2	1553.8	1552.9	1550.6	1548.3	1546.0	1543.7
152.5°	1580.1	1580.7	1579.9	1577.9	1575.8	1573.7	1571.7
155°	1617.6	1618.4	1617.6	1615.4	1613.1	1610.8	1608.4
157.5°	1648.3	1649.2	1648.6	1646.2	1643.9	1641.6	1639.3
160°	1667.7	1668.8	1668.3	1665.9	1663.6	1661.3	1659.1
162.5°	1685.7	1687.2	1686.8	1684.3	1681.7	1679.2	1676.6
165°	1708.3	1710.0	1709.7	1707.4	1705.1	1702.8	1700.5
167.5°	1725.6	1727.7	1727.4	1724.8	1722.3	1719.7	1717.1
170°	1734.7	1736.9	1736.8	1734.2	1731.6	1729.0	1726.4
172.5°	1741.2	1743.3	1743.0	1740.4	1737.8	1735.3	1732.7
175°	1748.9	1751.2	1751.0	1748.4	1745.8	1743.3	1740.7
177.5°	1751.2	1752.8	1752.7	1750.8	1749.0	1747.1	1745.3
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4

(END OF REPORT)