

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333726-830

Luminaire Tested: **S125RDIW-S1270D770U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333726-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D770U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7491.6 lumens
Efficiency: N/A
Efficacy: 125.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333726-830

CATALOG NUMBER: S125RDIW-S1270D770U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333726-830

CATALOG NUMBER: S125RDIW-S1270D770U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	50	48	44
3	84	74	67	61	78	70	63	58	62	57	52	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	45	39	34	39	35	31	34	31	28	25
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25	22
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12566	12566	12566
5°	12595	12452	12528
10°	12499	12336	12336
15°	12351	12085	11987
20°	12160	11736	11595
25°	11938	11393	11142
30°	11660	10992	10641
35°	11378	10578	10080
40°	11113	10146	9528
45°	10791	9664	8925
50°	10468	9139	8298
55°	10094	8637	7629
60°	9719	8029	6909
65°	9274	7321	6085
70°	8769	6437	5246
75°	8067	5425	4362
80°	7107	4262	3663
85°	5995	3483	3268



TEST NUMBER: P333726-830

CATALOG NUMBER: S125RDIW-S1270D770U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	2.4
10°-20°	511.3	6.8
20°-30°	741.4	9.9
30°-40°	845.0	11.3
40°-50°	823.6	11.0
50°-60°	693.3	9.3
60°-70°	486.0	6.5
70°-80°	249.8	3.3
80°-90°	65.1	0.9
90°-100°	34.2	0.5
100°-110°	211.0	2.8
110°-120°	382.7	5.1
120°-130°	491.1	6.6
130°-140°	528.2	7.1
140°-150°	495.8	6.6
150°-160°	401.1	5.4
160°-170°	259.4	3.5
170°-180°	89.5	1.2
0°-30°	1435.7	19.2
0°-40°	2280.6	30.4
0°-60°	3797.6	50.7
0°-90°	4598.5	61.4
90°-120°	627.9	8.4
90°-150°	2143.1	28.6
90°-180°	2893.0	38.6
0°-180°	7491.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1946	1946	1946	1946	1946	
5°	1943	1936	1921	1934	1932	184
15°	1847	1837	1808	1805	1793	520
25°	1675	1651	1599	1580	1564	770
35°	1443	1406	1342	1300	1278	903
45°	1182	1137	1058	1001	977	911
55°	896	847	767	703	678	802
65°	607	555	479	422	398	601
75°	323	278	217	186	175	342
85°	81	55	47	46	44	91
90°	1	6	11	15	17	5
95°	40	36	11	14	15	51
105°	205	208	208	208	208	218
115°	386	389	390	387	383	382
125°	548	553	553	550	548	489
135°	684	688	686	685	681	527
145°	793	794	794	794	791	496
155°	873	869	870	872	867	402
165°	921	917	918	921	916	260
175°	942	938	939	944	938	90
180°	942	942	942	942	942	



TEST NUMBER: P333726-830

CATALOG NUMBER: S125RDIW-S1270D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1949.2	1948.4	1947.6	1946.8	1946.1	1944.4	1941.7	1939.1	1936.5	1933.9	1936.5
5°	1942.8	1941.4	1940.1	1938.8	1937.5	1935.0	1931.5	1927.9	1924.3	1920.7	1923.9
7.5°	1923.6	1922.4	1921.2	1919.9	1918.6	1915.9	1911.6	1907.2	1903.0	1898.7	1900.9
10°	1906.0	1905.0	1904.0	1903.1	1902.1	1899.3	1894.7	1890.2	1885.6	1881.0	1882.0
12.5°	1886.0	1884.8	1883.5	1882.3	1881.0	1877.4	1871.2	1865.1	1858.9	1852.8	1853.5
15°	1847.2	1845.2	1843.3	1841.4	1839.4	1834.9	1828.1	1821.3	1814.4	1807.5	1807.2
17.5°	1803.4	1800.4	1797.4	1794.4	1791.4	1785.6	1777.0	1768.3	1759.7	1751.1	1749.5
20°	1769.3	1766.0	1762.7	1759.5	1756.2	1749.4	1739.0	1728.5	1718.1	1707.6	1706.0
22.5°	1731.7	1728.4	1725.1	1721.9	1718.6	1711.6	1700.5	1689.6	1678.6	1667.6	1664.4
25°	1675.3	1670.4	1665.5	1660.6	1655.7	1647.2	1635.1	1623.1	1610.9	1598.8	1594.6
27.5°	1610.6	1604.7	1598.7	1592.8	1586.9	1577.4	1564.4	1551.5	1538.6	1525.7	1519.8
30°	1563.6	1557.4	1551.1	1545.0	1538.8	1528.8	1515.0	1501.4	1487.6	1473.9	1466.4
32.5°	1517.8	1510.5	1503.3	1496.0	1488.7	1478.1	1464.1	1450.2	1436.2	1422.2	1413.9
35°	1443.1	1435.2	1427.4	1419.6	1411.7	1400.4	1385.7	1371.1	1356.4	1341.7	1332.2
37.5°	1369.9	1360.4	1350.9	1341.3	1331.7	1319.4	1304.3	1289.1	1273.9	1258.8	1247.5
40°	1318.1	1308.3	1298.5	1288.7	1279.0	1266.2	1250.6	1234.9	1219.2	1203.5	1191.2
42.5°	1264.1	1254.1	1244.0	1233.9	1223.9	1210.7	1194.6	1178.4	1162.2	1145.9	1134.1
45°	1181.5	1172.1	1162.5	1153.1	1143.6	1129.9	1111.9	1094.0	1076.0	1058.1	1045.0
47.5°	1096.0	1086.0	1076.0	1066.0	1056.0	1042.0	1023.9	1005.8	987.7	969.6	956.1
50°	1041.9	1031.1	1020.3	1009.6	998.8	984.1	965.4	946.9	928.2	909.6	895.9
52.5°	983.1	972.0	961.0	950.0	939.0	924.6	907.1	889.6	871.9	854.4	839.6
55°	896.5	886.0	875.5	865.1	854.6	840.3	822.0	803.7	785.4	767.1	752.4
57.5°	808.8	797.7	786.5	775.3	764.1	749.8	732.2	714.4	696.8	679.2	664.9
60°	752.4	740.9	729.5	718.1	706.7	692.1	674.5	656.9	639.2	621.6	607.3
62.5°	692.5	681.6	670.6	659.7	648.8	634.4	616.5	598.6	580.7	562.8	549.5
65°	606.9	595.8	584.8	573.6	562.5	548.3	531.0	513.7	496.3	479.1	466.0
67.5°	522.0	510.9	499.7	488.7	477.6	463.7	447.1	430.6	414.0	397.4	385.4
70°	464.4	453.3	442.1	431.0	420.0	406.2	389.9	373.6	357.2	340.9	330.8
72.5°	407.9	397.1	386.3	375.4	364.6	351.5	336.2	320.9	305.7	290.4	281.1
75°	323.3	313.5	303.7	293.9	284.1	272.4	258.6	245.0	231.2	217.4	210.3
77.5°	239.2	231.4	223.6	215.7	207.9	198.5	187.5	176.5	165.6	154.6	149.6
80°	191.1	183.2	175.4	167.5	159.7	151.2	142.0	132.9	123.8	114.6	111.7
82.5°	144.0	137.0	129.9	122.8	115.8	109.1	102.8	96.6	90.3	84.1	82.7
85°	80.9	74.9	69.1	63.2	57.3	53.5	51.9	50.3	48.6	47.0	46.7
87.5°	27.1	25.6	24.0	22.4	20.8	20.1	20.0	20.0	19.9	19.9	20.0
90°	0.7	2.0	3.2	4.4	5.7	6.8	7.9	9.0	10.1	11.2	12.0
92.5°	10.7	9.9	9.0	8.1	7.3	7.4	8.3	9.2	10.2	11.2	12.0
95°	39.8	39.3	38.8	38.5	38.0	34.8	28.8	23.0	17.1	11.2	12.0
97.5°	83.1	84.0	84.8	85.6	86.4	81.1	69.4	57.7	46.0	34.4	30.0
100°	116.6	117.1	117.5	118.0	118.5	119.0	119.7	120.3	120.9	121.5	98.4
102.5°	150.7	151.3	151.9	152.5	153.1	153.5	153.9	154.3	154.7	155.0	150.7
105°	205.3	205.9	206.6	207.2	207.8	208.1	208.1	208.1	208.1	208.1	208.1
107.5°	262.0	262.0	262.0	262.0	262.0	262.2	262.5	262.8	263.2	263.4	263.4
110°	298.9	298.9	298.9	298.9	298.9	299.1	299.4	299.7	300.0	300.3	299.8



TEST NUMBER: P333726-830

CATALOG NUMBER: S125RDIW-S1270D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.6	333.9	334.3	334.7	335.1	335.4	335.5	335.7	335.9	336.1	335.5
115°	385.5	386.3	387.1	387.9	388.6	389.1	389.3	389.4	389.6	389.7	389.1
117.5°	439.3	439.2	439.2	439.2	439.1	439.4	440.1	440.6	441.2	441.8	441.0
120°	472.8	472.7	472.5	472.3	472.2	472.3	472.8	473.3	473.7	474.2	473.9
122.5°	502.4	503.0	503.6	504.2	504.8	505.2	505.4	505.6	505.9	506.1	505.8
125°	548.3	549.3	550.4	551.5	552.6	553.1	553.1	553.1	553.1	553.1	552.5
127.5°	591.9	592.8	593.5	594.3	595.0	595.4	595.3	595.2	595.1	595.0	594.7
130°	618.8	619.5	620.3	621.1	621.9	622.4	622.5	622.6	622.8	622.9	622.5
132.5°	645.5	646.5	647.4	648.3	649.2	649.5	649.1	648.8	648.5	648.1	648.0
135°	683.7	684.7	685.6	686.5	687.5	687.8	687.5	687.1	686.8	686.5	686.2
137.5°	718.8	719.6	720.4	721.2	722.0	722.3	722.0	721.7	721.4	721.1	721.2
140°	741.7	742.0	742.3	742.6	742.9	743.0	742.8	742.7	742.5	742.3	742.7
142.5°	762.3	762.5	762.7	762.9	763.1	763.3	763.6	763.7	763.9	764.2	764.2
145°	792.7	793.0	793.3	793.6	793.9	794.1	794.1	794.1	794.1	794.1	794.2
147.5°	819.3	819.2	819.1	819.1	819.0	819.1	819.3	819.4	819.5	819.7	819.9
150°	835.9	835.7	835.4	835.0	834.7	834.7	835.0	835.4	835.7	835.9	836.3
152.5°	852.2	851.5	850.8	850.2	849.4	849.2	849.6	849.9	850.2	850.5	850.8
155°	873.0	872.0	871.1	870.2	869.3	868.9	869.3	869.6	869.9	870.2	870.6
157.5°	889.0	888.5	888.0	887.4	886.8	886.6	886.6	886.6	886.6	886.6	887.2
160°	900.2	899.3	898.3	897.4	896.5	896.1	896.3	896.5	896.5	896.7	897.4
162.5°	909.2	908.2	907.3	906.3	905.4	905.0	905.2	905.4	905.5	905.7	906.5
165°	921.1	920.2	919.4	918.4	917.5	917.1	917.2	917.4	917.6	917.7	918.6
167.5°	930.1	929.2	928.2	927.3	926.2	925.9	926.0	926.1	926.3	926.5	927.6
170°	935.2	934.1	932.9	931.9	930.8	930.3	930.5	930.7	930.8	930.9	932.2
172.5°	938.5	937.5	936.3	935.2	934.2	933.8	934.1	934.3	934.6	934.9	935.9
175°	942.2	941.2	940.3	939.3	938.4	938.0	938.2	938.3	938.5	938.7	939.9
177.5°	943.8	943.0	942.4	941.6	940.8	940.5	940.7	940.8	940.8	941.0	941.9
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333726-830

CATALOG NUMBER: S125RDIW-S1270D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7	1945.7
2.5°	1939.1	1941.7	1944.4	1945.5	1945.3	1945.0	1944.7	1944.5
5°	1927.2	1930.5	1933.7	1935.0	1934.4	1933.7	1933.1	1932.4
7.5°	1903.2	1905.5	1907.8	1908.6	1907.8	1907.1	1906.4	1905.7
10°	1882.9	1884.0	1884.9	1884.9	1884.0	1882.9	1882.0	1881.0
12.5°	1854.3	1854.9	1855.7	1855.3	1853.8	1852.3	1850.8	1849.3
15°	1806.9	1806.6	1806.2	1804.6	1801.7	1798.7	1795.7	1792.8
17.5°	1747.9	1746.2	1744.6	1742.6	1740.1	1737.7	1735.3	1732.9
20°	1704.3	1702.7	1701.1	1698.7	1695.8	1692.9	1690.0	1687.1
22.5°	1661.2	1658.0	1654.8	1652.0	1649.6	1647.2	1644.7	1642.4
25°	1590.4	1586.1	1581.9	1577.9	1574.3	1570.7	1567.2	1563.6
27.5°	1513.8	1507.9	1501.9	1497.2	1493.7	1490.3	1486.8	1483.4
30°	1459.0	1451.4	1443.9	1438.7	1435.8	1432.8	1429.8	1426.9
32.5°	1405.6	1397.3	1389.0	1383.0	1379.3	1375.5	1371.9	1368.1
35°	1322.8	1313.2	1303.8	1296.8	1292.2	1287.6	1283.1	1278.5
37.5°	1236.1	1224.7	1213.3	1205.4	1201.0	1196.6	1192.1	1187.7
40°	1178.7	1166.3	1154.0	1145.8	1141.8	1137.9	1134.0	1130.1
42.5°	1122.2	1110.3	1098.4	1089.6	1083.8	1078.1	1072.3	1066.6
45°	1031.9	1018.9	1005.8	996.8	991.9	987.0	982.1	977.2
47.5°	942.7	929.3	915.8	906.3	900.9	895.5	890.0	884.7
50°	882.2	868.5	854.8	845.5	840.6	835.7	830.8	825.9
52.5°	824.8	810.1	795.3	785.5	780.6	775.7	770.8	765.9
55°	737.7	723.0	708.3	698.3	693.1	687.9	682.7	677.5
57.5°	650.4	636.1	621.7	612.3	607.6	602.9	598.3	593.7
60°	592.9	578.5	564.1	554.5	549.6	544.7	539.8	534.9
62.5°	536.2	522.8	509.5	500.4	495.5	490.6	485.7	480.8
65°	453.0	439.9	426.8	417.8	412.9	408.0	403.1	398.2
67.5°	373.4	361.5	349.6	341.6	337.7	333.8	329.9	325.9
70°	320.7	310.6	300.5	293.4	289.5	285.6	281.6	277.8
72.5°	271.7	262.4	253.0	247.0	244.4	241.9	239.2	236.6
75°	203.1	196.0	188.8	184.0	181.7	179.5	177.2	174.8
77.5°	144.5	139.5	134.5	131.1	129.4	127.7	126.0	124.3
80°	108.8	105.8	102.8	101.0	100.4	99.7	99.2	98.5
82.5°	81.3	79.9	78.6	77.7	77.3	76.9	76.5	76.2
85°	46.4	46.1	45.7	45.4	45.1	44.8	44.4	44.1
87.5°	20.2	20.4	20.5	20.5	20.4	20.2	20.0	19.8
90°	12.7	13.5	14.2	14.9	15.4	15.8	16.3	16.8
92.5°	12.7	13.5	14.2	14.8	15.0	15.2	15.5	15.6
95°	12.7	13.5	14.2	14.7	14.7	14.7	14.7	14.7
97.5°	25.6	21.2	16.9	14.7	14.7	14.7	14.7	14.7
100°	75.3	52.1	29.0	17.2	16.5	15.9	15.3	14.7
102.5°	146.3	141.9	137.5	130.1	119.5	109.0	98.4	87.8
105°	208.1	208.1	208.1	208.0	207.9	207.7	207.5	207.5
107.5°	263.5	263.5	263.5	263.3	262.9	262.4	261.9	261.5
110°	299.4	298.9	298.4	298.3	298.4	298.6	298.8	298.9



TEST NUMBER: P333726-830

CATALOG NUMBER: S125RDIW-S1270D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	334.9	334.3	333.7	333.3	333.1	332.9	332.6	332.4
115°	388.4	387.9	387.2	386.4	385.5	384.6	383.6	382.7
117.5°	440.2	439.4	438.6	438.0	437.5	437.2	436.8	436.4
120°	473.6	473.3	473.0	472.4	471.6	470.9	470.1	469.3
122.5°	505.4	505.1	504.8	504.2	503.3	502.4	501.5	500.6
125°	551.9	551.3	550.6	550.1	549.6	549.1	548.7	548.3
127.5°	594.4	594.0	593.7	593.0	591.7	590.6	589.5	588.3
130°	622.1	621.6	621.1	620.5	619.7	619.0	618.1	617.4
132.5°	647.9	647.8	647.7	647.3	646.5	645.7	645.0	644.2
135°	685.9	685.6	685.3	684.7	683.7	682.8	681.8	680.9
137.5°	721.3	721.3	721.4	721.0	720.2	719.4	718.6	717.8
140°	743.0	743.3	743.7	743.3	742.3	741.5	740.6	739.6
142.5°	764.3	764.4	764.4	764.0	763.1	762.1	761.2	760.3
145°	794.4	794.6	794.7	794.3	793.3	792.4	791.5	790.6
147.5°	820.1	820.3	820.5	820.0	819.0	817.8	816.7	815.6
150°	836.6	836.9	837.3	836.8	835.5	834.2	833.0	831.8
152.5°	851.1	851.4	851.8	851.3	850.2	849.1	848.0	846.9
155°	871.1	871.6	872.0	871.7	870.4	869.2	868.0	866.7
157.5°	887.7	888.2	888.6	888.3	887.0	885.8	884.6	883.4
160°	898.0	898.6	899.2	898.9	897.7	896.5	895.2	893.9
162.5°	907.4	908.2	909.2	908.9	907.6	906.2	904.8	903.4
165°	919.5	920.5	921.4	921.2	920.0	918.8	917.6	916.2
167.5°	928.7	929.8	930.9	930.9	929.4	928.0	926.6	925.2
170°	933.4	934.7	935.9	935.9	934.4	933.0	931.6	930.3
172.5°	937.1	938.2	939.3	939.1	937.8	936.4	935.0	933.6
175°	941.1	942.4	943.6	943.5	942.2	940.8	939.3	937.9
177.5°	942.7	943.6	944.5	944.4	943.4	942.4	941.4	940.5
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2

(END OF REPORT)