

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333650-830

Luminaire Tested: **S125RDIW-S375D1050U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333650-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1050U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5314.1 lumens
Efficiency: N/A
Efficacy: 139.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333650-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333650-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34	26
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29	22
2	84	77	71	66	75	69	64	60	54	50	48	40	37	36	26	25	24	18
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	19	18	14
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16	12
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14	10
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	9
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10	8
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3725	3725	3725
5°	3734	3691	3713
10°	3705	3657	3657
15°	3661	3582	3553
20°	3604	3478	3437
25°	3539	3377	3302
30°	3456	3258	3155
35°	3372	3136	2988
40°	3295	3008	2824
45°	3199	2865	2645
50°	3104	2710	2460
55°	2992	2559	2262
60°	2880	2381	2047
65°	2749	2170	1803
70°	2598	1907	1554
75°	2393	1609	1293
80°	2105	1261	1086
85°	1771	1030	971



TEST NUMBER: P333650-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	1.0
10°-20°	151.6	2.9
20°-30°	219.8	4.1
30°-40°	250.5	4.7
40°-50°	244.1	4.6
50°-60°	205.5	3.9
60°-70°	144.1	2.7
70°-80°	74.1	1.4
80°-90°	21.4	0.4
90°-100°	46.7	0.9
100°-110°	288.0	5.4
110°-120°	522.3	9.8
120°-130°	670.4	12.6
130°-140°	721.0	13.6
140°-150°	676.8	12.7
150°-160°	547.5	10.3
160°-170°	354.1	6.7
170°-180°	122.1	2.3
0°-30°	425.6	8.0
0°-40°	676.0	12.7
0°-60°	1125.7	21.2
0°-90°	1365.2	25.7
90°-120°	857.1	16.1
90°-150°	2925.3	55.0
90°-180°	3949.0	74.3
0°-180°	5314.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	576	574	569	573	573	55
15°	548	545	536	535	531	154
25°	497	490	474	468	463	228
35°	428	417	398	385	379	268
45°	350	337	314	297	290	270
55°	266	251	227	208	201	238
65°	180	165	142	125	118	178
75°	96	83	64	55	52	101
85°	24	16	14	14	13	27
90°	1	8	15	20	23	3
95°	54	50	15	20	20	69
105°	280	284	284	284	283	297
115°	526	531	532	528	522	521
125°	748	755	755	751	748	668
135°	933	939	937	935	929	719
145°	1082	1084	1084	1084	1079	676
155°	1192	1186	1188	1190	1183	549
165°	1257	1252	1252	1258	1251	355
175°	1286	1281	1281	1288	1280	122
180°	1286	1286	1286	1286	1286	



TEST NUMBER: P333650-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	577.8	577.6	577.3	577.1	576.8	576.4	575.6	574.8	574.0	573.3	574.0
5°	575.9	575.5	575.1	574.7	574.3	573.6	572.5	571.5	570.4	569.3	570.3
7.5°	570.2	569.9	569.5	569.1	568.7	567.9	566.7	565.3	564.1	562.8	563.5
10°	565.0	564.7	564.4	564.1	563.8	563.0	561.7	560.2	558.9	557.6	557.9
12.5°	559.0	558.6	558.4	558.0	557.6	556.5	554.7	552.9	551.0	549.2	549.4
15°	547.5	547.0	546.4	545.8	545.3	543.9	541.9	539.9	537.8	535.8	535.7
17.5°	534.6	533.7	532.8	531.9	531.0	529.3	526.7	524.1	521.6	519.1	518.6
20°	524.4	523.5	522.5	521.6	520.6	518.6	515.5	512.4	509.3	506.1	505.7
22.5°	513.3	512.4	511.4	510.4	509.4	507.4	504.1	500.9	497.6	494.4	493.4
25°	496.6	495.1	493.7	492.2	490.8	488.2	484.7	481.1	477.5	473.9	472.7
27.5°	477.4	475.7	473.9	472.1	470.3	467.6	463.7	459.9	456.1	452.2	450.4
30°	463.4	461.7	459.8	458.0	456.1	453.2	449.1	445.1	441.0	436.9	434.7
32.5°	449.9	447.7	445.6	443.5	441.3	438.2	434.0	429.9	425.7	421.6	419.1
35°	427.7	425.5	423.1	420.8	418.5	415.1	410.8	406.4	402.1	397.8	394.9
37.5°	406.0	403.2	400.4	397.6	394.7	391.1	386.6	382.1	377.7	373.2	369.8
40°	390.8	387.9	384.9	382.0	379.1	375.3	370.7	366.1	361.4	356.8	353.1
42.5°	374.7	371.7	368.7	365.8	362.8	358.9	354.1	349.3	344.5	339.7	336.2
45°	350.2	347.4	344.6	341.8	339.0	334.9	329.6	324.3	319.0	313.7	309.7
47.5°	324.9	321.9	319.0	315.9	313.0	308.9	303.5	298.1	292.8	287.4	283.4
50°	308.9	305.7	302.5	299.3	296.1	291.7	286.2	280.7	275.1	269.7	265.6
52.5°	291.4	288.1	284.8	281.6	278.3	274.1	268.9	263.6	258.4	253.3	248.9
55°	265.7	262.6	259.5	256.5	253.4	249.1	243.6	238.2	232.8	227.3	223.0
57.5°	239.8	236.5	233.1	229.8	226.5	222.3	217.0	211.8	206.6	201.3	197.1
60°	223.0	219.6	216.2	212.8	209.4	205.2	199.9	194.7	189.5	184.3	180.0
62.5°	205.3	202.0	198.8	195.6	192.3	188.0	182.8	177.5	172.1	166.8	162.9
65°	179.9	176.6	173.3	170.0	166.7	162.5	157.4	152.3	147.1	142.0	138.2
67.5°	154.8	151.5	148.2	144.9	141.6	137.4	132.5	127.6	122.7	117.8	114.2
70°	137.6	134.4	131.1	127.8	124.5	120.5	115.6	110.7	105.9	101.0	98.0
72.5°	120.9	117.7	114.5	111.3	108.1	104.2	99.6	95.1	90.6	86.1	83.3
75°	95.9	92.9	90.0	87.1	84.3	80.8	76.6	72.6	68.5	64.5	62.3
77.5°	70.9	68.6	66.3	63.9	61.6	58.8	55.6	52.3	49.1	45.8	44.3
80°	56.6	54.3	52.0	49.7	47.3	44.9	42.1	39.4	36.7	33.9	33.1
82.5°	42.7	40.6	38.5	36.4	34.3	32.3	30.5	28.7	26.8	24.9	24.5
85°	23.9	22.2	20.5	18.8	17.0	15.8	15.4	14.9	14.4	13.9	13.9
87.5°	8.2	8.0	7.8	7.6	7.4	7.4	7.6	7.8	8.0	8.3	8.5
90°	0.9	2.6	4.3	6.0	7.7	9.3	10.8	12.3	13.8	15.3	16.3
92.5°	14.7	13.5	12.3	11.1	9.9	10.0	11.3	12.6	13.9	15.3	16.3
95°	54.3	53.7	53.1	52.4	51.8	47.4	39.4	31.4	23.3	15.3	16.3
97.5°	113.5	114.6	115.7	116.9	118.0	110.7	94.7	78.8	62.9	46.9	40.9
100°	159.2	159.9	160.4	161.1	161.7	162.5	163.3	164.2	165.0	165.9	134.3
102.5°	205.8	206.5	207.4	208.1	209.0	209.6	210.1	210.6	211.1	211.6	205.7
105°	280.2	281.1	281.9	282.8	283.6	284.1	284.1	284.1	284.1	284.1	284.1
107.5°	357.7	357.7	357.7	357.7	357.7	357.9	358.3	358.7	359.1	359.6	359.6
110°	408.0	408.0	408.0	408.0	408.0	408.2	408.6	409.1	409.4	409.9	409.3



TEST NUMBER: P333650-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	455.2	455.8	456.3	456.8	457.3	457.7	458.0	458.2	458.5	458.7	457.9
115°	526.2	527.3	528.3	529.3	530.5	531.0	531.3	531.5	531.7	531.9	531.0
117.5°	599.6	599.6	599.6	599.5	599.5	599.8	600.6	601.4	602.2	603.0	601.9
120°	645.4	645.2	644.9	644.7	644.5	644.7	645.4	646.0	646.6	647.2	646.9
122.5°	685.8	686.5	687.4	688.2	689.0	689.6	689.8	690.1	690.4	690.7	690.3
125°	748.3	749.8	751.3	752.7	754.2	755.0	755.0	755.0	755.0	755.0	754.1
127.5°	807.9	809.1	810.1	811.2	812.2	812.7	812.6	812.5	812.3	812.2	811.7
130°	844.6	845.6	846.7	847.7	848.9	849.4	849.7	849.9	850.1	850.3	849.7
132.5°	881.2	882.4	883.6	884.9	886.1	886.5	886.0	885.5	885.0	884.7	884.5
135°	933.2	934.5	935.8	937.1	938.3	938.8	938.3	937.9	937.5	937.1	936.6
137.5°	981.1	982.2	983.3	984.4	985.5	985.9	985.5	985.1	984.7	984.3	984.4
140°	1012.4	1012.8	1013.2	1013.6	1014.1	1014.2	1014.0	1013.7	1013.5	1013.3	1013.7
142.5°	1040.6	1040.8	1041.1	1041.3	1041.6	1041.9	1042.2	1042.5	1042.7	1043.0	1043.1
145°	1081.9	1082.4	1082.8	1083.3	1083.6	1083.8	1083.8	1083.8	1083.8	1083.8	1084.1
147.5°	1118.1	1118.1	1118.0	1117.9	1117.9	1117.9	1118.1	1118.4	1118.7	1118.9	1119.2
150°	1141.0	1140.7	1140.2	1139.8	1139.3	1139.3	1139.8	1140.2	1140.7	1141.0	1141.5
152.5°	1163.2	1162.2	1161.3	1160.4	1159.4	1159.2	1159.6	1160.1	1160.5	1160.8	1161.3
155°	1191.6	1190.3	1189.0	1187.8	1186.5	1186.1	1186.5	1186.9	1187.3	1187.8	1188.4
157.5°	1213.5	1212.8	1212.0	1211.3	1210.4	1210.1	1210.1	1210.1	1210.2	1210.2	1211.0
160°	1228.8	1227.5	1226.2	1224.9	1223.7	1223.1	1223.3	1223.6	1223.8	1224.0	1224.8
162.5°	1241.0	1239.7	1238.4	1237.2	1235.9	1235.3	1235.6	1235.8	1236.0	1236.1	1237.4
165°	1257.4	1256.1	1254.8	1253.6	1252.3	1251.7	1252.0	1252.2	1252.4	1252.5	1253.9
167.5°	1269.5	1268.3	1267.0	1265.6	1264.3	1263.8	1263.9	1264.1	1264.4	1264.6	1266.1
170°	1276.4	1275.0	1273.5	1272.0	1270.5	1269.9	1270.1	1270.3	1270.5	1270.7	1272.4
172.5°	1281.0	1279.5	1278.0	1276.6	1275.1	1274.5	1274.9	1275.3	1275.6	1276.0	1277.5
175°	1285.9	1284.7	1283.4	1282.1	1280.8	1280.3	1280.5	1280.7	1281.0	1281.2	1282.9
177.5°	1288.3	1287.2	1286.2	1285.2	1284.2	1283.7	1283.9	1284.1	1284.2	1284.4	1285.6
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9



TEST NUMBER: P333650-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	574.8	575.6	576.4	576.7	576.6	576.6	576.5	576.4
5°	571.3	572.2	573.2	573.6	573.4	573.2	573.0	572.8
7.5°	564.1	564.9	565.5	565.7	565.5	565.3	565.1	564.9
10°	558.2	558.5	558.7	558.7	558.5	558.2	557.9	557.6
12.5°	549.6	549.9	550.1	550.0	549.5	549.0	548.7	548.2
15°	535.6	535.5	535.4	534.9	534.0	533.2	532.3	531.4
17.5°	518.1	517.6	517.2	516.5	515.9	515.1	514.3	513.7
20°	505.2	504.7	504.3	503.6	502.7	501.8	501.0	500.1
22.5°	492.4	491.4	490.5	489.7	489.0	488.2	487.6	486.8
25°	471.5	470.1	468.9	467.8	466.7	465.6	464.6	463.4
27.5°	448.7	447.0	445.2	443.8	442.8	441.8	440.7	439.7
30°	432.4	430.3	428.0	426.5	425.6	424.7	423.9	423.0
32.5°	416.7	414.2	411.7	410.0	408.9	407.7	406.6	405.6
35°	392.1	389.3	386.4	384.4	383.0	381.7	380.3	379.0
37.5°	366.4	363.1	359.7	357.3	356.0	354.7	353.4	352.0
40°	349.4	345.7	342.0	339.6	338.5	337.3	336.1	335.0
42.5°	332.6	329.1	325.6	323.0	321.3	319.5	317.8	316.1
45°	305.9	302.0	298.1	295.5	294.1	292.6	291.2	289.6
47.5°	279.5	275.4	271.5	268.6	267.0	265.4	263.8	262.2
50°	261.5	257.4	253.4	250.6	249.2	247.7	246.3	244.8
52.5°	244.5	240.2	235.7	232.8	231.4	230.0	228.5	227.1
55°	218.7	214.3	210.0	207.0	205.5	203.9	202.4	200.9
57.5°	192.8	188.6	184.3	181.4	180.1	178.7	177.4	176.0
60°	175.8	171.4	167.2	164.4	162.9	161.5	160.0	158.5
62.5°	158.9	155.0	151.0	148.4	146.8	145.4	144.0	142.5
65°	134.2	130.4	126.5	123.9	122.4	120.9	119.5	118.0
67.5°	110.7	107.2	103.6	101.2	100.1	99.0	97.7	96.6
70°	95.1	92.1	89.1	87.0	85.8	84.6	83.5	82.3
72.5°	80.5	77.8	75.0	73.2	72.5	71.7	70.9	70.1
75°	60.2	58.1	56.0	54.6	53.9	53.2	52.5	51.8
77.5°	42.9	41.4	39.9	38.8	38.4	37.9	37.3	36.9
80°	32.2	31.4	30.5	30.0	29.8	29.6	29.4	29.2
82.5°	24.1	23.7	23.3	23.0	22.9	22.8	22.7	22.5
85°	13.8	13.7	13.6	13.5	13.4	13.3	13.2	13.1
87.5°	8.7	9.0	9.1	9.2	9.3	9.3	9.4	9.4
90°	17.3	18.5	19.5	20.4	21.0	21.6	22.2	22.9
92.5°	17.3	18.5	19.5	20.2	20.5	20.7	21.0	21.4
95°	17.3	18.5	19.5	20.0	20.0	20.0	20.0	20.0
97.5°	35.0	28.9	23.0	20.0	20.0	20.0	20.0	20.0
100°	102.7	71.2	39.6	23.4	22.5	21.7	20.8	20.0
102.5°	199.6	193.7	187.8	177.6	163.2	148.7	134.3	119.9
105°	284.1	284.1	284.1	284.0	283.8	283.5	283.3	283.1
107.5°	359.7	359.7	359.8	359.5	358.8	358.2	357.5	356.9
110°	408.6	408.0	407.4	407.2	407.4	407.6	407.7	408.0



TEST NUMBER: P333650-830

CATALOG NUMBER: S125RDIW-S375D1050U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	457.1	456.3	455.5	455.0	454.7	454.3	454.0	453.7
115°	530.2	529.3	528.5	527.4	526.2	524.9	523.7	522.4
117.5°	600.9	599.7	598.6	597.8	597.3	596.7	596.2	595.6
120°	646.4	646.0	645.5	644.8	643.8	642.7	641.7	640.6
122.5°	689.8	689.5	689.0	688.2	687.0	685.8	684.6	683.3
125°	753.3	752.4	751.6	750.8	750.3	749.6	748.9	748.3
127.5°	811.2	810.8	810.3	809.3	807.8	806.2	804.6	803.0
130°	849.0	848.4	847.7	846.9	845.8	844.8	843.8	842.7
132.5°	884.4	884.2	884.1	883.5	882.5	881.4	880.3	879.3
135°	936.2	935.8	935.4	934.5	933.2	932.0	930.7	929.4
137.5°	984.5	984.6	984.7	984.2	983.1	981.9	980.9	979.8
140°	1014.2	1014.6	1015.0	1014.6	1013.3	1012.0	1010.8	1009.5
142.5°	1043.2	1043.3	1043.4	1042.8	1041.5	1040.3	1039.0	1037.7
145°	1084.3	1084.5	1084.7	1084.2	1082.9	1081.7	1080.3	1079.1
147.5°	1119.5	1119.7	1119.9	1119.4	1117.8	1116.3	1114.7	1113.2
150°	1141.9	1142.4	1142.7	1142.1	1140.4	1138.7	1137.0	1135.3
152.5°	1161.7	1162.2	1162.5	1162.1	1160.5	1159.0	1157.4	1155.9
155°	1189.0	1189.7	1190.3	1189.8	1188.1	1186.4	1184.7	1183.0
157.5°	1211.6	1212.3	1213.0	1212.5	1210.8	1209.1	1207.4	1205.7
160°	1225.7	1226.5	1227.4	1226.9	1225.3	1223.6	1221.9	1220.2
162.5°	1238.6	1239.7	1241.0	1240.6	1238.7	1236.9	1235.0	1233.1
165°	1255.1	1256.4	1257.6	1257.4	1255.7	1254.1	1252.4	1250.7
167.5°	1267.6	1269.1	1270.7	1270.5	1268.6	1266.7	1264.8	1262.9
170°	1274.1	1275.8	1277.5	1277.3	1275.4	1273.6	1271.7	1269.7
172.5°	1279.1	1280.6	1282.1	1282.0	1280.1	1278.1	1276.2	1274.3
175°	1284.6	1286.3	1288.0	1287.9	1285.9	1284.0	1282.1	1280.3
177.5°	1286.8	1288.0	1289.2	1289.1	1287.7	1286.4	1285.1	1283.6
180°	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9	1285.9

(END OF REPORT)