

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333716-935

Luminaire Tested: **S125RDIW-S1090D1560U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333716-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D1560U935-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9040.5 lumens  
Efficiency: N/A  
Efficacy: 118.0 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41	35
2	88	81	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35	30
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30	26
4	73	63	55	50	67	58	51	46	48	43	39	39	35	33	30	28	26	22
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19
6	62	50	43	37	56	46	39	34	39	33	30	32	28	25	25	22	20	17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	20	21	18	16	14
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15	12
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9143	9143	9143	9143
5°	10519	9155	8085	9155
10°	12066	9108	7134	9108
15°	13032	9014	6341	9014
20°	14370	8906	5856	8906
25°	16631	8763	5433	8763
30°	18098	8611	5158	8611
35°	15266	8435	4902	8435
40°	10662	8118	4683	8118
45°	7909	7691	4469	7691
50°	6306	7246	4285	7246
55°	5353	6694	4122	6694
60°	4624	6200	3858	6200
65°	4121	5665	3321	5665
70°	3620	5189	3029	5189
75°	3132	4494	2842	4494
80°	2377	3782	2377	3782
85°	1979	2971	2238	2971



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.8	1.5
10°-20°	397.8	4.4
20°-30°	630.8	7.0
30°-40°	760.7	8.4
40°-50°	679.3	7.5
50°-60°	520.9	5.8
60°-70°	338.5	3.7
70°-80°	164.6	1.8
80°-90°	42.9	0.5
90°-100°	63.5	0.7
100°-110°	391.6	4.3
110°-120°	710.2	7.9
120°-130°	911.5	10.1
130°-140°	980.4	10.8
140°-150°	920.2	10.2
150°-160°	744.4	8.2
160°-170°	481.4	5.3
170°-180°	166.0	1.8
0°-30°	1164.4	12.9
0°-40°	1925.0	21.3
0°-60°	3125.2	34.6
0°-90°	3671.3	40.6
90°-120°	1165.3	12.9
90°-150°	3977.4	44.0
90°-180°	5369.0	59.4
0°-180°	9040.5	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1416	1416	1416	1416	1416	
5°	1622	1412	1247	1412	1622	162
15°	1949	1348	948	1348	1949	559
25°	2334	1230	762	1230	2334	1072
35°	1936	1070	622	1070	1936	1170
45°	866	842	489	842	866	691
55°	475	594	366	594	475	431
65°	270	371	217	371	270	268
75°	126	180	114	180	126	134
85°	27	40	30	40	27	32
90°	31	1	31	1	31	15
95°	27	74	27	74	27	22
105°	385	381	385	381	385	348
115°	710	716	710	716	710	705
125°	1017	1017	1017	1017	1017	905
135°	1264	1269	1264	1269	1264	975
145°	1467	1471	1467	1471	1467	916
155°	1608	1620	1608	1620	1608	741
165°	1700	1710	1700	1710	1700	480
175°	1741	1748	1741	1748	1741	166
180°	1748	1748	1748	1748	1748	



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1489.1	1488.2	1490.0	1484.9	1485.4	1477.5	1477.5	1471.4	1463.5	1457.5	1454.7
5°	1622.5	1623.7	1621.3	1612.7	1606.8	1598.1	1588.2	1570.8	1556.3	1542.3	1531.3
7.5°	1759.9	1760.7	1753.0	1750.3	1735.7	1725.0	1703.1	1679.3	1658.3	1631.6	1611.1
10°	1839.9	1839.3	1831.1	1824.7	1812.0	1795.7	1774.2	1746.3	1720.1	1691.1	1663.2
12.5°	1886.4	1884.8	1882.2	1874.5	1862.6	1848.2	1830.0	1802.5	1770.3	1738.5	1706.0
15°	1949.1	1945.0	1937.5	1927.6	1910.7	1893.9	1873.5	1849.2	1818.3	1782.3	1752.1
17.5°	2026.7	2026.9	2015.3	2001.5	1978.6	1948.9	1917.4	1878.1	1836.3	1796.6	1764.4
20°	2090.9	2089.1	2077.5	2050.8	2024.6	1987.4	1951.5	1903.2	1852.0	1800.4	1760.2
22.5°	2183.0	2178.4	2166.3	2131.2	2090.7	2042.8	1987.7	1928.7	1866.9	1808.2	1755.6
25°	2333.8	2330.3	2306.4	2265.8	2208.9	2135.0	2063.0	1982.2	1893.3	1816.0	1752.1
27.5°	2437.0	2433.2	2415.5	2381.7	2329.2	2251.5	2154.0	2046.0	1935.0	1828.7	1736.6
30°	2426.8	2435.5	2433.2	2417.5	2378.0	2308.3	2218.2	2096.7	1964.8	1839.9	1730.0
32.5°	2280.8	2288.6	2309.0	2339.9	2342.2	2314.3	2247.0	2134.8	1998.3	1856.1	1724.9
35°	1936.3	1946.8	1986.3	2048.5	2129.9	2197.8	2211.7	2151.3	2028.7	1875.9	1717.3
37.5°	1488.6	1545.8	1579.1	1644.5	1767.5	1892.5	2012.8	2057.1	2004.8	1867.8	1704.8
40°	1264.6	1278.5	1337.7	1411.5	1515.0	1645.2	1816.6	1940.3	1944.5	1849.2	1685.2
42.5°	1082.3	1099.9	1140.7	1199.5	1288.1	1418.3	1595.3	1758.6	1834.3	1798.0	1659.7
45°	865.9	879.3	908.9	954.2	1022.2	1129.7	1281.9	1470.8	1620.7	1679.5	1591.1
47.5°	711.3	718.5	744.3	778.9	829.1	907.5	1025.4	1189.3	1369.2	1495.2	1482.8
50°	627.6	635.8	655.5	681.7	724.1	790.3	884.5	1021.1	1206.4	1360.4	1391.2
52.5°	562.5	569.3	581.6	606.3	641.4	692.2	768.3	891.8	1058.6	1222.4	1293.6
55°	475.4	480.0	489.9	503.9	531.8	568.3	634.0	719.5	854.3	1019.3	1123.9
57.5°	403.6	405.9	412.2	425.1	444.4	471.1	518.5	590.9	687.6	836.2	951.7
60°	358.0	360.3	368.4	377.1	392.3	416.6	453.8	504.4	597.4	720.1	836.8
62.5°	321.7	323.1	326.6	335.3	348.5	367.4	396.7	437.9	511.9	619.6	729.9
65°	269.7	270.2	271.4	278.4	286.5	300.4	319.6	348.7	404.5	485.9	583.4
67.5°	219.6	220.5	224.5	227.0	235.5	242.8	254.1	276.3	315.6	370.4	446.3
70°	191.7	191.2	195.3	198.2	201.0	209.8	217.3	235.4	259.8	301.6	365.0
72.5°	165.7	164.2	166.0	167.0	170.8	176.8	184.3	195.4	214.2	243.1	291.5
75°	125.5	126.1	126.1	127.3	130.2	132.5	134.8	140.6	151.1	170.3	196.4
77.5°	88.1	87.1	89.6	90.0	91.7	94.3	96.3	98.6	102.9	110.7	124.2
80°	63.9	63.9	64.5	66.2	65.7	66.8	69.7	72.1	77.3	82.0	86.6
82.5°	49.1	48.6	49.2	49.5	49.4	50.5	51.6	52.1	54.1	56.4	59.6
85°	26.7	26.7	27.3	27.3	27.9	27.9	28.5	28.5	28.5	29.0	29.6
87.5°	16.4	15.8	15.2	15.0	15.3	16.0	15.2	14.5	14.2	13.9	13.9
90°	31.1	30.2	29.4	28.5	27.6	26.5	25.1	23.6	22.2	20.8	18.7
92.5°	29.0	28.7	28.2	27.8	27.4	26.5	25.1	23.6	22.2	20.8	18.9
95°	27.2	27.2	27.2	27.2	27.2	26.5	25.1	23.6	22.2	20.8	31.7
97.5°	27.2	27.2	27.2	27.2	27.2	31.3	39.4	47.5	55.6	63.8	85.4
100°	27.2	28.4	29.5	30.7	31.9	53.9	96.8	139.7	182.6	225.5	224.4
102.5°	163.1	182.6	202.2	221.8	241.4	255.3	263.4	271.5	279.7	287.7	287.1
105°	385.0	385.2	385.6	385.8	386.1	386.2	386.2	386.2	386.2	386.2	386.2
107.5°	485.3	486.1	487.0	487.8	488.7	489.1	489.0	489.0	489.0	488.9	488.4
110°	554.7	554.5	554.1	553.9	553.6	553.9	554.7	555.6	556.5	557.3	556.7



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	616.9	617.3	617.8	618.2	618.5	619.3	620.4	621.5	622.6	623.7	623.4
115°	710.2	712.0	713.7	715.5	717.2	718.6	719.8	720.9	722.0	723.2	723.0
117.5°	809.8	810.5	811.3	812.1	812.8	813.9	815.5	816.9	818.4	819.9	818.8
120°	871.0	872.5	873.8	875.3	876.8	877.8	878.3	878.9	879.5	880.0	879.2
122.5°	929.0	930.7	932.4	934.1	935.7	936.9	937.5	938.0	938.6	939.2	938.7
125°	1017.4	1018.3	1019.2	1020.0	1020.9	1021.9	1023.0	1024.2	1025.4	1026.5	1026.5
127.5°	1091.8	1094.0	1096.1	1098.2	1100.4	1101.7	1102.4	1103.0	1103.6	1104.3	1104.5
130°	1145.7	1147.2	1148.7	1150.1	1151.5	1152.7	1153.6	1154.4	1155.3	1156.2	1155.8
132.5°	1195.5	1197.0	1198.4	1199.9	1201.3	1202.1	1202.3	1202.5	1202.6	1202.8	1203.4
135°	1263.7	1265.4	1267.1	1268.9	1270.6	1271.8	1272.4	1272.9	1273.5	1274.1	1274.6
137.5°	1332.1	1333.6	1335.2	1336.6	1338.2	1338.9	1338.7	1338.6	1338.5	1338.3	1338.9
140°	1372.6	1374.3	1376.1	1377.8	1379.5	1380.1	1379.5	1378.9	1378.4	1377.8	1378.0
142.5°	1410.9	1412.6	1414.4	1416.1	1417.9	1418.7	1418.6	1418.4	1418.3	1418.2	1417.8
145°	1467.2	1469.0	1470.7	1472.4	1474.1	1474.8	1474.5	1474.3	1473.9	1473.7	1473.7
147.5°	1513.6	1515.7	1517.8	1519.8	1521.9	1522.8	1522.4	1522.1	1521.7	1521.4	1521.0
150°	1543.7	1546.0	1548.3	1550.6	1552.9	1553.8	1553.2	1552.6	1552.0	1551.4	1550.8
152.5°	1571.7	1573.7	1575.8	1577.9	1579.9	1580.7	1580.1	1579.6	1579.0	1578.4	1577.9
155°	1608.4	1610.8	1613.1	1615.4	1617.6	1618.4	1617.6	1616.7	1615.8	1615.0	1614.4
157.5°	1639.3	1641.6	1643.9	1646.2	1648.6	1649.2	1648.3	1647.4	1646.5	1645.5	1645.5
160°	1659.1	1661.3	1663.6	1665.9	1668.3	1668.8	1667.7	1666.5	1665.3	1664.2	1663.9
162.5°	1676.6	1679.2	1681.7	1684.3	1686.8	1687.2	1685.7	1684.0	1682.4	1680.8	1680.5
165°	1700.5	1702.8	1705.1	1707.4	1709.7	1710.0	1708.3	1706.5	1704.8	1703.1	1702.8
167.5°	1717.1	1719.7	1722.3	1724.8	1727.4	1727.7	1725.6	1723.5	1721.5	1719.4	1719.2
170°	1726.4	1729.0	1731.6	1734.2	1736.8	1736.9	1734.7	1732.3	1730.0	1727.7	1727.4
172.5°	1732.7	1735.3	1737.8	1740.4	1743.0	1743.3	1741.2	1739.1	1737.1	1735.0	1734.5
175°	1740.7	1743.3	1745.8	1748.4	1751.0	1751.2	1748.9	1746.5	1744.3	1742.0	1741.7
177.5°	1745.3	1747.1	1749.0	1750.8	1752.7	1752.8	1751.2	1749.6	1748.0	1746.4	1746.1
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1454.7	1451.4	1445.4	1439.8	1432.8	1426.8	1422.6	1417.5	1411.0	1403.1	1396.5
5°	1519.1	1506.2	1489.4	1474.9	1456.3	1441.7	1426.7	1412.1	1397.6	1379.0	1362.7
7.5°	1590.4	1564.0	1538.3	1506.1	1476.8	1450.6	1425.5	1400.1	1375.2	1348.8	1323.4
10°	1634.1	1602.1	1566.7	1526.0	1488.8	1453.4	1420.8	1388.9	1355.2	1325.5	1293.6
12.5°	1675.1	1633.7	1593.2	1541.9	1497.2	1453.9	1412.5	1372.6	1336.6	1298.1	1263.9
15°	1712.0	1671.3	1626.0	1563.2	1501.1	1448.7	1399.9	1348.2	1303.5	1260.4	1222.1
17.5°	1726.3	1683.6	1631.0	1570.6	1502.7	1436.9	1374.0	1317.3	1264.6	1214.5	1171.4
20°	1720.7	1679.5	1625.4	1567.9	1495.2	1426.7	1358.7	1295.9	1237.3	1184.3	1138.4
22.5°	1707.2	1664.6	1612.4	1551.6	1482.6	1409.9	1337.3	1270.3	1208.8	1154.1	1104.1
25°	1687.0	1628.9	1575.5	1516.1	1450.5	1378.5	1303.5	1229.7	1164.0	1108.2	1053.6
27.5°	1665.9	1593.5	1525.4	1466.5	1397.1	1332.8	1260.6	1184.9	1115.9	1059.0	1003.0
30°	1646.9	1565.6	1490.6	1423.7	1358.1	1297.1	1228.5	1154.7	1083.8	1025.1	968.2
32.5°	1623.2	1536.7	1454.3	1377.3	1313.9	1253.4	1191.3	1120.8	1051.7	991.2	933.3
35°	1593.5	1483.1	1393.5	1311.6	1241.3	1182.6	1126.8	1069.9	1000.7	938.0	881.6
37.5°	1554.4	1429.1	1325.5	1236.3	1162.1	1103.2	1059.1	1007.1	944.0	883.9	831.6
40°	1530.7	1390.1	1276.7	1188.4	1110.5	1048.4	1007.1	962.9	905.4	849.0	796.7
42.5°	1499.1	1354.3	1227.4	1135.4	1057.0	997.2	955.5	916.9	868.7	815.5	759.5
45°	1437.1	1284.9	1151.8	1053.0	974.0	915.2	876.3	842.1	805.5	756.6	707.8
47.5°	1356.4	1212.5	1073.2	965.4	887.9	833.4	795.7	768.6	742.4	700.9	653.5
50°	1291.8	1153.0	1016.9	912.4	829.8	778.1	742.7	721.2	697.3	659.6	620.1
52.5°	1215.6	1091.6	958.4	851.4	773.6	725.1	691.0	669.6	650.0	619.1	581.4
55°	1095.5	986.8	864.7	767.7	696.2	647.4	614.8	594.5	582.9	556.7	527.1
57.5°	956.7	878.9	771.3	677.7	614.5	566.3	542.4	525.1	512.0	493.5	472.6
60°	860.1	805.5	708.9	620.1	562.0	516.0	494.6	480.0	467.8	452.1	435.8
62.5°	762.0	722.2	638.3	562.0	508.5	470.0	449.9	436.8	422.8	412.2	396.3
65°	630.5	595.0	536.9	477.1	427.7	396.9	382.4	370.7	362.1	350.4	339.4
67.5°	490.5	476.0	435.9	394.7	359.2	331.8	319.3	311.2	300.7	293.7	286.1
70°	404.5	397.5	369.0	341.7	308.6	290.0	278.4	274.8	262.1	255.1	249.9
72.5°	328.2	324.9	308.6	289.6	266.3	250.0	239.3	235.4	227.2	221.6	218.3
75°	224.9	226.1	223.2	210.9	202.2	191.7	182.4	180.1	174.4	169.7	166.8
77.5°	142.2	148.2	148.4	147.8	144.4	137.9	134.1	132.4	126.7	124.9	124.2
80°	97.6	104.0	109.9	109.3	108.1	106.3	103.4	101.7	98.8	97.0	95.9
82.5°	65.1	71.0	75.9	79.0	78.8	77.1	75.1	74.3	73.7	72.4	72.2
85°	30.8	31.9	33.7	37.8	40.6	41.2	40.6	40.1	38.3	38.9	39.5
87.5°	14.0	13.6	13.7	13.3	12.3	14.2	15.2	15.2	14.6	14.2	13.7
90°	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	17.1	15.4	13.6	13.5	15.2	16.7	18.3	20.0	18.3	16.7	15.2
95°	42.6	53.6	64.5	70.4	71.3	72.2	73.0	73.9	73.0	72.2	71.3
97.5°	107.1	128.7	150.4	160.5	158.9	157.3	155.8	154.2	155.8	157.3	158.9
100°	223.3	222.1	220.9	219.9	219.0	218.2	217.3	216.5	217.3	218.2	219.0
102.5°	286.4	285.7	285.0	284.0	283.0	281.9	280.8	279.7	280.8	281.9	283.0
105°	386.2	386.2	386.2	385.6	384.5	383.4	382.2	381.1	382.2	383.4	384.5
107.5°	487.8	487.2	486.6	486.3	486.3	486.3	486.3	486.3	486.3	486.3	486.3
110°	556.2	555.6	555.0	554.7	554.7	554.7	554.7	554.7	554.7	554.7	554.7





TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	623.0	622.7	622.3	621.8	621.1	620.4	619.7	619.1	619.7	620.4	621.1
115°	722.6	722.4	722.0	721.2	719.8	718.3	716.9	715.5	716.9	718.3	719.8
117.5°	817.7	816.7	815.5	815.0	815.1	815.1	815.2	815.3	815.2	815.1	815.1
120°	878.3	877.4	876.6	876.3	876.6	876.9	877.2	877.4	877.2	876.9	876.6
122.5°	938.3	938.0	937.5	936.8	935.7	934.6	933.5	932.5	933.5	934.6	935.7
125°	1026.5	1026.5	1026.5	1025.5	1023.5	1021.5	1019.4	1017.4	1019.4	1021.5	1023.5
127.5°	1104.7	1104.8	1105.0	1104.3	1102.9	1101.5	1100.0	1098.5	1100.0	1101.5	1102.9
130°	1155.5	1155.3	1154.9	1154.1	1152.7	1151.2	1149.8	1148.3	1149.8	1151.2	1152.7
132.5°	1204.0	1204.7	1205.3	1204.8	1203.2	1201.4	1199.8	1198.1	1199.8	1201.4	1203.2
135°	1275.2	1275.8	1276.3	1275.8	1274.1	1272.4	1270.6	1268.9	1270.6	1272.4	1274.1
137.5°	1339.4	1339.9	1340.4	1340.0	1338.4	1337.0	1335.4	1333.9	1335.4	1337.0	1338.4
140°	1378.4	1378.6	1378.9	1378.8	1378.2	1377.6	1377.1	1376.5	1377.1	1377.6	1378.2
142.5°	1417.4	1417.0	1416.6	1416.2	1415.8	1415.5	1415.1	1414.8	1415.1	1415.5	1415.8
145°	1473.7	1473.7	1473.7	1473.4	1472.8	1472.2	1471.6	1471.1	1471.6	1472.2	1472.8
147.5°	1520.7	1520.4	1520.0	1519.8	1520.0	1520.1	1520.2	1520.4	1520.2	1520.1	1520.0
150°	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1550.8	1550.3	1549.7
152.5°	1577.3	1576.7	1576.1	1576.4	1577.7	1579.0	1580.3	1581.5	1580.3	1579.0	1577.7
155°	1613.8	1613.3	1612.7	1613.3	1615.0	1616.7	1618.4	1620.1	1618.4	1616.7	1615.0
157.5°	1645.5	1645.4	1645.3	1645.8	1646.8	1647.9	1648.9	1649.9	1648.9	1647.9	1646.8
160°	1663.6	1663.4	1663.0	1663.8	1665.5	1667.2	1669.0	1670.7	1669.0	1667.2	1665.5
162.5°	1680.2	1679.9	1679.6	1680.3	1682.0	1683.9	1685.6	1687.3	1685.6	1683.9	1682.0
165°	1702.5	1702.2	1701.9	1702.6	1704.3	1706.1	1707.9	1709.6	1707.9	1706.1	1704.3
167.5°	1718.8	1718.6	1718.3	1719.0	1720.8	1722.6	1724.4	1726.1	1724.4	1722.6	1720.8
170°	1727.2	1726.8	1726.6	1727.4	1729.4	1731.5	1733.5	1735.5	1733.5	1731.5	1729.4
172.5°	1734.0	1733.5	1732.9	1733.6	1735.7	1737.7	1739.7	1741.7	1739.7	1737.7	1735.7
175°	1741.4	1741.1	1740.9	1741.5	1743.3	1745.0	1746.7	1748.4	1746.7	1745.0	1743.3
177.5°	1745.9	1745.7	1745.4	1746.0	1747.4	1748.8	1750.2	1751.5	1750.2	1748.8	1747.4
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1391.9	1385.4	1380.8	1371.5	1364.9	1362.2	1357.0	1355.6	1360.7	1357.0	1356.6
5°	1350.6	1333.7	1320.3	1306.9	1292.4	1283.1	1269.2	1266.9	1263.3	1258.1	1257.0
7.5°	1300.9	1278.9	1261.7	1239.7	1220.5	1205.1	1187.6	1179.3	1174.8	1168.0	1159.0
10°	1267.4	1241.3	1218.1	1195.9	1172.2	1153.0	1135.5	1122.1	1113.4	1105.3	1101.8
12.5°	1234.4	1207.8	1178.0	1151.3	1124.7	1103.2	1083.9	1075.2	1065.6	1056.0	1047.9
15°	1183.2	1147.7	1115.2	1084.3	1061.7	1038.5	1019.9	1007.1	992.6	988.5	972.8
17.5°	1128.8	1094.0	1055.9	1023.5	997.2	971.6	951.1	936.7	925.7	910.8	903.5
20°	1094.8	1053.6	1016.4	986.8	957.7	927.5	906.5	894.3	883.9	871.7	865.9
22.5°	1058.6	1018.2	980.2	945.4	915.8	886.1	871.2	858.6	846.7	835.4	827.8
25°	1005.3	964.7	924.5	888.6	857.7	836.2	818.8	804.3	797.9	786.9	778.7
27.5°	952.7	909.5	867.9	831.9	807.8	786.5	772.2	760.7	749.2	739.5	732.5
30°	918.8	874.6	829.2	800.8	775.2	754.8	739.2	728.1	719.5	710.8	705.5
32.5°	884.8	839.3	799.0	768.3	744.1	726.5	710.3	699.8	690.6	681.0	674.8
35°	830.4	783.9	751.4	721.2	697.3	681.1	670.0	655.0	647.4	640.4	634.0
37.5°	779.9	736.7	701.5	674.9	654.2	638.1	623.8	615.6	606.3	600.0	594.7
40°	742.7	703.2	671.2	643.3	628.2	610.2	596.8	586.3	579.4	571.3	565.4
42.5°	709.2	672.4	641.4	616.3	597.5	582.3	569.4	559.0	550.1	544.3	539.4
45°	661.9	625.3	595.0	571.8	554.4	539.8	526.5	521.2	509.6	502.7	500.3
47.5°	612.9	580.2	551.0	529.6	511.8	498.0	485.4	474.8	468.4	461.5	457.8
50°	580.0	548.5	521.2	500.3	482.9	467.8	456.2	449.2	440.5	434.1	429.5
52.5°	547.0	517.9	490.6	470.6	455.5	440.4	427.4	420.4	412.2	408.0	404.8
55°	499.8	469.0	445.7	425.9	410.3	396.3	384.1	377.1	372.0	367.8	366.7
57.5°	446.3	421.9	400.3	382.5	366.2	353.1	342.4	335.8	331.1	330.5	327.1
60°	411.5	389.3	369.6	350.4	336.5	324.3	315.0	307.4	302.7	302.2	301.0
62.5°	376.6	355.4	337.1	320.2	307.6	295.9	287.1	278.6	275.8	272.9	270.4
65°	324.9	305.7	290.6	277.2	263.8	253.9	245.2	240.0	233.6	230.1	223.8
67.5°	274.1	259.2	244.7	233.4	222.9	213.5	206.3	198.5	194.2	191.4	186.8
70°	240.6	228.9	214.5	202.2	194.1	186.6	180.7	172.0	169.1	166.8	164.5
72.5°	209.0	198.7	186.6	176.7	168.5	161.4	154.7	150.6	147.7	145.4	144.0
75°	164.5	154.5	144.1	137.2	131.3	125.5	122.0	119.2	118.0	117.4	115.0
77.5°	120.8	115.5	107.2	101.6	97.7	95.4	92.3	90.7	90.7	88.1	87.3
80°	92.4	89.5	82.5	80.2	77.3	75.0	73.2	70.3	67.4	66.2	64.5
82.5°	68.7	65.8	63.0	59.2	56.8	55.4	53.7	52.6	53.0	51.4	50.5
85°	36.6	33.7	32.5	31.9	30.8	31.9	31.3	30.8	30.2	29.6	30.2
87.5°	13.7	14.1	14.1	15.4	14.5	15.3	15.6	15.4	15.7	16.0	15.8
90°	10.5	12.7	14.7	16.7	18.7	20.8	22.2	23.6	25.1	26.5	27.6
92.5°	13.5	13.6	15.4	17.1	18.9	20.8	22.2	23.6	25.1	26.5	27.4
95°	70.4	64.5	53.6	42.6	31.7	20.8	22.2	23.6	25.1	26.5	27.2
97.5°	160.5	150.4	128.7	107.1	85.4	63.8	55.6	47.5	39.4	31.3	27.2
100°	219.9	220.9	222.1	223.3	224.4	225.5	182.6	139.7	96.8	53.9	31.9
102.5°	284.0	285.0	285.7	286.4	287.1	287.7	279.7	271.5	263.4	255.3	241.4
105°	385.6	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.2	386.1
107.5°	486.3	486.6	487.2	487.8	488.4	488.9	489.0	489.0	489.0	489.1	488.7
110°	554.7	555.0	555.6	556.2	556.7	557.3	556.5	555.6	554.7	553.9	553.6



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	621.8	622.3	622.7	623.0	623.4	623.7	622.6	621.5	620.4	619.3	618.5
115°	721.2	722.0	722.4	722.6	723.0	723.2	722.0	720.9	719.8	718.6	717.2
117.5°	815.0	815.5	816.7	817.7	818.8	819.9	818.4	816.9	815.5	813.9	812.8
120°	876.3	876.6	877.4	878.3	879.2	880.0	879.5	878.9	878.3	877.8	876.8
122.5°	936.8	937.5	938.0	938.3	938.7	939.2	938.6	938.0	937.5	936.9	935.7
125°	1025.5	1026.5	1026.5	1026.5	1026.5	1026.5	1025.4	1024.2	1023.0	1021.9	1020.9
127.5°	1104.3	1105.0	1104.8	1104.7	1104.5	1104.3	1103.6	1103.0	1102.4	1101.7	1100.4
130°	1154.1	1154.9	1155.3	1155.5	1155.8	1156.2	1155.3	1154.4	1153.6	1152.7	1151.5
132.5°	1204.8	1205.3	1204.7	1204.0	1203.4	1202.8	1202.6	1202.5	1202.3	1202.1	1201.3
135°	1275.8	1276.3	1275.8	1275.2	1274.6	1274.1	1273.5	1272.9	1272.4	1271.8	1270.6
137.5°	1340.0	1340.4	1339.9	1339.4	1338.9	1338.3	1338.5	1338.6	1338.7	1338.9	1338.2
140°	1378.8	1378.9	1378.6	1378.4	1378.0	1377.8	1378.4	1378.9	1379.5	1380.1	1379.5
142.5°	1416.2	1416.6	1417.0	1417.4	1417.8	1418.2	1418.3	1418.4	1418.6	1418.7	1417.9
145°	1473.4	1473.7	1473.7	1473.7	1473.7	1473.7	1473.9	1474.3	1474.5	1474.8	1474.1
147.5°	1519.8	1520.0	1520.4	1520.7	1521.0	1521.4	1521.7	1522.1	1522.4	1522.8	1521.9
150°	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1552.0	1552.6	1553.2	1553.8	1552.9
152.5°	1576.4	1576.1	1576.7	1577.3	1577.9	1578.4	1579.0	1579.6	1580.1	1580.7	1579.9
155°	1613.3	1612.7	1613.3	1613.8	1614.4	1615.0	1615.8	1616.7	1617.6	1618.4	1617.6
157.5°	1645.8	1645.3	1645.4	1645.5	1645.5	1645.5	1646.5	1647.4	1648.3	1649.2	1648.6
160°	1663.8	1663.0	1663.4	1663.6	1663.9	1664.2	1665.3	1666.5	1667.7	1668.8	1668.3
162.5°	1680.3	1679.6	1679.9	1680.2	1680.5	1680.8	1682.4	1684.0	1685.7	1687.2	1686.8
165°	1702.6	1701.9	1702.2	1702.5	1702.8	1703.1	1704.8	1706.5	1708.3	1710.0	1709.7
167.5°	1719.0	1718.3	1718.6	1718.8	1719.2	1719.4	1721.5	1723.5	1725.6	1727.7	1727.4
170°	1727.4	1726.6	1726.8	1727.2	1727.4	1727.7	1730.0	1732.3	1734.7	1736.9	1736.8
172.5°	1733.6	1732.9	1733.5	1734.0	1734.5	1735.0	1737.1	1739.1	1741.2	1743.3	1743.0
175°	1741.5	1740.9	1741.1	1741.4	1741.7	1742.0	1744.3	1746.5	1748.9	1751.2	1751.0
177.5°	1746.0	1745.4	1745.7	1745.9	1746.1	1746.4	1748.0	1749.6	1751.2	1752.8	1752.7
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1356.1	1351.0	1349.6	1351.4	1349.6	1351.0	1356.1	1356.6	1357.0	1360.7	1355.6
5°	1251.2	1245.4	1248.3	1247.1	1248.3	1245.4	1251.2	1257.0	1258.1	1263.3	1266.9
7.5°	1158.9	1151.7	1144.0	1146.4	1144.0	1151.7	1158.9	1159.0	1168.0	1174.8	1179.3
10°	1094.2	1088.5	1084.9	1087.9	1084.9	1088.5	1094.2	1101.8	1105.3	1113.4	1122.1
12.5°	1039.8	1036.4	1033.4	1032.1	1033.4	1036.4	1039.8	1047.9	1056.0	1065.6	1075.2
15°	965.9	958.9	956.0	948.4	956.0	958.9	965.9	972.8	988.5	992.6	1007.1
17.5°	897.6	895.3	887.7	884.5	887.7	895.3	897.6	903.5	910.8	925.7	936.7
20°	857.1	854.8	847.3	852.0	847.3	854.8	857.1	865.9	871.7	883.9	894.3
22.5°	823.7	818.6	816.1	814.8	816.1	818.6	823.7	827.8	835.4	846.7	858.6
25°	776.4	768.8	765.9	762.4	765.9	768.8	776.4	778.7	786.9	797.9	804.3
27.5°	729.2	725.1	721.3	720.4	721.3	725.1	729.2	732.5	739.5	749.2	760.7
30°	698.5	694.5	691.6	691.6	691.6	694.5	698.5	705.5	710.8	719.5	728.1
32.5°	671.1	668.0	665.0	664.6	665.0	668.0	671.1	674.8	681.0	690.6	699.8
35°	631.1	626.5	625.3	621.8	625.3	626.5	631.1	634.0	640.4	647.4	655.0
37.5°	589.6	585.7	585.7	585.3	585.7	585.7	589.6	594.7	600.0	606.3	615.6
40°	563.1	560.2	559.6	555.5	559.6	560.2	563.1	565.4	571.3	579.4	586.3
42.5°	534.8	533.2	531.2	529.5	531.2	533.2	534.8	539.4	544.3	550.1	559.0
45°	496.3	492.2	492.2	489.3	492.2	492.2	496.3	500.3	502.7	509.6	521.2
47.5°	456.5	453.4	453.7	450.7	453.7	453.4	456.5	457.8	461.5	468.4	474.8
50°	430.1	428.3	427.7	426.5	427.7	428.3	430.1	429.5	434.1	440.5	449.2
52.5°	403.6	402.7	404.9	402.3	404.9	402.7	403.6	404.8	408.0	412.2	420.4
55°	367.8	366.1	369.6	366.1	369.6	366.1	367.8	366.7	367.8	372.0	377.1
57.5°	326.8	325.2	328.3	326.6	328.3	325.2	326.8	327.1	330.5	331.1	335.8
60°	299.9	296.4	298.1	298.7	298.1	296.4	299.9	301.0	302.2	302.7	307.4
62.5°	267.8	265.7	267.0	264.3	267.0	265.7	267.8	270.4	272.9	275.8	278.6
65°	222.6	220.8	218.5	217.3	218.5	220.8	222.6	223.8	230.1	233.6	240.0
67.5°	187.0	182.8	182.7	183.7	182.7	182.8	187.0	186.8	191.4	194.2	198.5
70°	161.0	161.0	160.4	160.4	160.4	161.0	161.0	164.5	166.8	169.1	172.0
72.5°	142.8	142.4	141.3	140.9	141.3	142.4	142.8	144.0	145.4	147.7	150.6
75°	115.0	115.6	114.5	113.9	114.5	115.6	115.0	115.0	117.4	118.0	119.2
77.5°	85.0	82.5	83.8	82.5	83.8	82.5	85.0	87.3	88.1	90.7	90.7
80°	64.5	63.9	65.7	63.9	65.7	63.9	64.5	64.5	66.2	67.4	70.3
82.5°	51.1	50.5	51.2	49.9	51.2	50.5	51.1	50.5	51.4	53.0	52.6
85°	30.8	30.2	29.6	30.2	29.6	30.2	30.8	30.2	29.6	30.2	30.8
87.5°	16.4	16.1	16.3	16.4	16.3	16.1	16.4	15.8	16.0	15.7	15.4
90°	28.5	29.4	30.2	31.1	30.2	29.4	28.5	27.6	26.5	25.1	23.6
92.5°	27.8	28.2	28.7	29.0	28.7	28.2	27.8	27.4	26.5	25.1	23.6
95°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	26.5	25.1	23.6
97.5°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	31.3	39.4	47.5
100°	30.7	29.5	28.4	27.2	28.4	29.5	30.7	31.9	53.9	96.8	139.7
102.5°	221.8	202.2	182.6	163.1	182.6	202.2	221.8	241.4	255.3	263.4	271.5
105°	385.8	385.6	385.2	385.0	385.2	385.6	385.8	386.1	386.2	386.2	386.2
107.5°	487.8	487.0	486.1	485.3	486.1	487.0	487.8	488.7	489.1	489.0	489.0
110°	553.9	554.1	554.5	554.7	554.5	554.1	553.9	553.6	553.9	554.7	555.6



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	618.2	617.8	617.3	616.9	617.3	617.8	618.2	618.5	619.3	620.4	621.5
115°	715.5	713.7	712.0	710.2	712.0	713.7	715.5	717.2	718.6	719.8	720.9
117.5°	812.1	811.3	810.5	809.8	810.5	811.3	812.1	812.8	813.9	815.5	816.9
120°	875.3	873.8	872.5	871.0	872.5	873.8	875.3	876.8	877.8	878.3	878.9
122.5°	934.1	932.4	930.7	929.0	930.7	932.4	934.1	935.7	936.9	937.5	938.0
125°	1020.0	1019.2	1018.3	1017.4	1018.3	1019.2	1020.0	1020.9	1021.9	1023.0	1024.2
127.5°	1098.2	1096.1	1094.0	1091.8	1094.0	1096.1	1098.2	1100.4	1101.7	1102.4	1103.0
130°	1150.1	1148.7	1147.2	1145.7	1147.2	1148.7	1150.1	1151.5	1152.7	1153.6	1154.4
132.5°	1199.9	1198.4	1197.0	1195.5	1197.0	1198.4	1199.9	1201.3	1202.1	1202.3	1202.5
135°	1268.9	1267.1	1265.4	1263.7	1265.4	1267.1	1268.9	1270.6	1271.8	1272.4	1272.9
137.5°	1336.6	1335.2	1333.6	1332.1	1333.6	1335.2	1336.6	1338.2	1338.9	1338.7	1338.6
140°	1377.8	1376.1	1374.3	1372.6	1374.3	1376.1	1377.8	1379.5	1380.1	1379.5	1378.9
142.5°	1416.1	1414.4	1412.6	1410.9	1412.6	1414.4	1416.1	1417.9	1418.7	1418.6	1418.4
145°	1472.4	1470.7	1469.0	1467.2	1469.0	1470.7	1472.4	1474.1	1474.8	1474.5	1474.3
147.5°	1519.8	1517.8	1515.7	1513.6	1515.7	1517.8	1519.8	1521.9	1522.8	1522.4	1522.1
150°	1550.6	1548.3	1546.0	1543.7	1546.0	1548.3	1550.6	1552.9	1553.8	1553.2	1552.6
152.5°	1577.9	1575.8	1573.7	1571.7	1573.7	1575.8	1577.9	1579.9	1580.7	1580.1	1579.6
155°	1615.4	1613.1	1610.8	1608.4	1610.8	1613.1	1615.4	1617.6	1618.4	1617.6	1616.7
157.5°	1646.2	1643.9	1641.6	1639.3	1641.6	1643.9	1646.2	1648.6	1649.2	1648.3	1647.4
160°	1665.9	1663.6	1661.3	1659.1	1661.3	1663.6	1665.9	1668.3	1668.8	1667.7	1666.5
162.5°	1684.3	1681.7	1679.2	1676.6	1679.2	1681.7	1684.3	1686.8	1687.2	1685.7	1684.0
165°	1707.4	1705.1	1702.8	1700.5	1702.8	1705.1	1707.4	1709.7	1710.0	1708.3	1706.5
167.5°	1724.8	1722.3	1719.7	1717.1	1719.7	1722.3	1724.8	1727.4	1727.7	1725.6	1723.5
170°	1734.2	1731.6	1729.0	1726.4	1729.0	1731.6	1734.2	1736.8	1736.9	1734.7	1732.3
172.5°	1740.4	1737.8	1735.3	1732.7	1735.3	1737.8	1740.4	1743.0	1743.3	1741.2	1739.1
175°	1748.4	1745.8	1743.3	1740.7	1743.3	1745.8	1748.4	1751.0	1751.2	1748.9	1746.5
177.5°	1750.8	1749.0	1747.1	1745.3	1747.1	1749.0	1750.8	1752.7	1752.8	1751.2	1749.6
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1357.0	1362.2	1364.9	1371.5	1380.8	1385.4	1391.9	1396.5	1403.1	1411.0	1417.5
5°	1269.2	1283.1	1292.4	1306.9	1320.3	1333.7	1350.6	1362.7	1379.0	1397.6	1412.1
7.5°	1187.6	1205.1	1220.5	1239.7	1261.7	1278.9	1300.9	1323.4	1348.8	1375.2	1400.1
10°	1135.5	1153.0	1172.2	1195.9	1218.1	1241.3	1267.4	1293.6	1325.5	1355.2	1388.9
12.5°	1083.9	1103.2	1124.7	1151.3	1178.0	1207.8	1234.4	1263.9	1298.1	1336.6	1372.6
15°	1019.9	1038.5	1061.7	1084.3	1115.2	1147.7	1183.2	1222.1	1260.4	1303.5	1348.2
17.5°	951.1	971.6	997.2	1023.5	1055.9	1094.0	1128.8	1171.4	1214.5	1264.6	1317.3
20°	906.5	927.5	957.7	986.8	1016.4	1053.6	1094.8	1138.4	1184.3	1237.3	1295.9
22.5°	871.2	886.1	915.8	945.4	980.2	1018.2	1058.6	1104.1	1154.1	1208.8	1270.3
25°	818.8	836.2	857.7	888.6	924.5	964.7	1005.3	1053.6	1108.2	1164.0	1229.7
27.5°	772.2	786.5	807.8	831.9	867.9	909.5	952.7	1003.0	1059.0	1115.9	1184.9
30°	739.2	754.8	775.2	800.8	829.2	874.6	918.8	968.2	1025.1	1083.8	1154.7
32.5°	710.3	726.5	744.1	768.3	799.0	839.3	884.8	933.3	991.2	1051.7	1120.8
35°	670.0	681.1	697.3	721.2	751.4	783.9	830.4	881.6	938.0	1000.7	1069.9
37.5°	623.8	638.1	654.2	674.9	701.5	736.7	779.9	831.6	883.9	944.0	1007.1
40°	596.8	610.2	628.2	643.3	671.2	703.2	742.7	796.7	849.0	905.4	962.9
42.5°	569.4	582.3	597.5	616.3	641.4	672.4	709.2	759.5	815.5	868.7	916.9
45°	526.5	539.8	554.4	571.8	595.0	625.3	661.9	707.8	756.6	805.5	842.1
47.5°	485.4	498.0	511.8	529.6	551.0	580.2	612.9	653.5	700.9	742.4	768.6
50°	456.2	467.8	482.9	500.3	521.2	548.5	580.0	620.1	659.6	697.3	721.2
52.5°	427.4	440.4	455.5	470.6	490.6	517.9	547.0	581.4	619.1	650.0	669.6
55°	384.1	396.3	410.3	425.9	445.7	469.0	499.8	527.1	556.7	582.9	594.5
57.5°	342.4	353.1	366.2	382.5	400.3	421.9	446.3	472.6	493.5	512.0	525.1
60°	315.0	324.3	336.5	350.4	369.6	389.3	411.5	435.8	452.1	467.8	480.0
62.5°	287.1	295.9	307.6	320.2	337.1	355.4	376.6	396.3	412.2	422.8	436.8
65°	245.2	253.9	263.8	277.2	290.6	305.7	324.9	339.4	350.4	362.1	370.7
67.5°	206.3	213.5	222.9	233.4	244.7	259.2	274.1	286.1	293.7	300.7	311.2
70°	180.7	186.6	194.1	202.2	214.5	228.9	240.6	249.9	255.1	262.1	274.8
72.5°	154.7	161.4	168.5	176.7	186.6	198.7	209.0	218.3	221.6	227.2	235.4
75°	122.0	125.5	131.3	137.2	144.1	154.5	164.5	166.8	169.7	174.4	180.1
77.5°	92.3	95.4	97.7	101.6	107.2	115.5	120.8	124.2	124.9	126.7	132.4
80°	73.2	75.0	77.3	80.2	82.5	89.5	92.4	95.9	97.0	98.8	101.7
82.5°	53.7	55.4	56.8	59.2	63.0	65.8	68.7	72.2	72.4	73.7	74.3
85°	31.3	31.9	30.8	31.9	32.5	33.7	36.6	39.5	38.9	38.3	40.1
87.5°	15.6	15.3	14.5	15.4	14.1	14.1	13.7	13.7	14.2	14.6	15.2
90°	22.2	20.8	18.7	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3
92.5°	22.2	20.8	18.9	17.1	15.4	13.6	13.5	15.2	16.7	18.3	20.0
95°	22.2	20.8	31.7	42.6	53.6	64.5	70.4	71.3	72.2	73.0	73.9
97.5°	55.6	63.8	85.4	107.1	128.7	150.4	160.5	158.9	157.3	155.8	154.2
100°	182.6	225.5	224.4	223.3	222.1	220.9	219.9	219.0	218.2	217.3	216.5
102.5°	279.7	287.7	287.1	286.4	285.7	285.0	284.0	283.0	281.9	280.8	279.7
105°	386.2	386.2	386.2	386.2	386.2	386.2	385.6	384.5	383.4	382.2	381.1
107.5°	489.0	488.9	488.4	487.8	487.2	486.6	486.3	486.3	486.3	486.3	486.3
110°	556.5	557.3	556.7	556.2	555.6	555.0	554.7	554.7	554.7	554.7	554.7



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	622.6	623.7	623.4	623.0	622.7	622.3	621.8	621.1	620.4	619.7	619.1
115°	722.0	723.2	723.0	722.6	722.4	722.0	721.2	719.8	718.3	716.9	715.5
117.5°	818.4	819.9	818.8	817.7	816.7	815.5	815.0	815.1	815.1	815.2	815.3
120°	879.5	880.0	879.2	878.3	877.4	876.6	876.3	876.6	876.9	877.2	877.4
122.5°	938.6	939.2	938.7	938.3	938.0	937.5	936.8	935.7	934.6	933.5	932.5
125°	1025.4	1026.5	1026.5	1026.5	1026.5	1026.5	1025.5	1023.5	1021.5	1019.4	1017.4
127.5°	1103.6	1104.3	1104.5	1104.7	1104.8	1105.0	1104.3	1102.9	1101.5	1100.0	1098.5
130°	1155.3	1156.2	1155.8	1155.5	1155.3	1154.9	1154.1	1152.7	1151.2	1149.8	1148.3
132.5°	1202.6	1202.8	1203.4	1204.0	1204.7	1205.3	1204.8	1203.2	1201.4	1199.8	1198.1
135°	1273.5	1274.1	1274.6	1275.2	1275.8	1276.3	1275.8	1274.1	1272.4	1270.6	1268.9
137.5°	1338.5	1338.3	1338.9	1339.4	1339.9	1340.4	1340.0	1338.4	1337.0	1335.4	1333.9
140°	1378.4	1377.8	1378.0	1378.4	1378.6	1378.9	1378.8	1378.2	1377.6	1377.1	1376.5
142.5°	1418.3	1418.2	1417.8	1417.4	1417.0	1416.6	1416.2	1415.8	1415.5	1415.1	1414.8
145°	1473.9	1473.7	1473.7	1473.7	1473.7	1473.7	1473.4	1472.8	1472.2	1471.6	1471.1
147.5°	1521.7	1521.4	1521.0	1520.7	1520.4	1520.0	1519.8	1520.0	1520.1	1520.2	1520.4
150°	1552.0	1551.4	1550.8	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4
152.5°	1579.0	1578.4	1577.9	1577.3	1576.7	1576.1	1576.4	1577.7	1579.0	1580.3	1581.5
155°	1615.8	1615.0	1614.4	1613.8	1613.3	1612.7	1613.3	1615.0	1616.7	1618.4	1620.1
157.5°	1646.5	1645.5	1645.5	1645.5	1645.4	1645.3	1645.8	1646.8	1647.9	1648.9	1649.9
160°	1665.3	1664.2	1663.9	1663.6	1663.4	1663.0	1663.8	1665.5	1667.2	1669.0	1670.7
162.5°	1682.4	1680.8	1680.5	1680.2	1679.9	1679.6	1680.3	1682.0	1683.9	1685.6	1687.3
165°	1704.8	1703.1	1702.8	1702.5	1702.2	1701.9	1702.6	1704.3	1706.1	1707.9	1709.6
167.5°	1721.5	1719.4	1719.2	1718.8	1718.6	1718.3	1719.0	1720.8	1722.6	1724.4	1726.1
170°	1730.0	1727.7	1727.4	1727.2	1726.8	1726.6	1727.4	1729.4	1731.5	1733.5	1735.5
172.5°	1737.1	1735.0	1734.5	1734.0	1733.5	1732.9	1733.6	1735.7	1737.7	1739.7	1741.7
175°	1744.3	1742.0	1741.7	1741.4	1741.1	1740.9	1741.5	1743.3	1745.0	1746.7	1748.4
177.5°	1748.0	1746.4	1746.1	1745.9	1745.7	1745.4	1746.0	1747.4	1748.8	1750.2	1751.5
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1422.6	1426.8	1432.8	1439.8	1445.4	1451.4	1454.7	1454.7	1457.5	1463.5	1471.4
5°	1426.7	1441.7	1456.3	1474.9	1489.4	1506.2	1519.1	1531.3	1542.3	1556.3	1570.8
7.5°	1425.5	1450.6	1476.8	1506.1	1538.3	1564.0	1590.4	1611.1	1631.6	1658.3	1679.3
10°	1420.8	1453.4	1488.8	1526.0	1566.7	1602.1	1634.1	1663.2	1691.1	1720.1	1746.3
12.5°	1412.5	1453.9	1497.2	1541.9	1593.2	1633.7	1675.1	1706.0	1738.5	1770.3	1802.5
15°	1399.9	1448.7	1501.1	1563.2	1626.0	1671.3	1712.0	1752.1	1782.3	1818.3	1849.2
17.5°	1374.0	1436.9	1502.7	1570.6	1631.0	1683.6	1726.3	1764.4	1796.6	1836.3	1878.1
20°	1358.7	1426.7	1495.2	1567.9	1625.4	1679.5	1720.7	1760.2	1800.4	1852.0	1903.2
22.5°	1337.3	1409.9	1482.6	1551.6	1612.4	1664.6	1707.2	1755.6	1808.2	1866.9	1928.7
25°	1303.5	1378.5	1450.5	1516.1	1575.5	1628.9	1687.0	1752.1	1816.0	1893.3	1982.2
27.5°	1260.6	1332.8	1397.1	1466.5	1525.4	1593.5	1665.9	1736.6	1828.7	1935.0	2046.0
30°	1228.5	1297.1	1358.1	1423.7	1490.6	1565.6	1646.9	1730.0	1839.9	1964.8	2096.7
32.5°	1191.3	1253.4	1313.9	1377.3	1454.3	1536.7	1623.2	1724.9	1856.1	1998.3	2134.8
35°	1126.8	1182.6	1241.3	1311.6	1393.5	1483.1	1593.5	1717.3	1875.9	2028.7	2151.3
37.5°	1059.1	1103.2	1162.1	1236.3	1325.5	1429.1	1554.4	1704.8	1867.8	2004.8	2057.1
40°	1007.1	1048.4	1110.5	1188.4	1276.7	1390.1	1530.7	1685.2	1849.2	1944.5	1940.3
42.5°	955.5	997.2	1057.0	1135.4	1227.4	1354.3	1499.1	1659.7	1798.0	1834.3	1758.6
45°	876.3	915.2	974.0	1053.0	1151.8	1284.9	1437.1	1591.1	1679.5	1620.7	1470.8
47.5°	795.7	833.4	887.9	965.4	1073.2	1212.5	1356.4	1482.8	1495.2	1369.2	1189.3
50°	742.7	778.1	829.8	912.4	1016.9	1153.0	1291.8	1391.2	1360.4	1206.4	1021.1
52.5°	691.0	725.1	773.6	851.4	958.4	1091.6	1215.6	1293.6	1222.4	1058.6	891.8
55°	614.8	647.4	696.2	767.7	864.7	986.8	1095.5	1123.9	1019.3	854.3	719.5
57.5°	542.4	566.3	614.5	677.7	771.3	878.9	956.7	951.7	836.2	687.6	590.9
60°	494.6	516.0	562.0	620.1	708.9	805.5	860.1	836.8	720.1	597.4	504.4
62.5°	449.9	470.0	508.5	562.0	638.3	722.2	762.0	729.9	619.6	511.9	437.9
65°	382.4	396.9	427.7	477.1	536.9	595.0	630.5	583.4	485.9	404.5	348.7
67.5°	319.3	331.8	359.2	394.7	435.9	476.0	490.5	446.3	370.4	315.6	276.3
70°	278.4	290.0	308.6	341.7	369.0	397.5	404.5	365.0	301.6	259.8	235.4
72.5°	239.3	250.0	266.3	289.6	308.6	324.9	328.2	291.5	243.1	214.2	195.4
75°	182.4	191.7	202.2	210.9	223.2	226.1	224.9	196.4	170.3	151.1	140.6
77.5°	134.1	137.9	144.4	147.8	148.4	148.2	142.2	124.2	110.7	102.9	98.6
80°	103.4	106.3	108.1	109.3	109.9	104.0	97.6	86.6	82.0	77.3	72.1
82.5°	75.1	77.1	78.8	79.0	75.9	71.0	65.1	59.6	56.4	54.1	52.1
85°	40.6	41.2	40.6	37.8	33.7	31.9	30.8	29.6	29.0	28.5	28.5
87.5°	15.2	14.2	12.3	13.3	13.7	13.6	14.0	13.9	13.9	14.2	14.5
90°	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.8	22.2	23.6
92.5°	18.3	16.7	15.2	13.5	13.6	15.4	17.1	18.9	20.8	22.2	23.6
95°	73.0	72.2	71.3	70.4	64.5	53.6	42.6	31.7	20.8	22.2	23.6
97.5°	155.8	157.3	158.9	160.5	150.4	128.7	107.1	85.4	63.8	55.6	47.5
100°	217.3	218.2	219.0	219.9	220.9	222.1	223.3	224.4	225.5	182.6	139.7
102.5°	280.8	281.9	283.0	284.0	285.0	285.7	286.4	287.1	287.7	279.7	271.5
105°	382.2	383.4	384.5	385.6	386.2	386.2	386.2	386.2	386.2	386.2	386.2
107.5°	486.3	486.3	486.3	486.3	486.6	487.2	487.8	488.4	488.9	489.0	489.0
110°	554.7	554.7	554.7	554.7	555.0	555.6	556.2	556.7	557.3	556.5	555.6





TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	619.7	620.4	621.1	621.8	622.3	622.7	623.0	623.4	623.7	622.6	621.5
115°	716.9	718.3	719.8	721.2	722.0	722.4	722.6	723.0	723.2	722.0	720.9
117.5°	815.2	815.1	815.1	815.0	815.5	816.7	817.7	818.8	819.9	818.4	816.9
120°	877.2	876.9	876.6	876.3	876.6	877.4	878.3	879.2	880.0	879.5	878.9
122.5°	933.5	934.6	935.7	936.8	937.5	938.0	938.3	938.7	939.2	938.6	938.0
125°	1019.4	1021.5	1023.5	1025.5	1026.5	1026.5	1026.5	1026.5	1026.5	1025.4	1024.2
127.5°	1100.0	1101.5	1102.9	1104.3	1105.0	1104.8	1104.7	1104.5	1104.3	1103.6	1103.0
130°	1149.8	1151.2	1152.7	1154.1	1154.9	1155.3	1155.5	1155.8	1156.2	1155.3	1154.4
132.5°	1199.8	1201.4	1203.2	1204.8	1205.3	1204.7	1204.0	1203.4	1202.8	1202.6	1202.5
135°	1270.6	1272.4	1274.1	1275.8	1276.3	1275.8	1275.2	1274.6	1274.1	1273.5	1272.9
137.5°	1335.4	1337.0	1338.4	1340.0	1340.4	1339.9	1339.4	1338.9	1338.3	1338.5	1338.6
140°	1377.1	1377.6	1378.2	1378.8	1378.9	1378.6	1378.4	1378.0	1377.8	1378.4	1378.9
142.5°	1415.1	1415.5	1415.8	1416.2	1416.6	1417.0	1417.4	1417.8	1418.2	1418.3	1418.4
145°	1471.6	1472.2	1472.8	1473.4	1473.7	1473.7	1473.7	1473.7	1473.7	1473.9	1474.3
147.5°	1520.2	1520.1	1520.0	1519.8	1520.0	1520.4	1520.7	1521.0	1521.4	1521.7	1522.1
150°	1550.8	1550.3	1549.7	1549.1	1549.1	1549.7	1550.3	1550.8	1551.4	1552.0	1552.6
152.5°	1580.3	1579.0	1577.7	1576.4	1576.1	1576.7	1577.3	1577.9	1578.4	1579.0	1579.6
155°	1618.4	1616.7	1615.0	1613.3	1612.7	1613.3	1613.8	1614.4	1615.0	1615.8	1616.7
157.5°	1648.9	1647.9	1646.8	1645.8	1645.3	1645.4	1645.5	1645.5	1645.5	1646.5	1647.4
160°	1669.0	1667.2	1665.5	1663.8	1663.0	1663.4	1663.6	1663.9	1664.2	1665.3	1666.5
162.5°	1685.6	1683.9	1682.0	1680.3	1679.6	1679.9	1680.2	1680.5	1680.8	1682.4	1684.0
165°	1707.9	1706.1	1704.3	1702.6	1701.9	1702.2	1702.5	1702.8	1703.1	1704.8	1706.5
167.5°	1724.4	1722.6	1720.8	1719.0	1718.3	1718.6	1718.8	1719.2	1719.4	1721.5	1723.5
170°	1733.5	1731.5	1729.4	1727.4	1726.6	1726.8	1727.2	1727.4	1727.7	1730.0	1732.3
172.5°	1739.7	1737.7	1735.7	1733.6	1732.9	1733.5	1734.0	1734.5	1735.0	1737.1	1739.1
175°	1746.7	1745.0	1743.3	1741.5	1740.9	1741.1	1741.4	1741.7	1742.0	1744.3	1746.5
177.5°	1750.2	1748.8	1747.4	1746.0	1745.4	1745.7	1745.9	1746.1	1746.4	1748.0	1749.6
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7	1415.7
2.5°	1477.5	1477.5	1485.4	1484.9	1490.0	1488.2	1489.1
5°	1588.2	1598.1	1606.8	1612.7	1621.3	1623.7	1622.5
7.5°	1703.1	1725.0	1735.7	1750.3	1753.0	1760.7	1759.9
10°	1774.2	1795.7	1812.0	1824.7	1831.1	1839.3	1839.9
12.5°	1830.0	1848.2	1862.6	1874.5	1882.2	1884.8	1886.4
15°	1873.5	1893.9	1910.7	1927.6	1937.5	1945.0	1949.1
17.5°	1917.4	1948.9	1978.6	2001.5	2015.3	2026.9	2026.7
20°	1951.5	1987.4	2024.6	2050.8	2077.5	2089.1	2090.9
22.5°	1987.7	2042.8	2090.7	2131.2	2166.3	2178.4	2183.0
25°	2063.0	2135.0	2208.9	2265.8	2306.4	2330.3	2333.8
27.5°	2154.0	2251.5	2329.2	2381.7	2415.5	2433.2	2437.0
30°	2218.2	2308.3	2378.0	2417.5	2433.2	2435.5	2426.8
32.5°	2247.0	2314.3	2342.2	2339.9	2309.0	2288.6	2280.8
35°	2211.7	2197.8	2129.9	2048.5	1986.3	1946.8	1936.3
37.5°	2012.8	1892.5	1767.5	1644.5	1579.1	1545.8	1488.6
40°	1816.6	1645.2	1515.0	1411.5	1337.7	1278.5	1264.6
42.5°	1595.3	1418.3	1288.1	1199.5	1140.7	1099.9	1082.3
45°	1281.9	1129.7	1022.2	954.2	908.9	879.3	865.9
47.5°	1025.4	907.5	829.1	778.9	744.3	718.5	711.3
50°	884.5	790.3	724.1	681.7	655.5	635.8	627.6
52.5°	768.3	692.2	641.4	606.3	581.6	569.3	562.5
55°	634.0	568.3	531.8	503.9	489.9	480.0	475.4
57.5°	518.5	471.1	444.4	425.1	412.2	405.9	403.6
60°	453.8	416.6	392.3	377.1	368.4	360.3	358.0
62.5°	396.7	367.4	348.5	335.3	326.6	323.1	321.7
65°	319.6	300.4	286.5	278.4	271.4	270.2	269.7
67.5°	254.1	242.8	235.5	227.0	224.5	220.5	219.6
70°	217.3	209.8	201.0	198.2	195.3	191.2	191.7
72.5°	184.3	176.8	170.8	167.0	166.0	164.2	165.7
75°	134.8	132.5	130.2	127.3	126.1	126.1	125.5
77.5°	96.3	94.3	91.7	90.0	89.6	87.1	88.1
80°	69.7	66.8	65.7	66.2	64.5	63.9	63.9
82.5°	51.6	50.5	49.4	49.5	49.2	48.6	49.1
85°	28.5	27.9	27.9	27.3	27.3	26.7	26.7
87.5°	15.2	16.0	15.3	15.0	15.2	15.8	16.4
90°	25.1	26.5	27.6	28.5	29.4	30.2	31.1
92.5°	25.1	26.5	27.4	27.8	28.2	28.7	29.0
95°	25.1	26.5	27.2	27.2	27.2	27.2	27.2
97.5°	39.4	31.3	27.2	27.2	27.2	27.2	27.2
100°	96.8	53.9	31.9	30.7	29.5	28.4	27.2
102.5°	263.4	255.3	241.4	221.8	202.2	182.6	163.1
105°	386.2	386.2	386.1	385.8	385.6	385.2	385.0
107.5°	489.0	489.1	488.7	487.8	487.0	486.1	485.3
110°	554.7	553.9	553.6	553.9	554.1	554.5	554.7



TEST NUMBER: P333716-935

CATALOG NUMBER: S125RDIW-S1090D1560U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	620.4	619.3	618.5	618.2	617.8	617.3	616.9
115°	719.8	718.6	717.2	715.5	713.7	712.0	710.2
117.5°	815.5	813.9	812.8	812.1	811.3	810.5	809.8
120°	878.3	877.8	876.8	875.3	873.8	872.5	871.0
122.5°	937.5	936.9	935.7	934.1	932.4	930.7	929.0
125°	1023.0	1021.9	1020.9	1020.0	1019.2	1018.3	1017.4
127.5°	1102.4	1101.7	1100.4	1098.2	1096.1	1094.0	1091.8
130°	1153.6	1152.7	1151.5	1150.1	1148.7	1147.2	1145.7
132.5°	1202.3	1202.1	1201.3	1199.9	1198.4	1197.0	1195.5
135°	1272.4	1271.8	1270.6	1268.9	1267.1	1265.4	1263.7
137.5°	1338.7	1338.9	1338.2	1336.6	1335.2	1333.6	1332.1
140°	1379.5	1380.1	1379.5	1377.8	1376.1	1374.3	1372.6
142.5°	1418.6	1418.7	1417.9	1416.1	1414.4	1412.6	1410.9
145°	1474.5	1474.8	1474.1	1472.4	1470.7	1469.0	1467.2
147.5°	1522.4	1522.8	1521.9	1519.8	1517.8	1515.7	1513.6
150°	1553.2	1553.8	1552.9	1550.6	1548.3	1546.0	1543.7
152.5°	1580.1	1580.7	1579.9	1577.9	1575.8	1573.7	1571.7
155°	1617.6	1618.4	1617.6	1615.4	1613.1	1610.8	1608.4
157.5°	1648.3	1649.2	1648.6	1646.2	1643.9	1641.6	1639.3
160°	1667.7	1668.8	1668.3	1665.9	1663.6	1661.3	1659.1
162.5°	1685.7	1687.2	1686.8	1684.3	1681.7	1679.2	1676.6
165°	1708.3	1710.0	1709.7	1707.4	1705.1	1702.8	1700.5
167.5°	1725.6	1727.7	1727.4	1724.8	1722.3	1719.7	1717.1
170°	1734.7	1736.9	1736.8	1734.2	1731.6	1729.0	1726.4
172.5°	1741.2	1743.3	1743.0	1740.4	1737.8	1735.3	1732.7
175°	1748.9	1751.2	1751.0	1748.4	1745.8	1743.3	1740.7
177.5°	1751.2	1752.8	1752.7	1750.8	1749.0	1747.1	1745.3
180°	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4	1748.4

(END OF REPORT)