

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333642-830

Luminaire Tested: **S125RDIW-S375D470U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333642-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D470U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3130.1 lumens
Efficiency: N/A
Efficacy: 136.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333642-830

CATALOG NUMBER: S125RDIW-S375D470U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333642-830

CATALOG NUMBER: S125RDIW-S375D470U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	18	16
8	53	41	34	28	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3725	3725	3725
5°	3734	3691	3713
10°	3705	3657	3657
15°	3661	3582	3553
20°	3604	3478	3437
25°	3539	3377	3302
30°	3456	3258	3155
35°	3372	3136	2988
40°	3295	3008	2824
45°	3199	2865	2645
50°	3104	2710	2460
55°	2992	2559	2262
60°	2880	2381	2047
65°	2749	2170	1803
70°	2598	1907	1554
75°	2393	1609	1293
80°	2105	1261	1086
85°	1771	1030	971



TEST NUMBER: P333642-830

CATALOG NUMBER: S125RDIW-S375D470U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	1.7
10°-20°	151.6	4.8
20°-30°	219.8	7.0
30°-40°	250.5	8.0
40°-50°	244.1	7.8
50°-60°	205.5	6.6
60°-70°	144.1	4.6
70°-80°	74.1	2.4
80°-90°	19.9	0.6
90°-100°	20.9	0.7
100°-110°	128.8	4.1
110°-120°	233.6	7.5
120°-130°	299.9	9.6
130°-140°	322.5	10.3
140°-150°	302.7	9.7
150°-160°	244.9	7.8
160°-170°	158.4	5.1
170°-180°	54.6	1.7
0°-30°	425.6	13.6
0°-40°	676.0	21.6
0°-60°	1125.7	36.0
0°-90°	1363.7	43.6
90°-120°	383.4	12.2
90°-150°	1308.5	41.8
90°-180°	1766.0	56.4
0°-180°	3130.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	576	574	569	573	573	55
15°	548	545	536	535	531	154
25°	497	490	474	468	463	228
35°	428	417	398	385	379	268
45°	350	337	314	297	290	270
55°	266	251	227	208	201	238
65°	180	165	142	125	118	178
75°	96	83	64	55	52	101
85°	24	16	14	14	13	27
90°	0	4	7	9	10	2
95°	24	22	7	9	9	31
105°	125	127	127	127	127	133
115°	235	237	238	236	234	233
125°	335	338	338	336	335	299
135°	418	420	419	418	416	322
145°	484	485	485	485	483	303
155°	533	531	531	532	529	245
165°	562	560	560	563	559	159
175°	575	573	573	576	573	55
180°	575	575	575	575	575	



TEST NUMBER: P333642-830

CATALOG NUMBER: S125RDIW-S375D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	577.8	577.6	577.3	577.1	576.8	576.4	575.6	574.8	574.0	573.3	574.0
5°	575.9	575.5	575.1	574.7	574.3	573.6	572.5	571.5	570.4	569.3	570.3
7.5°	570.2	569.9	569.5	569.1	568.7	567.9	566.7	565.3	564.1	562.8	563.5
10°	565.0	564.7	564.4	564.1	563.8	563.0	561.7	560.2	558.9	557.6	557.9
12.5°	559.0	558.6	558.4	558.0	557.6	556.5	554.7	552.9	551.0	549.2	549.4
15°	547.5	547.0	546.4	545.8	545.3	543.9	541.9	539.9	537.8	535.8	535.7
17.5°	534.6	533.7	532.8	531.9	531.0	529.3	526.7	524.1	521.6	519.1	518.6
20°	524.4	523.5	522.5	521.6	520.6	518.6	515.5	512.4	509.3	506.1	505.7
22.5°	513.3	512.4	511.4	510.4	509.4	507.4	504.1	500.9	497.6	494.4	493.4
25°	496.6	495.1	493.7	492.2	490.8	488.2	484.7	481.1	477.5	473.9	472.7
27.5°	477.4	475.7	473.9	472.1	470.3	467.6	463.7	459.9	456.1	452.2	450.4
30°	463.4	461.7	459.8	458.0	456.1	453.2	449.1	445.1	441.0	436.9	434.7
32.5°	449.9	447.7	445.6	443.5	441.3	438.2	434.0	429.9	425.7	421.6	419.1
35°	427.7	425.5	423.1	420.8	418.5	415.1	410.8	406.4	402.1	397.8	394.9
37.5°	406.0	403.2	400.4	397.6	394.7	391.1	386.6	382.1	377.7	373.2	369.8
40°	390.8	387.9	384.9	382.0	379.1	375.3	370.7	366.1	361.4	356.8	353.1
42.5°	374.7	371.7	368.7	365.8	362.8	358.9	354.1	349.3	344.5	339.7	336.2
45°	350.2	347.4	344.6	341.8	339.0	334.9	329.6	324.3	319.0	313.7	309.7
47.5°	324.9	321.9	319.0	315.9	313.0	308.9	303.5	298.1	292.8	287.4	283.4
50°	308.9	305.7	302.5	299.3	296.1	291.7	286.2	280.7	275.1	269.7	265.6
52.5°	291.4	288.1	284.8	281.6	278.3	274.1	268.9	263.6	258.4	253.3	248.9
55°	265.7	262.6	259.5	256.5	253.4	249.1	243.6	238.2	232.8	227.3	223.0
57.5°	239.8	236.5	233.1	229.8	226.5	222.3	217.0	211.8	206.6	201.3	197.1
60°	223.0	219.6	216.2	212.8	209.4	205.2	199.9	194.7	189.5	184.3	180.0
62.5°	205.3	202.0	198.8	195.6	192.3	188.0	182.8	177.5	172.1	166.8	162.9
65°	179.9	176.6	173.3	170.0	166.7	162.5	157.4	152.3	147.1	142.0	138.2
67.5°	154.8	151.5	148.2	144.9	141.6	137.4	132.5	127.6	122.7	117.8	114.2
70°	137.6	134.4	131.1	127.8	124.5	120.5	115.6	110.7	105.9	101.0	98.0
72.5°	120.9	117.7	114.5	111.3	108.1	104.2	99.6	95.1	90.6	86.1	83.3
75°	95.9	92.9	90.0	87.1	84.3	80.8	76.6	72.6	68.5	64.5	62.3
77.5°	70.9	68.6	66.3	63.9	61.6	58.8	55.6	52.3	49.1	45.8	44.3
80°	56.6	54.3	52.0	49.7	47.3	44.9	42.1	39.4	36.7	33.9	33.1
82.5°	42.7	40.6	38.5	36.4	34.3	32.3	30.5	28.7	26.8	24.9	24.5
85°	23.9	22.2	20.5	18.8	17.0	15.8	15.4	14.9	14.4	13.9	13.9
87.5°	8.1	7.7	7.4	7.0	6.5	6.4	6.4	6.5	6.5	6.6	6.7
90°	0.5	1.2	2.0	2.7	3.5	4.1	4.8	5.5	6.1	6.8	7.3
92.5°	6.6	6.0	5.5	5.0	4.4	4.4	5.1	5.7	6.2	6.8	7.3
95°	24.3	24.0	23.8	23.5	23.2	21.2	17.6	14.0	10.5	6.8	7.3
97.5°	50.7	51.3	51.7	52.3	52.8	49.5	42.3	35.3	28.1	21.0	18.3
100°	71.2	71.5	71.8	72.1	72.4	72.7	73.0	73.4	73.8	74.2	60.0
102.5°	92.0	92.4	92.7	93.1	93.5	93.8	94.0	94.2	94.4	94.6	92.0
105°	125.4	125.7	126.1	126.5	126.9	127.1	127.1	127.1	127.1	127.1	127.1
107.5°	159.9	159.9	159.9	159.9	159.9	160.0	160.2	160.4	160.6	160.8	160.9
110°	182.5	182.5	182.5	182.5	182.5	182.6	182.8	182.9	183.1	183.3	183.0



TEST NUMBER: P333642-830

CATALOG NUMBER: S125RDIW-S375D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	203.7	203.9	204.1	204.3	204.5	204.7	204.8	205.0	205.1	205.2	204.8
115°	235.4	235.8	236.3	236.8	237.2	237.5	237.6	237.7	237.8	237.9	237.5
117.5°	268.2	268.2	268.2	268.2	268.2	268.3	268.6	269.0	269.4	269.8	269.3
120°	288.7	288.6	288.5	288.4	288.3	288.4	288.7	289.0	289.3	289.5	289.4
122.5°	306.8	307.1	307.5	307.8	308.2	308.4	308.6	308.7	308.9	309.0	308.8
125°	334.7	335.4	336.0	336.7	337.3	337.7	337.7	337.7	337.7	337.7	337.3
127.5°	361.4	361.9	362.4	362.9	363.4	363.5	363.4	363.4	363.4	363.3	363.1
130°	377.8	378.2	378.7	379.2	379.7	379.9	380.0	380.1	380.2	380.3	380.0
132.5°	394.2	394.7	395.3	395.8	396.3	396.5	396.3	396.2	395.9	395.7	395.7
135°	417.5	418.0	418.6	419.1	419.7	419.9	419.7	419.5	419.3	419.1	419.0
137.5°	438.8	439.3	439.8	440.4	440.8	441.0	440.8	440.6	440.5	440.3	440.4
140°	452.8	453.0	453.2	453.4	453.6	453.6	453.6	453.5	453.4	453.3	453.5
142.5°	465.4	465.6	465.7	465.8	465.9	466.0	466.2	466.3	466.5	466.6	466.6
145°	484.0	484.2	484.4	484.6	484.7	484.8	484.8	484.8	484.8	484.8	484.9
147.5°	500.2	500.1	500.1	500.0	500.0	500.0	500.2	500.3	500.4	500.5	500.6
150°	510.4	510.2	510.0	509.8	509.6	509.6	509.8	510.0	510.2	510.4	510.6
152.5°	520.3	519.9	519.4	519.1	518.6	518.5	518.7	518.9	519.1	519.2	519.4
155°	533.0	532.4	531.9	531.3	530.7	530.6	530.7	530.9	531.1	531.3	531.6
157.5°	542.8	542.4	542.2	541.8	541.4	541.3	541.3	541.3	541.3	541.4	541.7
160°	549.6	549.0	548.5	547.9	547.3	547.1	547.2	547.3	547.4	547.5	547.9
162.5°	555.1	554.5	553.9	553.4	552.8	552.6	552.7	552.8	552.9	553.0	553.5
165°	562.4	561.8	561.3	560.7	560.2	559.9	560.0	560.1	560.2	560.2	560.8
167.5°	567.9	567.3	566.8	566.1	565.5	565.2	565.3	565.4	565.5	565.6	566.4
170°	571.0	570.3	569.6	568.9	568.3	568.0	568.1	568.2	568.3	568.4	569.1
172.5°	573.0	572.3	571.7	571.0	570.3	570.1	570.2	570.4	570.6	570.8	571.5
175°	575.2	574.7	574.1	573.5	573.0	572.7	572.8	572.9	573.0	573.1	573.8
177.5°	576.3	575.8	575.3	574.9	574.4	574.2	574.3	574.4	574.5	574.6	575.0
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2



TEST NUMBER: P333642-830

CATALOG NUMBER: S125RDIW-S375D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	574.8	575.6	576.4	576.7	576.6	576.6	576.5	576.4
5°	571.3	572.2	573.2	573.6	573.4	573.2	573.0	572.8
7.5°	564.1	564.9	565.5	565.7	565.5	565.3	565.1	564.9
10°	558.2	558.5	558.7	558.7	558.5	558.2	557.9	557.6
12.5°	549.6	549.9	550.1	550.0	549.5	549.0	548.7	548.2
15°	535.6	535.5	535.4	534.9	534.0	533.2	532.3	531.4
17.5°	518.1	517.6	517.2	516.5	515.9	515.1	514.3	513.7
20°	505.2	504.7	504.3	503.6	502.7	501.8	501.0	500.1
22.5°	492.4	491.4	490.5	489.7	489.0	488.2	487.6	486.8
25°	471.5	470.1	468.9	467.8	466.7	465.6	464.6	463.4
27.5°	448.7	447.0	445.2	443.8	442.8	441.8	440.7	439.7
30°	432.4	430.3	428.0	426.5	425.6	424.7	423.9	423.0
32.5°	416.7	414.2	411.7	410.0	408.9	407.7	406.6	405.6
35°	392.1	389.3	386.4	384.4	383.0	381.7	380.3	379.0
37.5°	366.4	363.1	359.7	357.3	356.0	354.7	353.4	352.0
40°	349.4	345.7	342.0	339.6	338.5	337.3	336.1	335.0
42.5°	332.6	329.1	325.6	323.0	321.3	319.5	317.8	316.1
45°	305.9	302.0	298.1	295.5	294.1	292.6	291.2	289.6
47.5°	279.5	275.4	271.5	268.6	267.0	265.4	263.8	262.2
50°	261.5	257.4	253.4	250.6	249.2	247.7	246.3	244.8
52.5°	244.5	240.2	235.7	232.8	231.4	230.0	228.5	227.1
55°	218.7	214.3	210.0	207.0	205.5	203.9	202.4	200.9
57.5°	192.8	188.6	184.3	181.4	180.1	178.7	177.4	176.0
60°	175.8	171.4	167.2	164.4	162.9	161.5	160.0	158.5
62.5°	158.9	155.0	151.0	148.4	146.8	145.4	144.0	142.5
65°	134.2	130.4	126.5	123.9	122.4	120.9	119.5	118.0
67.5°	110.7	107.2	103.6	101.2	100.1	99.0	97.7	96.6
70°	95.1	92.1	89.1	87.0	85.8	84.6	83.5	82.3
72.5°	80.5	77.8	75.0	73.2	72.5	71.7	70.9	70.1
75°	60.2	58.1	56.0	54.6	53.9	53.2	52.5	51.8
77.5°	42.9	41.4	39.9	38.8	38.4	37.9	37.3	36.9
80°	32.2	31.4	30.5	30.0	29.8	29.6	29.4	29.2
82.5°	24.1	23.7	23.3	23.0	22.9	22.8	22.7	22.5
85°	13.8	13.7	13.6	13.5	13.4	13.3	13.2	13.1
87.5°	6.8	6.9	7.0	7.0	7.0	7.0	7.0	6.9
90°	7.7	8.2	8.7	9.1	9.4	9.7	10.0	10.3
92.5°	7.7	8.2	8.7	9.0	9.1	9.3	9.4	9.5
95°	7.7	8.2	8.7	9.0	9.0	9.0	9.0	9.0
97.5°	15.6	13.0	10.3	9.0	9.0	9.0	9.0	9.0
100°	46.0	31.9	17.7	10.5	10.1	9.7	9.3	9.0
102.5°	89.4	86.6	84.0	79.5	73.0	66.5	60.0	53.6
105°	127.1	127.1	127.1	127.1	127.0	126.9	126.8	126.7
107.5°	160.9	160.9	160.9	160.8	160.5	160.2	159.9	159.7
110°	182.8	182.5	182.2	182.1	182.2	182.3	182.4	182.5



TEST NUMBER: P333642-830

CATALOG NUMBER: S125RDIW-S375D470U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	204.4	204.1	203.8	203.5	203.4	203.2	203.1	202.9
115°	237.1	236.8	236.4	235.9	235.4	234.8	234.2	233.7
117.5°	268.7	268.2	267.8	267.4	267.1	266.9	266.6	266.5
120°	289.2	289.0	288.8	288.4	287.9	287.5	287.0	286.5
122.5°	308.6	308.4	308.2	307.8	307.3	306.7	306.2	305.7
125°	337.0	336.6	336.2	335.8	335.5	335.3	335.0	334.7
127.5°	362.9	362.7	362.5	362.0	361.3	360.6	359.9	359.2
130°	379.8	379.5	379.2	378.8	378.3	377.9	377.4	376.9
132.5°	395.6	395.5	395.5	395.2	394.7	394.3	393.8	393.3
135°	418.8	418.6	418.4	418.0	417.5	416.9	416.3	415.8
137.5°	440.4	440.5	440.5	440.3	439.7	439.2	438.8	438.3
140°	453.6	453.8	454.0	453.8	453.3	452.7	452.1	451.6
142.5°	466.7	466.7	466.7	466.5	465.9	465.3	464.8	464.2
145°	485.0	485.1	485.2	484.9	484.4	483.8	483.2	482.7
147.5°	500.8	500.9	501.0	500.7	500.0	499.4	498.6	497.9
150°	510.8	511.0	511.1	510.9	510.1	509.3	508.6	507.8
152.5°	519.6	519.8	520.0	519.8	519.1	518.4	517.7	517.1
155°	531.9	532.2	532.4	532.2	531.4	530.7	529.9	529.1
157.5°	542.0	542.2	542.5	542.3	541.6	540.8	540.1	539.3
160°	548.3	548.7	549.0	548.8	548.1	547.3	546.6	545.8
162.5°	554.0	554.6	555.1	555.0	554.1	553.3	552.4	551.6
165°	561.5	562.0	562.6	562.5	561.8	560.9	560.2	559.4
167.5°	567.0	567.7	568.4	568.4	567.4	566.6	565.7	564.9
170°	569.9	570.7	571.5	571.4	570.5	569.7	568.8	568.0
172.5°	572.1	572.8	573.5	573.4	572.6	571.7	570.9	570.0
175°	574.6	575.3	576.1	576.1	575.2	574.4	573.5	572.7
177.5°	575.6	576.1	576.6	576.6	576.0	575.4	574.8	574.2
180°	575.2	575.2	575.2	575.2	575.2	575.2	575.2	575.2

(END OF REPORT)