

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333646-830

Luminaire Tested: **S125RDIW-S375D770U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333646-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D770U830-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4257.6 lumens
Efficiency: N/A
Efficacy: 140.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333646-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333646-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	27
2	86	78	73	68	77	71	66	62	57	53	50	43	41	39	31	30	29	23
3	78	69	62	56	70	62	56	52	50	46	42	38	36	33	28	26	24	20
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	25	23	21	17
5	66	54	47	41	59	49	43	37	40	35	31	31	27	25	22	20	18	15
6	60	49	41	35	54	44	37	32	36	31	27	28	24	22	20	18	16	13
7	56	44	36	31	50	40	33	28	32	27	24	25	22	19	19	16	14	12
8	52	40	32	27	46	36	30	25	29	24	21	23	20	17	17	15	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3725	3725	3725
5°	3734	3691	3713
10°	3705	3657	3657
15°	3661	3582	3553
20°	3604	3478	3437
25°	3539	3377	3302
30°	3456	3258	3155
35°	3372	3136	2988
40°	3295	3008	2824
45°	3199	2865	2645
50°	3104	2710	2460
55°	2992	2559	2262
60°	2880	2381	2047
65°	2749	2170	1803
70°	2598	1907	1554
75°	2393	1609	1293
80°	2105	1261	1086
85°	1771	1030	971



TEST NUMBER: P333646-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	1.3
10°-20°	151.6	3.6
20°-30°	219.8	5.2
30°-40°	250.5	5.9
40°-50°	244.1	5.7
50°-60°	205.5	4.8
60°-70°	144.1	3.4
70°-80°	74.1	1.7
80°-90°	20.7	0.5
90°-100°	34.2	0.8
100°-110°	211.0	5.0
110°-120°	382.7	9.0
120°-130°	491.1	11.5
130°-140°	528.2	12.4
140°-150°	495.8	11.6
150°-160°	401.1	9.4
160°-170°	259.4	6.1
170°-180°	89.5	2.1
0°-30°	425.6	10.0
0°-40°	676.0	15.9
0°-60°	1125.7	26.4
0°-90°	1364.5	32.0
90°-120°	627.9	14.7
90°-150°	2143.1	50.3
90°-180°	2893.0	67.9
0°-180°	4257.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	576	574	569	573	573	55
15°	548	545	536	535	531	154
25°	497	490	474	468	463	228
35°	428	417	398	385	379	268
45°	350	337	314	297	290	270
55°	266	251	227	208	201	238
65°	180	165	142	125	118	178
75°	96	83	64	55	52	101
85°	24	16	14	14	13	27
90°	1	6	11	15	17	3
95°	40	36	11	14	15	51
105°	205	208	208	208	208	218
115°	386	389	390	387	383	382
125°	548	553	553	550	548	489
135°	684	688	686	685	681	527
145°	793	794	794	794	791	496
155°	873	869	870	872	867	402
165°	921	917	918	921	916	260
175°	942	938	939	944	938	90
180°	942	942	942	942	942	



TEST NUMBER: P333646-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	577.8	577.6	577.3	577.1	576.8	576.4	575.6	574.8	574.0	573.3	574.0
5°	575.9	575.5	575.1	574.7	574.3	573.6	572.5	571.5	570.4	569.3	570.3
7.5°	570.2	569.9	569.5	569.1	568.7	567.9	566.7	565.3	564.1	562.8	563.5
10°	565.0	564.7	564.4	564.1	563.8	563.0	561.7	560.2	558.9	557.6	557.9
12.5°	559.0	558.6	558.4	558.0	557.6	556.5	554.7	552.9	551.0	549.2	549.4
15°	547.5	547.0	546.4	545.8	545.3	543.9	541.9	539.9	537.8	535.8	535.7
17.5°	534.6	533.7	532.8	531.9	531.0	529.3	526.7	524.1	521.6	519.1	518.6
20°	524.4	523.5	522.5	521.6	520.6	518.6	515.5	512.4	509.3	506.1	505.7
22.5°	513.3	512.4	511.4	510.4	509.4	507.4	504.1	500.9	497.6	494.4	493.4
25°	496.6	495.1	493.7	492.2	490.8	488.2	484.7	481.1	477.5	473.9	472.7
27.5°	477.4	475.7	473.9	472.1	470.3	467.6	463.7	459.9	456.1	452.2	450.4
30°	463.4	461.7	459.8	458.0	456.1	453.2	449.1	445.1	441.0	436.9	434.7
32.5°	449.9	447.7	445.6	443.5	441.3	438.2	434.0	429.9	425.7	421.6	419.1
35°	427.7	425.5	423.1	420.8	418.5	415.1	410.8	406.4	402.1	397.8	394.9
37.5°	406.0	403.2	400.4	397.6	394.7	391.1	386.6	382.1	377.7	373.2	369.8
40°	390.8	387.9	384.9	382.0	379.1	375.3	370.7	366.1	361.4	356.8	353.1
42.5°	374.7	371.7	368.7	365.8	362.8	358.9	354.1	349.3	344.5	339.7	336.2
45°	350.2	347.4	344.6	341.8	339.0	334.9	329.6	324.3	319.0	313.7	309.7
47.5°	324.9	321.9	319.0	315.9	313.0	308.9	303.5	298.1	292.8	287.4	283.4
50°	308.9	305.7	302.5	299.3	296.1	291.7	286.2	280.7	275.1	269.7	265.6
52.5°	291.4	288.1	284.8	281.6	278.3	274.1	268.9	263.6	258.4	253.3	248.9
55°	265.7	262.6	259.5	256.5	253.4	249.1	243.6	238.2	232.8	227.3	223.0
57.5°	239.8	236.5	233.1	229.8	226.5	222.3	217.0	211.8	206.6	201.3	197.1
60°	223.0	219.6	216.2	212.8	209.4	205.2	199.9	194.7	189.5	184.3	180.0
62.5°	205.3	202.0	198.8	195.6	192.3	188.0	182.8	177.5	172.1	166.8	162.9
65°	179.9	176.6	173.3	170.0	166.7	162.5	157.4	152.3	147.1	142.0	138.2
67.5°	154.8	151.5	148.2	144.9	141.6	137.4	132.5	127.6	122.7	117.8	114.2
70°	137.6	134.4	131.1	127.8	124.5	120.5	115.6	110.7	105.9	101.0	98.0
72.5°	120.9	117.7	114.5	111.3	108.1	104.2	99.6	95.1	90.6	86.1	83.3
75°	95.9	92.9	90.0	87.1	84.3	80.8	76.6	72.6	68.5	64.5	62.3
77.5°	70.9	68.6	66.3	63.9	61.6	58.8	55.6	52.3	49.1	45.8	44.3
80°	56.6	54.3	52.0	49.7	47.3	44.9	42.1	39.4	36.7	33.9	33.1
82.5°	42.7	40.6	38.5	36.4	34.3	32.3	30.5	28.7	26.8	24.9	24.5
85°	23.9	22.2	20.5	18.8	17.0	15.8	15.4	14.9	14.4	13.9	13.9
87.5°	8.2	7.8	7.5	7.3	7.0	6.9	7.1	7.2	7.4	7.4	7.6
90°	0.7	2.0	3.2	4.4	5.7	6.8	7.9	9.0	10.1	11.2	12.0
92.5°	10.7	9.9	9.0	8.1	7.3	7.4	8.3	9.2	10.2	11.2	12.0
95°	39.8	39.3	38.8	38.5	38.0	34.8	28.8	23.0	17.1	11.2	12.0
97.5°	83.1	84.0	84.8	85.6	86.4	81.1	69.4	57.7	46.0	34.4	30.0
100°	116.6	117.1	117.5	118.0	118.5	119.0	119.7	120.3	120.9	121.5	98.4
102.5°	150.7	151.3	151.9	152.5	153.1	153.5	153.9	154.3	154.7	155.0	150.7
105°	205.3	205.9	206.6	207.2	207.8	208.1	208.1	208.1	208.1	208.1	208.1
107.5°	262.0	262.0	262.0	262.0	262.0	262.2	262.5	262.8	263.2	263.4	263.4
110°	298.9	298.9	298.9	298.9	298.9	299.1	299.4	299.7	300.0	300.3	299.8



TEST NUMBER: P333646-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	333.6	333.9	334.3	334.7	335.1	335.4	335.5	335.7	335.9	336.1	335.5
115°	385.5	386.3	387.1	387.9	388.6	389.1	389.3	389.4	389.6	389.7	389.1
117.5°	439.3	439.2	439.2	439.2	439.1	439.4	440.1	440.6	441.2	441.8	441.0
120°	472.8	472.7	472.5	472.3	472.2	472.3	472.8	473.3	473.7	474.2	473.9
122.5°	502.4	503.0	503.6	504.2	504.8	505.2	505.4	505.6	505.9	506.1	505.8
125°	548.3	549.3	550.4	551.5	552.6	553.1	553.1	553.1	553.1	553.1	552.5
127.5°	591.9	592.8	593.5	594.3	595.0	595.4	595.3	595.2	595.1	595.0	594.7
130°	618.8	619.5	620.3	621.1	621.9	622.4	622.5	622.6	622.8	622.9	622.5
132.5°	645.5	646.5	647.4	648.3	649.2	649.5	649.1	648.8	648.5	648.1	648.0
135°	683.7	684.7	685.6	686.5	687.5	687.8	687.5	687.1	686.8	686.5	686.2
137.5°	718.8	719.6	720.4	721.2	722.0	722.3	722.0	721.7	721.4	721.1	721.2
140°	741.7	742.0	742.3	742.6	742.9	743.0	742.8	742.7	742.5	742.3	742.7
142.5°	762.3	762.5	762.7	762.9	763.1	763.3	763.6	763.7	763.9	764.2	764.2
145°	792.7	793.0	793.3	793.6	793.9	794.1	794.1	794.1	794.1	794.1	794.2
147.5°	819.3	819.2	819.1	819.1	819.0	819.1	819.3	819.4	819.5	819.7	819.9
150°	835.9	835.7	835.4	835.0	834.7	834.7	835.0	835.4	835.7	835.9	836.3
152.5°	852.2	851.5	850.8	850.2	849.4	849.2	849.6	849.9	850.2	850.5	850.8
155°	873.0	872.0	871.1	870.2	869.3	868.9	869.3	869.6	869.9	870.2	870.6
157.5°	889.0	888.5	888.0	887.4	886.8	886.6	886.6	886.6	886.6	886.6	887.2
160°	900.2	899.3	898.3	897.4	896.5	896.1	896.3	896.5	896.5	896.7	897.4
162.5°	909.2	908.2	907.3	906.3	905.4	905.0	905.2	905.4	905.5	905.7	906.5
165°	921.1	920.2	919.4	918.4	917.5	917.1	917.2	917.4	917.6	917.7	918.6
167.5°	930.1	929.2	928.2	927.3	926.2	925.9	926.0	926.1	926.3	926.5	927.6
170°	935.2	934.1	932.9	931.9	930.8	930.3	930.5	930.7	930.8	930.9	932.2
172.5°	938.5	937.5	936.3	935.2	934.2	933.8	934.1	934.3	934.6	934.9	935.9
175°	942.2	941.2	940.3	939.3	938.4	938.0	938.2	938.3	938.5	938.7	939.9
177.5°	943.8	943.0	942.4	941.6	940.8	940.5	940.7	940.8	940.8	941.0	941.9
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2



TEST NUMBER: P333646-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	576.7	576.7	576.7	576.7	576.7	576.7	576.7	576.7
2.5°	574.8	575.6	576.4	576.7	576.6	576.6	576.5	576.4
5°	571.3	572.2	573.2	573.6	573.4	573.2	573.0	572.8
7.5°	564.1	564.9	565.5	565.7	565.5	565.3	565.1	564.9
10°	558.2	558.5	558.7	558.7	558.5	558.2	557.9	557.6
12.5°	549.6	549.9	550.1	550.0	549.5	549.0	548.7	548.2
15°	535.6	535.5	535.4	534.9	534.0	533.2	532.3	531.4
17.5°	518.1	517.6	517.2	516.5	515.9	515.1	514.3	513.7
20°	505.2	504.7	504.3	503.6	502.7	501.8	501.0	500.1
22.5°	492.4	491.4	490.5	489.7	489.0	488.2	487.6	486.8
25°	471.5	470.1	468.9	467.8	466.7	465.6	464.6	463.4
27.5°	448.7	447.0	445.2	443.8	442.8	441.8	440.7	439.7
30°	432.4	430.3	428.0	426.5	425.6	424.7	423.9	423.0
32.5°	416.7	414.2	411.7	410.0	408.9	407.7	406.6	405.6
35°	392.1	389.3	386.4	384.4	383.0	381.7	380.3	379.0
37.5°	366.4	363.1	359.7	357.3	356.0	354.7	353.4	352.0
40°	349.4	345.7	342.0	339.6	338.5	337.3	336.1	335.0
42.5°	332.6	329.1	325.6	323.0	321.3	319.5	317.8	316.1
45°	305.9	302.0	298.1	295.5	294.1	292.6	291.2	289.6
47.5°	279.5	275.4	271.5	268.6	267.0	265.4	263.8	262.2
50°	261.5	257.4	253.4	250.6	249.2	247.7	246.3	244.8
52.5°	244.5	240.2	235.7	232.8	231.4	230.0	228.5	227.1
55°	218.7	214.3	210.0	207.0	205.5	203.9	202.4	200.9
57.5°	192.8	188.6	184.3	181.4	180.1	178.7	177.4	176.0
60°	175.8	171.4	167.2	164.4	162.9	161.5	160.0	158.5
62.5°	158.9	155.0	151.0	148.4	146.8	145.4	144.0	142.5
65°	134.2	130.4	126.5	123.9	122.4	120.9	119.5	118.0
67.5°	110.7	107.2	103.6	101.2	100.1	99.0	97.7	96.6
70°	95.1	92.1	89.1	87.0	85.8	84.6	83.5	82.3
72.5°	80.5	77.8	75.0	73.2	72.5	71.7	70.9	70.1
75°	60.2	58.1	56.0	54.6	53.9	53.2	52.5	51.8
77.5°	42.9	41.4	39.9	38.8	38.4	37.9	37.3	36.9
80°	32.2	31.4	30.5	30.0	29.8	29.6	29.4	29.2
82.5°	24.1	23.7	23.3	23.0	22.9	22.8	22.7	22.5
85°	13.8	13.7	13.6	13.5	13.4	13.3	13.2	13.1
87.5°	7.7	7.9	8.1	8.2	8.2	8.2	8.2	8.2
90°	12.7	13.5	14.2	14.9	15.4	15.8	16.3	16.8
92.5°	12.7	13.5	14.2	14.8	15.0	15.2	15.5	15.6
95°	12.7	13.5	14.2	14.7	14.7	14.7	14.7	14.7
97.5°	25.6	21.2	16.9	14.7	14.7	14.7	14.7	14.7
100°	75.3	52.1	29.0	17.2	16.5	15.9	15.3	14.7
102.5°	146.3	141.9	137.5	130.1	119.5	109.0	98.4	87.8
105°	208.1	208.1	208.1	208.0	207.9	207.7	207.5	207.5
107.5°	263.5	263.5	263.5	263.3	262.9	262.4	261.9	261.5
110°	299.4	298.9	298.4	298.3	298.4	298.6	298.8	298.9



TEST NUMBER: P333646-830

CATALOG NUMBER: S125RDIW-S375D770U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	334.9	334.3	333.7	333.3	333.1	332.9	332.6	332.4
115°	388.4	387.9	387.2	386.4	385.5	384.6	383.6	382.7
117.5°	440.2	439.4	438.6	438.0	437.5	437.2	436.8	436.4
120°	473.6	473.3	473.0	472.4	471.6	470.9	470.1	469.3
122.5°	505.4	505.1	504.8	504.2	503.3	502.4	501.5	500.6
125°	551.9	551.3	550.6	550.1	549.6	549.1	548.7	548.3
127.5°	594.4	594.0	593.7	593.0	591.7	590.6	589.5	588.3
130°	622.1	621.6	621.1	620.5	619.7	619.0	618.1	617.4
132.5°	647.9	647.8	647.7	647.3	646.5	645.7	645.0	644.2
135°	685.9	685.6	685.3	684.7	683.7	682.8	681.8	680.9
137.5°	721.3	721.3	721.4	721.0	720.2	719.4	718.6	717.8
140°	743.0	743.3	743.7	743.3	742.3	741.5	740.6	739.6
142.5°	764.3	764.4	764.4	764.0	763.1	762.1	761.2	760.3
145°	794.4	794.6	794.7	794.3	793.3	792.4	791.5	790.6
147.5°	820.1	820.3	820.5	820.0	819.0	817.8	816.7	815.6
150°	836.6	836.9	837.3	836.8	835.5	834.2	833.0	831.8
152.5°	851.1	851.4	851.8	851.3	850.2	849.1	848.0	846.9
155°	871.1	871.6	872.0	871.7	870.4	869.2	868.0	866.7
157.5°	887.7	888.2	888.6	888.3	887.0	885.8	884.6	883.4
160°	898.0	898.6	899.2	898.9	897.7	896.5	895.2	893.9
162.5°	907.4	908.2	909.2	908.9	907.6	906.2	904.8	903.4
165°	919.5	920.5	921.4	921.2	920.0	918.8	917.6	916.2
167.5°	928.7	929.8	930.9	930.9	929.4	928.0	926.6	925.2
170°	933.4	934.7	935.9	935.9	934.4	933.0	931.6	930.3
172.5°	937.1	938.2	939.3	939.1	937.8	936.4	935.0	933.6
175°	941.1	942.4	943.6	943.5	942.2	940.8	939.3	937.9
177.5°	942.7	943.6	944.5	944.4	943.4	942.4	941.4	940.5
180°	942.2	942.2	942.2	942.2	942.2	942.2	942.2	942.2

(END OF REPORT)